

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333494-935

Luminaire Tested: **S125RDIP-S375D365U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333494-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D365U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2336.7 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333494-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333494-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	53	52	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	56	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3402	3402	3402
5°	3411	3371	3392
10°	3385	3341	3341
15°	3344	3273	3245
20°	3293	3178	3140
25°	3233	3085	3017
30°	3157	2976	2882
35°	3080	2864	2730
40°	3010	2748	2580
45°	2922	2617	2417
50°	2834	2475	2247
55°	2733	2339	2066
60°	2631	2174	1870
65°	2512	1984	1647
70°	2374	1743	1420
75°	2186	1470	1183
80°	1923	1153	993
85°	1623	941	889



TEST NUMBER: P333494-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.5	2.1
10°-20°	138.4	5.9
20°-30°	200.8	8.6
30°-40°	228.8	9.8
40°-50°	223.0	9.5
50°-60°	187.7	8.0
60°-70°	131.6	5.6
70°-80°	67.6	2.9
80°-90°	17.9	0.8
90°-100°	26.2	1.1
100°-110°	77.3	3.3
110°-120°	131.0	5.6
120°-130°	172.4	7.4
130°-140°	193.2	8.3
140°-150°	189.3	8.1
150°-160°	159.0	6.8
160°-170°	105.7	4.5
170°-180°	37.0	1.6
0°-30°	388.7	16.6
0°-40°	617.6	26.4
0°-60°	1028.3	44.0
0°-90°	1245.5	53.3
90°-120°	234.5	10.0
90°-150°	789.5	33.8
90°-180°	1091.0	46.7
0°-180°	2336.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	523	50
15°	500	498	490	489	485	141
25°	454	447	433	428	423	209
35°	391	381	363	352	346	245
45°	320	308	286	271	265	247
55°	243	230	208	190	184	217
65°	164	150	130	114	108	163
75°	88	75	59	50	47	93
85°	22	15	13	12	12	25
90°	0	3	5	6	7	2
95°	20	21	23	26	26	21
105°	69	71	73	74	76	74
115°	131	132	133	133	132	130
125°	191	193	194	193	193	171
135°	249	251	251	251	250	192
145°	302	303	304	304	303	188
155°	345	345	345	346	345	159
165°	375	375	375	376	374	106
175°	390	389	389	390	389	37
180°	391	391	391	391	391	



TEST NUMBER: P333494-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	527.8	527.6	527.4	527.2	526.9	526.5	525.8	525.0	524.3	523.7	524.3
5°	526.1	525.7	525.4	525.0	524.6	524.0	523.0	522.0	521.1	520.0	521.0
7.5°	520.9	520.6	520.2	519.9	519.5	518.8	517.6	516.4	515.3	514.1	514.7
10°	516.1	515.8	515.6	515.3	515.1	514.3	513.1	511.8	510.6	509.4	509.6
12.5°	510.7	510.3	510.1	509.7	509.4	508.3	506.7	505.1	503.3	501.7	501.9
15°	500.2	499.6	499.1	498.6	498.1	496.9	495.0	493.2	491.3	489.5	489.4
17.5°	488.4	487.5	486.7	485.9	485.1	483.5	481.1	478.8	476.5	474.2	473.7
20°	479.1	478.2	477.3	476.5	475.5	473.7	470.9	468.0	465.2	462.4	461.9
22.5°	468.9	468.0	467.2	466.2	465.4	463.5	460.5	457.5	454.5	451.6	450.7
25°	453.7	452.3	451.0	449.6	448.3	446.0	442.7	439.5	436.2	432.9	431.8
27.5°	436.1	434.5	432.9	431.3	429.6	427.1	423.6	420.1	416.6	413.1	411.5
30°	423.4	421.7	420.0	418.4	416.6	414.0	410.3	406.6	402.9	399.1	397.1
32.5°	411.0	409.0	407.1	405.1	403.1	400.3	396.5	392.7	388.9	385.1	382.9
35°	390.7	388.7	386.5	384.4	382.3	379.2	375.2	371.3	367.3	363.3	360.8
37.5°	370.9	368.3	365.8	363.2	360.6	357.2	353.2	349.0	345.0	340.9	337.8
40°	357.0	354.3	351.6	349.0	346.3	342.9	338.6	334.4	330.1	325.9	322.5
42.5°	342.2	339.6	336.8	334.2	331.4	327.9	323.5	319.1	314.7	310.3	307.1
45°	319.9	317.4	314.8	312.2	309.7	305.9	301.1	296.3	291.4	286.5	282.9
47.5°	296.8	294.0	291.4	288.6	285.9	282.1	277.2	272.3	267.4	262.5	258.9
50°	282.1	279.2	276.3	273.4	270.4	266.5	261.4	256.4	251.3	246.3	242.6
52.5°	266.2	263.2	260.2	257.3	254.3	250.4	245.6	240.8	236.1	231.4	227.4
55°	242.7	239.9	237.0	234.3	231.4	227.6	222.6	217.6	212.7	207.7	203.7
57.5°	219.0	216.0	212.9	209.9	206.9	203.0	198.2	193.5	188.7	183.9	180.0
60°	203.7	200.6	197.5	194.4	191.3	187.4	182.6	177.9	173.1	168.3	164.5
62.5°	187.5	184.5	181.6	178.7	175.6	171.8	166.9	162.1	157.2	152.4	148.8
65°	164.4	161.4	158.3	155.3	152.3	148.4	143.8	139.1	134.4	129.8	126.2
67.5°	141.4	138.4	135.3	132.3	129.3	125.5	121.1	116.6	112.1	107.6	104.4
70°	125.7	122.8	119.8	116.8	113.7	110.0	105.6	101.2	96.8	92.3	89.5
72.5°	110.5	107.5	104.6	101.7	98.8	95.1	91.0	86.9	82.7	78.6	76.1
75°	87.6	84.9	82.2	79.6	77.0	73.8	70.0	66.3	62.6	58.9	56.9
77.5°	64.7	62.7	60.5	58.4	56.3	53.7	50.8	47.8	44.9	41.8	40.5
80°	51.7	49.6	47.5	45.4	43.2	41.0	38.5	36.0	33.5	31.0	30.2
82.5°	39.0	37.1	35.2	33.2	31.3	29.5	27.9	26.2	24.5	22.7	22.4
85°	21.9	20.3	18.7	17.1	15.5	14.5	14.0	13.6	13.2	12.7	12.7
87.5°	7.4	7.0	6.6	6.2	5.9	5.7	5.7	5.7	5.7	5.8	5.9
90°	0.3	0.9	1.4	1.9	2.5	3.0	3.4	4.0	4.4	4.9	5.2
92.5°	7.4	7.7	8.1	8.5	8.9	9.4	9.9	10.5	11.1	11.7	12.1
95°	19.8	19.9	20.1	20.1	20.3	20.8	21.4	22.0	22.7	23.4	23.9
97.5°	32.9	32.9	33.0	33.1	33.1	33.6	34.5	35.5	36.3	37.3	37.8
100°	42.6	42.6	42.6	42.6	42.6	43.0	43.9	44.8	45.7	46.6	47.2
102.5°	53.0	53.4	53.6	53.9	54.2	54.5	54.9	55.4	55.9	56.3	57.0
105°	69.4	69.7	70.1	70.4	70.8	71.1	71.5	71.9	72.3	72.8	73.1
107.5°	87.4	87.7	88.1	88.4	88.8	89.1	89.4	89.7	90.0	90.3	90.5
110°	99.8	100.1	100.5	100.8	101.2	101.4	101.6	101.9	102.0	102.3	102.5



TEST NUMBER: P333494-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	112.4	112.6	112.8	113.0	113.1	113.4	113.7	113.9	114.2	114.4	114.5
115°	131.1	131.4	131.7	132.0	132.2	132.4	132.6	132.7	132.9	133.0	132.9
117.5°	149.9	150.0	150.2	150.2	150.4	150.5	150.7	150.8	150.8	151.0	151.0
120°	161.6	162.0	162.3	162.6	162.9	163.2	163.2	163.2	163.3	163.4	163.4
122.5°	174.3	174.4	174.5	174.6	174.7	174.9	175.0	175.2	175.4	175.6	175.6
125°	191.4	191.8	192.3	192.6	193.0	193.3	193.4	193.4	193.5	193.6	193.4
127.5°	209.7	209.9	210.2	210.3	210.6	210.8	210.9	210.9	211.0	211.0	211.0
130°	220.6	220.9	221.3	221.6	222.0	222.2	222.3	222.5	222.7	222.7	222.7
132.5°	231.6	232.1	232.7	233.2	233.8	234.1	234.0	234.0	234.0	233.9	233.8
135°	248.9	249.3	249.8	250.1	250.6	250.8	250.9	250.9	251.0	251.1	251.1
137.5°	265.3	265.6	266.0	266.4	266.8	267.1	267.3	267.3	267.5	267.7	267.8
140°	275.7	276.0	276.4	276.7	277.1	277.3	277.5	277.8	277.9	278.1	278.3
142.5°	286.2	286.5	286.7	287.1	287.3	287.6	287.8	288.1	288.3	288.6	288.7
145°	301.6	301.9	302.1	302.4	302.6	302.9	303.1	303.3	303.5	303.7	303.7
147.5°	315.8	316.0	316.1	316.2	316.4	316.6	316.8	316.9	317.0	317.2	317.4
150°	325.3	325.3	325.2	325.1	325.0	325.1	325.4	325.7	326.0	326.2	326.2
152.5°	333.1	333.2	333.3	333.4	333.5	333.6	333.7	333.8	333.9	334.0	334.2
155°	345.1	345.1	345.1	345.1	345.1	345.1	345.2	345.3	345.3	345.4	345.7
157.5°	355.8	355.7	355.5	355.3	355.2	355.2	355.2	355.3	355.3	355.4	355.7
160°	362.1	362.0	361.7	361.5	361.4	361.3	361.4	361.4	361.4	361.5	361.8
162.5°	367.7	367.6	367.5	367.3	367.1	367.0	367.0	367.1	367.1	367.1	367.5
165°	375.2	375.1	375.0	374.8	374.7	374.6	374.7	374.8	374.9	374.9	375.2
167.5°	381.5	381.3	381.0	380.7	380.5	380.3	380.3	380.3	380.3	380.3	380.7
170°	385.0	384.7	384.4	384.2	383.8	383.7	383.7	383.7	383.7	383.7	384.2
172.5°	387.4	387.1	386.8	386.6	386.3	386.2	386.2	386.2	386.2	386.2	386.6
175°	390.1	389.9	389.6	389.3	389.1	388.9	388.9	388.9	388.9	388.9	389.3
177.5°	391.5	391.3	391.1	390.9	390.6	390.5	390.5	390.5	390.4	390.3	390.6
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1



TEST NUMBER: P333494-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	525.0	525.8	526.5	526.8	526.8	526.7	526.6	526.5
5°	521.9	522.7	523.6	524.0	523.8	523.6	523.4	523.2
7.5°	515.3	516.0	516.6	516.8	516.6	516.4	516.3	516.0
10°	509.9	510.1	510.4	510.4	510.1	509.9	509.6	509.4
12.5°	502.0	502.3	502.5	502.4	502.0	501.5	501.2	500.8
15°	489.2	489.1	489.0	488.6	487.8	487.1	486.3	485.4
17.5°	473.3	472.9	472.4	471.8	471.2	470.5	469.8	469.2
20°	461.5	461.1	460.6	460.0	459.2	458.4	457.6	456.8
22.5°	449.8	448.9	448.1	447.3	446.7	446.0	445.4	444.7
25°	430.7	429.5	428.3	427.3	426.3	425.3	424.4	423.4
27.5°	409.9	408.3	406.7	405.4	404.5	403.6	402.6	401.7
30°	395.0	393.0	391.0	389.6	388.7	388.0	387.2	386.4
32.5°	380.6	378.4	376.1	374.5	373.5	372.5	371.4	370.5
35°	358.2	355.6	353.0	351.1	349.9	348.7	347.4	346.2
37.5°	334.7	331.7	328.6	326.4	325.2	324.0	322.8	321.6
40°	319.2	315.8	312.5	310.2	309.2	308.2	307.0	306.0
42.5°	303.8	300.7	297.4	295.1	293.5	291.9	290.3	288.8
45°	279.4	275.9	272.3	269.9	268.6	267.3	266.0	264.6
47.5°	255.3	251.6	248.0	245.4	243.9	242.5	241.0	239.5
50°	238.8	235.1	231.4	228.9	227.6	226.3	225.0	223.6
52.5°	223.3	219.4	215.3	212.7	211.4	210.1	208.7	207.4
55°	199.8	195.8	191.8	189.1	187.7	186.2	184.9	183.5
57.5°	176.2	172.3	168.3	165.7	164.5	163.2	162.0	160.7
60°	160.6	156.6	152.7	150.2	148.8	147.5	146.2	144.8
62.5°	145.2	141.5	137.9	135.5	134.1	132.9	131.6	130.2
65°	122.6	119.1	115.5	113.1	111.8	110.5	109.2	107.8
67.5°	101.1	97.9	94.6	92.5	91.4	90.4	89.3	88.3
70°	86.9	84.1	81.4	79.5	78.4	77.3	76.3	75.2
72.5°	73.5	71.0	68.5	66.9	66.2	65.5	64.7	64.1
75°	55.0	53.0	51.1	49.9	49.2	48.6	48.0	47.4
77.5°	39.2	37.8	36.4	35.5	35.0	34.6	34.1	33.7
80°	29.4	28.7	27.9	27.4	27.2	27.0	26.9	26.7
82.5°	22.0	21.6	21.3	21.0	20.9	20.8	20.8	20.6
85°	12.6	12.5	12.4	12.3	12.2	12.1	12.1	12.0
87.5°	5.9	5.9	6.0	6.0	6.0	5.9	5.9	5.9
90°	5.5	5.9	6.2	6.5	6.7	6.9	7.1	7.3
92.5°	12.6	13.0	13.4	13.8	13.9	14.0	14.2	14.4
95°	24.4	24.9	25.3	25.7	25.7	25.9	26.0	26.2
97.5°	38.2	38.7	39.1	39.3	39.4	39.5	39.6	39.7
100°	47.8	48.4	49.0	49.3	49.5	49.7	49.8	49.9
102.5°	57.6	58.3	59.0	59.4	59.6	59.8	59.9	60.1
105°	73.5	74.0	74.4	74.6	74.8	75.1	75.3	75.5
107.5°	90.7	90.9	91.1	91.3	91.2	91.2	91.2	91.2
110°	102.6	102.9	103.1	103.1	103.1	103.0	102.9	102.9



TEST NUMBER: P333494-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	114.6	114.7	114.8	114.8	114.7	114.5	114.4	114.3
115°	132.9	132.8	132.7	132.7	132.6	132.5	132.4	132.3
117.5°	151.1	151.2	151.2	151.1	150.8	150.6	150.3	150.0
120°	163.4	163.4	163.4	163.2	163.0	162.7	162.5	162.2
122.5°	175.5	175.4	175.4	175.2	175.0	174.8	174.6	174.4
125°	193.3	193.1	193.0	192.9	192.9	192.8	192.7	192.6
127.5°	210.9	210.9	210.8	210.7	210.6	210.4	210.3	210.2
130°	222.7	222.6	222.5	222.4	222.2	222.1	222.0	221.9
132.5°	233.8	233.8	233.7	233.6	233.3	233.2	233.0	232.8
135°	251.1	251.1	251.1	250.9	250.6	250.4	250.1	249.9
137.5°	267.9	267.9	268.0	267.9	267.5	267.2	266.8	266.5
140°	278.4	278.5	278.7	278.6	278.3	277.9	277.6	277.2
142.5°	288.8	288.9	289.0	288.8	288.4	288.1	287.8	287.5
145°	303.7	303.7	303.7	303.6	303.4	303.2	303.0	302.8
147.5°	317.5	317.7	317.9	317.7	317.3	316.8	316.3	315.9
150°	326.2	326.2	326.2	326.1	326.1	325.9	325.7	325.6
152.5°	334.3	334.5	334.7	334.6	334.4	334.2	333.9	333.6
155°	345.9	346.2	346.5	346.5	346.1	345.8	345.4	345.1
157.5°	355.9	356.3	356.5	356.5	356.0	355.5	355.1	354.6
160°	362.1	362.3	362.6	362.6	362.2	361.9	361.5	361.2
162.5°	367.7	368.1	368.4	368.4	368.0	367.6	367.2	366.8
165°	375.5	375.7	376.0	375.9	375.5	375.1	374.7	374.3
167.5°	381.2	381.5	381.9	381.9	381.5	381.1	380.6	380.3
170°	384.5	385.0	385.4	385.3	384.9	384.4	383.9	383.4
172.5°	387.0	387.4	387.8	387.8	387.4	386.9	386.5	386.1
175°	389.7	390.1	390.5	390.5	390.0	389.5	389.1	388.6
177.5°	391.0	391.3	391.6	391.6	391.2	390.8	390.5	390.0
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1

(END OF REPORT)