

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333212-830

Luminaire Tested: **S125DIP-S850D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333212-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D365U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4415.2 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333212-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333212-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55	51
3	85	75	68	62	81	72	65	59	65	60	55	59	54	51	53	50	47	43
4	78	67	59	52	74	64	56	50	58	52	47	52	48	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	46	41	47	42	38	43	38	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28
7	61	49	40	35	58	47	39	33	43	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	33	28	25	22
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7991	7991	7991
5°	8009	7933	7983
10°	7960	7877	7922
15°	7874	7782	7815
20°	7750	7649	7663
25°	7617	7492	7485
30°	7454	7322	7285
35°	7278	7139	7039
40°	7098	6940	6842
45°	6902	6760	6625
50°	6688	6540	6344
55°	6481	6293	6117
60°	6234	6044	5829
65°	5938	5744	5550
70°	5655	5399	5214
75°	5153	4983	4811
80°	4590	4515	4407
85°	3987	4068	3838



TEST NUMBER: P333212-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	2.6
10°-20°	329.6	7.5
20°-30°	486.6	11.0
30°-40°	567.8	12.9
40°-50°	570.3	12.9
50°-60°	500.6	11.3
60°-70°	373.0	8.4
70°-80°	213.3	4.8
80°-90°	63.0	1.4
90°-100°	28.7	0.6
100°-110°	84.7	1.9
110°-120°	143.4	3.2
120°-130°	188.7	4.3
130°-140°	211.5	4.8
140°-150°	207.3	4.7
150°-160°	174.1	3.9
160°-170°	115.7	2.6
170°-180°	40.5	0.9
0°-30°	932.8	21.1
0°-40°	1500.6	34.0
0°-60°	2571.4	58.2
0°-90°	3220.7	72.9
90°-120°	256.8	5.8
90°-150°	864.2	19.6
90°-180°	1195.0	27.1
0°-180°	4415.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1237	1237	1237	1237	1237	
5°	1235	1233	1224	1232	1231	117
15°	1178	1174	1164	1169	1169	332
25°	1069	1064	1051	1053	1050	492
35°	923	919	906	900	893	577
45°	756	751	740	729	725	582
55°	576	572	559	550	543	514
65°	389	386	376	367	363	386
75°	206	204	200	197	193	220
85°	54	55	55	54	52	60
90°	0	3	5	7	8	4
95°	22	22	26	28	29	23
105°	76	78	80	82	83	81
115°	144	145	146	145	145	142
125°	210	211	212	211	211	188
135°	272	274	275	275	274	210
145°	330	331	332	332	332	206
155°	378	378	378	379	378	174
165°	411	410	410	412	410	116
175°	427	426	426	427	425	41
180°	428	428	428	428	428	



TEST NUMBER: P333212-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1240.5	1239.9	1239.4	1238.9	1238.3	1237.2	1235.5	1233.8	1232.0	1230.3	1232.0
5°	1235.4	1234.9	1234.4	1234.1	1233.6	1232.3	1230.1	1227.9	1225.8	1223.6	1225.6
7.5°	1224.0	1223.6	1223.1	1222.7	1222.3	1220.9	1218.4	1216.1	1213.7	1211.3	1213.1
10°	1213.8	1213.4	1213.0	1212.5	1212.1	1210.7	1208.2	1205.9	1203.5	1201.1	1202.9
12.5°	1201.3	1200.5	1199.8	1198.9	1198.2	1196.7	1194.5	1192.2	1190.0	1187.8	1189.2
15°	1177.6	1177.0	1176.3	1175.6	1175.0	1173.5	1171.1	1168.7	1166.3	1163.9	1165.0
17.5°	1150.4	1149.4	1148.5	1147.5	1146.6	1144.8	1142.4	1139.9	1137.4	1134.9	1136.2
20°	1127.7	1127.3	1126.8	1126.3	1126.0	1124.3	1121.4	1118.6	1115.8	1113.0	1114.6
22.5°	1104.9	1104.2	1103.4	1102.6	1101.8	1100.1	1097.5	1094.8	1092.1	1089.5	1090.5
25°	1068.9	1067.9	1066.8	1065.6	1064.6	1062.6	1059.8	1057.0	1054.1	1051.3	1051.8
27.5°	1026.8	1026.2	1025.6	1024.9	1024.3	1022.5	1019.5	1016.6	1013.7	1010.8	1010.9
30°	999.5	998.8	998.2	997.5	996.8	994.9	991.6	988.4	985.1	981.8	981.4
32.5°	969.7	968.7	967.7	966.7	965.7	963.7	960.8	957.9	955.0	952.1	951.3
35°	923.1	922.2	921.3	920.5	919.6	917.7	914.6	911.5	908.5	905.5	904.4
37.5°	874.8	873.6	872.5	871.5	870.3	868.4	865.5	862.6	859.8	857.0	855.3
40°	841.9	840.7	839.7	838.6	837.4	835.5	832.4	829.3	826.3	823.2	821.3
42.5°	806.6	805.7	804.7	803.9	803.0	801.0	798.0	794.8	791.8	788.8	787.0
45°	755.7	754.8	753.9	753.1	752.2	750.5	747.9	745.3	742.6	740.1	737.4
47.5°	700.9	701.0	701.0	701.0	701.1	699.6	696.4	693.2	690.1	687.0	684.3
50°	665.6	665.0	664.3	663.6	663.1	661.4	658.8	656.2	653.6	650.9	648.1
52.5°	629.6	629.1	628.7	628.2	627.7	626.0	623.3	620.5	617.7	614.9	612.5
55°	575.6	575.0	574.3	573.6	573.0	571.1	568.1	565.1	561.9	558.9	556.9
57.5°	518.6	518.3	517.9	517.6	517.3	515.8	513.2	510.7	508.0	505.5	502.9
60°	482.6	481.7	480.9	479.9	479.1	477.5	475.0	472.7	470.3	467.9	465.7
62.5°	445.0	444.3	443.7	442.9	442.2	440.8	438.8	436.8	434.7	432.6	430.4
65°	388.6	388.1	387.8	387.3	386.9	385.5	383.0	380.7	378.2	375.9	373.9
67.5°	334.0	333.1	332.2	331.2	330.4	328.9	327.3	325.5	323.7	321.9	320.2
70°	299.5	298.4	297.4	296.2	295.2	293.7	291.7	289.7	287.8	285.9	284.6
72.5°	261.9	261.2	260.4	259.8	259.0	258.0	256.7	255.4	254.2	253.0	251.5
75°	206.5	206.1	205.7	205.3	204.8	204.1	202.9	201.9	200.8	199.7	199.1
77.5°	155.4	155.2	155.1	155.0	154.8	154.4	153.7	153.2	152.5	151.9	151.6
80°	123.4	123.4	123.4	123.4	123.4	123.1	122.7	122.2	121.8	121.4	121.2
82.5°	95.1	94.8	94.4	94.1	93.8	93.5	93.4	93.4	93.3	93.2	92.8
85°	53.8	54.1	54.3	54.5	54.7	54.9	54.9	54.9	54.9	54.9	54.6
87.5°	21.2	21.3	21.5	21.6	21.7	21.7	21.7	21.6	21.5	21.4	21.5
90°	0.4	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7
92.5°	8.1	8.5	8.9	9.3	9.7	10.3	10.8	11.5	12.2	12.8	13.3
95°	21.7	21.8	22.0	22.1	22.2	22.7	23.5	24.1	24.9	25.6	26.2
97.5°	36.0	36.0	36.1	36.2	36.2	36.8	37.8	38.8	39.8	40.8	41.4
100°	46.7	46.7	46.7	46.7	46.7	47.1	48.1	49.0	50.0	51.0	51.7
102.5°	58.1	58.4	58.7	59.0	59.3	59.7	60.1	60.6	61.2	61.6	62.4
105°	76.0	76.3	76.7	77.1	77.5	77.9	78.3	78.7	79.2	79.6	80.0
107.5°	95.7	96.0	96.4	96.8	97.2	97.6	97.8	98.2	98.5	98.9	99.1
110°	109.2	109.6	110.0	110.4	110.7	111.0	111.2	111.5	111.7	112.0	112.2



TEST NUMBER: P333212-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.1	123.3	123.5	123.7	123.9	124.1	124.4	124.7	125.0	125.3	125.4
115°	143.5	143.8	144.2	144.5	144.8	145.0	145.2	145.2	145.4	145.6	145.5
117.5°	164.1	164.2	164.4	164.5	164.7	164.8	164.9	165.0	165.1	165.3	165.3
120°	176.9	177.3	177.7	178.0	178.3	178.6	178.7	178.7	178.8	178.9	178.9
122.5°	190.8	190.9	191.1	191.1	191.2	191.4	191.6	191.8	192.0	192.2	192.2
125°	209.5	210.0	210.5	210.8	211.3	211.6	211.7	211.7	211.8	211.9	211.7
127.5°	229.5	229.8	230.1	230.3	230.5	230.7	230.8	230.9	231.0	231.0	231.0
130°	241.5	241.9	242.2	242.6	243.0	243.3	243.4	243.6	243.7	243.8	243.7
132.5°	253.5	254.1	254.8	255.3	255.9	256.3	256.2	256.2	256.2	256.1	256.0
135°	272.5	273.0	273.4	273.8	274.3	274.6	274.7	274.7	274.8	274.8	274.8
137.5°	290.4	290.8	291.2	291.6	292.1	292.4	292.6	292.7	292.8	293.0	293.1
140°	301.8	302.2	302.6	302.9	303.3	303.6	303.8	304.1	304.3	304.4	304.6
142.5°	313.3	313.6	313.9	314.2	314.5	314.8	315.1	315.4	315.7	315.9	316.0
145°	330.2	330.5	330.7	331.0	331.3	331.6	331.8	332.1	332.2	332.4	332.4
147.5°	345.7	345.9	346.0	346.2	346.4	346.6	346.8	346.9	347.0	347.2	347.4
150°	356.1	356.1	356.0	355.9	355.8	355.9	356.2	356.6	356.8	357.1	357.1
152.5°	364.7	364.8	364.9	365.0	365.0	365.1	365.3	365.4	365.5	365.6	365.8
155°	377.8	377.8	377.8	377.8	377.8	377.8	377.9	378.0	378.1	378.1	378.4
157.5°	389.5	389.4	389.2	389.0	388.9	388.8	388.9	389.0	389.0	389.1	389.4
160°	396.4	396.2	396.0	395.8	395.6	395.5	395.6	395.6	395.7	395.8	396.1
162.5°	402.6	402.4	402.3	402.1	401.9	401.8	401.8	401.9	401.9	401.9	402.3
165°	410.8	410.6	410.5	410.3	410.2	410.1	410.2	410.3	410.4	410.4	410.8
167.5°	417.6	417.4	417.1	416.8	416.5	416.3	416.3	416.3	416.3	416.3	416.8
170°	421.4	421.1	420.8	420.6	420.2	420.1	420.1	420.1	420.1	420.1	420.6
172.5°	424.0	423.8	423.5	423.2	422.9	422.7	422.7	422.7	422.7	422.7	423.2
175°	427.1	426.8	426.5	426.2	425.9	425.7	425.7	425.7	425.7	425.7	426.2
177.5°	428.6	428.4	428.1	427.9	427.6	427.5	427.4	427.4	427.3	427.3	427.6
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333212-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1233.8	1235.5	1237.2	1238.0	1237.8	1237.7	1237.5	1237.3
5°	1227.6	1229.5	1231.4	1232.3	1232.1	1231.9	1231.6	1231.4
7.5°	1215.1	1217.0	1218.9	1219.7	1219.6	1219.4	1219.1	1218.9
10°	1204.6	1206.4	1208.1	1208.8	1208.6	1208.3	1208.2	1208.0
12.5°	1190.5	1191.9	1193.4	1194.0	1194.0	1193.9	1193.9	1193.8
15°	1166.1	1167.2	1168.3	1168.8	1168.8	1168.8	1168.8	1168.8
17.5°	1137.6	1139.0	1140.3	1140.5	1139.3	1138.3	1137.2	1136.1
20°	1116.1	1117.6	1119.1	1119.3	1118.2	1117.1	1116.1	1114.9
22.5°	1091.5	1092.5	1093.5	1093.6	1092.9	1092.1	1091.4	1090.7
25°	1052.2	1052.6	1053.1	1052.9	1052.3	1051.7	1051.0	1050.4
27.5°	1011.0	1011.1	1011.2	1010.9	1010.2	1009.6	1008.9	1008.2
30°	981.0	980.5	980.1	979.6	978.9	978.3	977.6	976.9
32.5°	950.5	949.7	949.0	947.9	946.8	945.6	944.4	943.3
35°	903.3	902.2	901.2	899.8	898.0	896.3	894.5	892.8
37.5°	853.7	852.1	850.5	849.1	848.2	847.2	846.2	845.2
40°	819.4	817.4	815.4	814.1	813.4	812.8	812.2	811.5
42.5°	785.2	783.4	781.7	780.2	779.3	778.3	777.2	776.3
45°	734.8	732.2	729.6	727.9	727.4	726.7	726.0	725.4
47.5°	681.6	679.0	676.4	674.3	672.8	671.3	669.7	668.2
50°	645.3	642.4	639.6	637.4	635.9	634.4	632.9	631.4
52.5°	610.0	607.5	605.0	602.9	601.2	599.6	597.9	596.2
55°	555.1	553.1	551.1	549.4	547.8	546.3	544.8	543.3
57.5°	500.5	497.9	495.4	493.7	492.9	492.1	491.3	490.4
60°	463.5	461.4	459.2	457.3	455.8	454.3	452.8	451.3
62.5°	428.0	425.7	423.3	421.5	420.4	419.1	418.0	416.8
65°	372.0	370.0	368.1	366.6	365.8	365.0	364.0	363.2
67.5°	318.6	316.9	315.3	314.1	313.7	313.1	312.5	312.1
70°	283.2	281.9	280.6	279.6	278.6	277.8	276.9	276.1
72.5°	250.0	248.5	247.0	245.8	245.0	244.1	243.3	242.3
75°	198.4	197.7	197.1	196.3	195.5	194.5	193.7	192.8
77.5°	151.2	150.7	150.3	149.9	149.2	148.6	148.1	147.4
80°	120.9	120.7	120.6	120.2	119.8	119.3	118.9	118.5
82.5°	92.4	92.0	91.6	91.4	91.3	91.2	91.1	91.0
85°	54.4	54.2	53.9	53.6	53.2	52.8	52.3	51.8
87.5°	21.6	21.7	21.7	21.6	21.3	21.0	20.7	20.4
90°	6.0	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	13.8	14.2	14.7	15.1	15.3	15.4	15.6	15.7
95°	26.7	27.2	27.7	28.1	28.2	28.4	28.5	28.7
97.5°	41.8	42.3	42.8	43.1	43.2	43.3	43.4	43.5
100°	52.3	53.0	53.6	54.0	54.2	54.4	54.5	54.7
102.5°	63.1	63.8	64.6	65.0	65.2	65.4	65.6	65.8
105°	80.5	81.0	81.4	81.7	81.9	82.2	82.4	82.7
107.5°	99.3	99.5	99.7	99.9	99.8	99.8	99.8	99.8
110°	112.4	112.6	112.8	112.9	112.8	112.7	112.6	112.6



TEST NUMBER: P333212-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	125.5	125.5	125.6	125.6	125.5	125.4	125.3	125.2
115°	145.4	145.3	145.2	145.2	145.2	145.1	145.0	144.9
117.5°	165.4	165.5	165.5	165.4	165.1	164.9	164.6	164.2
120°	178.9	178.9	178.9	178.7	178.4	178.1	177.9	177.6
122.5°	192.1	192.0	192.0	191.8	191.6	191.3	191.1	190.9
125°	211.6	211.4	211.3	211.1	211.1	211.0	210.9	210.8
127.5°	230.9	230.8	230.7	230.6	230.5	230.4	230.2	230.1
130°	243.7	243.6	243.6	243.5	243.3	243.2	243.0	242.9
132.5°	256.0	255.9	255.8	255.7	255.4	255.2	255.1	254.9
135°	274.8	274.8	274.8	274.7	274.4	274.1	273.8	273.5
137.5°	293.2	293.3	293.4	293.2	292.8	292.5	292.1	291.7
140°	304.8	304.9	305.1	305.0	304.6	304.3	303.9	303.5
142.5°	316.1	316.2	316.3	316.1	315.8	315.4	315.1	314.7
145°	332.4	332.4	332.4	332.3	332.2	331.9	331.7	331.5
147.5°	347.6	347.8	348.0	347.8	347.3	346.8	346.3	345.8
150°	357.1	357.1	357.1	357.0	356.9	356.8	356.6	356.5
152.5°	366.0	366.2	366.4	366.3	366.1	365.8	365.5	365.2
155°	378.7	379.0	379.3	379.3	378.9	378.5	378.1	377.8
157.5°	389.6	390.0	390.3	390.2	389.7	389.2	388.7	388.2
160°	396.3	396.6	396.9	396.9	396.5	396.2	395.8	395.4
162.5°	402.6	402.9	403.3	403.3	402.8	402.4	402.0	401.5
165°	411.0	411.3	411.6	411.5	411.0	410.7	410.2	409.7
167.5°	417.3	417.6	418.1	418.1	417.6	417.2	416.7	416.3
170°	420.9	421.4	421.9	421.8	421.3	420.8	420.3	419.7
172.5°	423.7	424.0	424.5	424.5	424.0	423.6	423.1	422.6
175°	426.6	427.1	427.5	427.4	427.0	426.4	425.9	425.4
177.5°	428.0	428.4	428.7	428.7	428.3	427.8	427.4	427.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1

(END OF REPORT)