

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333495-935

Luminaire Tested: **S125RDIP-S375D365U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333495-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D365U935-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2377.3 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333495-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333495-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	71	83	77	71	67	66	62	58	55	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	36	40	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	23	20	18	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3402	3402	3402
5°	3411	3371	3392
10°	3385	3341	3341
15°	3344	3273	3245
20°	3293	3178	3140
25°	3233	3085	3017
30°	3157	2976	2882
35°	3080	2864	2730
40°	3010	2748	2580
45°	2922	2617	2417
50°	2834	2475	2247
55°	2733	2339	2066
60°	2631	2174	1870
65°	2512	1984	1647
70°	2374	1743	1420
75°	2186	1470	1183
80°	1923	1153	993
85°	1623	941	889



TEST NUMBER: P333495-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.5	2.1
10°-20°	138.4	5.8
20°-30°	200.8	8.4
30°-40°	228.8	9.6
40°-50°	223.0	9.4
50°-60°	187.7	7.9
60°-70°	131.6	5.5
70°-80°	67.6	2.8
80°-90°	17.9	0.8
90°-100°	109.4	4.6
100°-110°	235.2	9.9
110°-120°	220.7	9.3
120°-130°	178.9	7.5
130°-140°	143.5	6.0
140°-150°	108.3	4.6
150°-160°	76.2	3.2
160°-170°	44.9	1.9
170°-180°	14.6	0.6
0°-30°	388.7	16.4
0°-40°	617.6	26.0
0°-60°	1028.3	43.3
0°-90°	1245.5	52.4
90°-120°	565.3	23.8
90°-150°	996.0	41.9
90°-180°	1132.0	47.6
0°-180°	2377.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	523	50
15°	500	498	490	489	485	141
25°	454	447	433	428	423	209
35°	391	381	363	352	346	245
45°	320	308	286	271	265	247
55°	243	230	208	190	184	217
65°	164	150	130	114	108	163
75°	88	75	59	50	47	93
85°	22	15	13	12	12	25
90°	0	3	5	6	7	2
95°	10	30	270	122	72	11
105°	34	48	221	434	403	36
115°	62	74	177	382	449	60
125°	85	100	170	304	354	76
135°	100	120	169	255	294	77
145°	116	133	169	211	232	73
155°	133	143	165	186	194	61
165°	145	149	158	168	170	41
175°	151	151	152	154	153	14
180°	151	151	151	151	151	



TEST NUMBER: P333495-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	527.8	527.6	527.4	527.2	526.9	526.5	525.8	525.0	524.3	523.7	524.3
5°	526.1	525.7	525.4	525.0	524.6	524.0	523.0	522.0	521.1	520.0	521.0
7.5°	520.9	520.6	520.2	519.9	519.5	518.8	517.6	516.4	515.3	514.1	514.7
10°	516.1	515.8	515.6	515.3	515.1	514.3	513.1	511.8	510.6	509.4	509.6
12.5°	510.7	510.3	510.1	509.7	509.4	508.3	506.7	505.1	503.3	501.7	501.9
15°	500.2	499.6	499.1	498.6	498.1	496.9	495.0	493.2	491.3	489.5	489.4
17.5°	488.4	487.5	486.7	485.9	485.1	483.5	481.1	478.8	476.5	474.2	473.7
20°	479.1	478.2	477.3	476.5	475.5	473.7	470.9	468.0	465.2	462.4	461.9
22.5°	468.9	468.0	467.2	466.2	465.4	463.5	460.5	457.5	454.5	451.6	450.7
25°	453.7	452.3	451.0	449.6	448.3	446.0	442.7	439.5	436.2	432.9	431.8
27.5°	436.1	434.5	432.9	431.3	429.6	427.1	423.6	420.1	416.6	413.1	411.5
30°	423.4	421.7	420.0	418.4	416.6	414.0	410.3	406.6	402.9	399.1	397.1
32.5°	411.0	409.0	407.1	405.1	403.1	400.3	396.5	392.7	388.9	385.1	382.9
35°	390.7	388.7	386.5	384.4	382.3	379.2	375.2	371.3	367.3	363.3	360.8
37.5°	370.9	368.3	365.8	363.2	360.6	357.2	353.2	349.0	345.0	340.9	337.8
40°	357.0	354.3	351.6	349.0	346.3	342.9	338.6	334.4	330.1	325.9	322.5
42.5°	342.2	339.6	336.8	334.2	331.4	327.9	323.5	319.1	314.7	310.3	307.1
45°	319.9	317.4	314.8	312.2	309.7	305.9	301.1	296.3	291.4	286.5	282.9
47.5°	296.8	294.0	291.4	288.6	285.9	282.1	277.2	272.3	267.4	262.5	258.9
50°	282.1	279.2	276.3	273.4	270.4	266.5	261.4	256.4	251.3	246.3	242.6
52.5°	266.2	263.2	260.2	257.3	254.3	250.4	245.6	240.8	236.1	231.4	227.4
55°	242.7	239.9	237.0	234.3	231.4	227.6	222.6	217.6	212.7	207.7	203.7
57.5°	219.0	216.0	212.9	209.9	206.9	203.0	198.2	193.5	188.7	183.9	180.0
60°	203.7	200.6	197.5	194.4	191.3	187.4	182.6	177.9	173.1	168.3	164.5
62.5°	187.5	184.5	181.6	178.7	175.6	171.8	166.9	162.1	157.2	152.4	148.8
65°	164.4	161.4	158.3	155.3	152.3	148.4	143.8	139.1	134.4	129.8	126.2
67.5°	141.4	138.4	135.3	132.3	129.3	125.5	121.1	116.6	112.1	107.6	104.4
70°	125.7	122.8	119.8	116.8	113.7	110.0	105.6	101.2	96.8	92.3	89.5
72.5°	110.5	107.5	104.6	101.7	98.8	95.1	91.0	86.9	82.7	78.6	76.1
75°	87.6	84.9	82.2	79.6	77.0	73.8	70.0	66.3	62.6	58.9	56.9
77.5°	64.7	62.7	60.5	58.4	56.3	53.7	50.8	47.8	44.9	41.8	40.5
80°	51.7	49.6	47.5	45.4	43.2	41.0	38.5	36.0	33.5	31.0	30.2
82.5°	39.0	37.1	35.2	33.2	31.3	29.5	27.9	26.2	24.5	22.7	22.4
85°	21.9	20.3	18.7	17.1	15.5	14.5	14.0	13.6	13.2	12.7	12.7
87.5°	7.4	7.0	6.5	6.2	5.9	5.7	5.7	5.7	5.7	5.8	5.8
90°	0.3	0.6	1.2	1.8	2.4	3.0	3.4	4.0	4.2	4.9	5.2
92.5°	3.7	4.5	7.1	10.8	16.1	25.0	41.6	69.4	99.7	98.1	79.4
95°	10.1	10.3	12.7	16.1	22.8	36.5	69.1	136.0	220.0	269.6	263.8
97.5°	16.7	17.0	18.8	22.1	28.2	38.0	59.5	108.6	196.5	287.9	333.8
100°	21.3	21.9	23.2	26.4	32.3	41.4	59.1	98.6	175.3	274.7	350.9
102.5°	26.4	26.8	27.7	31.3	36.7	45.5	61.2	94.5	159.2	251.7	340.6
105°	34.4	34.4	35.9	38.9	43.8	52.3	65.7	92.8	143.6	220.6	308.0
107.5°	42.2	42.8	44.3	46.8	51.8	59.5	72.4	95.6	137.1	199.2	274.6
110°	47.8	48.4	49.6	52.3	56.9	64.8	77.3	98.3	135.1	189.2	255.6



TEST NUMBER: P333495-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	53.4	54.0	54.9	57.7	62.3	69.9	81.9	101.7	135.1	183.4	241.5
115°	61.5	62.1	63.0	65.7	70.3	77.9	89.2	106.8	136.0	177.1	226.1
117.5°	68.8	69.7	70.7	73.4	78.6	85.9	96.6	112.6	138.0	174.0	216.9
120°	73.6	74.6	75.8	78.5	83.7	91.3	101.9	116.6	140.0	172.5	211.8
122.5°	78.8	79.4	80.4	83.2	88.8	96.4	107.0	120.9	141.6	171.3	207.4
125°	85.2	85.8	87.3	90.1	95.8	103.8	113.8	126.9	144.6	169.8	201.5
127.5°	90.2	91.2	93.1	96.6	102.7	110.6	120.3	132.3	147.7	169.1	196.0
130°	93.4	94.4	96.8	100.7	107.1	115.0	124.4	136.0	149.7	168.6	192.3
132.5°	95.8	97.0	100.0	104.4	111.0	118.9	128.4	139.2	151.9	168.6	189.4
135°	99.8	101.0	104.7	109.5	116.0	124.2	133.5	143.6	154.9	168.6	185.9
137.5°	104.8	105.7	109.1	114.0	120.3	128.7	137.3	146.9	157.6	168.9	182.8
140°	107.7	108.7	112.3	117.2	123.0	131.1	140.0	149.1	158.9	169.2	181.3
142.5°	111.2	111.8	115.2	120.1	125.6	133.4	141.6	150.3	159.5	169.4	180.1
145°	116.2	116.8	119.9	124.2	129.7	136.6	144.6	152.1	160.3	169.2	178.3
147.5°	121.6	121.9	124.6	128.5	133.3	139.4	146.4	153.3	160.7	168.4	176.4
150°	124.8	125.4	127.5	131.5	135.7	140.9	147.6	153.9	160.7	167.6	175.0
152.5°	128.2	128.5	130.4	133.9	137.9	142.6	148.8	154.5	160.4	166.7	173.2
155°	132.7	132.7	134.5	137.5	140.6	144.8	150.0	154.9	159.7	165.0	170.4
157.5°	136.7	136.6	138.1	140.7	143.4	146.6	151.0	155.2	158.9	163.1	167.7
160°	139.4	139.1	140.3	142.4	144.8	147.6	151.5	155.2	158.3	161.9	165.6
162.5°	141.5	141.3	142.5	144.4	146.3	148.5	152.1	155.0	157.5	160.4	163.6
165°	144.8	144.2	145.2	146.6	147.9	149.7	152.1	154.5	156.4	158.3	160.7
167.5°	147.1	146.7	147.3	148.1	149.0	150.2	152.1	153.9	154.7	156.1	157.8
170°	148.5	148.2	148.5	149.1	149.7	150.6	152.1	153.3	153.9	154.9	156.1
172.5°	149.5	149.0	149.2	149.8	150.2	150.6	151.9	152.9	153.0	153.4	154.4
175°	150.6	150.0	150.3	150.6	150.6	150.6	151.5	152.1	151.9	151.9	152.1
177.5°	151.2	150.7	150.7	150.9	150.7	150.7	151.2	151.4	150.9	150.9	151.2
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9



TEST NUMBER: P333495-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	525.0	525.8	526.5	526.8	526.8	526.7	526.6	526.5
5°	521.9	522.7	523.6	524.0	523.8	523.6	523.4	523.2
7.5°	515.3	516.0	516.6	516.8	516.6	516.4	516.3	516.0
10°	509.9	510.1	510.4	510.4	510.1	509.9	509.6	509.4
12.5°	502.0	502.3	502.5	502.4	502.0	501.5	501.2	500.8
15°	489.2	489.1	489.0	488.6	487.8	487.1	486.3	485.4
17.5°	473.3	472.9	472.4	471.8	471.2	470.5	469.8	469.2
20°	461.5	461.1	460.6	460.0	459.2	458.4	457.6	456.8
22.5°	449.8	448.9	448.1	447.3	446.7	446.0	445.4	444.7
25°	430.7	429.5	428.3	427.3	426.3	425.3	424.4	423.4
27.5°	409.9	408.3	406.7	405.4	404.5	403.6	402.6	401.7
30°	395.0	393.0	391.0	389.6	388.7	388.0	387.2	386.4
32.5°	380.6	378.4	376.1	374.5	373.5	372.5	371.4	370.5
35°	358.2	355.6	353.0	351.1	349.9	348.7	347.4	346.2
37.5°	334.7	331.7	328.6	326.4	325.2	324.0	322.8	321.6
40°	319.2	315.8	312.5	310.2	309.2	308.2	307.0	306.0
42.5°	303.8	300.7	297.4	295.1	293.5	291.9	290.3	288.8
45°	279.4	275.9	272.3	269.9	268.6	267.3	266.0	264.6
47.5°	255.3	251.6	248.0	245.4	243.9	242.5	241.0	239.5
50°	238.8	235.1	231.4	228.9	227.6	226.3	225.0	223.6
52.5°	223.3	219.4	215.3	212.7	211.4	210.1	208.7	207.4
55°	199.8	195.8	191.8	189.1	187.7	186.2	184.9	183.5
57.5°	176.2	172.3	168.3	165.7	164.5	163.2	162.0	160.7
60°	160.6	156.6	152.7	150.2	148.8	147.5	146.2	144.8
62.5°	145.2	141.5	137.9	135.5	134.1	132.9	131.6	130.2
65°	122.6	119.1	115.5	113.1	111.8	110.5	109.2	107.8
67.5°	101.1	97.9	94.6	92.5	91.4	90.4	89.3	88.3
70°	86.9	84.1	81.4	79.5	78.4	77.3	76.3	75.2
72.5°	73.5	71.0	68.5	66.9	66.2	65.5	64.7	64.1
75°	55.0	53.0	51.1	49.9	49.2	48.6	48.0	47.4
77.5°	39.2	37.8	36.4	35.5	35.0	34.6	34.1	33.7
80°	29.4	28.7	27.9	27.4	27.2	27.0	26.9	26.7
82.5°	22.0	21.6	21.3	21.0	20.9	20.8	20.8	20.6
85°	12.6	12.5	12.4	12.3	12.2	12.1	12.1	12.0
87.5°	5.9	5.9	6.0	6.1	6.0	5.9	5.9	5.9
90°	5.5	5.8	6.1	6.7	6.7	6.7	7.0	7.0
92.5°	53.9	39.1	29.4	25.0	21.1	20.3	19.9	19.4
95°	218.8	172.5	135.1	109.5	87.9	78.8	76.4	71.5
97.5°	325.8	293.4	256.9	221.4	202.6	185.5	176.8	172.8
100°	374.3	359.4	328.0	296.4	275.3	253.5	242.2	237.4
102.5°	390.5	399.8	384.8	363.3	340.9	325.3	313.1	309.4
105°	381.0	422.7	436.0	432.7	422.9	412.9	406.8	403.2
107.5°	346.6	402.3	436.6	452.5	457.4	457.4	455.4	453.0
110°	321.3	379.2	422.1	447.9	461.6	467.4	469.5	469.5





TEST NUMBER: P333495-935

CATALOG NUMBER: S125RDIP-S375D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	301.4	356.3	399.7	430.2	450.1	460.1	465.4	467.6
115°	276.3	323.5	365.2	398.3	422.1	436.6	445.1	449.1
117.5°	260.1	300.7	336.7	367.1	390.8	406.0	414.4	416.8
120°	251.3	287.8	321.3	348.1	370.7	385.2	393.5	395.9
122.5°	244.8	278.6	308.4	333.5	353.6	367.0	375.2	377.4
125°	235.2	266.2	292.7	314.6	331.7	344.1	350.9	353.9
127.5°	225.5	254.4	279.1	299.6	315.1	326.1	332.4	333.8
130°	219.4	246.2	269.9	289.7	304.9	315.0	321.1	322.9
132.5°	213.3	238.4	259.9	279.0	294.2	304.2	309.8	311.9
135°	205.4	226.4	245.9	263.2	276.6	286.6	292.1	293.9
137.5°	198.7	215.7	231.9	246.6	258.6	267.7	272.8	274.7
140°	195.0	209.3	223.3	236.1	247.4	255.3	259.8	261.4
142.5°	191.9	204.0	216.0	227.1	236.7	243.4	247.7	249.0
145°	187.8	197.2	206.6	214.8	222.1	227.3	230.7	231.9
147.5°	183.8	191.5	198.8	205.0	210.8	214.9	216.8	217.4
150°	181.7	188.4	194.2	199.6	204.1	207.8	209.1	209.3
152.5°	179.3	185.2	190.5	194.8	198.5	201.5	202.7	203.0
155°	175.6	180.5	184.7	188.0	191.1	193.2	194.2	194.4
157.5°	171.9	175.9	179.3	181.8	184.3	186.0	186.8	186.8
160°	169.5	172.5	175.6	177.7	179.9	181.3	181.9	181.7
162.5°	166.8	169.6	172.2	174.1	175.7	176.9	177.1	177.0
165°	163.1	165.2	167.0	168.6	169.8	170.4	170.4	170.4
167.5°	159.5	161.0	162.4	163.5	164.1	164.6	164.4	164.3
170°	157.6	158.5	159.5	160.1	160.7	161.0	161.0	160.7
172.5°	155.4	156.4	157.0	157.4	157.5	158.1	157.6	157.2
175°	153.1	153.1	153.7	153.7	153.7	153.9	153.3	153.1
177.5°	151.4	151.6	151.6	151.6	151.4	151.6	150.9	150.9
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9

(END OF REPORT)