

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333220-830

Luminaire Tested: **S125DIP-S850D590U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333220-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D590U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5448.9 lumens  
Efficiency: N/A  
Efficacy: 135.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333220-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333220-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50				
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42				
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35				
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	40	36	33	30				
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26				
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23				
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20				
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20	18				
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16				
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17	15				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7991	7991	7991
5°	8009	7933	7983
10°	7960	7877	7922
15°	7874	7782	7815
20°	7750	7649	7663
25°	7617	7492	7485
30°	7454	7322	7285
35°	7278	7139	7039
40°	7098	6940	6842
45°	6902	6760	6625
50°	6688	6540	6344
55°	6481	6293	6117
60°	6234	6044	5829
65°	5938	5744	5550
70°	5655	5399	5214
75°	5153	4983	4811
80°	4590	4515	4407
85°	3987	4068	3838



TEST NUMBER: P333220-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.7	2.1
10°-20°	329.6	6.0
20°-30°	486.6	8.9
30°-40°	567.8	10.4
40°-50°	570.3	10.5
50°-60°	500.6	9.2
60°-70°	373.0	6.8
70°-80°	213.3	3.9
80°-90°	63.6	1.2
90°-100°	26.4	0.5
100°-110°	162.5	3.0
110°-120°	294.7	5.4
120°-130°	378.2	6.9
130°-140°	406.7	7.5
140°-150°	381.8	7.0
150°-160°	308.8	5.7
160°-170°	199.7	3.7
170°-180°	68.9	1.3
0°-30°	932.8	17.1
0°-40°	1500.6	27.5
0°-60°	2571.4	47.2
0°-90°	3221.2	59.1
90°-120°	483.5	8.9
90°-150°	1650.2	30.3
90°-180°	2228.0	40.9
0°-180°	5448.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1237	1237	1237	1237	1237	
5°	1235	1233	1224	1232	1231	117
15°	1178	1174	1164	1169	1169	332
25°	1069	1064	1051	1053	1050	492
35°	923	919	906	900	893	577
45°	756	751	740	729	725	582
55°	576	572	559	550	543	514
65°	389	386	376	367	363	386
75°	206	204	200	197	193	220
85°	54	55	55	54	52	60
90°	1	5	9	11	13	4
95°	31	28	9	11	11	39
105°	158	160	160	160	160	168
115°	297	299	300	298	295	294
125°	422	426	426	424	422	377
135°	526	529	529	527	524	406
145°	610	611	611	612	609	382
155°	672	669	670	671	667	310
165°	709	706	707	709	706	200
175°	726	722	723	727	722	69
180°	726	726	726	726	726	



TEST NUMBER: P333220-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1240.5	1239.9	1239.4	1238.9	1238.3	1237.2	1235.5	1233.8	1232.0	1230.3	1232.0
5°	1235.4	1234.9	1234.4	1234.1	1233.6	1232.3	1230.1	1227.9	1225.8	1223.6	1225.6
7.5°	1224.0	1223.6	1223.1	1222.7	1222.3	1220.9	1218.4	1216.1	1213.7	1211.3	1213.1
10°	1213.8	1213.4	1213.0	1212.5	1212.1	1210.7	1208.2	1205.9	1203.5	1201.1	1202.9
12.5°	1201.3	1200.5	1199.8	1198.9	1198.2	1196.7	1194.5	1192.2	1190.0	1187.8	1189.2
15°	1177.6	1177.0	1176.3	1175.6	1175.0	1173.5	1171.1	1168.7	1166.3	1163.9	1165.0
17.5°	1150.4	1149.4	1148.5	1147.5	1146.6	1144.8	1142.4	1139.9	1137.4	1134.9	1136.2
20°	1127.7	1127.3	1126.8	1126.3	1126.0	1124.3	1121.4	1118.6	1115.8	1113.0	1114.6
22.5°	1104.9	1104.2	1103.4	1102.6	1101.8	1100.1	1097.5	1094.8	1092.1	1089.5	1090.5
25°	1068.9	1067.9	1066.8	1065.6	1064.6	1062.6	1059.8	1057.0	1054.1	1051.3	1051.8
27.5°	1026.8	1026.2	1025.6	1024.9	1024.3	1022.5	1019.5	1016.6	1013.7	1010.8	1010.9
30°	999.5	998.8	998.2	997.5	996.8	994.9	991.6	988.4	985.1	981.8	981.4
32.5°	969.7	968.7	967.7	966.7	965.7	963.7	960.8	957.9	955.0	952.1	951.3
35°	923.1	922.2	921.3	920.5	919.6	917.7	914.6	911.5	908.5	905.5	904.4
37.5°	874.8	873.6	872.5	871.5	870.3	868.4	865.5	862.6	859.8	857.0	855.3
40°	841.9	840.7	839.7	838.6	837.4	835.5	832.4	829.3	826.3	823.2	821.3
42.5°	806.6	805.7	804.7	803.9	803.0	801.0	798.0	794.8	791.8	788.8	787.0
45°	755.7	754.8	753.9	753.1	752.2	750.5	747.9	745.3	742.6	740.1	737.4
47.5°	700.9	701.0	701.0	701.0	701.1	699.6	696.4	693.2	690.1	687.0	684.3
50°	665.6	665.0	664.3	663.6	663.1	661.4	658.8	656.2	653.6	650.9	648.1
52.5°	629.6	629.1	628.7	628.2	627.7	626.0	623.3	620.5	617.7	614.9	612.5
55°	575.6	575.0	574.3	573.6	573.0	571.1	568.1	565.1	561.9	558.9	556.9
57.5°	518.6	518.3	517.9	517.6	517.3	515.8	513.2	510.7	508.0	505.5	502.9
60°	482.6	481.7	480.9	479.9	479.1	477.5	475.0	472.7	470.3	467.9	465.7
62.5°	445.0	444.3	443.7	442.9	442.2	440.8	438.8	436.8	434.7	432.6	430.4
65°	388.6	388.1	387.8	387.3	386.9	385.5	383.0	380.7	378.2	375.9	373.9
67.5°	334.0	333.1	332.2	331.2	330.4	328.9	327.3	325.5	323.7	321.9	320.2
70°	299.5	298.4	297.4	296.2	295.2	293.7	291.7	289.7	287.8	285.9	284.6
72.5°	261.9	261.2	260.4	259.8	259.0	258.0	256.7	255.4	254.2	253.0	251.5
75°	206.5	206.1	205.7	205.3	204.8	204.1	202.9	201.9	200.8	199.7	199.1
77.5°	155.4	155.2	155.1	155.0	154.8	154.4	153.7	153.2	152.5	151.9	151.6
80°	123.4	123.4	123.4	123.4	123.4	123.4	123.1	122.7	122.2	121.8	121.2
82.5°	95.1	94.8	94.4	94.1	93.8	93.5	93.4	93.4	93.3	93.2	92.8
85°	53.8	54.1	54.3	54.5	54.7	54.9	54.9	54.9	54.9	54.9	54.6
87.5°	21.2	21.4	21.7	21.9	22.1	22.1	22.1	22.1	22.1	22.1	22.2
90°	0.6	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2
92.5°	8.3	7.6	7.0	6.3	5.6	5.7	6.4	7.2	7.8	8.6	9.2
95°	30.6	30.3	30.0	29.6	29.2	26.8	22.2	17.7	13.1	8.6	9.2
97.5°	64.0	64.7	65.3	65.9	66.5	62.4	53.4	44.4	35.4	26.5	23.1
100°	89.8	90.2	90.5	90.9	91.2	91.6	92.2	92.7	93.1	93.6	75.8
102.5°	116.0	116.5	117.0	117.4	117.8	118.2	118.5	118.9	119.1	119.4	116.0
105°	158.1	158.5	159.1	159.6	160.0	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.8	201.8	201.8	201.8	201.9	202.1	202.4	202.6	202.8	202.8
110°	230.2	230.2	230.2	230.2	230.2	230.3	230.5	230.7	231.0	231.2	230.9



TEST NUMBER: P333220-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	256.8	257.1	257.4	257.7	258.0	258.2	258.4	258.4	258.6	258.7	258.4
115°	296.8	297.5	298.0	298.6	299.3	299.6	299.7	299.8	299.9	300.1	299.6
117.5°	338.3	338.2	338.2	338.2	338.2	338.4	338.8	339.3	339.7	340.2	339.6
120°	364.1	363.9	363.8	363.7	363.5	363.7	364.1	364.4	364.8	365.1	364.9
122.5°	386.8	387.3	387.8	388.2	388.7	389.0	389.2	389.4	389.5	389.6	389.5
125°	422.2	423.0	423.8	424.6	425.5	425.9	425.9	425.9	425.9	425.9	425.5
127.5°	455.8	456.4	457.0	457.6	458.2	458.5	458.4	458.4	458.3	458.2	457.9
130°	476.5	477.0	477.7	478.2	478.8	479.2	479.3	479.5	479.6	479.7	479.3
132.5°	497.1	497.8	498.5	499.2	499.8	500.1	499.8	499.5	499.3	499.1	499.0
135°	526.5	527.2	527.9	528.6	529.3	529.6	529.3	529.0	528.9	528.6	528.4
137.5°	553.5	554.1	554.7	555.3	555.9	556.2	555.9	555.7	555.5	555.3	555.3
140°	571.1	571.4	571.6	571.8	572.0	572.1	572.0	571.8	571.7	571.7	571.8
142.5°	587.0	587.2	587.3	587.5	587.6	587.8	588.0	588.1	588.2	588.4	588.4
145°	610.4	610.6	610.9	611.1	611.3	611.4	611.4	611.4	611.4	611.4	611.5
147.5°	630.7	630.7	630.7	630.7	630.6	630.7	630.7	630.9	631.0	631.2	631.4
150°	643.7	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.9
152.5°	656.2	655.6	655.2	654.6	654.0	653.9	654.1	654.4	654.6	654.9	655.2
155°	672.2	671.5	670.8	670.1	669.3	669.1	669.3	669.6	669.8	670.1	670.4
157.5°	684.6	684.1	683.7	683.2	682.9	682.7	682.7	682.7	682.7	682.8	683.2
160°	693.1	692.5	691.7	691.0	690.3	690.0	690.1	690.2	690.3	690.5	691.0
162.5°	700.0	699.4	698.6	697.9	697.2	696.9	697.0	697.1	697.2	697.4	698.0
165°	709.3	708.6	707.8	707.2	706.4	706.2	706.2	706.3	706.5	706.6	707.3
167.5°	716.1	715.5	714.7	714.0	713.2	712.9	713.0	713.1	713.2	713.4	714.3
170°	720.1	719.3	718.4	717.6	716.7	716.3	716.4	716.6	716.7	716.8	717.7
172.5°	722.6	721.8	721.0	720.1	719.3	719.0	719.2	719.4	719.6	719.8	720.7
175°	725.5	724.7	724.0	723.3	722.6	722.3	722.4	722.6	722.6	722.7	723.7
177.5°	726.7	726.1	725.6	725.0	724.4	724.2	724.2	724.3	724.4	724.5	725.3
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333220-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1233.8	1235.5	1237.2	1238.0	1237.8	1237.7	1237.5	1237.3
5°	1227.6	1229.5	1231.4	1232.3	1232.1	1231.9	1231.6	1231.4
7.5°	1215.1	1217.0	1218.9	1219.7	1219.6	1219.4	1219.1	1218.9
10°	1204.6	1206.4	1208.1	1208.8	1208.6	1208.3	1208.2	1208.0
12.5°	1190.5	1191.9	1193.4	1194.0	1194.0	1193.9	1193.9	1193.8
15°	1166.1	1167.2	1168.3	1168.8	1168.8	1168.8	1168.8	1168.8
17.5°	1137.6	1139.0	1140.3	1140.5	1139.3	1138.3	1137.2	1136.1
20°	1116.1	1117.6	1119.1	1119.3	1118.2	1117.1	1116.1	1114.9
22.5°	1091.5	1092.5	1093.5	1093.6	1092.9	1092.1	1091.4	1090.7
25°	1052.2	1052.6	1053.1	1052.9	1052.3	1051.7	1051.0	1050.4
27.5°	1011.0	1011.1	1011.2	1010.9	1010.2	1009.6	1008.9	1008.2
30°	981.0	980.5	980.1	979.6	978.9	978.3	977.6	976.9
32.5°	950.5	949.7	949.0	947.9	946.8	945.6	944.4	943.3
35°	903.3	902.2	901.2	899.8	898.0	896.3	894.5	892.8
37.5°	853.7	852.1	850.5	849.1	848.2	847.2	846.2	845.2
40°	819.4	817.4	815.4	814.1	813.4	812.8	812.2	811.5
42.5°	785.2	783.4	781.7	780.2	779.3	778.3	777.2	776.3
45°	734.8	732.2	729.6	727.9	727.4	726.7	726.0	725.4
47.5°	681.6	679.0	676.4	674.3	672.8	671.3	669.7	668.2
50°	645.3	642.4	639.6	637.4	635.9	634.4	632.9	631.4
52.5°	610.0	607.5	605.0	602.9	601.2	599.6	597.9	596.2
55°	555.1	553.1	551.1	549.4	547.8	546.3	544.8	543.3
57.5°	500.5	497.9	495.4	493.7	492.9	492.1	491.3	490.4
60°	463.5	461.4	459.2	457.3	455.8	454.3	452.8	451.3
62.5°	428.0	425.7	423.3	421.5	420.4	419.1	418.0	416.8
65°	372.0	370.0	368.1	366.6	365.8	365.0	364.0	363.2
67.5°	318.6	316.9	315.3	314.1	313.7	313.1	312.5	312.1
70°	283.2	281.9	280.6	279.6	278.6	277.8	276.9	276.1
72.5°	250.0	248.5	247.0	245.8	245.0	244.1	243.3	242.3
75°	198.4	197.7	197.1	196.3	195.5	194.5	193.7	192.8
77.5°	151.2	150.7	150.3	149.9	149.2	148.6	148.1	147.4
80°	120.9	120.7	120.6	120.2	119.8	119.3	118.9	118.5
82.5°	92.4	92.0	91.6	91.4	91.3	91.2	91.1	91.0
85°	54.4	54.2	53.9	53.6	53.2	52.8	52.3	51.8
87.5°	22.3	22.4	22.5	22.5	22.2	22.0	21.7	21.4
90°	9.8	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	9.8	10.4	11.0	11.4	11.5	11.7	11.9	12.1
95°	9.8	10.4	11.0	11.3	11.3	11.3	11.3	11.3
97.5°	19.7	16.3	13.0	11.3	11.3	11.3	11.3	11.3
100°	58.0	40.2	22.3	13.2	12.7	12.3	11.8	11.3
102.5°	112.6	109.2	105.9	100.2	92.0	83.9	75.8	67.7
105°	160.2	160.2	160.2	160.2	160.0	159.9	159.9	159.7
107.5°	202.9	202.9	202.9	202.7	202.5	202.1	201.7	201.3
110°	230.5	230.2	229.8	229.7	229.8	229.9	230.1	230.2





TEST NUMBER: P333220-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.9	257.4	256.9	256.7	256.5	256.3	256.2	256.0
115°	299.1	298.6	298.1	297.6	296.8	296.1	295.4	294.7
117.5°	338.9	338.3	337.7	337.2	337.0	336.6	336.3	336.0
120°	364.7	364.4	364.2	363.7	363.2	362.6	361.9	361.4
122.5°	389.2	389.0	388.7	388.2	387.6	386.8	386.2	385.5
125°	425.0	424.4	424.0	423.6	423.2	422.8	422.5	422.2
127.5°	457.6	457.4	457.1	456.6	455.6	454.8	453.9	453.0
130°	479.0	478.6	478.2	477.8	477.2	476.5	476.0	475.4
132.5°	498.9	498.8	498.8	498.4	497.9	497.2	496.6	496.1
135°	528.1	527.9	527.6	527.2	526.5	525.8	525.0	524.3
137.5°	555.3	555.4	555.4	555.2	554.6	553.9	553.4	552.7
140°	572.1	572.3	572.6	572.3	571.7	570.9	570.2	569.5
142.5°	588.5	588.5	588.6	588.2	587.6	586.8	586.1	585.4
145°	611.7	611.8	611.9	611.6	610.9	610.2	609.4	608.7
147.5°	631.5	631.7	631.8	631.4	630.6	629.7	628.9	628.0
150°	644.1	644.4	644.6	644.3	643.4	642.3	641.4	640.5
152.5°	655.3	655.6	655.8	655.5	654.7	653.8	652.9	652.1
155°	670.8	671.1	671.5	671.2	670.2	669.3	668.4	667.3
157.5°	683.5	683.9	684.3	684.0	683.1	682.0	681.1	680.1
160°	691.4	691.9	692.4	692.1	691.2	690.2	689.3	688.3
162.5°	698.7	699.4	700.0	699.8	698.8	697.8	696.7	695.6
165°	708.0	708.8	709.5	709.4	708.4	707.5	706.5	705.5
167.5°	715.1	716.0	716.8	716.7	715.7	714.5	713.5	712.4
170°	718.8	719.7	720.7	720.6	719.5	718.4	717.4	716.3
172.5°	721.5	722.5	723.3	723.2	722.1	721.0	719.9	718.9
175°	724.6	725.6	726.6	726.5	725.5	724.3	723.3	722.2
177.5°	725.9	726.6	727.3	727.2	726.4	725.7	724.9	724.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5

(END OF REPORT)