

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333530-935

Luminaire Tested: **S125RDIP-S610D590U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333530-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3808.8 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333530-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333530-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	41	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5607	5543	5577
10°	5564	5491	5491
15°	5498	5380	5336
20°	5413	5225	5161
25°	5315	5072	4960
30°	5190	4894	4737
35°	5065	4709	4487
40°	4947	4517	4242
45°	4804	4302	3974
50°	4660	4068	3693
55°	4494	3845	3396
60°	4326	3574	3077
65°	4129	3260	2709
70°	3903	2866	2334
75°	3593	2415	1941
80°	3165	1901	1629
85°	2668	1549	1452



TEST NUMBER: P333530-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	2.1
10°-20°	227.6	6.0
20°-30°	330.1	8.7
30°-40°	376.2	9.9
40°-50°	366.7	9.6
50°-60°	308.6	8.1
60°-70°	216.4	5.7
70°-80°	111.2	2.9
80°-90°	29.5	0.8
90°-100°	42.3	1.1
100°-110°	124.8	3.3
110°-120°	211.4	5.6
120°-130°	278.3	7.3
130°-140°	311.8	8.2
140°-150°	305.6	8.0
150°-160°	256.7	6.7
160°-170°	170.6	4.5
170°-180°	59.7	1.6
0°-30°	639.1	16.8
0°-40°	1015.3	26.7
0°-60°	1690.5	44.4
0°-90°	2047.6	53.8
90°-120°	378.5	9.9
90°-150°	1274.2	33.5
90°-180°	1761.0	46.2
0°-180°	3808.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	861	860	82
15°	822	818	805	804	798	232
25°	746	735	712	703	696	343
35°	642	626	597	579	569	402
45°	526	506	471	446	435	406
55°	399	377	342	313	302	357
65°	270	247	213	188	177	268
75°	144	124	97	83	78	152
85°	36	25	21	20	20	40
90°	0	4	8	10	12	3
95°	32	33	38	41	42	34
105°	112	114	117	120	122	120
115°	212	214	215	214	214	209
125°	309	312	312	311	311	277
135°	402	405	405	405	403	310
145°	487	489	490	490	489	304
155°	557	557	558	559	557	256
165°	606	605	605	607	604	171
175°	630	628	628	630	627	60
180°	631	631	631	631	631	



TEST NUMBER: P333530-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	867.7	867.4	867.0	866.7	866.3	865.6	864.4	863.2	862.0	860.9	862.0
5°	864.8	864.3	863.7	863.1	862.5	861.4	859.8	858.2	856.6	855.0	856.4
7.5°	856.4	855.7	855.2	854.6	854.1	852.9	850.9	849.0	847.1	845.2	846.2
10°	848.4	848.0	847.6	847.1	846.7	845.5	843.4	841.5	839.4	837.3	837.8
12.5°	839.6	839.0	838.4	837.9	837.3	835.7	833.0	830.3	827.5	824.8	825.1
15°	822.3	821.4	820.5	819.7	818.8	816.8	813.8	810.7	807.7	804.6	804.5
17.5°	802.8	801.5	800.1	798.8	797.5	794.9	791.0	787.2	783.3	779.5	778.8
20°	787.6	786.2	784.7	783.3	781.8	778.8	774.1	769.5	764.8	760.2	759.4
22.5°	770.9	769.4	768.0	766.5	765.1	761.9	757.0	752.2	747.3	742.4	741.0
25°	745.8	743.6	741.4	739.3	737.0	733.2	727.9	722.5	717.1	711.7	709.9
27.5°	717.0	714.4	711.7	709.0	706.4	702.2	696.5	690.7	684.9	679.2	676.5
30°	696.0	693.3	690.5	687.8	685.0	680.5	674.4	668.4	662.3	656.2	652.8
32.5°	675.6	672.4	669.2	666.0	662.7	658.0	651.8	645.6	639.3	633.1	629.4
35°	642.4	638.9	635.4	632.0	628.4	623.5	616.9	610.4	603.8	597.3	593.1
37.5°	609.8	605.5	601.3	597.1	592.9	587.4	580.6	573.9	567.1	560.3	555.3
40°	586.8	582.5	578.1	573.7	569.4	563.7	556.7	549.7	542.8	535.8	530.3
42.5°	562.7	558.3	553.8	549.3	544.8	539.0	531.8	524.5	517.4	510.1	504.8
45°	526.0	521.8	517.5	513.3	509.1	503.0	495.0	487.0	479.0	471.0	465.2
47.5°	487.9	483.5	479.0	474.6	470.1	463.8	455.8	447.7	439.7	431.6	425.7
50°	463.8	459.0	454.2	449.4	444.6	438.1	429.8	421.5	413.2	404.9	398.8
52.5°	437.6	432.7	427.8	422.9	418.0	411.6	403.8	396.0	388.1	380.3	373.8
55°	399.1	394.4	389.8	385.1	380.5	374.0	365.9	357.7	349.7	341.5	334.9
57.5°	360.1	355.1	350.1	345.2	340.2	333.7	325.9	318.1	310.2	302.4	295.9
60°	334.9	329.8	324.8	319.7	314.6	308.2	300.2	292.4	284.6	276.7	270.4
62.5°	308.2	303.4	298.5	293.7	288.9	282.4	274.5	266.5	258.6	250.6	244.6
65°	270.2	265.3	260.3	255.4	250.4	244.1	236.3	228.7	220.9	213.3	207.4
67.5°	232.4	227.4	222.5	217.6	212.6	206.5	199.1	191.7	184.3	176.8	171.6
70°	206.7	201.8	196.8	191.9	186.9	180.8	173.6	166.3	159.0	151.8	147.2
72.5°	181.6	176.8	171.9	167.1	162.3	156.4	149.6	142.8	136.0	129.2	125.1
75°	144.0	139.6	135.2	130.9	126.5	121.2	115.1	109.0	102.9	96.8	93.6
77.5°	106.5	103.0	99.5	96.0	92.6	88.3	83.4	78.6	73.7	68.8	66.6
80°	85.1	81.5	78.1	74.6	71.1	67.3	63.2	59.2	55.1	51.1	49.7
82.5°	64.1	61.0	57.9	54.7	51.6	48.6	45.8	43.0	40.2	37.5	36.9
85°	36.0	33.3	30.7	28.2	25.5	23.8	23.1	22.4	21.7	20.9	20.8
87.5°	12.1	11.5	10.8	10.2	9.6	9.3	9.3	9.4	9.4	9.4	9.6
90°	0.5	1.4	2.2	3.1	4.0	4.8	5.6	6.4	7.1	7.8	8.4
92.5°	11.9	12.5	13.1	13.7	14.3	15.1	16.0	17.0	17.9	18.9	19.5
95°	31.9	32.1	32.4	32.5	32.8	33.5	34.5	35.6	36.8	37.8	38.6
97.5°	53.0	53.1	53.2	53.3	53.4	54.2	55.7	57.2	58.7	60.2	61.0
100°	68.8	68.8	68.8	68.8	68.8	69.5	70.9	72.3	73.7	75.2	76.1
102.5°	85.7	86.1	86.5	87.0	87.4	88.0	88.7	89.5	90.1	90.8	92.0
105°	112.0	112.5	113.0	113.7	114.2	114.8	115.5	116.1	116.8	117.4	118.0
107.5°	141.0	141.6	142.2	142.7	143.3	143.8	144.3	144.7	145.3	145.8	146.1
110°	161.1	161.6	162.2	162.7	163.3	163.8	164.0	164.4	164.7	165.1	165.4



TEST NUMBER: P333530-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.5	181.8	182.1	182.4	182.7	183.0	183.5	183.8	184.3	184.7	184.9
115°	211.7	212.2	212.6	213.0	213.4	213.8	214.0	214.2	214.4	214.6	214.6
117.5°	241.9	242.1	242.4	242.5	242.7	243.0	243.1	243.3	243.5	243.7	243.8
120°	260.8	261.4	261.9	262.4	263.0	263.3	263.5	263.6	263.6	263.7	263.7
122.5°	281.3	281.5	281.6	281.8	282.1	282.2	282.6	282.8	283.1	283.4	283.4
125°	308.9	309.6	310.2	310.9	311.6	311.9	312.0	312.2	312.3	312.4	312.2
127.5°	338.5	338.8	339.1	339.5	339.9	340.2	340.3	340.4	340.5	340.7	340.6
130°	356.1	356.6	357.2	357.7	358.3	358.7	358.9	359.1	359.3	359.6	359.5
132.5°	373.8	374.7	375.6	376.4	377.4	377.8	377.7	377.7	377.6	377.6	377.5
135°	401.7	402.4	403.1	403.7	404.4	404.8	404.9	405.0	405.1	405.2	405.2
137.5°	428.1	428.8	429.4	430.0	430.7	431.1	431.4	431.5	431.8	432.0	432.1
140°	445.0	445.6	446.1	446.6	447.2	447.6	448.0	448.3	448.6	448.9	449.2
142.5°	461.9	462.4	462.8	463.3	463.7	464.2	464.6	465.0	465.5	465.8	466.0
145°	486.7	487.2	487.7	488.1	488.5	488.9	489.2	489.6	489.9	490.2	490.2
147.5°	509.7	510.0	510.2	510.5	510.7	510.9	511.2	511.5	511.8	512.0	512.3
150°	525.0	525.0	524.9	524.8	524.6	524.8	525.2	525.6	526.1	526.5	526.5
152.5°	537.6	537.8	538.0	538.1	538.2	538.4	538.6	538.7	538.9	539.2	539.4
155°	557.0	557.0	557.0	557.0	557.0	557.1	557.2	557.2	557.4	557.5	557.9
157.5°	574.3	574.0	573.8	573.6	573.3	573.3	573.3	573.5	573.6	573.7	574.1
160°	584.5	584.2	583.8	583.5	583.2	583.1	583.2	583.3	583.4	583.5	583.9
162.5°	593.6	593.3	593.1	592.8	592.5	592.5	592.5	592.5	592.5	592.5	593.1
165°	605.6	605.4	605.2	604.9	604.8	604.7	604.8	604.9	605.0	605.1	605.5
167.5°	615.9	615.4	614.9	614.5	614.1	613.9	613.9	613.9	613.9	613.9	614.5
170°	621.3	620.9	620.4	620.0	619.6	619.4	619.4	619.4	619.4	619.4	620.0
172.5°	625.3	624.8	624.4	624.0	623.5	623.3	623.3	623.3	623.3	623.3	624.0
175°	629.6	629.2	628.8	628.4	627.9	627.8	627.8	627.8	627.8	627.8	628.4
177.5°	632.0	631.6	631.3	630.9	630.5	630.3	630.3	630.2	630.1	630.0	630.5
180°	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2



TEST NUMBER: P333530-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	863.2	864.4	865.6	866.1	866.0	865.8	865.7	865.6
5°	857.9	859.4	860.8	861.4	861.1	860.8	860.6	860.2
7.5°	847.2	848.3	849.3	849.6	849.3	848.9	848.7	848.3
10°	838.2	838.6	839.1	839.1	838.6	838.2	837.8	837.3
12.5°	825.4	825.8	826.0	825.9	825.2	824.6	823.9	823.2
15°	804.3	804.2	804.1	803.3	802.0	800.7	799.4	798.1
17.5°	778.1	777.3	776.6	775.7	774.6	773.5	772.5	771.4
20°	758.7	757.9	757.2	756.2	754.9	753.6	752.3	751.0
22.5°	739.5	738.0	736.7	735.4	734.3	733.2	732.2	731.1
25°	708.0	706.1	704.2	702.4	700.9	699.2	697.7	696.0
27.5°	673.9	671.2	668.6	666.5	665.0	663.4	661.9	660.3
30°	649.5	646.1	642.7	640.4	639.1	637.8	636.5	635.2
32.5°	625.7	622.1	618.4	615.7	614.0	612.3	610.7	609.1
35°	588.8	584.6	580.4	577.3	575.2	573.2	571.2	569.1
37.5°	550.3	545.2	540.1	536.6	534.6	532.7	530.7	528.7
40°	524.7	519.2	513.7	510.1	508.3	506.5	504.8	503.1
42.5°	499.6	494.2	489.0	485.0	482.5	479.9	477.3	474.8
45°	459.3	453.6	447.7	443.8	441.6	439.4	437.2	435.1
47.5°	419.7	413.6	407.7	403.5	401.1	398.6	396.2	393.8
50°	392.7	386.6	380.5	376.3	374.2	372.0	369.8	367.6
52.5°	367.2	360.6	354.0	349.7	347.5	345.3	343.1	341.0
55°	328.4	321.8	315.3	310.9	308.6	306.3	303.9	301.6
57.5°	289.6	283.2	276.8	272.5	270.4	268.4	266.4	264.3
60°	263.9	257.5	251.2	246.8	244.7	242.5	240.3	238.2
62.5°	238.7	232.7	226.8	222.7	220.6	218.4	216.2	214.0
65°	201.6	195.8	190.0	186.0	183.8	181.7	179.4	177.3
67.5°	166.3	160.9	155.6	152.1	150.3	148.6	146.8	145.1
70°	142.8	138.3	133.7	130.6	128.9	127.2	125.4	123.6
72.5°	121.0	116.8	112.6	109.9	108.8	107.6	106.5	105.3
75°	90.4	87.2	84.0	81.9	80.9	79.9	78.9	77.8
77.5°	64.3	62.1	59.8	58.4	57.6	56.8	56.1	55.4
80°	48.4	47.1	45.8	45.0	44.7	44.4	44.1	43.8
82.5°	36.2	35.6	35.0	34.6	34.4	34.3	34.1	33.9
85°	20.7	20.5	20.3	20.2	20.1	19.9	19.8	19.6
87.5°	9.6	9.7	9.9	9.9	9.8	9.8	9.7	9.6
90°	9.0	9.5	10.1	10.5	10.8	11.1	11.5	11.8
92.5°	20.3	21.0	21.8	22.2	22.5	22.7	22.9	23.2
95°	39.3	40.1	40.9	41.3	41.6	41.8	42.0	42.3
97.5°	61.6	62.4	63.1	63.5	63.6	63.8	63.9	64.1
100°	77.1	78.1	79.0	79.6	79.9	80.2	80.3	80.6
102.5°	93.0	94.1	95.1	95.8	96.2	96.4	96.8	97.0
105°	118.7	119.3	120.0	120.5	120.8	121.1	121.5	121.8
107.5°	146.5	146.8	147.1	147.2	147.2	147.2	147.1	147.1
110°	165.7	166.0	166.3	166.4	166.3	166.3	166.1	166.0



TEST NUMBER: P333530-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	185.0	185.1	185.3	185.3	185.1	184.9	184.7	184.5
115°	214.4	214.3	214.2	214.1	214.0	213.9	213.8	213.7
117.5°	243.9	244.0	244.1	243.9	243.5	243.1	242.6	242.1
120°	263.7	263.7	263.7	263.6	263.1	262.7	262.3	261.8
122.5°	283.3	283.2	283.1	282.8	282.5	282.1	281.8	281.5
125°	311.9	311.8	311.5	311.3	311.3	311.2	311.0	310.9
127.5°	340.4	340.4	340.3	340.1	339.8	339.7	339.4	339.2
130°	359.3	359.2	359.1	359.0	358.7	358.5	358.3	358.1
132.5°	377.4	377.3	377.2	376.9	376.7	376.3	376.1	375.7
135°	405.2	405.2	405.2	405.0	404.6	404.2	403.7	403.3
137.5°	432.3	432.4	432.6	432.4	431.8	431.3	430.8	430.2
140°	449.4	449.6	449.8	449.6	449.1	448.6	448.0	447.5
142.5°	466.1	466.2	466.3	466.1	465.6	465.0	464.5	464.0
145°	490.2	490.2	490.2	490.0	489.7	489.4	489.0	488.7
147.5°	512.6	512.8	513.1	512.8	512.0	511.3	510.6	509.9
150°	526.5	526.5	526.5	526.4	526.2	526.0	525.8	525.6
152.5°	539.7	539.9	540.2	540.1	539.7	539.3	538.9	538.6
155°	558.4	558.8	559.2	559.2	558.6	558.1	557.5	557.0
157.5°	574.5	575.0	575.4	575.3	574.5	573.9	573.2	572.4
160°	584.4	584.8	585.2	585.2	584.7	584.1	583.6	583.1
162.5°	593.6	594.1	594.7	594.6	594.0	593.3	592.7	592.0
165°	606.0	606.4	606.9	606.7	606.1	605.5	604.8	604.2
167.5°	615.2	615.9	616.5	616.5	615.8	615.1	614.4	613.8
170°	620.7	621.3	622.0	621.9	621.2	620.4	619.7	618.9
172.5°	624.7	625.3	625.9	625.9	625.3	624.6	623.9	623.2
175°	629.0	629.6	630.3	630.3	629.6	628.8	628.0	627.2
177.5°	631.0	631.5	632.1	632.1	631.5	630.9	630.2	629.6
180°	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2

(END OF REPORT)