

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333221-830

Luminaire Tested: **S125DIP-S850D590U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333221-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D590U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5149.3 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333221-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333221-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	96	92	88	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	85	79	73	69	69	65	61	61	57	54	52	50	48	44
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	39	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	29	25	22	19
9	52	39	32	26	49	37	30	25	33	28	23	30	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	28	23	19	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7991	7991	7991
5°	8009	7933	7983
10°	7960	7877	7922
15°	7874	7782	7815
20°	7750	7649	7663
25°	7617	7492	7485
30°	7454	7322	7285
35°	7278	7139	7039
40°	7098	6940	6842
45°	6902	6760	6625
50°	6688	6540	6344
55°	6481	6293	6117
60°	6234	6044	5829
65°	5938	5744	5550
70°	5655	5399	5214
75°	5153	4983	4811
80°	4590	4515	4407
85°	3987	4068	3838



TEST NUMBER: P333221-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	2.3
10°-20°	329.6	6.4
20°-30°	486.6	9.4
30°-40°	567.8	11.0
40°-50°	570.3	11.1
50°-60°	500.6	9.7
60°-70°	373.0	7.2
70°-80°	213.3	4.1
80°-90°	63.6	1.2
90°-100°	46.3	0.9
100°-110°	136.7	2.7
110°-120°	231.5	4.5
120°-130°	304.6	5.9
130°-140°	341.3	6.6
140°-150°	334.5	6.5
150°-160°	281.0	5.5
160°-170°	186.8	3.6
170°-180°	65.4	1.3
0°-30°	932.8	18.1
0°-40°	1500.6	29.1
0°-60°	2571.4	49.9
0°-90°	3221.2	62.6
90°-120°	414.4	8.0
90°-150°	1394.9	27.1
90°-180°	1928.0	37.4
0°-180°	5149.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1237	1237	1237	1237	1237	
5°	1235	1233	1224	1232	1231	117
15°	1178	1174	1164	1169	1169	332
25°	1069	1064	1051	1053	1050	492
35°	923	919	906	900	893	577
45°	756	751	740	729	725	582
55°	576	572	559	550	543	514
65°	389	386	376	367	363	386
75°	206	204	200	197	193	220
85°	54	55	55	54	52	60
90°	1	5	9	11	13	5
95°	35	36	41	45	46	37
105°	123	125	128	132	133	131
115°	232	234	235	234	234	229
125°	338	341	342	341	340	303
135°	440	443	444	444	442	339
145°	533	535	537	536	535	333
155°	610	610	610	612	610	281
165°	663	662	662	664	661	187
175°	689	687	687	690	687	65
180°	691	691	691	691	691	



TEST NUMBER: P333221-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1240.5	1239.9	1239.4	1238.9	1238.3	1237.2	1235.5	1233.8	1232.0	1230.3	1232.0
5°	1235.4	1234.9	1234.4	1234.1	1233.6	1232.3	1230.1	1227.9	1225.8	1223.6	1225.6
7.5°	1224.0	1223.6	1223.1	1222.7	1222.3	1220.9	1218.4	1216.1	1213.7	1211.3	1213.1
10°	1213.8	1213.4	1213.0	1212.5	1212.1	1210.7	1208.2	1205.9	1203.5	1201.1	1202.9
12.5°	1201.3	1200.5	1199.8	1198.9	1198.2	1196.7	1194.5	1192.2	1190.0	1187.8	1189.2
15°	1177.6	1177.0	1176.3	1175.6	1175.0	1173.5	1171.1	1168.7	1166.3	1163.9	1165.0
17.5°	1150.4	1149.4	1148.5	1147.5	1146.6	1144.8	1142.4	1139.9	1137.4	1134.9	1136.2
20°	1127.7	1127.3	1126.8	1126.3	1126.0	1124.3	1121.4	1118.6	1115.8	1113.0	1114.6
22.5°	1104.9	1104.2	1103.4	1102.6	1101.8	1100.1	1097.5	1094.8	1092.1	1089.5	1090.5
25°	1068.9	1067.9	1066.8	1065.6	1064.6	1062.6	1059.8	1057.0	1054.1	1051.3	1051.8
27.5°	1026.8	1026.2	1025.6	1024.9	1024.3	1022.5	1019.5	1016.6	1013.7	1010.8	1010.9
30°	999.5	998.8	998.2	997.5	996.8	994.9	991.6	988.4	985.1	981.8	981.4
32.5°	969.7	968.7	967.7	966.7	965.7	963.7	960.8	957.9	955.0	952.1	951.3
35°	923.1	922.2	921.3	920.5	919.6	917.7	914.6	911.5	908.5	905.5	904.4
37.5°	874.8	873.6	872.5	871.5	870.3	868.4	865.5	862.6	859.8	857.0	855.3
40°	841.9	840.7	839.7	838.6	837.4	835.5	832.4	829.3	826.3	823.2	821.3
42.5°	806.6	805.7	804.7	803.9	803.0	801.0	798.0	794.8	791.8	788.8	787.0
45°	755.7	754.8	753.9	753.1	752.2	750.5	747.9	745.3	742.6	740.1	737.4
47.5°	700.9	701.0	701.0	701.0	701.1	699.6	696.4	693.2	690.1	687.0	684.3
50°	665.6	665.0	664.3	663.6	663.1	661.4	658.8	656.2	653.6	650.9	648.1
52.5°	629.6	629.1	628.7	628.2	627.7	626.0	623.3	620.5	617.7	614.9	612.5
55°	575.6	575.0	574.3	573.6	573.0	571.1	568.1	565.1	561.9	558.9	556.9
57.5°	518.6	518.3	517.9	517.6	517.3	515.8	513.2	510.7	508.0	505.5	502.9
60°	482.6	481.7	480.9	479.9	479.1	477.5	475.0	472.7	470.3	467.9	465.7
62.5°	445.0	444.3	443.7	442.9	442.2	440.8	438.8	436.8	434.7	432.6	430.4
65°	388.6	388.1	387.8	387.3	386.9	385.5	383.0	380.7	378.2	375.9	373.9
67.5°	334.0	333.1	332.2	331.2	330.4	328.9	327.3	325.5	323.7	321.9	320.2
70°	299.5	298.4	297.4	296.2	295.2	293.7	291.7	289.7	287.8	285.9	284.6
72.5°	261.9	261.2	260.4	259.8	259.0	258.0	256.7	255.4	254.2	253.0	251.5
75°	206.5	206.1	205.7	205.3	204.8	204.1	202.9	201.9	200.8	199.7	199.1
77.5°	155.4	155.2	155.1	155.0	154.8	154.4	153.7	153.2	152.5	151.9	151.6
80°	123.4	123.4	123.4	123.4	123.4	123.1	122.7	122.2	121.8	121.4	121.2
82.5°	95.1	94.8	94.4	94.1	93.8	93.5	93.4	93.4	93.3	93.2	92.8
85°	53.8	54.1	54.3	54.5	54.7	54.9	54.9	54.9	54.9	54.9	54.6
87.5°	21.2	21.4	21.7	21.9	22.1	22.1	22.1	22.1	22.1	22.1	22.2
90°	0.6	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2
92.5°	13.0	13.7	14.3	15.0	15.6	16.5	17.5	18.6	19.6	20.6	21.4
95°	35.0	35.2	35.4	35.6	35.9	36.7	37.8	39.0	40.2	41.4	42.2
97.5°	58.1	58.2	58.2	58.3	58.4	59.3	61.0	62.6	64.3	65.9	66.7
100°	75.3	75.3	75.3	75.3	75.3	76.1	77.6	79.2	80.7	82.3	83.3
102.5°	93.8	94.3	94.7	95.2	95.7	96.3	97.1	97.9	98.7	99.4	100.7
105°	122.6	123.2	123.8	124.4	125.0	125.6	126.4	127.1	127.8	128.5	129.2
107.5°	154.4	155.0	155.6	156.2	156.8	157.4	158.0	158.4	159.0	159.6	159.9
110°	176.3	176.9	177.6	178.1	178.8	179.3	179.6	179.9	180.3	180.7	181.1



TEST NUMBER: P333221-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	198.7	199.1	199.3	199.6	200.0	200.4	200.9	201.2	201.7	202.2	202.4
115°	231.8	232.2	232.7	233.2	233.7	234.0	234.2	234.5	234.7	235.0	234.9
117.5°	264.9	265.0	265.3	265.5	265.7	266.0	266.2	266.4	266.6	266.8	266.9
120°	285.5	286.2	286.7	287.3	287.9	288.2	288.4	288.5	288.6	288.7	288.7
122.5°	307.9	308.1	308.3	308.5	308.8	309.0	309.3	309.6	309.9	310.3	310.2
125°	338.2	338.9	339.6	340.4	341.1	341.5	341.6	341.8	341.9	342.0	341.8
127.5°	370.5	370.9	371.3	371.6	372.1	372.4	372.5	372.7	372.8	373.0	372.9
130°	389.8	390.4	391.1	391.6	392.2	392.7	392.9	393.1	393.3	393.6	393.5
132.5°	409.2	410.2	411.1	412.1	413.1	413.6	413.5	413.5	413.4	413.4	413.3
135°	439.8	440.5	441.3	442.0	442.7	443.1	443.3	443.4	443.5	443.6	443.6
137.5°	468.6	469.4	470.0	470.7	471.5	471.9	472.2	472.4	472.7	473.0	473.1
140°	487.1	487.8	488.3	488.9	489.6	490.0	490.4	490.8	491.1	491.4	491.7
142.5°	505.7	506.1	506.6	507.2	507.7	508.1	508.6	509.1	509.5	509.9	510.1
145°	532.8	533.3	533.9	534.3	534.8	535.2	535.6	535.9	536.3	536.6	536.6
147.5°	558.0	558.3	558.6	558.8	559.1	559.3	559.6	560.0	560.2	560.5	560.8
150°	574.8	574.7	574.6	574.5	574.3	574.5	575.0	575.4	575.9	576.4	576.4
152.5°	588.5	588.7	588.9	589.1	589.2	589.4	589.6	589.7	589.9	590.2	590.5
155°	609.7	609.7	609.7	609.7	609.7	609.8	609.9	610.0	610.2	610.3	610.8
157.5°	628.7	628.4	628.1	627.9	627.6	627.5	627.6	627.8	627.9	628.0	628.5
160°	639.9	639.5	639.1	638.8	638.4	638.3	638.4	638.6	638.7	638.8	639.2
162.5°	649.8	649.5	649.2	648.9	648.7	648.6	648.6	648.7	648.7	648.7	649.2
165°	663.0	662.7	662.5	662.2	662.0	661.9	662.0	662.2	662.3	662.4	662.9
167.5°	674.2	673.7	673.2	672.7	672.2	672.0	672.0	672.0	672.0	672.0	672.7
170°	680.1	679.7	679.2	678.7	678.3	678.1	678.1	678.1	678.1	678.1	678.7
172.5°	684.5	684.0	683.5	683.1	682.6	682.3	682.3	682.3	682.3	682.3	683.1
175°	689.3	688.8	688.3	687.9	687.4	687.2	687.2	687.2	687.2	687.2	687.9
177.5°	691.8	691.4	691.1	690.7	690.2	690.0	689.9	689.8	689.8	689.7	690.2
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333221-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1233.8	1235.5	1237.2	1238.0	1237.8	1237.7	1237.5	1237.3
5°	1227.6	1229.5	1231.4	1232.3	1232.1	1231.9	1231.6	1231.4
7.5°	1215.1	1217.0	1218.9	1219.7	1219.6	1219.4	1219.1	1218.9
10°	1204.6	1206.4	1208.1	1208.8	1208.6	1208.3	1208.2	1208.0
12.5°	1190.5	1191.9	1193.4	1194.0	1194.0	1193.9	1193.9	1193.8
15°	1166.1	1167.2	1168.3	1168.8	1168.8	1168.8	1168.8	1168.8
17.5°	1137.6	1139.0	1140.3	1140.5	1139.3	1138.3	1137.2	1136.1
20°	1116.1	1117.6	1119.1	1119.3	1118.2	1117.1	1116.1	1114.9
22.5°	1091.5	1092.5	1093.5	1093.6	1092.9	1092.1	1091.4	1090.7
25°	1052.2	1052.6	1053.1	1052.9	1052.3	1051.7	1051.0	1050.4
27.5°	1011.0	1011.1	1011.2	1010.9	1010.2	1009.6	1008.9	1008.2
30°	981.0	980.5	980.1	979.6	978.9	978.3	977.6	976.9
32.5°	950.5	949.7	949.0	947.9	946.8	945.6	944.4	943.3
35°	903.3	902.2	901.2	899.8	898.0	896.3	894.5	892.8
37.5°	853.7	852.1	850.5	849.1	848.2	847.2	846.2	845.2
40°	819.4	817.4	815.4	814.1	813.4	812.8	812.2	811.5
42.5°	785.2	783.4	781.7	780.2	779.3	778.3	777.2	776.3
45°	734.8	732.2	729.6	727.9	727.4	726.7	726.0	725.4
47.5°	681.6	679.0	676.4	674.3	672.8	671.3	669.7	668.2
50°	645.3	642.4	639.6	637.4	635.9	634.4	632.9	631.4
52.5°	610.0	607.5	605.0	602.9	601.2	599.6	597.9	596.2
55°	555.1	553.1	551.1	549.4	547.8	546.3	544.8	543.3
57.5°	500.5	497.9	495.4	493.7	492.9	492.1	491.3	490.4
60°	463.5	461.4	459.2	457.3	455.8	454.3	452.8	451.3
62.5°	428.0	425.7	423.3	421.5	420.4	419.1	418.0	416.8
65°	372.0	370.0	368.1	366.6	365.8	365.0	364.0	363.2
67.5°	318.6	316.9	315.3	314.1	313.7	313.1	312.5	312.1
70°	283.2	281.9	280.6	279.6	278.6	277.8	276.9	276.1
72.5°	250.0	248.5	247.0	245.8	245.0	244.1	243.3	242.3
75°	198.4	197.7	197.1	196.3	195.5	194.5	193.7	192.8
77.5°	151.2	150.7	150.3	149.9	149.2	148.6	148.1	147.4
80°	120.9	120.7	120.6	120.2	119.8	119.3	118.9	118.5
82.5°	92.4	92.0	91.6	91.4	91.3	91.2	91.1	91.0
85°	54.4	54.2	53.9	53.6	53.2	52.8	52.3	51.8
87.5°	22.3	22.4	22.5	22.5	22.2	22.0	21.7	21.4
90°	9.8	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	22.2	23.0	23.8	24.3	24.6	24.9	25.1	25.4
95°	43.1	43.9	44.8	45.2	45.5	45.8	46.0	46.3
97.5°	67.5	68.3	69.1	69.6	69.7	69.8	69.9	70.1
100°	84.5	85.5	86.5	87.2	87.5	87.8	87.9	88.2
102.5°	101.8	103.0	104.2	104.9	105.3	105.6	105.9	106.2
105°	130.0	130.6	131.4	132.0	132.2	132.6	133.0	133.4
107.5°	160.3	160.7	161.0	161.2	161.2	161.2	161.1	161.1
110°	181.3	181.7	182.1	182.2	182.1	182.0	181.8	181.7



TEST NUMBER: P333221-830

CATALOG NUMBER: S125DIP-S850D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	202.6	202.6	202.8	202.8	202.6	202.4	202.2	202.0
115°	234.7	234.6	234.5	234.4	234.2	234.1	234.0	233.9
117.5°	267.0	267.1	267.2	267.0	266.6	266.1	265.6	265.0
120°	288.7	288.7	288.7	288.5	288.0	287.6	287.1	286.6
122.5°	310.1	310.0	309.9	309.6	309.2	308.9	308.5	308.1
125°	341.5	341.3	341.0	340.8	340.7	340.6	340.4	340.4
127.5°	372.7	372.6	372.5	372.3	372.0	371.8	371.6	371.4
130°	393.3	393.2	393.1	392.9	392.7	392.5	392.2	392.0
132.5°	413.1	413.0	412.9	412.6	412.4	412.0	411.7	411.3
135°	443.6	443.6	443.6	443.4	442.9	442.4	442.0	441.5
137.5°	473.3	473.3	473.5	473.3	472.7	472.1	471.6	470.9
140°	491.9	492.2	492.4	492.2	491.6	491.1	490.4	489.8
142.5°	510.2	510.4	510.5	510.3	509.7	509.1	508.5	507.9
145°	536.6	536.6	536.6	536.4	536.1	535.7	535.4	535.0
147.5°	561.1	561.4	561.7	561.4	560.5	559.8	558.9	558.2
150°	576.4	576.4	576.4	576.3	576.1	575.8	575.6	575.3
152.5°	590.8	591.1	591.4	591.3	590.8	590.4	589.9	589.6
155°	611.2	611.7	612.2	612.2	611.5	611.0	610.3	609.7
157.5°	629.0	629.4	629.9	629.8	629.0	628.2	627.5	626.6
160°	639.7	640.2	640.6	640.6	640.1	639.4	638.9	638.3
162.5°	649.8	650.4	651.0	650.9	650.3	649.5	648.8	648.1
165°	663.4	663.8	664.4	664.2	663.5	662.8	662.0	661.4
167.5°	673.4	674.2	674.9	674.9	674.1	673.4	672.6	671.9
170°	679.5	680.1	680.9	680.8	680.0	679.2	678.3	677.5
172.5°	683.8	684.5	685.2	685.2	684.5	683.7	683.0	682.2
175°	688.6	689.3	690.0	689.9	689.2	688.3	687.5	686.6
177.5°	690.8	691.4	691.9	691.9	691.3	690.6	689.8	689.2
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0

(END OF REPORT)