

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333585-830

Luminaire Tested: **S125RDIP-S1090D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333585-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D365U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5219.9 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333585-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333585-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	76
1	104	100	96	92	99	95	92	88	87	84	81	79	77	75	72	70	69	65
2	95	87	81	76	90	84	78	73	76	72	68	70	66	63	63	61	58	55
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50	47
4	80	69	61	54	76	66	58	53	60	54	49	55	50	46	51	47	43	40
5	73	61	53	47	70	59	51	46	54	48	43	50	45	40	46	41	38	35
6	68	55	47	41	64	53	46	40	49	43	38	45	40	36	42	37	34	31
7	63	50	42	36	60	48	41	35	45	38	34	41	36	32	38	33	30	28
8	59	46	38	32	56	44	37	32	41	35	30	38	32	28	35	30	27	25
9	55	42	34	29	52	41	33	28	38	31	27	35	30	26	32	28	24	22
10	51	39	31	26	49	37	30	26	35	29	25	32	27	23	30	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333585-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	3.0
10°-20°	442.7	8.5
20°-30°	642.0	12.3
30°-40°	731.6	14.0
40°-50°	713.2	13.7
50°-60°	600.3	11.5
60°-70°	420.8	8.1
70°-80°	216.3	4.1
80°-90°	55.6	1.1
90°-100°	119.8	2.3
100°-110°	257.4	4.9
110°-120°	241.6	4.6
120°-130°	195.8	3.8
130°-140°	157.1	3.0
140°-150°	118.6	2.3
150°-160°	83.5	1.6
160°-170°	49.2	0.9
170°-180°	16.0	0.3
0°-30°	1243.1	23.8
0°-40°	1974.7	37.8
0°-60°	3288.2	63.0
0°-90°	3980.9	76.3
90°-120°	618.8	11.9
90°-150°	1090.3	20.9
90°-180°	1239.0	23.7
0°-180°	5219.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	0	3	5	7	8	4
95°	11	32	295	134	78	12
105°	38	53	242	476	441	40
115°	67	81	194	418	492	66
125°	93	109	186	332	387	83
135°	109	131	184	279	322	85
145°	127	146	185	231	254	80
155°	145	156	181	204	213	67
165°	158	163	173	184	186	45
175°	165	165	166	168	168	16
180°	165	165	165	165	165	



TEST NUMBER: P333585-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.5	22.0	20.5	19.0	17.6	16.9	16.7	16.6	16.4	16.3	16.4
90°	0.4	0.7	1.3	2.0	2.6	3.3	3.7	4.3	4.6	5.4	5.7
92.5°	4.1	4.9	7.7	11.9	17.6	27.3	45.5	76.0	109.1	107.4	86.9
95°	11.0	11.3	13.9	17.6	25.0	40.0	75.6	148.9	240.8	295.1	288.8
97.5°	18.3	18.7	20.5	24.2	30.8	41.6	65.1	118.9	215.1	315.2	365.4
100°	23.3	23.9	25.4	28.9	35.3	45.3	64.7	107.9	191.9	300.8	384.1
102.5°	28.9	29.3	30.3	34.3	40.2	49.9	67.0	103.4	174.3	275.5	372.9
105°	37.6	37.6	39.3	42.6	48.0	57.3	71.9	101.6	157.2	241.5	337.1
107.5°	46.2	46.8	48.4	51.2	56.7	65.1	79.3	104.6	150.1	218.1	300.6
110°	52.3	53.0	54.3	57.3	62.3	71.0	84.6	107.6	147.9	207.2	279.8



TEST NUMBER: P333585-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	58.4	59.1	60.1	63.2	68.1	76.5	89.6	111.3	147.9	200.8	264.4
115°	67.3	68.0	69.0	71.9	76.9	85.3	97.6	116.9	148.9	193.9	247.5
117.5°	75.3	76.3	77.4	80.3	86.1	94.1	105.8	123.3	151.1	190.5	237.4
120°	80.6	81.6	82.9	86.0	91.6	99.9	111.6	127.6	153.3	188.9	231.9
122.5°	86.2	86.9	88.0	91.0	97.2	105.6	117.2	132.3	155.0	187.6	227.1
125°	93.3	94.0	95.6	98.6	104.9	113.6	124.6	138.9	158.3	185.9	220.6
127.5°	98.8	99.8	101.9	105.8	112.4	121.1	131.7	144.9	161.7	185.1	214.5
130°	102.3	103.3	105.9	110.3	117.3	125.9	136.2	148.9	163.9	184.5	210.6
132.5°	104.9	106.2	109.4	114.2	121.5	130.2	140.5	152.4	166.3	184.5	207.4
135°	109.2	110.6	114.6	119.9	127.0	135.9	146.2	157.2	169.6	184.5	203.5
137.5°	114.7	115.7	119.4	124.8	131.7	140.9	150.3	160.8	172.6	184.9	200.1
140°	117.9	118.9	122.9	128.3	134.6	143.5	153.3	163.2	173.9	185.2	198.5
142.5°	121.7	122.3	126.1	131.5	137.5	146.0	155.0	164.6	174.7	185.5	197.2
145°	127.2	127.9	131.2	135.9	141.9	149.6	158.3	166.5	175.5	185.2	195.2
147.5°	133.1	133.5	136.4	140.7	145.9	152.6	160.2	167.8	175.9	184.4	193.1
150°	136.6	137.2	139.6	143.9	148.5	154.2	161.6	168.5	175.9	183.5	191.5
152.5°	140.3	140.7	142.8	146.6	151.0	156.1	162.9	169.1	175.6	182.5	189.6
155°	145.2	145.2	147.2	150.5	153.9	158.5	164.2	169.6	174.8	180.6	186.5
157.5°	149.7	149.6	151.2	154.0	156.9	160.5	165.3	169.8	174.0	178.5	183.6
160°	152.6	152.2	153.5	155.9	158.5	161.6	165.9	169.8	173.2	177.2	181.3
162.5°	155.0	154.7	156.0	158.1	160.1	162.6	166.5	169.7	172.4	175.6	179.1
165°	158.5	157.9	158.9	160.5	161.9	163.9	166.5	169.2	171.3	173.2	175.9
167.5°	161.0	160.6	161.3	162.1	163.1	164.4	166.5	168.4	169.4	170.9	172.8
170°	162.6	162.2	162.6	163.2	163.9	164.9	166.5	167.9	168.5	169.6	170.9
172.5°	163.6	163.1	163.3	164.0	164.4	164.9	166.3	167.4	167.5	168.0	169.0
175°	164.9	164.2	164.6	164.9	164.9	164.9	165.9	166.5	166.3	166.3	166.5
177.5°	165.5	164.9	164.9	165.2	164.9	164.9	165.5	165.8	165.2	165.2	165.5
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333585-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	16.5	16.5	16.6	16.6	16.4	16.2	16.0	15.7
90°	6.0	6.3	6.7	7.4	7.4	7.4	7.6	7.6
92.5°	59.0	42.8	32.2	27.3	23.1	22.2	21.8	21.2
95°	239.5	188.9	147.9	119.9	96.2	86.2	83.6	78.3
97.5°	356.7	321.2	281.3	242.3	221.8	203.1	193.5	189.2
100°	409.7	393.4	359.1	324.4	301.4	277.5	265.1	259.9
102.5°	427.5	437.6	421.2	397.8	373.2	356.1	342.7	338.7
105°	417.1	462.7	477.3	473.7	463.0	452.0	445.4	441.4
107.5°	379.5	440.4	478.0	495.4	500.8	500.8	498.5	495.9
110°	351.8	415.1	462.0	490.3	505.3	511.6	514.0	514.0



TEST NUMBER: P333585-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.9	390.0	437.5	470.9	492.8	503.7	509.4	511.9
115°	302.5	354.1	399.7	436.0	462.0	478.0	487.3	491.6
117.5°	284.7	329.2	368.5	401.9	427.8	444.4	453.6	456.3
120°	275.1	315.1	351.8	381.1	405.8	421.7	430.7	433.4
122.5°	268.0	305.0	337.6	365.0	387.1	401.7	410.8	413.1
125°	257.5	291.4	320.5	344.4	363.1	376.7	384.1	387.4
127.5°	246.9	278.5	305.6	328.0	345.0	357.0	363.9	365.4
130°	240.2	269.5	295.5	317.2	333.8	344.8	351.5	353.5
132.5°	233.5	261.0	284.6	305.4	322.1	333.0	339.1	341.4
135°	224.9	247.8	269.2	288.1	302.8	313.8	319.8	321.8
137.5°	217.5	236.1	253.8	269.9	283.0	293.0	298.6	300.8
140°	213.5	229.1	244.5	258.4	270.8	279.5	284.5	286.2
142.5°	210.1	223.3	236.5	248.6	259.1	266.5	271.2	272.6
145°	205.6	215.8	226.2	235.2	243.2	248.8	252.5	253.8
147.5°	201.2	209.6	217.6	224.4	230.7	235.3	237.3	238.0
150°	198.9	206.2	212.5	218.5	223.5	227.5	228.8	229.1
152.5°	196.2	202.7	208.5	213.2	217.4	220.6	221.9	222.3
155°	192.2	197.6	202.2	205.9	209.2	211.5	212.5	212.8
157.5°	188.2	192.6	196.2	199.1	201.7	203.6	204.5	204.4
160°	185.6	188.9	192.2	194.5	196.9	198.5	199.2	198.9
162.5°	182.6	185.7	188.5	190.6	192.4	193.7	193.9	193.8
165°	178.5	180.9	182.9	184.5	185.9	186.5	186.5	186.5
167.5°	174.7	176.3	177.8	179.0	179.6	180.2	179.9	179.8
170°	172.6	173.5	174.6	175.2	175.9	176.3	176.3	175.9
172.5°	170.1	171.2	171.9	172.3	172.4	173.1	172.5	172.1
175°	167.6	167.6	168.2	168.2	168.2	168.5	167.9	167.6
177.5°	165.8	166.0	166.0	166.0	165.8	166.0	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2

(END OF REPORT)