

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333628-830

Luminaire Tested: **S125RDIP-S1270D1035U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333628-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1035U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8538.2 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	57	59	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	46	41	38	38	36	33	30
5	70	59	51	45	65	55	48	42	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11559	11559	11559	11559
5°	13299	11575	10222	11575
10°	15255	11516	9020	11516
15°	16477	11397	8017	11397
20°	18168	11260	7403	11260
25°	21026	11078	6869	11078
30°	22881	10887	6520	10887
35°	19301	10664	6199	10664
40°	13478	10264	5922	10264
45°	9999	9724	5650	9724
50°	7973	9161	5419	9161
55°	6767	8463	5212	8463
60°	5846	7839	4879	7839
65°	5210	7163	4199	7163
70°	4577	6562	3828	6562
75°	3960	5682	3593	5682
80°	3005	4783	3005	4783
85°	2505	3757	2831	3757



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.6	2.0
10°-20°	503.0	5.9
20°-30°	797.5	9.3
30°-40°	961.7	11.3
40°-50°	858.8	10.1
50°-60°	658.6	7.7
60°-70°	428.0	5.0
70°-80°	208.1	2.4
80°-90°	52.3	0.6
90°-100°	46.1	0.5
100°-110°	284.3	3.3
110°-120°	515.7	6.0
120°-130°	661.8	7.8
130°-140°	711.8	8.3
140°-150°	668.2	7.8
150°-160°	540.5	6.3
160°-170°	349.6	4.1
170°-180°	120.6	1.4
0°-30°	1472.1	17.2
0°-40°	2433.8	28.5
0°-60°	3951.3	46.3
0°-90°	4639.7	54.3
90°-120°	846.1	9.9
90°-150°	2887.9	33.8
90°-180°	3899.0	45.7
0°-180°	8538.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1790	1790	1790	1790	1790	
5°	2051	1785	1577	1785	2051	205
15°	2464	1705	1199	1705	2464	706
25°	2951	1555	964	1555	2951	1355
35°	2448	1353	786	1353	2448	1479
45°	1095	1065	619	1065	1095	874
55°	601	752	463	752	601	545
65°	341	469	275	469	341	339
75°	159	228	144	228	159	169
85°	34	51	38	51	34	39
90°	23	1	23	1	23	11
95°	20	54	20	54	20	16
105°	280	277	280	277	280	253
115°	516	520	516	520	516	512
125°	739	739	739	739	739	657
135°	918	921	918	921	918	708
145°	1065	1068	1065	1068	1065	665
155°	1168	1176	1168	1176	1168	538
165°	1235	1241	1235	1241	1235	348
175°	1264	1270	1264	1270	1264	120
180°	1270	1270	1270	1270	1270	



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1882.6	1881.5	1883.9	1877.4	1877.9	1867.9	1867.9	1860.3	1850.3	1842.7	1839.2
5°	2051.3	2052.9	2049.8	2038.8	2031.6	2020.5	2008.0	1985.9	1967.6	1949.9	1936.0
7.5°	2225.1	2226.1	2216.4	2213.0	2194.4	2180.9	2153.1	2123.2	2096.6	2062.8	2036.9
10°	2326.1	2325.4	2315.1	2307.1	2290.8	2270.3	2243.2	2207.8	2174.8	2138.1	2102.8
12.5°	2384.9	2383.0	2379.7	2369.9	2354.9	2336.8	2313.7	2279.0	2238.3	2198.0	2156.8
15°	2464.3	2459.1	2449.6	2437.0	2415.7	2394.4	2368.7	2337.9	2299.0	2253.4	2215.2
17.5°	2562.4	2562.6	2547.9	2530.5	2501.6	2464.0	2424.3	2374.5	2321.6	2271.4	2230.8
20°	2643.5	2641.3	2626.7	2592.8	2559.8	2512.7	2467.2	2406.2	2341.6	2276.1	2225.4
22.5°	2760.0	2754.2	2738.9	2694.5	2643.3	2582.7	2513.0	2438.5	2360.4	2286.1	2219.6
25°	2950.6	2946.2	2916.1	2864.7	2792.7	2699.3	2608.3	2506.1	2393.8	2296.0	2215.2
27.5°	3081.2	3076.3	3053.9	3011.2	2944.8	2846.6	2723.3	2586.8	2446.5	2312.1	2195.5
30°	3068.2	3079.2	3076.3	3056.5	3006.5	2918.3	2804.4	2650.9	2484.1	2326.1	2187.3
32.5°	2883.6	2893.5	2919.3	2958.3	2961.2	2925.9	2840.9	2699.1	2526.4	2346.7	2180.8
35°	2448.1	2461.4	2511.3	2589.9	2692.7	2778.7	2796.3	2720.0	2564.9	2371.7	2171.1
37.5°	1882.1	1954.4	1996.4	2079.2	2234.6	2392.7	2544.8	2600.8	2534.8	2361.4	2155.4
40°	1598.7	1616.4	1691.3	1784.6	1915.4	2080.0	2296.8	2453.2	2458.3	2337.9	2130.7
42.5°	1368.4	1390.7	1442.1	1516.6	1628.6	1793.2	2016.9	2223.5	2319.1	2273.2	2098.4
45°	1094.8	1111.6	1149.1	1206.5	1292.4	1428.3	1620.8	1859.5	2049.2	2123.4	2011.7
47.5°	899.3	908.4	941.0	984.7	1048.3	1147.4	1296.4	1503.6	1731.0	1890.5	1874.7
50°	793.5	803.8	828.8	861.9	915.5	999.2	1118.2	1290.9	1525.3	1720.0	1759.0
52.5°	711.2	719.7	735.3	766.6	810.9	875.2	971.3	1127.5	1338.4	1545.4	1635.5
55°	601.0	606.9	619.3	637.0	672.3	718.6	801.5	909.6	1080.1	1288.7	1421.0
57.5°	510.2	513.1	521.0	537.3	561.8	595.6	655.5	747.1	869.3	1057.2	1203.2
60°	452.6	455.5	465.8	476.8	496.0	526.8	573.8	637.7	755.3	910.3	1058.0
62.5°	406.7	408.5	412.9	424.0	440.7	464.5	501.5	553.6	647.1	783.3	922.8
65°	340.9	341.7	343.1	351.9	362.2	379.8	404.1	440.8	511.3	614.3	737.6
67.5°	277.8	278.7	283.9	287.0	297.7	307.0	321.2	349.3	399.0	468.3	564.3
70°	242.4	241.8	246.9	250.5	254.2	265.2	274.8	297.6	328.4	381.4	461.4
72.5°	209.5	207.6	209.8	211.1	216.0	223.5	233.1	247.0	270.8	307.3	368.5
75°	158.7	159.5	159.5	160.9	164.6	167.5	170.4	177.8	191.1	215.3	248.4
77.5°	111.4	110.2	113.3	113.8	115.9	119.1	121.7	124.6	130.1	140.1	157.1
80°	80.8	80.8	81.5	83.8	83.0	84.5	88.1	91.1	97.7	103.6	109.4
82.5°	62.0	61.5	62.1	62.6	62.5	63.9	65.2	65.8	68.3	71.3	75.4
85°	33.8	33.8	34.5	34.5	35.3	35.3	36.0	36.0	36.0	36.8	37.5
87.5°	17.4	16.8	16.0	15.9	16.4	17.3	16.6	15.7	15.6	15.4	15.6
90°	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2	16.1	15.1	13.6
92.5°	21.1	20.8	20.5	20.2	19.9	19.2	18.2	17.2	16.1	15.1	13.8
95°	19.8	19.8	19.8	19.8	19.8	19.2	18.2	17.2	16.1	15.1	23.0
97.5°	19.8	19.8	19.8	19.8	19.8	22.7	28.7	34.5	40.4	46.3	62.0
100°	19.8	20.6	21.4	22.2	23.1	39.1	70.3	101.4	132.6	163.7	162.9
102.5°	118.4	132.6	146.8	161.1	175.3	185.3	191.2	197.1	203.0	209.0	208.4
105°	279.5	279.7	279.9	280.1	280.3	280.4	280.4	280.4	280.4	280.4	280.4
107.5°	352.3	353.0	353.6	354.2	354.9	355.2	355.2	355.1	355.1	355.0	354.6
110°	402.7	402.6	402.4	402.2	402.0	402.2	402.7	403.4	404.1	404.6	404.3



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	448.0	448.3	448.6	448.8	449.1	449.7	450.4	451.3	452.0	452.9	452.6
115°	515.8	517.0	518.2	519.5	520.8	521.8	522.6	523.5	524.3	525.1	524.9
117.5°	588.0	588.5	589.1	589.7	590.1	591.0	592.1	593.1	594.3	595.3	594.6
120°	632.4	633.5	634.5	635.6	636.6	637.3	637.7	638.2	638.6	639.0	638.4
122.5°	674.6	675.8	677.0	678.3	679.4	680.2	680.7	681.1	681.5	681.9	681.6
125°	738.8	739.4	740.0	740.6	741.3	742.0	742.8	743.7	744.5	745.4	745.4
127.5°	792.8	794.4	795.9	797.4	799.0	799.9	800.4	800.9	801.3	801.8	801.9
130°	831.9	833.0	834.1	835.1	836.1	837.0	837.5	838.2	838.9	839.4	839.2
132.5°	868.1	869.1	870.2	871.2	872.2	872.8	873.0	873.1	873.2	873.4	873.8
135°	917.6	918.8	920.1	921.3	922.6	923.4	923.9	924.3	924.6	925.1	925.5
137.5°	967.2	968.4	969.4	970.5	971.6	972.1	972.0	971.9	971.9	971.8	972.1
140°	996.6	997.9	999.1	1000.4	1001.6	1002.0	1001.6	1001.3	1000.8	1000.4	1000.6
142.5°	1024.4	1025.8	1027.0	1028.2	1029.5	1030.1	1030.0	1029.9	1029.8	1029.7	1029.4
145°	1065.4	1066.6	1067.8	1069.1	1070.4	1070.8	1070.6	1070.4	1070.3	1070.1	1070.1
147.5°	1099.0	1100.5	1102.0	1103.5	1105.0	1105.7	1105.4	1105.1	1104.9	1104.7	1104.4
150°	1120.9	1122.5	1124.2	1125.9	1127.6	1128.1	1127.8	1127.4	1126.9	1126.5	1126.1
152.5°	1141.1	1142.6	1144.2	1145.7	1147.2	1147.7	1147.4	1146.9	1146.5	1146.0	1145.7
155°	1167.9	1169.6	1171.2	1172.9	1174.6	1175.2	1174.5	1173.8	1173.3	1172.6	1172.1
157.5°	1190.3	1191.9	1193.6	1195.3	1197.0	1197.5	1196.8	1196.2	1195.5	1194.9	1194.8
160°	1204.6	1206.3	1208.0	1209.7	1211.3	1211.7	1210.9	1210.0	1209.2	1208.3	1208.2
162.5°	1217.4	1219.3	1221.1	1222.9	1224.7	1225.1	1223.9	1222.8	1221.6	1220.4	1220.2
165°	1234.7	1236.4	1238.0	1239.7	1241.4	1241.6	1240.4	1239.1	1237.8	1236.6	1236.4
167.5°	1246.8	1248.7	1250.6	1252.5	1254.3	1254.5	1253.0	1251.5	1250.0	1248.5	1248.2
170°	1253.6	1255.5	1257.4	1259.1	1261.0	1261.2	1259.5	1257.8	1256.1	1254.5	1254.2
172.5°	1258.1	1259.9	1261.8	1263.7	1265.6	1265.7	1264.2	1262.7	1261.2	1259.7	1259.3
175°	1263.9	1265.7	1267.6	1269.5	1271.4	1271.5	1269.9	1268.2	1266.5	1264.8	1264.6
177.5°	1267.2	1268.7	1270.0	1271.3	1272.6	1272.7	1271.6	1270.4	1269.2	1268.0	1267.9
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1839.2	1835.0	1827.4	1820.3	1811.6	1803.9	1798.6	1792.2	1784.0	1774.0	1765.7
5°	1920.5	1904.4	1883.1	1864.7	1841.3	1822.9	1803.7	1785.4	1767.0	1743.5	1723.0
7.5°	2010.8	1977.5	1944.9	1904.1	1867.1	1834.0	1802.2	1770.1	1738.6	1705.2	1673.1
10°	2066.1	2025.6	1980.8	1929.4	1882.4	1837.6	1796.4	1756.0	1713.4	1675.9	1635.5
12.5°	2117.8	2065.6	2014.3	1949.4	1892.9	1838.1	1785.8	1735.4	1689.9	1641.2	1597.9
15°	2164.5	2113.1	2055.8	1976.4	1897.8	1831.6	1769.9	1704.6	1647.9	1593.7	1545.1
17.5°	2182.6	2128.6	2062.1	1985.8	1899.9	1816.7	1737.2	1665.5	1598.9	1535.6	1481.0
20°	2175.5	2123.4	2055.0	1982.3	1890.5	1803.7	1717.8	1638.4	1564.2	1497.3	1439.4
22.5°	2158.5	2104.5	2038.5	1961.7	1874.5	1782.6	1690.7	1606.1	1528.3	1459.2	1395.8
25°	2132.9	2059.5	1991.9	1916.8	1833.9	1742.8	1647.9	1554.6	1471.7	1401.1	1332.1
27.5°	2106.3	2014.6	1928.6	1854.2	1766.4	1685.2	1593.7	1498.1	1410.8	1339.0	1268.1
30°	2082.2	1979.3	1884.5	1800.1	1717.0	1639.9	1553.2	1459.9	1370.3	1296.1	1224.1
32.5°	2052.2	1942.9	1838.7	1741.3	1661.2	1584.7	1506.2	1417.0	1329.7	1253.1	1180.0
35°	2014.6	1875.0	1761.9	1658.3	1569.3	1495.2	1424.7	1352.6	1265.2	1185.8	1114.6
37.5°	1965.2	1806.9	1675.9	1563.0	1469.3	1394.8	1339.1	1273.3	1193.4	1117.5	1051.4
40°	1935.2	1757.5	1614.2	1502.5	1404.0	1325.4	1273.3	1217.5	1144.7	1073.5	1007.3
42.5°	1895.3	1712.2	1551.9	1435.5	1336.4	1260.7	1208.1	1159.2	1098.3	1031.1	960.3
45°	1816.9	1624.5	1456.2	1331.3	1231.4	1157.2	1108.0	1064.6	1018.3	956.6	894.8
47.5°	1715.0	1533.0	1356.9	1220.5	1122.7	1053.8	1006.0	971.8	938.7	886.2	826.2
50°	1633.3	1457.7	1285.7	1153.5	1049.1	983.8	939.0	911.8	881.7	833.9	783.9
52.5°	1536.9	1380.1	1211.7	1076.5	978.1	916.8	873.7	846.6	821.7	782.8	735.2
55°	1385.0	1247.5	1093.3	970.5	880.2	818.5	777.3	751.6	737.0	703.9	666.4
57.5°	1209.7	1111.2	975.2	856.9	776.9	716.0	685.8	663.9	647.3	624.0	597.5
60°	1087.4	1018.3	896.4	783.9	710.5	652.4	625.3	606.9	591.4	571.7	551.0
62.5°	963.4	913.1	807.0	710.5	642.9	594.3	568.8	552.2	534.4	521.0	501.1
65°	797.2	752.3	678.9	603.2	540.7	501.8	483.4	468.7	457.7	443.0	429.0
67.5°	620.1	601.9	551.2	499.0	454.2	419.5	403.7	393.4	380.1	371.4	361.7
70°	511.3	502.6	466.6	432.1	390.1	366.6	351.9	347.5	331.4	322.5	315.9
72.5°	415.0	410.9	390.1	366.2	336.7	316.0	302.6	297.6	287.3	280.2	276.0
75°	284.4	285.8	282.1	266.7	255.7	242.4	230.7	227.7	220.5	214.5	210.8
77.5°	179.8	187.4	187.7	186.9	182.5	174.5	169.6	167.4	160.1	158.0	157.1
80°	123.5	131.5	138.8	138.1	136.7	134.5	130.8	128.6	124.9	122.7	121.2
82.5°	82.3	89.8	96.0	99.9	99.6	97.5	94.9	93.9	93.1	91.5	91.2
85°	38.9	40.4	42.6	47.8	51.5	52.1	51.5	50.7	48.4	49.2	50.0
87.5°	15.9	15.6	15.9	15.6	14.7	17.3	18.8	19.0	18.2	17.3	16.5
90°	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9	2.6	4.2	5.9
92.5°	12.4	11.1	9.9	9.8	10.9	12.2	13.3	14.5	13.3	12.2	10.9
95°	30.9	38.9	46.8	51.2	51.7	52.4	53.0	53.6	53.0	52.4	51.7
97.5°	77.8	93.5	109.2	116.5	115.4	114.2	113.1	112.0	113.1	114.2	115.4
100°	162.1	161.3	160.4	159.7	159.0	158.4	157.8	157.1	157.8	158.4	159.0
102.5°	207.9	207.5	206.9	206.2	205.5	204.7	203.9	203.1	203.9	204.7	205.5
105°	280.4	280.4	280.4	280.0	279.2	278.3	277.5	276.6	277.5	278.3	279.2
107.5°	354.1	353.7	353.3	353.1	353.1	353.1	353.1	353.1	353.1	353.1	353.1
110°	403.9	403.4	403.0	402.7	402.7	402.7	402.7	402.7	402.7	402.7	402.7



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	452.3	452.1	451.9	451.5	451.0	450.4	450.0	449.5	450.0	450.4	451.0
115°	524.7	524.5	524.3	523.7	522.6	521.6	520.6	519.5	520.6	521.6	522.6
117.5°	593.7	593.0	592.2	591.8	591.8	591.8	591.9	591.9	591.9	591.8	591.8
120°	637.7	637.2	636.5	636.3	636.5	636.7	636.9	637.2	636.9	636.7	636.5
122.5°	681.4	681.1	680.7	680.2	679.4	678.6	677.8	677.0	677.8	678.6	679.4
125°	745.4	745.4	745.4	744.6	743.2	741.7	740.2	738.8	740.2	741.7	743.2
127.5°	802.1	802.2	802.3	801.8	800.8	799.7	798.7	797.7	798.7	799.7	800.8
130°	839.1	838.9	838.6	838.0	837.0	835.9	834.9	833.8	834.9	835.9	837.0
132.5°	874.3	874.7	875.2	874.8	873.5	872.4	871.2	870.0	871.2	872.4	873.5
135°	926.0	926.3	926.8	926.3	925.1	923.9	922.6	921.3	922.6	923.9	925.1
137.5°	972.5	972.9	973.3	972.9	971.9	970.7	969.7	968.6	969.7	970.7	971.9
140°	1000.8	1001.0	1001.3	1001.1	1000.7	1000.3	999.8	999.5	999.8	1000.3	1000.7
142.5°	1029.2	1028.9	1028.6	1028.3	1028.0	1027.8	1027.6	1027.3	1027.6	1027.8	1028.0
145°	1070.1	1070.1	1070.1	1069.8	1069.4	1068.9	1068.6	1068.2	1068.6	1068.9	1069.4
147.5°	1104.2	1103.9	1103.6	1103.5	1103.6	1103.7	1103.8	1103.9	1103.8	1103.7	1103.6
150°	1125.7	1125.2	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5	1126.1	1125.7	1125.2
152.5°	1145.2	1144.8	1144.4	1144.6	1145.6	1146.5	1147.5	1148.3	1147.5	1146.5	1145.6
155°	1171.8	1171.4	1170.9	1171.4	1172.6	1173.8	1175.2	1176.4	1175.2	1173.8	1172.6
157.5°	1194.8	1194.7	1194.7	1195.0	1195.8	1196.6	1197.2	1198.0	1197.2	1196.6	1195.8
160°	1208.0	1207.8	1207.5	1208.1	1209.3	1210.6	1211.8	1213.1	1211.8	1210.6	1209.3
162.5°	1220.0	1219.7	1219.6	1220.1	1221.3	1222.6	1223.9	1225.1	1223.9	1222.6	1221.3
165°	1236.1	1236.0	1235.8	1236.3	1237.6	1238.8	1240.0	1241.3	1240.0	1238.8	1237.6
167.5°	1248.0	1247.8	1247.6	1248.2	1249.4	1250.8	1252.1	1253.4	1252.1	1250.8	1249.4
170°	1254.1	1253.9	1253.7	1254.2	1255.7	1257.2	1258.7	1260.1	1258.7	1257.2	1255.7
172.5°	1259.0	1258.6	1258.3	1258.8	1260.3	1261.7	1263.2	1264.6	1263.2	1261.7	1260.3
175°	1264.4	1264.2	1264.0	1264.5	1265.7	1267.1	1268.3	1269.5	1268.3	1267.1	1265.7
177.5°	1267.7	1267.5	1267.3	1267.8	1268.8	1269.8	1270.8	1271.8	1270.8	1269.8	1268.8
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1759.8	1751.6	1745.7	1733.9	1725.7	1722.2	1715.7	1713.9	1720.4	1715.7	1715.1
5°	1707.5	1686.2	1669.3	1652.4	1634.0	1622.3	1604.7	1601.7	1597.3	1590.6	1589.2
7.5°	1644.7	1617.0	1595.3	1567.4	1543.0	1523.5	1501.5	1491.0	1485.4	1476.8	1465.4
10°	1602.4	1569.3	1540.0	1512.0	1482.0	1457.7	1435.7	1418.7	1407.7	1397.4	1393.1
12.5°	1560.7	1527.0	1489.4	1455.7	1422.0	1394.8	1370.4	1359.4	1347.2	1335.1	1324.8
15°	1495.9	1451.0	1409.9	1371.0	1342.4	1313.0	1289.4	1273.3	1254.9	1249.8	1229.9
17.5°	1427.1	1383.2	1335.0	1294.0	1260.7	1228.4	1202.6	1184.2	1170.4	1151.5	1142.4
20°	1384.2	1332.1	1285.1	1247.5	1210.8	1172.6	1146.1	1130.8	1117.5	1102.1	1094.8
22.5°	1338.4	1287.4	1239.2	1195.2	1157.9	1120.3	1101.5	1085.5	1070.4	1056.2	1046.5
25°	1271.1	1219.7	1168.9	1123.4	1084.5	1057.2	1035.2	1016.8	1008.8	994.9	984.5
27.5°	1204.5	1149.8	1097.2	1051.8	1021.2	994.4	976.3	961.8	947.2	935.0	926.0
30°	1161.6	1105.8	1048.5	1012.5	980.1	954.4	934.5	920.6	909.6	898.5	891.9
32.5°	1118.7	1061.1	1010.2	971.3	940.8	918.5	898.1	884.8	873.2	860.9	853.2
35°	1049.9	991.2	950.0	911.8	881.7	861.1	847.2	828.0	818.5	809.6	801.5
37.5°	986.0	931.3	886.8	853.3	827.2	806.7	788.6	778.4	766.6	758.7	752.0
40°	939.0	889.0	848.6	813.3	794.3	771.5	754.6	741.3	732.5	722.3	714.9
42.5°	896.6	850.3	811.0	779.3	755.4	736.2	719.9	706.6	695.5	688.2	681.9
45°	836.9	790.6	752.3	722.9	701.0	682.6	665.6	659.0	644.3	635.6	632.6
47.5°	775.0	733.6	696.6	669.6	647.0	629.6	613.8	600.3	592.2	583.5	578.8
50°	733.3	693.6	659.0	632.6	610.6	591.4	576.7	568.0	556.9	548.8	543.0
52.5°	691.5	654.8	620.3	594.9	575.9	556.8	540.4	531.5	521.0	515.9	511.8
55°	631.9	593.0	563.5	538.6	518.7	501.1	485.7	476.8	470.2	465.1	463.6
57.5°	564.3	533.4	506.1	483.6	463.0	446.4	432.9	424.5	418.7	417.9	413.5
60°	520.2	492.3	467.3	443.0	425.4	410.0	398.2	388.7	382.8	382.0	380.6
62.5°	476.1	449.3	426.1	404.8	389.0	374.1	363.0	352.2	348.7	345.1	341.8
65°	410.7	386.4	367.4	350.4	333.6	321.0	310.1	303.4	295.4	291.0	282.9
67.5°	346.5	327.7	309.3	295.1	281.8	269.9	260.8	251.0	245.5	242.0	236.1
70°	304.2	289.5	271.1	255.7	245.4	235.8	228.5	217.4	213.8	210.8	207.9
72.5°	264.2	251.3	235.8	223.4	213.1	204.1	195.6	190.4	186.8	183.8	182.1
75°	207.9	195.5	182.2	173.4	166.1	158.7	154.3	150.6	149.1	148.5	145.4
77.5°	152.7	146.1	135.4	128.5	123.6	120.6	116.7	114.8	114.6	111.4	110.4
80°	116.8	113.1	104.3	101.4	97.7	94.8	92.6	88.9	85.2	83.8	81.5
82.5°	86.8	83.1	79.6	74.9	71.8	70.1	67.9	66.5	67.0	64.9	63.9
85°	46.3	42.6	41.2	40.4	38.9	40.4	39.7	38.9	38.2	37.5	38.2
87.5°	16.2	16.5	16.2	17.7	16.2	17.2	17.3	17.0	17.2	17.3	17.0
90°	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2	18.2	19.2	20.1
92.5°	9.8	9.9	11.1	12.4	13.8	15.1	16.1	17.2	18.2	19.2	19.9
95°	51.2	46.8	38.9	30.9	23.0	15.1	16.1	17.2	18.2	19.2	19.8
97.5°	116.5	109.2	93.5	77.8	62.0	46.3	40.4	34.5	28.7	22.7	19.8
100°	159.7	160.4	161.3	162.1	162.9	163.7	132.6	101.4	70.3	39.1	23.1
102.5°	206.2	206.9	207.5	207.9	208.4	209.0	203.0	197.1	191.2	185.3	175.3
105°	280.0	280.4	280.4	280.4	280.4	280.4	280.4	280.4	280.4	280.4	280.3
107.5°	353.1	353.3	353.7	354.1	354.6	355.0	355.1	355.1	355.2	355.2	354.9
110°	402.7	403.0	403.4	403.9	404.3	404.6	404.1	403.4	402.7	402.2	402.0



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	451.5	451.9	452.1	452.3	452.6	452.9	452.0	451.3	450.4	449.7	449.1
115°	523.7	524.3	524.5	524.7	524.9	525.1	524.3	523.5	522.6	521.8	520.8
117.5°	591.8	592.2	593.0	593.7	594.6	595.3	594.3	593.1	592.1	591.0	590.1
120°	636.3	636.5	637.2	637.7	638.4	639.0	638.6	638.2	637.7	637.3	636.6
122.5°	680.2	680.7	681.1	681.4	681.6	681.9	681.5	681.1	680.7	680.2	679.4
125°	744.6	745.4	745.4	745.4	745.4	745.4	744.5	743.7	742.8	742.0	741.3
127.5°	801.8	802.3	802.2	802.1	801.9	801.8	801.3	800.9	800.4	799.9	799.0
130°	838.0	838.6	838.9	839.1	839.2	839.4	838.9	838.2	837.5	837.0	836.1
132.5°	874.8	875.2	874.7	874.3	873.8	873.4	873.2	873.1	873.0	872.8	872.2
135°	926.3	926.8	926.3	926.0	925.5	925.1	924.6	924.3	923.9	923.4	922.6
137.5°	972.9	973.3	972.9	972.5	972.1	971.8	971.9	971.9	972.0	972.1	971.6
140°	1001.1	1001.3	1001.0	1000.8	1000.6	1000.4	1000.8	1001.3	1001.6	1002.0	1001.6
142.5°	1028.3	1028.6	1028.9	1029.2	1029.4	1029.7	1029.8	1029.9	1030.0	1030.1	1029.5
145°	1069.8	1070.1	1070.1	1070.1	1070.1	1070.1	1070.3	1070.4	1070.6	1070.8	1070.4
147.5°	1103.5	1103.6	1103.9	1104.2	1104.4	1104.7	1104.9	1105.1	1105.4	1105.7	1105.0
150°	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5	1126.9	1127.4	1127.8	1128.1	1127.6
152.5°	1144.6	1144.4	1144.8	1145.2	1145.7	1146.0	1146.5	1146.9	1147.4	1147.7	1147.2
155°	1171.4	1170.9	1171.4	1171.8	1172.1	1172.6	1173.3	1173.8	1174.5	1175.2	1174.6
157.5°	1195.0	1194.7	1194.7	1194.8	1194.8	1194.9	1195.5	1196.2	1196.8	1197.5	1197.0
160°	1208.1	1207.5	1207.8	1208.0	1208.2	1208.3	1209.2	1210.0	1210.9	1211.7	1211.3
162.5°	1220.1	1219.6	1219.7	1220.0	1220.2	1220.4	1221.6	1222.8	1223.9	1225.1	1224.7
165°	1236.3	1235.8	1236.0	1236.1	1236.4	1236.6	1237.8	1239.1	1240.4	1241.6	1241.4
167.5°	1248.2	1247.6	1247.8	1248.0	1248.2	1248.5	1250.0	1251.5	1253.0	1254.5	1254.3
170°	1254.2	1253.7	1253.9	1254.1	1254.2	1254.5	1256.1	1257.8	1259.5	1261.2	1261.0
172.5°	1258.8	1258.3	1258.6	1259.0	1259.3	1259.7	1261.2	1262.7	1264.2	1265.7	1265.6
175°	1264.5	1264.0	1264.2	1264.4	1264.6	1264.8	1266.5	1268.2	1269.9	1271.5	1271.4
177.5°	1267.8	1267.3	1267.5	1267.7	1267.9	1268.0	1269.2	1270.4	1271.6	1272.7	1272.6
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1714.6	1708.1	1706.3	1708.6	1706.3	1708.1	1714.6	1715.1	1715.7	1720.4	1713.9
5°	1581.9	1574.5	1578.2	1576.7	1578.2	1574.5	1581.9	1589.2	1590.6	1597.3	1601.7
7.5°	1465.2	1456.0	1446.3	1449.4	1446.3	1456.0	1465.2	1465.4	1476.8	1485.4	1491.0
10°	1383.5	1376.1	1371.7	1375.4	1371.7	1376.1	1383.5	1393.1	1397.4	1407.7	1418.7
12.5°	1314.8	1310.3	1306.5	1304.9	1306.5	1310.3	1314.8	1324.8	1335.1	1347.2	1359.4
15°	1221.1	1212.3	1208.6	1199.1	1208.6	1212.3	1221.1	1229.9	1249.8	1254.9	1273.3
17.5°	1134.8	1131.9	1122.4	1118.2	1122.4	1131.9	1134.8	1142.4	1151.5	1170.4	1184.2
20°	1083.7	1080.8	1071.2	1077.1	1071.2	1080.8	1083.7	1094.8	1102.1	1117.5	1130.8
22.5°	1041.4	1034.9	1031.8	1030.1	1031.8	1034.9	1041.4	1046.5	1056.2	1070.4	1085.5
25°	981.6	972.0	968.4	963.9	968.4	972.0	981.6	984.5	994.9	1008.8	1016.8
27.5°	921.9	916.8	911.9	910.8	911.9	916.8	921.9	926.0	935.0	947.2	961.8
30°	883.2	878.0	874.3	874.3	874.3	878.0	883.2	891.9	898.5	909.6	920.6
32.5°	848.5	844.5	840.8	840.3	840.8	844.5	848.5	853.2	860.9	873.2	884.8
35°	798.0	792.0	790.6	786.2	790.6	792.0	798.0	801.5	809.6	818.5	828.0
37.5°	745.5	740.6	740.5	740.0	740.5	740.6	745.5	752.0	758.7	766.6	778.4
40°	711.9	708.2	707.6	702.4	707.6	708.2	711.9	714.9	722.3	732.5	741.3
42.5°	676.1	674.2	671.7	669.5	671.7	674.2	676.1	681.9	688.2	695.5	706.6
45°	627.5	622.3	622.3	618.6	622.3	622.3	627.5	632.6	635.6	644.3	659.0
47.5°	577.2	573.3	573.6	569.9	573.6	573.3	577.2	578.8	583.5	592.2	600.3
50°	543.7	541.5	540.7	539.3	540.7	541.5	543.7	543.0	548.8	556.9	568.0
52.5°	510.2	509.2	512.0	508.7	512.0	509.2	510.2	511.8	515.9	521.0	531.5
55°	465.1	462.9	467.3	462.9	467.3	462.9	465.1	463.6	465.1	470.2	476.8
57.5°	413.2	411.1	415.1	412.9	415.1	411.1	413.2	413.5	417.9	418.7	424.5
60°	379.1	374.8	376.9	377.7	376.9	374.8	379.1	380.6	382.0	382.8	388.7
62.5°	338.6	335.9	337.5	334.1	337.5	335.9	338.6	341.8	345.1	348.7	352.2
65°	281.4	279.2	276.3	274.8	276.3	279.2	281.4	282.9	291.0	295.4	303.4
67.5°	236.4	231.1	231.0	232.1	231.0	231.1	236.4	236.1	242.0	245.5	251.0
70°	203.5	203.5	202.7	202.7	202.7	203.5	203.5	207.9	210.8	213.8	217.4
72.5°	180.6	180.0	178.7	178.1	178.7	180.0	180.6	182.1	183.8	186.8	190.4
75°	145.4	146.2	144.8	144.0	144.8	146.2	145.4	145.4	148.5	149.1	150.6
77.5°	107.4	104.3	105.9	104.3	105.9	104.3	107.4	110.4	111.4	114.6	114.8
80°	81.5	80.8	83.0	80.8	83.0	80.8	81.5	81.5	83.8	85.2	88.9
82.5°	64.5	63.8	64.8	63.2	64.8	63.8	64.5	63.9	64.9	67.0	66.5
85°	38.9	38.2	37.5	38.2	37.5	38.2	38.9	38.2	37.5	38.2	38.9
87.5°	17.6	17.2	17.3	17.4	17.3	17.2	17.6	17.0	17.3	17.2	17.0
90°	20.7	21.3	22.0	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2
92.5°	20.2	20.5	20.8	21.1	20.8	20.5	20.2	19.9	19.2	18.2	17.2
95°	19.8	19.8	19.8	19.8	19.8	19.8	19.8	19.8	19.2	18.2	17.2
97.5°	19.8	19.8	19.8	19.8	19.8	19.8	19.8	19.8	22.7	28.7	34.5
100°	22.2	21.4	20.6	19.8	20.6	21.4	22.2	23.1	39.1	70.3	101.4
102.5°	161.1	146.8	132.6	118.4	132.6	146.8	161.1	175.3	185.3	191.2	197.1
105°	280.1	279.9	279.7	279.5	279.7	279.9	280.1	280.3	280.4	280.4	280.4
107.5°	354.2	353.6	353.0	352.3	353.0	353.6	354.2	354.9	355.2	355.2	355.1
110°	402.2	402.4	402.6	402.7	402.6	402.4	402.2	402.0	402.2	402.7	403.4



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	448.8	448.6	448.3	448.0	448.3	448.6	448.8	449.1	449.7	450.4	451.3
115°	519.5	518.2	517.0	515.8	517.0	518.2	519.5	520.8	521.8	522.6	523.5
117.5°	589.7	589.1	588.5	588.0	588.5	589.1	589.7	590.1	591.0	592.1	593.1
120°	635.6	634.5	633.5	632.4	633.5	634.5	635.6	636.6	637.3	637.7	638.2
122.5°	678.3	677.0	675.8	674.6	675.8	677.0	678.3	679.4	680.2	680.7	681.1
125°	740.6	740.0	739.4	738.8	739.4	740.0	740.6	741.3	742.0	742.8	743.7
127.5°	797.4	795.9	794.4	792.8	794.4	795.9	797.4	799.0	799.9	800.4	800.9
130°	835.1	834.1	833.0	831.9	833.0	834.1	835.1	836.1	837.0	837.5	838.2
132.5°	871.2	870.2	869.1	868.1	869.1	870.2	871.2	872.2	872.8	873.0	873.1
135°	921.3	920.1	918.8	917.6	918.8	920.1	921.3	922.6	923.4	923.9	924.3
137.5°	970.5	969.4	968.4	967.2	968.4	969.4	970.5	971.6	972.1	972.0	971.9
140°	1000.4	999.1	997.9	996.6	997.9	999.1	1000.4	1001.6	1002.0	1001.6	1001.3
142.5°	1028.2	1027.0	1025.8	1024.4	1025.8	1027.0	1028.2	1029.5	1030.1	1030.0	1029.9
145°	1069.1	1067.8	1066.6	1065.4	1066.6	1067.8	1069.1	1070.4	1070.8	1070.6	1070.4
147.5°	1103.5	1102.0	1100.5	1099.0	1100.5	1102.0	1103.5	1105.0	1105.7	1105.4	1105.1
150°	1125.9	1124.2	1122.5	1120.9	1122.5	1124.2	1125.9	1127.6	1128.1	1127.8	1127.4
152.5°	1145.7	1144.2	1142.6	1141.1	1142.6	1144.2	1145.7	1147.2	1147.7	1147.4	1146.9
155°	1172.9	1171.2	1169.6	1167.9	1169.6	1171.2	1172.9	1174.6	1175.2	1174.5	1173.8
157.5°	1195.3	1193.6	1191.9	1190.3	1191.9	1193.6	1195.3	1197.0	1197.5	1196.8	1196.2
160°	1209.7	1208.0	1206.3	1204.6	1206.3	1208.0	1209.7	1211.3	1211.7	1210.9	1210.0
162.5°	1222.9	1221.1	1219.3	1217.4	1219.3	1221.1	1222.9	1224.7	1225.1	1223.9	1222.8
165°	1239.7	1238.0	1236.4	1234.7	1236.4	1238.0	1239.7	1241.4	1241.6	1240.4	1239.1
167.5°	1252.5	1250.6	1248.7	1246.8	1248.7	1250.6	1252.5	1254.3	1254.5	1253.0	1251.5
170°	1259.1	1257.4	1255.5	1253.6	1255.5	1257.4	1259.1	1261.0	1261.2	1259.5	1257.8
172.5°	1263.7	1261.8	1259.9	1258.1	1259.9	1261.8	1263.7	1265.6	1265.7	1264.2	1262.7
175°	1269.5	1267.6	1265.7	1263.9	1265.7	1267.6	1269.5	1271.4	1271.5	1269.9	1268.2
177.5°	1271.3	1270.0	1268.7	1267.2	1268.7	1270.0	1271.3	1272.6	1272.7	1271.6	1270.4
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1715.7	1722.2	1725.7	1733.9	1745.7	1751.6	1759.8	1765.7	1774.0	1784.0	1792.2
5°	1604.7	1622.3	1634.0	1652.4	1669.3	1686.2	1707.5	1723.0	1743.5	1767.0	1785.4
7.5°	1501.5	1523.5	1543.0	1567.4	1595.3	1617.0	1644.7	1673.1	1705.2	1738.6	1770.1
10°	1435.7	1457.7	1482.0	1512.0	1540.0	1569.3	1602.4	1635.5	1675.9	1713.4	1756.0
12.5°	1370.4	1394.8	1422.0	1455.7	1489.4	1527.0	1560.7	1597.9	1641.2	1689.9	1735.4
15°	1289.4	1313.0	1342.4	1371.0	1409.9	1451.0	1495.9	1545.1	1593.7	1647.9	1704.6
17.5°	1202.6	1228.4	1260.7	1294.0	1335.0	1383.2	1427.1	1481.0	1535.6	1598.9	1665.5
20°	1146.1	1172.6	1210.8	1247.5	1285.1	1332.1	1384.2	1439.4	1497.3	1564.2	1638.4
22.5°	1101.5	1120.3	1157.9	1195.2	1239.2	1287.4	1338.4	1395.8	1459.2	1528.3	1606.1
25°	1035.2	1057.2	1084.5	1123.4	1168.9	1219.7	1271.1	1332.1	1401.1	1471.7	1554.6
27.5°	976.3	994.4	1021.2	1051.8	1097.2	1149.8	1204.5	1268.1	1339.0	1410.8	1498.1
30°	934.5	954.4	980.1	1012.5	1048.5	1105.8	1161.6	1224.1	1296.1	1370.3	1459.9
32.5°	898.1	918.5	940.8	971.3	1010.2	1061.1	1118.7	1180.0	1253.1	1329.7	1417.0
35°	847.2	861.1	881.7	911.8	950.0	991.2	1049.9	1114.6	1185.8	1265.2	1352.6
37.5°	788.6	806.7	827.2	853.3	886.8	931.3	986.0	1051.4	1117.5	1193.4	1273.3
40°	754.6	771.5	794.3	813.3	848.6	889.0	939.0	1007.3	1073.5	1144.7	1217.5
42.5°	719.9	736.2	755.4	779.3	811.0	850.3	896.6	960.3	1031.1	1098.3	1159.2
45°	665.6	682.6	701.0	722.9	752.3	790.6	836.9	894.8	956.6	1018.3	1064.6
47.5°	613.8	629.6	647.0	669.6	696.6	733.6	775.0	826.2	886.2	938.7	971.8
50°	576.7	591.4	610.6	632.6	659.0	693.6	733.3	783.9	833.9	881.7	911.8
52.5°	540.4	556.8	575.9	594.9	620.3	654.8	691.5	735.2	782.8	821.7	846.6
55°	485.7	501.1	518.7	538.6	563.5	593.0	631.9	666.4	703.9	737.0	751.6
57.5°	432.9	446.4	463.0	483.6	506.1	533.4	564.3	597.5	624.0	647.3	663.9
60°	398.2	410.0	425.4	443.0	467.3	492.3	520.2	551.0	571.7	591.4	606.9
62.5°	363.0	374.1	389.0	404.8	426.1	449.3	476.1	501.1	521.0	534.4	552.2
65°	310.1	321.0	333.6	350.4	367.4	386.4	410.7	429.0	443.0	457.7	468.7
67.5°	260.8	269.9	281.8	295.1	309.3	327.7	346.5	361.7	371.4	380.1	393.4
70°	228.5	235.8	245.4	255.7	271.1	289.5	304.2	315.9	322.5	331.4	347.5
72.5°	195.6	204.1	213.1	223.4	235.8	251.3	264.2	276.0	280.2	287.3	297.6
75°	154.3	158.7	166.1	173.4	182.2	195.5	207.9	210.8	214.5	220.5	227.7
77.5°	116.7	120.6	123.6	128.5	135.4	146.1	152.7	157.1	158.0	160.1	167.4
80°	92.6	94.8	97.7	101.4	104.3	113.1	116.8	121.2	122.7	124.9	128.6
82.5°	67.9	70.1	71.8	74.9	79.6	83.1	86.8	91.2	91.5	93.1	93.9
85°	39.7	40.4	38.9	40.4	41.2	42.6	46.3	50.0	49.2	48.4	50.7
87.5°	17.3	17.2	16.2	17.7	16.2	16.5	16.2	16.5	17.3	18.2	19.0
90°	16.1	15.1	13.6	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9
92.5°	16.1	15.1	13.8	12.4	11.1	9.9	9.8	10.9	12.2	13.3	14.5
95°	16.1	15.1	23.0	30.9	38.9	46.8	51.2	51.7	52.4	53.0	53.6
97.5°	40.4	46.3	62.0	77.8	93.5	109.2	116.5	115.4	114.2	113.1	112.0
100°	132.6	163.7	162.9	162.1	161.3	160.4	159.7	159.0	158.4	157.8	157.1
102.5°	203.0	209.0	208.4	207.9	207.5	206.9	206.2	205.5	204.7	203.9	203.1
105°	280.4	280.4	280.4	280.4	280.4	280.4	280.0	279.2	278.3	277.5	276.6
107.5°	355.1	355.0	354.6	354.1	353.7	353.3	353.1	353.1	353.1	353.1	353.1
110°	404.1	404.6	404.3	403.9	403.4	403.0	402.7	402.7	402.7	402.7	402.7



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	452.0	452.9	452.6	452.3	452.1	451.9	451.5	451.0	450.4	450.0	449.5
115°	524.3	525.1	524.9	524.7	524.5	524.3	523.7	522.6	521.6	520.6	519.5
117.5°	594.3	595.3	594.6	593.7	593.0	592.2	591.8	591.8	591.8	591.9	591.9
120°	638.6	639.0	638.4	637.7	637.2	636.5	636.3	636.5	636.7	636.9	637.2
122.5°	681.5	681.9	681.6	681.4	681.1	680.7	680.2	679.4	678.6	677.8	677.0
125°	744.5	745.4	745.4	745.4	745.4	745.4	744.6	743.2	741.7	740.2	738.8
127.5°	801.3	801.8	801.9	802.1	802.2	802.3	801.8	800.8	799.7	798.7	797.7
130°	838.9	839.4	839.2	839.1	838.9	838.6	838.0	837.0	835.9	834.9	833.8
132.5°	873.2	873.4	873.8	874.3	874.7	875.2	874.8	873.5	872.4	871.2	870.0
135°	924.6	925.1	925.5	926.0	926.3	926.8	926.3	925.1	923.9	922.6	921.3
137.5°	971.9	971.8	972.1	972.5	972.9	973.3	972.9	971.9	970.7	969.7	968.6
140°	1000.8	1000.4	1000.6	1000.8	1001.0	1001.3	1001.1	1000.7	1000.3	999.8	999.5
142.5°	1029.8	1029.7	1029.4	1029.2	1028.9	1028.6	1028.3	1028.0	1027.8	1027.6	1027.3
145°	1070.3	1070.1	1070.1	1070.1	1070.1	1070.1	1069.8	1069.4	1068.9	1068.6	1068.2
147.5°	1104.9	1104.7	1104.4	1104.2	1103.9	1103.6	1103.5	1103.6	1103.7	1103.8	1103.9
150°	1126.9	1126.5	1126.1	1125.7	1125.2	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5
152.5°	1146.5	1146.0	1145.7	1145.2	1144.8	1144.4	1144.6	1145.6	1146.5	1147.5	1148.3
155°	1173.3	1172.6	1172.1	1171.8	1171.4	1170.9	1171.4	1172.6	1173.8	1175.2	1176.4
157.5°	1195.5	1194.9	1194.8	1194.8	1194.7	1194.7	1195.0	1195.8	1196.6	1197.2	1198.0
160°	1209.2	1208.3	1208.2	1208.0	1207.8	1207.5	1208.1	1209.3	1210.6	1211.8	1213.1
162.5°	1221.6	1220.4	1220.2	1220.0	1219.7	1219.6	1220.1	1221.3	1222.6	1223.9	1225.1
165°	1237.8	1236.6	1236.4	1236.1	1236.0	1235.8	1236.3	1237.6	1238.8	1240.0	1241.3
167.5°	1250.0	1248.5	1248.2	1248.0	1247.8	1247.6	1248.2	1249.4	1250.8	1252.1	1253.4
170°	1256.1	1254.5	1254.2	1254.1	1253.9	1253.7	1254.2	1255.7	1257.2	1258.7	1260.1
172.5°	1261.2	1259.7	1259.3	1259.0	1258.6	1258.3	1258.8	1260.3	1261.7	1263.2	1264.6
175°	1266.5	1264.8	1264.6	1264.4	1264.2	1264.0	1264.5	1265.7	1267.1	1268.3	1269.5
177.5°	1269.2	1268.0	1267.9	1267.7	1267.5	1267.3	1267.8	1268.8	1269.8	1270.8	1271.8
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1798.6	1803.9	1811.6	1820.3	1827.4	1835.0	1839.2	1839.2	1842.7	1850.3	1860.3
5°	1803.7	1822.9	1841.3	1864.7	1883.1	1904.4	1920.5	1936.0	1949.9	1967.6	1985.9
7.5°	1802.2	1834.0	1867.1	1904.1	1944.9	1977.5	2010.8	2036.9	2062.8	2096.6	2123.2
10°	1796.4	1837.6	1882.4	1929.4	1980.8	2025.6	2066.1	2102.8	2138.1	2174.8	2207.8
12.5°	1785.8	1838.1	1892.9	1949.4	2014.3	2065.6	2117.8	2156.8	2198.0	2238.3	2279.0
15°	1769.9	1831.6	1897.8	1976.4	2055.8	2113.1	2164.5	2215.2	2253.4	2299.0	2337.9
17.5°	1737.2	1816.7	1899.9	1985.8	2062.1	2128.6	2182.6	2230.8	2271.4	2321.6	2374.5
20°	1717.8	1803.7	1890.5	1982.3	2055.0	2123.4	2175.5	2225.4	2276.1	2341.6	2406.2
22.5°	1690.7	1782.6	1874.5	1961.7	2038.5	2104.5	2158.5	2219.6	2286.1	2360.4	2438.5
25°	1647.9	1742.8	1833.9	1916.8	1991.9	2059.5	2132.9	2215.2	2296.0	2393.8	2506.1
27.5°	1593.7	1685.2	1766.4	1854.2	1928.6	2014.6	2106.3	2195.5	2312.1	2446.5	2586.8
30°	1553.2	1639.9	1717.0	1800.1	1884.5	1979.3	2082.2	2187.3	2326.1	2484.1	2650.9
32.5°	1506.2	1584.7	1661.2	1741.3	1838.7	1942.9	2052.2	2180.8	2346.7	2526.4	2699.1
35°	1424.7	1495.2	1569.3	1658.3	1761.9	1875.0	2014.6	2171.1	2371.7	2564.9	2720.0
37.5°	1339.1	1394.8	1469.3	1563.0	1675.9	1806.9	1965.2	2155.4	2361.4	2534.8	2600.8
40°	1273.3	1325.4	1404.0	1502.5	1614.2	1757.5	1935.2	2130.7	2337.9	2458.3	2453.2
42.5°	1208.1	1260.7	1336.4	1435.5	1551.9	1712.2	1895.3	2098.4	2273.2	2319.1	2223.5
45°	1108.0	1157.2	1231.4	1331.3	1456.2	1624.5	1816.9	2011.7	2123.4	2049.2	1859.5
47.5°	1006.0	1053.8	1122.7	1220.5	1356.9	1533.0	1715.0	1874.7	1890.5	1731.0	1503.6
50°	939.0	983.8	1049.1	1153.5	1285.7	1457.7	1633.3	1759.0	1720.0	1525.3	1290.9
52.5°	873.7	916.8	978.1	1076.5	1211.7	1380.1	1536.9	1635.5	1545.4	1338.4	1127.5
55°	777.3	818.5	880.2	970.5	1093.3	1247.5	1385.0	1421.0	1288.7	1080.1	909.6
57.5°	685.8	716.0	776.9	856.9	975.2	1111.2	1209.7	1203.2	1057.2	869.3	747.1
60°	625.3	652.4	710.5	783.9	896.4	1018.3	1087.4	1058.0	910.3	755.3	637.7
62.5°	568.8	594.3	642.9	710.5	807.0	913.1	963.4	922.8	783.3	647.1	553.6
65°	483.4	501.8	540.7	603.2	678.9	752.3	797.2	737.6	614.3	511.3	440.8
67.5°	403.7	419.5	454.2	499.0	551.2	601.9	620.1	564.3	468.3	399.0	349.3
70°	351.9	366.6	390.1	432.1	466.6	502.6	511.3	461.4	381.4	328.4	297.6
72.5°	302.6	316.0	336.7	366.2	390.1	410.9	415.0	368.5	307.3	270.8	247.0
75°	230.7	242.4	255.7	266.7	282.1	285.8	284.4	248.4	215.3	191.1	177.8
77.5°	169.6	174.5	182.5	186.9	187.7	187.4	179.8	157.1	140.1	130.1	124.6
80°	130.8	134.5	136.7	138.1	138.8	131.5	123.5	109.4	103.6	97.7	91.1
82.5°	94.9	97.5	99.6	99.9	96.0	89.8	82.3	75.4	71.3	68.3	65.8
85°	51.5	52.1	51.5	47.8	42.6	40.4	38.9	37.5	36.8	36.0	36.0
87.5°	18.8	17.3	14.7	15.6	15.9	15.6	15.9	15.6	15.4	15.6	15.7
90°	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2
92.5°	13.3	12.2	10.9	9.8	9.9	11.1	12.4	13.8	15.1	16.1	17.2
95°	53.0	52.4	51.7	51.2	46.8	38.9	30.9	23.0	15.1	16.1	17.2
97.5°	113.1	114.2	115.4	116.5	109.2	93.5	77.8	62.0	46.3	40.4	34.5
100°	157.8	158.4	159.0	159.7	160.4	161.3	162.1	162.9	163.7	132.6	101.4
102.5°	203.9	204.7	205.5	206.2	206.9	207.5	207.9	208.4	209.0	203.0	197.1
105°	277.5	278.3	279.2	280.0	280.4	280.4	280.4	280.4	280.4	280.4	280.4
107.5°	353.1	353.1	353.1	353.1	353.3	353.7	354.1	354.6	355.0	355.1	355.1
110°	402.7	402.7	402.7	402.7	403.0	403.4	403.9	404.3	404.6	404.1	403.4



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	450.0	450.4	451.0	451.5	451.9	452.1	452.3	452.6	452.9	452.0	451.3
115°	520.6	521.6	522.6	523.7	524.3	524.5	524.7	524.9	525.1	524.3	523.5
117.5°	591.9	591.8	591.8	591.8	592.2	593.0	593.7	594.6	595.3	594.3	593.1
120°	636.9	636.7	636.5	636.3	636.5	637.2	637.7	638.4	639.0	638.6	638.2
122.5°	677.8	678.6	679.4	680.2	680.7	681.1	681.4	681.6	681.9	681.5	681.1
125°	740.2	741.7	743.2	744.6	745.4	745.4	745.4	745.4	745.4	744.5	743.7
127.5°	798.7	799.7	800.8	801.8	802.3	802.2	802.1	801.9	801.8	801.3	800.9
130°	834.9	835.9	837.0	838.0	838.6	838.9	839.1	839.2	839.4	838.9	838.2
132.5°	871.2	872.4	873.5	874.8	875.2	874.7	874.3	873.8	873.4	873.2	873.1
135°	922.6	923.9	925.1	926.3	926.8	926.3	926.0	925.5	925.1	924.6	924.3
137.5°	969.7	970.7	971.9	972.9	973.3	972.9	972.5	972.1	971.8	971.9	971.9
140°	999.8	1000.3	1000.7	1001.1	1001.3	1001.0	1000.8	1000.6	1000.4	1000.8	1001.3
142.5°	1027.6	1027.8	1028.0	1028.3	1028.6	1028.9	1029.2	1029.4	1029.7	1029.8	1029.9
145°	1068.6	1068.9	1069.4	1069.8	1070.1	1070.1	1070.1	1070.1	1070.1	1070.3	1070.4
147.5°	1103.8	1103.7	1103.6	1103.5	1103.6	1103.9	1104.2	1104.4	1104.7	1104.9	1105.1
150°	1126.1	1125.7	1125.2	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5	1126.9	1127.4
152.5°	1147.5	1146.5	1145.6	1144.6	1144.4	1144.8	1145.2	1145.7	1146.0	1146.5	1146.9
155°	1175.2	1173.8	1172.6	1171.4	1170.9	1171.4	1171.8	1172.1	1172.6	1173.3	1173.8
157.5°	1197.2	1196.6	1195.8	1195.0	1194.7	1194.7	1194.8	1194.8	1194.9	1195.5	1196.2
160°	1211.8	1210.6	1209.3	1208.1	1207.5	1207.8	1208.0	1208.2	1208.3	1209.2	1210.0
162.5°	1223.9	1222.6	1221.3	1220.1	1219.6	1219.7	1220.0	1220.2	1220.4	1221.6	1222.8
165°	1240.0	1238.8	1237.6	1236.3	1235.8	1236.0	1236.1	1236.4	1236.6	1237.8	1239.1
167.5°	1252.1	1250.8	1249.4	1248.2	1247.6	1247.8	1248.0	1248.2	1248.5	1250.0	1251.5
170°	1258.7	1257.2	1255.7	1254.2	1253.7	1253.9	1254.1	1254.2	1254.5	1256.1	1257.8
172.5°	1263.2	1261.7	1260.3	1258.8	1258.3	1258.6	1259.0	1259.3	1259.7	1261.2	1262.7
175°	1268.3	1267.1	1265.7	1264.5	1264.0	1264.2	1264.4	1264.6	1264.8	1266.5	1268.2
177.5°	1270.8	1269.8	1268.8	1267.8	1267.3	1267.5	1267.7	1267.9	1268.0	1269.2	1270.4
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1867.9	1867.9	1877.9	1877.4	1883.9	1881.5	1882.6
5°	2008.0	2020.5	2031.6	2038.8	2049.8	2052.9	2051.3
7.5°	2153.1	2180.9	2194.4	2213.0	2216.4	2226.1	2225.1
10°	2243.2	2270.3	2290.8	2307.1	2315.1	2325.4	2326.1
12.5°	2313.7	2336.8	2354.9	2369.9	2379.7	2383.0	2384.9
15°	2368.7	2394.4	2415.7	2437.0	2449.6	2459.1	2464.3
17.5°	2424.3	2464.0	2501.6	2530.5	2547.9	2562.6	2562.4
20°	2467.2	2512.7	2559.8	2592.8	2626.7	2641.3	2643.5
22.5°	2513.0	2582.7	2643.3	2694.5	2738.9	2754.2	2760.0
25°	2608.3	2699.3	2792.7	2864.7	2916.1	2946.2	2950.6
27.5°	2723.3	2846.6	2944.8	3011.2	3053.9	3076.3	3081.2
30°	2804.4	2918.3	3006.5	3056.5	3076.3	3079.2	3068.2
32.5°	2840.9	2925.9	2961.2	2958.3	2919.3	2893.5	2883.6
35°	2796.3	2778.7	2692.7	2589.9	2511.3	2461.4	2448.1
37.5°	2544.8	2392.7	2234.6	2079.2	1996.4	1954.4	1882.1
40°	2296.8	2080.0	1915.4	1784.6	1691.3	1616.4	1598.7
42.5°	2016.9	1793.2	1628.6	1516.6	1442.1	1390.7	1368.4
45°	1620.8	1428.3	1292.4	1206.5	1149.1	1111.6	1094.8
47.5°	1296.4	1147.4	1048.3	984.7	941.0	908.4	899.3
50°	1118.2	999.2	915.5	861.9	828.8	803.8	793.5
52.5°	971.3	875.2	810.9	766.6	735.3	719.7	711.2
55°	801.5	718.6	672.3	637.0	619.3	606.9	601.0
57.5°	655.5	595.6	561.8	537.3	521.0	513.1	510.2
60°	573.8	526.8	496.0	476.8	465.8	455.5	452.6
62.5°	501.5	464.5	440.7	424.0	412.9	408.5	406.7
65°	404.1	379.8	362.2	351.9	343.1	341.7	340.9
67.5°	321.2	307.0	297.7	287.0	283.9	278.7	277.8
70°	274.8	265.2	254.2	250.5	246.9	241.8	242.4
72.5°	233.1	223.5	216.0	211.1	209.8	207.6	209.5
75°	170.4	167.5	164.6	160.9	159.5	159.5	158.7
77.5°	121.7	119.1	115.9	113.8	113.3	110.2	111.4
80°	88.1	84.5	83.0	83.8	81.5	80.8	80.8
82.5°	65.2	63.9	62.5	62.6	62.1	61.5	62.0
85°	36.0	35.3	35.3	34.5	34.5	33.8	33.8
87.5°	16.6	17.3	16.4	15.9	16.0	16.8	17.4
90°	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	18.2	19.2	19.9	20.2	20.5	20.8	21.1
95°	18.2	19.2	19.8	19.8	19.8	19.8	19.8
97.5°	28.7	22.7	19.8	19.8	19.8	19.8	19.8
100°	70.3	39.1	23.1	22.2	21.4	20.6	19.8
102.5°	191.2	185.3	175.3	161.1	146.8	132.6	118.4
105°	280.4	280.4	280.3	280.1	279.9	279.7	279.5
107.5°	355.2	355.2	354.9	354.2	353.6	353.0	352.3
110°	402.7	402.2	402.0	402.2	402.4	402.6	402.7



TEST NUMBER: P333628-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	450.4	449.7	449.1	448.8	448.6	448.3	448.0
115°	522.6	521.8	520.8	519.5	518.2	517.0	515.8
117.5°	592.1	591.0	590.1	589.7	589.1	588.5	588.0
120°	637.7	637.3	636.6	635.6	634.5	633.5	632.4
122.5°	680.7	680.2	679.4	678.3	677.0	675.8	674.6
125°	742.8	742.0	741.3	740.6	740.0	739.4	738.8
127.5°	800.4	799.9	799.0	797.4	795.9	794.4	792.8
130°	837.5	837.0	836.1	835.1	834.1	833.0	831.9
132.5°	873.0	872.8	872.2	871.2	870.2	869.1	868.1
135°	923.9	923.4	922.6	921.3	920.1	918.8	917.6
137.5°	972.0	972.1	971.6	970.5	969.4	968.4	967.2
140°	1001.6	1002.0	1001.6	1000.4	999.1	997.9	996.6
142.5°	1030.0	1030.1	1029.5	1028.2	1027.0	1025.8	1024.4
145°	1070.6	1070.8	1070.4	1069.1	1067.8	1066.6	1065.4
147.5°	1105.4	1105.7	1105.0	1103.5	1102.0	1100.5	1099.0
150°	1127.8	1128.1	1127.6	1125.9	1124.2	1122.5	1120.9
152.5°	1147.4	1147.7	1147.2	1145.7	1144.2	1142.6	1141.1
155°	1174.5	1175.2	1174.6	1172.9	1171.2	1169.6	1167.9
157.5°	1196.8	1197.5	1197.0	1195.3	1193.6	1191.9	1190.3
160°	1210.9	1211.7	1211.3	1209.7	1208.0	1206.3	1204.6
162.5°	1223.9	1225.1	1224.7	1222.9	1221.1	1219.3	1217.4
165°	1240.4	1241.6	1241.4	1239.7	1238.0	1236.4	1234.7
167.5°	1253.0	1254.5	1254.3	1252.5	1250.6	1248.7	1246.8
170°	1259.5	1261.2	1261.0	1259.1	1257.4	1255.5	1253.6
172.5°	1264.2	1265.7	1265.6	1263.7	1261.8	1259.9	1258.1
175°	1269.9	1271.5	1271.4	1269.5	1267.6	1265.7	1263.9
177.5°	1271.6	1272.7	1272.6	1271.3	1270.0	1268.7	1267.2
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5

(END OF REPORT)