

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333284-840

Luminaire Tested: **S125DIP-S1090D1035U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333284-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1035U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8102.0 lumens
Efficiency: N/A
Efficacy: 133.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333284-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333284-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																				
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	53	51	46																				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39																				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33																				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28																				
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28	24																				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21																				
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19																				
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19	17																				
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15																				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11129	11129	11129
5°	11154	11048	11119
10°	11086	10970	11032
15°	10965	10838	10884
20°	10794	10653	10672
25°	10608	10434	10424
30°	10380	10197	10147
35°	10136	9942	9802
40°	9885	9666	9528
45°	9613	9414	9227
50°	9315	9109	8835
55°	9026	8765	8519
60°	8681	8418	8117
65°	8270	8000	7728
70°	7878	7517	7260
75°	7177	6939	6700
80°	6390	6289	6133
85°	5550	5654	5350



TEST NUMBER: P333284-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.0
10°-20°	459.0	5.7
20°-30°	677.7	8.4
30°-40°	790.7	9.8
40°-50°	794.2	9.8
50°-60°	697.1	8.6
60°-70°	519.5	6.4
70°-80°	297.0	3.7
80°-90°	89.2	1.1
90°-100°	86.8	1.1
100°-110°	256.2	3.2
110°-120°	434.0	5.4
120°-130°	571.2	7.0
130°-140°	640.0	7.9
140°-150°	627.3	7.7
150°-160°	526.9	6.5
160°-170°	350.2	4.3
170°-180°	122.6	1.5
0°-30°	1299.1	16.0
0°-40°	2089.8	25.8
0°-60°	3581.2	44.2
0°-90°	4486.8	55.4
90°-120°	777.0	9.6
90°-150°	2615.5	32.3
90°-180°	3615.0	44.6
0°-180°	8102.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1720	1717	1704	1716	1715	163
15°	1640	1635	1621	1627	1628	462
25°	1489	1481	1464	1466	1463	685
35°	1286	1279	1261	1254	1243	804
45°	1052	1046	1031	1015	1010	811
55°	802	797	778	766	757	715
65°	541	538	524	512	506	537
75°	288	285	278	274	268	307
85°	75	76	76	75	72	84
90°	1	9	16	21	24	8
95°	66	68	78	84	87	70
105°	230	235	241	247	250	245
115°	434	438	441	440	439	430
125°	634	640	641	639	638	568
135°	825	830	832	832	828	635
145°	999	1003	1006	1006	1003	624
155°	1143	1143	1144	1148	1143	526
165°	1243	1241	1242	1246	1240	351
175°	1292	1289	1288	1294	1288	123
180°	1296	1296	1296	1296	1296	



TEST NUMBER: P333284-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1727.6	1726.9	1726.1	1725.4	1724.6	1723.0	1720.6	1718.2	1715.8	1713.3	1715.8
5°	1720.5	1719.9	1719.3	1718.7	1718.1	1716.3	1713.2	1710.2	1707.2	1704.1	1706.9
7.5°	1704.7	1704.0	1703.4	1702.8	1702.2	1700.2	1696.9	1693.5	1690.2	1686.9	1689.6
10°	1690.5	1689.9	1689.3	1688.7	1688.1	1686.1	1682.7	1679.4	1676.1	1672.7	1675.2
12.5°	1673.0	1671.9	1670.8	1669.7	1668.7	1666.6	1663.4	1660.4	1657.3	1654.2	1656.2
15°	1640.0	1639.1	1638.2	1637.3	1636.4	1634.3	1630.9	1627.6	1624.3	1620.9	1622.4
17.5°	1602.2	1600.8	1599.4	1598.1	1596.8	1594.4	1590.9	1587.5	1584.1	1580.5	1582.5
20°	1570.5	1569.9	1569.3	1568.7	1568.1	1565.8	1561.9	1557.9	1554.0	1550.0	1552.2
22.5°	1538.8	1537.8	1536.7	1535.6	1534.5	1532.1	1528.4	1524.7	1521.1	1517.3	1518.7
25°	1488.7	1487.2	1485.7	1484.2	1482.7	1480.0	1476.0	1472.1	1468.1	1464.2	1464.8
27.5°	1430.1	1429.2	1428.3	1427.3	1426.4	1424.0	1419.9	1415.8	1411.8	1407.8	1407.9
30°	1391.9	1391.0	1390.1	1389.2	1388.3	1385.5	1381.0	1376.4	1371.9	1367.4	1366.8
32.5°	1350.5	1349.1	1347.7	1346.3	1344.9	1342.2	1338.1	1334.0	1330.0	1326.0	1324.8
35°	1285.6	1284.3	1283.1	1281.9	1280.7	1278.0	1273.7	1269.5	1265.3	1261.0	1259.5
37.5°	1218.2	1216.7	1215.2	1213.7	1212.1	1209.4	1205.4	1201.4	1197.4	1193.5	1191.1
40°	1172.5	1170.9	1169.4	1167.9	1166.4	1163.5	1159.2	1155.0	1150.7	1146.5	1143.8
42.5°	1123.4	1122.1	1120.8	1119.5	1118.2	1115.5	1111.3	1107.0	1102.8	1098.5	1096.0
45°	1052.5	1051.3	1050.1	1048.8	1047.6	1045.2	1041.6	1037.9	1034.3	1030.7	1027.0
47.5°	976.1	976.1	976.2	976.3	976.3	974.2	969.9	965.4	961.1	956.7	953.0
50°	927.1	926.1	925.2	924.3	923.4	921.1	917.5	913.8	910.2	906.6	902.6
52.5°	876.9	876.2	875.6	874.8	874.2	871.9	868.1	864.1	860.3	856.4	852.9
55°	801.6	800.7	799.8	798.9	798.0	795.4	791.1	786.9	782.6	778.4	775.7
57.5°	722.3	721.8	721.3	720.8	720.3	718.3	714.7	711.1	707.6	704.0	700.4
60°	672.1	670.9	669.6	668.4	667.2	665.0	661.7	658.3	655.0	651.7	648.6
62.5°	619.8	618.7	617.8	616.8	615.9	614.0	611.1	608.2	605.4	602.6	599.3
65°	541.2	540.6	540.0	539.4	538.8	536.8	533.5	530.2	526.8	523.5	520.8
67.5°	465.1	463.8	462.6	461.3	460.1	458.2	455.7	453.2	450.7	448.3	446.0
70°	417.2	415.7	414.1	412.6	411.1	409.0	406.3	403.5	400.8	398.1	396.3
72.5°	364.9	363.8	362.7	361.7	360.7	359.3	357.6	355.8	354.1	352.2	350.2
75°	287.6	287.0	286.4	285.8	285.2	284.2	282.7	281.1	279.6	278.1	277.2
77.5°	216.5	216.2	216.0	215.8	215.5	215.0	214.1	213.3	212.5	211.6	211.1
80°	171.8	171.8	171.8	171.8	171.8	171.5	170.9	170.3	169.7	169.1	168.7
82.5°	132.5	132.0	131.6	131.1	130.6	130.3	130.2	130.1	129.9	129.8	129.3
85°	74.9	75.2	75.5	75.8	76.1	76.3	76.3	76.3	76.3	76.3	76.0
87.5°	29.7	30.0	30.4	30.7	31.1	31.3	31.4	31.4	31.5	31.6	31.8
90°	1.0	2.8	4.5	6.4	8.2	9.9	11.4	13.0	14.5	16.2	17.3
92.5°	24.4	25.7	26.9	28.2	29.4	31.0	32.9	34.8	36.8	38.7	40.2
95°	65.5	65.9	66.4	66.9	67.4	68.7	70.9	73.1	75.4	77.7	79.2
97.5°	108.9	109.1	109.3	109.5	109.6	111.3	114.3	117.4	120.5	123.6	125.1
100°	141.2	141.2	141.2	141.2	141.2	142.6	145.5	148.5	151.4	154.2	156.2
102.5°	175.8	176.7	177.6	178.5	179.5	180.6	182.1	183.6	185.0	186.5	188.7
105°	229.8	231.0	232.1	233.3	234.4	235.6	236.9	238.2	239.6	241.0	242.3
107.5°	289.5	290.6	291.8	293.0	294.1	295.1	296.1	297.2	298.2	299.2	299.9
110°	330.7	331.8	333.0	334.1	335.2	336.1	336.7	337.4	338.1	338.7	339.4



TEST NUMBER: P333284-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.6	373.2	373.8	374.4	375.0	375.7	376.6	377.4	378.2	379.1	379.4
115°	434.5	435.5	436.4	437.3	438.1	438.8	439.2	439.7	440.1	440.6	440.4
117.5°	496.7	497.1	497.5	497.9	498.3	498.7	499.1	499.5	499.9	500.3	500.5
120°	535.3	536.4	537.6	538.8	539.9	540.5	540.7	541.0	541.2	541.4	541.4
122.5°	577.3	577.7	578.1	578.6	579.0	579.4	580.0	580.6	581.2	581.7	581.6
125°	634.2	635.5	636.8	638.2	639.5	640.4	640.6	640.8	641.0	641.3	640.8
127.5°	694.7	695.4	696.2	696.9	697.7	698.2	698.5	698.7	699.0	699.3	699.0
130°	730.9	732.1	733.2	734.3	735.4	736.2	736.7	737.1	737.5	738.0	737.8
132.5°	767.2	769.1	770.9	772.7	774.6	775.5	775.4	775.3	775.2	775.1	774.9
135°	824.8	826.1	827.4	828.7	830.1	830.9	831.1	831.3	831.5	831.7	831.7
137.5°	878.8	880.0	881.3	882.6	883.9	884.8	885.3	885.9	886.4	886.8	887.1
140°	913.4	914.5	915.6	916.8	917.9	918.8	919.5	920.2	920.8	921.5	921.9
142.5°	948.1	949.1	950.0	950.9	951.9	952.8	953.6	954.5	955.3	956.1	956.4
145°	999.2	1000.1	1000.9	1001.8	1002.7	1003.5	1004.2	1004.8	1005.5	1006.2	1006.2
147.5°	1046.3	1046.8	1047.3	1047.8	1048.2	1048.8	1049.4	1049.9	1050.4	1051.0	1051.5
150°	1077.7	1077.5	1077.3	1077.1	1076.9	1077.2	1078.1	1079.0	1079.8	1080.8	1080.8
152.5°	1103.6	1103.9	1104.2	1104.5	1104.8	1105.2	1105.5	1105.9	1106.2	1106.6	1107.1
155°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.4	1143.7	1143.9	1144.1	1144.3	1145.2
157.5°	1178.8	1178.3	1177.8	1177.3	1176.8	1176.7	1176.9	1177.1	1177.4	1177.6	1178.5
160°	1199.7	1199.1	1198.4	1197.7	1197.1	1196.9	1197.1	1197.3	1197.5	1197.7	1198.6
162.5°	1218.3	1217.8	1217.3	1216.8	1216.4	1216.1	1216.2	1216.2	1216.3	1216.3	1217.4
165°	1243.1	1242.6	1242.2	1241.7	1241.3	1241.2	1241.4	1241.6	1241.8	1242.1	1243.0
167.5°	1264.0	1263.1	1262.3	1261.4	1260.5	1260.0	1260.0	1260.0	1260.0	1260.0	1261.4
170°	1275.4	1274.4	1273.5	1272.7	1271.8	1271.3	1271.3	1271.3	1271.3	1271.3	1272.7
172.5°	1283.4	1282.5	1281.6	1280.7	1279.9	1279.4	1279.4	1279.4	1279.4	1279.4	1280.7
175°	1292.5	1291.6	1290.7	1289.8	1288.9	1288.5	1288.5	1288.5	1288.5	1288.5	1289.8
177.5°	1297.2	1296.5	1295.8	1294.9	1294.2	1293.8	1293.6	1293.4	1293.3	1293.1	1294.2
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333284-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1718.2	1720.6	1723.0	1724.1	1723.9	1723.6	1723.4	1723.2
5°	1709.6	1712.3	1715.1	1716.3	1716.0	1715.7	1715.4	1715.1
7.5°	1692.2	1695.0	1697.6	1698.8	1698.5	1698.2	1697.9	1697.6
10°	1677.6	1680.0	1682.4	1683.5	1683.2	1682.9	1682.6	1682.3
12.5°	1658.1	1660.0	1661.9	1662.9	1662.8	1662.7	1662.7	1662.6
15°	1624.0	1625.5	1627.0	1627.8	1627.8	1627.8	1627.8	1627.8
17.5°	1584.4	1586.2	1588.1	1588.3	1586.8	1585.3	1583.8	1582.3
20°	1554.3	1556.4	1558.5	1558.8	1557.3	1555.8	1554.3	1552.8
22.5°	1520.1	1521.6	1522.9	1523.1	1522.1	1521.1	1520.0	1518.9
25°	1465.4	1466.0	1466.6	1466.4	1465.5	1464.6	1463.7	1462.8
27.5°	1408.0	1408.1	1408.3	1407.9	1406.9	1406.0	1405.1	1404.2
30°	1366.1	1365.5	1364.9	1364.2	1363.3	1362.4	1361.5	1360.6
32.5°	1323.7	1322.6	1321.6	1320.2	1318.6	1317.0	1315.2	1313.6
35°	1258.0	1256.5	1255.0	1253.0	1250.6	1248.2	1245.8	1243.3
37.5°	1188.9	1186.7	1184.5	1182.7	1181.2	1179.8	1178.4	1177.1
40°	1141.0	1138.3	1135.6	1133.8	1132.9	1132.0	1131.0	1130.1
42.5°	1093.6	1091.1	1088.6	1086.6	1085.3	1083.9	1082.5	1081.1
45°	1023.4	1019.8	1016.1	1013.8	1012.9	1012.0	1011.1	1010.2
47.5°	949.4	945.6	942.0	939.1	937.0	934.8	932.7	930.6
50°	898.7	894.7	890.8	887.8	885.7	883.5	881.4	879.3
52.5°	849.5	846.1	842.6	839.7	837.3	835.0	832.6	830.2
55°	773.0	770.2	767.5	765.1	763.0	760.8	758.7	756.6
57.5°	697.0	693.5	689.9	687.6	686.5	685.3	684.2	683.0
60°	645.6	642.6	639.5	636.9	634.8	632.7	630.6	628.4
62.5°	596.0	592.8	589.5	587.0	585.4	583.8	582.1	580.5
65°	518.1	515.3	512.6	510.6	509.4	508.2	507.0	505.7
67.5°	443.6	441.3	439.0	437.5	436.8	436.1	435.4	434.6
70°	394.5	392.6	390.8	389.3	388.1	386.9	385.7	384.5
72.5°	348.2	346.1	344.1	342.4	341.2	340.0	338.8	337.6
75°	276.3	275.4	274.5	273.4	272.2	270.9	269.7	268.5
77.5°	210.5	210.0	209.4	208.7	207.8	207.0	206.1	205.3
80°	168.4	168.1	167.8	167.3	166.7	166.1	165.5	164.9
82.5°	128.7	128.2	127.6	127.2	127.1	127.0	126.9	126.7
85°	75.7	75.4	75.1	74.6	74.0	73.4	72.8	72.2
87.5°	32.0	32.2	32.5	32.4	32.1	31.7	31.4	31.0
90°	18.4	19.5	20.6	21.5	22.2	22.8	23.5	24.2
92.5°	41.7	43.1	44.6	45.6	46.2	46.6	47.1	47.6
95°	80.8	82.3	83.9	84.9	85.3	85.8	86.2	86.7
97.5°	126.5	128.1	129.6	130.4	130.7	131.0	131.2	131.5
100°	158.2	160.3	162.3	163.6	164.0	164.4	164.9	165.3
102.5°	190.9	193.1	195.3	196.7	197.3	197.9	198.6	199.2
105°	243.7	245.0	246.3	247.3	248.0	248.7	249.3	250.0
107.5°	300.5	301.2	301.9	302.3	302.2	302.2	302.2	302.1
110°	340.1	340.7	341.4	341.6	341.4	341.2	341.0	340.7



TEST NUMBER: P333284-840

CATALOG NUMBER: S125DIP-S1090D1035U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	379.7	380.0	380.3	380.3	379.9	379.5	379.1	378.7
115°	440.1	439.9	439.7	439.5	439.2	439.0	438.8	438.6
117.5°	500.6	500.8	501.0	500.6	499.7	498.9	498.0	497.1
120°	541.4	541.4	541.4	541.0	540.1	539.2	538.3	537.3
122.5°	581.4	581.2	581.0	580.6	579.9	579.2	578.5	577.7
125°	640.4	639.9	639.4	639.0	638.8	638.6	638.4	638.2
127.5°	698.8	698.6	698.4	698.0	697.6	697.1	696.7	696.3
130°	737.5	737.3	737.1	736.8	736.3	735.9	735.4	735.0
132.5°	774.7	774.5	774.2	773.8	773.2	772.5	771.9	771.2
135°	831.7	831.7	831.7	831.3	830.4	829.5	828.6	827.7
137.5°	887.4	887.6	887.9	887.5	886.4	885.2	884.1	883.0
140°	922.4	922.8	923.3	922.9	921.8	920.7	919.6	918.5
142.5°	956.7	956.9	957.3	956.8	955.7	954.6	953.5	952.3
145°	1006.2	1006.2	1006.2	1005.8	1005.2	1004.5	1003.8	1003.2
147.5°	1052.0	1052.6	1053.1	1052.6	1051.1	1049.6	1048.0	1046.5
150°	1080.8	1080.8	1080.8	1080.6	1080.2	1079.6	1079.2	1078.7
152.5°	1107.7	1108.2	1108.7	1108.6	1107.8	1107.0	1106.2	1105.4
155°	1146.1	1147.0	1147.9	1147.8	1146.7	1145.5	1144.4	1143.3
157.5°	1179.3	1180.2	1181.1	1180.8	1179.4	1177.9	1176.4	1175.0
160°	1199.5	1200.4	1201.3	1201.2	1200.1	1199.0	1197.9	1196.7
162.5°	1218.4	1219.5	1220.6	1220.5	1219.2	1217.9	1216.6	1215.3
165°	1243.9	1244.8	1245.7	1245.5	1244.2	1242.7	1241.4	1240.1
167.5°	1262.7	1264.0	1265.5	1265.4	1264.0	1262.6	1261.2	1259.8
170°	1274.0	1275.4	1276.7	1276.6	1275.1	1273.4	1271.9	1270.3
172.5°	1282.1	1283.4	1284.8	1284.8	1283.3	1282.0	1280.6	1279.2
175°	1291.2	1292.5	1293.8	1293.7	1292.2	1290.6	1289.0	1287.5
177.5°	1295.3	1296.4	1297.4	1297.4	1296.1	1294.8	1293.5	1292.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6

(END OF REPORT)