

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333634-830

Luminaire Tested: **S125RDIP-S1270D1205U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333634-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1205U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9177.9 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	32	28	32	28	25	27	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11559	11559	11559	11559
5°	13299	11575	10222	11575
10°	15255	11516	9020	11516
15°	16477	11397	8017	11397
20°	18168	11260	7403	11260
25°	21026	11078	6869	11078
30°	22881	10887	6520	10887
35°	19301	10664	6199	10664
40°	13478	10264	5922	10264
45°	9999	9724	5650	9724
50°	7973	9161	5419	9161
55°	6767	8463	5212	8463
60°	5846	7839	4879	7839
65°	5210	7163	4199	7163
70°	4577	6562	3828	6562
75°	3960	5682	3593	5682
80°	3005	4783	3005	4783
85°	2505	3757	2831	3757



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.6	1.9
10°-20°	503.0	5.5
20°-30°	797.5	8.7
30°-40°	961.7	10.5
40°-50°	858.8	9.4
50°-60°	658.6	7.2
60°-70°	428.0	4.7
70°-80°	208.1	2.3
80°-90°	52.7	0.6
90°-100°	53.7	0.6
100°-110°	330.9	3.6
110°-120°	600.2	6.5
120°-130°	770.3	8.4
130°-140°	828.6	9.0
140°-150°	777.7	8.5
150°-160°	629.1	6.9
160°-170°	406.9	4.4
170°-180°	140.3	1.5
0°-30°	1472.1	16.0
0°-40°	2433.8	26.5
0°-60°	3951.3	43.1
0°-90°	4640.1	50.6
90°-120°	984.9	10.7
90°-150°	3361.5	36.6
90°-180°	4538.0	49.4
0°-180°	9177.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1790	1790	1790	1790	1790	
5°	2051	1785	1577	1785	2051	205
15°	2464	1705	1199	1705	2464	706
25°	2951	1555	964	1555	2951	1355
35°	2448	1353	786	1353	2448	1479
45°	1095	1065	619	1065	1095	874
55°	601	752	463	752	601	545
65°	341	469	275	469	341	339
75°	159	228	144	228	159	169
85°	34	51	38	51	34	40
90°	26	1	26	1	26	13
95°	23	62	23	62	23	19
105°	325	322	325	322	325	294
115°	600	605	600	605	600	596
125°	860	860	860	860	860	765
135°	1068	1072	1068	1072	1068	824
145°	1240	1243	1240	1243	1240	775
155°	1359	1369	1359	1369	1359	627
165°	1437	1445	1437	1445	1437	406
175°	1471	1478	1471	1478	1471	140
180°	1478	1478	1478	1478	1478	



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1882.6	1881.5	1883.9	1877.4	1877.9	1867.9	1867.9	1860.3	1850.3	1842.7	1839.2
5°	2051.3	2052.9	2049.8	2038.8	2031.6	2020.5	2008.0	1985.9	1967.6	1949.9	1936.0
7.5°	2225.1	2226.1	2216.4	2213.0	2194.4	2180.9	2153.1	2123.2	2096.6	2062.8	2036.9
10°	2326.1	2325.4	2315.1	2307.1	2290.8	2270.3	2243.2	2207.8	2174.8	2138.1	2102.8
12.5°	2384.9	2383.0	2379.7	2369.9	2354.9	2336.8	2313.7	2279.0	2238.3	2198.0	2156.8
15°	2464.3	2459.1	2449.6	2437.0	2415.7	2394.4	2368.7	2337.9	2299.0	2253.4	2215.2
17.5°	2562.4	2562.6	2547.9	2530.5	2501.6	2464.0	2424.3	2374.5	2321.6	2271.4	2230.8
20°	2643.5	2641.3	2626.7	2592.8	2559.8	2512.7	2467.2	2406.2	2341.6	2276.1	2225.4
22.5°	2760.0	2754.2	2738.9	2694.5	2643.3	2582.7	2513.0	2438.5	2360.4	2286.1	2219.6
25°	2950.6	2946.2	2916.1	2864.7	2792.7	2699.3	2608.3	2506.1	2393.8	2296.0	2215.2
27.5°	3081.2	3076.3	3053.9	3011.2	2944.8	2846.6	2723.3	2586.8	2446.5	2312.1	2195.5
30°	3068.2	3079.2	3076.3	3056.5	3006.5	2918.3	2804.4	2650.9	2484.1	2326.1	2187.3
32.5°	2883.6	2893.5	2919.3	2958.3	2961.2	2925.9	2840.9	2699.1	2526.4	2346.7	2180.8
35°	2448.1	2461.4	2511.3	2589.9	2692.7	2778.7	2796.3	2720.0	2564.9	2371.7	2171.1
37.5°	1882.1	1954.4	1996.4	2079.2	2234.6	2392.7	2544.8	2600.8	2534.8	2361.4	2155.4
40°	1598.7	1616.4	1691.3	1784.6	1915.4	2080.0	2296.8	2453.2	2458.3	2337.9	2130.7
42.5°	1368.4	1390.7	1442.1	1516.6	1628.6	1793.2	2016.9	2223.5	2319.1	2273.2	2098.4
45°	1094.8	1111.6	1149.1	1206.5	1292.4	1428.3	1620.8	1859.5	2049.2	2123.4	2011.7
47.5°	899.3	908.4	941.0	984.7	1048.3	1147.4	1296.4	1503.6	1731.0	1890.5	1874.7
50°	793.5	803.8	828.8	861.9	915.5	999.2	1118.2	1290.9	1525.3	1720.0	1759.0
52.5°	711.2	719.7	735.3	766.6	810.9	875.2	971.3	1127.5	1338.4	1545.4	1635.5
55°	601.0	606.9	619.3	637.0	672.3	718.6	801.5	909.6	1080.1	1288.7	1421.0
57.5°	510.2	513.1	521.0	537.3	561.8	595.6	655.5	747.1	869.3	1057.2	1203.2
60°	452.6	455.5	465.8	476.8	496.0	526.8	573.8	637.7	755.3	910.3	1058.0
62.5°	406.7	408.5	412.9	424.0	440.7	464.5	501.5	553.6	647.1	783.3	922.8
65°	340.9	341.7	343.1	351.9	362.2	379.8	404.1	440.8	511.3	614.3	737.6
67.5°	277.8	278.7	283.9	287.0	297.7	307.0	321.2	349.3	399.0	468.3	564.3
70°	242.4	241.8	246.9	250.5	254.2	265.2	274.8	297.6	328.4	381.4	461.4
72.5°	209.5	207.6	209.8	211.1	216.0	223.5	233.1	247.0	270.8	307.3	368.5
75°	158.7	159.5	159.5	160.9	164.6	167.5	170.4	177.8	191.1	215.3	248.4
77.5°	111.4	110.2	113.3	113.8	115.9	119.1	121.7	124.6	130.1	140.1	157.1
80°	80.8	80.8	81.5	83.8	83.0	84.5	88.1	91.1	97.7	103.6	109.4
82.5°	62.0	61.5	62.1	62.6	62.5	63.9	65.2	65.8	68.3	71.3	75.4
85°	33.8	33.8	34.5	34.5	35.3	35.3	36.0	36.0	36.0	36.8	37.5
87.5°	18.2	17.4	16.7	16.6	17.1	18.0	17.2	16.3	16.1	15.8	16.1
90°	26.3	25.5	24.8	24.1	23.4	22.4	21.2	20.0	18.8	17.5	15.8
92.5°	24.5	24.2	23.8	23.5	23.2	22.4	21.2	20.0	18.8	17.5	16.0
95°	23.0	23.0	23.0	23.0	23.0	22.4	21.2	20.0	18.8	17.5	26.8
97.5°	23.0	23.0	23.0	23.0	23.0	26.4	33.3	40.2	47.0	53.9	72.2
100°	23.0	23.9	25.0	25.9	26.9	45.5	81.8	118.1	154.3	190.6	189.6
102.5°	137.8	154.4	170.9	187.5	204.1	215.7	222.6	229.4	236.3	243.2	242.6
105°	325.4	325.6	325.8	326.0	326.3	326.4	326.4	326.4	326.4	326.4	326.4
107.5°	410.1	410.9	411.6	412.3	413.0	413.4	413.3	413.3	413.2	413.2	412.7
110°	468.8	468.6	468.3	468.1	467.9	468.1	468.8	469.6	470.3	471.0	470.5



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	521.4	521.8	522.1	522.5	522.7	523.4	524.3	525.3	526.2	527.1	526.8
115°	600.3	601.7	603.2	604.6	606.1	607.4	608.3	609.3	610.3	611.2	611.0
117.5°	684.4	685.0	685.7	686.3	686.9	687.9	689.2	690.4	691.7	693.0	692.0
120°	736.1	737.4	738.6	739.8	741.0	741.9	742.3	742.8	743.3	743.8	743.0
122.5°	785.2	786.6	788.0	789.4	790.8	791.8	792.3	792.8	793.2	793.7	793.4
125°	859.9	860.6	861.4	862.0	862.8	863.7	864.6	865.6	866.6	867.5	867.5
127.5°	922.7	924.5	926.3	928.2	930.0	931.1	931.7	932.2	932.7	933.3	933.4
130°	968.4	969.6	970.8	971.9	973.2	974.2	974.9	975.6	976.4	977.1	976.9
132.5°	1010.4	1011.6	1012.9	1014.1	1015.3	1016.0	1016.1	1016.2	1016.4	1016.5	1017.1
135°	1068.0	1069.5	1070.9	1072.4	1073.8	1074.9	1075.3	1075.8	1076.3	1076.8	1077.2
137.5°	1125.9	1127.1	1128.4	1129.6	1131.0	1131.5	1131.4	1131.3	1131.2	1131.1	1131.5
140°	1160.1	1161.5	1163.0	1164.4	1165.8	1166.4	1165.8	1165.4	1164.9	1164.4	1164.7
142.5°	1192.5	1193.9	1195.4	1196.8	1198.3	1199.0	1198.9	1198.8	1198.7	1198.6	1198.3
145°	1240.0	1241.4	1242.9	1244.3	1245.9	1246.4	1246.2	1245.9	1245.8	1245.5	1245.5
147.5°	1279.2	1281.0	1282.7	1284.5	1286.2	1286.9	1286.7	1286.4	1286.1	1285.8	1285.5
150°	1304.7	1306.6	1308.5	1310.5	1312.4	1313.2	1312.7	1312.2	1311.6	1311.2	1310.7
152.5°	1328.3	1330.0	1331.8	1333.5	1335.3	1336.0	1335.5	1334.9	1334.5	1334.0	1333.5
155°	1359.4	1361.3	1363.3	1365.3	1367.2	1367.8	1367.1	1366.3	1365.6	1364.9	1364.4
157.5°	1385.4	1387.4	1389.4	1391.3	1393.3	1393.8	1393.1	1392.3	1391.5	1390.7	1390.7
160°	1402.1	1404.1	1406.0	1408.0	1409.9	1410.4	1409.4	1408.4	1407.5	1406.5	1406.3
162.5°	1417.0	1419.2	1421.3	1423.4	1425.6	1426.0	1424.7	1423.2	1421.9	1420.5	1420.3
165°	1437.2	1439.1	1441.1	1443.0	1444.9	1445.2	1443.8	1442.3	1440.9	1439.4	1439.1
167.5°	1451.2	1453.4	1455.6	1457.7	1460.0	1460.2	1458.4	1456.7	1454.9	1453.2	1452.9
170°	1459.1	1461.3	1463.5	1465.7	1467.8	1468.0	1466.0	1464.1	1462.2	1460.2	1459.9
172.5°	1464.3	1466.5	1468.8	1470.9	1473.1	1473.3	1471.6	1469.8	1468.1	1466.3	1465.8
175°	1471.1	1473.3	1475.6	1477.7	1479.9	1480.0	1478.1	1476.1	1474.1	1472.3	1472.0
177.5°	1475.1	1476.6	1478.2	1479.8	1481.3	1481.4	1480.1	1478.7	1477.3	1475.9	1475.7
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1839.2	1835.0	1827.4	1820.3	1811.6	1803.9	1798.6	1792.2	1784.0	1774.0	1765.7
5°	1920.5	1904.4	1883.1	1864.7	1841.3	1822.9	1803.7	1785.4	1767.0	1743.5	1723.0
7.5°	2010.8	1977.5	1944.9	1904.1	1867.1	1834.0	1802.2	1770.1	1738.6	1705.2	1673.1
10°	2066.1	2025.6	1980.8	1929.4	1882.4	1837.6	1796.4	1756.0	1713.4	1675.9	1635.5
12.5°	2117.8	2065.6	2014.3	1949.4	1892.9	1838.1	1785.8	1735.4	1689.9	1641.2	1597.9
15°	2164.5	2113.1	2055.8	1976.4	1897.8	1831.6	1769.9	1704.6	1647.9	1593.7	1545.1
17.5°	2182.6	2128.6	2062.1	1985.8	1899.9	1816.7	1737.2	1665.5	1598.9	1535.6	1481.0
20°	2175.5	2123.4	2055.0	1982.3	1890.5	1803.7	1717.8	1638.4	1564.2	1497.3	1439.4
22.5°	2158.5	2104.5	2038.5	1961.7	1874.5	1782.6	1690.7	1606.1	1528.3	1459.2	1395.8
25°	2132.9	2059.5	1991.9	1916.8	1833.9	1742.8	1647.9	1554.6	1471.7	1401.1	1332.1
27.5°	2106.3	2014.6	1928.6	1854.2	1766.4	1685.2	1593.7	1498.1	1410.8	1339.0	1268.1
30°	2082.2	1979.3	1884.5	1800.1	1717.0	1639.9	1553.2	1459.9	1370.3	1296.1	1224.1
32.5°	2052.2	1942.9	1838.7	1741.3	1661.2	1584.7	1506.2	1417.0	1329.7	1253.1	1180.0
35°	2014.6	1875.0	1761.9	1658.3	1569.3	1495.2	1424.7	1352.6	1265.2	1185.8	1114.6
37.5°	1965.2	1806.9	1675.9	1563.0	1469.3	1394.8	1339.1	1273.3	1193.4	1117.5	1051.4
40°	1935.2	1757.5	1614.2	1502.5	1404.0	1325.4	1273.3	1217.5	1144.7	1073.5	1007.3
42.5°	1895.3	1712.2	1551.9	1435.5	1336.4	1260.7	1208.1	1159.2	1098.3	1031.1	960.3
45°	1816.9	1624.5	1456.2	1331.3	1231.4	1157.2	1108.0	1064.6	1018.3	956.6	894.8
47.5°	1715.0	1533.0	1356.9	1220.5	1122.7	1053.8	1006.0	971.8	938.7	886.2	826.2
50°	1633.3	1457.7	1285.7	1153.5	1049.1	983.8	939.0	911.8	881.7	833.9	783.9
52.5°	1536.9	1380.1	1211.7	1076.5	978.1	916.8	873.7	846.6	821.7	782.8	735.2
55°	1385.0	1247.5	1093.3	970.5	880.2	818.5	777.3	751.6	737.0	703.9	666.4
57.5°	1209.7	1111.2	975.2	856.9	776.9	716.0	685.8	663.9	647.3	624.0	597.5
60°	1087.4	1018.3	896.4	783.9	710.5	652.4	625.3	606.9	591.4	571.7	551.0
62.5°	963.4	913.1	807.0	710.5	642.9	594.3	568.8	552.2	534.4	521.0	501.1
65°	797.2	752.3	678.9	603.2	540.7	501.8	483.4	468.7	457.7	443.0	429.0
67.5°	620.1	601.9	551.2	499.0	454.2	419.5	403.7	393.4	380.1	371.4	361.7
70°	511.3	502.6	466.6	432.1	390.1	366.6	351.9	347.5	331.4	322.5	315.9
72.5°	415.0	410.9	390.1	366.2	336.7	316.0	302.6	297.6	287.3	280.2	276.0
75°	284.4	285.8	282.1	266.7	255.7	242.4	230.7	227.7	220.5	214.5	210.8
77.5°	179.8	187.4	187.7	186.9	182.5	174.5	169.6	167.4	160.1	158.0	157.1
80°	123.5	131.5	138.8	138.1	136.7	134.5	130.8	128.6	124.9	122.7	121.2
82.5°	82.3	89.8	96.0	99.9	99.6	97.5	94.9	93.9	93.1	91.5	91.2
85°	38.9	40.4	42.6	47.8	51.5	52.1	51.5	50.7	48.4	49.2	50.0
87.5°	16.3	16.0	16.2	15.9	14.9	17.4	18.9	19.0	18.3	17.4	16.7
90°	14.1	12.4	10.7	8.9	7.0	5.0	3.0	1.1	3.0	5.0	7.0
92.5°	14.5	13.0	11.5	11.4	12.8	14.1	15.6	16.9	15.6	14.1	12.8
95°	36.0	45.2	54.6	59.5	60.2	61.0	61.7	62.4	61.7	61.0	60.2
97.5°	90.5	108.8	127.1	135.6	134.3	133.0	131.7	130.4	131.7	133.0	134.3
100°	188.7	187.7	186.7	185.9	185.1	184.4	183.7	182.9	183.7	184.4	185.1
102.5°	242.0	241.4	240.8	240.1	239.1	238.3	237.3	236.4	237.3	238.3	239.1
105°	326.4	326.4	326.4	325.9	325.0	324.0	323.0	322.1	323.0	324.0	325.0
107.5°	412.2	411.7	411.2	411.0	411.0	411.0	411.0	411.0	411.0	411.0	411.0
110°	470.0	469.6	469.1	468.8	468.8	468.8	468.8	468.8	468.8	468.8	468.8



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	526.5	526.2	525.9	525.5	524.9	524.3	523.8	523.2	523.8	524.3	524.9
115°	610.8	610.5	610.3	609.5	608.3	607.1	605.9	604.6	605.9	607.1	608.3
117.5°	691.1	690.2	689.3	688.8	688.9	688.9	689.0	689.0	689.0	688.9	688.9
120°	742.3	741.6	740.8	740.6	740.8	741.1	741.3	741.6	741.3	741.1	740.8
122.5°	793.1	792.7	792.4	791.7	790.8	789.9	789.0	788.1	789.0	789.9	790.8
125°	867.5	867.5	867.5	866.7	865.0	863.3	861.6	859.9	861.6	863.3	865.0
127.5°	933.6	933.7	933.9	933.3	932.1	930.9	929.7	928.5	929.7	930.9	932.1
130°	976.7	976.4	976.1	975.4	974.2	973.0	971.8	970.5	971.8	973.0	974.2
132.5°	1017.6	1018.1	1018.7	1018.2	1016.8	1015.4	1014.0	1012.6	1014.0	1015.4	1016.8
135°	1077.8	1078.3	1078.7	1078.3	1076.8	1075.3	1073.8	1072.4	1073.8	1075.3	1076.8
137.5°	1132.0	1132.5	1132.8	1132.5	1131.1	1129.9	1128.7	1127.4	1128.7	1129.9	1131.1
140°	1164.9	1165.2	1165.4	1165.3	1164.8	1164.3	1163.9	1163.3	1163.9	1164.3	1164.8
142.5°	1197.9	1197.6	1197.2	1196.9	1196.7	1196.4	1196.0	1195.7	1196.0	1196.4	1196.7
145°	1245.5	1245.5	1245.5	1245.2	1244.7	1244.3	1243.8	1243.3	1243.8	1244.3	1244.7
147.5°	1285.2	1284.9	1284.6	1284.5	1284.6	1284.7	1284.8	1284.9	1284.8	1284.7	1284.6
150°	1310.2	1309.8	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2	1310.7	1310.2	1309.8
152.5°	1333.0	1332.6	1332.0	1332.3	1333.4	1334.5	1335.6	1336.6	1335.6	1334.5	1333.4
155°	1363.9	1363.4	1362.9	1363.4	1364.9	1366.3	1367.8	1369.2	1367.8	1366.3	1364.9
157.5°	1390.6	1390.6	1390.5	1390.9	1391.9	1392.7	1393.5	1394.5	1393.5	1392.7	1391.9
160°	1406.0	1405.8	1405.5	1406.2	1407.6	1409.1	1410.5	1412.0	1410.5	1409.1	1407.6
162.5°	1420.0	1419.8	1419.6	1420.1	1421.6	1423.1	1424.6	1426.0	1424.6	1423.1	1421.6
165°	1438.9	1438.6	1438.4	1439.0	1440.5	1441.9	1443.4	1444.8	1443.4	1441.9	1440.5
167.5°	1452.6	1452.5	1452.2	1452.8	1454.3	1455.9	1457.4	1458.9	1457.4	1455.9	1454.3
170°	1459.7	1459.4	1459.2	1459.9	1461.6	1463.3	1465.1	1466.8	1465.1	1463.3	1461.6
172.5°	1465.5	1465.0	1464.5	1465.2	1466.9	1468.6	1470.3	1472.0	1470.3	1468.6	1466.9
175°	1471.8	1471.5	1471.2	1471.9	1473.3	1474.8	1476.2	1477.7	1476.2	1474.8	1473.3
177.5°	1475.6	1475.4	1475.2	1475.6	1476.9	1478.0	1479.1	1480.4	1479.1	1478.0	1476.9
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1759.8	1751.6	1745.7	1733.9	1725.7	1722.2	1715.7	1713.9	1720.4	1715.7	1715.1
5°	1707.5	1686.2	1669.3	1652.4	1634.0	1622.3	1604.7	1601.7	1597.3	1590.6	1589.2
7.5°	1644.7	1617.0	1595.3	1567.4	1543.0	1523.5	1501.5	1491.0	1485.4	1476.8	1465.4
10°	1602.4	1569.3	1540.0	1512.0	1482.0	1457.7	1435.7	1418.7	1407.7	1397.4	1393.1
12.5°	1560.7	1527.0	1489.4	1455.7	1422.0	1394.8	1370.4	1359.4	1347.2	1335.1	1324.8
15°	1495.9	1451.0	1409.9	1371.0	1342.4	1313.0	1289.4	1273.3	1254.9	1249.8	1229.9
17.5°	1427.1	1383.2	1335.0	1294.0	1260.7	1228.4	1202.6	1184.2	1170.4	1151.5	1142.4
20°	1384.2	1332.1	1285.1	1247.5	1210.8	1172.6	1146.1	1130.8	1117.5	1102.1	1094.8
22.5°	1338.4	1287.4	1239.2	1195.2	1157.9	1120.3	1101.5	1085.5	1070.4	1056.2	1046.5
25°	1271.1	1219.7	1168.9	1123.4	1084.5	1057.2	1035.2	1016.8	1008.8	994.9	984.5
27.5°	1204.5	1149.8	1097.2	1051.8	1021.2	994.4	976.3	961.8	947.2	935.0	926.0
30°	1161.6	1105.8	1048.5	1012.5	980.1	954.4	934.5	920.6	909.6	898.5	891.9
32.5°	1118.7	1061.1	1010.2	971.3	940.8	918.5	898.1	884.8	873.2	860.9	853.2
35°	1049.9	991.2	950.0	911.8	881.7	861.1	847.2	828.0	818.5	809.6	801.5
37.5°	986.0	931.3	886.8	853.3	827.2	806.7	788.6	778.4	766.6	758.7	752.0
40°	939.0	889.0	848.6	813.3	794.3	771.5	754.6	741.3	732.5	722.3	714.9
42.5°	896.6	850.3	811.0	779.3	755.4	736.2	719.9	706.6	695.5	688.2	681.9
45°	836.9	790.6	752.3	722.9	701.0	682.6	665.6	659.0	644.3	635.6	632.6
47.5°	775.0	733.6	696.6	669.6	647.0	629.6	613.8	600.3	592.2	583.5	578.8
50°	733.3	693.6	659.0	632.6	610.6	591.4	576.7	568.0	556.9	548.8	543.0
52.5°	691.5	654.8	620.3	594.9	575.9	556.8	540.4	531.5	521.0	515.9	511.8
55°	631.9	593.0	563.5	538.6	518.7	501.1	485.7	476.8	470.2	465.1	463.6
57.5°	564.3	533.4	506.1	483.6	463.0	446.4	432.9	424.5	418.7	417.9	413.5
60°	520.2	492.3	467.3	443.0	425.4	410.0	398.2	388.7	382.8	382.0	380.6
62.5°	476.1	449.3	426.1	404.8	389.0	374.1	363.0	352.2	348.7	345.1	341.8
65°	410.7	386.4	367.4	350.4	333.6	321.0	310.1	303.4	295.4	291.0	282.9
67.5°	346.5	327.7	309.3	295.1	281.8	269.9	260.8	251.0	245.5	242.0	236.1
70°	304.2	289.5	271.1	255.7	245.4	235.8	228.5	217.4	213.8	210.8	207.9
72.5°	264.2	251.3	235.8	223.4	213.1	204.1	195.6	190.4	186.8	183.8	182.1
75°	207.9	195.5	182.2	173.4	166.1	158.7	154.3	150.6	149.1	148.5	145.4
77.5°	152.7	146.1	135.4	128.5	123.6	120.6	116.7	114.8	114.6	111.4	110.4
80°	116.8	113.1	104.3	101.4	97.7	94.8	92.6	88.9	85.2	83.8	81.5
82.5°	86.8	83.1	79.6	74.9	71.8	70.1	67.9	66.5	67.0	64.9	63.9
85°	46.3	42.6	41.2	40.4	38.9	40.4	39.7	38.9	38.2	37.5	38.2
87.5°	16.5	16.9	16.6	18.1	16.7	17.6	17.8	17.5	17.7	18.0	17.6
90°	8.9	10.7	12.4	14.1	15.8	17.5	18.8	20.0	21.2	22.4	23.4
92.5°	11.4	11.5	13.0	14.5	16.0	17.5	18.8	20.0	21.2	22.4	23.2
95°	59.5	54.6	45.2	36.0	26.8	17.5	18.8	20.0	21.2	22.4	23.0
97.5°	135.6	127.1	108.8	90.5	72.2	53.9	47.0	40.2	33.3	26.4	23.0
100°	185.9	186.7	187.7	188.7	189.6	190.6	154.3	118.1	81.8	45.5	26.9
102.5°	240.1	240.8	241.4	242.0	242.6	243.2	236.3	229.4	222.6	215.7	204.1
105°	325.9	326.4	326.4	326.4	326.4	326.4	326.4	326.4	326.4	326.4	326.3
107.5°	411.0	411.2	411.7	412.2	412.7	413.2	413.2	413.3	413.3	413.4	413.0
110°	468.8	469.1	469.6	470.0	470.5	471.0	470.3	469.6	468.8	468.1	467.9



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	525.5	525.9	526.2	526.5	526.8	527.1	526.2	525.3	524.3	523.4	522.7
115°	609.5	610.3	610.5	610.8	611.0	611.2	610.3	609.3	608.3	607.4	606.1
117.5°	688.8	689.3	690.2	691.1	692.0	693.0	691.7	690.4	689.2	687.9	686.9
120°	740.6	740.8	741.6	742.3	743.0	743.8	743.3	742.8	742.3	741.9	741.0
122.5°	791.7	792.4	792.7	793.1	793.4	793.7	793.2	792.8	792.3	791.8	790.8
125°	866.7	867.5	867.5	867.5	867.5	867.5	866.6	865.6	864.6	863.7	862.8
127.5°	933.3	933.9	933.7	933.6	933.4	933.3	932.7	932.2	931.7	931.1	930.0
130°	975.4	976.1	976.4	976.7	976.9	977.1	976.4	975.6	974.9	974.2	973.2
132.5°	1018.2	1018.7	1018.1	1017.6	1017.1	1016.5	1016.4	1016.2	1016.1	1016.0	1015.3
135°	1078.3	1078.7	1078.3	1077.8	1077.2	1076.8	1076.3	1075.8	1075.3	1074.9	1073.8
137.5°	1132.5	1132.8	1132.5	1132.0	1131.5	1131.1	1131.2	1131.3	1131.4	1131.5	1131.0
140°	1165.3	1165.4	1165.2	1164.9	1164.7	1164.4	1164.9	1165.4	1165.8	1166.4	1165.8
142.5°	1196.9	1197.2	1197.6	1197.9	1198.3	1198.6	1198.7	1198.8	1198.9	1199.0	1198.3
145°	1245.2	1245.5	1245.5	1245.5	1245.5	1245.5	1245.8	1245.9	1246.2	1246.4	1245.9
147.5°	1284.5	1284.6	1284.9	1285.2	1285.5	1285.8	1286.1	1286.4	1286.7	1286.9	1286.2
150°	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2	1311.6	1312.2	1312.7	1313.2	1312.4
152.5°	1332.3	1332.0	1332.6	1333.0	1333.5	1334.0	1334.5	1334.9	1335.5	1336.0	1335.3
155°	1363.4	1362.9	1363.4	1363.9	1364.4	1364.9	1365.6	1366.3	1367.1	1367.8	1367.2
157.5°	1390.9	1390.5	1390.6	1390.6	1390.7	1390.7	1391.5	1392.3	1393.1	1393.8	1393.3
160°	1406.2	1405.5	1405.8	1406.0	1406.3	1406.5	1407.5	1408.4	1409.4	1410.4	1409.9
162.5°	1420.1	1419.6	1419.8	1420.0	1420.3	1420.5	1421.9	1423.2	1424.7	1426.0	1425.6
165°	1439.0	1438.4	1438.6	1438.9	1439.1	1439.4	1440.9	1442.3	1443.8	1445.2	1444.9
167.5°	1452.8	1452.2	1452.5	1452.6	1452.9	1453.2	1454.9	1456.7	1458.4	1460.2	1460.0
170°	1459.9	1459.2	1459.4	1459.7	1459.9	1460.2	1462.2	1464.1	1466.0	1468.0	1467.8
172.5°	1465.2	1464.5	1465.0	1465.5	1465.8	1466.3	1468.1	1469.8	1471.6	1473.3	1473.1
175°	1471.9	1471.2	1471.5	1471.8	1472.0	1472.3	1474.1	1476.1	1478.1	1480.0	1479.9
177.5°	1475.6	1475.2	1475.4	1475.6	1475.7	1475.9	1477.3	1478.7	1480.1	1481.4	1481.3
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1714.6	1708.1	1706.3	1708.6	1706.3	1708.1	1714.6	1715.1	1715.7	1720.4	1713.9
5°	1581.9	1574.5	1578.2	1576.7	1578.2	1574.5	1581.9	1589.2	1590.6	1597.3	1601.7
7.5°	1465.2	1456.0	1446.3	1449.4	1446.3	1456.0	1465.2	1465.4	1476.8	1485.4	1491.0
10°	1383.5	1376.1	1371.7	1375.4	1371.7	1376.1	1383.5	1393.1	1397.4	1407.7	1418.7
12.5°	1314.8	1310.3	1306.5	1304.9	1306.5	1310.3	1314.8	1324.8	1335.1	1347.2	1359.4
15°	1221.1	1212.3	1208.6	1199.1	1208.6	1212.3	1221.1	1229.9	1249.8	1254.9	1273.3
17.5°	1134.8	1131.9	1122.4	1118.2	1122.4	1131.9	1134.8	1142.4	1151.5	1170.4	1184.2
20°	1083.7	1080.8	1071.2	1077.1	1071.2	1080.8	1083.7	1094.8	1102.1	1117.5	1130.8
22.5°	1041.4	1034.9	1031.8	1030.1	1031.8	1034.9	1041.4	1046.5	1056.2	1070.4	1085.5
25°	981.6	972.0	968.4	963.9	968.4	972.0	981.6	984.5	994.9	1008.8	1016.8
27.5°	921.9	916.8	911.9	910.8	911.9	916.8	921.9	926.0	935.0	947.2	961.8
30°	883.2	878.0	874.3	874.3	874.3	878.0	883.2	891.9	898.5	909.6	920.6
32.5°	848.5	844.5	840.8	840.3	840.8	844.5	848.5	853.2	860.9	873.2	884.8
35°	798.0	792.0	790.6	786.2	790.6	792.0	798.0	801.5	809.6	818.5	828.0
37.5°	745.5	740.6	740.5	740.0	740.5	740.6	745.5	752.0	758.7	766.6	778.4
40°	711.9	708.2	707.6	702.4	707.6	708.2	711.9	714.9	722.3	732.5	741.3
42.5°	676.1	674.2	671.7	669.5	671.7	674.2	676.1	681.9	688.2	695.5	706.6
45°	627.5	622.3	622.3	618.6	622.3	622.3	627.5	632.6	635.6	644.3	659.0
47.5°	577.2	573.3	573.6	569.9	573.6	573.3	577.2	578.8	583.5	592.2	600.3
50°	543.7	541.5	540.7	539.3	540.7	541.5	543.7	543.0	548.8	556.9	568.0
52.5°	510.2	509.2	512.0	508.7	512.0	509.2	510.2	511.8	515.9	521.0	531.5
55°	465.1	462.9	467.3	462.9	467.3	462.9	465.1	463.6	465.1	470.2	476.8
57.5°	413.2	411.1	415.1	412.9	415.1	411.1	413.2	413.5	417.9	418.7	424.5
60°	379.1	374.8	376.9	377.7	376.9	374.8	379.1	380.6	382.0	382.8	388.7
62.5°	338.6	335.9	337.5	334.1	337.5	335.9	338.6	341.8	345.1	348.7	352.2
65°	281.4	279.2	276.3	274.8	276.3	279.2	281.4	282.9	291.0	295.4	303.4
67.5°	236.4	231.1	231.0	232.1	231.0	231.1	236.4	236.1	242.0	245.5	251.0
70°	203.5	203.5	202.7	202.7	202.7	203.5	203.5	207.9	210.8	213.8	217.4
72.5°	180.6	180.0	178.7	178.1	178.7	180.0	180.6	182.1	183.8	186.8	190.4
75°	145.4	146.2	144.8	144.0	144.8	146.2	145.4	145.4	148.5	149.1	150.6
77.5°	107.4	104.3	105.9	104.3	105.9	104.3	107.4	110.4	111.4	114.6	114.8
80°	81.5	80.8	83.0	80.8	83.0	80.8	81.5	81.5	83.8	85.2	88.9
82.5°	64.5	63.8	64.8	63.2	64.8	63.8	64.5	63.9	64.9	67.0	66.5
85°	38.9	38.2	37.5	38.2	37.5	38.2	38.9	38.2	37.5	38.2	38.9
87.5°	18.4	17.9	18.0	18.2	18.0	17.9	18.4	17.6	18.0	17.7	17.5
90°	24.1	24.8	25.5	26.3	25.5	24.8	24.1	23.4	22.4	21.2	20.0
92.5°	23.5	23.8	24.2	24.5	24.2	23.8	23.5	23.2	22.4	21.2	20.0
95°	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0	22.4	21.2	20.0
97.5°	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0	26.4	33.3	40.2
100°	25.9	25.0	23.9	23.0	23.9	25.0	25.9	26.9	45.5	81.8	118.1
102.5°	187.5	170.9	154.4	137.8	154.4	170.9	187.5	204.1	215.7	222.6	229.4
105°	326.0	325.8	325.6	325.4	325.6	325.8	326.0	326.3	326.4	326.4	326.4
107.5°	412.3	411.6	410.9	410.1	410.9	411.6	412.3	413.0	413.4	413.3	413.3
110°	468.1	468.3	468.6	468.8	468.6	468.3	468.1	467.9	468.1	468.8	469.6



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.5	522.1	521.8	521.4	521.8	522.1	522.5	522.7	523.4	524.3	525.3
115°	604.6	603.2	601.7	600.3	601.7	603.2	604.6	606.1	607.4	608.3	609.3
117.5°	686.3	685.7	685.0	684.4	685.0	685.7	686.3	686.9	687.9	689.2	690.4
120°	739.8	738.6	737.4	736.1	737.4	738.6	739.8	741.0	741.9	742.3	742.8
122.5°	789.4	788.0	786.6	785.2	786.6	788.0	789.4	790.8	791.8	792.3	792.8
125°	862.0	861.4	860.6	859.9	860.6	861.4	862.0	862.8	863.7	864.6	865.6
127.5°	928.2	926.3	924.5	922.7	924.5	926.3	928.2	930.0	931.1	931.7	932.2
130°	971.9	970.8	969.6	968.4	969.6	970.8	971.9	973.2	974.2	974.9	975.6
132.5°	1014.1	1012.9	1011.6	1010.4	1011.6	1012.9	1014.1	1015.3	1016.0	1016.1	1016.2
135°	1072.4	1070.9	1069.5	1068.0	1069.5	1070.9	1072.4	1073.8	1074.9	1075.3	1075.8
137.5°	1129.6	1128.4	1127.1	1125.9	1127.1	1128.4	1129.6	1131.0	1131.5	1131.4	1131.3
140°	1164.4	1163.0	1161.5	1160.1	1161.5	1163.0	1164.4	1165.8	1166.4	1165.8	1165.4
142.5°	1196.8	1195.4	1193.9	1192.5	1193.9	1195.4	1196.8	1198.3	1199.0	1198.9	1198.8
145°	1244.3	1242.9	1241.4	1240.0	1241.4	1242.9	1244.3	1245.9	1246.4	1246.2	1245.9
147.5°	1284.5	1282.7	1281.0	1279.2	1281.0	1282.7	1284.5	1286.2	1286.9	1286.7	1286.4
150°	1310.5	1308.5	1306.6	1304.7	1306.6	1308.5	1310.5	1312.4	1313.2	1312.7	1312.2
152.5°	1333.5	1331.8	1330.0	1328.3	1330.0	1331.8	1333.5	1335.3	1336.0	1335.5	1334.9
155°	1365.3	1363.3	1361.3	1359.4	1361.3	1363.3	1365.3	1367.2	1367.8	1367.1	1366.3
157.5°	1391.3	1389.4	1387.4	1385.4	1387.4	1389.4	1391.3	1393.3	1393.8	1393.1	1392.3
160°	1408.0	1406.0	1404.1	1402.1	1404.1	1406.0	1408.0	1409.9	1410.4	1409.4	1408.4
162.5°	1423.4	1421.3	1419.2	1417.0	1419.2	1421.3	1423.4	1425.6	1426.0	1424.7	1423.2
165°	1443.0	1441.1	1439.1	1437.2	1439.1	1441.1	1443.0	1444.9	1445.2	1443.8	1442.3
167.5°	1457.7	1455.6	1453.4	1451.2	1453.4	1455.6	1457.7	1460.0	1460.2	1458.4	1456.7
170°	1465.7	1463.5	1461.3	1459.1	1461.3	1463.5	1465.7	1467.8	1468.0	1466.0	1464.1
172.5°	1470.9	1468.8	1466.5	1464.3	1466.5	1468.8	1470.9	1473.1	1473.3	1471.6	1469.8
175°	1477.7	1475.6	1473.3	1471.1	1473.3	1475.6	1477.7	1479.9	1480.0	1478.1	1476.1
177.5°	1479.8	1478.2	1476.6	1475.1	1476.6	1478.2	1479.8	1481.3	1481.4	1480.1	1478.7
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1715.7	1722.2	1725.7	1733.9	1745.7	1751.6	1759.8	1765.7	1774.0	1784.0	1792.2
5°	1604.7	1622.3	1634.0	1652.4	1669.3	1686.2	1707.5	1723.0	1743.5	1767.0	1785.4
7.5°	1501.5	1523.5	1543.0	1567.4	1595.3	1617.0	1644.7	1673.1	1705.2	1738.6	1770.1
10°	1435.7	1457.7	1482.0	1512.0	1540.0	1569.3	1602.4	1635.5	1675.9	1713.4	1756.0
12.5°	1370.4	1394.8	1422.0	1455.7	1489.4	1527.0	1560.7	1597.9	1641.2	1689.9	1735.4
15°	1289.4	1313.0	1342.4	1371.0	1409.9	1451.0	1495.9	1545.1	1593.7	1647.9	1704.6
17.5°	1202.6	1228.4	1260.7	1294.0	1335.0	1383.2	1427.1	1481.0	1535.6	1598.9	1665.5
20°	1146.1	1172.6	1210.8	1247.5	1285.1	1332.1	1384.2	1439.4	1497.3	1564.2	1638.4
22.5°	1101.5	1120.3	1157.9	1195.2	1239.2	1287.4	1338.4	1395.8	1459.2	1528.3	1606.1
25°	1035.2	1057.2	1084.5	1123.4	1168.9	1219.7	1271.1	1332.1	1401.1	1471.7	1554.6
27.5°	976.3	994.4	1021.2	1051.8	1097.2	1149.8	1204.5	1268.1	1339.0	1410.8	1498.1
30°	934.5	954.4	980.1	1012.5	1048.5	1105.8	1161.6	1224.1	1296.1	1370.3	1459.9
32.5°	898.1	918.5	940.8	971.3	1010.2	1061.1	1118.7	1180.0	1253.1	1329.7	1417.0
35°	847.2	861.1	881.7	911.8	950.0	991.2	1049.9	1114.6	1185.8	1265.2	1352.6
37.5°	788.6	806.7	827.2	853.3	886.8	931.3	986.0	1051.4	1117.5	1193.4	1273.3
40°	754.6	771.5	794.3	813.3	848.6	889.0	939.0	1007.3	1073.5	1144.7	1217.5
42.5°	719.9	736.2	755.4	779.3	811.0	850.3	896.6	960.3	1031.1	1098.3	1159.2
45°	665.6	682.6	701.0	722.9	752.3	790.6	836.9	894.8	956.6	1018.3	1064.6
47.5°	613.8	629.6	647.0	669.6	696.6	733.6	775.0	826.2	886.2	938.7	971.8
50°	576.7	591.4	610.6	632.6	659.0	693.6	733.3	783.9	833.9	881.7	911.8
52.5°	540.4	556.8	575.9	594.9	620.3	654.8	691.5	735.2	782.8	821.7	846.6
55°	485.7	501.1	518.7	538.6	563.5	593.0	631.9	666.4	703.9	737.0	751.6
57.5°	432.9	446.4	463.0	483.6	506.1	533.4	564.3	597.5	624.0	647.3	663.9
60°	398.2	410.0	425.4	443.0	467.3	492.3	520.2	551.0	571.7	591.4	606.9
62.5°	363.0	374.1	389.0	404.8	426.1	449.3	476.1	501.1	521.0	534.4	552.2
65°	310.1	321.0	333.6	350.4	367.4	386.4	410.7	429.0	443.0	457.7	468.7
67.5°	260.8	269.9	281.8	295.1	309.3	327.7	346.5	361.7	371.4	380.1	393.4
70°	228.5	235.8	245.4	255.7	271.1	289.5	304.2	315.9	322.5	331.4	347.5
72.5°	195.6	204.1	213.1	223.4	235.8	251.3	264.2	276.0	280.2	287.3	297.6
75°	154.3	158.7	166.1	173.4	182.2	195.5	207.9	210.8	214.5	220.5	227.7
77.5°	116.7	120.6	123.6	128.5	135.4	146.1	152.7	157.1	158.0	160.1	167.4
80°	92.6	94.8	97.7	101.4	104.3	113.1	116.8	121.2	122.7	124.9	128.6
82.5°	67.9	70.1	71.8	74.9	79.6	83.1	86.8	91.2	91.5	93.1	93.9
85°	39.7	40.4	38.9	40.4	41.2	42.6	46.3	50.0	49.2	48.4	50.7
87.5°	17.8	17.6	16.7	18.1	16.6	16.9	16.5	16.7	17.4	18.3	19.0
90°	18.8	17.5	15.8	14.1	12.4	10.7	8.9	7.0	5.0	3.0	1.1
92.5°	18.8	17.5	16.0	14.5	13.0	11.5	11.4	12.8	14.1	15.6	16.9
95°	18.8	17.5	26.8	36.0	45.2	54.6	59.5	60.2	61.0	61.7	62.4
97.5°	47.0	53.9	72.2	90.5	108.8	127.1	135.6	134.3	133.0	131.7	130.4
100°	154.3	190.6	189.6	188.7	187.7	186.7	185.9	185.1	184.4	183.7	182.9
102.5°	236.3	243.2	242.6	242.0	241.4	240.8	240.1	239.1	238.3	237.3	236.4
105°	326.4	326.4	326.4	326.4	326.4	326.4	325.9	325.0	324.0	323.0	322.1
107.5°	413.2	413.2	412.7	412.2	411.7	411.2	411.0	411.0	411.0	411.0	411.0
110°	470.3	471.0	470.5	470.0	469.6	469.1	468.8	468.8	468.8	468.8	468.8



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	526.2	527.1	526.8	526.5	526.2	525.9	525.5	524.9	524.3	523.8	523.2
115°	610.3	611.2	611.0	610.8	610.5	610.3	609.5	608.3	607.1	605.9	604.6
117.5°	691.7	693.0	692.0	691.1	690.2	689.3	688.8	688.9	688.9	689.0	689.0
120°	743.3	743.8	743.0	742.3	741.6	740.8	740.6	740.8	741.1	741.3	741.6
122.5°	793.2	793.7	793.4	793.1	792.7	792.4	791.7	790.8	789.9	789.0	788.1
125°	866.6	867.5	867.5	867.5	867.5	867.5	866.7	865.0	863.3	861.6	859.9
127.5°	932.7	933.3	933.4	933.6	933.7	933.9	933.3	932.1	930.9	929.7	928.5
130°	976.4	977.1	976.9	976.7	976.4	976.1	975.4	974.2	973.0	971.8	970.5
132.5°	1016.4	1016.5	1017.1	1017.6	1018.1	1018.7	1018.2	1016.8	1015.4	1014.0	1012.6
135°	1076.3	1076.8	1077.2	1077.8	1078.3	1078.7	1078.3	1076.8	1075.3	1073.8	1072.4
137.5°	1131.2	1131.1	1131.5	1132.0	1132.5	1132.8	1132.5	1131.1	1129.9	1128.7	1127.4
140°	1164.9	1164.4	1164.7	1164.9	1165.2	1165.4	1165.3	1164.8	1164.3	1163.9	1163.3
142.5°	1198.7	1198.6	1198.3	1197.9	1197.6	1197.2	1196.9	1196.7	1196.4	1196.0	1195.7
145°	1245.8	1245.5	1245.5	1245.5	1245.5	1245.5	1245.2	1244.7	1244.3	1243.8	1243.3
147.5°	1286.1	1285.8	1285.5	1285.2	1284.9	1284.6	1284.5	1284.6	1284.7	1284.8	1284.9
150°	1311.6	1311.2	1310.7	1310.2	1309.8	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2
152.5°	1334.5	1334.0	1333.5	1333.0	1332.6	1332.0	1332.3	1333.4	1334.5	1335.6	1336.6
155°	1365.6	1364.9	1364.4	1363.9	1363.4	1362.9	1363.4	1364.9	1366.3	1367.8	1369.2
157.5°	1391.5	1390.7	1390.7	1390.6	1390.6	1390.5	1390.9	1391.9	1392.7	1393.5	1394.5
160°	1407.5	1406.5	1406.3	1406.0	1405.8	1405.5	1406.2	1407.6	1409.1	1410.5	1412.0
162.5°	1421.9	1420.5	1420.3	1420.0	1419.8	1419.6	1420.1	1421.6	1423.1	1424.6	1426.0
165°	1440.9	1439.4	1439.1	1438.9	1438.6	1438.4	1439.0	1440.5	1441.9	1443.4	1444.8
167.5°	1454.9	1453.2	1452.9	1452.6	1452.5	1452.2	1452.8	1454.3	1455.9	1457.4	1458.9
170°	1462.2	1460.2	1459.9	1459.7	1459.4	1459.2	1459.9	1461.6	1463.3	1465.1	1466.8
172.5°	1468.1	1466.3	1465.8	1465.5	1465.0	1464.5	1465.2	1466.9	1468.6	1470.3	1472.0
175°	1474.1	1472.3	1472.0	1471.8	1471.5	1471.2	1471.9	1473.3	1474.8	1476.2	1477.7
177.5°	1477.3	1475.9	1475.7	1475.6	1475.4	1475.2	1475.6	1476.9	1478.0	1479.1	1480.4
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1798.6	1803.9	1811.6	1820.3	1827.4	1835.0	1839.2	1839.2	1842.7	1850.3	1860.3
5°	1803.7	1822.9	1841.3	1864.7	1883.1	1904.4	1920.5	1936.0	1949.9	1967.6	1985.9
7.5°	1802.2	1834.0	1867.1	1904.1	1944.9	1977.5	2010.8	2036.9	2062.8	2096.6	2123.2
10°	1796.4	1837.6	1882.4	1929.4	1980.8	2025.6	2066.1	2102.8	2138.1	2174.8	2207.8
12.5°	1785.8	1838.1	1892.9	1949.4	2014.3	2065.6	2117.8	2156.8	2198.0	2238.3	2279.0
15°	1769.9	1831.6	1897.8	1976.4	2055.8	2113.1	2164.5	2215.2	2253.4	2299.0	2337.9
17.5°	1737.2	1816.7	1899.9	1985.8	2062.1	2128.6	2182.6	2230.8	2271.4	2321.6	2374.5
20°	1717.8	1803.7	1890.5	1982.3	2055.0	2123.4	2175.5	2225.4	2276.1	2341.6	2406.2
22.5°	1690.7	1782.6	1874.5	1961.7	2038.5	2104.5	2158.5	2219.6	2286.1	2360.4	2438.5
25°	1647.9	1742.8	1833.9	1916.8	1991.9	2059.5	2132.9	2215.2	2296.0	2393.8	2506.1
27.5°	1593.7	1685.2	1766.4	1854.2	1928.6	2014.6	2106.3	2195.5	2312.1	2446.5	2586.8
30°	1553.2	1639.9	1717.0	1800.1	1884.5	1979.3	2082.2	2187.3	2326.1	2484.1	2650.9
32.5°	1506.2	1584.7	1661.2	1741.3	1838.7	1942.9	2052.2	2180.8	2346.7	2526.4	2699.1
35°	1424.7	1495.2	1569.3	1658.3	1761.9	1875.0	2014.6	2171.1	2371.7	2564.9	2720.0
37.5°	1339.1	1394.8	1469.3	1563.0	1675.9	1806.9	1965.2	2155.4	2361.4	2534.8	2600.8
40°	1273.3	1325.4	1404.0	1502.5	1614.2	1757.5	1935.2	2130.7	2337.9	2458.3	2453.2
42.5°	1208.1	1260.7	1336.4	1435.5	1551.9	1712.2	1895.3	2098.4	2273.2	2319.1	2223.5
45°	1108.0	1157.2	1231.4	1331.3	1456.2	1624.5	1816.9	2011.7	2123.4	2049.2	1859.5
47.5°	1006.0	1053.8	1122.7	1220.5	1356.9	1533.0	1715.0	1874.7	1890.5	1731.0	1503.6
50°	939.0	983.8	1049.1	1153.5	1285.7	1457.7	1633.3	1759.0	1720.0	1525.3	1290.9
52.5°	873.7	916.8	978.1	1076.5	1211.7	1380.1	1536.9	1635.5	1545.4	1338.4	1127.5
55°	777.3	818.5	880.2	970.5	1093.3	1247.5	1385.0	1421.0	1288.7	1080.1	909.6
57.5°	685.8	716.0	776.9	856.9	975.2	1111.2	1209.7	1203.2	1057.2	869.3	747.1
60°	625.3	652.4	710.5	783.9	896.4	1018.3	1087.4	1058.0	910.3	755.3	637.7
62.5°	568.8	594.3	642.9	710.5	807.0	913.1	963.4	922.8	783.3	647.1	553.6
65°	483.4	501.8	540.7	603.2	678.9	752.3	797.2	737.6	614.3	511.3	440.8
67.5°	403.7	419.5	454.2	499.0	551.2	601.9	620.1	564.3	468.3	399.0	349.3
70°	351.9	366.6	390.1	432.1	466.6	502.6	511.3	461.4	381.4	328.4	297.6
72.5°	302.6	316.0	336.7	366.2	390.1	410.9	415.0	368.5	307.3	270.8	247.0
75°	230.7	242.4	255.7	266.7	282.1	285.8	284.4	248.4	215.3	191.1	177.8
77.5°	169.6	174.5	182.5	186.9	187.7	187.4	179.8	157.1	140.1	130.1	124.6
80°	130.8	134.5	136.7	138.1	138.8	131.5	123.5	109.4	103.6	97.7	91.1
82.5°	94.9	97.5	99.6	99.9	96.0	89.8	82.3	75.4	71.3	68.3	65.8
85°	51.5	52.1	51.5	47.8	42.6	40.4	38.9	37.5	36.8	36.0	36.0
87.5°	18.9	17.4	14.9	15.9	16.2	16.0	16.3	16.1	15.8	16.1	16.3
90°	3.0	5.0	7.0	8.9	10.7	12.4	14.1	15.8	17.5	18.8	20.0
92.5°	15.6	14.1	12.8	11.4	11.5	13.0	14.5	16.0	17.5	18.8	20.0
95°	61.7	61.0	60.2	59.5	54.6	45.2	36.0	26.8	17.5	18.8	20.0
97.5°	131.7	133.0	134.3	135.6	127.1	108.8	90.5	72.2	53.9	47.0	40.2
100°	183.7	184.4	185.1	185.9	186.7	187.7	188.7	189.6	190.6	154.3	118.1
102.5°	237.3	238.3	239.1	240.1	240.8	241.4	242.0	242.6	243.2	236.3	229.4
105°	323.0	324.0	325.0	325.9	326.4	326.4	326.4	326.4	326.4	326.4	326.4
107.5°	411.0	411.0	411.0	411.0	411.2	411.7	412.2	412.7	413.2	413.2	413.3
110°	468.8	468.8	468.8	468.8	469.1	469.6	470.0	470.5	471.0	470.3	469.6



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	523.8	524.3	524.9	525.5	525.9	526.2	526.5	526.8	527.1	526.2	525.3
115°	605.9	607.1	608.3	609.5	610.3	610.5	610.8	611.0	611.2	610.3	609.3
117.5°	689.0	688.9	688.9	688.8	689.3	690.2	691.1	692.0	693.0	691.7	690.4
120°	741.3	741.1	740.8	740.6	740.8	741.6	742.3	743.0	743.8	743.3	742.8
122.5°	789.0	789.9	790.8	791.7	792.4	792.7	793.1	793.4	793.7	793.2	792.8
125°	861.6	863.3	865.0	866.7	867.5	867.5	867.5	867.5	867.5	866.6	865.6
127.5°	929.7	930.9	932.1	933.3	933.9	933.7	933.6	933.4	933.3	932.7	932.2
130°	971.8	973.0	974.2	975.4	976.1	976.4	976.7	976.9	977.1	976.4	975.6
132.5°	1014.0	1015.4	1016.8	1018.2	1018.7	1018.1	1017.6	1017.1	1016.5	1016.4	1016.2
135°	1073.8	1075.3	1076.8	1078.3	1078.7	1078.3	1077.8	1077.2	1076.8	1076.3	1075.8
137.5°	1128.7	1129.9	1131.1	1132.5	1132.8	1132.5	1132.0	1131.5	1131.1	1131.2	1131.3
140°	1163.9	1164.3	1164.8	1165.3	1165.4	1165.2	1164.9	1164.7	1164.4	1164.9	1165.4
142.5°	1196.0	1196.4	1196.7	1196.9	1197.2	1197.6	1197.9	1198.3	1198.6	1198.7	1198.8
145°	1243.8	1244.3	1244.7	1245.2	1245.5	1245.5	1245.5	1245.5	1245.5	1245.8	1245.9
147.5°	1284.8	1284.7	1284.6	1284.5	1284.6	1284.9	1285.2	1285.5	1285.8	1286.1	1286.4
150°	1310.7	1310.2	1309.8	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2	1311.6	1312.2
152.5°	1335.6	1334.5	1333.4	1332.3	1332.0	1332.6	1333.0	1333.5	1334.0	1334.5	1334.9
155°	1367.8	1366.3	1364.9	1363.4	1362.9	1363.4	1363.9	1364.4	1364.9	1365.6	1366.3
157.5°	1393.5	1392.7	1391.9	1390.9	1390.5	1390.6	1390.6	1390.7	1390.7	1391.5	1392.3
160°	1410.5	1409.1	1407.6	1406.2	1405.5	1405.8	1406.0	1406.3	1406.5	1407.5	1408.4
162.5°	1424.6	1423.1	1421.6	1420.1	1419.6	1419.8	1420.0	1420.3	1420.5	1421.9	1423.2
165°	1443.4	1441.9	1440.5	1439.0	1438.4	1438.6	1438.9	1439.1	1439.4	1440.9	1442.3
167.5°	1457.4	1455.9	1454.3	1452.8	1452.2	1452.5	1452.6	1452.9	1453.2	1454.9	1456.7
170°	1465.1	1463.3	1461.6	1459.9	1459.2	1459.4	1459.7	1459.9	1460.2	1462.2	1464.1
172.5°	1470.3	1468.6	1466.9	1465.2	1464.5	1465.0	1465.5	1465.8	1466.3	1468.1	1469.8
175°	1476.2	1474.8	1473.3	1471.9	1471.2	1471.5	1471.8	1472.0	1472.3	1474.1	1476.1
177.5°	1479.1	1478.0	1476.9	1475.6	1475.2	1475.4	1475.6	1475.7	1475.9	1477.3	1478.7
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1867.9	1867.9	1877.9	1877.4	1883.9	1881.5	1882.6
5°	2008.0	2020.5	2031.6	2038.8	2049.8	2052.9	2051.3
7.5°	2153.1	2180.9	2194.4	2213.0	2216.4	2226.1	2225.1
10°	2243.2	2270.3	2290.8	2307.1	2315.1	2325.4	2326.1
12.5°	2313.7	2336.8	2354.9	2369.9	2379.7	2383.0	2384.9
15°	2368.7	2394.4	2415.7	2437.0	2449.6	2459.1	2464.3
17.5°	2424.3	2464.0	2501.6	2530.5	2547.9	2562.6	2562.4
20°	2467.2	2512.7	2559.8	2592.8	2626.7	2641.3	2643.5
22.5°	2513.0	2582.7	2643.3	2694.5	2738.9	2754.2	2760.0
25°	2608.3	2699.3	2792.7	2864.7	2916.1	2946.2	2950.6
27.5°	2723.3	2846.6	2944.8	3011.2	3053.9	3076.3	3081.2
30°	2804.4	2918.3	3006.5	3056.5	3076.3	3079.2	3068.2
32.5°	2840.9	2925.9	2961.2	2958.3	2919.3	2893.5	2883.6
35°	2796.3	2778.7	2692.7	2589.9	2511.3	2461.4	2448.1
37.5°	2544.8	2392.7	2234.6	2079.2	1996.4	1954.4	1882.1
40°	2296.8	2080.0	1915.4	1784.6	1691.3	1616.4	1598.7
42.5°	2016.9	1793.2	1628.6	1516.6	1442.1	1390.7	1368.4
45°	1620.8	1428.3	1292.4	1206.5	1149.1	1111.6	1094.8
47.5°	1296.4	1147.4	1048.3	984.7	941.0	908.4	899.3
50°	1118.2	999.2	915.5	861.9	828.8	803.8	793.5
52.5°	971.3	875.2	810.9	766.6	735.3	719.7	711.2
55°	801.5	718.6	672.3	637.0	619.3	606.9	601.0
57.5°	655.5	595.6	561.8	537.3	521.0	513.1	510.2
60°	573.8	526.8	496.0	476.8	465.8	455.5	452.6
62.5°	501.5	464.5	440.7	424.0	412.9	408.5	406.7
65°	404.1	379.8	362.2	351.9	343.1	341.7	340.9
67.5°	321.2	307.0	297.7	287.0	283.9	278.7	277.8
70°	274.8	265.2	254.2	250.5	246.9	241.8	242.4
72.5°	233.1	223.5	216.0	211.1	209.8	207.6	209.5
75°	170.4	167.5	164.6	160.9	159.5	159.5	158.7
77.5°	121.7	119.1	115.9	113.8	113.3	110.2	111.4
80°	88.1	84.5	83.0	83.8	81.5	80.8	80.8
82.5°	65.2	63.9	62.5	62.6	62.1	61.5	62.0
85°	36.0	35.3	35.3	34.5	34.5	33.8	33.8
87.5°	17.2	18.0	17.1	16.6	16.7	17.4	18.2
90°	21.2	22.4	23.4	24.1	24.8	25.5	26.3
92.5°	21.2	22.4	23.2	23.5	23.8	24.2	24.5
95°	21.2	22.4	23.0	23.0	23.0	23.0	23.0
97.5°	33.3	26.4	23.0	23.0	23.0	23.0	23.0
100°	81.8	45.5	26.9	25.9	25.0	23.9	23.0
102.5°	222.6	215.7	204.1	187.5	170.9	154.4	137.8
105°	326.4	326.4	326.3	326.0	325.8	325.6	325.4
107.5°	413.3	413.4	413.0	412.3	411.6	410.9	410.1
110°	468.8	468.1	467.9	468.1	468.3	468.6	468.8



TEST NUMBER: P333634-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	524.3	523.4	522.7	522.5	522.1	521.8	521.4
115°	608.3	607.4	606.1	604.6	603.2	601.7	600.3
117.5°	689.2	687.9	686.9	686.3	685.7	685.0	684.4
120°	742.3	741.9	741.0	739.8	738.6	737.4	736.1
122.5°	792.3	791.8	790.8	789.4	788.0	786.6	785.2
125°	864.6	863.7	862.8	862.0	861.4	860.6	859.9
127.5°	931.7	931.1	930.0	928.2	926.3	924.5	922.7
130°	974.9	974.2	973.2	971.9	970.8	969.6	968.4
132.5°	1016.1	1016.0	1015.3	1014.1	1012.9	1011.6	1010.4
135°	1075.3	1074.9	1073.8	1072.4	1070.9	1069.5	1068.0
137.5°	1131.4	1131.5	1131.0	1129.6	1128.4	1127.1	1125.9
140°	1165.8	1166.4	1165.8	1164.4	1163.0	1161.5	1160.1
142.5°	1198.9	1199.0	1198.3	1196.8	1195.4	1193.9	1192.5
145°	1246.2	1246.4	1245.9	1244.3	1242.9	1241.4	1240.0
147.5°	1286.7	1286.9	1286.2	1284.5	1282.7	1281.0	1279.2
150°	1312.7	1313.2	1312.4	1310.5	1308.5	1306.6	1304.7
152.5°	1335.5	1336.0	1335.3	1333.5	1331.8	1330.0	1328.3
155°	1367.1	1367.8	1367.2	1365.3	1363.3	1361.3	1359.4
157.5°	1393.1	1393.8	1393.3	1391.3	1389.4	1387.4	1385.4
160°	1409.4	1410.4	1409.9	1408.0	1406.0	1404.1	1402.1
162.5°	1424.7	1426.0	1425.6	1423.4	1421.3	1419.2	1417.0
165°	1443.8	1445.2	1444.9	1443.0	1441.1	1439.1	1437.2
167.5°	1458.4	1460.2	1460.0	1457.7	1455.6	1453.4	1451.2
170°	1466.0	1468.0	1467.8	1465.7	1463.5	1461.3	1459.1
172.5°	1471.6	1473.3	1473.1	1470.9	1468.8	1466.5	1464.3
175°	1478.1	1480.0	1479.9	1477.7	1475.6	1473.3	1471.1
177.5°	1480.1	1481.4	1481.3	1479.8	1478.2	1476.6	1475.1
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7

(END OF REPORT)