

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333257-840

Luminaire Tested: **S125DIP-S1090D365U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333257-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D365U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5764.9 lumens  
Efficiency: N/A  
Efficacy: 132.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333257-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333257-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	62	63	60	58	55
3	86	76	69	62	82	73	66	60	67	61	57	61	57	53	56	52	49	46
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	42	40
5	73	60	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37	34
6	67	54	46	40	64	52	44	39	48	42	37	45	39	35	41	36	33	30
7	62	49	41	35	59	47	40	34	44	37	32	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	30	40	34	29	37	32	27	35	30	26	24
9	54	41	33	28	51	40	32	27	37	31	26	34	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	21	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11129	11129	11129
5°	11154	11048	11119
10°	11086	10970	11032
15°	10965	10838	10884
20°	10794	10653	10672
25°	10608	10434	10424
30°	10380	10197	10147
35°	10136	9942	9802
40°	9885	9666	9528
45°	9613	9414	9227
50°	9315	9109	8835
55°	9026	8765	8519
60°	8681	8418	8117
65°	8270	8000	7728
70°	7878	7517	7260
75°	7177	6939	6700
80°	6390	6289	6133
85°	5550	5654	5350



TEST NUMBER: P333257-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.5	2.8
10°-20°	459.0	8.0
20°-30°	677.7	11.8
30°-40°	790.7	13.7
40°-50°	794.2	13.8
50°-60°	697.1	12.1
60°-70°	519.5	9.0
70°-80°	297.0	5.2
80°-90°	87.4	1.5
90°-100°	30.7	0.5
100°-110°	90.7	1.6
110°-120°	153.6	2.7
120°-130°	202.2	3.5
130°-140°	226.6	3.9
140°-150°	222.1	3.9
150°-160°	186.5	3.2
160°-170°	124.0	2.2
170°-180°	43.4	0.8
0°-30°	1299.1	22.5
0°-40°	2089.8	36.3
0°-60°	3581.2	62.1
0°-90°	4485.0	77.8
90°-120°	275.1	4.8
90°-150°	925.9	16.1
90°-180°	1280.0	22.2
0°-180°	5764.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1720	1717	1704	1716	1715	163
15°	1640	1635	1621	1627	1628	462
25°	1489	1481	1464	1466	1463	685
35°	1286	1279	1261	1254	1243	804
45°	1052	1046	1031	1015	1010	811
55°	802	797	778	766	757	715
65°	541	538	524	512	506	537
75°	288	285	278	274	268	307
85°	75	76	76	75	72	84
90°	0	3	6	7	9	5
95°	23	24	28	30	31	25
105°	81	83	85	87	89	87
115°	154	155	156	156	155	152
125°	224	227	227	226	226	201
135°	292	294	294	294	293	225
145°	354	355	356	356	355	221
155°	405	405	405	406	405	186
165°	440	439	440	441	439	124
175°	458	456	456	458	456	43
180°	459	459	459	459	459	



TEST NUMBER: P333257-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1727.6	1726.9	1726.1	1725.4	1724.6	1723.0	1720.6	1718.2	1715.8	1713.3	1715.8
5°	1720.5	1719.9	1719.3	1718.7	1718.1	1716.3	1713.2	1710.2	1707.2	1704.1	1706.9
7.5°	1704.7	1704.0	1703.4	1702.8	1702.2	1700.2	1696.9	1693.5	1690.2	1686.9	1689.6
10°	1690.5	1689.9	1689.3	1688.7	1688.1	1686.1	1682.7	1679.4	1676.1	1672.7	1675.2
12.5°	1673.0	1671.9	1670.8	1669.7	1668.7	1666.6	1663.4	1660.4	1657.3	1654.2	1656.2
15°	1640.0	1639.1	1638.2	1637.3	1636.4	1634.3	1630.9	1627.6	1624.3	1620.9	1622.4
17.5°	1602.2	1600.8	1599.4	1598.1	1596.8	1594.4	1590.9	1587.5	1584.1	1580.5	1582.5
20°	1570.5	1569.9	1569.3	1568.7	1568.1	1565.8	1561.9	1557.9	1554.0	1550.0	1552.2
22.5°	1538.8	1537.8	1536.7	1535.6	1534.5	1532.1	1528.4	1524.7	1521.1	1517.3	1518.7
25°	1488.7	1487.2	1485.7	1484.2	1482.7	1480.0	1476.0	1472.1	1468.1	1464.2	1464.8
27.5°	1430.1	1429.2	1428.3	1427.3	1426.4	1424.0	1419.9	1415.8	1411.8	1407.8	1407.9
30°	1391.9	1391.0	1390.1	1389.2	1388.3	1385.5	1381.0	1376.4	1371.9	1367.4	1366.8
32.5°	1350.5	1349.1	1347.7	1346.3	1344.9	1342.2	1338.1	1334.0	1330.0	1326.0	1324.8
35°	1285.6	1284.3	1283.1	1281.9	1280.7	1278.0	1273.7	1269.5	1265.3	1261.0	1259.5
37.5°	1218.2	1216.7	1215.2	1213.7	1212.1	1209.4	1205.4	1201.4	1197.4	1193.5	1191.1
40°	1172.5	1170.9	1169.4	1167.9	1166.4	1163.5	1159.2	1155.0	1150.7	1146.5	1143.8
42.5°	1123.4	1122.1	1120.8	1119.5	1118.2	1115.5	1111.3	1107.0	1102.8	1098.5	1096.0
45°	1052.5	1051.3	1050.1	1048.8	1047.6	1045.2	1041.6	1037.9	1034.3	1030.7	1027.0
47.5°	976.1	976.1	976.2	976.3	976.3	974.2	969.9	965.4	961.1	956.7	953.0
50°	927.1	926.1	925.2	924.3	923.4	921.1	917.5	913.8	910.2	906.6	902.6
52.5°	876.9	876.2	875.6	874.8	874.2	871.9	868.1	864.1	860.3	856.4	852.9
55°	801.6	800.7	799.8	798.9	798.0	795.4	791.1	786.9	782.6	778.4	775.7
57.5°	722.3	721.8	721.3	720.8	720.3	718.3	714.7	711.1	707.6	704.0	700.4
60°	672.1	670.9	669.6	668.4	667.2	665.0	661.7	658.3	655.0	651.7	648.6
62.5°	619.8	618.7	617.8	616.8	615.9	614.0	611.1	608.2	605.4	602.6	599.3
65°	541.2	540.6	540.0	539.4	538.8	536.8	533.5	530.2	526.8	523.5	520.8
67.5°	465.1	463.8	462.6	461.3	460.1	458.2	455.7	453.2	450.7	448.3	446.0
70°	417.2	415.7	414.1	412.6	411.1	409.0	406.3	403.5	400.8	398.1	396.3
72.5°	364.9	363.8	362.7	361.7	360.7	359.3	357.6	355.8	354.1	352.2	350.2
75°	287.6	287.0	286.4	285.8	285.2	284.2	282.7	281.1	279.6	278.1	277.2
77.5°	216.5	216.2	216.0	215.8	215.5	215.0	214.1	213.3	212.5	211.6	211.1
80°	171.8	171.8	171.8	171.8	171.8	171.5	170.9	170.3	169.7	169.1	168.7
82.5°	132.5	132.0	131.6	131.1	130.6	130.3	130.2	130.1	129.9	129.8	129.3
85°	74.9	75.2	75.5	75.8	76.1	76.3	76.3	76.3	76.3	76.3	76.0
87.5°	29.5	29.7	29.8	29.9	30.0	30.0	29.9	29.8	29.6	29.5	29.6
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.2	5.8	6.1
92.5°	8.7	9.1	9.5	10.0	10.4	11.0	11.6	12.3	13.0	13.7	14.2
95°	23.2	23.3	23.5	23.6	23.8	24.3	25.1	25.9	26.7	27.5	28.1
97.5°	38.6	38.6	38.7	38.8	38.8	39.4	40.5	41.6	42.6	43.7	44.3
100°	50.0	50.0	50.0	50.0	50.0	50.5	51.5	52.5	53.6	54.6	55.3
102.5°	62.2	62.6	62.9	63.2	63.5	63.9	64.4	64.9	65.5	66.0	66.9
105°	81.4	81.8	82.2	82.6	83.0	83.4	83.9	84.3	84.8	85.3	85.7
107.5°	102.5	102.9	103.3	103.7	104.1	104.5	104.8	105.2	105.5	105.9	106.1
110°	117.0	117.4	117.9	118.3	118.7	119.0	119.2	119.5	119.7	120.0	120.2



TEST NUMBER: P333257-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	131.9	132.1	132.3	132.5	132.7	133.0	133.3	133.6	133.9	134.2	134.3
115°	153.8	154.1	154.5	154.8	155.1	155.3	155.5	155.6	155.8	156.0	155.9
117.5°	175.8	175.9	176.1	176.2	176.4	176.5	176.7	176.8	176.9	177.1	177.1
120°	189.6	190.0	190.4	190.8	191.1	191.4	191.5	191.5	191.6	191.7	191.7
122.5°	204.4	204.5	204.7	204.8	204.9	205.1	205.3	205.5	205.7	205.9	205.9
125°	224.5	225.0	225.5	225.9	226.4	226.7	226.8	226.8	226.9	227.0	226.8
127.5°	245.9	246.2	246.5	246.7	247.0	247.2	247.3	247.4	247.5	247.5	247.5
130°	258.7	259.1	259.5	259.9	260.3	260.6	260.7	260.9	261.2	261.3	261.2
132.5°	271.7	272.3	273.0	273.6	274.2	274.6	274.5	274.5	274.5	274.4	274.3
135°	292.0	292.5	293.0	293.4	293.9	294.2	294.3	294.3	294.4	294.5	294.5
137.5°	311.1	311.5	312.0	312.5	313.0	313.3	313.5	313.6	313.8	314.0	314.1
140°	323.4	323.8	324.2	324.6	325.0	325.3	325.5	325.8	326.0	326.2	326.4
142.5°	335.7	336.0	336.3	336.7	337.0	337.3	337.6	337.9	338.2	338.5	338.6
145°	353.8	354.1	354.4	354.7	355.0	355.3	355.5	355.8	356.0	356.2	356.2
147.5°	370.4	370.6	370.7	370.9	371.1	371.3	371.5	371.7	371.8	372.0	372.2
150°	381.5	381.5	381.4	381.3	381.2	381.3	381.6	382.0	382.3	382.6	382.6
152.5°	390.7	390.8	390.9	391.0	391.1	391.2	391.4	391.5	391.6	391.7	391.9
155°	404.8	404.8	404.8	404.8	404.8	404.8	404.9	405.0	405.1	405.2	405.5
157.5°	417.3	417.2	417.0	416.8	416.7	416.6	416.7	416.8	416.8	416.9	417.2
160°	424.7	424.5	424.2	424.0	423.8	423.7	423.8	423.8	423.9	424.0	424.3
162.5°	431.3	431.1	431.0	430.8	430.6	430.5	430.5	430.6	430.6	430.6	431.0
165°	440.1	439.9	439.8	439.6	439.5	439.4	439.5	439.6	439.7	439.7	440.1
167.5°	447.5	447.2	446.9	446.6	446.3	446.1	446.1	446.1	446.1	446.1	446.6
170°	451.5	451.2	450.9	450.6	450.2	450.1	450.1	450.1	450.1	450.1	450.6
172.5°	454.3	454.0	453.7	453.4	453.1	452.9	452.9	452.9	452.9	452.9	453.4
175°	457.6	457.3	457.0	456.7	456.4	456.2	456.2	456.2	456.2	456.2	456.7
177.5°	459.2	459.0	458.7	458.5	458.2	458.1	458.0	458.0	457.9	457.8	458.2
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333257-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1718.2	1720.6	1723.0	1724.1	1723.9	1723.6	1723.4	1723.2
5°	1709.6	1712.3	1715.1	1716.3	1716.0	1715.7	1715.4	1715.1
7.5°	1692.2	1695.0	1697.6	1698.8	1698.5	1698.2	1697.9	1697.6
10°	1677.6	1680.0	1682.4	1683.5	1683.2	1682.9	1682.6	1682.3
12.5°	1658.1	1660.0	1661.9	1662.9	1662.8	1662.7	1662.7	1662.6
15°	1624.0	1625.5	1627.0	1627.8	1627.8	1627.8	1627.8	1627.8
17.5°	1584.4	1586.2	1588.1	1588.3	1586.8	1585.3	1583.8	1582.3
20°	1554.3	1556.4	1558.5	1558.8	1557.3	1555.8	1554.3	1552.8
22.5°	1520.1	1521.6	1522.9	1523.1	1522.1	1521.1	1520.0	1518.9
25°	1465.4	1466.0	1466.6	1466.4	1465.5	1464.6	1463.7	1462.8
27.5°	1408.0	1408.1	1408.3	1407.9	1406.9	1406.0	1405.1	1404.2
30°	1366.1	1365.5	1364.9	1364.2	1363.3	1362.4	1361.5	1360.6
32.5°	1323.7	1322.6	1321.6	1320.2	1318.6	1317.0	1315.2	1313.6
35°	1258.0	1256.5	1255.0	1253.0	1250.6	1248.2	1245.8	1243.3
37.5°	1188.9	1186.7	1184.5	1182.7	1181.2	1179.8	1178.4	1177.1
40°	1141.0	1138.3	1135.6	1133.8	1132.9	1132.0	1131.0	1130.1
42.5°	1093.6	1091.1	1088.6	1086.6	1085.3	1083.9	1082.5	1081.1
45°	1023.4	1019.8	1016.1	1013.8	1012.9	1012.0	1011.1	1010.2
47.5°	949.4	945.6	942.0	939.1	937.0	934.8	932.7	930.6
50°	898.7	894.7	890.8	887.8	885.7	883.5	881.4	879.3
52.5°	849.5	846.1	842.6	839.7	837.3	835.0	832.6	830.2
55°	773.0	770.2	767.5	765.1	763.0	760.8	758.7	756.6
57.5°	697.0	693.5	689.9	687.6	686.5	685.3	684.2	683.0
60°	645.6	642.6	639.5	636.9	634.8	632.7	630.6	628.4
62.5°	596.0	592.8	589.5	587.0	585.4	583.8	582.1	580.5
65°	518.1	515.3	512.6	510.6	509.4	508.2	507.0	505.7
67.5°	443.6	441.3	439.0	437.5	436.8	436.1	435.4	434.6
70°	394.5	392.6	390.8	389.3	388.1	386.9	385.7	384.5
72.5°	348.2	346.1	344.1	342.4	341.2	340.0	338.8	337.6
75°	276.3	275.4	274.5	273.4	272.2	270.9	269.7	268.5
77.5°	210.5	210.0	209.4	208.7	207.8	207.0	206.1	205.3
80°	168.4	168.1	167.8	167.3	166.7	166.1	165.5	164.9
82.5°	128.7	128.2	127.6	127.2	127.1	127.0	126.9	126.7
85°	75.7	75.4	75.1	74.6	74.0	73.4	72.8	72.2
87.5°	29.7	29.7	29.8	29.6	29.2	28.8	28.3	27.9
90°	6.5	6.9	7.3	7.6	7.9	8.1	8.3	8.6
92.5°	14.7	15.2	15.8	16.2	16.4	16.5	16.7	16.9
95°	28.6	29.2	29.7	30.1	30.2	30.4	30.5	30.7
97.5°	44.8	45.3	45.8	46.2	46.3	46.4	46.5	46.6
100°	56.0	56.8	57.5	57.9	58.1	58.3	58.4	58.6
102.5°	67.6	68.4	69.2	69.7	69.9	70.1	70.3	70.5
105°	86.2	86.7	87.3	87.6	87.8	88.1	88.3	88.6
107.5°	106.4	106.6	106.8	107.0	106.9	106.9	106.9	106.9
110°	120.4	120.7	120.9	121.0	120.9	120.8	120.7	120.7





TEST NUMBER: P333257-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	134.4	134.5	134.6	134.6	134.5	134.3	134.2	134.1
115°	155.8	155.7	155.6	155.6	155.5	155.4	155.3	155.2
117.5°	177.2	177.3	177.3	177.2	176.9	176.6	176.3	175.9
120°	191.7	191.7	191.7	191.5	191.2	190.9	190.6	190.3
122.5°	205.8	205.7	205.7	205.5	205.3	205.0	204.8	204.5
125°	226.7	226.5	226.4	226.2	226.2	226.1	226.0	225.9
127.5°	247.4	247.3	247.2	247.1	247.0	246.8	246.6	246.5
130°	261.2	261.1	260.9	260.8	260.6	260.5	260.3	260.2
132.5°	274.3	274.2	274.1	274.0	273.7	273.5	273.3	273.1
135°	294.5	294.5	294.5	294.3	294.0	293.7	293.4	293.1
137.5°	314.2	314.3	314.4	314.2	313.8	313.4	313.0	312.6
140°	326.6	326.7	326.9	326.8	326.4	326.0	325.6	325.2
142.5°	338.7	338.8	338.9	338.7	338.3	337.9	337.6	337.2
145°	356.2	356.2	356.2	356.1	355.9	355.6	355.4	355.2
147.5°	372.4	372.6	372.8	372.6	372.1	371.5	371.0	370.5
150°	382.6	382.6	382.6	382.5	382.4	382.2	382.0	381.9
152.5°	392.1	392.3	392.5	392.4	392.2	391.9	391.6	391.3
155°	405.8	406.1	406.4	406.4	406.0	405.6	405.2	404.8
157.5°	417.5	417.9	418.2	418.1	417.6	417.0	416.5	416.0
160°	424.6	425.0	425.3	425.3	424.9	424.4	424.0	423.6
162.5°	431.3	431.7	432.1	432.1	431.6	431.1	430.7	430.2
165°	440.4	440.7	441.0	440.9	440.4	440.0	439.5	439.0
167.5°	447.1	447.5	448.0	448.0	447.5	447.0	446.5	446.1
170°	451.0	451.5	452.0	451.9	451.4	450.8	450.3	449.7
172.5°	453.9	454.3	454.8	454.8	454.3	453.8	453.3	452.8
175°	457.1	457.6	458.1	458.0	457.5	456.9	456.4	455.8
177.5°	458.6	459.0	459.3	459.3	458.9	458.4	458.0	457.5
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

(END OF REPORT)