

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333637-830

Luminaire Tested: **S125RDIP-S1270D1205U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333637-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D1205U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9137.4 lumens  
Efficiency: N/A  
Efficacy: 127.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333637-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333637-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50																				
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43																				
2	89	82	76	71	82	76	71	66	65	61	58	54	51	49	44	43	41	36																				
3	82	72	65	59	75	67	61	56	57	52	49	48	45	42	40	37	35	31																				
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	35	33	30	27																				
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23																				
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	21																				
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18																				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16																				
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15																				
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15	13																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333637-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.0	2.0
10°-20°	511.3	5.6
20°-30°	741.4	8.1
30°-40°	845.0	9.2
40°-50°	823.6	9.0
50°-60°	693.3	7.6
60°-70°	486.0	5.3
70°-80°	249.8	2.7
80°-90°	66.2	0.7
90°-100°	53.7	0.6
100°-110°	330.9	3.6
110°-120°	600.2	6.6
120°-130°	770.3	8.4
130°-140°	828.6	9.1
140°-150°	777.7	8.5
150°-160°	629.1	6.9
160°-170°	406.9	4.5
170°-180°	140.3	1.5
0°-30°	1435.7	15.7
0°-40°	2280.6	25.0
0°-60°	3797.6	41.6
0°-90°	4599.6	50.3
90°-120°	984.9	10.8
90°-150°	3361.5	36.8
90°-180°	4538.0	49.7
0°-180°	9137.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	1	10	18	23	26	6
95°	62	57	18	23	23	80
105°	322	326	326	326	325	341
115°	605	610	611	607	600	599
125°	860	867	868	863	860	768
135°	1072	1078	1077	1074	1068	826
145°	1243	1245	1246	1246	1240	777
155°	1369	1363	1365	1368	1359	631
165°	1445	1439	1439	1445	1437	408
175°	1478	1472	1472	1480	1471	141
180°	1478	1478	1478	1478	1478	



TEST NUMBER: P333637-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.2	25.8	24.4	22.9	21.5	20.8	20.9	21.0	21.0	21.1	21.4
90°	1.1	3.0	5.0	7.0	8.9	10.7	12.4	14.1	15.8	17.5	18.8
92.5°	16.9	15.6	14.1	12.8	11.4	11.5	13.0	14.5	16.0	17.5	18.8
95°	62.4	61.7	61.0	60.2	59.5	54.6	45.2	36.0	26.8	17.5	18.8
97.5°	130.4	131.7	133.0	134.3	135.6	127.1	108.8	90.5	72.2	53.9	47.0
100°	182.9	183.7	184.4	185.1	185.9	186.7	187.7	188.7	189.6	190.6	154.3
102.5°	236.4	237.3	238.3	239.1	240.1	240.8	241.4	242.0	242.6	243.2	236.3
105°	322.1	323.0	324.0	325.0	325.9	326.4	326.4	326.4	326.4	326.4	326.4
107.5°	411.0	411.0	411.0	411.0	411.0	411.2	411.7	412.2	412.7	413.2	413.2
110°	468.8	468.8	468.8	468.8	468.8	469.1	469.6	470.0	470.5	471.0	470.3



TEST NUMBER: P333637-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	523.2	523.8	524.3	524.9	525.5	525.9	526.2	526.5	526.8	527.1	526.2
115°	604.6	605.9	607.1	608.3	609.5	610.3	610.5	610.8	611.0	611.2	610.3
117.5°	689.0	689.0	688.9	688.9	688.8	689.3	690.2	691.1	692.0	693.0	691.7
120°	741.6	741.3	741.1	740.8	740.6	740.8	741.6	742.3	743.0	743.8	743.3
122.5°	788.1	789.0	789.9	790.8	791.7	792.4	792.7	793.1	793.4	793.7	793.2
125°	859.9	861.6	863.3	865.0	866.7	867.5	867.5	867.5	867.5	867.5	866.6
127.5°	928.5	929.7	930.9	932.1	933.3	933.9	933.7	933.6	933.4	933.3	932.7
130°	970.5	971.8	973.0	974.2	975.4	976.1	976.4	976.7	976.9	977.1	976.4
132.5°	1012.6	1014.0	1015.4	1016.8	1018.2	1018.7	1018.1	1017.6	1017.1	1016.5	1016.4
135°	1072.4	1073.8	1075.3	1076.8	1078.3	1078.7	1078.3	1077.8	1077.2	1076.8	1076.3
137.5°	1127.4	1128.7	1129.9	1131.1	1132.5	1132.8	1132.5	1132.0	1131.5	1131.1	1131.2
140°	1163.3	1163.9	1164.3	1164.8	1165.3	1165.4	1165.2	1164.9	1164.7	1164.4	1164.9
142.5°	1195.7	1196.0	1196.4	1196.7	1196.9	1197.2	1197.6	1197.9	1198.3	1198.6	1198.7
145°	1243.3	1243.8	1244.3	1244.7	1245.2	1245.5	1245.5	1245.5	1245.5	1245.5	1245.8
147.5°	1284.9	1284.8	1284.7	1284.6	1284.5	1284.6	1284.9	1285.2	1285.5	1285.8	1286.1
150°	1311.2	1310.7	1310.2	1309.8	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2	1311.6
152.5°	1336.6	1335.6	1334.5	1333.4	1332.3	1332.0	1332.6	1333.0	1333.5	1334.0	1334.5
155°	1369.2	1367.8	1366.3	1364.9	1363.4	1362.9	1363.4	1363.9	1364.4	1364.9	1365.6
157.5°	1394.5	1393.5	1392.7	1391.9	1390.9	1390.5	1390.6	1390.6	1390.7	1390.7	1391.5
160°	1412.0	1410.5	1409.1	1407.6	1406.2	1405.5	1405.8	1406.0	1406.3	1406.5	1407.5
162.5°	1426.0	1424.6	1423.1	1421.6	1420.1	1419.6	1419.8	1420.0	1420.3	1420.5	1421.9
165°	1444.8	1443.4	1441.9	1440.5	1439.0	1438.4	1438.6	1438.9	1439.1	1439.4	1440.9
167.5°	1458.9	1457.4	1455.9	1454.3	1452.8	1452.2	1452.5	1452.6	1452.9	1453.2	1454.9
170°	1466.8	1465.1	1463.3	1461.6	1459.9	1459.2	1459.4	1459.7	1459.9	1460.2	1462.2
172.5°	1472.0	1470.3	1468.6	1466.9	1465.2	1464.5	1465.0	1465.5	1465.8	1466.3	1468.1
175°	1477.7	1476.2	1474.8	1473.3	1471.9	1471.2	1471.5	1471.8	1472.0	1472.3	1474.1
177.5°	1480.4	1479.1	1478.0	1476.9	1475.6	1475.2	1475.4	1475.6	1475.7	1475.9	1477.3
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333637-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	21.6	21.9	22.1	22.1	22.1	22.0	21.9	21.7
90°	20.0	21.2	22.4	23.4	24.1	24.8	25.5	26.3
92.5°	20.0	21.2	22.4	23.2	23.5	23.8	24.2	24.5
95°	20.0	21.2	22.4	23.0	23.0	23.0	23.0	23.0
97.5°	40.2	33.3	26.4	23.0	23.0	23.0	23.0	23.0
100°	118.1	81.8	45.5	26.9	25.9	25.0	23.9	23.0
102.5°	229.4	222.6	215.7	204.1	187.5	170.9	154.4	137.8
105°	326.4	326.4	326.4	326.3	326.0	325.8	325.6	325.4
107.5°	413.3	413.3	413.4	413.0	412.3	411.6	410.9	410.1
110°	469.6	468.8	468.1	467.9	468.1	468.3	468.6	468.8





TEST NUMBER: P333637-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	525.3	524.3	523.4	522.7	522.5	522.1	521.8	521.4
115°	609.3	608.3	607.4	606.1	604.6	603.2	601.7	600.3
117.5°	690.4	689.2	687.9	686.9	686.3	685.7	685.0	684.4
120°	742.8	742.3	741.9	741.0	739.8	738.6	737.4	736.1
122.5°	792.8	792.3	791.8	790.8	789.4	788.0	786.6	785.2
125°	865.6	864.6	863.7	862.8	862.0	861.4	860.6	859.9
127.5°	932.2	931.7	931.1	930.0	928.2	926.3	924.5	922.7
130°	975.6	974.9	974.2	973.2	971.9	970.8	969.6	968.4
132.5°	1016.2	1016.1	1016.0	1015.3	1014.1	1012.9	1011.6	1010.4
135°	1075.8	1075.3	1074.9	1073.8	1072.4	1070.9	1069.5	1068.0
137.5°	1131.3	1131.4	1131.5	1131.0	1129.6	1128.4	1127.1	1125.9
140°	1165.4	1165.8	1166.4	1165.8	1164.4	1163.0	1161.5	1160.1
142.5°	1198.8	1198.9	1199.0	1198.3	1196.8	1195.4	1193.9	1192.5
145°	1245.9	1246.2	1246.4	1245.9	1244.3	1242.9	1241.4	1240.0
147.5°	1286.4	1286.7	1286.9	1286.2	1284.5	1282.7	1281.0	1279.2
150°	1312.2	1312.7	1313.2	1312.4	1310.5	1308.5	1306.6	1304.7
152.5°	1334.9	1335.5	1336.0	1335.3	1333.5	1331.8	1330.0	1328.3
155°	1366.3	1367.1	1367.8	1367.2	1365.3	1363.3	1361.3	1359.4
157.5°	1392.3	1393.1	1393.8	1393.3	1391.3	1389.4	1387.4	1385.4
160°	1408.4	1409.4	1410.4	1409.9	1408.0	1406.0	1404.1	1402.1
162.5°	1423.2	1424.7	1426.0	1425.6	1423.4	1421.3	1419.2	1417.0
165°	1442.3	1443.8	1445.2	1444.9	1443.0	1441.1	1439.1	1437.2
167.5°	1456.7	1458.4	1460.2	1460.0	1457.7	1455.6	1453.4	1451.2
170°	1464.1	1466.0	1468.0	1467.8	1465.7	1463.5	1461.3	1459.1
172.5°	1469.8	1471.6	1473.3	1473.1	1470.9	1468.8	1466.5	1464.3
175°	1476.1	1478.1	1480.0	1479.9	1477.7	1475.6	1473.3	1471.1
177.5°	1478.7	1480.1	1481.4	1481.3	1479.8	1478.2	1476.6	1475.1
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7

(END OF REPORT)