

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333639-830

Luminaire Tested: **S125RDIP-S1270D1205U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333639-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1205U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8673.2 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333639-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333639-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38
3	82	73	66	60	76	68	61	56	58	53	50	49	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28	25
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333639-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	2.1
10°-20°	511.3	5.9
20°-30°	741.4	8.5
30°-40°	845.0	9.7
40°-50°	823.6	9.5
50°-60°	693.3	8.0
60°-70°	486.0	5.6
70°-80°	249.8	2.9
80°-90°	66.1	0.8
90°-100°	393.7	4.5
100°-110°	846.4	9.8
110°-120°	794.4	9.2
120°-130°	643.8	7.4
130°-140°	516.6	6.0
140°-150°	389.9	4.5
150°-160°	274.4	3.2
160°-170°	161.8	1.9
170°-180°	52.6	0.6
0°-30°	1435.7	16.6
0°-40°	2280.6	26.3
0°-60°	3797.6	43.8
0°-90°	4599.5	53.0
90°-120°	2034.5	23.5
90°-150°	3584.8	41.3
90°-180°	4074.0	47.0
0°-180°	8673.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	1	10	18	23	25	6
95°	36	107	970	440	257	38
105°	124	173	794	1563	1451	130
115°	221	267	637	1374	1616	218
125°	307	359	611	1093	1274	272
135°	359	432	607	916	1058	279
145°	418	479	609	758	834	262
155°	478	514	594	671	700	220
165°	521	536	570	604	613	147
175°	542	542	546	553	551	51
180°	543	543	543	543	543	



TEST NUMBER: P333639-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.2	25.6	24.2	22.9	21.5	20.8	20.8	21.0	20.9	21.1	21.4
90°	1.1	2.2	4.3	6.6	8.8	10.9	12.1	14.2	15.4	17.5	18.7
92.5°	13.4	16.2	25.4	39.0	57.9	89.8	149.6	250.0	358.8	353.1	285.9
95°	36.1	37.2	46.0	58.1	82.1	131.4	248.6	489.6	791.8	970.3	949.5
97.5°	60.0	61.4	67.5	79.6	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5
100°	76.6	78.9	83.2	95.3	116.1	148.9	212.4	354.9	630.8	988.9	1262.7
102.5°	95.1	96.4	99.9	112.8	131.9	163.8	220.4	340.0	573.0	905.7	1226.0
105°	123.8	123.8	129.2	140.2	157.7	188.4	236.6	334.0	516.9	794.0	1108.3
107.5°	151.7	154.0	159.2	168.2	186.4	214.0	260.6	344.1	493.2	717.1	988.4
110°	171.9	174.2	178.5	188.4	204.8	233.3	278.1	353.7	486.3	681.2	919.9



TEST NUMBER: P333639-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	192.1	194.3	197.7	207.6	224.0	251.7	294.8	366.0	486.3	660.2	869.1
115°	221.2	223.4	226.7	236.6	253.0	280.4	320.9	384.4	489.6	637.4	813.7
117.5°	247.5	250.8	254.3	264.2	282.8	309.2	347.6	405.5	496.8	626.2	780.6
120°	265.0	268.3	272.7	282.6	301.1	328.6	366.9	419.4	503.8	620.9	762.2
122.5°	283.4	285.9	289.4	299.2	319.6	346.9	385.3	435.3	509.9	616.6	746.5
125°	306.6	308.9	314.3	324.1	345.0	373.4	409.6	456.7	520.2	611.1	725.0
127.5°	324.8	328.1	335.2	347.6	369.8	398.2	433.0	476.5	531.8	608.5	705.3
130°	336.2	339.5	348.3	362.5	385.5	414.0	447.9	489.6	538.9	606.7	692.2
132.5°	345.0	349.1	359.7	375.7	399.5	428.0	461.9	501.0	546.7	606.7	681.6
135°	359.2	363.6	376.7	394.3	417.3	446.9	480.8	516.9	557.4	606.7	669.2
137.5°	377.2	380.5	392.8	410.3	432.8	463.3	494.2	528.8	567.3	608.0	658.0
140°	387.7	391.0	404.2	421.7	442.4	472.0	503.8	536.7	571.7	608.9	652.7
142.5°	399.9	402.4	414.6	432.2	452.1	479.9	509.9	541.0	574.3	609.8	648.4
145°	418.4	420.6	431.5	446.9	466.6	491.7	520.2	547.6	577.2	608.9	641.8
147.5°	437.6	438.9	448.4	462.6	479.7	501.8	526.8	551.6	578.2	606.1	635.0
150°	449.0	451.2	458.9	473.2	488.4	507.1	531.1	554.2	578.2	603.4	629.7
152.5°	461.3	462.6	469.4	481.9	496.3	513.2	535.6	555.9	577.4	599.9	623.6
155°	477.5	477.5	484.1	495.0	506.0	521.3	539.9	557.4	575.0	593.6	613.3
157.5°	492.0	491.7	497.0	506.4	516.0	527.6	543.7	558.6	572.1	587.0	603.7
160°	501.6	500.5	504.9	512.6	521.3	531.1	545.4	558.6	569.5	582.7	595.8
162.5°	509.4	508.4	512.7	519.5	526.6	534.7	547.1	557.7	566.8	577.4	588.8
165°	521.3	519.2	522.5	527.9	532.3	538.9	547.6	556.4	562.9	569.5	578.2
167.5°	529.2	528.1	530.1	533.1	536.2	540.4	547.6	553.7	556.8	561.8	568.0
170°	534.4	533.4	534.4	536.7	538.9	542.2	547.6	552.0	554.2	557.4	561.8
172.5°	538.0	536.0	537.1	539.2	540.5	542.2	546.7	550.3	550.6	552.2	555.7
175°	542.2	539.9	541.0	542.2	542.2	542.2	545.4	547.6	546.5	546.5	547.6
177.5°	544.1	542.3	542.3	543.2	542.3	542.3	544.1	545.0	543.2	543.2	544.1
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333639-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	21.6	21.8	22.1	22.3	22.1	21.8	21.8	21.5
90°	19.7	20.8	21.9	24.1	24.1	24.1	25.2	25.2
92.5°	194.1	140.8	106.0	89.8	75.8	73.1	71.6	69.8
95°	787.4	620.9	486.3	394.3	316.5	283.6	274.9	257.4
97.5°	1172.7	1056.0	924.8	796.8	729.2	667.9	636.1	622.1
100°	1347.1	1293.5	1180.6	1066.7	991.2	912.3	871.8	854.2
102.5°	1405.8	1438.9	1384.8	1307.7	1226.8	1170.7	1126.7	1113.6
105°	1371.2	1521.3	1569.4	1557.4	1522.3	1486.2	1464.2	1451.1
107.5°	1247.6	1447.8	1571.6	1628.8	1646.5	1646.3	1639.1	1630.3
110°	1156.5	1364.6	1519.0	1612.1	1661.4	1682.2	1689.9	1689.9



TEST NUMBER: P333639-830

CATALOG NUMBER: S125RDIP-S1270D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1084.7	1282.2	1438.4	1548.1	1620.2	1656.0	1675.0	1682.9
115°	994.5	1164.2	1314.2	1433.6	1519.0	1571.6	1602.2	1616.5
117.5°	936.1	1082.5	1211.7	1321.3	1406.7	1461.0	1491.5	1500.2
120°	904.7	1036.0	1156.5	1252.9	1334.0	1386.5	1416.1	1424.8
122.5°	881.0	1002.8	1110.1	1200.3	1272.6	1320.8	1350.4	1358.3
125°	846.6	958.3	1053.6	1132.5	1193.7	1238.7	1262.7	1273.8
127.5°	811.5	915.8	1004.8	1078.6	1134.2	1173.8	1196.7	1201.5
130°	789.7	886.0	971.5	1042.6	1097.4	1133.5	1155.5	1162.0
132.5°	767.7	858.0	935.5	1004.1	1058.9	1095.0	1115.1	1122.6
135°	739.2	814.8	885.0	947.3	995.5	1031.7	1051.4	1058.0
137.5°	715.2	776.3	834.5	887.6	930.7	963.6	981.8	988.9
140°	702.0	753.5	803.9	849.9	890.4	918.9	935.3	940.8
142.5°	690.6	734.2	777.6	817.5	851.9	875.9	891.5	896.1
145°	675.7	709.6	743.7	773.2	799.5	818.1	830.2	834.5
147.5°	661.8	689.3	715.4	737.7	758.6	773.5	780.4	782.4
150°	653.8	678.0	698.7	718.4	734.9	748.0	752.4	753.5
152.5°	645.1	666.6	685.6	701.0	714.7	725.2	729.6	730.8
155°	631.9	649.4	664.8	676.8	687.8	695.4	698.7	699.8
157.5°	618.8	633.2	645.1	654.5	663.0	669.4	672.4	672.2
160°	610.0	620.9	631.9	639.6	647.2	652.7	655.0	653.8
162.5°	600.4	610.5	619.6	626.4	632.4	637.0	637.4	637.2
165°	587.0	594.7	601.2	606.7	611.1	613.3	613.3	613.3
167.5°	574.3	579.4	584.4	588.3	590.5	592.5	591.6	591.4
170°	567.3	570.6	573.9	576.1	578.2	579.4	579.4	578.2
172.5°	559.4	562.7	565.1	566.5	566.8	568.8	567.1	566.0
175°	550.9	550.9	553.1	553.1	553.1	554.2	552.0	550.9
177.5°	545.0	545.8	545.8	545.8	545.0	545.8	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2

(END OF REPORT)