

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333258-840

Luminaire Tested: **S125DIP-S1090D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333258-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D365U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5812.5 lumens
Efficiency: N/A
Efficacy: 133.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333258-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333258-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	91	99	95	91	88	86	84	81	79	76	74	72	70	68	65
2	94	87	80	75	90	83	77	72	76	71	67	69	65	62	63	60	57	54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	53	56	52	49	46
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	50	46	42	39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	41	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	31	37	32	29	27
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	32	27	23	21
10	50	38	30	25	48	37	29	25	34	28	24	32	26	22	29	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11129	11129	11129
5°	11154	11048	11119
10°	11086	10970	11032
15°	10965	10838	10884
20°	10794	10653	10672
25°	10608	10434	10424
30°	10380	10197	10147
35°	10136	9942	9802
40°	9885	9666	9528
45°	9613	9414	9227
50°	9315	9109	8835
55°	9026	8765	8519
60°	8681	8418	8117
65°	8270	8000	7728
70°	7878	7517	7260
75°	7177	6939	6700
80°	6390	6289	6133
85°	5550	5654	5350



TEST NUMBER: P333258-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.8
10°-20°	459.0	7.9
20°-30°	677.7	11.7
30°-40°	790.7	13.6
40°-50°	794.2	13.7
50°-60°	697.1	12.0
60°-70°	519.5	8.9
70°-80°	297.0	5.1
80°-90°	87.4	1.5
90°-100°	128.3	2.2
100°-110°	275.8	4.7
110°-120°	258.9	4.5
120°-130°	209.8	3.6
130°-140°	168.4	2.9
140°-150°	127.0	2.2
150°-160°	89.4	1.5
160°-170°	52.7	0.9
170°-180°	17.1	0.3
0°-30°	1299.1	22.4
0°-40°	2089.8	36.0
0°-60°	3581.2	61.6
0°-90°	4485.0	77.2
90°-120°	663.0	11.4
90°-150°	1168.2	20.1
90°-180°	1328.0	22.8
0°-180°	5812.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1720	1717	1704	1716	1715	163
15°	1640	1635	1621	1627	1628	462
25°	1489	1481	1464	1466	1463	685
35°	1286	1279	1261	1254	1243	804
45°	1052	1046	1031	1015	1010	811
55°	802	797	778	766	757	715
65°	541	538	524	512	506	537
75°	288	285	278	274	268	307
85°	75	76	76	75	72	84
90°	0	3	6	8	8	5
95°	12	35	316	143	84	13
105°	40	56	259	510	473	43
115°	72	87	208	448	527	71
125°	100	117	199	356	415	89
135°	117	141	198	299	345	91
145°	136	156	198	247	272	85
155°	156	167	194	219	228	72
165°	170	175	186	197	200	48
175°	177	177	178	180	180	17
180°	177	177	177	177	177	



TEST NUMBER: P333258-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1727.6	1726.9	1726.1	1725.4	1724.6	1723.0	1720.6	1718.2	1715.8	1713.3	1715.8
5°	1720.5	1719.9	1719.3	1718.7	1718.1	1716.3	1713.2	1710.2	1707.2	1704.1	1706.9
7.5°	1704.7	1704.0	1703.4	1702.8	1702.2	1700.2	1696.9	1693.5	1690.2	1686.9	1689.6
10°	1690.5	1689.9	1689.3	1688.7	1688.1	1686.1	1682.7	1679.4	1676.1	1672.7	1675.2
12.5°	1673.0	1671.9	1670.8	1669.7	1668.7	1666.6	1663.4	1660.4	1657.3	1654.2	1656.2
15°	1640.0	1639.1	1638.2	1637.3	1636.4	1634.3	1630.9	1627.6	1624.3	1620.9	1622.4
17.5°	1602.2	1600.8	1599.4	1598.1	1596.8	1594.4	1590.9	1587.5	1584.1	1580.5	1582.5
20°	1570.5	1569.9	1569.3	1568.7	1568.1	1565.8	1561.9	1557.9	1554.0	1550.0	1552.2
22.5°	1538.8	1537.8	1536.7	1535.6	1534.5	1532.1	1528.4	1524.7	1521.1	1517.3	1518.7
25°	1488.7	1487.2	1485.7	1484.2	1482.7	1480.0	1476.0	1472.1	1468.1	1464.2	1464.8
27.5°	1430.1	1429.2	1428.3	1427.3	1426.4	1424.0	1419.9	1415.8	1411.8	1407.8	1407.9
30°	1391.9	1391.0	1390.1	1389.2	1388.3	1385.5	1381.0	1376.4	1371.9	1367.4	1366.8
32.5°	1350.5	1349.1	1347.7	1346.3	1344.9	1342.2	1338.1	1334.0	1330.0	1326.0	1324.8
35°	1285.6	1284.3	1283.1	1281.9	1280.7	1278.0	1273.7	1269.5	1265.3	1261.0	1259.5
37.5°	1218.2	1216.7	1215.2	1213.7	1212.1	1209.4	1205.4	1201.4	1197.4	1193.5	1191.1
40°	1172.5	1170.9	1169.4	1167.9	1166.4	1163.5	1159.2	1155.0	1150.7	1146.5	1143.8
42.5°	1123.4	1122.1	1120.8	1119.5	1118.2	1115.5	1111.3	1107.0	1102.8	1098.5	1096.0
45°	1052.5	1051.3	1050.1	1048.8	1047.6	1045.2	1041.6	1037.9	1034.3	1030.7	1027.0
47.5°	976.1	976.1	976.2	976.3	976.3	974.2	969.9	965.4	961.1	956.7	953.0
50°	927.1	926.1	925.2	924.3	923.4	921.1	917.5	913.8	910.2	906.6	902.6
52.5°	876.9	876.2	875.6	874.8	874.2	871.9	868.1	864.1	860.3	856.4	852.9
55°	801.6	800.7	799.8	798.9	798.0	795.4	791.1	786.9	782.6	778.4	775.7
57.5°	722.3	721.8	721.3	720.8	720.3	718.3	714.7	711.1	707.6	704.0	700.4
60°	672.1	670.9	669.6	668.4	667.2	665.0	661.7	658.3	655.0	651.7	648.6
62.5°	619.8	618.7	617.8	616.8	615.9	614.0	611.1	608.2	605.4	602.6	599.3
65°	541.2	540.6	540.0	539.4	538.8	536.8	533.5	530.2	526.8	523.5	520.8
67.5°	465.1	463.8	462.6	461.3	460.1	458.2	455.7	453.2	450.7	448.3	446.0
70°	417.2	415.7	414.1	412.6	411.1	409.0	406.3	403.5	400.8	398.1	396.3
72.5°	364.9	363.8	362.7	361.7	360.7	359.3	357.6	355.8	354.1	352.2	350.2
75°	287.6	287.0	286.4	285.8	285.2	284.2	282.7	281.1	279.6	278.1	277.2
77.5°	216.5	216.2	216.0	215.8	215.5	215.0	214.1	213.3	212.5	211.6	211.1
80°	171.8	171.8	171.8	171.8	171.8	171.5	170.9	170.3	169.7	169.1	168.7
82.5°	132.5	132.0	131.6	131.1	130.6	130.3	130.2	130.1	129.9	129.8	129.3
85°	74.9	75.2	75.5	75.8	76.1	76.3	76.3	76.3	76.3	76.3	76.0
87.5°	29.5	29.6	29.7	29.9	30.0	30.0	29.9	29.8	29.6	29.5	29.6
90°	0.4	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.8	6.1
92.5°	4.3	5.3	8.3	12.7	18.9	29.3	48.8	81.4	116.9	115.0	93.1
95°	11.8	12.1	14.9	18.9	26.8	42.8	81.0	159.6	258.0	316.2	309.4
97.5°	19.6	20.0	22.0	26.0	33.0	44.5	69.8	127.3	230.5	337.7	391.5
100°	24.9	25.7	27.2	31.0	37.9	48.6	69.3	115.6	205.6	322.2	411.5
102.5°	31.0	31.4	32.5	36.8	43.0	53.4	71.8	110.8	186.7	295.2	399.5
105°	40.3	40.3	42.1	45.6	51.4	61.4	77.1	108.9	168.4	258.7	361.2
107.5°	49.5	50.2	51.9	54.8	60.8	69.8	84.9	112.1	160.8	233.7	322.0
110°	56.0	56.8	58.2	61.4	66.8	76.0	90.7	115.3	158.4	222.0	299.8



TEST NUMBER: P333258-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.6	63.3	64.4	67.7	73.0	82.0	96.0	119.3	158.4	215.1	283.3
115°	72.1	72.8	73.9	77.1	82.4	91.4	104.6	125.2	159.6	207.7	265.2
117.5°	80.7	81.7	82.9	86.0	92.2	100.8	113.3	132.1	161.9	204.1	254.4
120°	86.3	87.5	88.9	92.1	98.2	107.0	119.6	136.7	164.2	202.4	248.4
122.5°	92.4	93.1	94.3	97.6	104.1	113.1	125.5	141.8	166.1	201.0	243.3
125°	100.0	100.7	102.4	105.6	112.4	121.7	133.5	148.9	169.6	199.1	236.3
127.5°	105.8	106.9	109.2	113.3	120.5	129.8	141.1	155.2	173.3	198.3	229.8
130°	109.6	110.7	113.5	118.2	125.6	134.9	145.9	159.6	175.6	197.7	225.6
132.5°	112.4	113.8	117.2	122.4	130.2	139.5	150.6	163.3	178.1	197.7	222.2
135°	117.0	118.5	122.8	128.5	136.0	145.6	156.6	168.4	181.7	197.7	218.0
137.5°	122.9	124.0	127.9	133.7	141.1	151.0	161.1	172.3	184.9	198.1	214.4
140°	126.3	127.4	131.7	137.4	144.2	153.8	164.2	174.9	186.3	198.4	212.7
142.5°	130.4	131.1	135.1	140.9	147.3	156.4	166.1	176.3	187.1	198.7	211.3
145°	136.3	137.0	140.6	145.6	152.1	160.3	169.6	178.4	188.0	198.4	209.1
147.5°	142.6	143.0	146.1	150.8	156.3	163.5	171.7	179.8	188.4	197.5	206.9
150°	146.3	147.0	149.6	154.2	159.2	165.2	173.1	180.6	188.4	196.6	205.2
152.5°	150.4	150.8	153.0	157.0	161.8	167.2	174.5	181.2	188.1	195.5	203.2
155°	155.6	155.6	157.7	161.3	164.9	169.9	175.9	181.7	187.3	193.5	199.9
157.5°	160.4	160.3	162.0	165.0	168.1	172.0	177.1	182.0	186.4	191.3	196.7
160°	163.5	163.1	164.5	167.0	169.9	173.1	177.7	182.0	185.6	189.9	194.2
162.5°	166.0	165.7	167.1	169.4	171.6	174.2	178.3	181.8	184.7	188.1	191.9
165°	169.9	169.2	170.3	172.0	173.5	175.6	178.4	181.3	183.5	185.6	188.4
167.5°	172.5	172.1	172.8	173.7	174.7	176.1	178.4	180.5	181.5	183.1	185.1
170°	174.2	173.8	174.2	174.9	175.6	176.6	178.4	179.9	180.6	181.7	183.1
172.5°	175.3	174.7	175.0	175.7	176.1	176.6	178.1	179.4	179.5	180.0	181.1
175°	176.6	175.9	176.3	176.6	176.6	176.6	177.7	178.4	178.1	178.1	178.4
177.5°	177.3	176.7	176.7	177.0	176.7	176.7	177.3	177.6	177.0	177.0	177.3
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333258-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1718.2	1720.6	1723.0	1724.1	1723.9	1723.6	1723.4	1723.2
5°	1709.6	1712.3	1715.1	1716.3	1716.0	1715.7	1715.4	1715.1
7.5°	1692.2	1695.0	1697.6	1698.8	1698.5	1698.2	1697.9	1697.6
10°	1677.6	1680.0	1682.4	1683.5	1683.2	1682.9	1682.6	1682.3
12.5°	1658.1	1660.0	1661.9	1662.9	1662.8	1662.7	1662.7	1662.6
15°	1624.0	1625.5	1627.0	1627.8	1627.8	1627.8	1627.8	1627.8
17.5°	1584.4	1586.2	1588.1	1588.3	1586.8	1585.3	1583.8	1582.3
20°	1554.3	1556.4	1558.5	1558.8	1557.3	1555.8	1554.3	1552.8
22.5°	1520.1	1521.6	1522.9	1523.1	1522.1	1521.1	1520.0	1518.9
25°	1465.4	1466.0	1466.6	1466.4	1465.5	1464.6	1463.7	1462.8
27.5°	1408.0	1408.1	1408.3	1407.9	1406.9	1406.0	1405.1	1404.2
30°	1366.1	1365.5	1364.9	1364.2	1363.3	1362.4	1361.5	1360.6
32.5°	1323.7	1322.6	1321.6	1320.2	1318.6	1317.0	1315.2	1313.6
35°	1258.0	1256.5	1255.0	1253.0	1250.6	1248.2	1245.8	1243.3
37.5°	1188.9	1186.7	1184.5	1182.7	1181.2	1179.8	1178.4	1177.1
40°	1141.0	1138.3	1135.6	1133.8	1132.9	1132.0	1131.0	1130.1
42.5°	1093.6	1091.1	1088.6	1086.6	1085.3	1083.9	1082.5	1081.1
45°	1023.4	1019.8	1016.1	1013.8	1012.9	1012.0	1011.1	1010.2
47.5°	949.4	945.6	942.0	939.1	937.0	934.8	932.7	930.6
50°	898.7	894.7	890.8	887.8	885.7	883.5	881.4	879.3
52.5°	849.5	846.1	842.6	839.7	837.3	835.0	832.6	830.2
55°	773.0	770.2	767.5	765.1	763.0	760.8	758.7	756.6
57.5°	697.0	693.5	689.9	687.6	686.5	685.3	684.2	683.0
60°	645.6	642.6	639.5	636.9	634.8	632.7	630.6	628.4
62.5°	596.0	592.8	589.5	587.0	585.4	583.8	582.1	580.5
65°	518.1	515.3	512.6	510.6	509.4	508.2	507.0	505.7
67.5°	443.6	441.3	439.0	437.5	436.8	436.1	435.4	434.6
70°	394.5	392.6	390.8	389.3	388.1	386.9	385.7	384.5
72.5°	348.2	346.1	344.1	342.4	341.2	340.0	338.8	337.6
75°	276.3	275.4	274.5	273.4	272.2	270.9	269.7	268.5
77.5°	210.5	210.0	209.4	208.7	207.8	207.0	206.1	205.3
80°	168.4	168.1	167.8	167.3	166.7	166.1	165.5	164.9
82.5°	128.7	128.2	127.6	127.2	127.1	127.0	126.9	126.7
85°	75.7	75.4	75.1	74.6	74.0	73.4	72.8	72.2
87.5°	29.7	29.7	29.8	29.7	29.2	28.7	28.3	27.8
90°	6.5	6.8	7.2	7.9	7.9	7.9	8.2	8.2
92.5°	63.2	45.8	34.5	29.3	24.7	23.8	23.3	22.7
95°	256.6	202.4	158.4	128.5	103.1	92.4	89.6	83.9
97.5°	382.1	344.2	301.3	259.6	237.6	217.6	207.3	202.7
100°	439.0	421.5	384.8	347.6	323.0	297.3	284.1	278.4
102.5°	458.1	468.9	451.3	426.2	399.8	381.5	367.2	362.9
105°	446.9	495.7	511.4	507.6	496.0	484.3	477.2	472.9
107.5°	406.6	471.8	512.1	530.8	536.5	536.5	534.1	531.3
110°	376.9	444.7	495.0	525.3	541.4	548.2	550.7	550.7



TEST NUMBER: P333258-840

CATALOG NUMBER: S125DIP-S1090D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	353.5	417.9	468.8	504.5	528.0	539.7	545.8	548.5
115°	324.1	379.4	428.3	467.2	495.0	512.1	522.1	526.7
117.5°	305.1	352.7	394.9	430.6	458.4	476.2	486.0	488.9
120°	294.8	337.6	376.9	408.3	434.7	451.8	461.5	464.3
122.5°	287.1	326.8	361.7	391.1	414.8	430.4	440.1	442.6
125°	275.9	312.3	343.4	369.0	389.0	403.6	411.5	415.1
127.5°	264.5	298.4	327.4	351.4	369.6	382.5	389.9	391.5
130°	257.3	288.7	316.6	339.8	357.6	369.4	376.6	378.7
132.5°	250.1	279.6	304.9	327.2	345.1	356.8	363.3	365.8
135°	241.0	265.5	288.4	308.7	324.5	336.2	342.6	344.8
137.5°	233.1	253.0	272.0	289.2	303.3	314.0	319.9	322.2
140°	228.7	245.5	262.0	276.9	290.1	299.4	304.8	306.6
142.5°	225.1	239.2	253.4	266.4	277.6	285.5	290.5	292.1
145°	220.3	231.3	242.4	252.0	260.5	266.6	270.5	272.0
147.5°	215.6	224.6	233.2	240.4	247.2	252.1	254.3	255.0
150°	213.1	221.0	227.7	234.1	239.4	243.8	245.2	245.5
152.5°	210.3	217.2	223.4	228.4	232.9	236.3	237.7	238.1
155°	205.9	211.7	216.6	220.6	224.1	226.6	227.7	228.0
157.5°	201.7	206.3	210.3	213.3	216.1	218.1	219.1	219.0
160°	198.8	202.4	205.9	208.4	211.0	212.7	213.4	213.1
162.5°	195.6	198.9	202.0	204.2	206.1	207.5	207.7	207.6
165°	191.3	193.8	195.9	197.7	199.1	199.9	199.9	199.9
167.5°	187.1	188.8	190.5	191.8	192.5	193.1	192.8	192.7
170°	184.9	185.9	187.0	187.7	188.4	188.8	188.8	188.4
172.5°	182.3	183.4	184.2	184.6	184.7	185.4	184.8	184.4
175°	179.6	179.6	180.3	180.3	180.3	180.6	179.9	179.6
177.5°	177.6	177.8	177.8	177.8	177.6	177.8	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0

(END OF REPORT)