

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333621-830

Luminaire Tested: **S125RDIP-S1270D590U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333621-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D590U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6597.8 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333621-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333621-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	98	94	91	97	93	90	86	83	81	78	74	72	71	66	65	63	59
2	94	86	80	75	88	82	76	71	73	69	65	66	62	59	59	56	54	50
3	86	76	69	63	81	72	65	60	65	60	55	58	54	51	52	49	46	43
4	79	68	59	53	74	64	57	51	58	52	47	52	47	44	47	43	40	37
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	42	38	35	32
6	67	54	46	40	63	52	44	39	47	41	36	43	37	34	38	34	31	28
7	62	49	41	35	58	47	40	34	43	37	32	39	34	30	35	31	28	25
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	23
9	54	41	34	28	51	39	32	28	36	30	26	33	28	24	30	26	23	21
10	50	38	31	26	48	36	30	25	33	27	23	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333621-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	2.8
10°-20°	511.3	7.7
20°-30°	741.4	11.2
30°-40°	845.0	12.8
40°-50°	823.6	12.5
50°-60°	693.3	10.5
60°-70°	486.0	7.4
70°-80°	249.8	3.8
80°-90°	64.6	1.0
90°-100°	193.3	2.9
100°-110°	415.5	6.3
110°-120°	390.0	5.9
120°-130°	316.0	4.8
130°-140°	253.6	3.8
140°-150°	191.4	2.9
150°-160°	134.7	2.0
160°-170°	79.4	1.2
170°-180°	25.8	0.4
0°-30°	1435.7	21.8
0°-40°	2280.6	34.6
0°-60°	3797.6	57.6
0°-90°	4598.0	69.7
90°-120°	998.8	15.1
90°-150°	1759.9	26.7
90°-180°	2000.0	30.3
0°-180°	6597.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	1	5	9	11	12	5
95°	18	52	476	216	126	19
105°	61	85	390	767	712	64
115°	109	131	313	674	794	107
125°	150	176	300	537	625	134
135°	176	212	298	450	519	137
145°	205	235	299	372	410	129
155°	234	252	291	329	344	108
165°	256	263	280	296	301	72
175°	266	266	268	272	270	25
180°	267	267	267	267	267	



TEST NUMBER: P333621-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.1	25.4	23.8	22.2	20.5	19.8	19.6	19.5	19.4	19.3	19.4
90°	0.6	1.0	2.2	3.2	4.3	5.4	5.9	7.0	7.5	8.6	9.1
92.5°	6.6	7.9	12.4	19.1	28.4	44.1	73.4	122.7	176.2	173.3	140.3
95°	17.7	18.3	22.6	28.5	40.3	64.6	122.1	240.3	388.7	476.4	466.2
97.5°	29.5	30.1	33.1	39.0	49.7	67.1	105.2	191.8	347.1	508.7	589.8
100°	37.6	38.7	40.9	46.8	57.0	73.1	104.3	174.2	309.7	485.5	619.9
102.5°	46.7	47.3	49.0	55.4	64.8	80.4	108.2	166.9	281.3	444.6	601.8
105°	60.8	60.8	63.4	68.8	77.4	92.5	116.1	164.0	253.7	389.8	544.1
107.5°	74.6	75.6	78.1	82.6	91.5	105.1	128.0	168.9	242.1	352.0	485.2
110°	84.5	85.5	87.7	92.5	100.6	114.5	136.6	173.6	238.7	334.4	451.7



TEST NUMBER: P333621-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	94.3	95.4	97.1	102.0	110.0	123.6	144.8	179.6	238.7	324.1	426.7
115°	108.6	109.7	111.3	116.1	124.2	137.6	157.5	188.7	240.3	312.9	399.4
117.5°	121.5	123.1	124.9	129.7	138.8	151.8	170.7	199.1	243.8	307.5	383.2
120°	130.1	131.8	133.8	138.7	147.9	161.3	180.1	205.9	247.3	304.8	374.2
122.5°	139.1	140.3	142.0	146.8	156.9	170.3	189.2	213.7	250.3	302.7	366.5
125°	150.5	151.7	154.3	159.1	169.4	183.3	201.0	224.2	255.4	300.0	355.9
127.5°	159.5	161.1	164.6	170.7	181.5	195.5	212.5	233.8	261.1	298.7	346.3
130°	165.0	166.6	171.0	178.0	189.3	203.2	219.9	240.3	264.6	297.8	339.8
132.5°	169.4	171.4	176.5	184.5	196.1	210.1	226.8	245.9	268.4	297.8	334.6
135°	176.3	178.5	184.9	193.6	204.8	219.3	236.0	253.7	273.6	297.8	328.5
137.5°	185.2	186.8	192.8	201.4	212.4	227.4	242.6	259.6	278.5	298.5	323.0
140°	190.3	191.9	198.4	207.0	217.3	231.8	247.3	263.4	280.7	299.0	320.5
142.5°	196.3	197.6	203.6	212.2	222.0	235.6	250.3	265.6	281.9	299.4	318.3
145°	205.4	206.4	211.8	219.3	229.0	241.4	255.4	268.8	283.3	299.0	315.1
147.5°	214.8	215.5	220.1	227.1	235.4	246.4	258.6	270.8	283.9	297.6	311.7
150°	220.5	221.5	225.3	232.2	239.8	248.9	260.8	272.0	283.9	296.2	309.2
152.5°	226.5	227.1	230.5	236.6	243.6	251.9	262.9	272.9	283.4	294.5	306.1
155°	234.4	234.4	237.6	243.0	248.4	255.9	265.0	273.6	282.3	291.4	301.0
157.5°	241.5	241.4	244.0	248.6	253.4	259.0	266.9	274.2	280.9	288.1	296.3
160°	246.3	245.7	247.9	251.7	255.9	260.8	267.8	274.2	279.6	286.1	292.5
162.5°	250.2	249.6	251.8	255.1	258.5	262.5	268.6	273.8	278.3	283.4	289.1
165°	255.9	254.9	256.5	259.1	261.3	264.6	268.8	273.1	276.4	279.6	283.9
167.5°	259.8	259.3	260.2	261.7	263.3	265.2	268.8	271.8	273.3	275.8	278.8
170°	262.4	261.8	262.4	263.4	264.6	266.2	268.8	271.0	272.0	273.6	275.8
172.5°	264.1	263.2	263.6	264.8	265.4	266.2	268.4	270.1	270.3	271.1	272.8
175°	266.2	265.0	265.6	266.2	266.2	266.2	267.8	268.8	268.2	268.2	268.8
177.5°	267.1	266.3	266.3	266.6	266.3	266.3	267.1	267.5	266.6	266.6	267.1
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333621-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	19.6	19.7	19.8	19.9	19.6	19.3	19.2	18.9
90°	9.7	10.2	10.7	11.8	11.8	11.8	12.3	12.3
92.5°	95.3	69.2	52.0	44.1	37.2	35.9	35.2	34.3
95°	386.5	304.8	238.7	193.6	155.4	139.2	135.0	126.4
97.5°	575.7	518.4	454.0	391.2	358.0	327.8	312.3	305.4
100°	661.3	635.0	579.6	523.7	486.5	447.9	428.0	419.3
102.5°	690.1	706.3	679.8	642.0	602.3	574.8	553.2	546.7
105°	673.2	746.8	770.4	764.5	747.3	729.6	718.9	712.4
107.5°	612.5	710.8	771.6	799.6	808.3	808.2	804.6	800.3
110°	567.8	670.0	745.7	791.5	815.6	825.9	829.6	829.6



TEST NUMBER: P333621-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	532.5	629.5	706.2	760.1	795.4	812.9	822.3	826.1
115°	488.1	571.6	645.2	703.8	745.7	771.6	786.6	793.6
117.5°	459.6	531.4	594.8	648.7	690.6	717.3	732.2	736.5
120°	444.1	508.6	567.8	615.1	654.9	680.7	695.2	699.5
122.5°	432.5	492.3	545.0	589.3	624.7	648.4	662.9	666.8
125°	415.6	470.4	517.3	555.9	586.1	608.1	619.9	625.3
127.5°	398.4	449.6	493.2	529.5	556.8	576.3	587.4	589.8
130°	387.7	435.0	476.9	511.8	538.8	556.5	567.2	570.4
132.5°	376.9	421.2	459.3	492.9	519.8	537.5	547.4	551.1
135°	362.9	400.0	434.4	465.1	488.7	506.4	516.1	519.3
137.5°	351.1	381.1	409.7	435.7	456.9	473.1	481.9	485.5
140°	344.6	369.9	394.6	417.3	437.2	451.1	459.1	461.8
142.5°	339.0	360.4	381.7	401.3	418.2	430.0	437.6	439.9
145°	331.8	348.4	365.0	379.6	392.5	401.6	407.6	409.7
147.5°	324.9	338.4	351.2	362.1	372.4	379.7	383.1	384.1
150°	320.9	332.8	343.0	352.7	360.8	367.2	369.4	369.9
152.5°	316.7	327.3	336.6	344.1	350.9	356.0	358.2	358.7
155°	310.2	318.9	326.3	332.2	337.6	341.4	343.0	343.6
157.5°	303.8	310.9	316.7	321.3	325.5	328.6	330.1	330.0
160°	299.4	304.8	310.2	314.0	317.7	320.5	321.5	320.9
162.5°	294.7	299.7	304.2	307.6	310.5	312.7	312.9	312.8
165°	288.1	291.9	295.2	297.8	300.0	301.0	301.0	301.0
167.5°	281.9	284.5	286.9	288.8	289.9	290.9	290.4	290.3
170°	278.5	280.1	281.7	282.8	283.9	284.5	284.5	283.9
172.5°	274.7	276.3	277.4	278.1	278.3	279.3	278.4	277.9
175°	270.4	270.4	271.5	271.5	271.5	272.0	271.0	270.4
177.5°	267.5	268.0	268.0	268.0	267.5	268.0	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6

(END OF REPORT)