

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333261-840

Luminaire Tested: **S125DIP-S1090D590U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333261-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D590U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6675.7 lumens
Efficiency: N/A
Efficacy: 136.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	73	73	73	68
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	65	63	62	58
2	93	86	80	74	88	81	76	71	73	68	65	65	61	58	57	55	53	49
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	67	59	53	73	64	56	51	57	51	47	51	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	28
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	24
8	57	44	37	31	54	42	35	30	39	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10371	10371	10371	10371
5°	12010	10407	9111	10407
10°	13973	10352	7984	10352
15°	15468	10277	7365	10277
20°	17314	10156	6868	10156
25°	20283	10020	6625	10020
30°	21908	9887	6415	9887
35°	18013	9635	6277	9635
40°	12803	9286	6126	9286
45°	9836	8815	6039	8815
50°	8397	8232	6027	8232
55°	7475	7659	6079	7659
60°	6744	7034	6234	7034
65°	6229	6406	6395	6406
70°	5663	5754	6488	5754
75°	5001	5068	6428	5068
80°	4206	4132	5880	4132
85°	3327	2979	4742	2979



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.6	2.3
10°-20°	460.3	6.9
20°-30°	747.4	11.2
30°-40°	911.7	13.7
40°-50°	829.4	12.4
50°-60°	660.6	9.9
60°-70°	460.1	6.9
70°-80°	245.4	3.7
80°-90°	63.5	1.0
90°-100°	207.1	3.1
100°-110°	445.2	6.7
110°-120°	417.8	6.3
120°-130°	338.6	5.1
130°-140°	271.7	4.1
140°-150°	205.1	3.1
150°-160°	144.3	2.2
160°-170°	85.1	1.3
170°-180°	27.7	0.4
0°-30°	1362.3	20.4
0°-40°	2274.0	34.1
0°-60°	3764.0	56.4
0°-90°	4533.1	67.9
90°-120°	1070.2	16.0
90°-150°	1885.6	28.2
90°-180°	2143.0	32.1
0°-180°	6675.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1606	1606	1606	1606	1606	
5°	1853	1605	1405	1605	1853	187
15°	2313	1537	1102	1537	2313	662
25°	2846	1406	930	1406	2846	1300
35°	2285	1222	796	1222	2285	1398
45°	1077	965	661	965	1077	862
55°	664	680	540	680	664	598
65°	408	419	418	419	408	405
75°	200	203	258	203	200	216
85°	45	40	64	40	45	52
90°	13	1	13	1	13	11
95°	135	19	135	19	135	192
105°	763	65	763	65	763	759
115°	850	116	850	116	850	831
125°	670	161	670	161	670	606
135°	556	189	556	189	556	431
145°	439	220	439	220	439	279
155°	368	251	368	251	368	172
165°	323	274	323	274	323	92
175°	290	285	290	285	290	28
180°	286	286	286	286	286	



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1698.6	1696.4	1694.3	1689.8	1693.1	1683.8	1679.5	1671.8	1662.5	1659.3	1655.5
5°	1852.6	1856.0	1859.5	1845.1	1846.4	1836.9	1815.1	1797.4	1783.1	1764.6	1751.7
7.5°	2038.0	2029.9	2029.3	2020.0	2004.1	1991.3	1968.3	1939.1	1911.0	1878.8	1852.2
10°	2130.7	2131.4	2125.3	2114.4	2097.3	2085.1	2055.1	2026.4	1991.7	1950.8	1921.5
12.5°	2200.5	2203.3	2195.6	2180.9	2172.5	2145.1	2121.6	2087.5	2046.2	2013.5	1968.9
15°	2313.4	2305.9	2300.5	2282.0	2267.8	2239.1	2201.6	2166.2	2121.1	2079.6	2038.0
17.5°	2422.2	2428.1	2417.9	2401.2	2356.7	2323.3	2273.0	2224.5	2168.5	2112.7	2063.1
20°	2519.2	2524.7	2509.0	2479.7	2426.5	2393.2	2327.0	2264.3	2199.6	2128.0	2073.5
22.5°	2640.3	2635.9	2614.7	2570.2	2524.2	2462.4	2390.9	2314.5	2233.3	2152.5	2080.0
25°	2846.4	2817.7	2804.8	2749.7	2689.0	2598.3	2500.1	2388.3	2287.4	2180.5	2087.8
27.5°	2960.6	2951.6	2937.2	2898.7	2835.0	2738.0	2622.3	2486.1	2343.8	2208.7	2087.4
30°	2937.7	2939.1	2940.4	2928.2	2887.3	2814.4	2699.2	2552.6	2383.6	2231.6	2091.1
32.5°	2734.9	2759.7	2783.4	2811.5	2823.0	2808.9	2736.8	2604.4	2430.4	2257.8	2089.0
35°	2284.7	2292.3	2369.2	2445.6	2549.2	2629.7	2683.5	2624.8	2478.3	2280.0	2086.4
37.5°	1781.5	1818.3	1871.6	1957.8	2107.4	2241.3	2413.5	2492.6	2445.4	2287.2	2081.6
40°	1518.6	1552.7	1587.5	1675.4	1801.5	1963.7	2159.3	2326.3	2365.2	2264.3	2065.3
42.5°	1315.8	1342.8	1381.4	1447.4	1552.9	1696.6	1883.4	2101.6	2235.9	2197.8	2030.9
45°	1076.9	1094.0	1124.0	1176.5	1252.8	1365.2	1530.2	1768.8	1976.7	2045.5	1949.4
47.5°	921.8	921.7	945.0	981.3	1036.3	1131.9	1253.8	1440.8	1662.8	1827.1	1819.5
50°	835.7	832.2	850.6	882.0	925.6	989.1	1105.6	1254.9	1468.1	1654.3	1706.1
52.5°	761.5	761.9	773.3	796.4	832.9	887.1	974.1	1108.7	1291.0	1482.0	1579.5
55°	663.9	661.2	674.1	689.8	716.4	751.8	814.6	917.5	1065.3	1253.4	1380.3
57.5°	574.4	582.0	587.1	598.0	620.2	643.9	696.7	772.2	889.6	1051.1	1185.1
60°	522.1	529.6	533.7	544.6	562.3	582.8	623.7	685.0	783.9	922.9	1055.8
62.5°	475.2	481.1	482.4	492.2	506.8	526.6	558.8	610.4	688.4	810.0	940.2
65°	407.6	407.6	410.3	420.5	427.4	445.0	469.6	507.2	569.9	664.6	775.7
67.5°	342.4	345.7	345.1	349.5	355.8	369.6	387.2	418.1	464.5	533.7	622.6
70°	299.9	302.7	301.9	305.4	312.1	321.0	335.4	364.7	398.1	457.4	533.7
72.5°	261.8	262.9	261.1	265.6	269.6	277.4	293.4	309.0	340.2	390.3	453.0
75°	200.4	201.8	203.1	205.8	210.0	214.0	222.2	237.9	258.3	295.8	336.1
77.5°	150.3	147.6	150.9	150.5	152.8	155.9	163.2	171.5	188.2	212.0	243.1
80°	113.1	113.8	113.8	114.5	118.0	120.0	126.1	132.2	145.2	162.9	184.7
82.5°	82.6	84.4	83.3	84.5	87.4	88.9	92.3	97.4	104.8	118.8	134.5
85°	44.9	41.6	42.9	44.3	44.3	44.9	47.7	49.8	53.8	59.3	65.4
87.5°	15.8	16.9	17.3	17.3	17.8	17.6	19.6	19.5	21.0	22.5	24.5
90°	13.2	13.2	12.6	12.6	12.6	11.5	10.9	10.4	9.8	9.2	8.1
92.5°	36.8	37.7	38.5	39.9	47.3	55.7	74.1	102.1	150.4	185.7	188.7
95°	135.4	144.6	149.2	166.5	207.4	255.8	326.6	414.1	499.5	510.4	416.5
97.5°	327.2	334.6	351.2	383.5	419.1	486.5	555.4	616.8	632.0	545.0	371.9
100°	449.3	458.6	479.9	521.3	561.1	621.0	680.3	708.5	664.2	520.2	331.8
102.5°	585.7	592.7	615.8	645.3	687.8	728.3	756.8	739.4	644.8	476.4	301.3
105°	763.3	770.2	781.7	800.7	819.1	825.5	800.1	721.2	583.0	417.7	271.9
107.5°	857.5	862.1	866.0	866.1	856.7	826.7	761.5	656.2	519.9	377.2	259.4
110°	888.9	888.9	884.8	873.8	848.0	799.0	717.8	608.3	483.9	358.3	255.8



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	885.1	881.0	871.0	852.2	814.4	756.6	674.5	570.6	457.2	347.3	255.8
115°	850.3	842.7	826.7	799.0	754.1	691.3	612.4	523.0	428.0	335.3	257.5
117.5°	789.1	784.5	768.5	739.9	695.0	637.3	569.4	492.4	410.6	329.4	261.3
120°	749.4	744.9	729.3	701.7	659.0	608.3	544.9	475.8	400.9	326.6	265.0
122.5°	714.4	710.2	694.7	669.3	631.4	583.9	527.5	463.4	392.6	324.4	268.2
125°	669.9	664.2	651.6	627.9	595.6	554.2	504.0	445.2	381.3	321.4	273.7
127.5°	632.0	629.3	617.4	596.5	567.3	528.5	481.7	426.9	371.0	320.0	279.7
130°	611.2	607.7	596.2	577.2	548.4	511.0	466.1	415.4	364.1	319.1	283.5
132.5°	590.5	586.5	575.9	556.9	528.2	492.1	451.3	403.8	358.5	319.1	287.6
135°	556.4	553.0	542.6	523.6	498.3	465.4	428.6	388.8	351.9	319.1	293.2
137.5°	520.2	516.3	506.9	489.5	466.9	439.0	408.3	376.2	346.1	319.8	298.4
140°	494.8	491.9	483.3	468.4	447.1	422.8	396.4	369.2	343.4	320.3	300.7
142.5°	471.3	468.9	460.7	448.1	430.0	409.0	386.2	363.2	341.0	320.7	302.1
145°	439.0	436.7	430.3	420.5	406.7	391.1	373.2	355.5	337.6	320.3	303.6
147.5°	411.5	410.5	406.8	399.0	388.0	376.3	362.5	348.1	334.0	318.8	304.2
150°	396.4	395.8	393.4	386.6	377.9	367.5	356.6	343.9	331.2	317.4	304.2
152.5°	384.4	383.7	381.4	376.0	368.7	360.6	350.6	339.3	328.0	315.6	303.7
155°	368.1	367.5	365.8	361.7	356.0	349.6	341.6	332.3	322.6	312.3	302.5
157.5°	353.6	353.7	352.0	348.7	344.3	339.3	333.1	325.5	317.5	308.7	300.9
160°	343.9	344.5	343.4	340.4	336.4	332.3	326.6	320.8	313.4	306.5	299.5
162.5°	335.2	335.3	335.1	332.6	329.5	325.9	321.1	315.8	309.7	303.7	298.2
165°	322.6	322.6	322.6	321.4	319.1	316.3	312.8	308.7	304.2	299.5	296.1
167.5°	311.0	311.1	311.6	310.6	309.4	307.4	304.8	302.1	298.7	295.5	292.9
170°	304.2	304.8	304.8	304.2	303.0	301.8	300.1	298.4	295.5	293.2	291.4
172.5°	297.7	298.3	299.2	298.2	297.9	297.2	296.0	294.3	292.3	290.4	289.6
175°	289.7	290.3	291.4	290.9	290.9	290.9	289.7	289.7	288.0	287.4	287.4
177.5°	285.7	285.7	287.1	286.6	287.1	287.1	287.1	286.6	286.2	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1652.2	1648.4	1644.1	1636.4	1627.1	1622.2	1614.6	1609.7	1599.8	1591.6	1583.0
5°	1736.1	1718.4	1702.0	1680.8	1657.7	1642.6	1625.0	1605.2	1584.8	1563.6	1540.4
7.5°	1822.9	1791.5	1757.5	1720.8	1685.0	1651.9	1620.4	1589.5	1560.6	1525.7	1496.1
10°	1881.3	1841.7	1799.5	1749.7	1701.3	1659.0	1616.1	1578.6	1540.4	1499.5	1463.4
12.5°	1939.5	1886.9	1827.2	1772.6	1714.3	1663.3	1612.9	1565.0	1517.0	1471.8	1429.6
15°	1980.7	1934.4	1879.2	1801.5	1736.1	1665.9	1599.0	1537.0	1479.0	1428.7	1375.5
17.5°	2007.9	1948.1	1888.9	1814.3	1728.6	1650.0	1574.4	1503.4	1438.0	1374.1	1322.8
20°	2012.8	1951.5	1889.5	1816.4	1728.6	1638.6	1563.0	1477.7	1407.5	1341.4	1278.7
22.5°	2011.1	1941.7	1874.1	1799.1	1713.3	1630.4	1538.9	1452.1	1375.9	1310.9	1245.5
25°	1995.8	1921.5	1836.9	1761.3	1676.8	1588.8	1496.1	1406.1	1328.5	1254.2	1189.4
27.5°	1983.0	1886.5	1790.9	1702.6	1621.0	1540.4	1451.7	1359.6	1273.3	1198.1	1137.1
30°	1967.1	1861.5	1753.7	1661.7	1577.9	1499.5	1415.7	1325.8	1235.8	1162.2	1096.7
32.5°	1953.0	1829.9	1716.2	1616.0	1527.2	1451.0	1373.7	1288.1	1199.7	1125.1	1059.7
35°	1925.5	1783.1	1652.9	1539.7	1445.0	1366.7	1301.9	1222.1	1141.0	1068.7	1006.0
37.5°	1890.8	1721.7	1582.1	1463.4	1359.6	1277.0	1216.7	1155.5	1077.6	1007.9	951.3
40°	1863.5	1678.1	1530.2	1408.9	1301.2	1215.3	1159.4	1101.5	1036.7	972.0	912.0
42.5°	1829.2	1638.9	1477.8	1347.3	1240.6	1157.0	1098.3	1049.1	992.0	931.6	876.0
45°	1766.1	1567.7	1393.2	1252.8	1145.1	1062.6	1002.0	965.1	922.2	864.9	817.9
47.5°	1673.2	1482.2	1301.7	1156.8	1045.7	969.3	912.4	877.1	846.9	804.3	761.6
50°	1590.8	1418.5	1235.8	1092.0	980.9	903.8	851.3	819.3	793.3	760.6	724.6
52.5°	1498.7	1338.3	1170.8	1028.6	918.7	842.7	791.3	763.2	741.5	718.1	682.6
55°	1352.3	1216.0	1060.6	925.6	824.0	749.7	704.8	680.2	662.6	644.8	623.0
57.5°	1191.0	1084.4	946.7	823.3	729.8	662.3	620.3	596.4	582.6	573.5	560.7
60°	1077.6	986.3	867.7	755.2	663.9	603.9	563.0	544.6	533.0	525.5	515.9
62.5°	972.4	897.4	787.5	684.9	605.0	548.3	511.8	493.9	482.8	479.2	471.3
65°	817.3	759.3	668.6	583.5	515.3	466.9	436.3	419.2	412.3	408.3	409.0
67.5°	664.4	629.1	556.3	483.6	429.3	388.7	364.2	351.0	347.6	342.1	342.0
70°	571.2	544.6	483.2	419.9	371.4	340.1	318.3	304.7	301.2	298.5	297.9
72.5°	488.9	465.5	412.3	361.5	318.0	290.5	272.5	264.3	258.7	257.1	257.0
75°	367.4	354.5	312.1	272.0	242.0	222.9	210.7	203.1	199.0	198.3	199.0
77.5°	261.2	249.8	223.0	194.5	175.6	161.2	150.8	148.1	143.5	143.7	143.0
80°	196.3	188.8	171.8	149.3	133.6	121.3	115.8	111.1	109.8	107.7	109.8
82.5°	142.3	134.3	122.7	108.4	95.4	88.1	82.6	81.1	80.3	79.4	79.8
85°	70.2	70.9	64.0	53.1	47.7	43.6	40.2	40.2	39.5	38.9	39.5
87.5°	25.4	24.1	21.9	20.0	17.1	15.1	14.4	14.8	13.3	13.0	13.7
90°	7.5	6.4	5.8	4.6	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	131.5	78.7	47.3	30.4	20.5	13.3	8.5	7.1	8.5	13.3	20.5
95°	257.5	130.8	69.2	43.2	30.5	24.2	19.6	19.0	19.6	24.2	30.5
97.5°	205.5	112.7	71.9	53.2	41.8	35.4	32.2	31.6	32.2	35.4	41.8
100°	186.6	111.8	78.4	61.1	50.1	43.8	41.5	40.3	41.5	43.8	50.1
102.5°	178.8	115.9	86.1	69.4	59.4	52.5	50.7	50.0	50.7	52.5	59.4
105°	175.7	124.4	99.1	82.9	73.7	68.0	65.1	65.1	65.1	68.0	73.7
107.5°	181.0	137.1	112.6	98.1	88.5	83.7	81.0	79.9	81.0	83.7	88.5
110°	186.0	146.3	122.7	107.8	99.1	93.9	91.6	90.5	91.6	93.9	99.1



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	192.5	155.1	132.4	117.9	109.3	104.0	102.2	101.1	102.2	104.0	109.3
115°	202.2	168.7	147.4	133.1	124.4	119.3	117.5	116.3	117.5	119.3	124.4
117.5°	213.3	182.9	162.7	148.8	139.0	133.8	131.9	130.2	131.9	133.8	139.0
120°	220.7	193.0	172.8	158.4	148.7	143.4	141.2	139.4	141.2	143.4	148.7
122.5°	228.9	202.7	182.5	168.1	157.3	152.2	150.4	149.1	150.4	152.2	157.3
125°	240.2	215.4	196.4	181.5	170.5	165.3	162.5	161.3	162.5	165.3	170.5
127.5°	250.5	227.7	209.4	194.5	182.9	176.3	172.6	170.9	172.6	176.3	182.9
130°	257.5	235.6	217.7	202.8	190.7	183.2	178.5	176.8	178.5	183.2	190.7
132.5°	263.5	243.0	225.1	210.2	197.6	189.1	183.7	181.5	183.7	189.1	197.6
135°	271.9	252.9	235.0	219.4	207.4	198.1	191.3	188.9	191.3	198.1	207.4
137.5°	278.1	259.9	243.7	227.6	215.8	206.6	200.2	198.4	200.2	206.6	215.8
140°	282.3	265.0	248.3	232.8	221.8	212.6	205.6	203.9	205.6	212.6	221.8
142.5°	284.6	268.2	252.5	237.8	227.3	218.1	211.7	210.4	211.7	218.1	227.3
145°	288.0	273.7	258.6	245.4	235.0	226.9	221.2	220.0	221.2	226.9	235.0
147.5°	290.1	277.1	264.0	252.3	243.3	235.8	230.9	230.1	230.9	235.8	243.3
150°	291.4	279.4	266.7	256.9	248.8	241.4	237.3	236.2	237.3	241.4	248.8
152.5°	292.4	281.7	269.9	261.1	253.5	246.9	243.3	242.7	243.3	246.9	253.5
155°	293.2	284.0	274.2	266.1	260.3	254.6	251.2	251.2	251.2	254.6	260.3
157.5°	293.8	286.0	277.5	271.5	266.4	261.5	258.6	258.7	258.6	261.5	266.4
160°	293.8	286.9	279.4	274.2	269.6	265.6	263.3	263.9	263.3	265.6	269.6
162.5°	293.4	287.8	281.2	277.0	273.3	269.7	267.4	268.0	267.4	269.7	273.3
165°	292.7	288.0	283.5	279.9	277.6	274.8	273.1	274.2	273.1	274.8	277.6
167.5°	291.2	288.0	284.2	282.1	280.4	278.8	277.8	278.3	277.8	278.8	280.4
170°	290.3	288.0	285.2	283.5	282.3	281.1	280.5	281.1	280.5	281.1	282.3
172.5°	289.4	287.6	285.2	284.4	283.7	282.5	282.0	283.0	282.0	282.5	283.7
175°	288.0	286.9	285.2	285.2	285.2	284.6	284.0	285.2	284.0	284.6	285.2
177.5°	286.6	286.2	285.3	285.3	285.7	285.3	285.3	286.2	285.3	285.3	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1578.0	1572.1	1567.1	1556.2	1550.2	1542.1	1535.5	1542.6	1535.0	1538.2	1533.4
5°	1528.8	1509.7	1496.1	1476.3	1459.4	1443.6	1432.1	1430.0	1424.5	1421.8	1413.6
7.5°	1469.7	1445.8	1422.4	1396.4	1374.6	1352.4	1338.3	1326.6	1318.8	1308.6	1301.6
10°	1434.8	1402.7	1375.5	1344.1	1316.9	1293.0	1273.9	1264.4	1255.6	1242.5	1237.8
12.5°	1391.7	1358.6	1325.3	1291.8	1265.6	1239.0	1222.6	1208.2	1202.0	1187.5	1186.0
15°	1340.1	1290.3	1257.6	1223.5	1187.4	1165.6	1152.0	1136.2	1129.4	1119.2	1111.7
17.5°	1278.4	1234.0	1193.1	1157.8	1126.8	1108.4	1091.6	1080.8	1069.0	1062.4	1050.1
20°	1233.8	1191.4	1150.5	1113.1	1089.2	1068.0	1054.4	1044.2	1032.0	1028.5	1016.3
22.5°	1196.1	1149.4	1110.2	1078.7	1052.7	1028.9	1014.1	1007.1	998.7	988.2	985.7
25°	1134.9	1086.5	1053.1	1021.8	998.6	976.7	966.5	957.7	949.5	942.0	939.3
27.5°	1082.0	1038.7	999.1	970.8	950.6	930.7	921.7	910.9	904.9	898.9	891.5
30°	1044.9	1000.6	965.8	938.6	916.8	899.1	889.5	882.0	876.6	871.1	867.0
32.5°	1006.7	965.7	932.0	905.3	883.5	870.1	861.7	856.4	850.4	843.8	838.7
35°	956.3	911.3	878.6	855.5	838.4	828.2	818.6	813.9	807.0	807.0	801.5
37.5°	899.5	860.6	831.7	810.6	795.3	786.2	775.8	772.5	768.2	765.3	763.4
40°	865.7	829.5	802.2	781.1	764.8	757.3	749.1	743.7	740.9	737.5	736.1
42.5°	830.7	796.3	770.1	750.6	736.4	730.0	722.4	718.5	713.1	708.6	707.8
45°	777.7	744.3	720.4	704.8	692.5	685.0	680.2	672.1	669.3	663.9	663.2
47.5°	727.4	695.4	672.0	659.1	648.3	642.2	634.7	626.5	623.4	620.7	620.4
50°	689.8	660.5	638.6	626.4	616.2	607.3	599.9	594.4	592.3	592.3	593.7
52.5°	651.7	626.6	608.1	593.1	583.5	574.0	567.1	563.8	560.7	564.0	566.4
55°	595.7	570.5	556.8	542.6	533.0	522.1	518.7	517.4	515.3	520.8	523.5
57.5°	536.5	518.9	502.9	488.7	480.1	473.8	469.2	468.4	472.2	474.8	483.6
60°	499.0	478.5	464.1	453.2	443.0	439.0	437.6	436.3	439.0	446.5	458.1
62.5°	457.5	440.9	425.5	417.3	409.8	402.9	402.7	403.5	409.0	417.6	429.1
65°	396.7	382.3	372.1	362.6	356.5	352.3	353.8	356.5	362.6	374.2	387.2
67.5°	335.0	325.2	316.0	308.2	302.4	302.4	303.8	307.8	315.1	328.4	340.2
70°	295.2	284.3	276.7	273.4	268.5	265.8	269.9	276.7	282.9	295.2	305.4
72.5°	255.3	246.1	240.2	237.9	235.8	233.7	235.0	242.4	250.6	263.0	274.8
75°	196.3	192.9	188.8	186.1	184.0	185.4	186.7	193.6	200.4	213.4	227.0
77.5°	143.3	139.8	137.2	136.6	135.5	136.2	140.0	145.0	151.7	161.2	171.5
80°	108.4	107.0	105.6	104.9	104.9	105.6	111.1	114.5	120.7	129.5	137.6
82.5°	79.0	78.1	77.9	77.7	78.3	78.4	81.7	86.1	91.2	97.9	104.9
85°	41.6	40.2	42.2	42.9	41.6	43.6	44.9	47.7	49.8	53.1	56.6
87.5°	14.5	15.9	15.5	16.3	16.4	17.7	17.3	19.5	20.7	21.9	21.6
90°	4.6	5.8	6.4	7.5	8.1	9.2	9.8	10.4	10.9	11.5	12.6
92.5°	30.4	47.3	78.7	131.5	188.7	185.7	150.4	102.1	74.1	55.7	47.3
95°	43.2	69.2	130.8	257.5	416.5	510.4	499.5	414.1	326.6	255.8	207.4
97.5°	53.2	71.9	112.7	205.5	371.9	545.0	632.0	616.8	555.4	486.5	419.1
100°	61.1	78.4	111.8	186.6	331.8	520.2	664.2	708.5	680.3	621.0	561.1
102.5°	69.4	86.1	115.9	178.8	301.3	476.4	644.8	739.4	756.8	728.3	687.8
105°	82.9	99.1	124.4	175.7	271.9	417.7	583.0	721.2	800.1	825.5	819.1
107.5°	98.1	112.6	137.1	181.0	259.4	377.2	519.9	656.2	761.5	826.7	856.7
110°	107.8	122.7	146.3	186.0	255.8	358.3	483.9	608.3	717.8	799.0	848.0



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.9	132.4	155.1	192.5	255.8	347.3	457.2	570.6	674.5	756.6	814.4
115°	133.1	147.4	168.7	202.2	257.5	335.3	428.0	523.0	612.4	691.3	754.1
117.5°	148.8	162.7	182.9	213.3	261.3	329.4	410.6	492.4	569.4	637.3	695.0
120°	158.4	172.8	193.0	220.7	265.0	326.6	400.9	475.8	544.9	608.3	659.0
122.5°	168.1	182.5	202.7	228.9	268.2	324.4	392.6	463.4	527.5	583.9	631.4
125°	181.5	196.4	215.4	240.2	273.7	321.4	381.3	445.2	504.0	554.2	595.6
127.5°	194.5	209.4	227.7	250.5	279.7	320.0	371.0	426.9	481.7	528.5	567.3
130°	202.8	217.7	235.6	257.5	283.5	319.1	364.1	415.4	466.1	511.0	548.4
132.5°	210.2	225.1	243.0	263.5	287.6	319.1	358.5	403.8	451.3	492.1	528.2
135°	219.4	235.0	252.9	271.9	293.2	319.1	351.9	388.8	428.6	465.4	498.3
137.5°	227.6	243.7	259.9	278.1	298.4	319.8	346.1	376.2	408.3	439.0	466.9
140°	232.8	248.3	265.0	282.3	300.7	320.3	343.4	369.2	396.4	422.8	447.1
142.5°	237.8	252.5	268.2	284.6	302.1	320.7	341.0	363.2	386.2	409.0	430.0
145°	245.4	258.6	273.7	288.0	303.6	320.3	337.6	355.5	373.2	391.1	406.7
147.5°	252.3	264.0	277.1	290.1	304.2	318.8	334.0	348.1	362.5	376.3	388.0
150°	256.9	266.7	279.4	291.4	304.2	317.4	331.2	343.9	356.6	367.5	377.9
152.5°	261.1	269.9	281.7	292.4	303.7	315.6	328.0	339.3	350.6	360.6	368.7
155°	266.1	274.2	284.0	293.2	302.5	312.3	322.6	332.3	341.6	349.6	356.0
157.5°	271.5	277.5	286.0	293.8	300.9	308.7	317.5	325.5	333.1	339.3	344.3
160°	274.2	279.4	286.9	293.8	299.5	306.5	313.4	320.8	326.6	332.3	336.4
162.5°	277.0	281.2	287.8	293.4	298.2	303.7	309.7	315.8	321.1	325.9	329.5
165°	279.9	283.5	288.0	292.7	296.1	299.5	304.2	308.7	312.8	316.3	319.1
167.5°	282.1	284.2	288.0	291.2	292.9	295.5	298.7	302.1	304.8	307.4	309.4
170°	283.5	285.2	288.0	290.3	291.4	293.2	295.5	298.4	300.1	301.8	303.0
172.5°	284.4	285.2	287.6	289.4	289.6	290.4	292.3	294.3	296.0	297.2	297.9
175°	285.2	285.2	286.9	288.0	287.4	287.4	288.0	289.7	289.7	290.9	290.9
177.5°	285.3	285.3	286.2	286.6	285.7	285.7	286.2	286.6	287.1	287.1	287.1
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1530.0	1533.9	1530.7	1535.0	1530.7	1533.9	1530.0	1533.4	1538.2	1535.0	1542.6
5°	1410.3	1404.1	1408.2	1405.4	1408.2	1404.1	1410.3	1413.6	1421.8	1424.5	1430.0
7.5°	1299.6	1293.7	1287.0	1283.8	1287.0	1293.7	1299.6	1301.6	1308.6	1318.8	1326.6
10°	1230.3	1222.8	1222.1	1217.4	1222.1	1222.8	1230.3	1237.8	1242.5	1255.6	1264.4
12.5°	1179.6	1172.7	1164.9	1162.9	1164.9	1172.7	1179.6	1186.0	1187.5	1202.0	1208.2
15°	1107.6	1102.2	1097.4	1101.5	1097.4	1102.2	1107.6	1111.7	1119.2	1129.4	1136.2
17.5°	1047.7	1043.3	1042.5	1037.4	1042.5	1043.3	1047.7	1050.1	1062.4	1069.0	1080.8
20°	1010.2	1006.7	1008.1	999.3	1008.1	1006.7	1010.2	1016.3	1028.5	1032.0	1044.2
22.5°	980.2	973.5	972.7	970.9	972.7	973.5	980.2	985.7	988.2	998.7	1007.1
25°	933.1	929.7	926.3	929.7	926.3	929.7	933.1	939.3	942.0	949.5	957.7
27.5°	892.1	888.0	887.1	887.5	887.1	888.0	892.1	891.5	898.9	904.9	910.9
30°	867.0	860.2	860.9	860.2	860.9	860.2	867.0	867.0	871.1	876.6	882.0
32.5°	839.7	835.1	834.1	832.9	834.1	835.1	839.7	838.7	843.8	850.4	856.4
35°	799.5	799.5	796.1	796.1	796.1	799.5	799.5	801.5	807.0	807.0	813.9
37.5°	761.7	761.0	759.0	759.3	759.0	761.0	761.7	763.4	765.3	768.2	772.5
40°	733.4	732.8	730.6	726.6	730.6	732.8	733.4	736.1	737.5	740.9	743.7
42.5°	706.1	703.9	702.9	701.6	702.9	703.9	706.1	707.8	708.6	713.1	718.5
45°	663.2	663.2	661.9	661.2	661.9	663.2	663.2	663.2	663.9	669.3	672.1
47.5°	621.5	622.7	625.3	624.9	625.3	622.7	621.5	620.4	620.7	623.4	626.5
50°	596.4	597.1	599.2	599.9	599.2	597.1	596.4	593.7	592.3	592.3	594.4
52.5°	568.6	572.6	575.1	574.7	575.1	572.6	568.6	566.4	564.0	560.7	563.8
55°	529.6	534.4	539.2	539.9	539.2	534.4	529.6	523.5	520.8	515.3	517.4
57.5°	491.0	497.7	502.7	504.4	502.7	497.7	491.0	483.6	474.8	472.2	468.4
60°	464.8	473.7	479.9	482.6	479.9	473.7	464.8	458.1	446.5	439.0	436.3
62.5°	439.8	449.7	455.9	456.4	455.9	449.7	439.8	429.1	417.6	409.0	403.5
65°	398.7	409.0	414.4	418.5	414.4	409.0	398.7	387.2	374.2	362.6	356.5
67.5°	354.6	364.8	370.8	374.1	370.8	364.8	354.6	340.2	328.4	315.1	307.8
70°	322.4	332.6	340.8	343.6	340.8	332.6	322.4	305.4	295.2	282.9	276.7
72.5°	290.7	299.9	306.5	309.7	306.5	299.9	290.7	274.8	263.0	250.6	242.4
75°	235.8	248.1	254.3	257.6	254.3	248.1	235.8	227.0	213.4	200.4	193.6
77.5°	181.9	193.0	196.7	198.4	196.7	193.0	181.9	171.5	161.2	151.7	145.0
80°	145.8	152.7	157.4	158.1	157.4	152.7	145.8	137.6	129.5	120.7	114.5
82.5°	112.1	117.8	119.3	121.1	119.3	117.8	112.1	104.9	97.9	91.2	86.1
85°	61.3	64.0	64.7	64.0	64.7	64.0	61.3	56.6	53.1	49.8	47.7
87.5°	22.7	22.1	22.3	23.3	22.3	22.1	22.7	21.6	21.9	20.7	19.5
90°	12.6	12.6	13.2	13.2	13.2	12.6	12.6	12.6	11.5	10.9	10.4
92.5°	39.9	38.5	37.7	36.8	37.7	38.5	39.9	47.3	55.7	74.1	102.1
95°	166.5	149.2	144.6	135.4	144.6	149.2	166.5	207.4	255.8	326.6	414.1
97.5°	383.5	351.2	334.6	327.2	334.6	351.2	383.5	419.1	486.5	555.4	616.8
100°	521.3	479.9	458.6	449.3	458.6	479.9	521.3	561.1	621.0	680.3	708.5
102.5°	645.3	615.8	592.7	585.7	592.7	615.8	645.3	687.8	728.3	756.8	739.4
105°	800.7	781.7	770.2	763.3	770.2	781.7	800.7	819.1	825.5	800.1	721.2
107.5°	866.1	866.0	862.1	857.5	862.1	866.0	866.1	856.7	826.7	761.5	656.2
110°	873.8	884.8	888.9	888.9	888.9	884.8	873.8	848.0	799.0	717.8	608.3



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	852.2	871.0	881.0	885.1	881.0	871.0	852.2	814.4	756.6	674.5	570.6
115°	799.0	826.7	842.7	850.3	842.7	826.7	799.0	754.1	691.3	612.4	523.0
117.5°	739.9	768.5	784.5	789.1	784.5	768.5	739.9	695.0	637.3	569.4	492.4
120°	701.7	729.3	744.9	749.4	744.9	729.3	701.7	659.0	608.3	544.9	475.8
122.5°	669.3	694.7	710.2	714.4	710.2	694.7	669.3	631.4	583.9	527.5	463.4
125°	627.9	651.6	664.2	669.9	664.2	651.6	627.9	595.6	554.2	504.0	445.2
127.5°	596.5	617.4	629.3	632.0	629.3	617.4	596.5	567.3	528.5	481.7	426.9
130°	577.2	596.2	607.7	611.2	607.7	596.2	577.2	548.4	511.0	466.1	415.4
132.5°	556.9	575.9	586.5	590.5	586.5	575.9	556.9	528.2	492.1	451.3	403.8
135°	523.6	542.6	553.0	556.4	553.0	542.6	523.6	498.3	465.4	428.6	388.8
137.5°	489.5	506.9	516.3	520.2	516.3	506.9	489.5	466.9	439.0	408.3	376.2
140°	468.4	483.3	491.9	494.8	491.9	483.3	468.4	447.1	422.8	396.4	369.2
142.5°	448.1	460.7	468.9	471.3	468.9	460.7	448.1	430.0	409.0	386.2	363.2
145°	420.5	430.3	436.7	439.0	436.7	430.3	420.5	406.7	391.1	373.2	355.5
147.5°	399.0	406.8	410.5	411.5	410.5	406.8	399.0	388.0	376.3	362.5	348.1
150°	386.6	393.4	395.8	396.4	395.8	393.4	386.6	377.9	367.5	356.6	343.9
152.5°	376.0	381.4	383.7	384.4	383.7	381.4	376.0	368.7	360.6	350.6	339.3
155°	361.7	365.8	367.5	368.1	367.5	365.8	361.7	356.0	349.6	341.6	332.3
157.5°	348.7	352.0	353.7	353.6	353.7	352.0	348.7	344.3	339.3	333.1	325.5
160°	340.4	343.4	344.5	343.9	344.5	343.4	340.4	336.4	332.3	326.6	320.8
162.5°	332.6	335.1	335.3	335.2	335.3	335.1	332.6	329.5	325.9	321.1	315.8
165°	321.4	322.6	322.6	322.6	322.6	322.6	321.4	319.1	316.3	312.8	308.7
167.5°	310.6	311.6	311.1	311.0	311.1	311.6	310.6	309.4	307.4	304.8	302.1
170°	304.2	304.8	304.8	304.2	304.8	304.8	304.2	303.0	301.8	300.1	298.4
172.5°	298.2	299.2	298.3	297.7	298.3	299.2	298.2	297.9	297.2	296.0	294.3
175°	290.9	291.4	290.3	289.7	290.3	291.4	290.9	290.9	290.9	289.7	289.7
177.5°	286.6	287.1	285.7	285.7	285.7	287.1	286.6	287.1	287.1	287.1	286.6
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1535.5	1542.1	1550.2	1556.2	1567.1	1572.1	1578.0	1583.0	1591.6	1599.8	1609.7
5°	1432.1	1443.6	1459.4	1476.3	1496.1	1509.7	1528.8	1540.4	1563.6	1584.8	1605.2
7.5°	1338.3	1352.4	1374.6	1396.4	1422.4	1445.8	1469.7	1496.1	1525.7	1560.6	1589.5
10°	1273.9	1293.0	1316.9	1344.1	1375.5	1402.7	1434.8	1463.4	1499.5	1540.4	1578.6
12.5°	1222.6	1239.0	1265.6	1291.8	1325.3	1358.6	1391.7	1429.6	1471.8	1517.0	1565.0
15°	1152.0	1165.6	1187.4	1223.5	1257.6	1290.3	1340.1	1375.5	1428.7	1479.0	1537.0
17.5°	1091.6	1108.4	1126.8	1157.8	1193.1	1234.0	1278.4	1322.8	1374.1	1438.0	1503.4
20°	1054.4	1068.0	1089.2	1113.1	1150.5	1191.4	1233.8	1278.7	1341.4	1407.5	1477.7
22.5°	1014.1	1028.9	1052.7	1078.7	1110.2	1149.4	1196.1	1245.5	1310.9	1375.9	1452.1
25°	966.5	976.7	998.6	1021.8	1053.1	1086.5	1134.9	1189.4	1254.2	1328.5	1406.1
27.5°	921.7	930.7	950.6	970.8	999.1	1038.7	1082.0	1137.1	1198.1	1273.3	1359.6
30°	889.5	899.1	916.8	938.6	965.8	1000.6	1044.9	1096.7	1162.2	1235.8	1325.8
32.5°	861.7	870.1	883.5	905.3	932.0	965.7	1006.7	1059.7	1125.1	1199.7	1288.1
35°	818.6	828.2	838.4	855.5	878.6	911.3	956.3	1006.0	1068.7	1141.0	1222.1
37.5°	775.8	786.2	795.3	810.6	831.7	860.6	899.5	951.3	1007.9	1077.6	1155.5
40°	749.1	757.3	764.8	781.1	802.2	829.5	865.7	912.0	972.0	1036.7	1101.5
42.5°	722.4	730.0	736.4	750.6	770.1	796.3	830.7	876.0	931.6	992.0	1049.1
45°	680.2	685.0	692.5	704.8	720.4	744.3	777.7	817.9	864.9	922.2	965.1
47.5°	634.7	642.2	648.3	659.1	672.0	695.4	727.4	761.6	804.3	846.9	877.1
50°	599.9	607.3	616.2	626.4	638.6	660.5	689.8	724.6	760.6	793.3	819.3
52.5°	567.1	574.0	583.5	593.1	608.1	626.6	651.7	682.6	718.1	741.5	763.2
55°	518.7	522.1	533.0	542.6	556.8	570.5	595.7	623.0	644.8	662.6	680.2
57.5°	469.2	473.8	480.1	488.7	502.9	518.9	536.5	560.7	573.5	582.6	596.4
60°	437.6	439.0	443.0	453.2	464.1	478.5	499.0	515.9	525.5	533.0	544.6
62.5°	402.7	402.9	409.8	417.3	425.5	440.9	457.5	471.3	479.2	482.8	493.9
65°	353.8	352.3	356.5	362.6	372.1	382.3	396.7	409.0	408.3	412.3	419.2
67.5°	303.8	302.4	302.4	308.2	316.0	325.2	335.0	342.0	342.1	347.6	351.0
70°	269.9	265.8	268.5	273.4	276.7	284.3	295.2	297.9	298.5	301.2	304.7
72.5°	235.0	233.7	235.8	237.9	240.2	246.1	255.3	257.0	257.1	258.7	264.3
75°	186.7	185.4	184.0	186.1	188.8	192.9	196.3	199.0	198.3	199.0	203.1
77.5°	140.0	136.2	135.5	136.6	137.2	139.8	143.3	143.0	143.7	143.5	148.1
80°	111.1	105.6	104.9	104.9	105.6	107.0	108.4	109.8	107.7	109.8	111.1
82.5°	81.7	78.4	78.3	77.7	77.9	78.1	79.0	79.8	79.4	80.3	81.1
85°	44.9	43.6	41.6	42.9	42.2	40.2	41.6	39.5	38.9	39.5	40.2
87.5°	17.3	17.7	16.4	16.3	15.5	15.9	14.5	13.7	13.0	13.3	14.8
90°	9.8	9.2	8.1	7.5	6.4	5.8	4.6	3.4	2.3	1.1	0.6
92.5°	150.4	185.7	188.7	131.5	78.7	47.3	30.4	20.5	13.3	8.5	7.1
95°	499.5	510.4	416.5	257.5	130.8	69.2	43.2	30.5	24.2	19.6	19.0
97.5°	632.0	545.0	371.9	205.5	112.7	71.9	53.2	41.8	35.4	32.2	31.6
100°	664.2	520.2	331.8	186.6	111.8	78.4	61.1	50.1	43.8	41.5	40.3
102.5°	644.8	476.4	301.3	178.8	115.9	86.1	69.4	59.4	52.5	50.7	50.0
105°	583.0	417.7	271.9	175.7	124.4	99.1	82.9	73.7	68.0	65.1	65.1
107.5°	519.9	377.2	259.4	181.0	137.1	112.6	98.1	88.5	83.7	81.0	79.9
110°	483.9	358.3	255.8	186.0	146.3	122.7	107.8	99.1	93.9	91.6	90.5



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.2	347.3	255.8	192.5	155.1	132.4	117.9	109.3	104.0	102.2	101.1
115°	428.0	335.3	257.5	202.2	168.7	147.4	133.1	124.4	119.3	117.5	116.3
117.5°	410.6	329.4	261.3	213.3	182.9	162.7	148.8	139.0	133.8	131.9	130.2
120°	400.9	326.6	265.0	220.7	193.0	172.8	158.4	148.7	143.4	141.2	139.4
122.5°	392.6	324.4	268.2	228.9	202.7	182.5	168.1	157.3	152.2	150.4	149.1
125°	381.3	321.4	273.7	240.2	215.4	196.4	181.5	170.5	165.3	162.5	161.3
127.5°	371.0	320.0	279.7	250.5	227.7	209.4	194.5	182.9	176.3	172.6	170.9
130°	364.1	319.1	283.5	257.5	235.6	217.7	202.8	190.7	183.2	178.5	176.8
132.5°	358.5	319.1	287.6	263.5	243.0	225.1	210.2	197.6	189.1	183.7	181.5
135°	351.9	319.1	293.2	271.9	252.9	235.0	219.4	207.4	198.1	191.3	188.9
137.5°	346.1	319.8	298.4	278.1	259.9	243.7	227.6	215.8	206.6	200.2	198.4
140°	343.4	320.3	300.7	282.3	265.0	248.3	232.8	221.8	212.6	205.6	203.9
142.5°	341.0	320.7	302.1	284.6	268.2	252.5	237.8	227.3	218.1	211.7	210.4
145°	337.6	320.3	303.6	288.0	273.7	258.6	245.4	235.0	226.9	221.2	220.0
147.5°	334.0	318.8	304.2	290.1	277.1	264.0	252.3	243.3	235.8	230.9	230.1
150°	331.2	317.4	304.2	291.4	279.4	266.7	256.9	248.8	241.4	237.3	236.2
152.5°	328.0	315.6	303.7	292.4	281.7	269.9	261.1	253.5	246.9	243.3	242.7
155°	322.6	312.3	302.5	293.2	284.0	274.2	266.1	260.3	254.6	251.2	251.2
157.5°	317.5	308.7	300.9	293.8	286.0	277.5	271.5	266.4	261.5	258.6	258.7
160°	313.4	306.5	299.5	293.8	286.9	279.4	274.2	269.6	265.6	263.3	263.9
162.5°	309.7	303.7	298.2	293.4	287.8	281.2	277.0	273.3	269.7	267.4	268.0
165°	304.2	299.5	296.1	292.7	288.0	283.5	279.9	277.6	274.8	273.1	274.2
167.5°	298.7	295.5	292.9	291.2	288.0	284.2	282.1	280.4	278.8	277.8	278.3
170°	295.5	293.2	291.4	290.3	288.0	285.2	283.5	282.3	281.1	280.5	281.1
172.5°	292.3	290.4	289.6	289.4	287.6	285.2	284.4	283.7	282.5	282.0	283.0
175°	288.0	287.4	287.4	288.0	286.9	285.2	285.2	285.2	284.6	284.0	285.2
177.5°	286.2	285.7	285.7	286.6	286.2	285.3	285.3	285.7	285.3	285.3	286.2
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1614.6	1622.2	1627.1	1636.4	1644.1	1648.4	1652.2	1655.5	1659.3	1662.5	1671.8
5°	1625.0	1642.6	1657.7	1680.8	1702.0	1718.4	1736.1	1751.7	1764.6	1783.1	1797.4
7.5°	1620.4	1651.9	1685.0	1720.8	1757.5	1791.5	1822.9	1852.2	1878.8	1911.0	1939.1
10°	1616.1	1659.0	1701.3	1749.7	1799.5	1841.7	1881.3	1921.5	1950.8	1991.7	2026.4
12.5°	1612.9	1663.3	1714.3	1772.6	1827.2	1886.9	1939.5	1968.9	2013.5	2046.2	2087.5
15°	1599.0	1665.9	1736.1	1801.5	1879.2	1934.4	1980.7	2038.0	2079.6	2121.1	2166.2
17.5°	1574.4	1650.0	1728.6	1814.3	1888.9	1948.1	2007.9	2063.1	2112.7	2168.5	2224.5
20°	1563.0	1638.6	1728.6	1816.4	1889.5	1951.5	2012.8	2073.5	2128.0	2199.6	2264.3
22.5°	1538.9	1630.4	1713.3	1799.1	1874.1	1941.7	2011.1	2080.0	2152.5	2233.3	2314.5
25°	1496.1	1588.8	1676.8	1761.3	1836.9	1921.5	1995.8	2087.8	2180.5	2287.4	2388.3
27.5°	1451.7	1540.4	1621.0	1702.6	1790.9	1886.5	1983.0	2087.4	2208.7	2343.8	2486.1
30°	1415.7	1499.5	1577.9	1661.7	1753.7	1861.5	1967.1	2091.1	2231.6	2383.6	2552.6
32.5°	1373.7	1451.0	1527.2	1616.0	1716.2	1829.9	1953.0	2089.0	2257.8	2430.4	2604.4
35°	1301.9	1366.7	1445.0	1539.7	1652.9	1783.1	1925.5	2086.4	2280.0	2478.3	2624.8
37.5°	1216.7	1277.0	1359.6	1463.4	1582.1	1721.7	1890.8	2081.6	2287.2	2445.4	2492.6
40°	1159.4	1215.3	1301.2	1408.9	1530.2	1678.1	1863.5	2065.3	2264.3	2365.2	2326.3
42.5°	1098.3	1157.0	1240.6	1347.3	1477.8	1638.9	1829.2	2030.9	2197.8	2235.9	2101.6
45°	1002.0	1062.6	1145.1	1252.8	1393.2	1567.7	1766.1	1949.4	2045.5	1976.7	1768.8
47.5°	912.4	969.3	1045.7	1156.8	1301.7	1482.2	1673.2	1819.5	1827.1	1662.8	1440.8
50°	851.3	903.8	980.9	1092.0	1235.8	1418.5	1590.8	1706.1	1654.3	1468.1	1254.9
52.5°	791.3	842.7	918.7	1028.6	1170.8	1338.3	1498.7	1579.5	1482.0	1291.0	1108.7
55°	704.8	749.7	824.0	925.6	1060.6	1216.0	1352.3	1380.3	1253.4	1065.3	917.5
57.5°	620.3	662.3	729.8	823.3	946.7	1084.4	1191.0	1185.1	1051.1	889.6	772.2
60°	563.0	603.9	663.9	755.2	867.7	986.3	1077.6	1055.8	922.9	783.9	685.0
62.5°	511.8	548.3	605.0	684.9	787.5	897.4	972.4	940.2	810.0	688.4	610.4
65°	436.3	466.9	515.3	583.5	668.6	759.3	817.3	775.7	664.6	569.9	507.2
67.5°	364.2	388.7	429.3	483.6	556.3	629.1	664.4	622.6	533.7	464.5	418.1
70°	318.3	340.1	371.4	419.9	483.2	544.6	571.2	533.7	457.4	398.1	364.7
72.5°	272.5	290.5	318.0	361.5	412.3	465.5	488.9	453.0	390.3	340.2	309.0
75°	210.7	222.9	242.0	272.0	312.1	354.5	367.4	336.1	295.8	258.3	237.9
77.5°	150.8	161.2	175.6	194.5	223.0	249.8	261.2	243.1	212.0	188.2	171.5
80°	115.8	121.3	133.6	149.3	171.8	188.8	196.3	184.7	162.9	145.2	132.2
82.5°	82.6	88.1	95.4	108.4	122.7	134.3	142.3	134.5	118.8	104.8	97.4
85°	40.2	43.6	47.7	53.1	64.0	70.9	70.2	65.4	59.3	53.8	49.8
87.5°	14.4	15.1	17.1	20.0	21.9	24.1	25.4	24.5	22.5	21.0	19.5
90°	1.1	2.3	3.4	4.6	5.8	6.4	7.5	8.1	9.2	9.8	10.4
92.5°	8.5	13.3	20.5	30.4	47.3	78.7	131.5	188.7	185.7	150.4	102.1
95°	19.6	24.2	30.5	43.2	69.2	130.8	257.5	416.5	510.4	499.5	414.1
97.5°	32.2	35.4	41.8	53.2	71.9	112.7	205.5	371.9	545.0	632.0	616.8
100°	41.5	43.8	50.1	61.1	78.4	111.8	186.6	331.8	520.2	664.2	708.5
102.5°	50.7	52.5	59.4	69.4	86.1	115.9	178.8	301.3	476.4	644.8	739.4
105°	65.1	68.0	73.7	82.9	99.1	124.4	175.7	271.9	417.7	583.0	721.2
107.5°	81.0	83.7	88.5	98.1	112.6	137.1	181.0	259.4	377.2	519.9	656.2
110°	91.6	93.9	99.1	107.8	122.7	146.3	186.0	255.8	358.3	483.9	608.3



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	102.2	104.0	109.3	117.9	132.4	155.1	192.5	255.8	347.3	457.2	570.6
115°	117.5	119.3	124.4	133.1	147.4	168.7	202.2	257.5	335.3	428.0	523.0
117.5°	131.9	133.8	139.0	148.8	162.7	182.9	213.3	261.3	329.4	410.6	492.4
120°	141.2	143.4	148.7	158.4	172.8	193.0	220.7	265.0	326.6	400.9	475.8
122.5°	150.4	152.2	157.3	168.1	182.5	202.7	228.9	268.2	324.4	392.6	463.4
125°	162.5	165.3	170.5	181.5	196.4	215.4	240.2	273.7	321.4	381.3	445.2
127.5°	172.6	176.3	182.9	194.5	209.4	227.7	250.5	279.7	320.0	371.0	426.9
130°	178.5	183.2	190.7	202.8	217.7	235.6	257.5	283.5	319.1	364.1	415.4
132.5°	183.7	189.1	197.6	210.2	225.1	243.0	263.5	287.6	319.1	358.5	403.8
135°	191.3	198.1	207.4	219.4	235.0	252.9	271.9	293.2	319.1	351.9	388.8
137.5°	200.2	206.6	215.8	227.6	243.7	259.9	278.1	298.4	319.8	346.1	376.2
140°	205.6	212.6	221.8	232.8	248.3	265.0	282.3	300.7	320.3	343.4	369.2
142.5°	211.7	218.1	227.3	237.8	252.5	268.2	284.6	302.1	320.7	341.0	363.2
145°	221.2	226.9	235.0	245.4	258.6	273.7	288.0	303.6	320.3	337.6	355.5
147.5°	230.9	235.8	243.3	252.3	264.0	277.1	290.1	304.2	318.8	334.0	348.1
150°	237.3	241.4	248.8	256.9	266.7	279.4	291.4	304.2	317.4	331.2	343.9
152.5°	243.3	246.9	253.5	261.1	269.9	281.7	292.4	303.7	315.6	328.0	339.3
155°	251.2	254.6	260.3	266.1	274.2	284.0	293.2	302.5	312.3	322.6	332.3
157.5°	258.6	261.5	266.4	271.5	277.5	286.0	293.8	300.9	308.7	317.5	325.5
160°	263.3	265.6	269.6	274.2	279.4	286.9	293.8	299.5	306.5	313.4	320.8
162.5°	267.4	269.7	273.3	277.0	281.2	287.8	293.4	298.2	303.7	309.7	315.8
165°	273.1	274.8	277.6	279.9	283.5	288.0	292.7	296.1	299.5	304.2	308.7
167.5°	277.8	278.8	280.4	282.1	284.2	288.0	291.2	292.9	295.5	298.7	302.1
170°	280.5	281.1	282.3	283.5	285.2	288.0	290.3	291.4	293.2	295.5	298.4
172.5°	282.0	282.5	283.7	284.4	285.2	287.6	289.4	289.6	290.4	292.3	294.3
175°	284.0	284.6	285.2	285.2	285.2	286.9	288.0	287.4	287.4	288.0	289.7
177.5°	285.3	285.3	285.7	285.3	285.3	286.2	286.6	285.7	285.7	286.2	286.6
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1679.5	1683.8	1693.1	1689.8	1694.3	1696.4	1698.6
5°	1815.1	1836.9	1846.4	1845.1	1859.5	1856.0	1852.6
7.5°	1968.3	1991.3	2004.1	2020.0	2029.3	2029.9	2038.0
10°	2055.1	2085.1	2097.3	2114.4	2125.3	2131.4	2130.7
12.5°	2121.6	2145.1	2172.5	2180.9	2195.6	2203.3	2200.5
15°	2201.6	2239.1	2267.8	2282.0	2300.5	2305.9	2313.4
17.5°	2273.0	2323.3	2356.7	2401.2	2417.9	2428.1	2422.2
20°	2327.0	2393.2	2426.5	2479.7	2509.0	2524.7	2519.2
22.5°	2390.9	2462.4	2524.2	2570.2	2614.7	2635.9	2640.3
25°	2500.1	2598.3	2689.0	2749.7	2804.8	2817.7	2846.4
27.5°	2622.3	2738.0	2835.0	2898.7	2937.2	2951.6	2960.6
30°	2699.2	2814.4	2887.3	2928.2	2940.4	2939.1	2937.7
32.5°	2736.8	2808.9	2823.0	2811.5	2783.4	2759.7	2734.9
35°	2683.5	2629.7	2549.2	2445.6	2369.2	2292.3	2284.7
37.5°	2413.5	2241.3	2107.4	1957.8	1871.6	1818.3	1781.5
40°	2159.3	1963.7	1801.5	1675.4	1587.5	1552.7	1518.6
42.5°	1883.4	1696.6	1552.9	1447.4	1381.4	1342.8	1315.8
45°	1530.2	1365.2	1252.8	1176.5	1124.0	1094.0	1076.9
47.5°	1253.8	1131.9	1036.3	981.3	945.0	921.7	921.8
50°	1105.6	989.1	925.6	882.0	850.6	832.2	835.7
52.5°	974.1	887.1	832.9	796.4	773.3	761.9	761.5
55°	814.6	751.8	716.4	689.8	674.1	661.2	663.9
57.5°	696.7	643.9	620.2	598.0	587.1	582.0	574.4
60°	623.7	582.8	562.3	544.6	533.7	529.6	522.1
62.5°	558.8	526.6	506.8	492.2	482.4	481.1	475.2
65°	469.6	445.0	427.4	420.5	410.3	407.6	407.6
67.5°	387.2	369.6	355.8	349.5	345.1	345.7	342.4
70°	335.4	321.0	312.1	305.4	301.9	302.7	299.9
72.5°	293.4	277.4	269.6	265.6	261.1	262.9	261.8
75°	222.2	214.0	210.0	205.8	203.1	201.8	200.4
77.5°	163.2	155.9	152.8	150.5	150.9	147.6	150.3
80°	126.1	120.0	118.0	114.5	113.8	113.8	113.1
82.5°	92.3	88.9	87.4	84.5	83.3	84.4	82.6
85°	47.7	44.9	44.3	44.3	42.9	41.6	44.9
87.5°	19.6	17.6	17.8	17.3	17.3	16.9	15.8
90°	10.9	11.5	12.6	12.6	12.6	13.2	13.2
92.5°	74.1	55.7	47.3	39.9	38.5	37.7	36.8
95°	326.6	255.8	207.4	166.5	149.2	144.6	135.4
97.5°	555.4	486.5	419.1	383.5	351.2	334.6	327.2
100°	680.3	621.0	561.1	521.3	479.9	458.6	449.3
102.5°	756.8	728.3	687.8	645.3	615.8	592.7	585.7
105°	800.1	825.5	819.1	800.7	781.7	770.2	763.3
107.5°	761.5	826.7	856.7	866.1	866.0	862.1	857.5
110°	717.8	799.0	848.0	873.8	884.8	888.9	888.9



TEST NUMBER: P333261-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	674.5	756.6	814.4	852.2	871.0	881.0	885.1
115°	612.4	691.3	754.1	799.0	826.7	842.7	850.3
117.5°	569.4	637.3	695.0	739.9	768.5	784.5	789.1
120°	544.9	608.3	659.0	701.7	729.3	744.9	749.4
122.5°	527.5	583.9	631.4	669.3	694.7	710.2	714.4
125°	504.0	554.2	595.6	627.9	651.6	664.2	669.9
127.5°	481.7	528.5	567.3	596.5	617.4	629.3	632.0
130°	466.1	511.0	548.4	577.2	596.2	607.7	611.2
132.5°	451.3	492.1	528.2	556.9	575.9	586.5	590.5
135°	428.6	465.4	498.3	523.6	542.6	553.0	556.4
137.5°	408.3	439.0	466.9	489.5	506.9	516.3	520.2
140°	396.4	422.8	447.1	468.4	483.3	491.9	494.8
142.5°	386.2	409.0	430.0	448.1	460.7	468.9	471.3
145°	373.2	391.1	406.7	420.5	430.3	436.7	439.0
147.5°	362.5	376.3	388.0	399.0	406.8	410.5	411.5
150°	356.6	367.5	377.9	386.6	393.4	395.8	396.4
152.5°	350.6	360.6	368.7	376.0	381.4	383.7	384.4
155°	341.6	349.6	356.0	361.7	365.8	367.5	368.1
157.5°	333.1	339.3	344.3	348.7	352.0	353.7	353.6
160°	326.6	332.3	336.4	340.4	343.4	344.5	343.9
162.5°	321.1	325.9	329.5	332.6	335.1	335.3	335.2
165°	312.8	316.3	319.1	321.4	322.6	322.6	322.6
167.5°	304.8	307.4	309.4	310.6	311.6	311.1	311.0
170°	300.1	301.8	303.0	304.2	304.8	304.8	304.2
172.5°	296.0	297.2	297.9	298.2	299.2	298.3	297.7
175°	289.7	290.9	290.9	290.9	291.4	290.3	289.7
177.5°	287.1	287.1	287.1	286.6	287.1	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7

(END OF REPORT)