

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333627-830

Luminaire Tested: **S125RDIP-S1270D810U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333627-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D810U830-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7339.8 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333627-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333627-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	94	91	87	84	80	77	75	70	68	66	60	59	58	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	56	53	51	49	45
3	84	75	67	61	79	70	64	59	62	57	53	55	51	47	48	45	42	38
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	43	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	29
6	66	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	26
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	30	26	23	20
9	53	40	33	28	49	38	31	27	34	29	25	31	26	22	27	23	21	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333627-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.0	2.5
10°-20°	511.3	7.0
20°-30°	741.4	10.1
30°-40°	845.0	11.5
40°-50°	823.6	11.2
50°-60°	693.3	9.4
60°-70°	486.0	6.6
70°-80°	249.8	3.4
80°-90°	65.1	0.9
90°-100°	264.9	3.6
100°-110°	569.6	7.8
110°-120°	534.5	7.3
120°-130°	433.2	5.9
130°-140°	347.7	4.7
140°-150°	262.4	3.6
150°-160°	184.7	2.5
160°-170°	108.8	1.5
170°-180°	35.4	0.5
0°-30°	1435.7	19.6
0°-40°	2280.6	31.1
0°-60°	3797.6	51.7
0°-90°	4598.6	62.7
90°-120°	1369.1	18.7
90°-150°	2412.3	32.9
90°-180°	2741.0	37.3
0°-180°	7339.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	1	7	12	15	17	5
95°	24	72	653	296	173	26
105°	83	116	534	1052	976	88
115°	149	179	429	925	1088	146
125°	206	242	411	736	857	183
135°	242	291	408	616	712	188
145°	282	322	410	510	562	176
155°	321	346	399	451	471	148
165°	351	360	383	406	413	99
175°	365	365	368	372	371	35
180°	366	366	366	366	366	



TEST NUMBER: P333627-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.1	25.5	23.9	22.4	20.9	20.2	20.1	20.1	20.0	20.0	20.2
90°	0.8	1.5	2.9	4.4	5.9	7.4	8.1	9.6	10.3	11.8	12.5
92.5°	9.0	10.9	17.1	26.2	38.9	60.4	100.7	168.1	241.4	237.6	192.4
95°	24.3	25.1	30.9	39.0	55.2	88.4	167.3	329.4	532.8	653.0	638.9
97.5°	40.3	41.3	45.4	53.5	68.1	92.0	144.1	263.0	475.8	697.3	808.4
100°	51.6	53.1	56.0	64.1	78.1	100.2	143.0	238.7	424.5	665.5	849.7
102.5°	64.0	64.8	67.2	75.9	88.7	110.3	148.3	228.8	385.6	609.4	825.0
105°	83.3	83.3	87.0	94.3	106.1	126.8	159.2	224.8	347.9	534.3	745.8
107.5°	102.2	103.6	107.2	113.2	125.5	144.0	175.4	231.6	332.0	482.6	665.1
110°	115.7	117.2	120.1	126.8	137.8	156.9	187.2	238.1	327.3	458.4	619.1



TEST NUMBER: P333627-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	129.2	130.7	133.1	139.7	150.8	169.4	198.4	246.3	327.3	444.2	584.8
115°	148.8	150.3	152.6	159.2	170.2	188.7	215.9	258.6	329.4	429.0	547.5
117.5°	166.5	168.8	171.2	177.8	190.3	208.1	233.9	272.9	334.3	421.4	525.3
120°	178.3	180.6	183.5	190.1	202.6	221.1	246.9	282.3	339.0	417.8	512.9
122.5°	190.8	192.4	194.7	201.3	215.1	233.5	259.3	292.8	343.1	414.9	502.3
125°	206.3	207.8	211.5	218.1	232.1	251.3	275.6	307.3	350.1	411.2	487.9
127.5°	218.6	220.8	225.6	233.9	248.8	268.0	291.4	320.6	357.9	409.4	474.6
130°	226.2	228.5	234.3	243.9	259.4	278.6	301.4	329.4	362.6	408.3	465.8
132.5°	232.1	235.0	242.0	252.8	268.8	288.0	310.9	337.1	367.9	408.3	458.7
135°	241.8	244.7	253.5	265.3	280.8	300.7	323.6	347.9	375.1	408.3	450.3
137.5°	253.8	256.0	264.3	276.1	291.2	311.7	332.5	355.8	381.7	409.2	442.8
140°	260.9	263.1	271.9	283.7	297.7	317.6	339.0	361.1	384.7	409.7	439.2
142.5°	269.1	270.8	279.0	290.8	304.3	322.9	343.1	364.1	386.4	410.4	436.3
145°	281.5	283.0	290.4	300.7	314.0	330.9	350.1	368.4	388.4	409.7	431.9
147.5°	294.5	295.4	301.7	311.3	322.8	337.7	354.5	371.2	389.1	407.8	427.3
150°	302.2	303.6	308.8	318.4	328.7	341.2	357.4	372.9	389.1	406.0	423.8
152.5°	310.4	311.3	315.8	324.2	334.0	345.3	360.3	374.1	388.5	403.7	419.6
155°	321.3	321.3	325.7	333.1	340.4	350.8	363.4	375.1	386.9	399.4	412.7
157.5°	331.0	330.9	334.4	340.7	347.2	355.1	365.8	375.9	385.0	395.0	406.2
160°	337.5	336.8	339.8	344.9	350.8	357.4	367.0	375.9	383.2	392.1	401.0
162.5°	342.8	342.1	345.1	349.6	354.3	359.8	368.2	375.2	381.4	388.5	396.2
165°	350.8	349.3	351.6	355.2	358.2	362.6	368.4	374.4	378.8	383.2	389.1
167.5°	356.1	355.3	356.7	358.7	360.8	363.6	368.4	372.6	374.7	378.1	382.2
170°	359.7	358.9	359.7	361.1	362.6	364.8	368.4	371.5	372.9	375.1	378.1
172.5°	362.0	360.7	361.4	362.9	363.7	364.8	367.9	370.2	370.5	371.6	373.9
175°	364.8	363.4	364.1	364.8	364.8	364.8	367.0	368.4	367.8	367.8	368.4
177.5°	366.1	365.0	365.0	365.5	365.0	365.0	366.1	366.7	365.5	365.5	366.1
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333627-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	20.3	20.5	20.5	20.7	20.5	20.3	20.1	19.9
90°	13.3	14.0	14.7	16.2	16.2	16.2	17.0	17.0
92.5°	130.6	94.8	71.4	60.4	51.0	49.2	48.2	47.0
95°	529.9	417.8	327.3	265.3	213.0	190.9	185.0	173.1
97.5°	789.2	710.6	622.3	536.2	490.7	449.4	428.0	418.6
100°	906.4	870.3	794.5	717.8	666.9	613.9	586.6	574.9
102.5°	945.9	968.3	931.8	880.0	825.6	787.8	758.2	749.3
105°	922.7	1023.7	1056.1	1048.0	1024.4	1000.0	985.3	976.5
107.5°	839.5	974.3	1057.5	1096.0	1108.0	1107.8	1103.0	1097.0
110°	778.3	918.2	1022.2	1084.8	1117.9	1132.0	1137.2	1137.2





TEST NUMBER: P333627-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	729.9	862.8	967.9	1041.8	1090.2	1114.3	1127.1	1132.5
115°	669.2	783.4	884.4	964.7	1022.2	1057.5	1078.2	1087.8
117.5°	630.0	728.4	815.4	889.1	946.6	983.1	1003.6	1009.5
120°	608.7	697.2	778.3	843.1	897.6	933.0	952.9	958.8
122.5°	592.9	674.8	747.0	807.8	856.4	888.8	908.7	914.0
125°	569.7	644.9	709.0	762.0	803.3	833.5	849.7	857.1
127.5°	546.1	616.2	676.1	725.8	763.2	789.9	805.2	808.4
130°	531.3	596.3	653.7	701.6	738.5	762.8	777.5	781.9
132.5°	516.6	577.3	629.5	675.6	712.5	736.8	750.4	755.4
135°	497.5	548.3	595.5	637.4	669.9	694.2	707.5	711.9
137.5°	481.3	522.4	561.6	597.2	626.3	648.4	660.6	665.5
140°	472.4	507.0	540.9	571.8	599.2	618.3	629.3	633.0
142.5°	464.8	494.1	523.2	550.1	573.3	589.5	599.9	602.9
145°	454.7	477.6	500.4	520.3	538.0	550.5	558.6	561.6
147.5°	445.3	463.8	481.4	496.4	510.4	520.5	525.2	526.5
150°	440.0	456.2	470.1	483.4	494.6	503.3	506.3	507.0
152.5°	434.0	448.6	461.4	471.6	481.0	488.0	491.0	491.7
155°	425.3	437.1	447.3	455.4	462.8	468.0	470.1	470.9
157.5°	416.4	426.1	434.0	440.5	446.2	450.4	452.5	452.3
160°	410.5	417.8	425.3	430.4	435.5	439.2	440.7	440.0
162.5°	404.0	410.8	417.0	421.5	425.6	428.6	429.0	428.8
165°	395.0	400.2	404.6	408.3	411.2	412.7	412.7	412.7
167.5°	386.4	389.8	393.2	395.9	397.4	398.7	398.1	397.9
170°	381.7	384.0	386.2	387.7	389.1	389.8	389.8	389.1
172.5°	376.5	378.6	380.3	381.2	381.4	382.8	381.6	380.9
175°	370.7	370.7	372.2	372.2	372.2	372.9	371.5	370.7
177.5°	366.7	367.3	367.3	367.3	366.7	367.3	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5

(END OF REPORT)