

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333270-840

Luminaire Tested: **S125DIP-S1090D810U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333270-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D810U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7470.7 lumens
Efficiency: N/A
Efficacy: 137.3 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	46	46	43	41	37
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	43	36	30	52	41	34	29	37	31	27	32	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	36	29	24	46	35	28	23	31	25	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10371	10371	10371	10371
5°	12010	10407	9111	10407
10°	13973	10352	7984	10352
15°	15468	10277	7365	10277
20°	17314	10156	6868	10156
25°	20283	10020	6625	10020
30°	21908	9887	6415	9887
35°	18013	9635	6277	9635
40°	12803	9286	6126	9286
45°	9836	8815	6039	8815
50°	8397	8232	6027	8232
55°	7475	7659	6079	7659
60°	6744	7034	6234	7034
65°	6229	6406	6395	6406
70°	5663	5754	6488	5754
75°	5001	5068	6428	5068
80°	4206	4132	5880	4132
85°	3327	2979	4742	2979



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.6	2.1
10°-20°	460.3	6.2
20°-30°	747.4	10.0
30°-40°	911.7	12.2
40°-50°	829.4	11.1
50°-60°	660.6	8.8
60°-70°	460.1	6.2
70°-80°	245.4	3.3
80°-90°	64.1	0.9
90°-100°	283.9	3.8
100°-110°	610.3	8.2
110°-120°	572.7	7.7
120°-130°	464.2	6.2
130°-140°	372.5	5.0
140°-150°	281.1	3.8
150°-160°	197.9	2.6
160°-170°	116.6	1.6
170°-180°	37.9	0.5
0°-30°	1362.3	18.2
0°-40°	2274.0	30.4
0°-60°	3764.0	50.4
0°-90°	4533.6	60.7
90°-120°	1466.9	19.6
90°-150°	2584.6	34.6
90°-180°	2937.0	39.3
0°-180°	7470.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1606	1606	1606	1606	1606	
5°	1853	1605	1405	1605	1853	187
15°	2313	1537	1102	1537	2313	662
25°	2846	1406	930	1406	2846	1300
35°	2285	1222	796	1222	2285	1398
45°	1077	965	661	965	1077	862
55°	664	680	540	680	664	598
65°	408	419	418	419	408	405
75°	200	203	258	203	200	216
85°	45	40	64	40	45	52
90°	18	1	18	1	18	14
95°	186	26	186	26	186	263
105°	1046	89	1046	89	1046	1040
115°	1166	160	1166	160	1166	1139
125°	918	221	918	221	918	831
135°	763	259	763	259	763	591
145°	602	302	602	302	602	382
155°	504	344	504	344	504	235
165°	442	376	442	376	442	126
175°	397	391	397	391	397	39
180°	392	392	392	392	392	



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1698.6	1696.4	1694.3	1689.8	1693.1	1683.8	1679.5	1671.8	1662.5	1659.3	1655.5
5°	1852.6	1856.0	1859.5	1845.1	1846.4	1836.9	1815.1	1797.4	1783.1	1764.6	1751.7
7.5°	2038.0	2029.9	2029.3	2020.0	2004.1	1991.3	1968.3	1939.1	1911.0	1878.8	1852.2
10°	2130.7	2131.4	2125.3	2114.4	2097.3	2085.1	2055.1	2026.4	1991.7	1950.8	1921.5
12.5°	2200.5	2203.3	2195.6	2180.9	2172.5	2145.1	2121.6	2087.5	2046.2	2013.5	1968.9
15°	2313.4	2305.9	2300.5	2282.0	2267.8	2239.1	2201.6	2166.2	2121.1	2079.6	2038.0
17.5°	2422.2	2428.1	2417.9	2401.2	2356.7	2323.3	2273.0	2224.5	2168.5	2112.7	2063.1
20°	2519.2	2524.7	2509.0	2479.7	2426.5	2393.2	2327.0	2264.3	2199.6	2128.0	2073.5
22.5°	2640.3	2635.9	2614.7	2570.2	2524.2	2462.4	2390.9	2314.5	2233.3	2152.5	2080.0
25°	2846.4	2817.7	2804.8	2749.7	2689.0	2598.3	2500.1	2388.3	2287.4	2180.5	2087.8
27.5°	2960.6	2951.6	2937.2	2898.7	2835.0	2738.0	2622.3	2486.1	2343.8	2208.7	2087.4
30°	2937.7	2939.1	2940.4	2928.2	2887.3	2814.4	2699.2	2552.6	2383.6	2231.6	2091.1
32.5°	2734.9	2759.7	2783.4	2811.5	2823.0	2808.9	2736.8	2604.4	2430.4	2257.8	2089.0
35°	2284.7	2292.3	2369.2	2445.6	2549.2	2629.7	2683.5	2624.8	2478.3	2280.0	2086.4
37.5°	1781.5	1818.3	1871.6	1957.8	2107.4	2241.3	2413.5	2492.6	2445.4	2287.2	2081.6
40°	1518.6	1552.7	1587.5	1675.4	1801.5	1963.7	2159.3	2326.3	2365.2	2264.3	2065.3
42.5°	1315.8	1342.8	1381.4	1447.4	1552.9	1696.6	1883.4	2101.6	2235.9	2197.8	2030.9
45°	1076.9	1094.0	1124.0	1176.5	1252.8	1365.2	1530.2	1768.8	1976.7	2045.5	1949.4
47.5°	921.8	921.7	945.0	981.3	1036.3	1131.9	1253.8	1440.8	1662.8	1827.1	1819.5
50°	835.7	832.2	850.6	882.0	925.6	989.1	1105.6	1254.9	1468.1	1654.3	1706.1
52.5°	761.5	761.9	773.3	796.4	832.9	887.1	974.1	1108.7	1291.0	1482.0	1579.5
55°	663.9	661.2	674.1	689.8	716.4	751.8	814.6	917.5	1065.3	1253.4	1380.3
57.5°	574.4	582.0	587.1	598.0	620.2	643.9	696.7	772.2	889.6	1051.1	1185.1
60°	522.1	529.6	533.7	544.6	562.3	582.8	623.7	685.0	783.9	922.9	1055.8
62.5°	475.2	481.1	482.4	492.2	506.8	526.6	558.8	610.4	688.4	810.0	940.2
65°	407.6	407.6	410.3	420.5	427.4	445.0	469.6	507.2	569.9	664.6	775.7
67.5°	342.4	345.7	345.1	349.5	355.8	369.6	387.2	418.1	464.5	533.7	622.6
70°	299.9	302.7	301.9	305.4	312.1	321.0	335.4	364.7	398.1	457.4	533.7
72.5°	261.8	262.9	261.1	265.6	269.6	277.4	293.4	309.0	340.2	390.3	453.0
75°	200.4	201.8	203.1	205.8	210.0	214.0	222.2	237.9	258.3	295.8	336.1
77.5°	150.3	147.6	150.9	150.5	152.8	155.9	163.2	171.5	188.2	212.0	243.1
80°	113.1	113.8	113.8	114.5	118.0	120.0	126.1	132.2	145.2	162.9	184.7
82.5°	82.6	84.4	83.3	84.5	87.4	88.9	92.3	97.4	104.8	118.8	134.5
85°	44.9	41.6	42.9	44.3	44.3	44.9	47.7	49.8	53.8	59.3	65.4
87.5°	16.8	17.8	18.2	18.2	18.8	18.4	20.4	20.3	21.8	23.2	25.1
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2	13.4	12.6	11.0
92.5°	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0	206.1	254.6	258.6
95°	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7	684.6	699.6	570.9
97.5°	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6	866.2	747.1	509.8
100°	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2	910.4	713.1	454.8
102.5°	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5	883.9	653.0	413.1
105°	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6	799.1	572.5	372.7
107.5°	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5	712.6	517.1	355.7
110°	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8	663.3	491.1	350.6



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0	626.6	475.9	350.6
115°	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0	586.6	459.6	352.9
117.5°	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0	562.8	451.5	358.2
120°	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2	549.6	447.7	363.2
122.5°	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2	538.2	444.5	367.6
125°	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4	522.7	440.6	375.1
127.5°	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1	508.5	438.7	383.4
130°	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3	499.1	437.5	388.5
132.5°	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5	491.5	437.5	394.2
135°	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0	482.4	437.5	401.9
137.5°	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6	474.4	438.4	409.0
140°	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1	470.6	439.0	412.1
142.5°	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0	467.5	439.7	414.0
145°	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2	462.7	439.0	416.2
147.5°	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1	457.8	437.0	416.9
150°	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4	454.0	435.0	416.9
152.5°	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0	449.6	432.5	416.3
155°	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7	442.2	428.0	414.5
157.5°	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2	435.3	423.2	412.5
160°	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8	429.6	420.1	410.6
162.5°	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8	424.4	416.3	408.7
165°	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2	416.9	410.6	405.9
167.5°	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0	409.5	405.1	401.4
170°	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0	405.1	401.9	399.5
172.5°	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3	400.6	398.1	397.0
175°	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2	394.8	394.0	394.0
177.5°	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9	392.2	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1652.2	1648.4	1644.1	1636.4	1627.1	1622.2	1614.6	1609.7	1599.8	1591.6	1583.0
5°	1736.1	1718.4	1702.0	1680.8	1657.7	1642.6	1625.0	1605.2	1584.8	1563.6	1540.4
7.5°	1822.9	1791.5	1757.5	1720.8	1685.0	1651.9	1620.4	1589.5	1560.6	1525.7	1496.1
10°	1881.3	1841.7	1799.5	1749.7	1701.3	1659.0	1616.1	1578.6	1540.4	1499.5	1463.4
12.5°	1939.5	1886.9	1827.2	1772.6	1714.3	1663.3	1612.9	1565.0	1517.0	1471.8	1429.6
15°	1980.7	1934.4	1879.2	1801.5	1736.1	1665.9	1599.0	1537.0	1479.0	1428.7	1375.5
17.5°	2007.9	1948.1	1888.9	1814.3	1728.6	1650.0	1574.4	1503.4	1438.0	1374.1	1322.8
20°	2012.8	1951.5	1889.5	1816.4	1728.6	1638.6	1563.0	1477.7	1407.5	1341.4	1278.7
22.5°	2011.1	1941.7	1874.1	1799.1	1713.3	1630.4	1538.9	1452.1	1375.9	1310.9	1245.5
25°	1995.8	1921.5	1836.9	1761.3	1676.8	1588.8	1496.1	1406.1	1328.5	1254.2	1189.4
27.5°	1983.0	1886.5	1790.9	1702.6	1621.0	1540.4	1451.7	1359.6	1273.3	1198.1	1137.1
30°	1967.1	1861.5	1753.7	1661.7	1577.9	1499.5	1415.7	1325.8	1235.8	1162.2	1096.7
32.5°	1953.0	1829.9	1716.2	1616.0	1527.2	1451.0	1373.7	1288.1	1199.7	1125.1	1059.7
35°	1925.5	1783.1	1652.9	1539.7	1445.0	1366.7	1301.9	1222.1	1141.0	1068.7	1006.0
37.5°	1890.8	1721.7	1582.1	1463.4	1359.6	1277.0	1216.7	1155.5	1077.6	1007.9	951.3
40°	1863.5	1678.1	1530.2	1408.9	1301.2	1215.3	1159.4	1101.5	1036.7	972.0	912.0
42.5°	1829.2	1638.9	1477.8	1347.3	1240.6	1157.0	1098.3	1049.1	992.0	931.6	876.0
45°	1766.1	1567.7	1393.2	1252.8	1145.1	1062.6	1002.0	965.1	922.2	864.9	817.9
47.5°	1673.2	1482.2	1301.7	1156.8	1045.7	969.3	912.4	877.1	846.9	804.3	761.6
50°	1590.8	1418.5	1235.8	1092.0	980.9	903.8	851.3	819.3	793.3	760.6	724.6
52.5°	1498.7	1338.3	1170.8	1028.6	918.7	842.7	791.3	763.2	741.5	718.1	682.6
55°	1352.3	1216.0	1060.6	925.6	824.0	749.7	704.8	680.2	662.6	644.8	623.0
57.5°	1191.0	1084.4	946.7	823.3	729.8	662.3	620.3	596.4	582.6	573.5	560.7
60°	1077.6	986.3	867.7	755.2	663.9	603.9	563.0	544.6	533.0	525.5	515.9
62.5°	972.4	897.4	787.5	684.9	605.0	548.3	511.8	493.9	482.8	479.2	471.3
65°	817.3	759.3	668.6	583.5	515.3	466.9	436.3	419.2	412.3	408.3	409.0
67.5°	664.4	629.1	556.3	483.6	429.3	388.7	364.2	351.0	347.6	342.1	342.0
70°	571.2	544.6	483.2	419.9	371.4	340.1	318.3	304.7	301.2	298.5	297.9
72.5°	488.9	465.5	412.3	361.5	318.0	290.5	272.5	264.3	258.7	257.1	257.0
75°	367.4	354.5	312.1	272.0	242.0	222.9	210.7	203.1	199.0	198.3	199.0
77.5°	261.2	249.8	223.0	194.5	175.6	161.2	150.8	148.1	143.5	143.7	143.0
80°	196.3	188.8	171.8	149.3	133.6	121.3	115.8	111.1	109.8	107.7	109.8
82.5°	142.3	134.3	122.7	108.4	95.4	88.1	82.6	81.1	80.3	79.4	79.8
85°	70.2	70.9	64.0	53.1	47.7	43.6	40.2	40.2	39.5	38.9	39.5
87.5°	26.1	24.6	22.3	20.3	17.3	15.3	14.5	14.8	13.4	13.1	14.0
90°	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6	11.7	18.3	28.1
95°	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1	26.9	33.1	41.8
97.5°	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2	44.2	48.7	57.4
100°	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2	56.9	60.0	68.7
102.5°	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6	69.5	72.0	81.3
105°	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3	89.3	93.2	101.1
107.5°	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5	111.0	114.8	121.3
110°	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0	125.5	128.7	135.8



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5	140.1	142.6	149.7
115°	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5	161.1	163.5	170.6
117.5°	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4	180.9	183.4	190.5
120°	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1	193.5	196.6	203.7
122.5°	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4	206.1	208.6	215.7
125°	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1	222.7	226.6	233.7
127.5°	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2	236.6	241.7	250.6
130°	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4	244.8	251.1	261.4
132.5°	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7	251.8	259.3	270.8
135°	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0	262.2	271.7	284.3
137.5°	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0	274.3	283.2	295.8
140°	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5	281.9	291.3	304.0
142.5°	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3	290.1	298.9	311.5
145°	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6	303.2	311.1	322.1
147.5°	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5	316.5	323.3	333.6
150°	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8	325.3	330.8	341.1
152.5°	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5	333.6	338.4	347.4
155°	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3	344.3	349.0	356.9
157.5°	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7	354.6	358.3	365.1
160°	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6	360.8	364.1	369.5
162.5°	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3	366.6	369.7	374.6
165°	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9	374.3	376.7	380.6
167.5°	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5	380.7	382.1	384.4
170°	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4	384.6	385.4	386.9
172.5°	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9	386.5	387.2	388.8
175°	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8	389.3	390.1	390.8
177.5°	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2	391.0	391.0	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1578.0	1572.1	1567.1	1556.2	1550.2	1542.1	1535.5	1542.6	1535.0	1538.2	1533.4
5°	1528.8	1509.7	1496.1	1476.3	1459.4	1443.6	1432.1	1430.0	1424.5	1421.8	1413.6
7.5°	1469.7	1445.8	1422.4	1396.4	1374.6	1352.4	1338.3	1326.6	1318.8	1308.6	1301.6
10°	1434.8	1402.7	1375.5	1344.1	1316.9	1293.0	1273.9	1264.4	1255.6	1242.5	1237.8
12.5°	1391.7	1358.6	1325.3	1291.8	1265.6	1239.0	1222.6	1208.2	1202.0	1187.5	1186.0
15°	1340.1	1290.3	1257.6	1223.5	1187.4	1165.6	1152.0	1136.2	1129.4	1119.2	1111.7
17.5°	1278.4	1234.0	1193.1	1157.8	1126.8	1108.4	1091.6	1080.8	1069.0	1062.4	1050.1
20°	1233.8	1191.4	1150.5	1113.1	1089.2	1068.0	1054.4	1044.2	1032.0	1028.5	1016.3
22.5°	1196.1	1149.4	1110.2	1078.7	1052.7	1028.9	1014.1	1007.1	998.7	988.2	985.7
25°	1134.9	1086.5	1053.1	1021.8	998.6	976.7	966.5	957.7	949.5	942.0	939.3
27.5°	1082.0	1038.7	999.1	970.8	950.6	930.7	921.7	910.9	904.9	898.9	891.5
30°	1044.9	1000.6	965.8	938.6	916.8	899.1	889.5	882.0	876.6	871.1	867.0
32.5°	1006.7	965.7	932.0	905.3	883.5	870.1	861.7	856.4	850.4	843.8	838.7
35°	956.3	911.3	878.6	855.5	838.4	828.2	818.6	813.9	807.0	807.0	801.5
37.5°	899.5	860.6	831.7	810.6	795.3	786.2	775.8	772.5	768.2	765.3	763.4
40°	865.7	829.5	802.2	781.1	764.8	757.3	749.1	743.7	740.9	737.5	736.1
42.5°	830.7	796.3	770.1	750.6	736.4	730.0	722.4	718.5	713.1	708.6	707.8
45°	777.7	744.3	720.4	704.8	692.5	685.0	680.2	672.1	669.3	663.9	663.2
47.5°	727.4	695.4	672.0	659.1	648.3	642.2	634.7	626.5	623.4	620.7	620.4
50°	689.8	660.5	638.6	626.4	616.2	607.3	599.9	594.4	592.3	592.3	593.7
52.5°	651.7	626.6	608.1	593.1	583.5	574.0	567.1	563.8	560.7	564.0	566.4
55°	595.7	570.5	556.8	542.6	533.0	522.1	518.7	517.4	515.3	520.8	523.5
57.5°	536.5	518.9	502.9	488.7	480.1	473.8	469.2	468.4	472.2	474.8	483.6
60°	499.0	478.5	464.1	453.2	443.0	439.0	437.6	436.3	439.0	446.5	458.1
62.5°	457.5	440.9	425.5	417.3	409.8	402.9	402.7	403.5	409.0	417.6	429.1
65°	396.7	382.3	372.1	362.6	356.5	352.3	353.8	356.5	362.6	374.2	387.2
67.5°	335.0	325.2	316.0	308.2	302.4	302.4	303.8	307.8	315.1	328.4	340.2
70°	295.2	284.3	276.7	273.4	268.5	265.8	269.9	276.7	282.9	295.2	305.4
72.5°	255.3	246.1	240.2	237.9	235.8	233.7	235.0	242.4	250.6	263.0	274.8
75°	196.3	192.9	188.8	186.1	184.0	185.4	186.7	193.6	200.4	213.4	227.0
77.5°	143.3	139.8	137.2	136.6	135.5	136.2	140.0	145.0	151.7	161.2	171.5
80°	108.4	107.0	105.6	104.9	104.9	105.6	111.1	114.5	120.7	129.5	137.6
82.5°	79.0	78.1	77.9	77.7	78.3	78.4	81.7	86.1	91.2	97.9	104.9
85°	41.6	40.2	42.2	42.9	41.6	43.6	44.9	47.7	49.8	53.1	56.6
87.5°	14.9	16.3	16.0	16.8	17.0	18.4	18.0	20.3	21.5	22.8	22.5
90°	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2	15.0	15.8	17.4
92.5°	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0	101.6	76.4	64.7
95°	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7	447.7	350.6	284.3
97.5°	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6	761.3	666.7	574.5
100°	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2	932.5	851.2	769.1
102.5°	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5	1037.4	998.4	942.8
105°	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6	1096.8	1131.6	1122.9
107.5°	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5	1043.9	1133.1	1174.3
110°	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8	983.8	1095.2	1162.3



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0	924.4	1037.0	1116.2
115°	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0	839.4	947.6	1033.6
117.5°	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0	780.4	873.6	952.6
120°	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2	747.0	833.8	903.3
122.5°	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2	723.0	800.3	865.5
125°	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4	690.9	759.6	816.5
127.5°	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1	660.2	724.4	777.6
130°	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3	638.8	700.3	751.7
132.5°	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5	618.5	674.5	723.9
135°	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0	587.4	638.0	683.0
137.5°	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6	559.7	601.7	639.9
140°	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1	543.2	579.6	612.7
142.5°	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0	529.4	560.6	589.4
145°	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2	511.7	536.1	557.4
147.5°	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1	497.0	515.7	531.9
150°	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4	488.8	503.7	518.0
152.5°	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0	480.6	494.3	505.3
155°	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7	468.3	479.3	488.0
157.5°	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2	456.6	465.0	471.9
160°	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8	447.7	455.7	461.1
162.5°	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8	440.1	446.8	451.6
165°	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2	428.8	433.5	437.5
167.5°	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0	417.7	421.3	424.1
170°	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0	411.4	413.7	415.4
172.5°	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3	405.7	407.5	408.4
175°	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2	397.2	398.8	398.8
177.5°	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9	393.5	393.5	393.5
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1530.0	1533.9	1530.7	1535.0	1530.7	1533.9	1530.0	1533.4	1538.2	1535.0	1542.6
5°	1410.3	1404.1	1408.2	1405.4	1408.2	1404.1	1410.3	1413.6	1421.8	1424.5	1430.0
7.5°	1299.6	1293.7	1287.0	1283.8	1287.0	1293.7	1299.6	1301.6	1308.6	1318.8	1326.6
10°	1230.3	1222.8	1222.1	1217.4	1222.1	1222.8	1230.3	1237.8	1242.5	1255.6	1264.4
12.5°	1179.6	1172.7	1164.9	1162.9	1164.9	1172.7	1179.6	1186.0	1187.5	1202.0	1208.2
15°	1107.6	1102.2	1097.4	1101.5	1097.4	1102.2	1107.6	1111.7	1119.2	1129.4	1136.2
17.5°	1047.7	1043.3	1042.5	1037.4	1042.5	1043.3	1047.7	1050.1	1062.4	1069.0	1080.8
20°	1010.2	1006.7	1008.1	999.3	1008.1	1006.7	1010.2	1016.3	1028.5	1032.0	1044.2
22.5°	980.2	973.5	972.7	970.9	972.7	973.5	980.2	985.7	988.2	998.7	1007.1
25°	933.1	929.7	926.3	929.7	926.3	929.7	933.1	939.3	942.0	949.5	957.7
27.5°	892.1	888.0	887.1	887.5	887.1	888.0	892.1	891.5	898.9	904.9	910.9
30°	867.0	860.2	860.9	860.2	860.9	860.2	867.0	867.0	871.1	876.6	882.0
32.5°	839.7	835.1	834.1	832.9	834.1	835.1	839.7	838.7	843.8	850.4	856.4
35°	799.5	799.5	796.1	796.1	796.1	799.5	799.5	801.5	807.0	807.0	813.9
37.5°	761.7	761.0	759.0	759.3	759.0	761.0	761.7	763.4	765.3	768.2	772.5
40°	733.4	732.8	730.6	726.6	730.6	732.8	733.4	736.1	737.5	740.9	743.7
42.5°	706.1	703.9	702.9	701.6	702.9	703.9	706.1	707.8	708.6	713.1	718.5
45°	663.2	663.2	661.9	661.2	661.9	663.2	663.2	663.2	663.9	669.3	672.1
47.5°	621.5	622.7	625.3	624.9	625.3	622.7	621.5	620.4	620.7	623.4	626.5
50°	596.4	597.1	599.2	599.9	599.2	597.1	596.4	593.7	592.3	592.3	594.4
52.5°	568.6	572.6	575.1	574.7	575.1	572.6	568.6	566.4	564.0	560.7	563.8
55°	529.6	534.4	539.2	539.9	539.2	534.4	529.6	523.5	520.8	515.3	517.4
57.5°	491.0	497.7	502.7	504.4	502.7	497.7	491.0	483.6	474.8	472.2	468.4
60°	464.8	473.7	479.9	482.6	479.9	473.7	464.8	458.1	446.5	439.0	436.3
62.5°	439.8	449.7	455.9	456.4	455.9	449.7	439.8	429.1	417.6	409.0	403.5
65°	398.7	409.0	414.4	418.5	414.4	409.0	398.7	387.2	374.2	362.6	356.5
67.5°	354.6	364.8	370.8	374.1	370.8	364.8	354.6	340.2	328.4	315.1	307.8
70°	322.4	332.6	340.8	343.6	340.8	332.6	322.4	305.4	295.2	282.9	276.7
72.5°	290.7	299.9	306.5	309.7	306.5	299.9	290.7	274.8	263.0	250.6	242.4
75°	235.8	248.1	254.3	257.6	254.3	248.1	235.8	227.0	213.4	200.4	193.6
77.5°	181.9	193.0	196.7	198.4	196.7	193.0	181.9	171.5	161.2	151.7	145.0
80°	145.8	152.7	157.4	158.1	157.4	152.7	145.8	137.6	129.5	120.7	114.5
82.5°	112.1	117.8	119.3	121.1	119.3	117.8	112.1	104.9	97.9	91.2	86.1
85°	61.3	64.0	64.7	64.0	64.7	64.0	61.3	56.6	53.1	49.8	47.7
87.5°	23.6	23.1	23.2	24.3	23.2	23.1	23.6	22.5	22.8	21.5	20.3
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2
92.5°	54.6	52.7	51.6	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0
95°	228.2	204.5	198.2	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7
97.5°	525.7	481.5	458.6	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6
100°	714.6	657.7	628.5	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2
102.5°	884.5	844.0	812.3	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5
105°	1097.5	1071.5	1055.7	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6
107.5°	1187.1	1186.9	1181.7	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5
110°	1197.8	1212.8	1218.4	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1168.1	1193.9	1207.6	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0
115°	1095.2	1133.1	1155.2	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0
117.5°	1014.2	1053.3	1075.3	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0
120°	961.7	999.7	1021.0	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2
122.5°	917.6	952.3	973.6	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2
125°	860.7	893.0	910.4	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4
127.5°	817.7	846.3	862.7	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1
130°	791.2	817.3	833.0	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3
132.5°	763.4	789.4	804.0	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5
135°	717.7	743.8	758.0	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0
137.5°	671.1	694.7	707.8	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6
140°	642.0	662.5	674.3	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1
142.5°	614.2	631.6	642.8	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0
145°	576.4	589.9	598.5	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2
147.5°	546.8	557.6	562.7	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1
150°	529.9	539.3	542.5	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4
152.5°	515.3	522.9	526.0	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0
155°	495.8	501.4	503.7	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7
157.5°	478.1	482.6	484.8	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2
160°	466.7	470.6	472.2	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8
162.5°	456.0	459.2	459.6	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8
165°	440.6	442.2	442.2	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2
167.5°	425.8	427.2	426.6	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0
170°	416.9	417.7	417.7	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0
172.5°	408.7	410.1	408.9	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3
175°	398.8	399.5	398.0	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2
177.5°	392.9	393.5	391.6	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1535.5	1542.1	1550.2	1556.2	1567.1	1572.1	1578.0	1583.0	1591.6	1599.8	1609.7
5°	1432.1	1443.6	1459.4	1476.3	1496.1	1509.7	1528.8	1540.4	1563.6	1584.8	1605.2
7.5°	1338.3	1352.4	1374.6	1396.4	1422.4	1445.8	1469.7	1496.1	1525.7	1560.6	1589.5
10°	1273.9	1293.0	1316.9	1344.1	1375.5	1402.7	1434.8	1463.4	1499.5	1540.4	1578.6
12.5°	1222.6	1239.0	1265.6	1291.8	1325.3	1358.6	1391.7	1429.6	1471.8	1517.0	1565.0
15°	1152.0	1165.6	1187.4	1223.5	1257.6	1290.3	1340.1	1375.5	1428.7	1479.0	1537.0
17.5°	1091.6	1108.4	1126.8	1157.8	1193.1	1234.0	1278.4	1322.8	1374.1	1438.0	1503.4
20°	1054.4	1068.0	1089.2	1113.1	1150.5	1191.4	1233.8	1278.7	1341.4	1407.5	1477.7
22.5°	1014.1	1028.9	1052.7	1078.7	1110.2	1149.4	1196.1	1245.5	1310.9	1375.9	1452.1
25°	966.5	976.7	998.6	1021.8	1053.1	1086.5	1134.9	1189.4	1254.2	1328.5	1406.1
27.5°	921.7	930.7	950.6	970.8	999.1	1038.7	1082.0	1137.1	1198.1	1273.3	1359.6
30°	889.5	899.1	916.8	938.6	965.8	1000.6	1044.9	1096.7	1162.2	1235.8	1325.8
32.5°	861.7	870.1	883.5	905.3	932.0	965.7	1006.7	1059.7	1125.1	1199.7	1288.1
35°	818.6	828.2	838.4	855.5	878.6	911.3	956.3	1006.0	1068.7	1141.0	1222.1
37.5°	775.8	786.2	795.3	810.6	831.7	860.6	899.5	951.3	1007.9	1077.6	1155.5
40°	749.1	757.3	764.8	781.1	802.2	829.5	865.7	912.0	972.0	1036.7	1101.5
42.5°	722.4	730.0	736.4	750.6	770.1	796.3	830.7	876.0	931.6	992.0	1049.1
45°	680.2	685.0	692.5	704.8	720.4	744.3	777.7	817.9	864.9	922.2	965.1
47.5°	634.7	642.2	648.3	659.1	672.0	695.4	727.4	761.6	804.3	846.9	877.1
50°	599.9	607.3	616.2	626.4	638.6	660.5	689.8	724.6	760.6	793.3	819.3
52.5°	567.1	574.0	583.5	593.1	608.1	626.6	651.7	682.6	718.1	741.5	763.2
55°	518.7	522.1	533.0	542.6	556.8	570.5	595.7	623.0	644.8	662.6	680.2
57.5°	469.2	473.8	480.1	488.7	502.9	518.9	536.5	560.7	573.5	582.6	596.4
60°	437.6	439.0	443.0	453.2	464.1	478.5	499.0	515.9	525.5	533.0	544.6
62.5°	402.7	402.9	409.8	417.3	425.5	440.9	457.5	471.3	479.2	482.8	493.9
65°	353.8	352.3	356.5	362.6	372.1	382.3	396.7	409.0	408.3	412.3	419.2
67.5°	303.8	302.4	302.4	308.2	316.0	325.2	335.0	342.0	342.1	347.6	351.0
70°	269.9	265.8	268.5	273.4	276.7	284.3	295.2	297.9	298.5	301.2	304.7
72.5°	235.0	233.7	235.8	237.9	240.2	246.1	255.3	257.0	257.1	258.7	264.3
75°	186.7	185.4	184.0	186.1	188.8	192.9	196.3	199.0	198.3	199.0	203.1
77.5°	140.0	136.2	135.5	136.6	137.2	139.8	143.3	143.0	143.7	143.5	148.1
80°	111.1	105.6	104.9	104.9	105.6	107.0	108.4	109.8	107.7	109.8	111.1
82.5°	81.7	78.4	78.3	77.7	77.9	78.1	79.0	79.8	79.4	80.3	81.1
85°	44.9	43.6	41.6	42.9	42.2	40.2	41.6	39.5	38.9	39.5	40.2
87.5°	18.0	18.4	17.0	16.8	16.0	16.3	14.9	14.0	13.1	13.4	14.8
90°	13.4	12.6	11.0	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8
92.5°	206.1	254.6	258.6	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6
95°	684.6	699.6	570.9	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1
97.5°	866.2	747.1	509.8	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2
100°	910.4	713.1	454.8	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2
102.5°	883.9	653.0	413.1	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6
105°	799.1	572.5	372.7	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3
107.5°	712.6	517.1	355.7	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5
110°	663.3	491.1	350.6	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	626.6	475.9	350.6	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5
115°	586.6	459.6	352.9	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5
117.5°	562.8	451.5	358.2	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4
120°	549.6	447.7	363.2	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1
122.5°	538.2	444.5	367.6	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4
125°	522.7	440.6	375.1	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1
127.5°	508.5	438.7	383.4	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2
130°	499.1	437.5	388.5	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4
132.5°	491.5	437.5	394.2	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7
135°	482.4	437.5	401.9	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0
137.5°	474.4	438.4	409.0	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0
140°	470.6	439.0	412.1	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5
142.5°	467.5	439.7	414.0	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3
145°	462.7	439.0	416.2	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6
147.5°	457.8	437.0	416.9	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5
150°	454.0	435.0	416.9	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8
152.5°	449.6	432.5	416.3	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5
155°	442.2	428.0	414.5	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3
157.5°	435.3	423.2	412.5	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7
160°	429.6	420.1	410.6	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6
162.5°	424.4	416.3	408.7	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3
165°	416.9	410.6	405.9	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9
167.5°	409.5	405.1	401.4	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5
170°	405.1	401.9	399.5	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4
172.5°	400.6	398.1	397.0	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9
175°	394.8	394.0	394.0	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8
177.5°	392.2	391.6	391.6	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1614.6	1622.2	1627.1	1636.4	1644.1	1648.4	1652.2	1655.5	1659.3	1662.5	1671.8
5°	1625.0	1642.6	1657.7	1680.8	1702.0	1718.4	1736.1	1751.7	1764.6	1783.1	1797.4
7.5°	1620.4	1651.9	1685.0	1720.8	1757.5	1791.5	1822.9	1852.2	1878.8	1911.0	1939.1
10°	1616.1	1659.0	1701.3	1749.7	1799.5	1841.7	1881.3	1921.5	1950.8	1991.7	2026.4
12.5°	1612.9	1663.3	1714.3	1772.6	1827.2	1886.9	1939.5	1968.9	2013.5	2046.2	2087.5
15°	1599.0	1665.9	1736.1	1801.5	1879.2	1934.4	1980.7	2038.0	2079.6	2121.1	2166.2
17.5°	1574.4	1650.0	1728.6	1814.3	1888.9	1948.1	2007.9	2063.1	2112.7	2168.5	2224.5
20°	1563.0	1638.6	1728.6	1816.4	1889.5	1951.5	2012.8	2073.5	2128.0	2199.6	2264.3
22.5°	1538.9	1630.4	1713.3	1799.1	1874.1	1941.7	2011.1	2080.0	2152.5	2233.3	2314.5
25°	1496.1	1588.8	1676.8	1761.3	1836.9	1921.5	1995.8	2087.8	2180.5	2287.4	2388.3
27.5°	1451.7	1540.4	1621.0	1702.6	1790.9	1886.5	1983.0	2087.4	2208.7	2343.8	2486.1
30°	1415.7	1499.5	1577.9	1661.7	1753.7	1861.5	1967.1	2091.1	2231.6	2383.6	2552.6
32.5°	1373.7	1451.0	1527.2	1616.0	1716.2	1829.9	1953.0	2089.0	2257.8	2430.4	2604.4
35°	1301.9	1366.7	1445.0	1539.7	1652.9	1783.1	1925.5	2086.4	2280.0	2478.3	2624.8
37.5°	1216.7	1277.0	1359.6	1463.4	1582.1	1721.7	1890.8	2081.6	2287.2	2445.4	2492.6
40°	1159.4	1215.3	1301.2	1408.9	1530.2	1678.1	1863.5	2065.3	2264.3	2365.2	2326.3
42.5°	1098.3	1157.0	1240.6	1347.3	1477.8	1638.9	1829.2	2030.9	2197.8	2235.9	2101.6
45°	1002.0	1062.6	1145.1	1252.8	1393.2	1567.7	1766.1	1949.4	2045.5	1976.7	1768.8
47.5°	912.4	969.3	1045.7	1156.8	1301.7	1482.2	1673.2	1819.5	1827.1	1662.8	1440.8
50°	851.3	903.8	980.9	1092.0	1235.8	1418.5	1590.8	1706.1	1654.3	1468.1	1254.9
52.5°	791.3	842.7	918.7	1028.6	1170.8	1338.3	1498.7	1579.5	1482.0	1291.0	1108.7
55°	704.8	749.7	824.0	925.6	1060.6	1216.0	1352.3	1380.3	1253.4	1065.3	917.5
57.5°	620.3	662.3	729.8	823.3	946.7	1084.4	1191.0	1185.1	1051.1	889.6	772.2
60°	563.0	603.9	663.9	755.2	867.7	986.3	1077.6	1055.8	922.9	783.9	685.0
62.5°	511.8	548.3	605.0	684.9	787.5	897.4	972.4	940.2	810.0	688.4	610.4
65°	436.3	466.9	515.3	583.5	668.6	759.3	817.3	775.7	664.6	569.9	507.2
67.5°	364.2	388.7	429.3	483.6	556.3	629.1	664.4	622.6	533.7	464.5	418.1
70°	318.3	340.1	371.4	419.9	483.2	544.6	571.2	533.7	457.4	398.1	364.7
72.5°	272.5	290.5	318.0	361.5	412.3	465.5	488.9	453.0	390.3	340.2	309.0
75°	210.7	222.9	242.0	272.0	312.1	354.5	367.4	336.1	295.8	258.3	237.9
77.5°	150.8	161.2	175.6	194.5	223.0	249.8	261.2	243.1	212.0	188.2	171.5
80°	115.8	121.3	133.6	149.3	171.8	188.8	196.3	184.7	162.9	145.2	132.2
82.5°	82.6	88.1	95.4	108.4	122.7	134.3	142.3	134.5	118.8	104.8	97.4
85°	40.2	43.6	47.7	53.1	64.0	70.9	70.2	65.4	59.3	53.8	49.8
87.5°	14.5	15.3	17.3	20.3	22.3	24.6	26.1	25.1	23.2	21.8	20.3
90°	1.6	3.1	4.7	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2
92.5°	11.7	18.3	28.1	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0
95°	26.9	33.1	41.8	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7
97.5°	44.2	48.7	57.4	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6
100°	56.9	60.0	68.7	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2
102.5°	69.5	72.0	81.3	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5
105°	89.3	93.2	101.1	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6
107.5°	111.0	114.8	121.3	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5
110°	125.5	128.7	135.8	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.1	142.6	149.7	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0
115°	161.1	163.5	170.6	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0
117.5°	180.9	183.4	190.5	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0
120°	193.5	196.6	203.7	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2
122.5°	206.1	208.6	215.7	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2
125°	222.7	226.6	233.7	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4
127.5°	236.6	241.7	250.6	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1
130°	244.8	251.1	261.4	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3
132.5°	251.8	259.3	270.8	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5
135°	262.2	271.7	284.3	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0
137.5°	274.3	283.2	295.8	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6
140°	281.9	291.3	304.0	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1
142.5°	290.1	298.9	311.5	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0
145°	303.2	311.1	322.1	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2
147.5°	316.5	323.3	333.6	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1
150°	325.3	330.8	341.1	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4
152.5°	333.6	338.4	347.4	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0
155°	344.3	349.0	356.9	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7
157.5°	354.6	358.3	365.1	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2
160°	360.8	364.1	369.5	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8
162.5°	366.6	369.7	374.6	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8
165°	374.3	376.7	380.6	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2
167.5°	380.7	382.1	384.4	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0
170°	384.6	385.4	386.9	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0
172.5°	386.5	387.2	388.8	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3
175°	389.3	390.1	390.8	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2
177.5°	391.0	391.0	391.6	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1679.5	1683.8	1693.1	1689.8	1694.3	1696.4	1698.6
5°	1815.1	1836.9	1846.4	1845.1	1859.5	1856.0	1852.6
7.5°	1968.3	1991.3	2004.1	2020.0	2029.3	2029.9	2038.0
10°	2055.1	2085.1	2097.3	2114.4	2125.3	2131.4	2130.7
12.5°	2121.6	2145.1	2172.5	2180.9	2195.6	2203.3	2200.5
15°	2201.6	2239.1	2267.8	2282.0	2300.5	2305.9	2313.4
17.5°	2273.0	2323.3	2356.7	2401.2	2417.9	2428.1	2422.2
20°	2327.0	2393.2	2426.5	2479.7	2509.0	2524.7	2519.2
22.5°	2390.9	2462.4	2524.2	2570.2	2614.7	2635.9	2640.3
25°	2500.1	2598.3	2689.0	2749.7	2804.8	2817.7	2846.4
27.5°	2622.3	2738.0	2835.0	2898.7	2937.2	2951.6	2960.6
30°	2699.2	2814.4	2887.3	2928.2	2940.4	2939.1	2937.7
32.5°	2736.8	2808.9	2823.0	2811.5	2783.4	2759.7	2734.9
35°	2683.5	2629.7	2549.2	2445.6	2369.2	2292.3	2284.7
37.5°	2413.5	2241.3	2107.4	1957.8	1871.6	1818.3	1781.5
40°	2159.3	1963.7	1801.5	1675.4	1587.5	1552.7	1518.6
42.5°	1883.4	1696.6	1552.9	1447.4	1381.4	1342.8	1315.8
45°	1530.2	1365.2	1252.8	1176.5	1124.0	1094.0	1076.9
47.5°	1253.8	1131.9	1036.3	981.3	945.0	921.7	921.8
50°	1105.6	989.1	925.6	882.0	850.6	832.2	835.7
52.5°	974.1	887.1	832.9	796.4	773.3	761.9	761.5
55°	814.6	751.8	716.4	689.8	674.1	661.2	663.9
57.5°	696.7	643.9	620.2	598.0	587.1	582.0	574.4
60°	623.7	582.8	562.3	544.6	533.7	529.6	522.1
62.5°	558.8	526.6	506.8	492.2	482.4	481.1	475.2
65°	469.6	445.0	427.4	420.5	410.3	407.6	407.6
67.5°	387.2	369.6	355.8	349.5	345.1	345.7	342.4
70°	335.4	321.0	312.1	305.4	301.9	302.7	299.9
72.5°	293.4	277.4	269.6	265.6	261.1	262.9	261.8
75°	222.2	214.0	210.0	205.8	203.1	201.8	200.4
77.5°	163.2	155.9	152.8	150.5	150.9	147.6	150.3
80°	126.1	120.0	118.0	114.5	113.8	113.8	113.1
82.5°	92.3	88.9	87.4	84.5	83.3	84.4	82.6
85°	47.7	44.9	44.3	44.3	42.9	41.6	44.9
87.5°	20.4	18.4	18.8	18.2	18.2	17.8	16.8
90°	15.0	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.6	76.4	64.7	54.6	52.7	51.6	50.4
95°	447.7	350.6	284.3	228.2	204.5	198.2	185.5
97.5°	761.3	666.7	574.5	525.7	481.5	458.6	448.5
100°	932.5	851.2	769.1	714.6	657.7	628.5	615.9
102.5°	1037.4	998.4	942.8	884.5	844.0	812.3	802.8
105°	1096.8	1131.6	1122.9	1097.5	1071.5	1055.7	1046.2
107.5°	1043.9	1133.1	1174.3	1187.1	1186.9	1181.7	1175.4
110°	983.8	1095.2	1162.3	1197.8	1212.8	1218.4	1218.4



TEST NUMBER: P333270-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	924.4	1037.0	1116.2	1168.1	1193.9	1207.6	1213.4
115°	839.4	947.6	1033.6	1095.2	1133.1	1155.2	1165.5
117.5°	780.4	873.6	952.6	1014.2	1053.3	1075.3	1081.6
120°	747.0	833.8	903.3	961.7	999.7	1021.0	1027.2
122.5°	723.0	800.3	865.5	917.6	952.3	973.6	979.3
125°	690.9	759.6	816.5	860.7	893.0	910.4	918.3
127.5°	660.2	724.4	777.6	817.7	846.3	862.7	866.2
130°	638.8	700.3	751.7	791.2	817.3	833.0	837.8
132.5°	618.5	674.5	723.9	763.4	789.4	804.0	809.3
135°	587.4	638.0	683.0	717.7	743.8	758.0	762.8
137.5°	559.7	601.7	639.9	671.1	694.7	707.8	713.1
140°	543.2	579.6	612.7	642.0	662.5	674.3	678.2
142.5°	529.4	560.6	589.4	614.2	631.6	642.8	646.0
145°	511.7	536.1	557.4	576.4	589.9	598.5	601.7
147.5°	497.0	515.7	531.9	546.8	557.6	562.7	564.1
150°	488.8	503.7	518.0	529.9	539.3	542.5	543.2
152.5°	480.6	494.3	505.3	515.3	522.9	526.0	526.8
155°	468.3	479.3	488.0	495.8	501.4	503.7	504.5
157.5°	456.6	465.0	471.9	478.1	482.6	484.8	484.6
160°	447.7	455.7	461.1	466.7	470.6	472.2	471.4
162.5°	440.1	446.8	451.6	456.0	459.2	459.6	459.4
165°	428.8	433.5	437.5	440.6	442.2	442.2	442.2
167.5°	417.7	421.3	424.1	425.8	427.2	426.6	426.4
170°	411.4	413.7	415.4	416.9	417.7	417.7	416.9
172.5°	405.7	407.5	408.4	408.7	410.1	408.9	408.1
175°	397.2	398.8	398.8	398.8	399.5	398.0	397.2
177.5°	393.5	393.5	393.5	392.9	393.5	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6

(END OF REPORT)