

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333328-840

Luminaire Tested: **S125DIP-S1270D1035U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333328-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1035U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9358.6 lumens
Efficiency: N/A
Efficacy: 140.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333328-840

CATALOG NUMBER: S125DIP-S1270D1035U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333328-840

CATALOG NUMBER: S125DIP-S1270D1035U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	53	51	46
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333328-840

CATALOG NUMBER: S125DIP-S1270D1035U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.6	2.0
10°-20°	530.1	5.7
20°-30°	782.7	8.4
30°-40°	913.3	9.8
40°-50°	917.2	9.8
50°-60°	805.1	8.6
60°-70°	599.9	6.4
70°-80°	343.0	3.7
80°-90°	102.6	1.1
90°-100°	49.4	0.5
100°-110°	304.6	3.3
110°-120°	552.5	5.9
120°-130°	709.1	7.6
130°-140°	762.7	8.1
140°-150°	715.9	7.6
150°-160°	579.1	6.2
160°-170°	374.5	4.0
170°-180°	129.2	1.4
0°-30°	1500.4	16.0
0°-40°	2413.6	25.8
0°-60°	4136.0	44.2
0°-90°	5181.6	55.4
90°-120°	906.6	9.7
90°-150°	3094.2	33.1
90°-180°	4177.0	44.6
0°-180°	9358.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	1	9	16	21	24	7
95°	58	52	16	21	21	73
105°	296	300	300	300	299	314
115°	557	561	563	559	553	552
125°	792	798	799	795	792	707
135°	987	993	991	989	983	761
145°	1144	1146	1146	1147	1142	715
155°	1260	1255	1256	1259	1251	580
165°	1330	1324	1325	1330	1323	376
175°	1360	1355	1355	1362	1354	129
180°	1360	1360	1360	1360	1360	



TEST NUMBER: P333328-840

CATALOG NUMBER: S125DIP-S1270D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.2	34.5	34.9	35.2	35.6	35.9	35.9	36.0	36.0	36.0	36.2
90°	1.0	2.8	4.5	6.4	8.2	9.9	11.4	13.0	14.5	16.2	17.3
92.5°	15.6	14.2	13.0	11.7	10.5	10.6	11.9	13.3	14.7	16.2	17.3
95°	57.5	56.8	56.1	55.4	54.8	50.2	41.7	33.1	24.6	16.2	17.3
97.5°	120.0	121.2	122.4	123.6	124.8	117.0	100.2	83.3	66.4	49.6	43.3
100°	168.3	169.1	169.8	170.4	171.1	171.9	172.8	173.7	174.5	175.4	142.1
102.5°	217.6	218.4	219.3	220.2	221.0	221.7	222.3	222.8	223.3	223.9	217.5
105°	296.4	297.3	298.2	299.1	300.0	300.4	300.4	300.4	300.4	300.4	300.4
107.5°	378.3	378.3	378.3	378.3	378.3	378.5	379.0	379.4	379.9	380.3	380.4
110°	431.5	431.5	431.5	431.5	431.5	431.8	432.2	432.7	433.1	433.5	432.9



TEST NUMBER: P333328-840

CATALOG NUMBER: S125DIP-S1270D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.6	482.1	482.6	483.2	483.7	484.1	484.4	484.6	484.9	485.2	484.3
115°	556.6	557.7	558.9	560.0	561.1	561.8	562.0	562.2	562.4	562.6	561.8
117.5°	634.2	634.2	634.1	634.1	634.1	634.5	635.3	636.1	637.0	637.8	636.7
120°	682.7	682.4	682.2	682.0	681.8	682.0	682.7	683.3	684.0	684.7	684.2
122.5°	725.4	726.2	727.1	727.9	728.8	729.3	729.7	730.0	730.3	730.6	730.1
125°	791.5	793.0	794.7	796.3	797.8	798.6	798.6	798.6	798.6	798.6	797.7
127.5°	854.6	855.8	856.9	858.0	859.1	859.6	859.5	859.4	859.2	859.1	858.6
130°	893.3	894.5	895.6	896.8	897.9	898.5	898.8	899.0	899.2	899.4	898.8
132.5°	932.1	933.4	934.7	935.9	937.3	937.7	937.2	936.8	936.2	935.7	935.5
135°	987.1	988.5	989.9	991.2	992.5	993.0	992.5	992.1	991.6	991.2	990.7
137.5°	1037.7	1038.9	1040.1	1041.3	1042.4	1042.8	1042.4	1042.0	1041.6	1041.2	1041.3
140°	1070.9	1071.3	1071.8	1072.2	1072.6	1072.8	1072.5	1072.3	1072.1	1071.9	1072.3
142.5°	1100.7	1101.0	1101.3	1101.5	1101.8	1102.1	1102.4	1102.7	1103.0	1103.3	1103.4
145°	1144.5	1144.9	1145.3	1145.8	1146.2	1146.5	1146.5	1146.5	1146.5	1146.5	1146.7
147.5°	1182.8	1182.7	1182.6	1182.5	1182.3	1182.5	1182.8	1183.1	1183.3	1183.6	1183.9
150°	1207.0	1206.5	1206.1	1205.6	1205.2	1205.2	1205.6	1206.1	1206.5	1207.0	1207.4
152.5°	1230.3	1229.4	1228.4	1227.4	1226.4	1226.2	1226.6	1227.0	1227.5	1227.9	1228.4
155°	1260.4	1259.1	1257.7	1256.4	1255.1	1254.6	1255.1	1255.5	1255.9	1256.4	1257.1
157.5°	1283.5	1282.7	1282.0	1281.2	1280.4	1280.0	1280.0	1280.1	1280.1	1280.2	1280.9
160°	1299.7	1298.4	1297.1	1295.7	1294.3	1293.7	1294.0	1294.2	1294.4	1294.6	1295.6
162.5°	1312.6	1311.3	1309.9	1308.6	1307.3	1306.7	1306.9	1307.2	1307.4	1307.6	1308.9
165°	1330.0	1328.6	1327.3	1326.0	1324.6	1324.0	1324.2	1324.4	1324.7	1324.9	1326.3
167.5°	1342.9	1341.5	1340.1	1338.7	1337.4	1336.8	1337.0	1337.2	1337.4	1337.7	1339.3
170°	1350.1	1348.6	1347.0	1345.4	1343.8	1343.2	1343.4	1343.6	1343.8	1344.1	1345.8
172.5°	1354.9	1353.4	1351.8	1350.3	1348.7	1348.2	1348.5	1348.9	1349.3	1349.7	1351.3
175°	1360.2	1358.9	1357.6	1356.1	1354.8	1354.3	1354.5	1354.7	1354.9	1355.1	1357.0
177.5°	1362.6	1361.6	1360.5	1359.4	1358.4	1357.9	1358.1	1358.3	1358.5	1358.6	1359.9
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333328-840

CATALOG NUMBER: S125DIP-S1270D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	36.5	36.7	36.9	36.8	36.4	36.0	35.4	35.0
90°	18.4	19.5	20.6	21.5	22.2	22.8	23.5	24.2
92.5°	18.4	19.5	20.6	21.3	21.6	21.9	22.3	22.6
95°	18.4	19.5	20.6	21.2	21.2	21.2	21.2	21.2
97.5°	37.0	30.7	24.3	21.2	21.2	21.2	21.2	21.2
100°	108.7	75.3	41.9	24.7	23.8	22.9	22.1	21.2
102.5°	211.2	204.9	198.5	187.8	172.6	157.3	142.1	126.8
105°	300.4	300.4	300.4	300.3	300.1	299.9	299.7	299.4
107.5°	380.4	380.5	380.5	380.2	379.5	378.9	378.2	377.5
110°	432.2	431.5	430.9	430.7	430.9	431.1	431.3	431.5



TEST NUMBER: P333328-840

CATALOG NUMBER: S125DIP-S1270D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	483.5	482.6	481.8	481.2	480.9	480.6	480.3	480.0
115°	560.9	560.0	559.1	558.0	556.6	555.2	553.9	552.6
117.5°	635.5	634.4	633.2	632.3	631.8	631.2	630.6	630.0
120°	683.8	683.3	682.9	682.1	681.0	679.8	678.7	677.6
122.5°	729.7	729.3	728.8	727.9	726.7	725.4	724.1	722.8
125°	796.8	795.9	795.0	794.3	793.6	792.8	792.2	791.5
127.5°	858.1	857.6	857.1	856.1	854.3	852.7	851.1	849.4
130°	898.1	897.4	896.8	895.9	894.7	893.6	892.5	891.3
132.5°	935.4	935.3	935.1	934.5	933.4	932.3	931.2	930.1
135°	990.3	989.9	989.4	988.5	987.1	985.8	984.4	983.1
137.5°	1041.4	1041.5	1041.6	1041.0	1039.9	1038.6	1037.5	1036.3
140°	1072.8	1073.2	1073.6	1073.2	1071.9	1070.5	1069.1	1067.8
142.5°	1103.5	1103.6	1103.7	1103.1	1101.7	1100.3	1099.0	1097.6
145°	1146.9	1147.1	1147.3	1146.8	1145.5	1144.1	1142.8	1141.5
147.5°	1184.1	1184.4	1184.7	1184.0	1182.3	1180.7	1179.1	1177.5
150°	1207.9	1208.3	1208.7	1208.1	1206.3	1204.5	1202.6	1200.9
152.5°	1228.8	1229.3	1229.7	1229.1	1227.5	1225.9	1224.3	1222.6
155°	1257.7	1258.4	1259.1	1258.5	1256.7	1254.9	1253.1	1251.3
157.5°	1281.6	1282.3	1283.0	1282.5	1280.7	1278.9	1277.1	1275.4
160°	1296.5	1297.4	1298.3	1297.8	1296.1	1294.2	1292.4	1290.6
162.5°	1310.1	1311.3	1312.6	1312.2	1310.3	1308.3	1306.4	1304.3
165°	1327.6	1329.0	1330.3	1330.1	1328.3	1326.5	1324.7	1322.9
167.5°	1340.9	1342.5	1344.1	1343.9	1341.9	1339.9	1337.9	1335.8
170°	1347.7	1349.5	1351.3	1351.1	1349.1	1347.2	1345.1	1343.1
172.5°	1352.9	1354.5	1356.1	1355.9	1353.9	1351.9	1349.9	1348.0
175°	1358.8	1360.6	1362.3	1362.2	1360.2	1358.2	1356.1	1354.1
177.5°	1361.1	1362.4	1363.6	1363.5	1362.1	1360.7	1359.3	1357.8
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2

(END OF REPORT)