

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333338-840

Luminaire Tested: **S125DIP-S1270D1205U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333338-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1205U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9389.9 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333338-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333338-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	32	27	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333338-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.6	2.0
10°-20°	530.1	5.6
20°-30°	782.7	8.3
30°-40°	913.3	9.7
40°-50°	917.2	9.8
50°-60°	805.1	8.6
60°-70°	599.9	6.4
70°-80°	343.0	3.7
80°-90°	103.1	1.1
90°-100°	101.0	1.1
100°-110°	298.2	3.2
110°-120°	505.2	5.4
120°-130°	664.8	7.1
130°-140°	745.0	7.9
140°-150°	730.1	7.8
150°-160°	613.2	6.5
160°-170°	407.6	4.3
170°-180°	142.7	1.5
0°-30°	1500.4	16.0
0°-40°	2413.6	25.7
0°-60°	4136.0	44.0
0°-90°	5182.1	55.2
90°-120°	904.4	9.6
90°-150°	3044.3	32.4
90°-180°	4208.0	44.8
0°-180°	9389.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	1	10	19	24	28	9
95°	76	79	90	98	101	81
105°	268	274	280	287	291	286
115°	506	510	513	512	510	500
125°	738	745	746	744	743	661
135°	960	967	968	968	963	740
145°	1163	1168	1171	1171	1168	727
155°	1331	1331	1332	1336	1331	613
165°	1447	1445	1446	1450	1443	408
175°	1504	1500	1500	1506	1498	143
180°	1508	1508	1508	1508	1508	



TEST NUMBER: P333338-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.2	34.6	35.0	35.4	36.0	36.2	36.3	36.4	36.5	36.5	36.8
90°	1.2	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1
92.5°	28.4	29.9	31.3	32.8	34.2	36.1	38.4	40.6	42.8	45.0	46.8
95°	76.2	76.7	77.4	77.9	78.4	79.9	82.5	85.1	87.8	90.4	92.2
97.5°	126.7	126.9	127.1	127.3	127.5	129.5	133.1	136.6	140.3	143.9	145.6
100°	164.3	164.3	164.3	164.3	164.3	166.0	169.4	172.8	176.1	179.6	181.9
102.5°	204.7	205.7	206.7	207.8	208.8	210.3	212.0	213.7	215.4	217.1	219.6
105°	267.5	268.8	270.1	271.5	272.8	274.2	275.8	277.3	278.9	280.4	282.1
107.5°	337.0	338.3	339.6	340.9	342.2	343.5	344.7	345.9	347.1	348.3	349.1
110°	385.0	386.2	387.5	388.8	390.1	391.1	391.9	392.7	393.5	394.3	395.1



TEST NUMBER: P333338-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	433.7	434.4	435.0	435.8	436.5	437.3	438.3	439.3	440.2	441.2	441.6
115°	505.7	506.9	507.9	508.9	510.0	510.7	511.3	511.8	512.3	512.8	512.6
117.5°	578.0	578.6	579.1	579.5	580.0	580.4	580.9	581.4	581.8	582.3	582.5
120°	623.1	624.4	625.7	627.0	628.3	629.1	629.3	629.7	630.0	630.2	630.2
122.5°	672.0	672.5	672.9	673.4	673.8	674.4	675.1	675.8	676.4	677.1	676.9
125°	738.1	739.7	741.2	742.9	744.4	745.3	745.6	745.8	746.1	746.4	745.8
127.5°	808.6	809.4	810.3	811.2	812.1	812.7	813.0	813.3	813.6	814.0	813.6
130°	850.8	852.1	853.4	854.7	856.0	857.0	857.5	858.0	858.5	859.0	858.8
132.5°	893.0	895.1	897.4	899.5	901.6	902.6	902.5	902.4	902.3	902.2	901.9
135°	960.0	961.5	963.1	964.6	966.2	967.1	967.3	967.7	967.9	968.2	968.2
137.5°	1022.8	1024.3	1025.8	1027.3	1028.9	1030.0	1030.5	1031.1	1031.7	1032.2	1032.5
140°	1063.2	1064.5	1065.8	1067.1	1068.4	1069.4	1070.3	1071.1	1071.8	1072.6	1073.1
142.5°	1103.6	1104.7	1105.8	1106.8	1107.9	1109.0	1109.9	1111.0	1112.0	1113.0	1113.3
145°	1163.0	1164.0	1165.1	1166.1	1167.1	1168.0	1168.8	1169.6	1170.3	1171.1	1171.1
147.5°	1217.9	1218.4	1219.0	1219.6	1220.1	1220.7	1221.4	1222.0	1222.6	1223.2	1223.9
150°	1254.5	1254.3	1253.9	1253.7	1253.4	1253.8	1254.9	1255.9	1257.0	1258.0	1258.0
152.5°	1284.5	1284.9	1285.3	1285.7	1286.0	1286.4	1286.8	1287.2	1287.7	1288.1	1288.7
155°	1330.8	1330.8	1330.8	1330.8	1330.8	1330.9	1331.2	1331.4	1331.7	1331.9	1333.0
157.5°	1372.1	1371.5	1370.9	1370.4	1369.8	1369.6	1369.9	1370.2	1370.4	1370.7	1371.7
160°	1396.4	1395.7	1394.9	1394.1	1393.3	1393.1	1393.3	1393.6	1393.9	1394.1	1395.1
162.5°	1418.1	1417.5	1416.9	1416.3	1415.7	1415.5	1415.5	1415.6	1415.6	1415.7	1416.9
165°	1446.9	1446.4	1445.9	1445.4	1444.8	1444.7	1445.0	1445.2	1445.5	1445.7	1446.8
167.5°	1471.4	1470.3	1469.3	1468.2	1467.1	1466.6	1466.6	1466.6	1466.6	1466.6	1468.2
170°	1484.5	1483.5	1482.4	1481.4	1480.4	1479.8	1479.8	1479.8	1479.8	1479.8	1481.4
172.5°	1493.9	1492.9	1491.8	1490.8	1489.8	1489.1	1489.1	1489.1	1489.1	1489.1	1490.8
175°	1504.4	1503.4	1502.4	1501.3	1500.3	1499.8	1499.8	1499.8	1499.8	1499.8	1501.3
177.5°	1509.8	1509.0	1508.1	1507.3	1506.5	1506.0	1505.8	1505.6	1505.3	1505.1	1506.4
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333338-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	37.1	37.3	37.6	37.5	37.1	36.7	36.3	35.9
90°	21.4	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	48.5	50.2	51.9	53.1	53.6	54.2	54.8	55.3
95°	94.0	95.8	97.7	98.9	99.4	99.9	100.4	100.9
97.5°	147.3	149.1	150.8	151.8	152.1	152.4	152.7	153.0
100°	184.2	186.6	188.9	190.4	190.9	191.4	192.0	192.5
102.5°	222.2	224.8	227.3	228.9	229.7	230.5	231.2	231.9
105°	283.6	285.2	286.7	287.9	288.7	289.4	290.2	291.0
107.5°	349.8	350.6	351.4	351.8	351.7	351.7	351.6	351.5
110°	395.9	396.7	397.4	397.7	397.4	397.2	396.9	396.7



TEST NUMBER: P333338-840

CATALOG NUMBER: S125DIP-S1270D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	442.0	442.3	442.7	442.6	442.2	441.7	441.2	440.8
115°	512.3	512.0	511.8	511.5	511.3	511.0	510.7	510.5
117.5°	582.7	582.9	583.1	582.7	581.7	580.7	579.6	578.6
120°	630.2	630.2	630.2	629.7	628.6	627.5	626.5	625.5
122.5°	676.7	676.5	676.3	675.8	674.9	674.1	673.3	672.5
125°	745.3	744.8	744.3	743.9	743.7	743.4	743.1	742.9
127.5°	813.4	813.1	812.9	812.5	812.0	811.4	810.9	810.4
130°	858.5	858.2	858.0	857.6	857.1	856.6	856.0	855.5
132.5°	901.7	901.4	901.1	900.7	899.9	899.2	898.5	897.8
135°	968.2	968.2	968.2	967.7	966.5	965.5	964.5	963.4
137.5°	1032.9	1033.2	1033.5	1033.0	1031.7	1030.4	1029.1	1027.7
140°	1073.6	1074.2	1074.7	1074.3	1073.0	1071.7	1070.4	1069.0
142.5°	1113.6	1113.9	1114.2	1113.7	1112.4	1111.2	1109.8	1108.5
145°	1171.1	1171.1	1171.1	1170.7	1170.0	1169.2	1168.4	1167.6
147.5°	1224.6	1225.2	1225.8	1225.2	1223.5	1221.6	1219.9	1218.1
150°	1258.0	1258.0	1258.0	1257.8	1257.2	1256.7	1256.2	1255.7
152.5°	1289.3	1289.9	1290.5	1290.4	1289.5	1288.5	1287.6	1286.7
155°	1334.0	1335.0	1336.2	1336.0	1334.6	1333.3	1332.1	1330.8
157.5°	1372.7	1373.8	1374.8	1374.5	1372.8	1371.1	1369.4	1367.7
160°	1396.2	1397.2	1398.3	1398.2	1396.8	1395.5	1394.2	1393.0
162.5°	1418.3	1419.5	1420.8	1420.6	1419.1	1417.5	1416.0	1414.5
165°	1447.8	1448.9	1450.0	1449.7	1448.1	1446.5	1445.0	1443.4
167.5°	1469.8	1471.4	1472.9	1472.9	1471.3	1469.7	1468.0	1466.4
170°	1482.9	1484.5	1486.0	1485.9	1484.1	1482.3	1480.5	1478.6
172.5°	1492.3	1493.9	1495.4	1495.4	1493.8	1492.2	1490.6	1488.9
175°	1502.9	1504.4	1506.0	1505.9	1504.1	1502.3	1500.4	1498.5
177.5°	1507.6	1508.9	1510.2	1510.1	1508.6	1507.1	1505.7	1504.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)