

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333303-840

Luminaire Tested: **S125DIP-S1270D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333303-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D365U840-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6507.2 lumens  
Efficiency: N/A  
Efficacy: 130.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333303-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333303-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	74	72	70	67
2	95	87	81	75	91	84	78	73	77	72	68	70	67	63	65	62	59	56
3	87	77	69	63	83	74	66	61	68	62	57	62	58	54	57	54	50	47
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41
5	73	61	52	46	70	58	50	45	54	47	42	50	44	40	46	42	38	35
6	67	55	46	40	64	53	45	39	49	42	37	45	40	35	42	37	33	31
7	62	50	41	35	60	48	40	34	44	38	33	41	35	31	38	33	30	27
8	58	45	37	31	55	44	36	31	41	34	29	38	32	28	35	30	27	25
9	54	41	33	28	52	40	33	28	37	31	26	35	29	25	33	28	24	22
10	51	38	31	25	49	37	30	25	35	28	24	32	27	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333303-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.6	2.9
10°-20°	530.1	8.1
20°-30°	782.7	12.0
30°-40°	913.3	14.0
40°-50°	917.2	14.1
50°-60°	805.1	12.4
60°-70°	599.9	9.2
70°-80°	343.0	5.3
80°-90°	100.8	1.5
90°-100°	128.3	2.0
100°-110°	275.8	4.2
110°-120°	258.9	4.0
120°-130°	209.8	3.2
130°-140°	168.4	2.6
140°-150°	127.0	2.0
150°-160°	89.4	1.4
160°-170°	52.7	0.8
170°-180°	17.1	0.3
0°-30°	1500.4	23.1
0°-40°	2413.6	37.1
0°-60°	4136.0	63.6
0°-90°	5179.7	79.6
90°-120°	663.0	10.2
90°-150°	1168.2	18.0
90°-180°	1328.0	20.4
0°-180°	6507.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	0	3	6	8	8	5
95°	12	35	316	143	84	13
105°	40	56	259	510	473	43
115°	72	87	208	448	527	71
125°	100	117	199	356	415	89
135°	117	141	198	299	345	91
145°	136	156	198	247	272	85
155°	156	167	194	219	228	72
165°	170	175	186	197	200	48
175°	177	177	178	180	180	17
180°	177	177	177	177	177	



TEST NUMBER: P333303-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.0	34.1	34.3	34.4	34.5	34.5	34.3	34.2	34.0	33.9	33.9
90°	0.4	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.8	6.1
92.5°	4.3	5.3	8.3	12.7	18.9	29.3	48.8	81.4	116.9	115.0	93.1
95°	11.8	12.1	14.9	18.9	26.8	42.8	81.0	159.6	258.0	316.2	309.4
97.5°	19.6	20.0	22.0	26.0	33.0	44.5	69.8	127.3	230.5	337.7	391.5
100°	24.9	25.7	27.2	31.0	37.9	48.6	69.3	115.6	205.6	322.2	411.5
102.5°	31.0	31.4	32.5	36.8	43.0	53.4	71.8	110.8	186.7	295.2	399.5
105°	40.3	40.3	42.1	45.6	51.4	61.4	77.1	108.9	168.4	258.7	361.2
107.5°	49.5	50.2	51.9	54.8	60.8	69.8	84.9	112.1	160.8	233.7	322.0
110°	56.0	56.8	58.2	61.4	66.8	76.0	90.7	115.3	158.4	222.0	299.8



TEST NUMBER: P333303-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.6	63.3	64.4	67.7	73.0	82.0	96.0	119.3	158.4	215.1	283.3
115°	72.1	72.8	73.9	77.1	82.4	91.4	104.6	125.2	159.6	207.7	265.2
117.5°	80.7	81.7	82.9	86.0	92.2	100.8	113.3	132.1	161.9	204.1	254.4
120°	86.3	87.5	88.9	92.1	98.2	107.0	119.6	136.7	164.2	202.4	248.4
122.5°	92.4	93.1	94.3	97.6	104.1	113.1	125.5	141.8	166.1	201.0	243.3
125°	100.0	100.7	102.4	105.6	112.4	121.7	133.5	148.9	169.6	199.1	236.3
127.5°	105.8	106.9	109.2	113.3	120.5	129.8	141.1	155.2	173.3	198.3	229.8
130°	109.6	110.7	113.5	118.2	125.6	134.9	145.9	159.6	175.6	197.7	225.6
132.5°	112.4	113.8	117.2	122.4	130.2	139.5	150.6	163.3	178.1	197.7	222.2
135°	117.0	118.5	122.8	128.5	136.0	145.6	156.6	168.4	181.7	197.7	218.0
137.5°	122.9	124.0	127.9	133.7	141.1	151.0	161.1	172.3	184.9	198.1	214.4
140°	126.3	127.4	131.7	137.4	144.2	153.8	164.2	174.9	186.3	198.4	212.7
142.5°	130.4	131.1	135.1	140.9	147.3	156.4	166.1	176.3	187.1	198.7	211.3
145°	136.3	137.0	140.6	145.6	152.1	160.3	169.6	178.4	188.0	198.4	209.1
147.5°	142.6	143.0	146.1	150.8	156.3	163.5	171.7	179.8	188.4	197.5	206.9
150°	146.3	147.0	149.6	154.2	159.2	165.2	173.1	180.6	188.4	196.6	205.2
152.5°	150.4	150.8	153.0	157.0	161.8	167.2	174.5	181.2	188.1	195.5	203.2
155°	155.6	155.6	157.7	161.3	164.9	169.9	175.9	181.7	187.3	193.5	199.9
157.5°	160.4	160.3	162.0	165.0	168.1	172.0	177.1	182.0	186.4	191.3	196.7
160°	163.5	163.1	164.5	167.0	169.9	173.1	177.7	182.0	185.6	189.9	194.2
162.5°	166.0	165.7	167.1	169.4	171.6	174.2	178.3	181.8	184.7	188.1	191.9
165°	169.9	169.2	170.3	172.0	173.5	175.6	178.4	181.3	183.5	185.6	188.4
167.5°	172.5	172.1	172.8	173.7	174.7	176.1	178.4	180.5	181.5	183.1	185.1
170°	174.2	173.8	174.2	174.9	175.6	176.6	178.4	179.9	180.6	181.7	183.1
172.5°	175.3	174.7	175.0	175.7	176.1	176.6	178.1	179.4	179.5	180.0	181.1
175°	176.6	175.9	176.3	176.6	176.6	176.6	177.7	178.4	178.1	178.1	178.4
177.5°	177.3	176.7	176.7	177.0	176.7	176.7	177.3	177.6	177.0	177.0	177.3
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333303-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	34.0	34.1	34.1	34.0	33.5	32.9	32.4	31.9
90°	6.5	6.8	7.2	7.9	7.9	7.9	8.2	8.2
92.5°	63.2	45.8	34.5	29.3	24.7	23.8	23.3	22.7
95°	256.6	202.4	158.4	128.5	103.1	92.4	89.6	83.9
97.5°	382.1	344.2	301.3	259.6	237.6	217.6	207.3	202.7
100°	439.0	421.5	384.8	347.6	323.0	297.3	284.1	278.4
102.5°	458.1	468.9	451.3	426.2	399.8	381.5	367.2	362.9
105°	446.9	495.7	511.4	507.6	496.0	484.3	477.2	472.9
107.5°	406.6	471.8	512.1	530.8	536.5	536.5	534.1	531.3
110°	376.9	444.7	495.0	525.3	541.4	548.2	550.7	550.7





TEST NUMBER: P333303-840

CATALOG NUMBER: S125DIP-S1270D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	353.5	417.9	468.8	504.5	528.0	539.7	545.8	548.5
115°	324.1	379.4	428.3	467.2	495.0	512.1	522.1	526.7
117.5°	305.1	352.7	394.9	430.6	458.4	476.2	486.0	488.9
120°	294.8	337.6	376.9	408.3	434.7	451.8	461.5	464.3
122.5°	287.1	326.8	361.7	391.1	414.8	430.4	440.1	442.6
125°	275.9	312.3	343.4	369.0	389.0	403.6	411.5	415.1
127.5°	264.5	298.4	327.4	351.4	369.6	382.5	389.9	391.5
130°	257.3	288.7	316.6	339.8	357.6	369.4	376.6	378.7
132.5°	250.1	279.6	304.9	327.2	345.1	356.8	363.3	365.8
135°	241.0	265.5	288.4	308.7	324.5	336.2	342.6	344.8
137.5°	233.1	253.0	272.0	289.2	303.3	314.0	319.9	322.2
140°	228.7	245.5	262.0	276.9	290.1	299.4	304.8	306.6
142.5°	225.1	239.2	253.4	266.4	277.6	285.5	290.5	292.1
145°	220.3	231.3	242.4	252.0	260.5	266.6	270.5	272.0
147.5°	215.6	224.6	233.2	240.4	247.2	252.1	254.3	255.0
150°	213.1	221.0	227.7	234.1	239.4	243.8	245.2	245.5
152.5°	210.3	217.2	223.4	228.4	232.9	236.3	237.7	238.1
155°	205.9	211.7	216.6	220.6	224.1	226.6	227.7	228.0
157.5°	201.7	206.3	210.3	213.3	216.1	218.1	219.1	219.0
160°	198.8	202.4	205.9	208.4	211.0	212.7	213.4	213.1
162.5°	195.6	198.9	202.0	204.2	206.1	207.5	207.7	207.6
165°	191.3	193.8	195.9	197.7	199.1	199.9	199.9	199.9
167.5°	187.1	188.8	190.5	191.8	192.5	193.1	192.8	192.7
170°	184.9	185.9	187.0	187.7	188.4	188.8	188.8	188.4
172.5°	182.3	183.4	184.2	184.6	184.7	185.4	184.8	184.4
175°	179.6	179.6	180.3	180.3	180.3	180.6	179.9	179.6
177.5°	177.6	177.8	177.8	177.8	177.6	177.8	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0

(END OF REPORT)