

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333537-830

Luminaire Tested: **S125RDIP-S610D810U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333537-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D810U830-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4983.2 lumens  
Efficiency: N/A  
Efficacy: 129.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333537-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333537-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	93	89	85	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	41	39	37	32
3	81	71	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	28	24
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6124	6124	6124
5°	6137	6067	6105
10°	6091	6011	6011
15°	6019	5889	5841
20°	5926	5720	5650
25°	5818	5552	5430
30°	5683	5357	5186
35°	5544	5155	4912
40°	5415	4945	4643
45°	5259	4709	4350
50°	5101	4454	4044
55°	4919	4209	3718
60°	4735	3912	3367
65°	4520	3568	2966
70°	4273	3138	2555
75°	3933	2643	2126
80°	3463	2079	1785
85°	2920	1697	1593



TEST NUMBER: P333537-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.2	1.8
10°-20°	249.2	5.0
20°-30°	361.3	7.3
30°-40°	411.8	8.3
40°-50°	401.4	8.1
50°-60°	337.9	6.8
60°-70°	236.8	4.8
70°-80°	121.7	2.4
80°-90°	32.8	0.7
90°-100°	264.9	5.3
100°-110°	569.6	11.4
110°-120°	534.5	10.7
120°-130°	433.2	8.7
130°-140°	347.7	7.0
140°-150°	262.4	5.3
150°-160°	184.7	3.7
160°-170°	108.8	2.2
170°-180°	35.4	0.7
0°-30°	699.6	14.0
0°-40°	1111.4	22.3
0°-60°	1850.7	37.1
0°-90°	2242.0	45.0
90°-120°	1369.1	27.5
90°-150°	2412.3	48.4
90°-180°	2741.0	55.0
0°-180°	4983.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	944	936	943	942	90
15°	900	895	881	880	874	254
25°	816	805	779	770	762	375
35°	703	685	654	634	623	440
45°	576	554	516	488	476	444
55°	437	413	374	343	330	391
65°	296	271	234	206	194	293
75°	158	136	106	91	85	167
85°	39	27	23	22	22	44
90°	1	7	12	15	17	3
95°	24	72	653	296	173	26
105°	83	116	534	1052	976	88
115°	149	179	429	925	1088	146
125°	206	242	411	736	857	183
135°	242	291	408	616	712	188
145°	282	322	410	510	562	176
155°	321	346	399	451	471	148
165°	351	360	383	406	413	99
175°	365	365	368	372	371	35
180°	366	366	366	366	366	



TEST NUMBER: P333537-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	949.9	949.5	949.1	948.8	948.4	947.5	946.2	945.0	943.7	942.4	943.7
5°	946.7	946.1	945.5	944.8	944.1	943.0	941.2	939.5	937.7	935.9	937.5
7.5°	937.5	936.8	936.2	935.6	935.0	933.7	931.5	929.4	927.4	925.2	926.3
10°	928.8	928.3	927.8	927.4	926.9	925.6	923.3	921.1	918.9	916.6	917.1
12.5°	919.1	918.5	917.8	917.3	916.6	914.8	911.9	908.9	905.9	902.9	903.2
15°	900.2	899.2	898.2	897.3	896.4	894.2	890.9	887.5	884.2	880.8	880.7
17.5°	878.8	877.4	875.9	874.5	873.0	870.2	865.9	861.8	857.5	853.4	852.5
20°	862.2	860.6	859.0	857.4	855.8	852.5	847.4	842.4	837.3	832.2	831.3
22.5°	843.9	842.3	840.7	839.1	837.5	834.1	828.7	823.4	818.0	812.7	811.2
25°	816.4	814.0	811.6	809.3	806.8	802.7	796.8	790.9	785.0	779.1	777.1
27.5°	784.9	782.0	779.1	776.2	773.3	768.7	762.4	756.1	749.8	743.5	740.6
30°	762.0	758.9	755.9	752.9	749.9	745.0	738.3	731.7	725.0	718.3	714.6
32.5°	739.6	736.1	732.5	729.1	725.5	720.3	713.5	706.7	699.8	693.1	689.0
35°	703.2	699.5	695.6	691.8	688.0	682.5	675.3	668.2	661.0	653.8	649.2
37.5°	667.6	662.9	658.3	653.7	649.0	643.0	635.6	628.2	620.9	613.4	607.9
40°	642.3	637.6	632.8	628.0	623.3	617.1	609.4	601.8	594.2	586.5	580.5
42.5°	616.0	611.1	606.2	601.3	596.4	590.0	582.1	574.2	566.4	558.5	552.6
45°	575.8	571.2	566.6	561.9	557.3	550.6	541.9	533.1	524.3	515.6	509.3
47.5°	534.1	529.2	524.3	519.5	514.6	507.7	499.0	490.1	481.4	472.5	466.0
50°	507.7	502.5	497.2	492.0	486.7	479.6	470.5	461.5	452.3	443.3	436.6
52.5°	479.1	473.7	468.3	463.0	457.6	450.6	442.1	433.5	424.9	416.3	409.2
55°	436.9	431.8	426.7	421.6	416.5	409.4	400.6	391.6	382.8	373.8	366.6
57.5°	394.2	388.7	383.2	377.9	372.4	365.3	356.8	348.2	339.6	331.0	324.0
60°	366.6	361.1	355.5	350.0	344.4	337.3	328.7	320.1	311.5	302.9	296.0
62.5°	337.4	332.2	326.8	321.5	316.2	309.2	300.5	291.7	283.0	274.3	267.8
65°	295.8	290.4	284.9	279.6	274.1	267.2	258.7	250.3	241.9	233.5	227.1
67.5°	254.4	248.9	243.6	238.2	232.7	226.0	217.9	209.8	201.7	193.6	187.8
70°	226.3	220.9	215.5	210.1	204.6	197.9	190.0	182.1	174.1	166.2	161.2
72.5°	198.8	193.5	188.2	182.9	177.7	171.3	163.8	156.4	148.9	141.5	137.0
75°	157.6	152.8	148.0	143.3	138.5	132.7	126.0	119.3	112.6	105.9	102.5
77.5°	116.6	112.7	109.0	105.1	101.3	96.7	91.3	86.1	80.7	75.3	72.9
80°	93.1	89.3	85.5	81.6	77.9	73.7	69.2	64.8	60.3	55.9	54.4
82.5°	70.2	66.7	63.3	59.9	56.5	53.2	50.1	47.0	44.0	41.0	40.3
85°	39.4	36.5	33.6	30.8	27.9	26.1	25.3	24.5	23.8	22.9	22.7
87.5°	13.3	12.5	12.0	11.4	10.7	10.6	10.6	10.7	10.7	10.9	11.1
90°	0.8	1.5	2.9	4.4	5.9	7.4	8.1	9.6	10.3	11.8	12.5
92.5°	9.0	10.9	17.1	26.2	38.9	60.4	100.7	168.1	241.4	237.6	192.4
95°	24.3	25.1	30.9	39.0	55.2	88.4	167.3	329.4	532.8	653.0	638.9
97.5°	40.3	41.3	45.4	53.5	68.1	92.0	144.1	263.0	475.8	697.3	808.4
100°	51.6	53.1	56.0	64.1	78.1	100.2	143.0	238.7	424.5	665.5	849.7
102.5°	64.0	64.8	67.2	75.9	88.7	110.3	148.3	228.8	385.6	609.4	825.0
105°	83.3	83.3	87.0	94.3	106.1	126.8	159.2	224.8	347.9	534.3	745.8
107.5°	102.2	103.6	107.2	113.2	125.5	144.0	175.4	231.6	332.0	482.6	665.1
110°	115.7	117.2	120.1	126.8	137.8	156.9	187.2	238.1	327.3	458.4	619.1



TEST NUMBER: P333537-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	129.2	130.7	133.1	139.7	150.8	169.4	198.4	246.3	327.3	444.2	584.8
115°	148.8	150.3	152.6	159.2	170.2	188.7	215.9	258.6	329.4	429.0	547.5
117.5°	166.5	168.8	171.2	177.8	190.3	208.1	233.9	272.9	334.3	421.4	525.3
120°	178.3	180.6	183.5	190.1	202.6	221.1	246.9	282.3	339.0	417.8	512.9
122.5°	190.8	192.4	194.7	201.3	215.1	233.5	259.3	292.8	343.1	414.9	502.3
125°	206.3	207.8	211.5	218.1	232.1	251.3	275.6	307.3	350.1	411.2	487.9
127.5°	218.6	220.8	225.6	233.9	248.8	268.0	291.4	320.6	357.9	409.4	474.6
130°	226.2	228.5	234.3	243.9	259.4	278.6	301.4	329.4	362.6	408.3	465.8
132.5°	232.1	235.0	242.0	252.8	268.8	288.0	310.9	337.1	367.9	408.3	458.7
135°	241.8	244.7	253.5	265.3	280.8	300.7	323.6	347.9	375.1	408.3	450.3
137.5°	253.8	256.0	264.3	276.1	291.2	311.7	332.5	355.8	381.7	409.2	442.8
140°	260.9	263.1	271.9	283.7	297.7	317.6	339.0	361.1	384.7	409.7	439.2
142.5°	269.1	270.8	279.0	290.8	304.3	322.9	343.1	364.1	386.4	410.4	436.3
145°	281.5	283.0	290.4	300.7	314.0	330.9	350.1	368.4	388.4	409.7	431.9
147.5°	294.5	295.4	301.7	311.3	322.8	337.7	354.5	371.2	389.1	407.8	427.3
150°	302.2	303.6	308.8	318.4	328.7	341.2	357.4	372.9	389.1	406.0	423.8
152.5°	310.4	311.3	315.8	324.2	334.0	345.3	360.3	374.1	388.5	403.7	419.6
155°	321.3	321.3	325.7	333.1	340.4	350.8	363.4	375.1	386.9	399.4	412.7
157.5°	331.0	330.9	334.4	340.7	347.2	355.1	365.8	375.9	385.0	395.0	406.2
160°	337.5	336.8	339.8	344.9	350.8	357.4	367.0	375.9	383.2	392.1	401.0
162.5°	342.8	342.1	345.1	349.6	354.3	359.8	368.2	375.2	381.4	388.5	396.2
165°	350.8	349.3	351.6	355.2	358.2	362.6	368.4	374.4	378.8	383.2	389.1
167.5°	356.1	355.3	356.7	358.7	360.8	363.6	368.4	372.6	374.7	378.1	382.2
170°	359.7	358.9	359.7	361.1	362.6	364.8	368.4	371.5	372.9	375.1	378.1
172.5°	362.0	360.7	361.4	362.9	363.7	364.8	367.9	370.2	370.5	371.6	373.9
175°	364.8	363.4	364.1	364.8	364.8	364.8	367.0	368.4	367.8	367.8	368.4
177.5°	366.1	365.0	365.0	365.5	365.0	365.0	366.1	366.7	365.5	365.5	366.1
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333537-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	945.0	946.2	947.5	948.1	948.0	947.8	947.7	947.6
5°	939.1	940.8	942.4	943.0	942.6	942.4	942.1	941.7
7.5°	927.5	928.6	929.7	930.1	929.7	929.3	929.1	928.7
10°	917.6	918.0	918.6	918.6	918.0	917.6	917.1	916.6
12.5°	903.6	904.0	904.3	904.1	903.3	902.7	901.9	901.2
15°	880.5	880.3	880.2	879.4	878.0	876.6	875.2	873.6
17.5°	851.8	850.9	850.2	849.1	848.0	846.8	845.6	844.4
20°	830.6	829.7	829.0	827.8	826.4	825.0	823.6	822.1
22.5°	809.5	807.9	806.4	805.0	803.9	802.7	801.5	800.3
25°	775.1	773.0	770.9	768.9	767.2	765.4	763.7	762.0
27.5°	737.7	734.8	731.9	729.6	727.9	726.2	724.5	722.8
30°	711.0	707.3	703.6	701.1	699.6	698.2	696.8	695.4
32.5°	684.9	681.0	676.9	674.0	672.1	670.3	668.5	666.8
35°	644.6	640.0	635.4	632.0	629.7	627.5	625.3	623.0
37.5°	602.4	596.8	591.3	587.4	585.2	583.2	581.0	578.8
40°	574.4	568.4	562.3	558.4	556.5	554.5	552.6	550.7
42.5°	546.9	541.0	535.3	530.9	528.2	525.4	522.5	519.8
45°	502.8	496.5	490.1	485.8	483.4	481.0	478.6	476.3
47.5°	459.4	452.8	446.3	441.7	439.0	436.4	433.8	431.1
50°	429.9	423.2	416.5	412.0	409.6	407.3	404.8	402.5
52.5°	402.0	394.7	387.6	382.8	380.4	378.1	375.6	373.2
55°	359.5	352.3	345.2	340.4	337.8	335.3	332.7	330.2
57.5°	317.0	310.0	303.0	298.3	296.1	293.8	291.6	289.4
60°	288.9	281.9	274.9	270.2	267.9	265.4	263.1	260.7
62.5°	261.3	254.8	248.3	243.8	241.5	239.1	236.7	234.3
65°	220.7	214.3	208.0	203.6	201.2	198.9	196.4	194.1
67.5°	182.0	176.2	170.3	166.5	164.6	162.7	160.7	158.8
70°	156.3	151.4	146.4	143.0	141.1	139.2	137.2	135.3
72.5°	132.4	127.8	123.3	120.4	119.1	117.8	116.6	115.3
75°	99.0	95.5	92.0	89.6	88.6	87.5	86.3	85.2
77.5°	70.4	68.0	65.5	63.9	63.1	62.2	61.5	60.6
80°	53.0	51.6	50.1	49.3	48.9	48.6	48.3	48.0
82.5°	39.6	38.9	38.3	37.9	37.7	37.5	37.3	37.1
85°	22.6	22.4	22.2	22.1	22.0	21.8	21.7	21.5
87.5°	11.2	11.4	11.5	11.8	11.7	11.5	11.5	11.4
90°	13.3	14.0	14.7	16.2	16.2	16.2	17.0	17.0
92.5°	130.6	94.8	71.4	60.4	51.0	49.2	48.2	47.0
95°	529.9	417.8	327.3	265.3	213.0	190.9	185.0	173.1
97.5°	789.2	710.6	622.3	536.2	490.7	449.4	428.0	418.6
100°	906.4	870.3	794.5	717.8	666.9	613.9	586.6	574.9
102.5°	945.9	968.3	931.8	880.0	825.6	787.8	758.2	749.3
105°	922.7	1023.7	1056.1	1048.0	1024.4	1000.0	985.3	976.5
107.5°	839.5	974.3	1057.5	1096.0	1108.0	1107.8	1103.0	1097.0
110°	778.3	918.2	1022.2	1084.8	1117.9	1132.0	1137.2	1137.2





TEST NUMBER: P333537-830

CATALOG NUMBER: S125RDIP-S610D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	729.9	862.8	967.9	1041.8	1090.2	1114.3	1127.1	1132.5
115°	669.2	783.4	884.4	964.7	1022.2	1057.5	1078.2	1087.8
117.5°	630.0	728.4	815.4	889.1	946.6	983.1	1003.6	1009.5
120°	608.7	697.2	778.3	843.1	897.6	933.0	952.9	958.8
122.5°	592.9	674.8	747.0	807.8	856.4	888.8	908.7	914.0
125°	569.7	644.9	709.0	762.0	803.3	833.5	849.7	857.1
127.5°	546.1	616.2	676.1	725.8	763.2	789.9	805.2	808.4
130°	531.3	596.3	653.7	701.6	738.5	762.8	777.5	781.9
132.5°	516.6	577.3	629.5	675.6	712.5	736.8	750.4	755.4
135°	497.5	548.3	595.5	637.4	669.9	694.2	707.5	711.9
137.5°	481.3	522.4	561.6	597.2	626.3	648.4	660.6	665.5
140°	472.4	507.0	540.9	571.8	599.2	618.3	629.3	633.0
142.5°	464.8	494.1	523.2	550.1	573.3	589.5	599.9	602.9
145°	454.7	477.6	500.4	520.3	538.0	550.5	558.6	561.6
147.5°	445.3	463.8	481.4	496.4	510.4	520.5	525.2	526.5
150°	440.0	456.2	470.1	483.4	494.6	503.3	506.3	507.0
152.5°	434.0	448.6	461.4	471.6	481.0	488.0	491.0	491.7
155°	425.3	437.1	447.3	455.4	462.8	468.0	470.1	470.9
157.5°	416.4	426.1	434.0	440.5	446.2	450.4	452.5	452.3
160°	410.5	417.8	425.3	430.4	435.5	439.2	440.7	440.0
162.5°	404.0	410.8	417.0	421.5	425.6	428.6	429.0	428.8
165°	395.0	400.2	404.6	408.3	411.2	412.7	412.7	412.7
167.5°	386.4	389.8	393.2	395.9	397.4	398.7	398.1	397.9
170°	381.7	384.0	386.2	387.7	389.1	389.8	389.8	389.1
172.5°	376.5	378.6	380.3	381.2	381.4	382.8	381.6	380.9
175°	370.7	370.7	372.2	372.2	372.2	372.9	371.5	370.7
177.5°	366.7	367.3	367.3	367.3	366.7	367.3	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5

(END OF REPORT)