

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333571-830

Luminaire Tested: **S125RDIP-S850D1035U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333571-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1035U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6963.0 lumens
Efficiency: N/A
Efficacy: 133.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333571-830

CATALOG NUMBER: S125RDIP-S850D1035U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333571-830

CATALOG NUMBER: S125RDIP-S850D1035U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16
8	53	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8371	8371	8371
5°	8390	8294	8345
10°	8326	8217	8217
15°	8227	8050	7985
20°	8100	7818	7724
25°	7953	7590	7422
30°	7767	7322	7088
35°	7579	7046	6714
40°	7403	6759	6347
45°	7188	6437	5945
50°	6973	6089	5528
55°	6723	5754	5082
60°	6473	5349	4602
65°	6178	4876	4053
70°	5840	4288	3493
75°	5375	3616	2907
80°	4731	2838	2440
85°	3987	2319	2179



TEST NUMBER: P333571-830

CATALOG NUMBER: S125RDIP-S850D1035U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.9	1.8
10°-20°	340.6	4.9
20°-30°	493.9	7.1
30°-40°	562.9	8.1
40°-50°	548.6	7.9
50°-60°	461.8	6.6
60°-70°	323.7	4.6
70°-80°	166.4	2.4
80°-90°	44.7	0.6
90°-100°	46.1	0.7
100°-110°	284.3	4.1
110°-120°	515.7	7.4
120°-130°	661.8	9.5
130°-140°	711.8	10.2
140°-150°	668.2	9.6
150°-160°	540.5	7.8
160°-170°	349.6	5.0
170°-180°	120.6	1.7
0°-30°	956.3	13.7
0°-40°	1519.2	21.8
0°-60°	2529.7	36.3
0°-90°	3064.5	44.0
90°-120°	846.1	12.2
90°-150°	2887.9	41.5
90°-180°	3899.0	56.0
0°-180°	6963.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1296	1296	1296	1296	1296	
5°	1294	1290	1279	1289	1287	123
15°	1230	1224	1204	1203	1194	347
25°	1116	1100	1065	1052	1042	513
35°	961	937	894	866	852	602
45°	787	757	705	667	651	607
55°	597	564	511	468	451	534
65°	404	370	319	281	265	400
75°	215	185	145	124	116	228
85°	54	37	31	30	29	60
90°	1	8	15	20	23	5
95°	54	49	15	20	20	68
105°	277	280	280	280	280	293
115°	520	524	525	521	516	515
125°	739	745	745	742	739	660
135°	921	927	925	923	918	710
145°	1068	1070	1070	1071	1065	668
155°	1176	1171	1173	1175	1168	542
165°	1241	1236	1237	1242	1235	351
175°	1270	1264	1265	1271	1264	121
180°	1270	1270	1270	1270	1270	



TEST NUMBER: P333571-830

CATALOG NUMBER: S125RDIP-S850D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1298.4	1297.9	1297.3	1296.8	1296.3	1295.1	1293.5	1291.7	1290.0	1288.2	1290.0
5°	1294.1	1293.3	1292.3	1291.5	1290.6	1289.0	1286.6	1284.2	1281.8	1279.4	1281.6
7.5°	1281.4	1280.5	1279.7	1278.8	1278.1	1276.2	1273.4	1270.5	1267.6	1264.7	1266.2
10°	1269.6	1268.9	1268.3	1267.6	1267.0	1265.2	1262.2	1259.0	1256.0	1253.0	1253.6
12.5°	1256.3	1255.5	1254.6	1253.9	1253.0	1250.6	1246.4	1242.4	1238.3	1234.2	1234.6
15°	1230.5	1229.2	1227.9	1226.5	1225.2	1222.3	1217.8	1213.1	1208.6	1204.0	1203.8
17.5°	1201.3	1199.3	1197.3	1195.3	1193.3	1189.4	1183.6	1177.9	1172.1	1166.4	1165.4
20°	1178.6	1176.4	1174.2	1172.1	1169.9	1165.3	1158.4	1151.4	1144.4	1137.5	1136.4
22.5°	1153.5	1151.3	1149.1	1147.0	1144.8	1140.1	1132.7	1125.5	1118.1	1110.9	1108.7
25°	1116.0	1112.7	1109.4	1106.2	1102.9	1097.2	1089.2	1081.1	1073.1	1065.1	1062.2
27.5°	1072.9	1068.9	1065.0	1061.0	1057.1	1050.7	1042.2	1033.5	1024.9	1016.2	1012.3
30°	1041.5	1037.4	1033.3	1029.2	1025.0	1018.3	1009.3	1000.1	991.0	981.8	976.9
32.5°	1011.0	1006.2	1001.4	996.6	991.6	984.6	975.3	966.0	956.7	947.3	941.9
35°	961.3	956.0	950.8	945.6	940.4	932.8	923.1	913.3	903.5	893.7	887.4
37.5°	912.5	906.2	899.8	893.4	887.1	878.9	868.8	858.7	848.6	838.5	830.9
40°	878.1	871.6	865.0	858.5	852.0	843.5	833.0	822.6	812.2	801.7	793.4
42.5°	842.1	835.4	828.7	821.9	815.2	806.5	795.7	784.9	774.1	763.4	755.4
45°	787.0	780.7	774.4	768.1	761.8	752.6	740.6	728.8	716.8	704.8	696.1
47.5°	730.1	723.4	716.7	710.1	703.4	694.1	682.0	670.0	657.9	645.8	636.9
50°	694.0	686.8	679.7	672.5	665.3	655.5	643.1	630.7	618.3	606.0	596.8
52.5°	654.9	647.5	640.2	632.8	625.5	616.0	604.3	592.6	580.8	569.1	559.3
55°	597.1	590.1	583.2	576.3	569.3	559.7	547.5	535.4	523.2	511.0	501.1
57.5°	538.8	531.3	523.9	516.4	509.1	499.5	487.7	475.9	464.2	452.4	442.9
60°	501.1	493.6	486.0	478.3	470.7	461.1	449.3	437.5	425.8	414.1	404.5
62.5°	461.3	454.0	446.8	439.4	432.2	422.6	410.7	398.8	386.8	374.9	366.1
65°	404.3	396.9	389.5	382.1	374.7	365.2	353.7	342.1	330.6	319.1	310.4
67.5°	347.7	340.3	332.9	325.6	318.1	308.9	297.8	286.8	275.8	264.7	256.7
70°	309.3	301.9	294.5	287.1	279.7	270.6	259.8	248.8	238.0	227.1	220.4
72.5°	271.7	264.5	257.3	250.1	242.9	234.1	223.9	213.8	203.6	193.4	187.2
75°	215.4	208.9	202.3	195.8	189.3	181.4	172.3	163.2	154.0	144.9	140.1
77.5°	159.4	154.1	148.9	143.7	138.5	132.2	124.9	117.6	110.3	103.0	99.6
80°	127.2	122.1	116.8	111.6	106.4	100.8	94.6	88.5	82.5	76.3	74.4
82.5°	96.0	91.2	86.5	81.8	77.1	72.7	68.5	64.4	60.1	56.0	55.0
85°	53.8	50.0	46.0	42.1	38.2	35.6	34.6	33.5	32.4	31.3	31.1
87.5°	18.2	17.3	16.4	15.6	14.7	14.3	14.4	14.5	14.6	14.8	15.0
90°	0.9	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1
92.5°	14.5	13.3	12.2	10.9	9.8	9.9	11.1	12.4	13.8	15.1	16.1
95°	53.6	53.0	52.4	51.7	51.2	46.8	38.9	30.9	23.0	15.1	16.1
97.5°	112.0	113.1	114.2	115.4	116.5	109.2	93.5	77.8	62.0	46.3	40.4
100°	157.1	157.8	158.4	159.0	159.7	160.4	161.3	162.1	162.9	163.7	132.6
102.5°	203.1	203.9	204.7	205.5	206.2	206.9	207.5	207.9	208.4	209.0	203.0
105°	276.6	277.5	278.3	279.2	280.0	280.4	280.4	280.4	280.4	280.4	280.4
107.5°	353.1	353.1	353.1	353.1	353.1	353.3	353.7	354.1	354.6	355.0	355.1
110°	402.7	402.7	402.7	402.7	402.7	403.0	403.4	403.9	404.3	404.6	404.1



TEST NUMBER: P333571-830

CATALOG NUMBER: S125RDIP-S850D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	449.5	450.0	450.4	451.0	451.5	451.9	452.1	452.3	452.6	452.9	452.0
115°	519.5	520.6	521.6	522.6	523.7	524.3	524.5	524.7	524.9	525.1	524.3
117.5°	591.9	591.9	591.8	591.8	591.8	592.2	593.0	593.7	594.6	595.3	594.3
120°	637.2	636.9	636.7	636.5	636.3	636.5	637.2	637.7	638.4	639.0	638.6
122.5°	677.0	677.8	678.6	679.4	680.2	680.7	681.1	681.4	681.6	681.9	681.5
125°	738.8	740.2	741.7	743.2	744.6	745.4	745.4	745.4	745.4	745.4	744.5
127.5°	797.7	798.7	799.7	800.8	801.8	802.3	802.2	802.1	801.9	801.8	801.3
130°	833.8	834.9	835.9	837.0	838.0	838.6	838.9	839.1	839.2	839.4	838.9
132.5°	870.0	871.2	872.4	873.5	874.8	875.2	874.7	874.3	873.8	873.4	873.2
135°	921.3	922.6	923.9	925.1	926.3	926.8	926.3	926.0	925.5	925.1	924.6
137.5°	968.6	969.7	970.7	971.9	972.9	973.3	972.9	972.5	972.1	971.8	971.9
140°	999.5	999.8	1000.3	1000.7	1001.1	1001.3	1001.0	1000.8	1000.6	1000.4	1000.8
142.5°	1027.3	1027.6	1027.8	1028.0	1028.3	1028.6	1028.9	1029.2	1029.4	1029.7	1029.8
145°	1068.2	1068.6	1068.9	1069.4	1069.8	1070.1	1070.1	1070.1	1070.1	1070.1	1070.3
147.5°	1103.9	1103.8	1103.7	1103.6	1103.5	1103.6	1103.9	1104.2	1104.4	1104.7	1104.9
150°	1126.5	1126.1	1125.7	1125.2	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5	1126.9
152.5°	1148.3	1147.5	1146.5	1145.6	1144.6	1144.4	1144.8	1145.2	1145.7	1146.0	1146.5
155°	1176.4	1175.2	1173.8	1172.6	1171.4	1170.9	1171.4	1171.8	1172.1	1172.6	1173.3
157.5°	1198.0	1197.2	1196.6	1195.8	1195.0	1194.7	1194.7	1194.8	1194.8	1194.9	1195.5
160°	1213.1	1211.8	1210.6	1209.3	1208.1	1207.5	1207.8	1208.0	1208.2	1208.3	1209.2
162.5°	1225.1	1223.9	1222.6	1221.3	1220.1	1219.6	1219.7	1220.0	1220.2	1220.4	1221.6
165°	1241.3	1240.0	1238.8	1237.6	1236.3	1235.8	1236.0	1236.1	1236.4	1236.6	1237.8
167.5°	1253.4	1252.1	1250.8	1249.4	1248.2	1247.6	1247.8	1248.0	1248.2	1248.5	1250.0
170°	1260.1	1258.7	1257.2	1255.7	1254.2	1253.7	1253.9	1254.1	1254.2	1254.5	1256.1
172.5°	1264.6	1263.2	1261.7	1260.3	1258.8	1258.3	1258.6	1259.0	1259.3	1259.7	1261.2
175°	1269.5	1268.3	1267.1	1265.7	1264.5	1264.0	1264.2	1264.4	1264.6	1264.8	1266.5
177.5°	1271.8	1270.8	1269.8	1268.8	1267.8	1267.3	1267.5	1267.7	1267.9	1268.0	1269.2
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333571-830

CATALOG NUMBER: S125RDIP-S850D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1291.7	1293.5	1295.1	1296.0	1295.8	1295.6	1295.4	1295.2
5°	1283.7	1285.9	1288.1	1289.0	1288.5	1288.1	1287.7	1287.2
7.5°	1267.8	1269.3	1270.8	1271.3	1270.8	1270.4	1269.9	1269.4
10°	1254.2	1254.9	1255.6	1255.6	1254.9	1254.2	1253.6	1253.0
12.5°	1235.1	1235.6	1236.1	1235.9	1234.8	1233.8	1232.8	1231.8
15°	1203.6	1203.3	1203.2	1202.1	1200.1	1198.2	1196.2	1194.2
17.5°	1164.2	1163.2	1162.1	1160.7	1159.1	1157.5	1155.9	1154.3
20°	1135.3	1134.2	1133.1	1131.6	1129.6	1127.7	1125.7	1123.8
22.5°	1106.5	1104.5	1102.3	1100.4	1098.8	1097.2	1095.6	1094.0
25°	1059.4	1056.6	1053.8	1051.1	1048.7	1046.3	1044.0	1041.5
27.5°	1008.3	1004.4	1000.4	997.3	995.0	992.7	990.4	988.1
30°	971.9	966.9	961.8	958.4	956.4	954.4	952.4	950.5
32.5°	936.3	930.8	925.3	921.2	918.8	916.3	913.8	911.3
35°	881.1	874.8	868.5	863.8	860.7	857.7	854.7	851.6
37.5°	823.4	815.8	808.2	803.0	800.0	797.0	794.1	791.2
40°	785.1	776.9	768.6	763.2	760.6	758.0	755.4	752.8
42.5°	747.5	739.6	731.7	725.8	722.0	718.1	714.3	710.5
45°	687.4	678.7	670.0	664.0	660.7	657.5	654.2	650.9
47.5°	627.9	619.0	610.0	603.7	600.1	596.5	592.9	589.3
50°	587.7	578.5	569.4	563.2	560.0	556.7	553.4	550.2
52.5°	549.5	539.6	529.8	523.2	520.0	516.7	513.5	510.2
55°	491.4	481.6	471.8	465.1	461.8	458.3	454.8	451.3
57.5°	433.3	423.8	414.2	407.8	404.7	401.6	398.6	395.5
60°	394.9	385.3	375.8	369.4	366.1	362.9	359.6	356.3
62.5°	357.1	348.3	339.4	333.4	330.1	326.8	323.6	320.3
65°	301.7	293.0	284.3	278.3	275.0	271.8	268.5	265.2
67.5°	248.7	240.8	232.8	227.5	225.0	222.3	219.7	217.2
70°	213.6	206.9	200.1	195.5	192.8	190.2	187.7	185.0
72.5°	181.0	174.7	168.5	164.6	162.8	161.1	159.4	157.6
75°	135.3	130.5	125.7	122.6	121.0	119.5	118.0	116.5
77.5°	96.2	92.9	89.5	87.4	86.2	85.1	84.0	82.8
80°	72.5	70.5	68.5	67.3	66.9	66.4	66.0	65.6
82.5°	54.2	53.3	52.3	51.7	51.5	51.3	51.0	50.7
85°	30.9	30.6	30.4	30.3	30.0	29.8	29.6	29.4
87.5°	15.2	15.4	15.6	15.6	15.6	15.6	15.6	15.5
90°	17.2	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	17.2	18.2	19.2	19.9	20.2	20.5	20.8	21.1
95°	17.2	18.2	19.2	19.8	19.8	19.8	19.8	19.8
97.5°	34.5	28.7	22.7	19.8	19.8	19.8	19.8	19.8
100°	101.4	70.3	39.1	23.1	22.2	21.4	20.6	19.8
102.5°	197.1	191.2	185.3	175.3	161.1	146.8	132.6	118.4
105°	280.4	280.4	280.4	280.3	280.1	279.9	279.7	279.5
107.5°	355.1	355.2	355.2	354.9	354.2	353.6	353.0	352.3
110°	403.4	402.7	402.2	402.0	402.2	402.4	402.6	402.7



TEST NUMBER: P333571-830

CATALOG NUMBER: S125RDIP-S850D1035U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.3	450.4	449.7	449.1	448.8	448.6	448.3	448.0
115°	523.5	522.6	521.8	520.8	519.5	518.2	517.0	515.8
117.5°	593.1	592.1	591.0	590.1	589.7	589.1	588.5	588.0
120°	638.2	637.7	637.3	636.6	635.6	634.5	633.5	632.4
122.5°	681.1	680.7	680.2	679.4	678.3	677.0	675.8	674.6
125°	743.7	742.8	742.0	741.3	740.6	740.0	739.4	738.8
127.5°	800.9	800.4	799.9	799.0	797.4	795.9	794.4	792.8
130°	838.2	837.5	837.0	836.1	835.1	834.1	833.0	831.9
132.5°	873.1	873.0	872.8	872.2	871.2	870.2	869.1	868.1
135°	924.3	923.9	923.4	922.6	921.3	920.1	918.8	917.6
137.5°	971.9	972.0	972.1	971.6	970.5	969.4	968.4	967.2
140°	1001.3	1001.6	1002.0	1001.6	1000.4	999.1	997.9	996.6
142.5°	1029.9	1030.0	1030.1	1029.5	1028.2	1027.0	1025.8	1024.4
145°	1070.4	1070.6	1070.8	1070.4	1069.1	1067.8	1066.6	1065.4
147.5°	1105.1	1105.4	1105.7	1105.0	1103.5	1102.0	1100.5	1099.0
150°	1127.4	1127.8	1128.1	1127.6	1125.9	1124.2	1122.5	1120.9
152.5°	1146.9	1147.4	1147.7	1147.2	1145.7	1144.2	1142.6	1141.1
155°	1173.8	1174.5	1175.2	1174.6	1172.9	1171.2	1169.6	1167.9
157.5°	1196.2	1196.8	1197.5	1197.0	1195.3	1193.6	1191.9	1190.3
160°	1210.0	1210.9	1211.7	1211.3	1209.7	1208.0	1206.3	1204.6
162.5°	1222.8	1223.9	1225.1	1224.7	1222.9	1221.1	1219.3	1217.4
165°	1239.1	1240.4	1241.6	1241.4	1239.7	1238.0	1236.4	1234.7
167.5°	1251.5	1253.0	1254.5	1254.3	1252.5	1250.6	1248.7	1246.8
170°	1257.8	1259.5	1261.2	1261.0	1259.1	1257.4	1255.5	1253.6
172.5°	1262.7	1264.2	1265.7	1265.6	1263.7	1261.8	1259.9	1258.1
175°	1268.2	1269.9	1271.5	1271.4	1269.5	1267.6	1265.7	1263.9
177.5°	1270.4	1271.6	1272.7	1272.6	1271.3	1270.0	1268.7	1267.2
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5

(END OF REPORT)