

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333140-840

Luminaire Tested: **S125DIP-S375D810U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333140-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D810U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4368.8 lumens  
Efficiency: N/A  
Efficacy: 140.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333140-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333140-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	94	90	86	83	85	82	78	75	66	63	61	51	50	48	37	37	36	30
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	71	63	57	52	51	46	43	39	36	34	29	27	26	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3810	3810	3810
5°	3818	3782	3806
10°	3796	3756	3777
15°	3754	3710	3726
20°	3696	3647	3654
25°	3632	3572	3569
30°	3554	3491	3473
35°	3470	3404	3356
40°	3384	3309	3262
45°	3291	3222	3159
50°	3189	3118	3024
55°	3090	3001	2916
60°	2971	2882	2780
65°	2832	2740	2647
70°	2696	2574	2485
75°	2458	2376	2293
80°	2187	2153	2101
85°	1904	1941	1830



TEST NUMBER: P333140-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.6	1.3
10°-20°	157.1	3.6
20°-30°	232.0	5.3
30°-40°	270.7	6.2
40°-50°	271.9	6.2
50°-60°	238.7	5.5
60°-70°	177.8	4.1
70°-80°	101.7	2.3
80°-90°	31.8	0.7
90°-100°	68.0	1.6
100°-110°	200.7	4.6
110°-120°	339.9	7.8
120°-130°	447.4	10.2
130°-140°	501.3	11.5
140°-150°	491.3	11.2
150°-160°	412.7	9.4
160°-170°	274.3	6.3
170°-180°	96.0	2.2
0°-30°	444.7	10.2
0°-40°	715.5	16.4
0°-60°	1226.0	28.1
0°-90°	1537.3	35.2
90°-120°	608.6	13.9
90°-150°	2048.6	46.9
90°-180°	2832.0	64.8
0°-180°	4368.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	589	588	583	587	587	56
15°	562	560	555	557	557	158
25°	510	507	501	502	501	234
35°	440	438	432	429	426	275
45°	360	358	353	348	346	278
55°	274	273	266	262	259	245
65°	185	184	179	175	173	184
75°	98	98	95	94	92	105
85°	26	26	26	26	25	29
90°	1	7	13	17	19	4
95°	51	53	61	66	68	55
105°	180	184	189	193	196	192
115°	340	343	345	344	344	336
125°	497	501	502	501	500	445
135°	646	650	652	651	648	498
145°	782	786	788	788	786	489
155°	895	895	896	899	895	412
165°	974	972	973	976	971	275
175°	1012	1009	1009	1013	1008	96
180°	1015	1015	1015	1015	1015	



TEST NUMBER: P333140-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	591.4	591.2	591.0	590.7	590.5	589.9	589.1	588.2	587.4	586.5	587.4
5°	589.0	588.8	588.5	588.3	588.1	587.5	586.5	585.5	584.4	583.4	584.3
7.5°	583.6	583.4	583.2	583.0	582.8	582.1	581.0	579.8	578.7	577.5	578.5
10°	578.8	578.6	578.3	578.1	577.9	577.2	576.1	574.9	573.8	572.7	573.5
12.5°	572.8	572.4	572.0	571.7	571.3	570.6	569.5	568.5	567.3	566.3	566.9
15°	561.5	561.2	560.9	560.6	560.2	559.5	558.4	557.2	556.0	554.9	555.4
17.5°	548.5	548.1	547.5	547.1	546.6	545.8	544.6	543.5	542.3	541.1	541.8
20°	537.7	537.5	537.2	537.0	536.8	536.0	534.7	533.3	532.0	530.7	531.4
22.5°	526.8	526.4	526.0	525.7	525.3	524.5	523.2	522.0	520.7	519.5	520.0
25°	509.7	509.2	508.6	508.1	507.6	506.6	505.3	503.9	502.6	501.3	501.5
27.5°	489.6	489.3	489.0	488.7	488.4	487.5	486.1	484.7	483.3	481.9	482.0
30°	476.6	476.3	475.8	475.5	475.2	474.3	472.8	471.2	469.7	468.1	467.9
32.5°	462.3	461.8	461.4	460.9	460.4	459.5	458.1	456.7	455.3	453.9	453.5
35°	440.1	439.7	439.3	438.9	438.5	437.5	436.1	434.6	433.1	431.7	431.2
37.5°	417.1	416.6	416.1	415.5	415.0	414.0	412.6	411.3	409.9	408.6	407.8
40°	401.4	400.8	400.3	399.8	399.3	398.3	396.9	395.5	393.9	392.5	391.6
42.5°	384.6	384.2	383.7	383.2	382.8	381.9	380.4	379.0	377.5	376.1	375.3
45°	360.3	359.9	359.5	359.1	358.6	357.8	356.6	355.4	354.1	352.8	351.6
47.5°	334.2	334.2	334.2	334.3	334.3	333.6	332.0	330.5	329.0	327.5	326.3
50°	317.4	317.1	316.8	316.4	316.1	315.4	314.1	312.9	311.6	310.3	309.0
52.5°	300.2	299.9	299.7	299.5	299.3	298.5	297.2	295.9	294.5	293.2	292.1
55°	274.4	274.1	273.8	273.5	273.2	272.3	270.8	269.4	267.9	266.5	265.6
57.5°	247.3	247.1	246.9	246.8	246.6	245.9	244.7	243.5	242.3	241.1	239.8
60°	230.0	229.6	229.2	228.8	228.4	227.6	226.5	225.4	224.2	223.1	222.1
62.5°	212.2	211.9	211.5	211.2	210.9	210.2	209.2	208.2	207.2	206.3	205.2
65°	185.3	185.1	184.9	184.7	184.5	183.8	182.7	181.5	180.4	179.3	178.2
67.5°	159.3	158.9	158.3	157.9	157.5	156.8	156.0	155.1	154.3	153.5	152.7
70°	142.8	142.3	141.8	141.3	140.8	140.0	139.1	138.1	137.2	136.3	135.6
72.5°	124.9	124.5	124.2	123.8	123.5	123.0	122.4	121.8	121.2	120.6	119.9
75°	98.5	98.3	98.1	97.9	97.7	97.3	96.7	96.2	95.7	95.2	94.9
77.5°	74.1	74.0	73.9	73.8	73.8	73.6	73.3	73.0	72.7	72.4	72.2
80°	58.8	58.8	58.8	58.8	58.8	58.7	58.5	58.3	58.1	57.9	57.8
82.5°	45.3	45.2	45.0	44.8	44.7	44.6	44.5	44.5	44.4	44.4	44.2
85°	25.7	25.8	25.9	26.0	26.1	26.2	26.2	26.2	26.2	26.2	26.1
87.5°	10.2	10.5	10.8	11.1	11.4	11.6	11.7	11.9	12.1	12.2	12.4
90°	0.8	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5
92.5°	19.1	20.1	21.1	22.0	23.0	24.2	25.8	27.3	28.8	30.3	31.5
95°	51.3	51.7	52.0	52.4	52.7	53.8	55.5	57.3	59.1	60.8	62.0
97.5°	85.3	85.4	85.5	85.7	85.8	87.2	89.6	92.0	94.4	96.8	98.0
100°	110.6	110.6	110.6	110.6	110.6	111.7	114.0	116.2	118.6	120.8	122.4
102.5°	137.7	138.5	139.2	139.9	140.6	141.5	142.6	143.8	144.9	146.1	147.8
105°	180.1	181.0	181.8	182.7	183.6	184.5	185.6	186.6	187.6	188.7	189.8
107.5°	226.8	227.6	228.5	229.4	230.4	231.2	232.0	232.8	233.6	234.4	234.9
110°	259.0	259.9	260.7	261.7	262.6	263.3	263.8	264.3	264.8	265.3	265.9



TEST NUMBER: P333140-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	291.9	292.4	292.8	293.3	293.7	294.3	294.9	295.6	296.3	296.9	297.2
115°	340.3	341.0	341.7	342.4	343.2	343.7	344.1	344.4	344.8	345.1	344.9
117.5°	389.0	389.3	389.6	389.9	390.2	390.6	390.9	391.2	391.5	391.8	391.9
120°	419.3	420.2	421.1	421.9	422.8	423.3	423.5	423.7	423.8	424.0	424.0
122.5°	452.1	452.5	452.8	453.1	453.4	453.8	454.2	454.7	455.1	455.7	455.4
125°	496.7	497.8	498.8	499.9	500.9	501.5	501.7	501.9	502.0	502.2	501.9
127.5°	544.1	544.7	545.2	545.8	546.4	546.8	547.0	547.2	547.5	547.8	547.5
130°	572.5	573.4	574.3	575.1	576.0	576.6	576.9	577.3	577.6	578.0	577.8
132.5°	601.0	602.4	603.8	605.2	606.7	607.3	607.3	607.2	607.1	607.1	606.9
135°	645.9	647.0	648.0	649.1	650.2	650.8	651.0	651.2	651.3	651.5	651.5
137.5°	688.3	689.3	690.3	691.4	692.4	693.1	693.5	693.8	694.2	694.6	694.8
140°	715.5	716.3	717.2	718.1	718.9	719.6	720.1	720.7	721.2	721.8	722.2
142.5°	742.7	743.4	744.1	744.8	745.6	746.3	746.9	747.6	748.2	748.9	749.1
145°	782.5	783.3	784.0	784.7	785.4	786.0	786.5	787.0	787.6	788.1	788.1
147.5°	819.5	819.9	820.3	820.7	821.0	821.4	821.9	822.3	822.7	823.1	823.5
150°	844.1	843.9	843.8	843.6	843.4	843.7	844.4	845.2	845.9	846.6	846.6
152.5°	864.3	864.6	864.8	865.2	865.4	865.7	865.9	866.2	866.5	866.8	867.2
155°	895.4	895.4	895.4	895.4	895.4	895.5	895.8	896.0	896.1	896.3	897.0
157.5°	923.3	922.9	922.5	922.1	921.7	921.6	921.8	922.0	922.1	922.3	923.0
160°	939.7	939.2	938.7	938.2	937.6	937.5	937.6	937.8	938.0	938.2	938.9
162.5°	954.2	953.8	953.4	953.1	952.7	952.5	952.5	952.6	952.6	952.7	953.5
165°	973.7	973.3	973.0	972.6	972.3	972.2	972.3	972.5	972.7	972.9	973.6
167.5°	990.1	989.4	988.7	988.0	987.2	986.9	986.9	986.9	986.9	986.9	988.0
170°	999.0	998.3	997.5	996.8	996.1	995.7	995.7	995.7	995.7	995.7	996.8
172.5°	1005.2	1004.5	1003.8	1003.1	1002.4	1002.1	1002.1	1002.1	1002.1	1002.1	1003.1
175°	1012.4	1011.7	1011.0	1010.3	1009.6	1009.2	1009.2	1009.2	1009.2	1009.2	1010.3
177.5°	1016.0	1015.4	1014.9	1014.3	1013.7	1013.4	1013.3	1013.1	1013.0	1012.8	1013.7
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333140-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	588.2	589.1	589.9	590.3	590.2	590.1	590.1	590.0
5°	585.2	586.2	587.1	587.5	587.4	587.3	587.2	587.1
7.5°	579.4	580.3	581.2	581.6	581.5	581.4	581.3	581.2
10°	574.3	575.1	576.0	576.3	576.2	576.1	576.0	575.9
12.5°	567.6	568.4	569.0	569.3	569.3	569.3	569.3	569.2
15°	555.9	556.4	557.0	557.2	557.2	557.2	557.2	557.2
17.5°	542.4	543.0	543.7	543.7	543.2	542.7	542.2	541.7
20°	532.1	532.8	533.5	533.7	533.1	532.6	532.1	531.6
22.5°	520.4	520.9	521.4	521.4	521.1	520.7	520.4	520.0
25°	501.7	501.9	502.1	502.0	501.7	501.4	501.1	500.8
27.5°	482.0	482.0	482.1	482.0	481.6	481.3	481.0	480.7
30°	467.7	467.5	467.3	467.1	466.8	466.5	466.1	465.7
32.5°	453.2	452.8	452.4	452.0	451.4	450.8	450.3	449.7
35°	430.7	430.2	429.6	429.0	428.2	427.3	426.5	425.7
37.5°	407.1	406.3	405.5	404.9	404.3	403.9	403.4	402.9
40°	390.6	389.7	388.8	388.2	387.9	387.5	387.2	386.9
42.5°	374.4	373.5	372.6	372.0	371.5	371.0	370.6	370.1
45°	350.3	349.1	347.9	347.1	346.8	346.5	346.2	345.9
47.5°	325.0	323.8	322.4	321.4	320.7	320.0	319.3	318.6
50°	307.7	306.3	305.0	304.0	303.2	302.5	301.7	301.0
52.5°	290.8	289.6	288.4	287.5	286.7	285.9	285.1	284.3
55°	264.6	263.7	262.8	262.0	261.3	260.4	259.7	259.0
57.5°	238.6	237.4	236.2	235.4	235.0	234.6	234.2	233.8
60°	221.1	219.9	218.9	218.0	217.3	216.6	215.9	215.2
62.5°	204.1	202.9	201.8	201.0	200.5	199.9	199.2	198.7
65°	177.3	176.4	175.5	174.8	174.4	174.0	173.6	173.2
67.5°	151.9	151.1	150.3	149.8	149.6	149.3	149.1	148.8
70°	135.0	134.4	133.8	133.3	132.9	132.5	132.0	131.6
72.5°	119.2	118.5	117.8	117.2	116.8	116.4	115.9	115.5
75°	94.6	94.3	93.9	93.6	93.2	92.8	92.4	91.9
77.5°	72.1	71.9	71.7	71.5	71.2	70.9	70.6	70.3
80°	57.7	57.6	57.5	57.3	57.1	56.9	56.7	56.5
82.5°	44.0	43.8	43.7	43.5	43.5	43.5	43.4	43.4
85°	26.0	25.9	25.8	25.5	25.3	25.1	24.9	24.7
87.5°	12.6	12.7	12.9	13.0	12.9	12.8	12.8	12.7
90°	14.3	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	32.6	33.8	34.9	35.7	36.2	36.5	36.9	37.3
95°	63.2	64.5	65.7	66.6	66.9	67.3	67.6	67.9
97.5°	99.2	100.3	101.5	102.1	102.3	102.5	102.8	103.0
100°	124.0	125.5	127.1	128.2	128.5	128.8	129.2	129.5
102.5°	149.6	151.3	153.0	154.1	154.6	155.0	155.5	156.0
105°	190.9	191.9	193.0	193.7	194.3	194.8	195.3	195.8
107.5°	235.4	235.9	236.5	236.7	236.7	236.6	236.6	236.6
110°	266.4	266.9	267.4	267.6	267.4	267.2	267.1	266.9





TEST NUMBER: P333140-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.4	297.6	297.9	297.9	297.5	297.2	296.9	296.6
115°	344.8	344.6	344.4	344.2	344.1	343.9	343.7	343.6
117.5°	392.1	392.2	392.4	392.1	391.4	390.7	390.0	389.3
120°	424.0	424.0	424.0	423.7	423.0	422.3	421.6	420.9
122.5°	455.3	455.2	455.0	454.7	454.1	453.6	453.0	452.5
125°	501.5	501.2	500.8	500.6	500.4	500.2	500.1	499.9
127.5°	547.3	547.1	547.0	546.7	546.4	546.0	545.7	545.3
130°	577.6	577.5	577.3	577.0	576.7	576.3	576.0	575.6
132.5°	606.7	606.5	606.4	606.0	605.6	605.1	604.6	604.1
135°	651.5	651.5	651.5	651.2	650.5	649.7	649.0	648.3
137.5°	695.0	695.2	695.4	695.1	694.2	693.4	692.5	691.6
140°	722.5	722.8	723.2	722.9	722.1	721.1	720.2	719.4
142.5°	749.3	749.5	749.7	749.4	748.5	747.7	746.8	745.9
145°	788.1	788.1	788.1	787.8	787.3	786.8	786.3	785.7
147.5°	823.9	824.5	824.9	824.5	823.2	822.0	820.9	819.7
150°	846.6	846.6	846.6	846.4	846.0	845.7	845.3	845.0
152.5°	867.6	868.0	868.4	868.3	867.7	867.1	866.5	865.8
155°	897.7	898.4	899.1	899.0	898.1	897.3	896.4	895.4
157.5°	923.7	924.4	925.1	924.9	923.7	922.6	921.4	920.3
160°	939.6	940.2	940.9	940.9	940.0	939.1	938.2	937.4
162.5°	954.3	955.2	956.0	955.9	954.9	953.9	952.9	951.9
165°	974.3	975.0	975.6	975.5	974.4	973.4	972.3	971.3
167.5°	989.1	990.1	991.2	991.1	990.1	989.0	987.8	986.7
170°	997.8	999.0	1000.0	999.9	998.7	997.4	996.2	995.0
172.5°	1004.2	1005.2	1006.3	1006.3	1005.2	1004.1	1003.0	1001.9
175°	1011.3	1012.4	1013.4	1013.3	1012.1	1010.9	1009.7	1008.5
177.5°	1014.5	1015.3	1016.2	1016.1	1015.1	1014.2	1013.2	1012.2
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7

(END OF REPORT)