

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333198-840

Luminaire Tested: **S125DIP-S610D1205U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333198-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S610D1205U840-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6918.3 lumens  
Efficiency: N/A  
Efficacy: 140.0 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	82	79	76	67	65	63	52	51	50	39	38	38	31
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32	27
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27	23
4	72	62	54	48	65	56	50	45	46	41	37	37	33	30	28	25	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	21	17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	28	47	37	30	26	31	25	22	25	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	17	15	13	11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5837	5837	5837	5837
5°	6760	5857	5128	5857
10°	7864	5827	4494	5827
15°	8705	5784	4145	5784
20°	9745	5716	3865	5716
25°	11416	5640	3729	5640
30°	12331	5565	3610	5565
35°	10138	5423	3533	5423
40°	7206	5227	3447	5227
45°	5536	4961	3399	4961
50°	4725	4633	3392	4633
55°	4208	4310	3422	4310
60°	3796	3959	3509	3959
65°	3506	3605	3599	3605
70°	3186	3238	3652	3238
75°	2815	2852	3618	2852
80°	2369	2325	3310	2325
85°	1875	1675	2675	1675



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.0	1.3
10°-20°	259.1	3.7
20°-30°	420.7	6.1
30°-40°	513.1	7.4
40°-50°	466.8	6.7
50°-60°	371.8	5.4
60°-70°	259.0	3.7
70°-80°	138.1	2.0
80°-90°	38.1	0.6
90°-100°	421.9	6.1
100°-110°	906.9	13.1
110°-120°	851.1	12.3
120°-130°	689.8	10.0
130°-140°	553.5	8.0
140°-150°	417.7	6.0
150°-160°	294.0	4.3
160°-170°	173.3	2.5
170°-180°	56.4	0.8
0°-30°	766.7	11.1
0°-40°	1279.9	18.5
0°-60°	2118.5	30.6
0°-90°	2553.6	36.9
90°-120°	2179.9	31.5
90°-150°	3840.9	55.5
90°-180°	4365.0	63.1
0°-180°	6918.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1043	903	791	903	1043	105
15°	1302	865	620	865	1302	373
25°	1602	791	523	791	1602	732
35°	1286	688	448	688	1286	787
45°	606	543	372	543	606	485
55°	374	383	304	383	374	337
65°	229	236	236	236	229	228
75°	113	114	145	114	113	121
85°	25	23	36	23	25	30
90°	27	1	27	1	27	19
95°	276	39	276	39	276	391
105°	1555	133	1555	133	1555	1545
115°	1732	237	1732	237	1732	1692
125°	1365	328	1365	328	1365	1235
135°	1134	385	1134	385	1134	878
145°	894	448	894	448	894	568
155°	750	512	750	512	750	349
165°	657	559	657	559	657	188
175°	590	581	590	581	590	57
180°	582	582	582	582	582	



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	956.0	954.7	953.5	951.1	952.9	947.7	945.2	941.0	935.7	933.9	931.7
5°	1042.7	1044.6	1046.5	1038.4	1039.3	1033.9	1021.6	1011.6	1003.6	993.2	985.9
7.5°	1147.0	1142.5	1142.2	1136.9	1127.9	1120.7	1107.8	1091.4	1075.5	1057.4	1042.5
10°	1199.2	1199.6	1196.2	1190.0	1180.4	1173.5	1156.6	1140.5	1121.0	1097.9	1081.5
12.5°	1238.5	1240.1	1235.8	1227.5	1222.7	1207.3	1194.1	1174.9	1151.7	1133.3	1108.1
15°	1302.0	1297.8	1294.7	1284.3	1276.3	1260.2	1239.1	1219.1	1193.9	1170.4	1147.0
17.5°	1363.2	1366.7	1360.9	1351.4	1326.5	1307.6	1279.3	1252.0	1220.4	1189.1	1161.1
20°	1417.9	1421.0	1412.1	1395.6	1365.7	1346.9	1309.7	1274.3	1238.0	1197.7	1167.0
22.5°	1486.0	1483.6	1471.7	1446.5	1420.7	1385.8	1345.6	1302.6	1257.0	1211.4	1170.6
25°	1602.0	1585.9	1578.6	1547.5	1513.4	1462.4	1407.1	1344.2	1287.5	1227.2	1175.1
27.5°	1666.3	1661.2	1653.1	1631.4	1595.6	1541.1	1475.9	1399.3	1319.1	1243.1	1174.8
30°	1653.5	1654.2	1655.0	1648.0	1625.1	1584.0	1519.1	1436.6	1341.5	1256.0	1177.0
32.5°	1539.2	1553.2	1566.6	1582.4	1588.8	1580.9	1540.3	1465.8	1368.0	1270.7	1175.7
35°	1285.9	1290.1	1333.5	1376.4	1434.7	1480.1	1510.4	1477.3	1394.8	1283.2	1174.3
37.5°	1002.6	1023.4	1053.4	1102.0	1186.1	1261.4	1358.4	1402.9	1376.2	1287.3	1171.5
40°	854.7	873.9	893.4	942.9	1013.9	1105.2	1215.3	1309.3	1331.2	1274.3	1162.4
42.5°	740.5	755.8	777.5	814.7	873.9	954.8	1060.1	1182.9	1258.4	1237.0	1143.1
45°	606.1	615.7	632.6	662.2	705.1	768.4	861.2	995.5	1112.5	1151.2	1097.1
47.5°	518.8	518.8	531.9	552.3	583.3	637.0	705.7	810.9	935.8	1028.3	1024.0
50°	470.3	468.4	478.8	496.4	521.0	556.6	622.3	706.3	826.4	931.1	960.2
52.5°	428.6	428.8	435.2	448.2	468.8	499.3	548.3	624.0	726.6	834.0	889.0
55°	373.7	372.1	379.4	388.2	403.2	423.1	458.5	516.3	599.6	705.5	776.8
57.5°	323.4	327.5	330.4	336.6	349.0	362.3	392.1	434.6	500.7	591.6	667.0
60°	293.9	298.1	300.3	306.5	316.5	328.0	351.0	385.6	441.2	519.5	594.2
62.5°	267.4	270.7	271.6	277.0	285.2	296.4	314.5	343.5	387.5	455.9	529.2
65°	229.4	229.4	231.0	236.7	240.5	250.5	264.3	285.4	320.7	374.1	436.6
67.5°	192.7	194.6	194.2	196.7	200.3	208.0	217.9	235.3	261.5	300.3	350.4
70°	168.7	170.4	170.0	171.9	175.7	180.7	188.7	205.2	224.0	257.4	300.3
72.5°	147.3	147.9	146.9	149.5	151.8	156.1	165.1	173.9	191.5	219.6	255.0
75°	112.8	113.5	114.3	115.8	118.2	120.5	125.0	133.9	145.4	166.5	189.1
77.5°	84.5	83.1	84.9	84.7	86.0	87.8	91.8	96.5	105.9	119.3	136.8
80°	63.7	64.0	64.0	64.4	66.3	67.6	71.0	74.4	81.7	91.7	103.9
82.5°	46.5	47.5	46.9	47.6	49.2	50.0	51.9	54.7	59.0	66.9	75.7
85°	25.3	23.4	24.1	24.9	24.9	25.3	26.9	28.0	30.3	33.3	36.9
87.5°	12.7	13.3	13.4	13.4	13.7	13.3	14.2	14.0	14.7	15.5	16.2
90°	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1	20.0	18.8	16.5
92.5°	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9	306.3	378.3	384.5
95°	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6	1017.3	1039.7	848.4
97.5°	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5	1287.3	1110.2	757.6
100°	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3	1352.9	1059.6	675.9
102.5°	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2	1313.5	970.4	613.9
105°	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2	1187.5	850.7	553.8
107.5°	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8	1058.9	768.3	528.5
110°	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1	985.6	729.8	521.0



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2	931.2	707.3	521.0
115°	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5	871.8	683.0	524.5
117.5°	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0	836.4	671.0	532.3
120°	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3	816.7	665.3	539.8
122.5°	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9	799.8	660.7	546.3
125°	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1	776.8	654.8	557.3
127.5°	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5	755.7	652.0	569.8
130°	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1	741.6	650.1	577.3
132.5°	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5	730.3	650.1	585.7
135°	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0	717.0	650.1	597.2
137.5°	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3	705.0	651.5	607.8
140°	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1	699.3	652.4	612.5
142.5°	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9	694.7	653.4	615.3
145°	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0	687.6	652.4	618.4
147.5°	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0	680.3	649.3	619.6
150°	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5	674.7	646.5	619.6
152.5°	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2	668.1	642.8	618.6
155°	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0	657.1	636.0	616.0
157.5°	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0	646.8	628.9	613.0
160°	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6	638.3	624.3	610.2
162.5°	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3	630.9	618.6	607.3
165°	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9	619.6	610.2	603.1
167.5°	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3	608.5	602.0	596.5
170°	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8	602.0	597.2	593.8
172.5°	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4	595.4	591.7	590.0
175°	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3	586.7	585.5	585.5
177.5°	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9	583.0	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	929.9	927.8	925.3	921.0	915.7	913.0	908.8	905.9	900.4	895.9	890.9
5°	977.0	967.1	958.0	946.0	933.0	924.5	914.5	903.4	891.9	880.0	867.0
7.5°	1025.9	1008.4	989.2	968.5	948.4	929.8	912.0	894.6	878.4	858.7	842.0
10°	1058.8	1036.5	1012.8	984.7	957.6	933.7	909.6	888.5	867.0	843.9	823.6
12.5°	1091.7	1062.0	1028.4	997.6	964.9	936.2	907.8	880.8	853.8	828.3	804.7
15°	1114.8	1088.7	1057.6	1013.9	977.0	937.6	900.0	865.1	832.4	804.1	774.2
17.5°	1130.0	1096.5	1063.1	1021.2	972.9	928.7	886.1	846.2	809.4	773.4	744.6
20°	1132.9	1098.3	1063.4	1022.4	972.9	922.2	879.7	831.7	792.1	755.0	719.6
22.5°	1132.0	1092.8	1054.8	1012.5	964.3	917.7	866.2	817.3	774.4	737.8	700.9
25°	1123.3	1081.5	1033.9	991.3	943.7	894.2	842.0	791.4	747.7	705.9	669.4
27.5°	1116.0	1061.8	1007.9	958.3	912.3	867.0	817.1	765.2	716.7	674.3	640.0
30°	1107.1	1047.6	987.0	935.2	888.1	843.9	796.8	746.2	695.5	654.1	617.2
32.5°	1099.1	1029.9	965.9	909.5	859.6	816.7	773.2	725.0	675.3	633.2	596.4
35°	1083.8	1003.6	930.3	866.6	813.2	769.2	732.8	687.8	642.2	601.5	566.2
37.5°	1064.2	969.1	890.4	823.6	765.2	718.7	684.8	650.4	606.5	567.3	535.4
40°	1048.8	944.5	861.2	792.9	732.4	684.0	652.6	620.0	583.5	547.0	513.3
42.5°	1029.5	922.4	831.7	758.3	698.3	651.2	618.1	590.5	558.4	524.3	493.0
45°	994.0	882.3	784.2	705.1	644.5	598.0	563.9	543.2	519.1	486.9	460.4
47.5°	941.7	834.2	732.7	651.1	588.5	545.5	513.5	493.6	476.7	452.7	428.7
50°	895.3	798.3	695.5	614.6	552.0	508.7	479.2	461.1	446.6	428.1	407.8
52.5°	843.5	753.2	659.0	579.0	517.1	474.3	445.4	429.5	417.4	404.1	384.2
55°	761.1	684.4	596.9	521.0	463.8	422.0	396.7	382.8	372.8	362.9	350.6
57.5°	670.3	610.4	532.8	463.4	410.8	372.7	349.1	335.7	327.9	322.8	315.6
60°	606.5	555.1	488.4	425.1	373.7	339.9	316.9	306.5	300.0	295.8	290.4
62.5°	547.2	505.0	443.2	385.5	340.5	308.6	288.0	278.0	271.8	269.7	265.2
65°	460.0	427.4	376.4	328.4	290.0	262.8	245.5	235.9	232.1	229.7	230.1
67.5°	374.0	354.1	313.2	272.3	241.6	218.7	204.9	197.5	195.6	192.6	192.5
70°	321.4	306.5	272.0	236.3	209.0	191.5	179.2	171.5	169.6	168.0	167.6
72.5°	275.1	262.1	232.1	203.5	179.0	163.5	153.4	148.8	145.6	144.7	144.6
75°	206.8	199.4	175.7	153.1	136.2	125.4	118.6	114.3	112.0	111.6	112.0
77.5°	147.0	140.7	125.5	109.5	98.9	90.7	84.8	83.4	80.8	80.9	80.5
80°	110.5	106.2	96.6	84.0	75.2	68.3	65.2	62.5	61.8	60.6	61.8
82.5°	80.1	75.5	69.1	61.0	53.7	49.6	46.5	45.6	45.1	44.6	44.8
85°	39.5	39.9	36.1	29.9	26.9	24.5	22.6	22.6	22.2	21.9	22.2
87.5°	16.6	15.5	14.0	12.6	10.6	9.2	8.5	8.5	7.9	8.0	8.8
90°	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2	2.3	4.6	7.1
92.5°	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3	17.4	27.3	41.8
95°	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7	39.9	49.3	62.2
97.5°	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3	65.7	72.3	85.2
100°	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1	84.5	89.2	102.1
102.5°	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9	103.3	107.0	120.9
105°	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6	132.6	138.5	150.2
107.5°	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6	165.0	170.6	180.3
110°	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2	186.6	191.3	201.9





TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8	208.1	211.9	222.5
115°	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0	239.3	242.9	253.5
117.5°	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2	268.7	272.5	283.1
120°	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0	287.5	292.2	302.8
122.5°	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7	306.3	310.0	320.5
125°	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5	330.9	336.8	347.3
127.5°	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0	351.5	359.1	372.4
130°	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2	363.8	373.1	388.4
132.5°	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6	374.1	385.4	402.5
135°	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9	389.6	403.6	422.4
137.5°	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1	407.7	420.8	439.6
140°	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4	418.9	433.0	451.8
142.5°	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5	431.1	444.2	463.0
145°	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3	450.6	462.3	478.8
147.5°	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9	470.3	480.4	495.6
150°	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1	483.4	491.7	507.0
152.5°	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2	495.6	502.9	516.3
155°	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6	511.6	518.7	530.4
157.5°	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1	526.8	532.5	542.6
160°	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5	536.2	541.0	549.2
162.5°	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8	544.7	549.4	556.6
165°	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6	556.2	559.8	565.6
167.5°	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0	565.8	567.9	571.2
170°	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6	571.5	572.6	575.0
172.5°	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4	574.3	575.4	577.7
175°	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9	578.5	579.7	580.9
177.5°	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0	581.1	581.1	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	888.2	884.7	882.0	875.9	872.5	867.9	864.2	868.2	863.9	865.8	863.0
5°	860.5	849.7	842.0	830.9	821.3	812.5	806.0	804.9	801.7	800.2	795.7
7.5°	827.2	813.7	800.5	786.0	773.7	761.2	753.2	746.6	742.3	736.5	732.6
10°	807.5	789.5	774.2	756.5	741.1	727.7	717.0	711.7	706.6	699.3	696.7
12.5°	783.3	764.7	745.9	727.0	712.4	697.3	688.1	680.0	676.6	668.3	667.5
15°	754.2	726.2	707.8	688.6	668.2	656.0	648.3	639.5	635.7	630.0	625.7
17.5°	719.5	694.5	671.5	651.7	634.2	623.9	614.3	608.2	601.7	597.9	591.0
20°	694.4	670.6	647.5	626.4	613.0	601.2	593.5	587.7	580.8	578.9	572.0
22.5°	673.2	646.9	624.8	607.1	592.5	579.1	570.8	566.8	562.1	556.1	554.8
25°	638.7	611.5	592.7	575.0	562.0	549.8	544.0	539.0	534.4	530.2	528.7
27.5°	608.9	584.6	562.3	546.3	535.0	523.8	518.8	512.7	509.3	505.9	501.8
30°	588.1	563.2	543.6	528.3	515.9	506.0	500.6	496.4	493.3	490.3	488.0
32.5°	566.6	543.5	524.5	509.6	497.3	489.8	484.9	482.0	478.6	474.9	472.0
35°	538.3	512.9	494.5	481.4	471.8	466.1	460.7	458.1	454.2	454.2	451.1
37.5°	506.2	484.3	468.1	456.2	447.6	442.4	436.7	434.8	432.3	430.7	429.7
40°	487.2	466.9	451.5	439.6	430.4	426.2	421.6	418.5	417.0	415.1	414.3
42.5°	467.6	448.2	433.4	422.4	414.4	410.8	406.6	404.5	401.3	398.8	398.4
45°	437.7	418.9	405.5	396.7	389.8	385.6	382.8	378.3	376.7	373.7	373.2
47.5°	409.4	391.3	378.2	370.9	364.9	361.4	357.2	352.6	350.8	349.3	349.2
50°	388.2	371.7	359.4	352.5	346.8	341.8	337.6	334.6	333.4	333.4	334.2
52.5°	366.8	352.7	342.2	333.9	328.4	323.1	319.2	317.3	315.6	317.4	318.8
55°	335.3	321.1	313.5	305.4	300.0	293.9	292.0	291.1	290.0	293.1	294.6
57.5°	301.9	292.1	283.1	275.1	270.2	266.7	264.1	263.7	265.8	267.2	272.3
60°	280.8	269.3	261.3	255.1	249.3	247.0	246.3	245.5	247.0	251.3	257.8
62.5°	257.5	248.1	239.4	234.9	230.7	226.8	226.6	227.1	230.1	235.0	241.6
65°	223.3	215.2	209.4	204.1	200.7	198.3	199.1	200.7	204.1	210.7	217.9
67.5°	188.5	183.0	177.8	173.5	170.2	170.2	171.0	173.3	177.3	184.8	191.5
70°	166.1	160.0	155.7	153.8	151.2	149.7	151.9	155.7	159.2	166.1	171.9
72.5°	143.7	138.5	135.2	133.9	132.7	131.5	132.3	136.4	141.1	148.0	154.7
75°	110.5	108.6	106.2	104.7	103.6	104.3	105.1	109.0	112.8	120.1	127.7
77.5°	80.7	78.7	77.3	76.9	76.2	76.6	78.8	81.6	85.4	90.7	96.5
80°	61.0	60.2	59.5	59.1	59.1	59.5	62.5	64.4	67.9	72.9	77.5
82.5°	44.4	43.9	43.8	43.7	44.0	44.1	45.9	48.5	51.3	55.1	59.1
85°	23.4	22.6	23.8	24.1	23.4	24.5	25.3	26.9	28.0	29.9	31.8
87.5°	9.6	10.6	10.6	11.3	11.6	12.6	12.6	14.0	14.8	15.8	15.9
90°	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1	22.3	23.4	25.9
92.5°	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9	150.9	113.6	96.2
95°	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6	665.3	521.0	422.4
97.5°	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5	1131.5	990.9	853.7
100°	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3	1385.8	1265.0	1142.9
102.5°	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2	1541.7	1483.7	1401.1
105°	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2	1629.9	1681.5	1668.6
107.5°	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8	1551.3	1683.8	1745.1
110°	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1	1462.1	1627.5	1727.3



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2	1373.8	1541.2	1658.7
115°	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5	1247.4	1408.1	1536.0
117.5°	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0	1159.8	1298.3	1415.6
120°	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3	1110.0	1239.1	1342.4
122.5°	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9	1074.4	1189.4	1286.1
125°	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1	1026.7	1128.8	1213.4
127.5°	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5	981.2	1076.5	1155.6
130°	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1	949.3	1040.9	1117.1
132.5°	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5	919.3	1002.3	1075.8
135°	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0	873.0	948.2	1015.0
137.5°	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3	831.7	894.1	951.0
140°	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1	807.3	861.3	910.6
142.5°	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9	786.7	833.1	875.9
145°	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0	760.3	796.8	828.4
147.5°	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0	738.5	766.5	790.4
150°	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5	726.4	748.6	769.7
152.5°	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2	714.2	734.6	751.0
155°	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0	695.8	712.3	725.2
157.5°	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0	678.4	691.2	701.3
160°	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6	665.3	677.0	685.3
162.5°	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3	654.1	663.9	671.2
165°	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9	637.1	644.2	650.1
167.5°	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3	620.8	626.1	630.4
170°	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8	611.4	614.9	617.2
172.5°	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4	602.9	605.5	606.9
175°	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3	590.3	592.6	592.6
177.5°	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9	584.8	584.8	584.8
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	861.1	863.3	861.5	863.9	861.5	863.3	861.1	863.0	865.8	863.9	868.2
5°	793.8	790.2	792.5	791.0	792.5	790.2	793.8	795.7	800.2	801.7	804.9
7.5°	731.4	728.1	724.4	722.6	724.4	728.1	731.4	732.6	736.5	742.3	746.6
10°	692.5	688.2	687.8	685.2	687.8	688.2	692.5	696.7	699.3	706.6	711.7
12.5°	663.9	659.9	655.6	654.5	655.6	659.9	663.9	667.5	668.3	676.6	680.0
15°	623.4	620.4	617.6	620.0	617.6	620.4	623.4	625.7	630.0	635.7	639.5
17.5°	589.7	587.1	586.7	583.9	586.7	587.1	589.7	591.0	597.9	601.7	608.2
20°	568.6	566.6	567.3	562.4	567.3	566.6	568.6	572.0	578.9	580.8	587.7
22.5°	551.7	547.9	547.4	546.4	547.4	547.9	551.7	554.8	556.1	562.1	566.8
25°	525.2	523.3	521.4	523.3	521.4	523.3	525.2	528.7	530.2	534.4	539.0
27.5°	502.1	499.8	499.3	499.5	499.3	499.8	502.1	501.8	505.9	509.3	512.7
30°	488.0	484.1	484.5	484.1	484.5	484.1	488.0	488.0	490.3	493.3	496.4
32.5°	472.6	470.0	469.5	468.8	469.5	470.0	472.6	472.0	474.9	478.6	482.0
35°	450.0	450.0	448.1	448.1	448.1	450.0	450.0	451.1	454.2	454.2	458.1
37.5°	428.7	428.4	427.2	427.4	427.2	428.4	428.7	429.7	430.7	432.3	434.8
40°	412.7	412.4	411.2	408.9	411.2	412.4	412.7	414.3	415.1	417.0	418.5
42.5°	397.5	396.2	395.6	394.9	395.6	396.2	397.5	398.4	398.8	401.3	404.5
45°	373.2	373.2	372.5	372.1	372.5	373.2	373.2	373.2	373.7	376.7	378.3
47.5°	349.8	350.5	351.9	351.7	351.9	350.5	349.8	349.2	349.3	350.8	352.6
50°	335.7	336.1	337.2	337.6	337.2	336.1	335.7	334.2	333.4	333.4	334.6
52.5°	320.0	322.2	323.7	323.5	323.7	322.2	320.0	318.8	317.4	315.6	317.3
55°	298.1	300.7	303.5	303.9	303.5	300.7	298.1	294.6	293.1	290.0	291.1
57.5°	276.4	280.1	283.0	283.9	283.0	280.1	276.4	272.3	267.2	265.8	263.7
60°	261.7	266.6	270.0	271.7	270.0	266.6	261.7	257.8	251.3	247.0	245.5
62.5°	247.5	253.1	256.6	256.9	256.6	253.1	247.5	241.6	235.0	230.1	227.1
65°	224.4	230.1	233.3	235.5	233.3	230.1	224.4	217.9	210.7	204.1	200.7
67.5°	199.5	205.3	208.7	210.6	208.7	205.3	199.5	191.5	184.8	177.3	173.3
70°	181.5	187.2	191.8	193.4	191.8	187.2	181.5	171.9	166.1	159.2	155.7
72.5°	163.7	168.7	172.5	174.3	172.5	168.7	163.7	154.7	148.0	141.1	136.4
75°	132.7	139.7	143.1	145.0	143.1	139.7	132.7	127.7	120.1	112.8	109.0
77.5°	102.4	108.7	110.7	111.7	110.7	108.7	102.4	96.5	90.7	85.4	81.6
80°	82.1	85.9	88.7	89.0	88.7	85.9	82.1	77.5	72.9	67.9	64.4
82.5°	63.1	66.2	67.2	68.2	67.2	66.2	63.1	59.1	55.1	51.3	48.5
85°	34.5	36.1	36.5	36.1	36.5	36.1	34.5	31.8	29.9	28.0	26.9
87.5°	16.6	16.3	16.5	17.1	16.5	16.3	16.6	15.9	15.8	14.8	14.0
90°	25.9	25.9	27.0	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1
92.5°	81.2	78.4	76.7	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9
95°	339.1	303.9	294.6	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6
97.5°	781.2	715.6	681.6	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5
100°	1062.0	977.4	934.0	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3
102.5°	1314.4	1254.4	1207.2	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2
105°	1631.0	1592.4	1568.8	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2
107.5°	1764.1	1763.9	1756.2	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8
110°	1780.1	1802.4	1810.6	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1736.0	1774.2	1794.6	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2
115°	1627.5	1683.8	1716.7	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5
117.5°	1507.1	1565.4	1598.0	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0
120°	1429.3	1485.5	1517.2	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3
122.5°	1363.5	1415.1	1446.8	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9
125°	1279.0	1327.2	1352.9	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1
127.5°	1215.2	1257.7	1282.1	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5
130°	1175.8	1214.5	1238.0	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1
132.5°	1134.5	1173.2	1194.8	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5
135°	1066.6	1105.4	1126.5	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0
137.5°	997.1	1032.4	1051.9	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3
140°	954.0	984.5	1002.1	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1
142.5°	912.7	938.5	955.1	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9
145°	856.6	876.6	889.5	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0
147.5°	812.7	828.7	836.2	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0
150°	787.4	801.4	806.2	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5
152.5°	765.8	777.0	781.7	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2
155°	736.9	745.1	748.6	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0
157.5°	710.3	717.2	720.4	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0
160°	693.5	699.3	701.8	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6
162.5°	677.5	682.5	683.0	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3
165°	654.8	657.1	657.1	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9
167.5°	632.7	634.8	633.9	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3
170°	619.6	620.8	620.8	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8
172.5°	607.3	609.5	607.6	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4
175°	592.6	593.8	591.4	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3
177.5°	583.9	584.8	582.0	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	864.2	867.9	872.5	875.9	882.0	884.7	888.2	890.9	895.9	900.4	905.9
5°	806.0	812.5	821.3	830.9	842.0	849.7	860.5	867.0	880.0	891.9	903.4
7.5°	753.2	761.2	773.7	786.0	800.5	813.7	827.2	842.0	858.7	878.4	894.6
10°	717.0	727.7	741.1	756.5	774.2	789.5	807.5	823.6	843.9	867.0	888.5
12.5°	688.1	697.3	712.4	727.0	745.9	764.7	783.3	804.7	828.3	853.8	880.8
15°	648.3	656.0	668.2	688.6	707.8	726.2	754.2	774.2	804.1	832.4	865.1
17.5°	614.3	623.9	634.2	651.7	671.5	694.5	719.5	744.6	773.4	809.4	846.2
20°	593.5	601.2	613.0	626.4	647.5	670.6	694.4	719.6	755.0	792.1	831.7
22.5°	570.8	579.1	592.5	607.1	624.8	646.9	673.2	700.9	737.8	774.4	817.3
25°	544.0	549.8	562.0	575.0	592.7	611.5	638.7	669.4	705.9	747.7	791.4
27.5°	518.8	523.8	535.0	546.3	562.3	584.6	608.9	640.0	674.3	716.7	765.2
30°	500.6	506.0	515.9	528.3	543.6	563.2	588.1	617.2	654.1	695.5	746.2
32.5°	484.9	489.8	497.3	509.6	524.5	543.5	566.6	596.4	633.2	675.3	725.0
35°	460.7	466.1	471.8	481.4	494.5	512.9	538.3	566.2	601.5	642.2	687.8
37.5°	436.7	442.4	447.6	456.2	468.1	484.3	506.2	535.4	567.3	606.5	650.4
40°	421.6	426.2	430.4	439.6	451.5	466.9	487.2	513.3	547.0	583.5	620.0
42.5°	406.6	410.8	414.4	422.4	433.4	448.2	467.6	493.0	524.3	558.4	590.5
45°	382.8	385.6	389.8	396.7	405.5	418.9	437.7	460.4	486.9	519.1	543.2
47.5°	357.2	361.4	364.9	370.9	378.2	391.3	409.4	428.7	452.7	476.7	493.6
50°	337.6	341.8	346.8	352.5	359.4	371.7	388.2	407.8	428.1	446.6	461.1
52.5°	319.2	323.1	328.4	333.9	342.2	352.7	366.8	384.2	404.1	417.4	429.5
55°	292.0	293.9	300.0	305.4	313.5	321.1	335.3	350.6	362.9	372.8	382.8
57.5°	264.1	266.7	270.2	275.1	283.1	292.1	301.9	315.6	322.8	327.9	335.7
60°	246.3	247.0	249.3	255.1	261.3	269.3	280.8	290.4	295.8	300.0	306.5
62.5°	226.6	226.8	230.7	234.9	239.4	248.1	257.5	265.2	269.7	271.8	278.0
65°	199.1	198.3	200.7	204.1	209.4	215.2	223.3	230.1	229.7	232.1	235.9
67.5°	171.0	170.2	170.2	173.5	177.8	183.0	188.5	192.5	192.6	195.6	197.5
70°	151.9	149.7	151.2	153.8	155.7	160.0	166.1	167.6	168.0	169.6	171.5
72.5°	132.3	131.5	132.7	133.9	135.2	138.5	143.7	144.6	144.7	145.6	148.8
75°	105.1	104.3	103.6	104.7	106.2	108.6	110.5	112.0	111.6	112.0	114.3
77.5°	78.8	76.6	76.2	76.9	77.3	78.7	80.7	80.5	80.9	80.8	83.4
80°	62.5	59.5	59.1	59.1	59.5	60.2	61.0	61.8	60.6	61.8	62.5
82.5°	45.9	44.1	44.0	43.7	43.8	43.9	44.4	44.8	44.6	45.1	45.6
85°	25.3	24.5	23.4	24.1	23.8	22.6	23.4	22.2	21.9	22.2	22.6
87.5°	12.6	12.6	11.6	11.3	10.6	10.6	9.6	8.8	8.0	7.9	8.5
90°	20.0	18.8	16.5	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2
92.5°	306.3	378.3	384.5	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3
95°	1017.3	1039.7	848.4	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7
97.5°	1287.3	1110.2	757.6	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3
100°	1352.9	1059.6	675.9	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1
102.5°	1313.5	970.4	613.9	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9
105°	1187.5	850.7	553.8	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6
107.5°	1058.9	768.3	528.5	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6
110°	985.6	729.8	521.0	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	931.2	707.3	521.0	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8
115°	871.8	683.0	524.5	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0
117.5°	836.4	671.0	532.3	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2
120°	816.7	665.3	539.8	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0
122.5°	799.8	660.7	546.3	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7
125°	776.8	654.8	557.3	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5
127.5°	755.7	652.0	569.8	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0
130°	741.6	650.1	577.3	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2
132.5°	730.3	650.1	585.7	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6
135°	717.0	650.1	597.2	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9
137.5°	705.0	651.5	607.8	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1
140°	699.3	652.4	612.5	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4
142.5°	694.7	653.4	615.3	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5
145°	687.6	652.4	618.4	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3
147.5°	680.3	649.3	619.6	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9
150°	674.7	646.5	619.6	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1
152.5°	668.1	642.8	618.6	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2
155°	657.1	636.0	616.0	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6
157.5°	646.8	628.9	613.0	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1
160°	638.3	624.3	610.2	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5
162.5°	630.9	618.6	607.3	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8
165°	619.6	610.2	603.1	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6
167.5°	608.5	602.0	596.5	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0
170°	602.0	597.2	593.8	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6
172.5°	595.4	591.7	590.0	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4
175°	586.7	585.5	585.5	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9
177.5°	583.0	582.0	582.0	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	908.8	913.0	915.7	921.0	925.3	927.8	929.9	931.7	933.9	935.7	941.0
5°	914.5	924.5	933.0	946.0	958.0	967.1	977.0	985.9	993.2	1003.6	1011.6
7.5°	912.0	929.8	948.4	968.5	989.2	1008.4	1025.9	1042.5	1057.4	1075.5	1091.4
10°	909.6	933.7	957.6	984.7	1012.8	1036.5	1058.8	1081.5	1097.9	1121.0	1140.5
12.5°	907.8	936.2	964.9	997.6	1028.4	1062.0	1091.7	1108.1	1133.3	1151.7	1174.9
15°	900.0	937.6	977.0	1013.9	1057.6	1088.7	1114.8	1147.0	1170.4	1193.9	1219.1
17.5°	886.1	928.7	972.9	1021.2	1063.1	1096.5	1130.0	1161.1	1189.1	1220.4	1252.0
20°	879.7	922.2	972.9	1022.4	1063.4	1098.3	1132.9	1167.0	1197.7	1238.0	1274.3
22.5°	866.2	917.7	964.3	1012.5	1054.8	1092.8	1132.0	1170.6	1211.4	1257.0	1302.6
25°	842.0	894.2	943.7	991.3	1033.9	1081.5	1123.3	1175.1	1227.2	1287.5	1344.2
27.5°	817.1	867.0	912.3	958.3	1007.9	1061.8	1116.0	1174.8	1243.1	1319.1	1399.3
30°	796.8	843.9	888.1	935.2	987.0	1047.6	1107.1	1177.0	1256.0	1341.5	1436.6
32.5°	773.2	816.7	859.6	909.5	965.9	1029.9	1099.1	1175.7	1270.7	1368.0	1465.8
35°	732.8	769.2	813.2	866.6	930.3	1003.6	1083.8	1174.3	1283.2	1394.8	1477.3
37.5°	684.8	718.7	765.2	823.6	890.4	969.1	1064.2	1171.5	1287.3	1376.2	1402.9
40°	652.6	684.0	732.4	792.9	861.2	944.5	1048.8	1162.4	1274.3	1331.2	1309.3
42.5°	618.1	651.2	698.3	758.3	831.7	922.4	1029.5	1143.1	1237.0	1258.4	1182.9
45°	563.9	598.0	644.5	705.1	784.2	882.3	994.0	1097.1	1151.2	1112.5	995.5
47.5°	513.5	545.5	588.5	651.1	732.7	834.2	941.7	1024.0	1028.3	935.8	810.9
50°	479.2	508.7	552.0	614.6	695.5	798.3	895.3	960.2	931.1	826.4	706.3
52.5°	445.4	474.3	517.1	579.0	659.0	753.2	843.5	889.0	834.0	726.6	624.0
55°	396.7	422.0	463.8	521.0	596.9	684.4	761.1	776.8	705.5	599.6	516.3
57.5°	349.1	372.7	410.8	463.4	532.8	610.4	670.3	667.0	591.6	500.7	434.6
60°	316.9	339.9	373.7	425.1	488.4	555.1	606.5	594.2	519.5	441.2	385.6
62.5°	288.0	308.6	340.5	385.5	443.2	505.0	547.2	529.2	455.9	387.5	343.5
65°	245.5	262.8	290.0	328.4	376.4	427.4	460.0	436.6	374.1	320.7	285.4
67.5°	204.9	218.7	241.6	272.3	313.2	354.1	374.0	350.4	300.3	261.5	235.3
70°	179.2	191.5	209.0	236.3	272.0	306.5	321.4	300.3	257.4	224.0	205.2
72.5°	153.4	163.5	179.0	203.5	232.1	262.1	275.1	255.0	219.6	191.5	173.9
75°	118.6	125.4	136.2	153.1	175.7	199.4	206.8	189.1	166.5	145.4	133.9
77.5°	84.8	90.7	98.9	109.5	125.5	140.7	147.0	136.8	119.3	105.9	96.5
80°	65.2	68.3	75.2	84.0	96.6	106.2	110.5	103.9	91.7	81.7	74.4
82.5°	46.5	49.6	53.7	61.0	69.1	75.5	80.1	75.7	66.9	59.0	54.7
85°	22.6	24.5	26.9	29.9	36.1	39.9	39.5	36.9	33.3	30.3	28.0
87.5°	8.5	9.2	10.6	12.6	14.0	15.5	16.6	16.2	15.5	14.7	14.0
90°	2.3	4.6	7.1	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1
92.5°	17.4	27.3	41.8	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9
95°	39.9	49.3	62.2	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6
97.5°	65.7	72.3	85.2	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5
100°	84.5	89.2	102.1	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3
102.5°	103.3	107.0	120.9	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2
105°	132.6	138.5	150.2	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2
107.5°	165.0	170.6	180.3	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8
110°	186.6	191.3	201.9	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1





TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	208.1	211.9	222.5	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2
115°	239.3	242.9	253.5	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5
117.5°	268.7	272.5	283.1	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0
120°	287.5	292.2	302.8	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3
122.5°	306.3	310.0	320.5	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9
125°	330.9	336.8	347.3	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1
127.5°	351.5	359.1	372.4	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5
130°	363.8	373.1	388.4	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1
132.5°	374.1	385.4	402.5	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5
135°	389.6	403.6	422.4	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0
137.5°	407.7	420.8	439.6	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3
140°	418.9	433.0	451.8	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1
142.5°	431.1	444.2	463.0	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9
145°	450.6	462.3	478.8	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0
147.5°	470.3	480.4	495.6	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0
150°	483.4	491.7	507.0	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5
152.5°	495.6	502.9	516.3	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2
155°	511.6	518.7	530.4	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0
157.5°	526.8	532.5	542.6	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0
160°	536.2	541.0	549.2	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6
162.5°	544.7	549.4	556.6	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3
165°	556.2	559.8	565.6	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9
167.5°	565.8	567.9	571.2	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3
170°	571.5	572.6	575.0	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8
172.5°	574.3	575.4	577.7	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4
175°	578.5	579.7	580.9	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3
177.5°	581.1	581.1	582.0	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	945.2	947.7	952.9	951.1	953.5	954.7	956.0
5°	1021.6	1033.9	1039.3	1038.4	1046.5	1044.6	1042.7
7.5°	1107.8	1120.7	1127.9	1136.9	1142.2	1142.5	1147.0
10°	1156.6	1173.5	1180.4	1190.0	1196.2	1199.6	1199.2
12.5°	1194.1	1207.3	1222.7	1227.5	1235.8	1240.1	1238.5
15°	1239.1	1260.2	1276.3	1284.3	1294.7	1297.8	1302.0
17.5°	1279.3	1307.6	1326.5	1351.4	1360.9	1366.7	1363.2
20°	1309.7	1346.9	1365.7	1395.6	1412.1	1421.0	1417.9
22.5°	1345.6	1385.8	1420.7	1446.5	1471.7	1483.6	1486.0
25°	1407.1	1462.4	1513.4	1547.5	1578.6	1585.9	1602.0
27.5°	1475.9	1541.1	1595.6	1631.4	1653.1	1661.2	1666.3
30°	1519.1	1584.0	1625.1	1648.0	1655.0	1654.2	1653.5
32.5°	1540.3	1580.9	1588.8	1582.4	1566.6	1553.2	1539.2
35°	1510.4	1480.1	1434.7	1376.4	1333.5	1290.1	1285.9
37.5°	1358.4	1261.4	1186.1	1102.0	1053.4	1023.4	1002.6
40°	1215.3	1105.2	1013.9	942.9	893.4	873.9	854.7
42.5°	1060.1	954.8	873.9	814.7	777.5	755.8	740.5
45°	861.2	768.4	705.1	662.2	632.6	615.7	606.1
47.5°	705.7	637.0	583.3	552.3	531.9	518.8	518.8
50°	622.3	556.6	521.0	496.4	478.8	468.4	470.3
52.5°	548.3	499.3	468.8	448.2	435.2	428.8	428.6
55°	458.5	423.1	403.2	388.2	379.4	372.1	373.7
57.5°	392.1	362.3	349.0	336.6	330.4	327.5	323.4
60°	351.0	328.0	316.5	306.5	300.3	298.1	293.9
62.5°	314.5	296.4	285.2	277.0	271.6	270.7	267.4
65°	264.3	250.5	240.5	236.7	231.0	229.4	229.4
67.5°	217.9	208.0	200.3	196.7	194.2	194.6	192.7
70°	188.7	180.7	175.7	171.9	170.0	170.4	168.7
72.5°	165.1	156.1	151.8	149.5	146.9	147.9	147.3
75°	125.0	120.5	118.2	115.8	114.3	113.5	112.8
77.5°	91.8	87.8	86.0	84.7	84.9	83.1	84.5
80°	71.0	67.6	66.3	64.4	64.0	64.0	63.7
82.5°	51.9	50.0	49.2	47.6	46.9	47.5	46.5
85°	26.9	25.3	24.9	24.9	24.1	23.4	25.3
87.5°	14.2	13.3	13.7	13.4	13.4	13.3	12.7
90°	22.3	23.4	25.9	25.9	25.9	27.0	27.0
92.5°	150.9	113.6	96.2	81.2	78.4	76.7	74.8
95°	665.3	521.0	422.4	339.1	303.9	294.6	275.8
97.5°	1131.5	990.9	853.7	781.2	715.6	681.6	666.5
100°	1385.8	1265.0	1142.9	1062.0	977.4	934.0	915.2
102.5°	1541.7	1483.7	1401.1	1314.4	1254.4	1207.2	1193.2
105°	1629.9	1681.5	1668.6	1631.0	1592.4	1568.8	1554.8
107.5°	1551.3	1683.8	1745.1	1764.1	1763.9	1756.2	1746.8
110°	1462.1	1627.5	1727.3	1780.1	1802.4	1810.6	1810.6



TEST NUMBER: P333198-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1373.8	1541.2	1658.7	1736.0	1774.2	1794.6	1803.1
115°	1247.4	1408.1	1536.0	1627.5	1683.8	1716.7	1731.9
117.5°	1159.8	1298.3	1415.6	1507.1	1565.4	1598.0	1607.3
120°	1110.0	1239.1	1342.4	1429.3	1485.5	1517.2	1526.6
122.5°	1074.4	1189.4	1286.1	1363.5	1415.1	1446.8	1455.3
125°	1026.7	1128.8	1213.4	1279.0	1327.2	1352.9	1364.7
127.5°	981.2	1076.5	1155.6	1215.2	1257.7	1282.1	1287.3
130°	949.3	1040.9	1117.1	1175.8	1214.5	1238.0	1245.0
132.5°	919.3	1002.3	1075.8	1134.5	1173.2	1194.8	1202.7
135°	873.0	948.2	1015.0	1066.6	1105.4	1126.5	1133.6
137.5°	831.7	894.1	951.0	997.1	1032.4	1051.9	1059.6
140°	807.3	861.3	910.6	954.0	984.5	1002.1	1007.9
142.5°	786.7	833.1	875.9	912.7	938.5	955.1	960.1
145°	760.3	796.8	828.4	856.6	876.6	889.5	894.1
147.5°	738.5	766.5	790.4	812.7	828.7	836.2	838.3
150°	726.4	748.6	769.7	787.4	801.4	806.2	807.3
152.5°	714.2	734.6	751.0	765.8	777.0	781.7	782.9
155°	695.8	712.3	725.2	736.9	745.1	748.6	749.8
157.5°	678.4	691.2	701.3	710.3	717.2	720.4	720.2
160°	665.3	677.0	685.3	693.5	699.3	701.8	700.5
162.5°	654.1	663.9	671.2	677.5	682.5	683.0	682.7
165°	637.1	644.2	650.1	654.8	657.1	657.1	657.1
167.5°	620.8	626.1	630.4	632.7	634.8	633.9	633.7
170°	611.4	614.9	617.2	619.6	620.8	620.8	619.6
172.5°	602.9	605.5	606.9	607.3	609.5	607.6	606.4
175°	590.3	592.6	592.6	592.6	593.8	591.4	590.3
177.5°	584.8	584.8	584.8	583.9	584.8	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0

(END OF REPORT)