

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333555-830

Luminaire Tested: **S125RDIP-S850D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333555-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D365U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4301.8 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333555-830

CATALOG NUMBER: S125RDIP-S850D365U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333555-830

CATALOG NUMBER: S125RDIP-S850D365U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	99	95	91	97	93	90	87	84	81	79	75	73	72	67	66	65	61
2	94	86	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	51
3	86	76	69	63	81	73	66	60	66	60	56	59	55	51	53	50	47	44
4	79	68	60	54	74	65	57	52	59	53	48	53	48	44	48	44	41	38
5	73	61	52	46	68	58	50	45	53	46	42	48	43	39	43	39	36	33
6	67	55	46	40	63	52	45	39	48	41	37	43	38	34	39	35	32	29
7	62	50	41	36	59	47	40	35	43	37	32	39	34	30	36	32	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	25	31	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8371	8371	8371
5°	8390	8294	8345
10°	8326	8217	8217
15°	8227	8050	7985
20°	8100	7818	7724
25°	7953	7590	7422
30°	7767	7322	7088
35°	7579	7046	6714
40°	7403	6759	6347
45°	7188	6437	5945
50°	6973	6089	5528
55°	6723	5754	5082
60°	6473	5349	4602
65°	6178	4876	4053
70°	5840	4288	3493
75°	5375	3616	2907
80°	4731	2838	2440
85°	3987	2319	2179



TEST NUMBER: P333555-830

CATALOG NUMBER: S125RDIP-S850D365U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.9	2.8
10°-20°	340.6	7.9
20°-30°	493.9	11.5
30°-40°	562.9	13.1
40°-50°	548.6	12.8
50°-60°	461.8	10.7
60°-70°	323.7	7.5
70°-80°	166.4	3.9
80°-90°	42.9	1.0
90°-100°	119.8	2.8
100°-110°	257.4	6.0
110°-120°	241.6	5.6
120°-130°	195.8	4.6
130°-140°	157.1	3.7
140°-150°	118.6	2.8
150°-160°	83.5	1.9
160°-170°	49.2	1.1
170°-180°	16.0	0.4
0°-30°	956.3	22.2
0°-40°	1519.2	35.3
0°-60°	2529.7	58.8
0°-90°	3062.8	71.2
90°-120°	618.8	14.4
90°-150°	1090.3	25.3
90°-180°	1239.0	28.8
0°-180°	4301.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1296	1296	1296	1296	1296	
5°	1294	1290	1279	1289	1287	123
15°	1230	1224	1204	1203	1194	347
25°	1116	1100	1065	1052	1042	513
35°	961	937	894	866	852	602
45°	787	757	705	667	651	607
55°	597	564	511	468	451	534
65°	404	370	319	281	265	400
75°	215	185	145	124	116	228
85°	54	37	31	30	29	60
90°	0	3	5	7	8	3
95°	11	32	295	134	78	12
105°	38	53	242	476	441	40
115°	67	81	194	418	492	66
125°	93	109	186	332	387	83
135°	109	131	184	279	322	85
145°	127	146	185	231	254	80
155°	145	156	181	204	213	67
165°	158	163	173	184	186	45
175°	165	165	166	168	168	16
180°	165	165	165	165	165	



TEST NUMBER: P333555-830

CATALOG NUMBER: S125RDIP-S850D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1298.4	1297.9	1297.3	1296.8	1296.3	1295.1	1293.5	1291.7	1290.0	1288.2	1290.0
5°	1294.1	1293.3	1292.3	1291.5	1290.6	1289.0	1286.6	1284.2	1281.8	1279.4	1281.6
7.5°	1281.4	1280.5	1279.7	1278.8	1278.1	1276.2	1273.4	1270.5	1267.6	1264.7	1266.2
10°	1269.6	1268.9	1268.3	1267.6	1267.0	1265.2	1262.2	1259.0	1256.0	1253.0	1253.6
12.5°	1256.3	1255.5	1254.6	1253.9	1253.0	1250.6	1246.4	1242.4	1238.3	1234.2	1234.6
15°	1230.5	1229.2	1227.9	1226.5	1225.2	1222.3	1217.8	1213.1	1208.6	1204.0	1203.8
17.5°	1201.3	1199.3	1197.3	1195.3	1193.3	1189.4	1183.6	1177.9	1172.1	1166.4	1165.4
20°	1178.6	1176.4	1174.2	1172.1	1169.9	1165.3	1158.4	1151.4	1144.4	1137.5	1136.4
22.5°	1153.5	1151.3	1149.1	1147.0	1144.8	1140.1	1132.7	1125.5	1118.1	1110.9	1108.7
25°	1116.0	1112.7	1109.4	1106.2	1102.9	1097.2	1089.2	1081.1	1073.1	1065.1	1062.2
27.5°	1072.9	1068.9	1065.0	1061.0	1057.1	1050.7	1042.2	1033.5	1024.9	1016.2	1012.3
30°	1041.5	1037.4	1033.3	1029.2	1025.0	1018.3	1009.3	1000.1	991.0	981.8	976.9
32.5°	1011.0	1006.2	1001.4	996.6	991.6	984.6	975.3	966.0	956.7	947.3	941.9
35°	961.3	956.0	950.8	945.6	940.4	932.8	923.1	913.3	903.5	893.7	887.4
37.5°	912.5	906.2	899.8	893.4	887.1	878.9	868.8	858.7	848.6	838.5	830.9
40°	878.1	871.6	865.0	858.5	852.0	843.5	833.0	822.6	812.2	801.7	793.4
42.5°	842.1	835.4	828.7	821.9	815.2	806.5	795.7	784.9	774.1	763.4	755.4
45°	787.0	780.7	774.4	768.1	761.8	752.6	740.6	728.8	716.8	704.8	696.1
47.5°	730.1	723.4	716.7	710.1	703.4	694.1	682.0	670.0	657.9	645.8	636.9
50°	694.0	686.8	679.7	672.5	665.3	655.5	643.1	630.7	618.3	606.0	596.8
52.5°	654.9	647.5	640.2	632.8	625.5	616.0	604.3	592.6	580.8	569.1	559.3
55°	597.1	590.1	583.2	576.3	569.3	559.7	547.5	535.4	523.2	511.0	501.1
57.5°	538.8	531.3	523.9	516.4	509.1	499.5	487.7	475.9	464.2	452.4	442.9
60°	501.1	493.6	486.0	478.3	470.7	461.1	449.3	437.5	425.8	414.1	404.5
62.5°	461.3	454.0	446.8	439.4	432.2	422.6	410.7	398.8	386.8	374.9	366.1
65°	404.3	396.9	389.5	382.1	374.7	365.2	353.7	342.1	330.6	319.1	310.4
67.5°	347.7	340.3	332.9	325.6	318.1	308.9	297.8	286.8	275.8	264.7	256.7
70°	309.3	301.9	294.5	287.1	279.7	270.6	259.8	248.8	238.0	227.1	220.4
72.5°	271.7	264.5	257.3	250.1	242.9	234.1	223.9	213.8	203.6	193.4	187.2
75°	215.4	208.9	202.3	195.8	189.3	181.4	172.3	163.2	154.0	144.9	140.1
77.5°	159.4	154.1	148.9	143.7	138.5	132.2	124.9	117.6	110.3	103.0	99.6
80°	127.2	122.1	116.8	111.6	106.4	100.8	94.6	88.5	82.5	76.3	74.4
82.5°	96.0	91.2	86.5	81.8	77.1	72.7	68.5	64.4	60.1	56.0	55.0
85°	53.8	50.0	46.0	42.1	38.2	35.6	34.6	33.5	32.4	31.3	31.1
87.5°	18.1	17.0	15.8	14.8	13.7	13.1	13.0	13.0	12.8	12.8	12.9
90°	0.4	0.7	1.3	2.0	2.6	3.3	3.7	4.3	4.6	5.4	5.7
92.5°	4.1	4.9	7.7	11.9	17.6	27.3	45.5	76.0	109.1	107.4	86.9
95°	11.0	11.3	13.9	17.6	25.0	40.0	75.6	148.9	240.8	295.1	288.8
97.5°	18.3	18.7	20.5	24.2	30.8	41.6	65.1	118.9	215.1	315.2	365.4
100°	23.3	23.9	25.4	28.9	35.3	45.3	64.7	107.9	191.9	300.8	384.1
102.5°	28.9	29.3	30.3	34.3	40.2	49.9	67.0	103.4	174.3	275.5	372.9
105°	37.6	37.6	39.3	42.6	48.0	57.3	71.9	101.6	157.2	241.5	337.1
107.5°	46.2	46.8	48.4	51.2	56.7	65.1	79.3	104.6	150.1	218.1	300.6
110°	52.3	53.0	54.3	57.3	62.3	71.0	84.6	107.6	147.9	207.2	279.8



TEST NUMBER: P333555-830

CATALOG NUMBER: S125RDIP-S850D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	58.4	59.1	60.1	63.2	68.1	76.5	89.6	111.3	147.9	200.8	264.4
115°	67.3	68.0	69.0	71.9	76.9	85.3	97.6	116.9	148.9	193.9	247.5
117.5°	75.3	76.3	77.4	80.3	86.1	94.1	105.8	123.3	151.1	190.5	237.4
120°	80.6	81.6	82.9	86.0	91.6	99.9	111.6	127.6	153.3	188.9	231.9
122.5°	86.2	86.9	88.0	91.0	97.2	105.6	117.2	132.3	155.0	187.6	227.1
125°	93.3	94.0	95.6	98.6	104.9	113.6	124.6	138.9	158.3	185.9	220.6
127.5°	98.8	99.8	101.9	105.8	112.4	121.1	131.7	144.9	161.7	185.1	214.5
130°	102.3	103.3	105.9	110.3	117.3	125.9	136.2	148.9	163.9	184.5	210.6
132.5°	104.9	106.2	109.4	114.2	121.5	130.2	140.5	152.4	166.3	184.5	207.4
135°	109.2	110.6	114.6	119.9	127.0	135.9	146.2	157.2	169.6	184.5	203.5
137.5°	114.7	115.7	119.4	124.8	131.7	140.9	150.3	160.8	172.6	184.9	200.1
140°	117.9	118.9	122.9	128.3	134.6	143.5	153.3	163.2	173.9	185.2	198.5
142.5°	121.7	122.3	126.1	131.5	137.5	146.0	155.0	164.6	174.7	185.5	197.2
145°	127.2	127.9	131.2	135.9	141.9	149.6	158.3	166.5	175.5	185.2	195.2
147.5°	133.1	133.5	136.4	140.7	145.9	152.6	160.2	167.8	175.9	184.4	193.1
150°	136.6	137.2	139.6	143.9	148.5	154.2	161.6	168.5	175.9	183.5	191.5
152.5°	140.3	140.7	142.8	146.6	151.0	156.1	162.9	169.1	175.6	182.5	189.6
155°	145.2	145.2	147.2	150.5	153.9	158.5	164.2	169.6	174.8	180.6	186.5
157.5°	149.7	149.6	151.2	154.0	156.9	160.5	165.3	169.8	174.0	178.5	183.6
160°	152.6	152.2	153.5	155.9	158.5	161.6	165.9	169.8	173.2	177.2	181.3
162.5°	155.0	154.7	156.0	158.1	160.1	162.6	166.5	169.7	172.4	175.6	179.1
165°	158.5	157.9	158.9	160.5	161.9	163.9	166.5	169.2	171.3	173.2	175.9
167.5°	161.0	160.6	161.3	162.1	163.1	164.4	166.5	168.4	169.4	170.9	172.8
170°	162.6	162.2	162.6	163.2	163.9	164.9	166.5	167.9	168.5	169.6	170.9
172.5°	163.6	163.1	163.3	164.0	164.4	164.9	166.3	167.4	167.5	168.0	169.0
175°	164.9	164.2	164.6	164.9	164.9	164.9	165.9	166.5	166.3	166.3	166.5
177.5°	165.5	164.9	164.9	165.2	164.9	164.9	165.5	165.8	165.2	165.2	165.5
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333555-830

CATALOG NUMBER: S125RDIP-S850D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1291.7	1293.5	1295.1	1296.0	1295.8	1295.6	1295.4	1295.2
5°	1283.7	1285.9	1288.1	1289.0	1288.5	1288.1	1287.7	1287.2
7.5°	1267.8	1269.3	1270.8	1271.3	1270.8	1270.4	1269.9	1269.4
10°	1254.2	1254.9	1255.6	1255.6	1254.9	1254.2	1253.6	1253.0
12.5°	1235.1	1235.6	1236.1	1235.9	1234.8	1233.8	1232.8	1231.8
15°	1203.6	1203.3	1203.2	1202.1	1200.1	1198.2	1196.2	1194.2
17.5°	1164.2	1163.2	1162.1	1160.7	1159.1	1157.5	1155.9	1154.3
20°	1135.3	1134.2	1133.1	1131.6	1129.6	1127.7	1125.7	1123.8
22.5°	1106.5	1104.5	1102.3	1100.4	1098.8	1097.2	1095.6	1094.0
25°	1059.4	1056.6	1053.8	1051.1	1048.7	1046.3	1044.0	1041.5
27.5°	1008.3	1004.4	1000.4	997.3	995.0	992.7	990.4	988.1
30°	971.9	966.9	961.8	958.4	956.4	954.4	952.4	950.5
32.5°	936.3	930.8	925.3	921.2	918.8	916.3	913.8	911.3
35°	881.1	874.8	868.5	863.8	860.7	857.7	854.7	851.6
37.5°	823.4	815.8	808.2	803.0	800.0	797.0	794.1	791.2
40°	785.1	776.9	768.6	763.2	760.6	758.0	755.4	752.8
42.5°	747.5	739.6	731.7	725.8	722.0	718.1	714.3	710.5
45°	687.4	678.7	670.0	664.0	660.7	657.5	654.2	650.9
47.5°	627.9	619.0	610.0	603.7	600.1	596.5	592.9	589.3
50°	587.7	578.5	569.4	563.2	560.0	556.7	553.4	550.2
52.5°	549.5	539.6	529.8	523.2	520.0	516.7	513.5	510.2
55°	491.4	481.6	471.8	465.1	461.8	458.3	454.8	451.3
57.5°	433.3	423.8	414.2	407.8	404.7	401.6	398.6	395.5
60°	394.9	385.3	375.8	369.4	366.1	362.9	359.6	356.3
62.5°	357.1	348.3	339.4	333.4	330.1	326.8	323.6	320.3
65°	301.7	293.0	284.3	278.3	275.0	271.8	268.5	265.2
67.5°	248.7	240.8	232.8	227.5	225.0	222.3	219.7	217.2
70°	213.6	206.9	200.1	195.5	192.8	190.2	187.7	185.0
72.5°	181.0	174.7	168.5	164.6	162.8	161.1	159.4	157.6
75°	135.3	130.5	125.7	122.6	121.0	119.5	118.0	116.5
77.5°	96.2	92.9	89.5	87.4	86.2	85.1	84.0	82.8
80°	72.5	70.5	68.5	67.3	66.9	66.4	66.0	65.6
82.5°	54.2	53.3	52.3	51.7	51.5	51.3	51.0	50.7
85°	30.9	30.6	30.4	30.3	30.0	29.8	29.6	29.4
87.5°	12.9	13.0	13.1	13.1	12.9	12.8	12.6	12.5
90°	6.0	6.3	6.7	7.4	7.4	7.4	7.6	7.6
92.5°	59.0	42.8	32.2	27.3	23.1	22.2	21.8	21.2
95°	239.5	188.9	147.9	119.9	96.2	86.2	83.6	78.3
97.5°	356.7	321.2	281.3	242.3	221.8	203.1	193.5	189.2
100°	409.7	393.4	359.1	324.4	301.4	277.5	265.1	259.9
102.5°	427.5	437.6	421.2	397.8	373.2	356.1	342.7	338.7
105°	417.1	462.7	477.3	473.7	463.0	452.0	445.4	441.4
107.5°	379.5	440.4	478.0	495.4	500.8	500.8	498.5	495.9
110°	351.8	415.1	462.0	490.3	505.3	511.6	514.0	514.0



TEST NUMBER: P333555-830

CATALOG NUMBER: S125RDIP-S850D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.9	390.0	437.5	470.9	492.8	503.7	509.4	511.9
115°	302.5	354.1	399.7	436.0	462.0	478.0	487.3	491.6
117.5°	284.7	329.2	368.5	401.9	427.8	444.4	453.6	456.3
120°	275.1	315.1	351.8	381.1	405.8	421.7	430.7	433.4
122.5°	268.0	305.0	337.6	365.0	387.1	401.7	410.8	413.1
125°	257.5	291.4	320.5	344.4	363.1	376.7	384.1	387.4
127.5°	246.9	278.5	305.6	328.0	345.0	357.0	363.9	365.4
130°	240.2	269.5	295.5	317.2	333.8	344.8	351.5	353.5
132.5°	233.5	261.0	284.6	305.4	322.1	333.0	339.1	341.4
135°	224.9	247.8	269.2	288.1	302.8	313.8	319.8	321.8
137.5°	217.5	236.1	253.8	269.9	283.0	293.0	298.6	300.8
140°	213.5	229.1	244.5	258.4	270.8	279.5	284.5	286.2
142.5°	210.1	223.3	236.5	248.6	259.1	266.5	271.2	272.6
145°	205.6	215.8	226.2	235.2	243.2	248.8	252.5	253.8
147.5°	201.2	209.6	217.6	224.4	230.7	235.3	237.3	238.0
150°	198.9	206.2	212.5	218.5	223.5	227.5	228.8	229.1
152.5°	196.2	202.7	208.5	213.2	217.4	220.6	221.9	222.3
155°	192.2	197.6	202.2	205.9	209.2	211.5	212.5	212.8
157.5°	188.2	192.6	196.2	199.1	201.7	203.6	204.5	204.4
160°	185.6	188.9	192.2	194.5	196.9	198.5	199.2	198.9
162.5°	182.6	185.7	188.5	190.6	192.4	193.7	193.9	193.8
165°	178.5	180.9	182.9	184.5	185.9	186.5	186.5	186.5
167.5°	174.7	176.3	177.8	179.0	179.6	180.2	179.9	179.8
170°	172.6	173.5	174.6	175.2	175.9	176.3	176.3	175.9
172.5°	170.1	171.2	171.9	172.3	172.4	173.1	172.5	172.1
175°	167.6	167.6	168.2	168.2	168.2	168.5	167.9	167.6
177.5°	165.8	166.0	166.0	166.0	165.8	166.0	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2

(END OF REPORT)