

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333203-840

Luminaire Tested: **S125DIP-S610D1205U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333203-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D1205U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6734.9 lumens
Efficiency: N/A
Efficacy: 136.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333203-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333203-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38
1	95	91	87	83	86	82	79	76	67	65	62	53	51	50	39	38	38	31
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	21	17	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6264	6264	6264
5°	6278	6218	6257
10°	6239	6174	6209
15°	6171	6100	6125
20°	6075	5996	6006
25°	5971	5872	5867
30°	5842	5739	5711
35°	5705	5595	5517
40°	5563	5440	5363
45°	5411	5298	5193
50°	5243	5127	4972
55°	5080	4933	4796
60°	4886	4738	4570
65°	4655	4504	4351
70°	4434	4232	4086
75°	4040	3905	3773
80°	3593	3537	3451
85°	3127	3179	3016



TEST NUMBER: P333203-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.4
10°-20°	258.3	3.8
20°-30°	381.4	5.7
30°-40°	445.0	6.6
40°-50°	447.0	6.6
50°-60°	392.4	5.8
60°-70°	292.4	4.3
70°-80°	167.2	2.5
80°-90°	51.9	0.8
90°-100°	101.0	1.5
100°-110°	298.2	4.4
110°-120°	505.2	7.5
120°-130°	664.8	9.9
130°-140°	745.0	11.1
140°-150°	730.1	10.8
150°-160°	613.2	9.1
160°-170°	407.6	6.1
170°-180°	142.7	2.1
0°-30°	731.2	10.9
0°-40°	1176.2	17.5
0°-60°	2015.6	29.9
0°-90°	2527.0	37.5
90°-120°	904.4	13.4
90°-150°	3044.3	45.2
90°-180°	4208.0	62.5
0°-180°	6734.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	968	966	959	966	965	92
15°	923	920	912	916	916	260
25°	838	834	824	825	823	385
35°	724	720	710	706	700	452
45°	592	589	580	571	569	456
55°	451	448	438	431	426	403
65°	305	303	295	288	285	302
75°	162	160	156	154	151	173
85°	42	43	43	42	41	47
90°	1	10	19	24	28	7
95°	76	79	90	98	101	81
105°	268	274	280	287	291	286
115°	506	510	513	512	510	500
125°	738	745	746	744	743	661
135°	960	967	968	968	963	740
145°	1163	1168	1171	1171	1168	727
155°	1331	1331	1332	1336	1331	613
165°	1447	1445	1446	1450	1443	408
175°	1504	1500	1500	1506	1498	143
180°	1508	1508	1508	1508	1508	



TEST NUMBER: P333203-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	972.3	971.9	971.5	971.1	970.7	969.8	968.5	967.0	965.7	964.3	965.7
5°	968.4	968.0	967.7	967.2	966.9	965.9	964.2	962.5	960.8	959.1	960.7
7.5°	959.4	959.1	958.8	958.4	958.1	956.9	955.0	953.2	951.3	949.5	950.9
10°	951.4	951.1	950.8	950.4	950.1	949.0	947.1	945.2	943.3	941.5	942.8
12.5°	941.6	941.0	940.4	939.8	939.2	938.0	936.2	934.5	932.7	931.0	932.1
15°	923.0	922.5	922.0	921.5	921.0	919.8	918.0	916.0	914.1	912.3	913.1
17.5°	901.7	901.0	900.2	899.5	898.7	897.4	895.4	893.4	891.5	889.6	890.6
20°	883.9	883.5	883.2	882.9	882.5	881.3	879.1	876.9	874.6	872.4	873.6
22.5°	866.1	865.5	864.8	864.2	863.6	862.3	860.2	858.2	856.1	853.9	854.7
25°	837.9	837.0	836.2	835.4	834.5	832.9	830.7	828.5	826.3	824.0	824.5
27.5°	804.9	804.4	803.9	803.3	802.8	801.4	799.1	796.9	794.6	792.3	792.3
30°	783.4	782.8	782.3	781.8	781.3	779.8	777.3	774.7	772.1	769.6	769.2
32.5°	760.0	759.3	758.5	757.7	756.9	755.4	753.2	750.8	748.5	746.3	745.7
35°	723.6	722.9	722.2	721.5	720.8	719.3	716.9	714.5	712.2	709.7	708.9
37.5°	685.6	684.8	684.0	683.1	682.3	680.6	678.4	676.2	673.9	671.7	670.4
40°	659.8	659.0	658.1	657.3	656.4	654.8	652.5	650.1	647.6	645.3	643.8
42.5°	632.3	631.6	630.8	630.1	629.3	627.8	625.4	623.1	620.7	618.2	616.9
45°	592.4	591.7	591.0	590.3	589.7	588.2	586.2	584.2	582.1	580.1	578.0
47.5°	549.4	549.4	549.5	549.5	549.5	548.3	545.8	543.4	541.0	538.5	536.4
50°	521.8	521.2	520.7	520.2	519.7	518.5	516.3	514.3	512.3	510.3	508.1
52.5°	493.5	493.1	492.8	492.4	492.0	490.7	488.6	486.4	484.2	482.0	480.1
55°	451.2	450.6	450.1	449.6	449.1	447.7	445.2	442.9	440.5	438.1	436.6
57.5°	406.5	406.3	406.0	405.7	405.5	404.2	402.2	400.2	398.2	396.3	394.3
60°	378.3	377.6	376.9	376.2	375.6	374.3	372.4	370.5	368.6	366.8	365.1
62.5°	348.8	348.3	347.7	347.2	346.6	345.6	344.0	342.3	340.7	339.1	337.3
65°	304.6	304.3	304.0	303.6	303.3	302.2	300.2	298.4	296.5	294.7	293.1
67.5°	261.8	261.1	260.3	259.6	258.9	257.9	256.5	255.1	253.7	252.3	251.0
70°	234.8	234.0	233.1	232.3	231.4	230.1	228.6	227.1	225.6	224.1	223.0
72.5°	205.3	204.7	204.2	203.6	203.0	202.2	201.3	200.3	199.2	198.2	197.1
75°	161.9	161.6	161.2	160.9	160.6	160.0	159.1	158.2	157.3	156.5	156.0
77.5°	121.9	121.7	121.6	121.4	121.3	121.0	120.5	120.1	119.6	119.1	118.8
80°	96.6	96.6	96.6	96.6	96.6	96.5	96.1	95.8	95.5	95.1	94.9
82.5°	74.6	74.3	74.0	73.7	73.5	73.3	73.2	73.2	73.1	73.0	72.7
85°	42.2	42.4	42.5	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.8
87.5°	16.8	17.3	17.7	18.1	18.5	18.8	19.0	19.3	19.5	19.7	20.0
90°	1.2	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1
92.5°	28.4	29.9	31.3	32.8	34.2	36.1	38.4	40.6	42.8	45.0	46.8
95°	76.2	76.7	77.4	77.9	78.4	79.9	82.5	85.1	87.8	90.4	92.2
97.5°	126.7	126.9	127.1	127.3	127.5	129.5	133.1	136.6	140.3	143.9	145.6
100°	164.3	164.3	164.3	164.3	164.3	166.0	169.4	172.8	176.1	179.6	181.9
102.5°	204.7	205.7	206.7	207.8	208.8	210.3	212.0	213.7	215.4	217.1	219.6
105°	267.5	268.8	270.1	271.5	272.8	274.2	275.8	277.3	278.9	280.4	282.1
107.5°	337.0	338.3	339.6	340.9	342.2	343.5	344.7	345.9	347.1	348.3	349.1
110°	385.0	386.2	387.5	388.8	390.1	391.1	391.9	392.7	393.5	394.3	395.1



TEST NUMBER: P333203-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	433.7	434.4	435.0	435.8	436.5	437.3	438.3	439.3	440.2	441.2	441.6
115°	505.7	506.9	507.9	508.9	510.0	510.7	511.3	511.8	512.3	512.8	512.6
117.5°	578.0	578.6	579.1	579.5	580.0	580.4	580.9	581.4	581.8	582.3	582.5
120°	623.1	624.4	625.7	627.0	628.3	629.1	629.3	629.7	630.0	630.2	630.2
122.5°	672.0	672.5	672.9	673.4	673.8	674.4	675.1	675.8	676.4	677.1	676.9
125°	738.1	739.7	741.2	742.9	744.4	745.3	745.6	745.8	746.1	746.4	745.8
127.5°	808.6	809.4	810.3	811.2	812.1	812.7	813.0	813.3	813.6	814.0	813.6
130°	850.8	852.1	853.4	854.7	856.0	857.0	857.5	858.0	858.5	859.0	858.8
132.5°	893.0	895.1	897.4	899.5	901.6	902.6	902.5	902.4	902.3	902.2	901.9
135°	960.0	961.5	963.1	964.6	966.2	967.1	967.3	967.7	967.9	968.2	968.2
137.5°	1022.8	1024.3	1025.8	1027.3	1028.9	1030.0	1030.5	1031.1	1031.7	1032.2	1032.5
140°	1063.2	1064.5	1065.8	1067.1	1068.4	1069.4	1070.3	1071.1	1071.8	1072.6	1073.1
142.5°	1103.6	1104.7	1105.8	1106.8	1107.9	1109.0	1109.9	1111.0	1112.0	1113.0	1113.3
145°	1163.0	1164.0	1165.1	1166.1	1167.1	1168.0	1168.8	1169.6	1170.3	1171.1	1171.1
147.5°	1217.9	1218.4	1219.0	1219.6	1220.1	1220.7	1221.4	1222.0	1222.6	1223.2	1223.9
150°	1254.5	1254.3	1253.9	1253.7	1253.4	1253.8	1254.9	1255.9	1257.0	1258.0	1258.0
152.5°	1284.5	1284.9	1285.3	1285.7	1286.0	1286.4	1286.8	1287.2	1287.7	1288.1	1288.7
155°	1330.8	1330.8	1330.8	1330.8	1330.8	1330.9	1331.2	1331.4	1331.7	1331.9	1333.0
157.5°	1372.1	1371.5	1370.9	1370.4	1369.8	1369.6	1369.9	1370.2	1370.4	1370.7	1371.7
160°	1396.4	1395.7	1394.9	1394.1	1393.3	1393.1	1393.3	1393.6	1393.9	1394.1	1395.1
162.5°	1418.1	1417.5	1416.9	1416.3	1415.7	1415.5	1415.5	1415.6	1415.6	1415.7	1416.9
165°	1446.9	1446.4	1445.9	1445.4	1444.8	1444.7	1445.0	1445.2	1445.5	1445.7	1446.8
167.5°	1471.4	1470.3	1469.3	1468.2	1467.1	1466.6	1466.6	1466.6	1466.6	1466.6	1468.2
170°	1484.5	1483.5	1482.4	1481.4	1480.4	1479.8	1479.8	1479.8	1479.8	1479.8	1481.4
172.5°	1493.9	1492.9	1491.8	1490.8	1489.8	1489.1	1489.1	1489.1	1489.1	1489.1	1490.8
175°	1504.4	1503.4	1502.4	1501.3	1500.3	1499.8	1499.8	1499.8	1499.8	1499.8	1501.3
177.5°	1509.8	1509.0	1508.1	1507.3	1506.5	1506.0	1505.8	1505.6	1505.3	1505.1	1506.4
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333203-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	967.0	968.5	969.8	970.4	970.3	970.1	970.0	969.9
5°	962.2	963.7	965.2	965.9	965.7	965.6	965.4	965.2
7.5°	952.4	953.9	955.4	956.1	955.9	955.7	955.6	955.4
10°	944.2	945.5	947.0	947.6	947.4	947.2	947.0	946.8
12.5°	933.2	934.3	935.3	935.9	935.8	935.8	935.8	935.7
15°	914.0	914.8	915.7	916.1	916.1	916.1	916.1	916.1
17.5°	891.7	892.7	893.8	893.9	893.0	892.2	891.4	890.5
20°	874.7	876.0	877.2	877.4	876.5	875.7	874.7	873.9
22.5°	855.6	856.4	857.2	857.3	856.7	856.1	855.5	855.0
25°	824.8	825.1	825.5	825.4	824.9	824.4	823.8	823.3
27.5°	792.4	792.5	792.5	792.3	791.8	791.3	790.8	790.3
30°	768.9	768.6	768.2	767.8	767.3	766.8	766.3	765.8
32.5°	745.1	744.4	743.8	743.1	742.1	741.2	740.2	739.3
35°	708.0	707.2	706.3	705.2	703.9	702.5	701.1	699.7
37.5°	669.1	667.9	666.6	665.6	664.8	664.1	663.3	662.5
40°	642.2	640.7	639.1	638.1	637.6	637.1	636.6	636.1
42.5°	615.5	614.1	612.7	611.6	610.8	610.1	609.3	608.4
45°	575.9	573.9	571.9	570.6	570.1	569.6	569.1	568.6
47.5°	534.3	532.2	530.2	528.6	527.4	526.1	524.9	523.7
50°	505.8	503.6	501.4	499.7	498.5	497.3	496.0	494.9
52.5°	478.1	476.2	474.2	472.6	471.3	469.9	468.6	467.3
55°	435.0	433.5	432.0	430.6	429.4	428.2	427.1	425.9
57.5°	392.2	390.3	388.3	387.0	386.4	385.7	385.1	384.5
60°	363.3	361.6	359.9	358.5	357.3	356.1	354.9	353.8
62.5°	335.5	333.7	331.7	330.4	329.5	328.5	327.6	326.7
65°	291.5	290.0	288.5	287.4	286.7	286.0	285.4	284.7
67.5°	249.7	248.4	247.1	246.2	245.8	245.4	245.0	244.6
70°	222.0	221.0	219.9	219.1	218.4	217.7	217.0	216.4
72.5°	195.9	194.8	193.6	192.7	192.0	191.4	190.7	190.0
75°	155.5	155.0	154.5	153.9	153.2	152.5	151.9	151.2
77.5°	118.5	118.2	117.9	117.4	116.9	116.5	116.0	115.5
80°	94.8	94.6	94.4	94.2	93.8	93.5	93.2	92.8
82.5°	72.4	72.1	71.8	71.6	71.6	71.5	71.4	71.4
85°	42.6	42.4	42.3	42.0	41.7	41.3	41.0	40.7
87.5°	20.2	20.5	20.8	20.8	20.7	20.6	20.5	20.4
90°	21.4	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	48.5	50.2	51.9	53.1	53.6	54.2	54.8	55.3
95°	94.0	95.8	97.7	98.9	99.4	99.9	100.4	100.9
97.5°	147.3	149.1	150.8	151.8	152.1	152.4	152.7	153.0
100°	184.2	186.6	188.9	190.4	190.9	191.4	192.0	192.5
102.5°	222.2	224.8	227.3	228.9	229.7	230.5	231.2	231.9
105°	283.6	285.2	286.7	287.9	288.7	289.4	290.2	291.0
107.5°	349.8	350.6	351.4	351.8	351.7	351.7	351.6	351.5
110°	395.9	396.7	397.4	397.7	397.4	397.2	396.9	396.7



TEST NUMBER: P333203-840

CATALOG NUMBER: S125DIP-S610D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	442.0	442.3	442.7	442.6	442.2	441.7	441.2	440.8
115°	512.3	512.0	511.8	511.5	511.3	511.0	510.7	510.5
117.5°	582.7	582.9	583.1	582.7	581.7	580.7	579.6	578.6
120°	630.2	630.2	630.2	629.7	628.6	627.5	626.5	625.5
122.5°	676.7	676.5	676.3	675.8	674.9	674.1	673.3	672.5
125°	745.3	744.8	744.3	743.9	743.7	743.4	743.1	742.9
127.5°	813.4	813.1	812.9	812.5	812.0	811.4	810.9	810.4
130°	858.5	858.2	858.0	857.6	857.1	856.6	856.0	855.5
132.5°	901.7	901.4	901.1	900.7	899.9	899.2	898.5	897.8
135°	968.2	968.2	968.2	967.7	966.5	965.5	964.5	963.4
137.5°	1032.9	1033.2	1033.5	1033.0	1031.7	1030.4	1029.1	1027.7
140°	1073.6	1074.2	1074.7	1074.3	1073.0	1071.7	1070.4	1069.0
142.5°	1113.6	1113.9	1114.2	1113.7	1112.4	1111.2	1109.8	1108.5
145°	1171.1	1171.1	1171.1	1170.7	1170.0	1169.2	1168.4	1167.6
147.5°	1224.6	1225.2	1225.8	1225.2	1223.5	1221.6	1219.9	1218.1
150°	1258.0	1258.0	1258.0	1257.8	1257.2	1256.7	1256.2	1255.7
152.5°	1289.3	1289.9	1290.5	1290.4	1289.5	1288.5	1287.6	1286.7
155°	1334.0	1335.0	1336.2	1336.0	1334.6	1333.3	1332.1	1330.8
157.5°	1372.7	1373.8	1374.8	1374.5	1372.8	1371.1	1369.4	1367.7
160°	1396.2	1397.2	1398.3	1398.2	1396.8	1395.5	1394.2	1393.0
162.5°	1418.3	1419.5	1420.8	1420.6	1419.1	1417.5	1416.0	1414.5
165°	1447.8	1448.9	1450.0	1449.7	1448.1	1446.5	1445.0	1443.4
167.5°	1469.8	1471.4	1472.9	1472.9	1471.3	1469.7	1468.0	1466.4
170°	1482.9	1484.5	1486.0	1485.9	1484.1	1482.3	1480.5	1478.6
172.5°	1492.3	1493.9	1495.4	1495.4	1493.8	1492.2	1490.6	1488.9
175°	1502.9	1504.4	1506.0	1505.9	1504.1	1502.3	1500.4	1498.5
177.5°	1507.6	1508.9	1510.2	1510.1	1508.6	1507.1	1505.7	1504.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)