

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333166-840

Luminaire Tested: **S125DIP-S610D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333166-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D365U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4003.5 lumens
Efficiency: N/A
Efficacy: 145.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333166-840

CATALOG NUMBER: S125DIP-S610D365U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333166-840

CATALOG NUMBER: S125DIP-S610D365U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	44
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	44	41	37
4	76	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	28
6	65	52	44	38	61	50	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	17
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6264	6264	6264
5°	6278	6218	6257
10°	6239	6174	6209
15°	6171	6100	6125
20°	6075	5996	6006
25°	5971	5872	5867
30°	5842	5739	5711
35°	5705	5595	5517
40°	5563	5440	5363
45°	5411	5298	5193
50°	5243	5127	4972
55°	5080	4933	4796
60°	4886	4738	4570
65°	4655	4504	4351
70°	4434	4232	4086
75°	4040	3905	3773
80°	3593	3537	3451
85°	3127	3179	3016



TEST NUMBER: P333166-840

CATALOG NUMBER: S125DIP-S610D365U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	2.3
10°-20°	258.3	6.5
20°-30°	381.4	9.5
30°-40°	445.0	11.1
40°-50°	447.0	11.2
50°-60°	392.4	9.8
60°-70°	292.4	7.3
70°-80°	167.2	4.2
80°-90°	49.6	1.2
90°-100°	17.5	0.4
100°-110°	107.8	2.7
110°-120°	195.6	4.9
120°-130°	251.0	6.3
130°-140°	270.0	6.7
140°-150°	253.4	6.3
150°-160°	205.0	5.1
160°-170°	132.6	3.3
170°-180°	45.7	1.1
0°-30°	731.2	18.3
0°-40°	1176.2	29.4
0°-60°	2015.6	50.3
0°-90°	2524.7	63.1
90°-120°	321.0	8.0
90°-150°	1095.4	27.4
90°-180°	1479.0	36.9
0°-180°	4003.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	968	966	959	966	965	92
15°	923	920	912	916	916	260
25°	838	834	824	825	823	385
35°	724	720	710	706	700	452
45°	592	589	580	571	569	456
55°	451	448	438	431	426	403
65°	305	303	295	288	285	302
75°	162	160	156	154	151	173
85°	42	43	43	42	41	47
90°	0	3	6	7	9	3
95°	20	19	6	7	8	26
105°	105	106	106	106	106	111
115°	197	199	199	198	196	195
125°	280	283	283	281	280	250
135°	350	351	351	350	348	269
145°	405	406	406	406	404	253
155°	446	444	445	446	443	206
165°	471	469	469	471	468	133
175°	482	480	480	482	479	46
180°	482	482	482	482	482	



TEST NUMBER: P333166-840

CATALOG NUMBER: S125DIP-S610D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	972.3	971.9	971.5	971.1	970.7	969.8	968.5	967.0	965.7	964.3	965.7
5°	968.4	968.0	967.7	967.2	966.9	965.9	964.2	962.5	960.8	959.1	960.7
7.5°	959.4	959.1	958.8	958.4	958.1	956.9	955.0	953.2	951.3	949.5	950.9
10°	951.4	951.1	950.8	950.4	950.1	949.0	947.1	945.2	943.3	941.5	942.8
12.5°	941.6	941.0	940.4	939.8	939.2	938.0	936.2	934.5	932.7	931.0	932.1
15°	923.0	922.5	922.0	921.5	921.0	919.8	918.0	916.0	914.1	912.3	913.1
17.5°	901.7	901.0	900.2	899.5	898.7	897.4	895.4	893.4	891.5	889.6	890.6
20°	883.9	883.5	883.2	882.9	882.5	881.3	879.1	876.9	874.6	872.4	873.6
22.5°	866.1	865.5	864.8	864.2	863.6	862.3	860.2	858.2	856.1	853.9	854.7
25°	837.9	837.0	836.2	835.4	834.5	832.9	830.7	828.5	826.3	824.0	824.5
27.5°	804.9	804.4	803.9	803.3	802.8	801.4	799.1	796.9	794.6	792.3	792.3
30°	783.4	782.8	782.3	781.8	781.3	779.8	777.3	774.7	772.1	769.6	769.2
32.5°	760.0	759.3	758.5	757.7	756.9	755.4	753.2	750.8	748.5	746.3	745.7
35°	723.6	722.9	722.2	721.5	720.8	719.3	716.9	714.5	712.2	709.7	708.9
37.5°	685.6	684.8	684.0	683.1	682.3	680.6	678.4	676.2	673.9	671.7	670.4
40°	659.8	659.0	658.1	657.3	656.4	654.8	652.5	650.1	647.6	645.3	643.8
42.5°	632.3	631.6	630.8	630.1	629.3	627.8	625.4	623.1	620.7	618.2	616.9
45°	592.4	591.7	591.0	590.3	589.7	588.2	586.2	584.2	582.1	580.1	578.0
47.5°	549.4	549.4	549.5	549.5	549.5	548.3	545.8	543.4	541.0	538.5	536.4
50°	521.8	521.2	520.7	520.2	519.7	518.5	516.3	514.3	512.3	510.3	508.1
52.5°	493.5	493.1	492.8	492.4	492.0	490.7	488.6	486.4	484.2	482.0	480.1
55°	451.2	450.6	450.1	449.6	449.1	447.7	445.2	442.9	440.5	438.1	436.6
57.5°	406.5	406.3	406.0	405.7	405.5	404.2	402.2	400.2	398.2	396.3	394.3
60°	378.3	377.6	376.9	376.2	375.6	374.3	372.4	370.5	368.6	366.8	365.1
62.5°	348.8	348.3	347.7	347.2	346.6	345.6	344.0	342.3	340.7	339.1	337.3
65°	304.6	304.3	304.0	303.6	303.3	302.2	300.2	298.4	296.5	294.7	293.1
67.5°	261.8	261.1	260.3	259.6	258.9	257.9	256.5	255.1	253.7	252.3	251.0
70°	234.8	234.0	233.1	232.3	231.4	230.1	228.6	227.1	225.6	224.1	223.0
72.5°	205.3	204.7	204.2	203.6	203.0	202.2	201.3	200.3	199.2	198.2	197.1
75°	161.9	161.6	161.2	160.9	160.6	160.0	159.1	158.2	157.3	156.5	156.0
77.5°	121.9	121.7	121.6	121.4	121.3	121.0	120.5	120.1	119.6	119.1	118.8
80°	96.6	96.6	96.6	96.6	96.6	96.5	96.1	95.8	95.5	95.1	94.9
82.5°	74.6	74.3	74.0	73.7	73.5	73.3	73.2	73.2	73.1	73.0	72.7
85°	42.2	42.4	42.5	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.8
87.5°	16.7	16.8	16.9	17.1	17.2	17.2	17.2	17.2	17.2	17.1	17.2
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.2	5.8	6.1
92.5°	5.5	5.0	4.6	4.1	3.7	3.7	4.2	4.7	5.3	5.8	6.1
95°	20.3	20.1	19.9	19.6	19.4	17.8	14.7	11.7	8.7	5.8	6.1
97.5°	42.5	42.9	43.3	43.7	44.2	41.4	35.4	29.5	23.5	17.6	15.3
100°	59.6	59.9	60.1	60.3	60.6	60.8	61.2	61.5	61.8	62.1	50.3
102.5°	77.1	77.4	77.7	78.0	78.3	78.5	78.7	78.9	79.1	79.3	77.1
105°	104.9	105.2	105.6	105.9	106.2	106.3	106.3	106.3	106.3	106.3	106.3
107.5°	133.9	133.9	133.9	133.9	133.9	134.0	134.2	134.3	134.5	134.6	134.6
110°	152.8	152.8	152.8	152.8	152.8	152.9	153.0	153.2	153.3	153.5	153.3



TEST NUMBER: P333166-840

CATALOG NUMBER: S125DIP-S610D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.5	170.7	170.9	171.1	171.3	171.4	171.5	171.6	171.7	171.8	171.5
115°	197.0	197.4	197.8	198.2	198.6	198.8	198.9	199.0	199.1	199.1	198.8
117.5°	224.5	224.5	224.5	224.5	224.5	224.6	224.9	225.2	225.5	225.8	225.4
120°	241.7	241.6	241.6	241.5	241.4	241.5	241.7	241.9	242.2	242.4	242.3
122.5°	256.8	257.1	257.4	257.7	258.0	258.2	258.3	258.4	258.5	258.6	258.5
125°	280.2	280.7	281.3	281.9	282.5	282.8	282.8	282.8	282.8	282.8	282.4
127.5°	302.6	303.0	303.4	303.8	304.2	304.4	304.3	304.3	304.2	304.2	304.0
130°	316.3	316.7	317.1	317.5	317.9	318.1	318.2	318.2	318.3	318.4	318.2
132.5°	330.0	330.4	330.9	331.3	331.8	331.9	331.8	331.6	331.4	331.2	331.2
135°	349.5	349.9	350.4	350.9	351.3	351.5	351.3	351.2	351.0	350.9	350.7
137.5°	367.4	367.8	368.2	368.6	369.0	369.2	369.0	368.9	368.7	368.6	368.6
140°	379.1	379.3	379.4	379.6	379.7	379.8	379.7	379.6	379.5	379.5	379.6
142.5°	389.7	389.8	389.9	389.9	390.0	390.1	390.3	390.4	390.5	390.6	390.6
145°	405.2	405.4	405.5	405.7	405.8	405.9	405.9	405.9	405.9	405.9	406.0
147.5°	418.7	418.7	418.7	418.6	418.6	418.6	418.7	418.8	418.9	419.0	419.1
150°	427.3	427.2	427.0	426.8	426.7	426.7	426.8	427.0	427.2	427.3	427.5
152.5°	435.6	435.3	434.8	434.5	434.1	434.0	434.2	434.4	434.5	434.7	434.8
155°	446.3	445.8	445.2	444.7	444.3	444.1	444.3	444.4	444.6	444.7	445.0
157.5°	454.4	454.1	453.8	453.5	453.3	453.1	453.1	453.2	453.2	453.2	453.4
160°	460.1	459.7	459.2	458.7	458.3	458.1	458.1	458.2	458.3	458.4	458.7
162.5°	464.7	464.2	463.7	463.2	462.8	462.6	462.7	462.7	462.8	462.9	463.3
165°	470.8	470.4	469.9	469.4	469.0	468.8	468.8	468.9	469.0	469.1	469.5
167.5°	475.4	474.9	474.4	473.9	473.4	473.2	473.3	473.4	473.5	473.5	474.1
170°	478.0	477.5	476.9	476.4	475.7	475.5	475.6	475.6	475.7	475.8	476.5
172.5°	479.7	479.2	478.6	478.1	477.5	477.3	477.4	477.6	477.7	477.9	478.4
175°	481.5	481.1	480.6	480.1	479.7	479.5	479.5	479.6	479.7	479.8	480.4
177.5°	482.4	482.0	481.6	481.3	480.9	480.7	480.8	480.9	480.9	481.0	481.4
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5



TEST NUMBER: P333166-840

CATALOG NUMBER: S125DIP-S610D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	967.0	968.5	969.8	970.4	970.3	970.1	970.0	969.9
5°	962.2	963.7	965.2	965.9	965.7	965.6	965.4	965.2
7.5°	952.4	953.9	955.4	956.1	955.9	955.7	955.6	955.4
10°	944.2	945.5	947.0	947.6	947.4	947.2	947.0	946.8
12.5°	933.2	934.3	935.3	935.9	935.8	935.8	935.8	935.7
15°	914.0	914.8	915.7	916.1	916.1	916.1	916.1	916.1
17.5°	891.7	892.7	893.8	893.9	893.0	892.2	891.4	890.5
20°	874.7	876.0	877.2	877.4	876.5	875.7	874.7	873.9
22.5°	855.6	856.4	857.2	857.3	856.7	856.1	855.5	855.0
25°	824.8	825.1	825.5	825.4	824.9	824.4	823.8	823.3
27.5°	792.4	792.5	792.5	792.3	791.8	791.3	790.8	790.3
30°	768.9	768.6	768.2	767.8	767.3	766.8	766.3	765.8
32.5°	745.1	744.4	743.8	743.1	742.1	741.2	740.2	739.3
35°	708.0	707.2	706.3	705.2	703.9	702.5	701.1	699.7
37.5°	669.1	667.9	666.6	665.6	664.8	664.1	663.3	662.5
40°	642.2	640.7	639.1	638.1	637.6	637.1	636.6	636.1
42.5°	615.5	614.1	612.7	611.6	610.8	610.1	609.3	608.4
45°	575.9	573.9	571.9	570.6	570.1	569.6	569.1	568.6
47.5°	534.3	532.2	530.2	528.6	527.4	526.1	524.9	523.7
50°	505.8	503.6	501.4	499.7	498.5	497.3	496.0	494.9
52.5°	478.1	476.2	474.2	472.6	471.3	469.9	468.6	467.3
55°	435.0	433.5	432.0	430.6	429.4	428.2	427.1	425.9
57.5°	392.2	390.3	388.3	387.0	386.4	385.7	385.1	384.5
60°	363.3	361.6	359.9	358.5	357.3	356.1	354.9	353.8
62.5°	335.5	333.7	331.7	330.4	329.5	328.5	327.6	326.7
65°	291.5	290.0	288.5	287.4	286.7	286.0	285.4	284.7
67.5°	249.7	248.4	247.1	246.2	245.8	245.4	245.0	244.6
70°	222.0	221.0	219.9	219.1	218.4	217.7	217.0	216.4
72.5°	195.9	194.8	193.6	192.7	192.0	191.4	190.7	190.0
75°	155.5	155.0	154.5	153.9	153.2	152.5	151.9	151.2
77.5°	118.5	118.2	117.9	117.4	116.9	116.5	116.0	115.5
80°	94.8	94.6	94.4	94.2	93.8	93.5	93.2	92.8
82.5°	72.4	72.1	71.8	71.6	71.6	71.5	71.4	71.4
85°	42.6	42.4	42.3	42.0	41.7	41.3	41.0	40.7
87.5°	17.3	17.4	17.4	17.4	17.2	16.9	16.7	16.5
90°	6.5	6.9	7.3	7.6	7.9	8.1	8.3	8.6
92.5°	6.5	6.9	7.3	7.6	7.7	7.8	7.9	8.0
95°	6.5	6.9	7.3	7.5	7.5	7.5	7.5	7.5
97.5°	13.1	10.8	8.6	7.5	7.5	7.5	7.5	7.5
100°	38.5	26.7	14.8	8.8	8.5	8.2	7.8	7.5
102.5°	74.7	72.5	70.3	66.4	61.1	55.7	50.3	44.9
105°	106.3	106.3	106.3	106.3	106.2	106.1	106.1	106.0
107.5°	134.7	134.7	134.7	134.6	134.4	134.1	133.9	133.6
110°	153.0	152.8	152.6	152.5	152.6	152.6	152.7	152.8



TEST NUMBER: P333166-840

CATALOG NUMBER: S125DIP-S610D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	171.2	170.9	170.6	170.4	170.3	170.2	170.1	170.0
115°	198.5	198.2	197.9	197.5	197.0	196.6	196.1	195.6
117.5°	225.0	224.6	224.2	223.9	223.7	223.5	223.3	223.1
120°	242.1	241.9	241.8	241.5	241.1	240.7	240.2	239.8
122.5°	258.3	258.2	258.0	257.7	257.2	256.8	256.3	255.9
125°	282.1	281.8	281.4	281.1	280.9	280.7	280.4	280.2
127.5°	303.8	303.6	303.5	303.1	302.5	301.8	301.3	300.7
130°	317.9	317.7	317.5	317.1	316.8	316.4	316.0	315.6
132.5°	331.1	331.1	331.0	330.8	330.4	330.0	329.6	329.3
135°	350.6	350.4	350.2	349.9	349.5	349.0	348.5	348.0
137.5°	368.7	368.7	368.7	368.5	368.1	367.7	367.3	366.9
140°	379.8	379.9	380.1	379.9	379.5	379.0	378.5	378.0
142.5°	390.6	390.7	390.7	390.5	390.0	389.5	389.1	388.6
145°	406.1	406.1	406.2	406.0	405.6	405.1	404.6	404.0
147.5°	419.2	419.3	419.4	419.2	418.6	418.0	417.5	416.9
150°	427.6	427.8	427.9	427.7	427.1	426.5	425.8	425.2
152.5°	435.0	435.2	435.4	435.2	434.5	434.0	433.4	432.8
155°	445.2	445.5	445.8	445.6	444.9	444.2	443.6	443.0
157.5°	453.7	453.9	454.2	454.0	453.4	452.7	452.1	451.5
160°	459.0	459.3	459.6	459.5	458.8	458.2	457.6	457.0
162.5°	463.8	464.2	464.7	464.5	463.8	463.1	462.5	461.8
165°	470.0	470.5	471.0	470.9	470.3	469.6	469.0	468.4
167.5°	474.7	475.2	475.8	475.7	475.0	474.3	473.6	472.9
170°	477.1	477.8	478.4	478.4	477.7	477.0	476.2	475.4
172.5°	479.0	479.6	480.1	480.1	479.4	478.6	477.9	477.2
175°	481.0	481.7	482.3	482.3	481.5	480.8	480.1	479.4
177.5°	481.9	482.3	482.7	482.7	482.2	481.7	481.2	480.7
180°	481.5	481.5	481.5	481.5	481.5	481.5	481.5	481.5

(END OF REPORT)