

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333292-930

Luminaire Tested: **S125DIP-S1090D1205U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333292-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D1205U930-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7547.9 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333292-930  
CATALOG NUMBER: S125DIP-S1090D1205U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333292-930

CATALOG NUMBER: S125DIP-S1090D1205U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48	48	48	48	48	48	48																
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40	40	40	40	40	40	40	40	40	40	40	40	40																
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38	34	34	34	34	34	34	34	34	34	34	34	34	34																
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	29	29	29	29	29	29	29	29	29	29	29	29	29																
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24	24	24	24	24	24	24	24	24	24	24																
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	25	21	21	21	21	21	21	21	21	21	21	21	21	21	21															
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	22	19	19	19	19	19	19	19	19	19	19	19	19	19	19															
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17	17	17	17	17	17	17	17	17	17	17	17	17	17															
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15	15	15	15	15	15	15	15	15	15	15	15	15	15															
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13	13	13	13	13	13	13	13	13	13	13	13															
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	20	16	14	12	12	12	12	12	12	12	12	12	12	12	12	12	12															

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8985	8985	8985
5°	9005	8919	8976
10°	8950	8857	8907
15°	8852	8750	8787
20°	8715	8601	8616
25°	8565	8424	8416
30°	8380	8232	8192
35°	8183	8027	7914
40°	7981	7804	7692
45°	7761	7600	7448
50°	7519	7354	7133
55°	7287	7076	6877
60°	7009	6795	6554
65°	6677	6460	6240
70°	6360	6069	5861
75°	5794	5602	5410
80°	5159	5077	4950
85°	4483	4565	4320



TEST NUMBER: P333292-930

CATALOG NUMBER: S125DIP-S1090D1205U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.2	1.7
10°-20°	370.5	4.9
20°-30°	547.1	7.2
30°-40°	638.4	8.5
40°-50°	641.2	8.5
50°-60°	562.8	7.5
60°-70°	419.4	5.6
70°-80°	239.8	3.2
80°-90°	72.4	1.0
90°-100°	46.5	0.6
100°-110°	286.3	3.8
110°-120°	519.2	6.9
120°-130°	666.3	8.8
130°-140°	716.7	9.5
140°-150°	672.7	8.9
150°-160°	544.2	7.2
160°-170°	351.9	4.7
170°-180°	121.4	1.6
0°-30°	1048.8	13.9
0°-40°	1687.2	22.4
0°-60°	2891.2	38.3
0°-90°	3622.8	48.0
90°-120°	851.9	11.3
90°-150°	2907.7	38.5
90°-180°	3925.0	52.0
0°-180°	7547.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1389	1386	1376	1385	1385	132
15°	1324	1320	1309	1314	1314	373
25°	1202	1196	1182	1184	1181	553
35°	1038	1033	1018	1012	1004	649
45°	850	845	832	819	816	655
55°	647	643	628	619	611	578
65°	437	434	423	413	408	433
75°	232	230	224	221	217	248
85°	60	62	62	60	58	68
90°	1	8	15	20	23	6
95°	54	49	15	20	20	69
105°	279	282	282	282	281	295
115°	523	528	529	525	519	518
125°	744	750	750	747	744	664
135°	928	933	931	929	924	715
145°	1076	1077	1077	1078	1073	672
155°	1184	1179	1181	1183	1176	545
165°	1250	1244	1245	1250	1243	353
175°	1278	1273	1274	1280	1272	122
180°	1278	1278	1278	1278	1278	



TEST NUMBER: P333292-930

CATALOG NUMBER: S125DIP-S1090D1205U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1394.7	1394.2	1393.5	1392.9	1392.4	1391.1	1389.1	1387.2	1385.2	1383.2	1385.2
5°	1389.0	1388.5	1388.0	1387.6	1387.1	1385.6	1383.2	1380.7	1378.3	1375.8	1378.0
7.5°	1376.2	1375.7	1375.2	1374.8	1374.3	1372.6	1369.9	1367.3	1364.6	1361.9	1364.1
10°	1364.8	1364.3	1363.8	1363.3	1362.9	1361.2	1358.5	1355.8	1353.2	1350.5	1352.4
12.5°	1350.7	1349.8	1348.9	1348.0	1347.2	1345.5	1343.0	1340.5	1338.0	1335.5	1337.1
15°	1324.0	1323.3	1322.6	1321.8	1321.1	1319.4	1316.7	1314.0	1311.3	1308.6	1309.9
17.5°	1293.5	1292.4	1291.3	1290.2	1289.2	1287.2	1284.4	1281.7	1278.9	1276.0	1277.6
20°	1268.0	1267.5	1267.0	1266.5	1266.0	1264.1	1260.9	1257.8	1254.6	1251.4	1253.1
22.5°	1242.4	1241.5	1240.6	1239.7	1238.8	1236.9	1234.0	1230.9	1228.0	1225.0	1226.1
25°	1201.9	1200.7	1199.5	1198.2	1197.0	1194.8	1191.6	1188.5	1185.3	1182.1	1182.6
27.5°	1154.5	1153.8	1153.1	1152.3	1151.6	1149.7	1146.3	1143.0	1139.8	1136.5	1136.6
30°	1123.7	1123.0	1122.3	1121.5	1120.8	1118.6	1114.9	1111.3	1107.6	1103.9	1103.4
32.5°	1090.3	1089.2	1088.0	1086.9	1085.8	1083.6	1080.3	1077.0	1073.7	1070.5	1069.6
35°	1037.9	1036.9	1035.9	1034.9	1034.0	1031.8	1028.3	1024.9	1021.5	1018.1	1016.8
37.5°	983.5	982.3	981.0	979.8	978.6	976.4	973.1	970.0	966.7	963.5	961.6
40°	946.6	945.3	944.1	942.9	941.7	939.3	935.9	932.5	929.0	925.6	923.4
42.5°	906.9	905.9	904.9	903.8	902.8	900.6	897.2	893.7	890.3	886.9	884.8
45°	849.7	848.7	847.7	846.8	845.8	843.8	840.9	838.0	835.0	832.1	829.2
47.5°	788.1	788.1	788.1	788.2	788.2	786.5	783.0	779.4	775.9	772.4	769.4
50°	748.4	747.7	747.0	746.2	745.5	743.6	740.7	737.8	734.8	731.9	728.7
52.5°	707.9	707.4	706.9	706.3	705.8	703.9	700.8	697.7	694.6	691.4	688.6
55°	647.2	646.5	645.7	645.0	644.2	642.1	638.7	635.3	631.9	628.4	626.2
57.5°	583.1	582.7	582.4	582.0	581.6	579.9	577.0	574.1	571.3	568.3	565.5
60°	542.6	541.6	540.6	539.6	538.7	536.9	534.2	531.5	528.8	526.1	523.7
62.5°	500.3	499.5	498.8	498.0	497.3	495.7	493.3	491.1	488.8	486.5	483.8
65°	436.9	436.4	435.9	435.5	435.0	433.4	430.7	428.0	425.3	422.7	420.4
67.5°	375.5	374.5	373.5	372.4	371.5	369.9	367.9	365.9	363.9	361.9	360.0
70°	336.8	335.6	334.4	333.1	331.9	330.2	328.0	325.8	323.6	321.4	319.9
72.5°	294.6	293.7	292.9	292.0	291.2	290.1	288.7	287.2	285.8	284.4	282.7
75°	232.2	231.7	231.2	230.7	230.2	229.4	228.2	227.0	225.8	224.5	223.8
77.5°	174.8	174.6	174.4	174.2	174.0	173.6	172.8	172.2	171.5	170.8	170.4
80°	138.7	138.7	138.7	138.7	138.7	138.4	137.9	137.5	137.0	136.5	136.2
82.5°	107.0	106.6	106.2	105.8	105.4	105.2	105.1	105.0	104.8	104.8	104.4
85°	60.5	60.7	61.0	61.2	61.5	61.6	61.6	61.6	61.6	61.6	61.4
87.5°	24.0	24.3	24.6	24.9	25.3	25.5	25.6	25.8	25.8	25.9	26.2
90°	1.0	2.6	4.3	6.0	7.7	9.3	10.8	12.2	13.7	15.2	16.2
92.5°	14.6	13.5	12.2	11.1	9.9	9.9	11.3	12.6	13.9	15.2	16.2
95°	54.0	53.4	52.7	52.1	51.4	47.2	39.1	31.1	23.2	15.2	16.2
97.5°	112.8	113.9	115.0	116.2	117.3	110.0	94.1	78.3	62.5	46.6	40.7
100°	158.2	158.9	159.5	160.1	160.8	161.5	162.3	163.2	164.0	164.9	133.5
102.5°	204.5	205.3	206.1	206.8	207.7	208.3	208.8	209.4	209.9	210.3	204.4
105°	278.6	279.4	280.2	281.1	281.9	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	355.6	355.6	355.6	355.6	355.6	355.7	356.1	356.5	357.0	357.4	357.4
110°	405.5	405.5	405.5	405.5	405.5	405.8	406.2	406.6	407.0	407.4	406.8



TEST NUMBER: P333292-930

CATALOG NUMBER: S125DIP-S1090D1205U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	452.6	453.1	453.6	454.0	454.5	454.9	455.2	455.4	455.7	455.9	455.2
115°	523.0	524.1	525.1	526.2	527.3	527.9	528.1	528.3	528.5	528.7	527.9
117.5°	596.0	596.0	595.9	595.9	595.8	596.2	597.0	597.8	598.6	599.4	598.3
120°	641.5	641.2	641.1	640.8	640.7	640.8	641.5	642.1	642.7	643.4	642.9
122.5°	681.7	682.5	683.2	684.0	684.9	685.4	685.7	686.0	686.3	686.6	686.2
125°	743.8	745.3	746.7	748.2	749.7	750.4	750.4	750.4	750.4	750.4	749.6
127.5°	803.2	804.2	805.2	806.2	807.3	807.8	807.6	807.6	807.4	807.3	806.8
130°	839.5	840.6	841.6	842.7	843.8	844.3	844.6	844.8	845.0	845.2	844.6
132.5°	875.9	877.1	878.3	879.5	880.8	881.2	880.7	880.2	879.8	879.3	879.2
135°	927.6	928.9	930.2	931.4	932.7	933.1	932.7	932.3	931.8	931.4	931.0
137.5°	975.2	976.3	977.4	978.4	979.6	979.9	979.6	979.2	978.8	978.4	978.5
140°	1006.2	1006.7	1007.1	1007.5	1008.0	1008.0	1007.9	1007.6	1007.5	1007.2	1007.6
142.5°	1034.3	1034.5	1034.9	1035.1	1035.3	1035.6	1035.9	1036.2	1036.5	1036.8	1036.9
145°	1075.5	1075.9	1076.3	1076.7	1077.1	1077.3	1077.3	1077.3	1077.3	1077.3	1077.6
147.5°	1111.4	1111.3	1111.3	1111.2	1111.1	1111.2	1111.4	1111.7	1112.0	1112.2	1112.5
150°	1134.2	1133.8	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1134.6
152.5°	1156.2	1155.3	1154.3	1153.4	1152.4	1152.2	1152.7	1153.1	1153.5	1153.9	1154.3
155°	1184.4	1183.2	1181.9	1180.6	1179.3	1178.9	1179.3	1179.7	1180.2	1180.6	1181.3
157.5°	1206.2	1205.4	1204.7	1204.0	1203.1	1202.8	1202.9	1202.9	1203.0	1203.0	1203.6
160°	1221.4	1220.1	1218.9	1217.6	1216.3	1215.8	1216.0	1216.2	1216.4	1216.6	1217.5
162.5°	1233.5	1232.2	1230.9	1229.7	1228.4	1227.9	1228.1	1228.3	1228.6	1228.7	1230.0
165°	1249.8	1248.5	1247.2	1246.0	1244.7	1244.2	1244.4	1244.6	1244.8	1245.0	1246.3
167.5°	1261.9	1260.6	1259.3	1258.0	1256.7	1256.1	1256.4	1256.5	1256.8	1257.0	1258.5
170°	1268.8	1267.3	1265.8	1264.3	1262.8	1262.2	1262.4	1262.7	1262.8	1263.1	1264.8
172.5°	1273.3	1271.8	1270.3	1268.9	1267.4	1266.8	1267.2	1267.6	1268.0	1268.4	1269.9
175°	1278.2	1276.9	1275.7	1274.4	1273.2	1272.6	1272.8	1273.1	1273.3	1273.5	1275.1
177.5°	1280.5	1279.4	1278.5	1277.5	1276.4	1276.0	1276.2	1276.4	1276.5	1276.7	1277.9
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333292-930

CATALOG NUMBER: S125DIP-S1090D1205U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1387.2	1389.1	1391.1	1392.0	1391.8	1391.6	1391.4	1391.2
5°	1380.2	1382.4	1384.6	1385.6	1385.4	1385.1	1384.9	1384.6
7.5°	1366.2	1368.4	1370.5	1371.5	1371.3	1371.0	1370.8	1370.5
10°	1354.4	1356.3	1358.3	1359.2	1358.9	1358.7	1358.5	1358.2
12.5°	1338.6	1340.2	1341.7	1342.6	1342.5	1342.4	1342.4	1342.3
15°	1311.1	1312.3	1313.5	1314.2	1314.2	1314.2	1314.2	1314.2
17.5°	1279.1	1280.6	1282.1	1282.3	1281.1	1279.9	1278.6	1277.4
20°	1254.8	1256.5	1258.3	1258.5	1257.3	1256.1	1254.8	1253.6
22.5°	1227.3	1228.4	1229.5	1229.6	1228.8	1228.0	1227.2	1226.3
25°	1183.1	1183.6	1184.1	1183.9	1183.2	1182.4	1181.7	1181.0
27.5°	1136.7	1136.8	1136.9	1136.6	1135.9	1135.1	1134.4	1133.7
30°	1102.9	1102.4	1102.0	1101.4	1100.7	1099.9	1099.2	1098.5
32.5°	1068.7	1067.8	1067.0	1065.8	1064.5	1063.2	1061.8	1060.5
35°	1015.6	1014.4	1013.2	1011.6	1009.7	1007.7	1005.8	1003.8
37.5°	959.9	958.1	956.3	954.8	953.7	952.5	951.4	950.3
40°	921.2	919.0	916.8	915.3	914.6	913.9	913.1	912.4
42.5°	882.9	880.8	878.9	877.3	876.2	875.1	873.9	872.8
45°	826.2	823.3	820.4	818.5	817.7	817.0	816.3	815.5
47.5°	766.5	763.4	760.5	758.1	756.4	754.7	753.0	751.3
50°	725.5	722.4	719.2	716.7	715.0	713.3	711.6	709.9
52.5°	685.8	683.1	680.3	677.9	676.0	674.1	672.2	670.3
55°	624.0	621.8	619.6	617.7	616.0	614.2	612.5	610.8
57.5°	562.7	559.9	557.0	555.1	554.2	553.3	552.4	551.4
60°	521.2	518.8	516.3	514.2	512.5	510.8	509.1	507.4
62.5°	481.2	478.6	475.9	473.9	472.6	471.3	469.9	468.6
65°	418.2	416.0	413.8	412.2	411.2	410.3	409.3	408.3
67.5°	358.2	356.3	354.4	353.2	352.6	352.0	351.5	350.9
70°	318.5	317.0	315.5	314.3	313.3	312.3	311.4	310.4
72.5°	281.1	279.4	277.8	276.5	275.5	274.5	273.5	272.6
75°	223.1	222.3	221.6	220.7	219.7	218.7	217.8	216.8
77.5°	169.9	169.5	169.1	168.5	167.8	167.1	166.4	165.8
80°	136.0	135.7	135.5	135.1	134.6	134.1	133.6	133.1
82.5°	103.9	103.5	103.1	102.7	102.6	102.6	102.5	102.3
85°	61.1	60.9	60.7	60.3	59.8	59.3	58.8	58.3
87.5°	26.3	26.6	26.7	26.7	26.5	26.2	25.9	25.7
90°	17.3	18.3	19.4	20.2	20.9	21.4	22.1	22.7
92.5°	17.3	18.3	19.4	20.1	20.3	20.6	21.0	21.2
95°	17.3	18.3	19.4	19.9	19.9	19.9	19.9	19.9
97.5°	34.7	28.8	22.8	19.9	19.9	19.9	19.9	19.9
100°	102.2	70.8	39.4	23.2	22.4	21.6	20.7	19.9
102.5°	198.4	192.6	186.6	176.5	162.2	147.8	133.5	119.2
105°	282.3	282.3	282.3	282.3	282.0	281.8	281.6	281.4
107.5°	357.5	357.5	357.6	357.3	356.6	356.0	355.4	354.7
110°	406.2	405.5	404.9	404.7	404.9	405.1	405.4	405.5





TEST NUMBER: P333292-930

CATALOG NUMBER: S125DIP-S1090D1205U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	454.4	453.6	452.7	452.2	451.9	451.6	451.3	451.0
115°	527.0	526.2	525.4	524.3	523.0	521.8	520.5	519.3
117.5°	597.2	596.1	595.0	594.2	593.6	593.1	592.6	592.0
120°	642.5	642.1	641.7	641.0	639.9	638.9	637.8	636.7
122.5°	685.7	685.3	684.9	684.0	682.8	681.6	680.4	679.2
125°	748.8	747.9	747.1	746.3	745.7	745.1	744.4	743.8
127.5°	806.3	805.9	805.4	804.5	802.9	801.3	799.7	798.2
130°	843.9	843.3	842.7	841.8	840.7	839.8	838.7	837.6
132.5°	879.1	878.9	878.8	878.2	877.2	876.1	875.1	874.0
135°	930.6	930.2	929.8	928.9	927.6	926.3	925.1	923.8
137.5°	978.6	978.7	978.8	978.3	977.1	976.1	974.9	973.9
140°	1008.0	1008.4	1008.9	1008.4	1007.2	1006.0	1004.7	1003.5
142.5°	1037.0	1037.1	1037.1	1036.6	1035.3	1034.0	1032.7	1031.5
145°	1077.7	1078.0	1078.2	1077.7	1076.4	1075.1	1073.8	1072.6
147.5°	1112.7	1113.0	1113.2	1112.6	1111.1	1109.5	1108.1	1106.5
150°	1135.1	1135.5	1135.9	1135.2	1133.6	1131.9	1130.2	1128.5
152.5°	1154.7	1155.2	1155.6	1155.0	1153.5	1152.0	1150.5	1149.0
155°	1181.9	1182.5	1183.2	1182.6	1181.0	1179.2	1177.5	1175.9
157.5°	1204.4	1205.0	1205.7	1205.2	1203.5	1201.8	1200.1	1198.4
160°	1218.3	1219.1	1220.0	1219.6	1217.9	1216.2	1214.6	1212.8
162.5°	1231.1	1232.3	1233.5	1233.1	1231.3	1229.4	1227.6	1225.7
165°	1247.6	1248.9	1250.1	1249.9	1248.2	1246.5	1244.8	1243.2
167.5°	1260.0	1261.5	1263.1	1262.9	1260.9	1259.1	1257.2	1255.3
170°	1266.4	1268.1	1269.8	1269.7	1267.8	1265.9	1264.0	1262.1
172.5°	1271.4	1272.9	1274.4	1274.2	1272.4	1270.5	1268.5	1266.6
175°	1276.8	1278.6	1280.2	1280.1	1278.2	1276.4	1274.4	1272.5
177.5°	1279.0	1280.3	1281.4	1281.3	1280.0	1278.6	1277.2	1275.9
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2

(END OF REPORT)