

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333180-840

Luminaire Tested: **S125DIP-S610D810U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333180-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5489.6 lumens
Efficiency: N/A
Efficacy: 143.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	46				
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45	40				
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29				
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	31	28	25				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19				
7	58	46	38	32	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	30	25	46	35	29	24	30	25	21	25	21	18	21	18	16	13				
10	47	35	28	23	43	32	26	22	28	23	19	24	19	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5837	5837	5837	5837
5°	6760	5857	5128	5857
10°	7864	5827	4494	5827
15°	8705	5784	4145	5784
20°	9745	5716	3865	5716
25°	11416	5640	3729	5640
30°	12331	5565	3610	5565
35°	10138	5423	3533	5423
40°	7206	5227	3447	5227
45°	5536	4961	3399	4961
50°	4725	4633	3392	4633
55°	4208	4310	3422	4310
60°	3796	3959	3509	3959
65°	3506	3605	3599	3605
70°	3186	3238	3652	3238
75°	2815	2852	3618	2852
80°	2369	2325	3310	2325
85°	1875	1675	2675	1675



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.6
10°-20°	259.1	4.7
20°-30°	420.7	7.7
30°-40°	513.1	9.3
40°-50°	466.8	8.5
50°-60°	371.8	6.8
60°-70°	259.0	4.7
70°-80°	138.1	2.5
80°-90°	37.0	0.7
90°-100°	283.9	5.2
100°-110°	610.3	11.1
110°-120°	572.7	10.4
120°-130°	464.2	8.5
130°-140°	372.5	6.8
140°-150°	281.1	5.1
150°-160°	197.9	3.6
160°-170°	116.6	2.1
170°-180°	37.9	0.7
0°-30°	766.7	14.0
0°-40°	1279.9	23.3
0°-60°	2118.5	38.6
0°-90°	2552.6	46.5
90°-120°	1466.9	26.7
90°-150°	2584.6	47.1
90°-180°	2937.0	53.5
0°-180°	5489.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1043	903	791	903	1043	105
15°	1302	865	620	865	1302	373
25°	1602	791	523	791	1602	732
35°	1286	688	448	688	1286	787
45°	606	543	372	543	606	485
55°	374	383	304	383	374	337
65°	229	236	236	236	229	228
75°	113	114	145	114	113	121
85°	25	23	36	23	25	30
90°	18	1	18	1	18	13
95°	186	26	186	26	186	263
105°	1046	89	1046	89	1046	1040
115°	1166	160	1166	160	1166	1139
125°	918	221	918	221	918	831
135°	763	259	763	259	763	591
145°	602	302	602	302	602	382
155°	504	344	504	344	504	235
165°	442	376	442	376	442	126
175°	397	391	397	391	397	39
180°	392	392	392	392	392	



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	956.0	954.7	953.5	951.1	952.9	947.7	945.2	941.0	935.7	933.9	931.7
5°	1042.7	1044.6	1046.5	1038.4	1039.3	1033.9	1021.6	1011.6	1003.6	993.2	985.9
7.5°	1147.0	1142.5	1142.2	1136.9	1127.9	1120.7	1107.8	1091.4	1075.5	1057.4	1042.5
10°	1199.2	1199.6	1196.2	1190.0	1180.4	1173.5	1156.6	1140.5	1121.0	1097.9	1081.5
12.5°	1238.5	1240.1	1235.8	1227.5	1222.7	1207.3	1194.1	1174.9	1151.7	1133.3	1108.1
15°	1302.0	1297.8	1294.7	1284.3	1276.3	1260.2	1239.1	1219.1	1193.9	1170.4	1147.0
17.5°	1363.2	1366.7	1360.9	1351.4	1326.5	1307.6	1279.3	1252.0	1220.4	1189.1	1161.1
20°	1417.9	1421.0	1412.1	1395.6	1365.7	1346.9	1309.7	1274.3	1238.0	1197.7	1167.0
22.5°	1486.0	1483.6	1471.7	1446.5	1420.7	1385.8	1345.6	1302.6	1257.0	1211.4	1170.6
25°	1602.0	1585.9	1578.6	1547.5	1513.4	1462.4	1407.1	1344.2	1287.5	1227.2	1175.1
27.5°	1666.3	1661.2	1653.1	1631.4	1595.6	1541.1	1475.9	1399.3	1319.1	1243.1	1174.8
30°	1653.5	1654.2	1655.0	1648.0	1625.1	1584.0	1519.1	1436.6	1341.5	1256.0	1177.0
32.5°	1539.2	1553.2	1566.6	1582.4	1588.8	1580.9	1540.3	1465.8	1368.0	1270.7	1175.7
35°	1285.9	1290.1	1333.5	1376.4	1434.7	1480.1	1510.4	1477.3	1394.8	1283.2	1174.3
37.5°	1002.6	1023.4	1053.4	1102.0	1186.1	1261.4	1358.4	1402.9	1376.2	1287.3	1171.5
40°	854.7	873.9	893.4	942.9	1013.9	1105.2	1215.3	1309.3	1331.2	1274.3	1162.4
42.5°	740.5	755.8	777.5	814.7	873.9	954.8	1060.1	1182.9	1258.4	1237.0	1143.1
45°	606.1	615.7	632.6	662.2	705.1	768.4	861.2	995.5	1112.5	1151.2	1097.1
47.5°	518.8	518.8	531.9	552.3	583.3	637.0	705.7	810.9	935.8	1028.3	1024.0
50°	470.3	468.4	478.8	496.4	521.0	556.6	622.3	706.3	826.4	931.1	960.2
52.5°	428.6	428.8	435.2	448.2	468.8	499.3	548.3	624.0	726.6	834.0	889.0
55°	373.7	372.1	379.4	388.2	403.2	423.1	458.5	516.3	599.6	705.5	776.8
57.5°	323.4	327.5	330.4	336.6	349.0	362.3	392.1	434.6	500.7	591.6	667.0
60°	293.9	298.1	300.3	306.5	316.5	328.0	351.0	385.6	441.2	519.5	594.2
62.5°	267.4	270.7	271.6	277.0	285.2	296.4	314.5	343.5	387.5	455.9	529.2
65°	229.4	229.4	231.0	236.7	240.5	250.5	264.3	285.4	320.7	374.1	436.6
67.5°	192.7	194.6	194.2	196.7	200.3	208.0	217.9	235.3	261.5	300.3	350.4
70°	168.7	170.4	170.0	171.9	175.7	180.7	188.7	205.2	224.0	257.4	300.3
72.5°	147.3	147.9	146.9	149.5	151.8	156.1	165.1	173.9	191.5	219.6	255.0
75°	112.8	113.5	114.3	115.8	118.2	120.5	125.0	133.9	145.4	166.5	189.1
77.5°	84.5	83.1	84.9	84.7	86.0	87.8	91.8	96.5	105.9	119.3	136.8
80°	63.7	64.0	64.0	64.4	66.3	67.6	71.0	74.4	81.7	91.7	103.9
82.5°	46.5	47.5	46.9	47.6	49.2	50.0	51.9	54.7	59.0	66.9	75.7
85°	25.3	23.4	24.1	24.9	24.9	25.3	26.9	28.0	30.3	33.3	36.9
87.5°	11.0	11.6	11.7	11.7	12.0	11.7	12.8	12.6	13.4	14.2	15.1
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2	13.4	12.6	11.0
92.5°	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0	206.1	254.6	258.6
95°	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7	684.6	699.6	570.9
97.5°	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6	866.2	747.1	509.8
100°	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2	910.4	713.1	454.8
102.5°	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5	883.9	653.0	413.1
105°	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6	799.1	572.5	372.7
107.5°	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5	712.6	517.1	355.7
110°	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8	663.3	491.1	350.6



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0	626.6	475.9	350.6
115°	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0	586.6	459.6	352.9
117.5°	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0	562.8	451.5	358.2
120°	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2	549.6	447.7	363.2
122.5°	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2	538.2	444.5	367.6
125°	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4	522.7	440.6	375.1
127.5°	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1	508.5	438.7	383.4
130°	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3	499.1	437.5	388.5
132.5°	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5	491.5	437.5	394.2
135°	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0	482.4	437.5	401.9
137.5°	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6	474.4	438.4	409.0
140°	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1	470.6	439.0	412.1
142.5°	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0	467.5	439.7	414.0
145°	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2	462.7	439.0	416.2
147.5°	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1	457.8	437.0	416.9
150°	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4	454.0	435.0	416.9
152.5°	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0	449.6	432.5	416.3
155°	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7	442.2	428.0	414.5
157.5°	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2	435.3	423.2	412.5
160°	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8	429.6	420.1	410.6
162.5°	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8	424.4	416.3	408.7
165°	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2	416.9	410.6	405.9
167.5°	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0	409.5	405.1	401.4
170°	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0	405.1	401.9	399.5
172.5°	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3	400.6	398.1	397.0
175°	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2	394.8	394.0	394.0
177.5°	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9	392.2	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	929.9	927.8	925.3	921.0	915.7	913.0	908.8	905.9	900.4	895.9	890.9
5°	977.0	967.1	958.0	946.0	933.0	924.5	914.5	903.4	891.9	880.0	867.0
7.5°	1025.9	1008.4	989.2	968.5	948.4	929.8	912.0	894.6	878.4	858.7	842.0
10°	1058.8	1036.5	1012.8	984.7	957.6	933.7	909.6	888.5	867.0	843.9	823.6
12.5°	1091.7	1062.0	1028.4	997.6	964.9	936.2	907.8	880.8	853.8	828.3	804.7
15°	1114.8	1088.7	1057.6	1013.9	977.0	937.6	900.0	865.1	832.4	804.1	774.2
17.5°	1130.0	1096.5	1063.1	1021.2	972.9	928.7	886.1	846.2	809.4	773.4	744.6
20°	1132.9	1098.3	1063.4	1022.4	972.9	922.2	879.7	831.7	792.1	755.0	719.6
22.5°	1132.0	1092.8	1054.8	1012.5	964.3	917.7	866.2	817.3	774.4	737.8	700.9
25°	1123.3	1081.5	1033.9	991.3	943.7	894.2	842.0	791.4	747.7	705.9	669.4
27.5°	1116.0	1061.8	1007.9	958.3	912.3	867.0	817.1	765.2	716.7	674.3	640.0
30°	1107.1	1047.6	987.0	935.2	888.1	843.9	796.8	746.2	695.5	654.1	617.2
32.5°	1099.1	1029.9	965.9	909.5	859.6	816.7	773.2	725.0	675.3	633.2	596.4
35°	1083.8	1003.6	930.3	866.6	813.2	769.2	732.8	687.8	642.2	601.5	566.2
37.5°	1064.2	969.1	890.4	823.6	765.2	718.7	684.8	650.4	606.5	567.3	535.4
40°	1048.8	944.5	861.2	792.9	732.4	684.0	652.6	620.0	583.5	547.0	513.3
42.5°	1029.5	922.4	831.7	758.3	698.3	651.2	618.1	590.5	558.4	524.3	493.0
45°	994.0	882.3	784.2	705.1	644.5	598.0	563.9	543.2	519.1	486.9	460.4
47.5°	941.7	834.2	732.7	651.1	588.5	545.5	513.5	493.6	476.7	452.7	428.7
50°	895.3	798.3	695.5	614.6	552.0	508.7	479.2	461.1	446.6	428.1	407.8
52.5°	843.5	753.2	659.0	579.0	517.1	474.3	445.4	429.5	417.4	404.1	384.2
55°	761.1	684.4	596.9	521.0	463.8	422.0	396.7	382.8	372.8	362.9	350.6
57.5°	670.3	610.4	532.8	463.4	410.8	372.7	349.1	335.7	327.9	322.8	315.6
60°	606.5	555.1	488.4	425.1	373.7	339.9	316.9	306.5	300.0	295.8	290.4
62.5°	547.2	505.0	443.2	385.5	340.5	308.6	288.0	278.0	271.8	269.7	265.2
65°	460.0	427.4	376.4	328.4	290.0	262.8	245.5	235.9	232.1	229.7	230.1
67.5°	374.0	354.1	313.2	272.3	241.6	218.7	204.9	197.5	195.6	192.6	192.5
70°	321.4	306.5	272.0	236.3	209.0	191.5	179.2	171.5	169.6	168.0	167.6
72.5°	275.1	262.1	232.1	203.5	179.0	163.5	153.4	148.8	145.6	144.7	144.6
75°	206.8	199.4	175.7	153.1	136.2	125.4	118.6	114.3	112.0	111.6	112.0
77.5°	147.0	140.7	125.5	109.5	98.9	90.7	84.8	83.4	80.8	80.9	80.5
80°	110.5	106.2	96.6	84.0	75.2	68.3	65.2	62.5	61.8	60.6	61.8
82.5°	80.1	75.5	69.1	61.0	53.7	49.6	46.5	45.6	45.1	44.6	44.8
85°	39.5	39.9	36.1	29.9	26.9	24.5	22.6	22.6	22.2	21.9	22.2
87.5°	15.6	14.6	13.2	12.0	10.2	8.9	8.3	8.5	7.7	7.7	8.3
90°	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6	11.7	18.3	28.1
95°	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1	26.9	33.1	41.8
97.5°	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2	44.2	48.7	57.4
100°	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2	56.9	60.0	68.7
102.5°	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6	69.5	72.0	81.3
105°	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3	89.3	93.2	101.1
107.5°	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5	111.0	114.8	121.3
110°	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0	125.5	128.7	135.8



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5	140.1	142.6	149.7
115°	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5	161.1	163.5	170.6
117.5°	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4	180.9	183.4	190.5
120°	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1	193.5	196.6	203.7
122.5°	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4	206.1	208.6	215.7
125°	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1	222.7	226.6	233.7
127.5°	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2	236.6	241.7	250.6
130°	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4	244.8	251.1	261.4
132.5°	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7	251.8	259.3	270.8
135°	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0	262.2	271.7	284.3
137.5°	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0	274.3	283.2	295.8
140°	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5	281.9	291.3	304.0
142.5°	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3	290.1	298.9	311.5
145°	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6	303.2	311.1	322.1
147.5°	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5	316.5	323.3	333.6
150°	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8	325.3	330.8	341.1
152.5°	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5	333.6	338.4	347.4
155°	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3	344.3	349.0	356.9
157.5°	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7	354.6	358.3	365.1
160°	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6	360.8	364.1	369.5
162.5°	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3	366.6	369.7	374.6
165°	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9	374.3	376.7	380.6
167.5°	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5	380.7	382.1	384.4
170°	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4	384.6	385.4	386.9
172.5°	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9	386.5	387.2	388.8
175°	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8	389.3	390.1	390.8
177.5°	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2	391.0	391.0	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	888.2	884.7	882.0	875.9	872.5	867.9	864.2	868.2	863.9	865.8	863.0
5°	860.5	849.7	842.0	830.9	821.3	812.5	806.0	804.9	801.7	800.2	795.7
7.5°	827.2	813.7	800.5	786.0	773.7	761.2	753.2	746.6	742.3	736.5	732.6
10°	807.5	789.5	774.2	756.5	741.1	727.7	717.0	711.7	706.6	699.3	696.7
12.5°	783.3	764.7	745.9	727.0	712.4	697.3	688.1	680.0	676.6	668.3	667.5
15°	754.2	726.2	707.8	688.6	668.2	656.0	648.3	639.5	635.7	630.0	625.7
17.5°	719.5	694.5	671.5	651.7	634.2	623.9	614.3	608.2	601.7	597.9	591.0
20°	694.4	670.6	647.5	626.4	613.0	601.2	593.5	587.7	580.8	578.9	572.0
22.5°	673.2	646.9	624.8	607.1	592.5	579.1	570.8	566.8	562.1	556.1	554.8
25°	638.7	611.5	592.7	575.0	562.0	549.8	544.0	539.0	534.4	530.2	528.7
27.5°	608.9	584.6	562.3	546.3	535.0	523.8	518.8	512.7	509.3	505.9	501.8
30°	588.1	563.2	543.6	528.3	515.9	506.0	500.6	496.4	493.3	490.3	488.0
32.5°	566.6	543.5	524.5	509.6	497.3	489.8	484.9	482.0	478.6	474.9	472.0
35°	538.3	512.9	494.5	481.4	471.8	466.1	460.7	458.1	454.2	454.2	451.1
37.5°	506.2	484.3	468.1	456.2	447.6	442.4	436.7	434.8	432.3	430.7	429.7
40°	487.2	466.9	451.5	439.6	430.4	426.2	421.6	418.5	417.0	415.1	414.3
42.5°	467.6	448.2	433.4	422.4	414.4	410.8	406.6	404.5	401.3	398.8	398.4
45°	437.7	418.9	405.5	396.7	389.8	385.6	382.8	378.3	376.7	373.7	373.2
47.5°	409.4	391.3	378.2	370.9	364.9	361.4	357.2	352.6	350.8	349.3	349.2
50°	388.2	371.7	359.4	352.5	346.8	341.8	337.6	334.6	333.4	333.4	334.2
52.5°	366.8	352.7	342.2	333.9	328.4	323.1	319.2	317.3	315.6	317.4	318.8
55°	335.3	321.1	313.5	305.4	300.0	293.9	292.0	291.1	290.0	293.1	294.6
57.5°	301.9	292.1	283.1	275.1	270.2	266.7	264.1	263.7	265.8	267.2	272.3
60°	280.8	269.3	261.3	255.1	249.3	247.0	246.3	245.5	247.0	251.3	257.8
62.5°	257.5	248.1	239.4	234.9	230.7	226.8	226.6	227.1	230.1	235.0	241.6
65°	223.3	215.2	209.4	204.1	200.7	198.3	199.1	200.7	204.1	210.7	217.9
67.5°	188.5	183.0	177.8	173.5	170.2	170.2	171.0	173.3	177.3	184.8	191.5
70°	166.1	160.0	155.7	153.8	151.2	149.7	151.9	155.7	159.2	166.1	171.9
72.5°	143.7	138.5	135.2	133.9	132.7	131.5	132.3	136.4	141.1	148.0	154.7
75°	110.5	108.6	106.2	104.7	103.6	104.3	105.1	109.0	112.8	120.1	127.7
77.5°	80.7	78.7	77.3	76.9	76.2	76.6	78.8	81.6	85.4	90.7	96.5
80°	61.0	60.2	59.5	59.1	59.1	59.5	62.5	64.4	67.9	72.9	77.5
82.5°	44.4	43.9	43.8	43.7	44.0	44.1	45.9	48.5	51.3	55.1	59.1
85°	23.4	22.6	23.8	24.1	23.4	24.5	25.3	26.9	28.0	29.9	31.8
87.5°	8.9	9.9	9.7	10.3	10.5	11.4	11.3	12.6	13.4	14.2	14.2
90°	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2	15.0	15.8	17.4
92.5°	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0	101.6	76.4	64.7
95°	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7	447.7	350.6	284.3
97.5°	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6	761.3	666.7	574.5
100°	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2	932.5	851.2	769.1
102.5°	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5	1037.4	998.4	942.8
105°	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6	1096.8	1131.6	1122.9
107.5°	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5	1043.9	1133.1	1174.3
110°	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8	983.8	1095.2	1162.3



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0	924.4	1037.0	1116.2
115°	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0	839.4	947.6	1033.6
117.5°	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0	780.4	873.6	952.6
120°	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2	747.0	833.8	903.3
122.5°	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2	723.0	800.3	865.5
125°	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4	690.9	759.6	816.5
127.5°	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1	660.2	724.4	777.6
130°	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3	638.8	700.3	751.7
132.5°	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5	618.5	674.5	723.9
135°	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0	587.4	638.0	683.0
137.5°	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6	559.7	601.7	639.9
140°	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1	543.2	579.6	612.7
142.5°	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0	529.4	560.6	589.4
145°	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2	511.7	536.1	557.4
147.5°	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1	497.0	515.7	531.9
150°	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4	488.8	503.7	518.0
152.5°	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0	480.6	494.3	505.3
155°	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7	468.3	479.3	488.0
157.5°	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2	456.6	465.0	471.9
160°	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8	447.7	455.7	461.1
162.5°	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8	440.1	446.8	451.6
165°	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2	428.8	433.5	437.5
167.5°	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0	417.7	421.3	424.1
170°	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0	411.4	413.7	415.4
172.5°	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3	405.7	407.5	408.4
175°	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2	397.2	398.8	398.8
177.5°	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9	393.5	393.5	393.5
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	861.1	863.3	861.5	863.9	861.5	863.3	861.1	863.0	865.8	863.9	868.2
5°	793.8	790.2	792.5	791.0	792.5	790.2	793.8	795.7	800.2	801.7	804.9
7.5°	731.4	728.1	724.4	722.6	724.4	728.1	731.4	732.6	736.5	742.3	746.6
10°	692.5	688.2	687.8	685.2	687.8	688.2	692.5	696.7	699.3	706.6	711.7
12.5°	663.9	659.9	655.6	654.5	655.6	659.9	663.9	667.5	668.3	676.6	680.0
15°	623.4	620.4	617.6	620.0	617.6	620.4	623.4	625.7	630.0	635.7	639.5
17.5°	589.7	587.1	586.7	583.9	586.7	587.1	589.7	591.0	597.9	601.7	608.2
20°	568.6	566.6	567.3	562.4	567.3	566.6	568.6	572.0	578.9	580.8	587.7
22.5°	551.7	547.9	547.4	546.4	547.4	547.9	551.7	554.8	556.1	562.1	566.8
25°	525.2	523.3	521.4	523.3	521.4	523.3	525.2	528.7	530.2	534.4	539.0
27.5°	502.1	499.8	499.3	499.5	499.3	499.8	502.1	501.8	505.9	509.3	512.7
30°	488.0	484.1	484.5	484.1	484.5	484.1	488.0	488.0	490.3	493.3	496.4
32.5°	472.6	470.0	469.5	468.8	469.5	470.0	472.6	472.0	474.9	478.6	482.0
35°	450.0	450.0	448.1	448.1	448.1	450.0	450.0	451.1	454.2	454.2	458.1
37.5°	428.7	428.4	427.2	427.4	427.2	428.4	428.7	429.7	430.7	432.3	434.8
40°	412.7	412.4	411.2	408.9	411.2	412.4	412.7	414.3	415.1	417.0	418.5
42.5°	397.5	396.2	395.6	394.9	395.6	396.2	397.5	398.4	398.8	401.3	404.5
45°	373.2	373.2	372.5	372.1	372.5	373.2	373.2	373.2	373.7	376.7	378.3
47.5°	349.8	350.5	351.9	351.7	351.9	350.5	349.8	349.2	349.3	350.8	352.6
50°	335.7	336.1	337.2	337.6	337.2	336.1	335.7	334.2	333.4	333.4	334.6
52.5°	320.0	322.2	323.7	323.5	323.7	322.2	320.0	318.8	317.4	315.6	317.3
55°	298.1	300.7	303.5	303.9	303.5	300.7	298.1	294.6	293.1	290.0	291.1
57.5°	276.4	280.1	283.0	283.9	283.0	280.1	276.4	272.3	267.2	265.8	263.7
60°	261.7	266.6	270.0	271.7	270.0	266.6	261.7	257.8	251.3	247.0	245.5
62.5°	247.5	253.1	256.6	256.9	256.6	253.1	247.5	241.6	235.0	230.1	227.1
65°	224.4	230.1	233.3	235.5	233.3	230.1	224.4	217.9	210.7	204.1	200.7
67.5°	199.5	205.3	208.7	210.6	208.7	205.3	199.5	191.5	184.8	177.3	173.3
70°	181.5	187.2	191.8	193.4	191.8	187.2	181.5	171.9	166.1	159.2	155.7
72.5°	163.7	168.7	172.5	174.3	172.5	168.7	163.7	154.7	148.0	141.1	136.4
75°	132.7	139.7	143.1	145.0	143.1	139.7	132.7	127.7	120.1	112.8	109.0
77.5°	102.4	108.7	110.7	111.7	110.7	108.7	102.4	96.5	90.7	85.4	81.6
80°	82.1	85.9	88.7	89.0	88.7	85.9	82.1	77.5	72.9	67.9	64.4
82.5°	63.1	66.2	67.2	68.2	67.2	66.2	63.1	59.1	55.1	51.3	48.5
85°	34.5	36.1	36.5	36.1	36.5	36.1	34.5	31.8	29.9	28.0	26.9
87.5°	14.8	14.5	14.6	15.2	14.6	14.5	14.8	14.2	14.2	13.4	12.6
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2
92.5°	54.6	52.7	51.6	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0
95°	228.2	204.5	198.2	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7
97.5°	525.7	481.5	458.6	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6
100°	714.6	657.7	628.5	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2
102.5°	884.5	844.0	812.3	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5
105°	1097.5	1071.5	1055.7	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6
107.5°	1187.1	1186.9	1181.7	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5
110°	1197.8	1212.8	1218.4	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1168.1	1193.9	1207.6	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0
115°	1095.2	1133.1	1155.2	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0
117.5°	1014.2	1053.3	1075.3	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0
120°	961.7	999.7	1021.0	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2
122.5°	917.6	952.3	973.6	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2
125°	860.7	893.0	910.4	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4
127.5°	817.7	846.3	862.7	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1
130°	791.2	817.3	833.0	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3
132.5°	763.4	789.4	804.0	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5
135°	717.7	743.8	758.0	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0
137.5°	671.1	694.7	707.8	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6
140°	642.0	662.5	674.3	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1
142.5°	614.2	631.6	642.8	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0
145°	576.4	589.9	598.5	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2
147.5°	546.8	557.6	562.7	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1
150°	529.9	539.3	542.5	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4
152.5°	515.3	522.9	526.0	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0
155°	495.8	501.4	503.7	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7
157.5°	478.1	482.6	484.8	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2
160°	466.7	470.6	472.2	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8
162.5°	456.0	459.2	459.6	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8
165°	440.6	442.2	442.2	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2
167.5°	425.8	427.2	426.6	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0
170°	416.9	417.7	417.7	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0
172.5°	408.7	410.1	408.9	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3
175°	398.8	399.5	398.0	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2
177.5°	392.9	393.5	391.6	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	864.2	867.9	872.5	875.9	882.0	884.7	888.2	890.9	895.9	900.4	905.9
5°	806.0	812.5	821.3	830.9	842.0	849.7	860.5	867.0	880.0	891.9	903.4
7.5°	753.2	761.2	773.7	786.0	800.5	813.7	827.2	842.0	858.7	878.4	894.6
10°	717.0	727.7	741.1	756.5	774.2	789.5	807.5	823.6	843.9	867.0	888.5
12.5°	688.1	697.3	712.4	727.0	745.9	764.7	783.3	804.7	828.3	853.8	880.8
15°	648.3	656.0	668.2	688.6	707.8	726.2	754.2	774.2	804.1	832.4	865.1
17.5°	614.3	623.9	634.2	651.7	671.5	694.5	719.5	744.6	773.4	809.4	846.2
20°	593.5	601.2	613.0	626.4	647.5	670.6	694.4	719.6	755.0	792.1	831.7
22.5°	570.8	579.1	592.5	607.1	624.8	646.9	673.2	700.9	737.8	774.4	817.3
25°	544.0	549.8	562.0	575.0	592.7	611.5	638.7	669.4	705.9	747.7	791.4
27.5°	518.8	523.8	535.0	546.3	562.3	584.6	608.9	640.0	674.3	716.7	765.2
30°	500.6	506.0	515.9	528.3	543.6	563.2	588.1	617.2	654.1	695.5	746.2
32.5°	484.9	489.8	497.3	509.6	524.5	543.5	566.6	596.4	633.2	675.3	725.0
35°	460.7	466.1	471.8	481.4	494.5	512.9	538.3	566.2	601.5	642.2	687.8
37.5°	436.7	442.4	447.6	456.2	468.1	484.3	506.2	535.4	567.3	606.5	650.4
40°	421.6	426.2	430.4	439.6	451.5	466.9	487.2	513.3	547.0	583.5	620.0
42.5°	406.6	410.8	414.4	422.4	433.4	448.2	467.6	493.0	524.3	558.4	590.5
45°	382.8	385.6	389.8	396.7	405.5	418.9	437.7	460.4	486.9	519.1	543.2
47.5°	357.2	361.4	364.9	370.9	378.2	391.3	409.4	428.7	452.7	476.7	493.6
50°	337.6	341.8	346.8	352.5	359.4	371.7	388.2	407.8	428.1	446.6	461.1
52.5°	319.2	323.1	328.4	333.9	342.2	352.7	366.8	384.2	404.1	417.4	429.5
55°	292.0	293.9	300.0	305.4	313.5	321.1	335.3	350.6	362.9	372.8	382.8
57.5°	264.1	266.7	270.2	275.1	283.1	292.1	301.9	315.6	322.8	327.9	335.7
60°	246.3	247.0	249.3	255.1	261.3	269.3	280.8	290.4	295.8	300.0	306.5
62.5°	226.6	226.8	230.7	234.9	239.4	248.1	257.5	265.2	269.7	271.8	278.0
65°	199.1	198.3	200.7	204.1	209.4	215.2	223.3	230.1	229.7	232.1	235.9
67.5°	171.0	170.2	170.2	173.5	177.8	183.0	188.5	192.5	192.6	195.6	197.5
70°	151.9	149.7	151.2	153.8	155.7	160.0	166.1	167.6	168.0	169.6	171.5
72.5°	132.3	131.5	132.7	133.9	135.2	138.5	143.7	144.6	144.7	145.6	148.8
75°	105.1	104.3	103.6	104.7	106.2	108.6	110.5	112.0	111.6	112.0	114.3
77.5°	78.8	76.6	76.2	76.9	77.3	78.7	80.7	80.5	80.9	80.8	83.4
80°	62.5	59.5	59.1	59.1	59.5	60.2	61.0	61.8	60.6	61.8	62.5
82.5°	45.9	44.1	44.0	43.7	43.8	43.9	44.4	44.8	44.6	45.1	45.6
85°	25.3	24.5	23.4	24.1	23.8	22.6	23.4	22.2	21.9	22.2	22.6
87.5°	11.3	11.4	10.5	10.3	9.7	9.9	8.9	8.3	7.7	7.7	8.5
90°	13.4	12.6	11.0	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8
92.5°	206.1	254.6	258.6	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6
95°	684.6	699.6	570.9	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1
97.5°	866.2	747.1	509.8	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2
100°	910.4	713.1	454.8	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2
102.5°	883.9	653.0	413.1	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6
105°	799.1	572.5	372.7	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3
107.5°	712.6	517.1	355.7	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5
110°	663.3	491.1	350.6	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	626.6	475.9	350.6	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5
115°	586.6	459.6	352.9	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5
117.5°	562.8	451.5	358.2	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4
120°	549.6	447.7	363.2	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1
122.5°	538.2	444.5	367.6	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4
125°	522.7	440.6	375.1	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1
127.5°	508.5	438.7	383.4	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2
130°	499.1	437.5	388.5	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4
132.5°	491.5	437.5	394.2	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7
135°	482.4	437.5	401.9	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0
137.5°	474.4	438.4	409.0	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0
140°	470.6	439.0	412.1	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5
142.5°	467.5	439.7	414.0	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3
145°	462.7	439.0	416.2	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6
147.5°	457.8	437.0	416.9	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5
150°	454.0	435.0	416.9	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8
152.5°	449.6	432.5	416.3	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5
155°	442.2	428.0	414.5	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3
157.5°	435.3	423.2	412.5	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7
160°	429.6	420.1	410.6	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6
162.5°	424.4	416.3	408.7	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3
165°	416.9	410.6	405.9	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9
167.5°	409.5	405.1	401.4	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5
170°	405.1	401.9	399.5	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4
172.5°	400.6	398.1	397.0	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9
175°	394.8	394.0	394.0	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8
177.5°	392.2	391.6	391.6	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	908.8	913.0	915.7	921.0	925.3	927.8	929.9	931.7	933.9	935.7	941.0
5°	914.5	924.5	933.0	946.0	958.0	967.1	977.0	985.9	993.2	1003.6	1011.6
7.5°	912.0	929.8	948.4	968.5	989.2	1008.4	1025.9	1042.5	1057.4	1075.5	1091.4
10°	909.6	933.7	957.6	984.7	1012.8	1036.5	1058.8	1081.5	1097.9	1121.0	1140.5
12.5°	907.8	936.2	964.9	997.6	1028.4	1062.0	1091.7	1108.1	1133.3	1151.7	1174.9
15°	900.0	937.6	977.0	1013.9	1057.6	1088.7	1114.8	1147.0	1170.4	1193.9	1219.1
17.5°	886.1	928.7	972.9	1021.2	1063.1	1096.5	1130.0	1161.1	1189.1	1220.4	1252.0
20°	879.7	922.2	972.9	1022.4	1063.4	1098.3	1132.9	1167.0	1197.7	1238.0	1274.3
22.5°	866.2	917.7	964.3	1012.5	1054.8	1092.8	1132.0	1170.6	1211.4	1257.0	1302.6
25°	842.0	894.2	943.7	991.3	1033.9	1081.5	1123.3	1175.1	1227.2	1287.5	1344.2
27.5°	817.1	867.0	912.3	958.3	1007.9	1061.8	1116.0	1174.8	1243.1	1319.1	1399.3
30°	796.8	843.9	888.1	935.2	987.0	1047.6	1107.1	1177.0	1256.0	1341.5	1436.6
32.5°	773.2	816.7	859.6	909.5	965.9	1029.9	1099.1	1175.7	1270.7	1368.0	1465.8
35°	732.8	769.2	813.2	866.6	930.3	1003.6	1083.8	1174.3	1283.2	1394.8	1477.3
37.5°	684.8	718.7	765.2	823.6	890.4	969.1	1064.2	1171.5	1287.3	1376.2	1402.9
40°	652.6	684.0	732.4	792.9	861.2	944.5	1048.8	1162.4	1274.3	1331.2	1309.3
42.5°	618.1	651.2	698.3	758.3	831.7	922.4	1029.5	1143.1	1237.0	1258.4	1182.9
45°	563.9	598.0	644.5	705.1	784.2	882.3	994.0	1097.1	1151.2	1112.5	995.5
47.5°	513.5	545.5	588.5	651.1	732.7	834.2	941.7	1024.0	1028.3	935.8	810.9
50°	479.2	508.7	552.0	614.6	695.5	798.3	895.3	960.2	931.1	826.4	706.3
52.5°	445.4	474.3	517.1	579.0	659.0	753.2	843.5	889.0	834.0	726.6	624.0
55°	396.7	422.0	463.8	521.0	596.9	684.4	761.1	776.8	705.5	599.6	516.3
57.5°	349.1	372.7	410.8	463.4	532.8	610.4	670.3	667.0	591.6	500.7	434.6
60°	316.9	339.9	373.7	425.1	488.4	555.1	606.5	594.2	519.5	441.2	385.6
62.5°	288.0	308.6	340.5	385.5	443.2	505.0	547.2	529.2	455.9	387.5	343.5
65°	245.5	262.8	290.0	328.4	376.4	427.4	460.0	436.6	374.1	320.7	285.4
67.5°	204.9	218.7	241.6	272.3	313.2	354.1	374.0	350.4	300.3	261.5	235.3
70°	179.2	191.5	209.0	236.3	272.0	306.5	321.4	300.3	257.4	224.0	205.2
72.5°	153.4	163.5	179.0	203.5	232.1	262.1	275.1	255.0	219.6	191.5	173.9
75°	118.6	125.4	136.2	153.1	175.7	199.4	206.8	189.1	166.5	145.4	133.9
77.5°	84.8	90.7	98.9	109.5	125.5	140.7	147.0	136.8	119.3	105.9	96.5
80°	65.2	68.3	75.2	84.0	96.6	106.2	110.5	103.9	91.7	81.7	74.4
82.5°	46.5	49.6	53.7	61.0	69.1	75.5	80.1	75.7	66.9	59.0	54.7
85°	22.6	24.5	26.9	29.9	36.1	39.9	39.5	36.9	33.3	30.3	28.0
87.5°	8.3	8.9	10.2	12.0	13.2	14.6	15.6	15.1	14.2	13.4	12.6
90°	1.6	3.1	4.7	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2
92.5°	11.7	18.3	28.1	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0
95°	26.9	33.1	41.8	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7
97.5°	44.2	48.7	57.4	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6
100°	56.9	60.0	68.7	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2
102.5°	69.5	72.0	81.3	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5
105°	89.3	93.2	101.1	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6
107.5°	111.0	114.8	121.3	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5
110°	125.5	128.7	135.8	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.1	142.6	149.7	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0
115°	161.1	163.5	170.6	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0
117.5°	180.9	183.4	190.5	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0
120°	193.5	196.6	203.7	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2
122.5°	206.1	208.6	215.7	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2
125°	222.7	226.6	233.7	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4
127.5°	236.6	241.7	250.6	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1
130°	244.8	251.1	261.4	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3
132.5°	251.8	259.3	270.8	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5
135°	262.2	271.7	284.3	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0
137.5°	274.3	283.2	295.8	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6
140°	281.9	291.3	304.0	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1
142.5°	290.1	298.9	311.5	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0
145°	303.2	311.1	322.1	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2
147.5°	316.5	323.3	333.6	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1
150°	325.3	330.8	341.1	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4
152.5°	333.6	338.4	347.4	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0
155°	344.3	349.0	356.9	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7
157.5°	354.6	358.3	365.1	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2
160°	360.8	364.1	369.5	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8
162.5°	366.6	369.7	374.6	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8
165°	374.3	376.7	380.6	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2
167.5°	380.7	382.1	384.4	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0
170°	384.6	385.4	386.9	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0
172.5°	386.5	387.2	388.8	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3
175°	389.3	390.1	390.8	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2
177.5°	391.0	391.0	391.6	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	945.2	947.7	952.9	951.1	953.5	954.7	956.0
5°	1021.6	1033.9	1039.3	1038.4	1046.5	1044.6	1042.7
7.5°	1107.8	1120.7	1127.9	1136.9	1142.2	1142.5	1147.0
10°	1156.6	1173.5	1180.4	1190.0	1196.2	1199.6	1199.2
12.5°	1194.1	1207.3	1222.7	1227.5	1235.8	1240.1	1238.5
15°	1239.1	1260.2	1276.3	1284.3	1294.7	1297.8	1302.0
17.5°	1279.3	1307.6	1326.5	1351.4	1360.9	1366.7	1363.2
20°	1309.7	1346.9	1365.7	1395.6	1412.1	1421.0	1417.9
22.5°	1345.6	1385.8	1420.7	1446.5	1471.7	1483.6	1486.0
25°	1407.1	1462.4	1513.4	1547.5	1578.6	1585.9	1602.0
27.5°	1475.9	1541.1	1595.6	1631.4	1653.1	1661.2	1666.3
30°	1519.1	1584.0	1625.1	1648.0	1655.0	1654.2	1653.5
32.5°	1540.3	1580.9	1588.8	1582.4	1566.6	1553.2	1539.2
35°	1510.4	1480.1	1434.7	1376.4	1333.5	1290.1	1285.9
37.5°	1358.4	1261.4	1186.1	1102.0	1053.4	1023.4	1002.6
40°	1215.3	1105.2	1013.9	942.9	893.4	873.9	854.7
42.5°	1060.1	954.8	873.9	814.7	777.5	755.8	740.5
45°	861.2	768.4	705.1	662.2	632.6	615.7	606.1
47.5°	705.7	637.0	583.3	552.3	531.9	518.8	518.8
50°	622.3	556.6	521.0	496.4	478.8	468.4	470.3
52.5°	548.3	499.3	468.8	448.2	435.2	428.8	428.6
55°	458.5	423.1	403.2	388.2	379.4	372.1	373.7
57.5°	392.1	362.3	349.0	336.6	330.4	327.5	323.4
60°	351.0	328.0	316.5	306.5	300.3	298.1	293.9
62.5°	314.5	296.4	285.2	277.0	271.6	270.7	267.4
65°	264.3	250.5	240.5	236.7	231.0	229.4	229.4
67.5°	217.9	208.0	200.3	196.7	194.2	194.6	192.7
70°	188.7	180.7	175.7	171.9	170.0	170.4	168.7
72.5°	165.1	156.1	151.8	149.5	146.9	147.9	147.3
75°	125.0	120.5	118.2	115.8	114.3	113.5	112.8
77.5°	91.8	87.8	86.0	84.7	84.9	83.1	84.5
80°	71.0	67.6	66.3	64.4	64.0	64.0	63.7
82.5°	51.9	50.0	49.2	47.6	46.9	47.5	46.5
85°	26.9	25.3	24.9	24.9	24.1	23.4	25.3
87.5°	12.8	11.7	12.0	11.7	11.7	11.6	11.0
90°	15.0	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.6	76.4	64.7	54.6	52.7	51.6	50.4
95°	447.7	350.6	284.3	228.2	204.5	198.2	185.5
97.5°	761.3	666.7	574.5	525.7	481.5	458.6	448.5
100°	932.5	851.2	769.1	714.6	657.7	628.5	615.9
102.5°	1037.4	998.4	942.8	884.5	844.0	812.3	802.8
105°	1096.8	1131.6	1122.9	1097.5	1071.5	1055.7	1046.2
107.5°	1043.9	1133.1	1174.3	1187.1	1186.9	1181.7	1175.4
110°	983.8	1095.2	1162.3	1197.8	1212.8	1218.4	1218.4



TEST NUMBER: P333180-840

CATALOG NUMBER: S125DIP-S610D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	924.4	1037.0	1116.2	1168.1	1193.9	1207.6	1213.4
115°	839.4	947.6	1033.6	1095.2	1133.1	1155.2	1165.5
117.5°	780.4	873.6	952.6	1014.2	1053.3	1075.3	1081.6
120°	747.0	833.8	903.3	961.7	999.7	1021.0	1027.2
122.5°	723.0	800.3	865.5	917.6	952.3	973.6	979.3
125°	690.9	759.6	816.5	860.7	893.0	910.4	918.3
127.5°	660.2	724.4	777.6	817.7	846.3	862.7	866.2
130°	638.8	700.3	751.7	791.2	817.3	833.0	837.8
132.5°	618.5	674.5	723.9	763.4	789.4	804.0	809.3
135°	587.4	638.0	683.0	717.7	743.8	758.0	762.8
137.5°	559.7	601.7	639.9	671.1	694.7	707.8	713.1
140°	543.2	579.6	612.7	642.0	662.5	674.3	678.2
142.5°	529.4	560.6	589.4	614.2	631.6	642.8	646.0
145°	511.7	536.1	557.4	576.4	589.9	598.5	601.7
147.5°	497.0	515.7	531.9	546.8	557.6	562.7	564.1
150°	488.8	503.7	518.0	529.9	539.3	542.5	543.2
152.5°	480.6	494.3	505.3	515.3	522.9	526.0	526.8
155°	468.3	479.3	488.0	495.8	501.4	503.7	504.5
157.5°	456.6	465.0	471.9	478.1	482.6	484.8	484.6
160°	447.7	455.7	461.1	466.7	470.6	472.2	471.4
162.5°	440.1	446.8	451.6	456.0	459.2	459.6	459.4
165°	428.8	433.5	437.5	440.6	442.2	442.2	442.2
167.5°	417.7	421.3	424.1	425.8	427.2	426.6	426.4
170°	411.4	413.7	415.4	416.9	417.7	417.7	416.9
172.5°	405.7	407.5	408.4	408.7	410.1	408.9	408.1
175°	397.2	398.8	398.8	398.8	399.5	398.0	397.2
177.5°	393.5	393.5	393.5	392.9	393.5	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6

(END OF REPORT)