

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333257-930

Luminaire Tested: **S125DIP-S1090D365U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333257-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D365U930-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4654.2 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333257-930  
CATALOG NUMBER: S125DIP-S1090D365U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333257-930

CATALOG NUMBER: S125DIP-S1090D365U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	62	63	60	58	55
3	86	76	69	62	82	73	66	60	67	61	57	61	57	53	56	52	49	46
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	42	40
5	73	60	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37	34
6	67	54	46	40	64	52	44	39	48	42	37	45	39	35	41	36	33	30
7	62	49	41	35	59	47	40	34	44	37	32	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	30	40	34	29	37	32	27	35	30	26	24
9	54	41	33	28	51	40	32	27	37	31	26	34	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	21	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8985	8985	8985
5°	9005	8919	8976
10°	8950	8857	8907
15°	8852	8750	8787
20°	8715	8601	8616
25°	8565	8424	8416
30°	8380	8232	8192
35°	8183	8027	7914
40°	7981	7804	7692
45°	7761	7600	7448
50°	7519	7354	7133
55°	7287	7076	6877
60°	7009	6795	6554
65°	6677	6460	6240
70°	6360	6069	5861
75°	5794	5602	5410
80°	5159	5077	4950
85°	4483	4565	4320



TEST NUMBER: P333257-930

CATALOG NUMBER: S125DIP-S1090D365U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.2	2.8
10°-20°	370.5	8.0
20°-30°	547.1	11.8
30°-40°	638.4	13.7
40°-50°	641.2	13.8
50°-60°	562.8	12.1
60°-70°	419.4	9.0
70°-80°	239.8	5.2
80°-90°	70.6	1.5
90°-100°	24.8	0.5
100°-110°	73.2	1.6
110°-120°	124.0	2.7
120°-130°	163.2	3.5
130°-140°	182.9	3.9
140°-150°	179.3	3.9
150°-160°	150.6	3.2
160°-170°	100.1	2.2
170°-180°	35.0	0.8
0°-30°	1048.8	22.5
0°-40°	1687.2	36.3
0°-60°	2891.2	62.1
0°-90°	3620.9	77.8
90°-120°	222.1	4.8
90°-150°	747.5	16.1
90°-180°	1033.0	22.2
0°-180°	4654.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1389	1386	1376	1385	1385	132
15°	1324	1320	1309	1314	1314	373
25°	1202	1196	1182	1184	1181	553
35°	1038	1033	1018	1012	1004	649
45°	850	845	832	819	816	655
55°	647	643	628	619	611	578
65°	437	434	423	413	408	433
75°	232	230	224	221	217	248
85°	60	62	62	60	58	68
90°	0	3	5	6	7	4
95°	19	19	22	24	25	20
105°	66	67	69	71	72	70
115°	124	125	126	126	125	123
125°	181	183	183	183	182	162
135°	236	237	238	238	237	182
145°	286	287	288	288	287	178
155°	327	327	327	328	327	150
165°	355	355	355	356	354	100
175°	369	368	368	370	368	35
180°	370	370	370	370	370	



TEST NUMBER: P333257-930

CATALOG NUMBER: S125DIP-S1090D365U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1394.7	1394.2	1393.5	1392.9	1392.4	1391.1	1389.1	1387.2	1385.2	1383.2	1385.2
5°	1389.0	1388.5	1388.0	1387.6	1387.1	1385.6	1383.2	1380.7	1378.3	1375.8	1378.0
7.5°	1376.2	1375.7	1375.2	1374.8	1374.3	1372.6	1369.9	1367.3	1364.6	1361.9	1364.1
10°	1364.8	1364.3	1363.8	1363.3	1362.9	1361.2	1358.5	1355.8	1353.2	1350.5	1352.4
12.5°	1350.7	1349.8	1348.9	1348.0	1347.2	1345.5	1343.0	1340.5	1338.0	1335.5	1337.1
15°	1324.0	1323.3	1322.6	1321.8	1321.1	1319.4	1316.7	1314.0	1311.3	1308.6	1309.9
17.5°	1293.5	1292.4	1291.3	1290.2	1289.2	1287.2	1284.4	1281.7	1278.9	1276.0	1277.6
20°	1268.0	1267.5	1267.0	1266.5	1266.0	1264.1	1260.9	1257.8	1254.6	1251.4	1253.1
22.5°	1242.4	1241.5	1240.6	1239.7	1238.8	1236.9	1234.0	1230.9	1228.0	1225.0	1226.1
25°	1201.9	1200.7	1199.5	1198.2	1197.0	1194.8	1191.6	1188.5	1185.3	1182.1	1182.6
27.5°	1154.5	1153.8	1153.1	1152.3	1151.6	1149.7	1146.3	1143.0	1139.8	1136.5	1136.6
30°	1123.7	1123.0	1122.3	1121.5	1120.8	1118.6	1114.9	1111.3	1107.6	1103.9	1103.4
32.5°	1090.3	1089.2	1088.0	1086.9	1085.8	1083.6	1080.3	1077.0	1073.7	1070.5	1069.6
35°	1037.9	1036.9	1035.9	1034.9	1034.0	1031.8	1028.3	1024.9	1021.5	1018.1	1016.8
37.5°	983.5	982.3	981.0	979.8	978.6	976.4	973.1	970.0	966.7	963.5	961.6
40°	946.6	945.3	944.1	942.9	941.7	939.3	935.9	932.5	929.0	925.6	923.4
42.5°	906.9	905.9	904.9	903.8	902.8	900.6	897.2	893.7	890.3	886.9	884.8
45°	849.7	848.7	847.7	846.8	845.8	843.8	840.9	838.0	835.0	832.1	829.2
47.5°	788.1	788.1	788.1	788.2	788.2	786.5	783.0	779.4	775.9	772.4	769.4
50°	748.4	747.7	747.0	746.2	745.5	743.6	740.7	737.8	734.8	731.9	728.7
52.5°	707.9	707.4	706.9	706.3	705.8	703.9	700.8	697.7	694.6	691.4	688.6
55°	647.2	646.5	645.7	645.0	644.2	642.1	638.7	635.3	631.9	628.4	626.2
57.5°	583.1	582.7	582.4	582.0	581.6	579.9	577.0	574.1	571.3	568.3	565.5
60°	542.6	541.6	540.6	539.6	538.7	536.9	534.2	531.5	528.8	526.1	523.7
62.5°	500.3	499.5	498.8	498.0	497.3	495.7	493.3	491.1	488.8	486.5	483.8
65°	436.9	436.4	435.9	435.5	435.0	433.4	430.7	428.0	425.3	422.7	420.4
67.5°	375.5	374.5	373.5	372.4	371.5	369.9	367.9	365.9	363.9	361.9	360.0
70°	336.8	335.6	334.4	333.1	331.9	330.2	328.0	325.8	323.6	321.4	319.9
72.5°	294.6	293.7	292.9	292.0	291.2	290.1	288.7	287.2	285.8	284.4	282.7
75°	232.2	231.7	231.2	230.7	230.2	229.4	228.2	227.0	225.8	224.5	223.8
77.5°	174.8	174.6	174.4	174.2	174.0	173.6	172.8	172.2	171.5	170.8	170.4
80°	138.7	138.7	138.7	138.7	138.7	138.4	137.9	137.5	137.0	136.5	136.2
82.5°	107.0	106.6	106.2	105.8	105.4	105.2	105.1	105.0	104.8	104.8	104.4
85°	60.5	60.7	61.0	61.2	61.5	61.6	61.6	61.6	61.6	61.6	61.4
87.5°	23.8	24.0	24.1	24.1	24.2	24.2	24.1	24.1	23.9	23.8	23.9
90°	0.3	0.8	1.3	1.8	2.4	2.9	3.3	3.8	4.2	4.6	4.9
92.5°	7.0	7.3	7.7	8.1	8.4	8.9	9.4	9.9	10.5	11.1	11.5
95°	18.8	18.8	19.0	19.1	19.2	19.6	20.3	20.9	21.5	22.2	22.7
97.5°	31.1	31.1	31.2	31.3	31.3	31.8	32.7	33.6	34.4	35.3	35.8
100°	40.4	40.4	40.4	40.4	40.4	40.8	41.6	42.4	43.3	44.1	44.7
102.5°	50.2	50.5	50.8	51.0	51.3	51.6	52.0	52.4	52.9	53.3	54.0
105°	65.7	66.0	66.4	66.7	67.0	67.3	67.8	68.1	68.5	68.9	69.2
107.5°	82.8	83.1	83.4	83.7	84.1	84.4	84.6	85.0	85.2	85.5	85.7
110°	94.5	94.8	95.1	95.5	95.8	96.0	96.2	96.4	96.6	96.9	97.0



TEST NUMBER: P333257-930

CATALOG NUMBER: S125DIP-S1090D365U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	106.5	106.6	106.8	107.0	107.1	107.4	107.6	107.9	108.1	108.4	108.4
115°	124.2	124.4	124.7	125.0	125.2	125.4	125.6	125.6	125.8	126.0	125.9
117.5°	141.9	142.0	142.2	142.3	142.4	142.5	142.7	142.8	142.8	143.0	143.0
120°	153.0	153.4	153.7	154.0	154.3	154.5	154.6	154.6	154.7	154.7	154.7
122.5°	165.0	165.1	165.3	165.3	165.4	165.6	165.8	165.9	166.1	166.2	166.2
125°	181.2	181.6	182.1	182.4	182.8	183.0	183.1	183.1	183.2	183.3	183.1
127.5°	198.5	198.8	199.0	199.2	199.4	199.6	199.7	199.7	199.8	199.8	199.8
130°	208.9	209.2	209.5	209.9	210.2	210.4	210.5	210.7	210.8	210.9	210.8
132.5°	219.3	219.8	220.4	220.9	221.4	221.7	221.6	221.6	221.6	221.5	221.4
135°	235.7	236.1	236.5	236.8	237.3	237.5	237.6	237.6	237.7	237.7	237.7
137.5°	251.2	251.5	251.9	252.3	252.7	252.9	253.1	253.2	253.3	253.5	253.6
140°	261.1	261.4	261.7	262.0	262.4	262.6	262.8	263.0	263.2	263.3	263.5
142.5°	271.0	271.3	271.5	271.8	272.1	272.3	272.6	272.8	273.0	273.3	273.4
145°	285.6	285.8	286.1	286.3	286.6	286.8	287.0	287.2	287.4	287.6	287.6
147.5°	299.1	299.2	299.3	299.5	299.6	299.8	299.9	300.1	300.2	300.4	300.5
150°	308.0	308.0	307.9	307.9	307.8	307.9	308.1	308.4	308.7	308.9	308.9
152.5°	315.4	315.5	315.6	315.7	315.8	315.8	316.0	316.1	316.2	316.3	316.4
155°	326.8	326.8	326.8	326.8	326.8	326.8	326.9	326.9	327.0	327.1	327.3
157.5°	336.9	336.8	336.6	336.5	336.4	336.3	336.4	336.5	336.5	336.6	336.8
160°	342.9	342.8	342.5	342.3	342.2	342.1	342.2	342.2	342.3	342.3	342.6
162.5°	348.2	348.1	348.0	347.8	347.6	347.6	347.6	347.6	347.6	347.6	348.0
165°	355.3	355.1	355.1	354.9	354.8	354.7	354.8	354.9	355.0	355.0	355.3
167.5°	361.3	361.0	360.8	360.5	360.3	360.1	360.1	360.1	360.1	360.1	360.5
170°	364.5	364.3	364.0	363.8	363.5	363.4	363.4	363.4	363.4	363.4	363.8
172.5°	366.8	366.6	366.3	366.1	365.8	365.7	365.7	365.7	365.7	365.7	366.1
175°	369.4	369.2	368.9	368.7	368.4	368.3	368.3	368.3	368.3	368.3	368.7
177.5°	370.7	370.6	370.3	370.1	369.9	369.8	369.7	369.7	369.7	369.6	369.9
180°	370.3	370.3	370.3	370.3	370.3	370.3	370.3	370.3	370.3	370.3	370.3



TEST NUMBER: P333257-930

CATALOG NUMBER: S125DIP-S1090D365U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1387.2	1389.1	1391.1	1392.0	1391.8	1391.6	1391.4	1391.2
5°	1380.2	1382.4	1384.6	1385.6	1385.4	1385.1	1384.9	1384.6
7.5°	1366.2	1368.4	1370.5	1371.5	1371.3	1371.0	1370.8	1370.5
10°	1354.4	1356.3	1358.3	1359.2	1358.9	1358.7	1358.5	1358.2
12.5°	1338.6	1340.2	1341.7	1342.6	1342.5	1342.4	1342.4	1342.3
15°	1311.1	1312.3	1313.5	1314.2	1314.2	1314.2	1314.2	1314.2
17.5°	1279.1	1280.6	1282.1	1282.3	1281.1	1279.9	1278.6	1277.4
20°	1254.8	1256.5	1258.3	1258.5	1257.3	1256.1	1254.8	1253.6
22.5°	1227.3	1228.4	1229.5	1229.6	1228.8	1228.0	1227.2	1226.3
25°	1183.1	1183.6	1184.1	1183.9	1183.2	1182.4	1181.7	1181.0
27.5°	1136.7	1136.8	1136.9	1136.6	1135.9	1135.1	1134.4	1133.7
30°	1102.9	1102.4	1102.0	1101.4	1100.7	1099.9	1099.2	1098.5
32.5°	1068.7	1067.8	1067.0	1065.8	1064.5	1063.2	1061.8	1060.5
35°	1015.6	1014.4	1013.2	1011.6	1009.7	1007.7	1005.8	1003.8
37.5°	959.9	958.1	956.3	954.8	953.7	952.5	951.4	950.3
40°	921.2	919.0	916.8	915.3	914.6	913.9	913.1	912.4
42.5°	882.9	880.8	878.9	877.3	876.2	875.1	873.9	872.8
45°	826.2	823.3	820.4	818.5	817.7	817.0	816.3	815.5
47.5°	766.5	763.4	760.5	758.1	756.4	754.7	753.0	751.3
50°	725.5	722.4	719.2	716.7	715.0	713.3	711.6	709.9
52.5°	685.8	683.1	680.3	677.9	676.0	674.1	672.2	670.3
55°	624.0	621.8	619.6	617.7	616.0	614.2	612.5	610.8
57.5°	562.7	559.9	557.0	555.1	554.2	553.3	552.4	551.4
60°	521.2	518.8	516.3	514.2	512.5	510.8	509.1	507.4
62.5°	481.2	478.6	475.9	473.9	472.6	471.3	469.9	468.6
65°	418.2	416.0	413.8	412.2	411.2	410.3	409.3	408.3
67.5°	358.2	356.3	354.4	353.2	352.6	352.0	351.5	350.9
70°	318.5	317.0	315.5	314.3	313.3	312.3	311.4	310.4
72.5°	281.1	279.4	277.8	276.5	275.5	274.5	273.5	272.6
75°	223.1	222.3	221.6	220.7	219.7	218.7	217.8	216.8
77.5°	169.9	169.5	169.1	168.5	167.8	167.1	166.4	165.8
80°	136.0	135.7	135.5	135.1	134.6	134.1	133.6	133.1
82.5°	103.9	103.5	103.1	102.7	102.6	102.6	102.5	102.3
85°	61.1	60.9	60.7	60.3	59.8	59.3	58.8	58.3
87.5°	24.0	24.0	24.1	23.9	23.6	23.2	22.8	22.5
90°	5.2	5.5	5.9	6.1	6.4	6.5	6.7	6.9
92.5°	11.9	12.3	12.7	13.0	13.2	13.3	13.5	13.6
95°	23.1	23.6	24.0	24.3	24.4	24.5	24.6	24.8
97.5°	36.2	36.6	37.0	37.3	37.3	37.4	37.5	37.6
100°	45.2	45.8	46.4	46.7	46.9	47.0	47.1	47.3
102.5°	54.5	55.2	55.8	56.3	56.4	56.6	56.7	56.9
105°	69.6	70.0	70.4	70.7	70.8	71.1	71.3	71.5
107.5°	85.9	86.1	86.3	86.4	86.3	86.3	86.3	86.3
110°	97.2	97.4	97.6	97.7	97.6	97.5	97.4	97.4





TEST NUMBER: P333257-930

CATALOG NUMBER: S125DIP-S1090D365U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	108.5	108.6	108.7	108.7	108.6	108.4	108.4	108.3
115°	125.8	125.7	125.6	125.6	125.6	125.5	125.4	125.3
117.5°	143.1	143.2	143.2	143.1	142.8	142.6	142.4	142.0
120°	154.7	154.7	154.7	154.6	154.3	154.1	153.8	153.6
122.5°	166.2	166.1	166.1	165.9	165.8	165.5	165.3	165.1
125°	183.0	182.9	182.8	182.6	182.6	182.5	182.5	182.4
127.5°	199.7	199.7	199.6	199.5	199.4	199.3	199.1	199.0
130°	210.8	210.8	210.7	210.6	210.4	210.3	210.2	210.1
132.5°	221.4	221.4	221.3	221.2	220.9	220.8	220.6	220.5
135°	237.7	237.7	237.7	237.6	237.3	237.1	236.8	236.6
137.5°	253.6	253.7	253.8	253.6	253.3	253.0	252.7	252.3
140°	263.7	263.7	263.9	263.8	263.5	263.2	262.9	262.5
142.5°	273.5	273.5	273.6	273.5	273.1	272.8	272.6	272.2
145°	287.6	287.6	287.6	287.5	287.3	287.1	286.9	286.7
147.5°	300.7	300.8	301.0	300.8	300.4	299.9	299.5	299.1
150°	308.9	308.9	308.9	308.8	308.8	308.6	308.4	308.3
152.5°	316.6	316.7	316.9	316.8	316.7	316.4	316.2	315.9
155°	327.6	327.8	328.1	328.1	327.8	327.4	327.1	326.8
157.5°	337.0	337.4	337.6	337.5	337.1	336.6	336.2	335.8
160°	342.8	343.1	343.3	343.3	343.0	342.7	342.3	342.0
162.5°	348.2	348.5	348.9	348.9	348.5	348.1	347.7	347.3
165°	355.6	355.8	356.0	356.0	355.6	355.2	354.8	354.4
167.5°	360.9	361.3	361.7	361.7	361.3	360.9	360.4	360.1
170°	364.1	364.5	364.9	364.8	364.4	363.9	363.5	363.1
172.5°	366.5	366.8	367.2	367.2	366.8	366.4	366.0	365.6
175°	369.0	369.4	369.8	369.7	369.3	368.8	368.4	367.9
177.5°	370.2	370.6	370.8	370.8	370.5	370.1	369.7	369.3
180°	370.3	370.3	370.3	370.3	370.3	370.3	370.3	370.3

(END OF REPORT)