

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333234-840

Luminaire Tested: **S125DIP-S850D1035U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333234-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1035U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7238.7 lumens
Efficiency: N/A
Efficacy: 139.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	38	34	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	20
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	26	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7979	7979	7979	7979
5°	9240	8006	7010	8006
10°	10750	7965	6142	7965
15°	11900	7906	5666	7906
20°	13320	7813	5283	7813
25°	15605	7709	5097	7709
30°	16855	7607	4935	7607
35°	13858	7413	4829	7413
40°	9850	7144	4713	7144
45°	7567	6783	4646	6783
50°	6459	6333	4636	6333
55°	5751	5892	4677	5892
60°	5187	5412	4795	5412
65°	4792	4927	4919	4927
70°	4358	4426	4991	4426
75°	3848	3898	4946	3898
80°	3239	3176	4526	3176
85°	2564	2290	3653	2290



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.9	1.6
10°-20°	354.1	4.9
20°-30°	575.0	7.9
30°-40°	701.4	9.7
40°-50°	638.1	8.8
50°-60°	508.2	7.0
60°-70°	354.0	4.9
70°-80°	188.8	2.6
80°-90°	50.4	0.7
90°-100°	362.4	5.0
100°-110°	779.1	10.8
110°-120°	731.2	10.1
120°-130°	592.6	8.2
130°-140°	475.6	6.6
140°-150°	358.9	5.0
150°-160°	252.6	3.5
160°-170°	148.9	2.1
170°-180°	48.4	0.7
0°-30°	1048.1	14.5
0°-40°	1749.5	24.2
0°-60°	2895.8	40.0
0°-90°	3489.0	48.2
90°-120°	1872.8	25.9
90°-150°	3299.8	45.6
90°-180°	3750.0	51.8
0°-180°	7238.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1236	1236	1236	1236	1236	
5°	1425	1235	1081	1235	1425	144
15°	1780	1182	847	1182	1780	509
25°	2190	1082	715	1082	2190	1000
35°	1758	940	612	940	1758	1076
45°	828	743	509	743	828	663
55°	511	523	415	523	511	460
65°	314	322	322	322	314	311
75°	154	156	198	156	154	166
85°	35	31	49	31	35	41
90°	23	1	23	1	23	17
95°	237	33	237	33	237	336
105°	1336	114	1336	114	1336	1328
115°	1488	204	1488	204	1488	1454
125°	1172	282	1172	282	1172	1061
135°	974	331	974	331	974	755
145°	768	385	768	385	768	488
155°	644	440	644	440	644	300
165°	564	480	564	480	564	161
175°	507	499	507	499	507	49
180°	500	500	500	500	500	



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1306.8	1305.0	1303.4	1300.0	1302.5	1295.5	1292.0	1286.2	1279.1	1276.6	1273.6
5°	1425.2	1427.8	1430.5	1419.5	1420.6	1413.2	1396.4	1382.8	1371.8	1357.7	1347.7
7.5°	1567.9	1561.7	1561.2	1554.1	1541.8	1532.0	1514.3	1491.9	1470.2	1445.4	1424.9
10°	1639.2	1639.7	1635.0	1626.6	1613.6	1604.1	1581.0	1558.9	1532.3	1500.8	1478.2
12.5°	1692.9	1695.1	1689.1	1677.8	1671.4	1650.2	1632.1	1606.0	1574.2	1549.0	1514.7
15°	1779.8	1773.9	1769.8	1755.7	1744.6	1722.6	1693.7	1666.5	1631.8	1599.8	1567.9
17.5°	1863.4	1868.0	1860.2	1847.2	1813.1	1787.4	1748.7	1711.3	1668.3	1625.4	1587.2
20°	1938.1	1942.3	1930.3	1907.7	1866.8	1841.1	1790.2	1742.0	1692.1	1637.1	1595.2
22.5°	2031.2	2027.9	2011.7	1977.3	1941.9	1894.4	1839.3	1780.6	1718.2	1656.0	1600.2
25°	2189.8	2167.8	2157.8	2115.4	2068.7	1998.9	1923.4	1837.4	1759.8	1677.5	1606.2
27.5°	2277.6	2270.8	2259.7	2230.1	2181.0	2106.5	2017.4	1912.6	1803.1	1699.2	1605.9
30°	2260.1	2261.1	2262.2	2252.7	2221.3	2165.2	2076.6	1963.8	1833.7	1716.8	1608.8
32.5°	2104.1	2123.1	2141.3	2162.9	2171.7	2161.0	2105.5	2003.7	1869.9	1737.0	1607.1
35°	1757.7	1763.5	1822.7	1881.5	1961.2	2023.1	2064.5	2019.4	1906.6	1754.0	1605.1
37.5°	1370.5	1398.9	1439.9	1506.2	1621.2	1724.2	1856.7	1917.6	1881.3	1759.6	1601.4
40°	1168.3	1194.6	1221.2	1288.9	1385.9	1510.8	1661.2	1789.7	1819.6	1742.0	1588.8
42.5°	1012.3	1033.0	1062.7	1113.6	1194.7	1305.1	1449.0	1616.9	1720.2	1690.8	1562.5
45°	828.5	841.6	864.7	905.0	963.8	1050.4	1177.2	1360.8	1520.7	1573.7	1499.8
47.5°	709.1	709.0	727.0	754.9	797.3	870.8	964.6	1108.4	1279.3	1405.6	1399.8
50°	642.9	640.3	654.4	678.5	712.1	760.8	850.5	965.3	1129.5	1272.6	1312.5
52.5°	585.8	586.1	594.8	612.7	640.8	682.5	749.4	852.9	993.2	1140.1	1215.2
55°	510.8	508.7	518.6	530.7	551.1	578.3	626.6	705.8	819.6	964.3	1061.9
57.5°	441.9	447.7	451.7	460.1	477.1	495.3	536.0	594.1	684.4	808.6	911.7
60°	401.6	407.5	410.6	419.0	432.6	448.4	479.8	527.0	603.0	710.0	812.2
62.5°	365.6	370.1	371.1	378.7	389.8	405.2	429.9	469.5	529.6	623.2	723.4
65°	313.6	313.6	315.7	323.6	328.8	342.4	361.3	390.1	438.4	511.3	596.7
67.5°	263.5	266.0	265.4	268.9	273.8	284.3	297.8	321.6	357.4	410.6	479.0
70°	230.8	232.8	232.3	234.9	240.1	247.0	258.0	280.5	306.2	351.8	410.6
72.5°	201.4	202.2	200.9	204.3	207.4	213.4	225.7	237.7	261.8	300.2	348.5
75°	154.2	155.2	156.2	158.3	161.5	164.6	171.0	183.0	198.7	227.6	258.5
77.5°	115.5	113.6	116.1	115.8	117.5	120.0	125.5	131.9	144.8	163.1	187.0
80°	87.1	87.6	87.6	88.1	90.7	92.3	97.0	101.7	111.7	125.3	142.1
82.5°	63.5	64.9	64.1	65.0	67.3	68.4	71.0	74.8	80.7	91.4	103.5
85°	34.6	32.0	33.0	34.1	34.1	34.6	36.7	38.3	41.4	45.6	50.3
87.5°	14.7	15.6	15.8	15.8	16.2	15.8	17.3	17.1	18.1	19.2	20.4
90°	23.2	23.2	22.2	22.2	22.2	20.2	19.2	18.2	17.2	16.2	14.1
92.5°	64.3	65.9	67.4	69.8	82.7	97.6	129.7	178.6	263.1	325.0	330.2
95°	236.9	253.1	261.2	291.3	362.9	447.6	571.6	724.9	874.0	893.2	728.9
97.5°	572.6	585.5	614.7	671.3	733.5	851.2	972.0	1079.5	1105.9	953.9	650.9
100°	786.4	802.4	839.8	912.3	981.9	1086.7	1190.6	1240.0	1162.4	910.3	580.7
102.5°	1025.0	1037.1	1077.7	1129.3	1203.7	1274.7	1324.4	1294.0	1128.5	833.7	527.5
105°	1335.7	1347.9	1368.1	1401.3	1433.5	1444.6	1400.3	1262.1	1020.3	730.8	475.8
107.5°	1500.7	1508.7	1515.4	1515.6	1499.2	1446.6	1332.7	1148.4	909.7	660.1	454.0
110°	1555.5	1555.5	1548.4	1529.3	1484.0	1398.3	1256.1	1064.6	846.8	627.0	447.6



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1549.0	1541.9	1524.3	1491.4	1425.1	1324.0	1180.3	998.5	800.0	607.7	447.6
115°	1488.0	1474.9	1446.6	1398.3	1319.6	1209.7	1071.7	915.3	749.0	586.7	450.6
117.5°	1380.9	1372.8	1344.8	1294.8	1216.2	1115.4	996.4	861.7	718.6	576.4	457.3
120°	1311.6	1303.5	1276.3	1227.9	1153.3	1064.6	953.7	832.7	701.7	571.6	463.7
122.5°	1250.3	1243.0	1215.8	1171.4	1104.9	1021.8	923.0	810.9	687.1	567.5	469.4
125°	1172.5	1162.4	1140.1	1098.8	1042.4	969.8	882.1	779.3	667.4	562.5	478.9
127.5°	1105.9	1101.5	1080.5	1044.0	992.8	924.8	843.0	747.0	649.2	560.1	489.6
130°	1069.6	1063.6	1043.4	1010.2	959.8	894.2	815.6	726.9	637.1	558.5	496.0
132.5°	1033.3	1026.4	1007.9	974.6	924.2	861.1	789.7	706.7	627.4	558.5	503.2
135°	973.8	967.8	949.7	916.4	872.0	814.6	750.0	680.4	615.9	558.5	513.1
137.5°	910.3	903.7	887.0	856.7	817.0	768.2	714.6	658.3	605.7	559.7	522.2
140°	866.0	860.9	845.9	819.6	782.3	739.9	693.6	646.2	600.9	560.5	526.2
142.5°	824.9	820.6	806.3	784.2	752.5	715.8	675.8	635.7	596.8	561.3	528.7
145°	768.2	764.2	753.1	735.9	711.8	684.5	653.3	622.0	590.8	560.5	531.3
147.5°	720.2	718.4	712.0	698.2	679.0	658.5	634.5	609.2	584.5	557.8	532.3
150°	693.6	692.6	688.5	676.4	661.4	643.2	624.0	601.9	579.7	555.4	532.3
152.5°	672.6	671.6	667.6	657.9	645.2	631.1	613.5	593.8	574.0	552.3	531.5
155°	644.2	643.2	640.2	633.1	623.0	612.0	597.8	581.7	564.5	546.4	529.3
157.5°	618.7	618.9	616.1	610.4	602.5	593.8	582.9	569.6	555.6	540.4	526.6
160°	601.9	602.9	600.9	595.8	588.8	581.7	571.6	561.5	548.5	536.3	524.2
162.5°	586.5	586.7	586.3	582.1	576.6	570.4	561.9	552.7	542.0	531.5	521.8
165°	564.5	564.5	564.5	562.5	558.5	553.5	547.4	540.4	532.3	524.2	518.2
167.5°	544.4	544.6	545.4	543.6	541.6	538.0	533.3	528.7	522.8	517.2	512.5
170°	532.3	533.3	533.3	532.3	530.3	528.3	525.2	522.2	517.2	513.1	510.1
172.5°	521.0	522.0	523.6	521.8	521.4	520.2	518.0	514.9	511.5	508.3	506.9
175°	507.1	508.1	510.1	509.1	509.1	509.1	507.1	507.1	504.0	503.0	503.0
177.5°	500.0	500.0	502.4	501.6	502.4	502.4	502.4	501.6	500.8	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1271.1	1268.2	1264.8	1258.9	1251.8	1248.0	1242.1	1238.4	1230.8	1224.6	1217.8
5°	1335.5	1321.9	1309.4	1293.1	1275.3	1263.7	1250.1	1234.9	1219.2	1203.0	1185.1
7.5°	1402.4	1378.3	1352.0	1323.8	1296.3	1270.9	1246.7	1222.8	1200.6	1173.8	1151.0
10°	1447.2	1416.8	1384.3	1346.0	1308.9	1276.4	1243.3	1214.5	1185.1	1153.7	1125.8
12.5°	1492.2	1451.7	1405.7	1363.7	1318.9	1279.7	1240.8	1204.0	1167.1	1132.3	1099.8
15°	1523.9	1488.1	1445.7	1385.9	1335.5	1281.6	1230.2	1182.5	1137.9	1099.1	1058.2
17.5°	1544.7	1498.7	1453.2	1395.8	1329.8	1269.4	1211.2	1156.6	1106.3	1057.1	1017.7
20°	1548.5	1501.3	1453.6	1397.5	1329.8	1260.6	1202.4	1136.8	1082.9	1032.0	983.7
22.5°	1547.2	1493.8	1441.8	1384.0	1318.1	1254.4	1184.0	1117.1	1058.5	1008.5	958.2
25°	1535.4	1478.2	1413.2	1355.0	1290.0	1222.3	1151.0	1081.8	1022.0	964.8	915.0
27.5°	1525.5	1451.4	1377.8	1309.9	1247.1	1185.1	1116.8	1045.9	979.7	921.7	874.7
30°	1513.4	1432.1	1349.2	1278.4	1214.0	1153.7	1089.1	1020.0	950.7	894.0	843.7
32.5°	1502.5	1407.8	1320.3	1243.2	1174.9	1116.3	1056.8	991.0	923.0	865.6	815.2
35°	1481.4	1371.8	1271.6	1184.6	1111.7	1051.4	1001.6	940.2	877.8	822.2	774.0
37.5°	1454.6	1324.5	1217.1	1125.8	1045.9	982.4	936.0	888.9	829.0	775.5	731.8
40°	1433.6	1291.0	1177.2	1083.9	1001.1	934.9	892.0	847.4	797.6	747.8	701.7
42.5°	1407.2	1260.8	1137.0	1036.5	954.4	890.1	845.0	807.1	763.2	716.7	673.9
45°	1358.7	1206.1	1071.9	963.8	880.9	817.5	770.8	742.6	709.5	665.4	629.2
47.5°	1287.3	1140.3	1001.5	890.0	804.5	745.7	702.0	674.8	651.5	618.7	585.9
50°	1223.9	1091.3	950.7	840.0	754.6	695.3	655.0	630.3	610.4	585.2	557.4
52.5°	1153.0	1029.6	900.8	791.4	706.8	648.3	608.8	587.1	570.6	552.5	525.1
55°	1040.4	935.5	816.0	712.1	634.0	576.8	542.2	523.3	509.7	496.0	479.3
57.5°	916.3	834.2	728.3	633.5	561.5	509.5	477.2	458.8	448.3	441.2	431.3
60°	829.0	758.8	667.5	581.0	510.8	464.6	433.1	419.0	410.1	404.2	397.0
62.5°	748.1	690.4	605.8	526.8	465.4	421.8	393.7	380.0	371.4	368.6	362.5
65°	628.7	584.2	514.4	448.9	396.5	359.2	335.6	322.4	317.2	314.1	314.7
67.5°	511.2	484.0	428.0	372.1	330.2	299.0	280.1	270.0	267.4	263.3	263.2
70°	439.4	419.0	371.8	323.1	285.8	261.7	244.9	234.4	231.8	229.6	229.1
72.5°	376.1	358.2	317.2	278.1	244.7	223.5	209.6	203.4	199.0	197.8	197.7
75°	282.7	272.7	240.1	209.2	186.1	171.5	162.1	156.2	153.1	152.6	153.1
77.5°	201.0	192.3	171.6	149.7	135.1	124.0	116.0	114.0	110.5	110.6	110.0
80°	151.0	145.2	132.2	114.8	102.8	93.3	89.2	85.4	84.4	82.8	84.4
82.5°	109.5	103.3	94.4	83.4	73.4	67.8	63.5	62.4	61.8	61.0	61.4
85°	54.0	54.5	49.3	40.9	36.7	33.5	30.9	30.9	30.4	29.9	30.4
87.5°	21.1	19.8	18.0	16.3	13.8	12.1	11.3	11.5	10.5	10.5	11.3
90°	13.1	11.1	10.1	8.1	6.1	4.0	2.0	1.0	2.0	4.0	6.1
92.5°	230.0	137.7	82.7	53.2	35.9	23.4	14.9	12.3	14.9	23.4	35.9
95°	450.6	228.8	121.0	75.6	53.4	42.3	34.2	33.2	34.2	42.3	53.4
97.5°	359.7	197.2	125.8	93.1	73.2	62.1	56.5	55.2	56.5	62.1	73.2
100°	326.6	195.6	137.1	106.8	87.7	76.6	72.6	70.6	72.6	76.6	87.7
102.5°	313.0	202.9	150.8	121.4	103.8	91.9	88.7	87.6	88.7	91.9	103.8
105°	307.5	217.7	173.4	145.2	129.1	119.0	113.9	113.9	113.9	119.0	129.1
107.5°	316.8	239.9	197.0	171.6	154.8	146.5	141.8	139.8	141.8	146.5	154.8
110°	325.6	256.1	214.7	188.5	173.4	164.3	160.3	158.2	160.3	164.3	173.4



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	336.9	271.4	231.7	206.2	191.2	182.1	178.8	176.8	178.8	182.1	191.2
115°	353.9	295.4	258.1	232.9	217.7	208.6	205.6	203.7	205.6	208.6	217.7
117.5°	373.2	320.0	284.7	260.3	243.2	234.1	230.9	227.8	230.9	234.1	243.2
120°	386.1	337.7	302.5	277.2	260.1	251.1	247.0	244.0	247.0	251.1	260.1
122.5°	400.6	354.7	319.4	294.2	275.4	266.3	263.1	260.9	263.1	266.3	275.4
125°	420.4	377.1	343.8	317.6	298.4	289.3	284.3	282.3	284.3	289.3	298.4
127.5°	438.5	398.6	366.6	340.3	320.0	308.5	302.1	299.0	302.1	308.5	320.0
130°	450.6	412.3	381.0	354.9	333.7	320.6	312.6	309.5	312.6	320.6	333.7
132.5°	461.1	425.3	393.9	367.8	345.8	331.0	321.3	317.6	321.3	331.0	345.8
135°	475.8	442.5	411.3	384.1	362.9	346.8	334.7	330.6	334.7	346.8	362.9
137.5°	486.8	454.8	426.5	398.4	377.7	361.5	350.2	347.2	350.2	361.5	377.7
140°	494.0	463.7	434.5	407.3	388.1	372.0	359.9	356.9	359.9	372.0	388.1
142.5°	498.0	469.4	441.7	416.2	397.8	381.6	370.4	368.2	370.4	381.6	397.8
145°	504.0	478.9	452.6	429.5	411.3	397.2	387.1	385.1	387.1	397.2	411.3
147.5°	507.7	484.9	461.9	441.5	425.9	412.7	404.0	402.8	404.0	412.7	425.9
150°	510.1	489.0	466.8	449.6	435.6	422.4	415.4	413.3	415.4	422.4	435.6
152.5°	511.7	493.0	472.4	456.9	443.5	432.1	425.9	424.6	425.9	432.1	443.5
155°	513.1	497.0	479.9	465.7	455.7	445.6	439.5	439.5	439.5	445.6	455.7
157.5°	514.1	500.4	485.7	475.0	466.2	457.5	452.6	452.8	452.6	457.5	466.2
160°	514.1	502.0	489.0	479.9	471.8	464.7	460.7	461.7	460.7	464.7	471.8
162.5°	513.3	503.6	492.2	484.7	478.3	472.0	468.0	469.0	468.0	472.0	478.3
165°	512.1	504.0	496.0	490.0	485.9	480.9	477.9	479.9	477.9	480.9	485.9
167.5°	509.7	504.0	497.4	493.6	490.8	488.0	486.1	487.2	486.1	488.0	490.8
170°	508.1	504.0	499.0	496.0	494.0	492.0	491.0	492.0	491.0	492.0	494.0
172.5°	506.4	503.2	499.0	497.6	496.3	494.4	493.4	495.2	493.4	494.4	496.3
175°	504.0	502.0	499.0	499.0	499.0	498.0	497.0	499.0	497.0	498.0	499.0
177.5°	501.6	500.8	499.2	499.2	500.0	499.2	499.2	500.8	499.2	499.2	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1214.1	1209.4	1205.7	1197.3	1192.7	1186.4	1181.3	1186.8	1180.9	1183.5	1179.6
5°	1176.2	1161.5	1151.0	1135.8	1122.7	1110.6	1101.8	1100.1	1095.9	1093.9	1087.5
7.5°	1130.6	1112.3	1094.3	1074.4	1057.5	1040.5	1029.6	1020.6	1014.6	1006.7	1001.4
10°	1103.8	1079.1	1058.2	1034.1	1013.1	994.7	980.1	972.7	965.9	955.9	952.3
12.5°	1070.7	1045.2	1019.6	993.8	973.7	953.2	940.6	929.5	924.8	913.5	912.4
15°	1031.0	992.7	967.5	941.3	913.4	896.7	886.2	874.1	868.9	861.0	855.3
17.5°	983.5	949.4	917.9	890.7	866.9	852.7	839.7	831.4	822.4	817.3	807.9
20°	949.2	916.7	885.1	856.3	838.0	821.7	811.2	803.3	794.0	791.3	781.8
22.5°	920.2	884.3	854.1	829.9	809.8	791.5	780.1	774.9	768.3	760.2	758.3
25°	873.1	835.9	810.2	786.1	768.2	751.4	743.6	736.8	730.4	724.7	722.6
27.5°	832.4	799.1	768.6	746.8	731.3	716.0	709.0	700.7	696.2	691.6	685.9
30°	803.9	769.8	743.1	722.1	705.3	691.7	684.3	678.5	674.4	670.1	667.0
32.5°	774.5	743.0	717.0	696.5	679.7	669.4	662.9	658.8	654.2	649.1	645.2
35°	735.7	701.0	675.9	658.1	645.0	637.1	629.8	626.1	620.9	620.9	616.6
37.5°	692.0	662.1	639.9	623.6	611.9	604.8	596.8	594.3	591.0	588.8	587.3
40°	666.0	638.1	617.2	601.0	588.3	582.6	576.3	572.1	570.0	567.3	566.3
42.5°	639.1	612.6	592.5	577.4	566.5	561.6	555.7	552.8	548.6	545.1	544.5
45°	598.3	572.6	554.3	542.2	532.8	527.0	523.3	517.1	514.9	510.8	510.2
47.5°	559.6	534.9	516.9	507.1	498.8	494.0	488.3	482.0	479.6	477.5	477.3
50°	530.7	508.2	491.3	481.9	474.0	467.3	461.4	457.3	455.7	455.7	456.8
52.5°	501.3	482.1	467.9	456.4	448.9	441.6	436.3	433.7	431.3	433.8	435.8
55°	458.3	438.9	428.4	417.4	410.1	401.6	399.1	398.0	396.5	400.6	402.7
57.5°	412.8	399.2	386.9	376.0	369.4	364.6	361.0	360.3	363.2	365.3	372.1
60°	383.8	368.1	357.1	348.7	340.8	337.7	336.7	335.6	337.7	343.5	352.3
62.5°	351.9	339.2	327.3	321.0	315.3	310.0	309.8	310.4	314.7	321.2	330.1
65°	305.2	294.2	286.3	278.9	274.3	271.1	272.2	274.3	278.9	287.9	297.8
67.5°	257.7	250.1	243.1	237.1	232.6	232.6	233.7	236.8	242.4	252.7	261.8
70°	227.0	218.6	212.9	210.3	206.6	204.5	207.6	212.9	217.6	227.0	234.9
72.5°	196.4	189.3	184.8	183.0	181.5	179.8	180.8	186.4	192.9	202.3	211.5
75°	151.0	148.3	145.2	143.2	141.6	142.6	143.7	149.0	154.2	164.1	174.6
77.5°	110.2	107.4	105.6	105.1	104.2	104.7	107.8	111.6	116.7	124.0	131.9
80°	83.4	82.3	81.3	80.8	80.8	81.3	85.4	88.1	92.8	99.7	105.9
82.5°	60.7	60.1	59.9	59.8	60.2	60.3	62.8	66.2	70.2	75.3	80.8
85°	32.0	30.9	32.5	33.0	32.0	33.5	34.6	36.7	38.3	40.9	43.5
87.5°	12.1	13.3	13.1	13.9	14.1	15.3	15.1	17.1	18.1	19.1	19.1
90°	8.1	10.1	11.1	13.1	14.1	16.2	17.2	18.2	19.2	20.2	22.2
92.5°	53.2	82.7	137.7	230.0	330.2	325.0	263.1	178.6	129.7	97.6	82.7
95°	75.6	121.0	228.8	450.6	728.9	893.2	874.0	724.9	571.6	447.6	362.9
97.5°	93.1	125.8	197.2	359.7	650.9	953.9	1105.9	1079.5	972.0	851.2	733.5
100°	106.8	137.1	195.6	326.6	580.7	910.3	1162.4	1240.0	1190.6	1086.7	981.9
102.5°	121.4	150.8	202.9	313.0	527.5	833.7	1128.5	1294.0	1324.4	1274.7	1203.7
105°	145.2	173.4	217.7	307.5	475.8	730.8	1020.3	1262.1	1400.3	1444.6	1433.5
107.5°	171.6	197.0	239.9	316.8	454.0	660.1	909.7	1148.4	1332.7	1446.6	1499.2
110°	188.5	214.7	256.1	325.6	447.6	627.0	846.8	1064.6	1256.1	1398.3	1484.0



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	206.2	231.7	271.4	336.9	447.6	607.7	800.0	998.5	1180.3	1324.0	1425.1
115°	232.9	258.1	295.4	353.9	450.6	586.7	749.0	915.3	1071.7	1209.7	1319.6
117.5°	260.3	284.7	320.0	373.2	457.3	576.4	718.6	861.7	996.4	1115.4	1216.2
120°	277.2	302.5	337.7	386.1	463.7	571.6	701.7	832.7	953.7	1064.6	1153.3
122.5°	294.2	319.4	354.7	400.6	469.4	567.5	687.1	810.9	923.0	1021.8	1104.9
125°	317.6	343.8	377.1	420.4	478.9	562.5	667.4	779.3	882.1	969.8	1042.4
127.5°	340.3	366.6	398.6	438.5	489.6	560.1	649.2	747.0	843.0	924.8	992.8
130°	354.9	381.0	412.3	450.6	496.0	558.5	637.1	726.9	815.6	894.2	959.8
132.5°	367.8	393.9	425.3	461.1	503.2	558.5	627.4	706.7	789.7	861.1	924.2
135°	384.1	411.3	442.5	475.8	513.1	558.5	615.9	680.4	750.0	814.6	872.0
137.5°	398.4	426.5	454.8	486.8	522.2	559.7	605.7	658.3	714.6	768.2	817.0
140°	407.3	434.5	463.7	494.0	526.2	560.5	600.9	646.2	693.6	739.9	782.3
142.5°	416.2	441.7	469.4	498.0	528.7	561.3	596.8	635.7	675.8	715.8	752.5
145°	429.5	452.6	478.9	504.0	531.3	560.5	590.8	622.0	653.3	684.5	711.8
147.5°	441.5	461.9	484.9	507.7	532.3	557.8	584.5	609.2	634.5	658.5	679.0
150°	449.6	466.8	489.0	510.1	532.3	555.4	579.7	601.9	624.0	643.2	661.4
152.5°	456.9	472.4	493.0	511.7	531.5	552.3	574.0	593.8	613.5	631.1	645.2
155°	465.7	479.9	497.0	513.1	529.3	546.4	564.5	581.7	597.8	612.0	623.0
157.5°	475.0	485.7	500.4	514.1	526.6	540.4	555.6	569.6	582.9	593.8	602.5
160°	479.9	489.0	502.0	514.1	524.2	536.3	548.5	561.5	571.6	581.7	588.8
162.5°	484.7	492.2	503.6	513.3	521.8	531.5	542.0	552.7	561.9	570.4	576.6
165°	490.0	496.0	504.0	512.1	518.2	524.2	532.3	540.4	547.4	553.5	558.5
167.5°	493.6	497.4	504.0	509.7	512.5	517.2	522.8	528.7	533.3	538.0	541.6
170°	496.0	499.0	504.0	508.1	510.1	513.1	517.2	522.2	525.2	528.3	530.3
172.5°	497.6	499.0	503.2	506.4	506.9	508.3	511.5	514.9	518.0	520.2	521.4
175°	499.0	499.0	502.0	504.0	503.0	503.0	504.0	507.1	507.1	509.1	509.1
177.5°	499.2	499.2	500.8	501.6	500.0	500.0	500.8	501.6	502.4	502.4	502.4
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1177.1	1180.0	1177.5	1180.9	1177.5	1180.0	1177.1	1179.6	1183.5	1180.9	1186.8
5°	1084.9	1080.3	1083.4	1081.3	1083.4	1080.3	1084.9	1087.5	1093.9	1095.9	1100.1
7.5°	999.8	995.2	990.2	987.7	990.2	995.2	999.8	1001.4	1006.7	1014.6	1020.6
10°	946.5	940.7	940.2	936.5	940.2	940.7	946.5	952.3	955.9	965.9	972.7
12.5°	907.5	902.1	896.2	894.6	896.2	902.1	907.5	912.4	913.5	924.8	929.5
15°	852.1	847.9	844.2	847.4	844.2	847.9	852.1	855.3	861.0	868.9	874.1
17.5°	806.1	802.6	801.9	798.1	801.9	802.6	806.1	807.9	817.3	822.4	831.4
20°	777.1	774.5	775.6	768.7	775.6	774.5	777.1	781.8	791.3	794.0	803.3
22.5°	754.1	748.9	748.3	746.9	748.3	748.9	754.1	758.3	760.2	768.3	774.9
25°	717.9	715.3	712.7	715.3	712.7	715.3	717.9	722.6	724.7	730.4	736.8
27.5°	686.3	683.2	682.5	682.8	682.5	683.2	686.3	685.9	691.6	696.2	700.7
30°	667.0	661.8	662.3	661.8	662.3	661.8	667.0	667.0	670.1	674.4	678.5
32.5°	646.0	642.5	641.8	640.8	641.8	642.5	646.0	645.2	649.1	654.2	658.8
35°	615.1	615.1	612.5	612.5	612.5	615.1	615.1	616.6	620.9	620.9	626.1
37.5°	586.0	585.5	583.9	584.2	583.9	585.5	586.0	587.3	588.8	591.0	594.3
40°	564.2	563.7	562.1	559.0	562.1	563.7	564.2	566.3	567.3	570.0	572.1
42.5°	543.2	541.5	540.8	539.7	540.8	541.5	543.2	544.5	545.1	548.6	552.8
45°	510.2	510.2	509.2	508.7	509.2	510.2	510.2	510.2	510.8	514.9	517.1
47.5°	478.2	479.1	481.1	480.8	481.1	479.1	478.2	477.3	477.5	479.6	482.0
50°	458.8	459.4	460.9	461.4	460.9	459.4	458.8	456.8	455.7	455.7	457.3
52.5°	437.5	440.5	442.4	442.1	442.4	440.5	437.5	435.8	433.8	431.3	433.7
55°	407.5	411.1	414.8	415.4	414.8	411.1	407.5	402.7	400.6	396.5	398.0
57.5°	377.8	382.9	386.8	388.0	386.8	382.9	377.8	372.1	365.3	363.2	360.3
60°	357.6	364.5	369.2	371.2	369.2	364.5	357.6	352.3	343.5	337.7	335.6
62.5°	338.3	346.0	350.7	351.1	350.7	346.0	338.3	330.1	321.2	314.7	310.4
65°	306.8	314.7	318.8	321.9	318.8	314.7	306.8	297.8	287.9	278.9	274.3
67.5°	272.8	280.6	285.3	287.8	285.3	280.6	272.8	261.8	252.7	242.4	236.8
70°	248.0	255.9	262.2	264.3	262.2	255.9	248.0	234.9	227.0	217.6	212.9
72.5°	223.7	230.8	235.8	238.2	235.8	230.8	223.7	211.5	202.3	192.9	186.4
75°	181.5	190.9	195.6	198.2	195.6	190.9	181.5	174.6	164.1	154.2	149.0
77.5°	139.9	148.6	151.4	152.7	151.4	148.6	139.9	131.9	124.0	116.7	111.6
80°	112.2	117.4	121.1	121.7	121.1	117.4	112.2	105.9	99.7	92.8	88.1
82.5°	86.2	90.6	91.8	93.1	91.8	90.6	86.2	80.8	75.3	70.2	66.2
85°	47.2	49.3	49.8	49.3	49.8	49.3	47.2	43.5	40.9	38.3	36.7
87.5°	20.0	19.5	19.7	20.6	19.7	19.5	20.0	19.1	19.1	18.1	17.1
90°	22.2	22.2	23.2	23.2	23.2	22.2	22.2	22.2	20.2	19.2	18.2
92.5°	69.8	67.4	65.9	64.3	65.9	67.4	69.8	82.7	97.6	129.7	178.6
95°	291.3	261.2	253.1	236.9	253.1	261.2	291.3	362.9	447.6	571.6	724.9
97.5°	671.3	614.7	585.5	572.6	585.5	614.7	671.3	733.5	851.2	972.0	1079.5
100°	912.3	839.8	802.4	786.4	802.4	839.8	912.3	981.9	1086.7	1190.6	1240.0
102.5°	1129.3	1077.7	1037.1	1025.0	1037.1	1077.7	1129.3	1203.7	1274.7	1324.4	1294.0
105°	1401.3	1368.1	1347.9	1335.7	1347.9	1368.1	1401.3	1433.5	1444.6	1400.3	1262.1
107.5°	1515.6	1515.4	1508.7	1500.7	1508.7	1515.4	1515.6	1499.2	1446.6	1332.7	1148.4
110°	1529.3	1548.4	1555.5	1555.5	1555.5	1548.4	1529.3	1484.0	1398.3	1256.1	1064.6



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1491.4	1524.3	1541.9	1549.0	1541.9	1524.3	1491.4	1425.1	1324.0	1180.3	998.5
115°	1398.3	1446.6	1474.9	1488.0	1474.9	1446.6	1398.3	1319.6	1209.7	1071.7	915.3
117.5°	1294.8	1344.8	1372.8	1380.9	1372.8	1344.8	1294.8	1216.2	1115.4	996.4	861.7
120°	1227.9	1276.3	1303.5	1311.6	1303.5	1276.3	1227.9	1153.3	1064.6	953.7	832.7
122.5°	1171.4	1215.8	1243.0	1250.3	1243.0	1215.8	1171.4	1104.9	1021.8	923.0	810.9
125°	1098.8	1140.1	1162.4	1172.5	1162.4	1140.1	1098.8	1042.4	969.8	882.1	779.3
127.5°	1044.0	1080.5	1101.5	1105.9	1101.5	1080.5	1044.0	992.8	924.8	843.0	747.0
130°	1010.2	1043.4	1063.6	1069.6	1063.6	1043.4	1010.2	959.8	894.2	815.6	726.9
132.5°	974.6	1007.9	1026.4	1033.3	1026.4	1007.9	974.6	924.2	861.1	789.7	706.7
135°	916.4	949.7	967.8	973.8	967.8	949.7	916.4	872.0	814.6	750.0	680.4
137.5°	856.7	887.0	903.7	910.3	903.7	887.0	856.7	817.0	768.2	714.6	658.3
140°	819.6	845.9	860.9	866.0	860.9	845.9	819.6	782.3	739.9	693.6	646.2
142.5°	784.2	806.3	820.6	824.9	820.6	806.3	784.2	752.5	715.8	675.8	635.7
145°	735.9	753.1	764.2	768.2	764.2	753.1	735.9	711.8	684.5	653.3	622.0
147.5°	698.2	712.0	718.4	720.2	718.4	712.0	698.2	679.0	658.5	634.5	609.2
150°	676.4	688.5	692.6	693.6	692.6	688.5	676.4	661.4	643.2	624.0	601.9
152.5°	657.9	667.6	671.6	672.6	671.6	667.6	657.9	645.2	631.1	613.5	593.8
155°	633.1	640.2	643.2	644.2	643.2	640.2	633.1	623.0	612.0	597.8	581.7
157.5°	610.4	616.1	618.9	618.7	618.9	616.1	610.4	602.5	593.8	582.9	569.6
160°	595.8	600.9	602.9	601.9	602.9	600.9	595.8	588.8	581.7	571.6	561.5
162.5°	582.1	586.3	586.7	586.5	586.7	586.3	582.1	576.6	570.4	561.9	552.7
165°	562.5	564.5	564.5	564.5	564.5	564.5	562.5	558.5	553.5	547.4	540.4
167.5°	543.6	545.4	544.6	544.4	544.6	545.4	543.6	541.6	538.0	533.3	528.7
170°	532.3	533.3	533.3	532.3	533.3	533.3	532.3	530.3	528.3	525.2	522.2
172.5°	521.8	523.6	522.0	521.0	522.0	523.6	521.8	521.4	520.2	518.0	514.9
175°	509.1	510.1	508.1	507.1	508.1	510.1	509.1	509.1	509.1	507.1	507.1
177.5°	501.6	502.4	500.0	500.0	500.0	502.4	501.6	502.4	502.4	502.4	501.6
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1181.3	1186.4	1192.7	1197.3	1205.7	1209.4	1214.1	1217.8	1224.6	1230.8	1238.4
5°	1101.8	1110.6	1122.7	1135.8	1151.0	1161.5	1176.2	1185.1	1203.0	1219.2	1234.9
7.5°	1029.6	1040.5	1057.5	1074.4	1094.3	1112.3	1130.6	1151.0	1173.8	1200.6	1222.8
10°	980.1	994.7	1013.1	1034.1	1058.2	1079.1	1103.8	1125.8	1153.7	1185.1	1214.5
12.5°	940.6	953.2	973.7	993.8	1019.6	1045.2	1070.7	1099.8	1132.3	1167.1	1204.0
15°	886.2	896.7	913.4	941.3	967.5	992.7	1031.0	1058.2	1099.1	1137.9	1182.5
17.5°	839.7	852.7	866.9	890.7	917.9	949.4	983.5	1017.7	1057.1	1106.3	1156.6
20°	811.2	821.7	838.0	856.3	885.1	916.7	949.2	983.7	1032.0	1082.9	1136.8
22.5°	780.1	791.5	809.8	829.9	854.1	884.3	920.2	958.2	1008.5	1058.5	1117.1
25°	743.6	751.4	768.2	786.1	810.2	835.9	873.1	915.0	964.8	1022.0	1081.8
27.5°	709.0	716.0	731.3	746.8	768.6	799.1	832.4	874.7	921.7	979.7	1045.9
30°	684.3	691.7	705.3	722.1	743.1	769.8	803.9	843.7	894.0	950.7	1020.0
32.5°	662.9	669.4	679.7	696.5	717.0	743.0	774.5	815.2	865.6	923.0	991.0
35°	629.8	637.1	645.0	658.1	675.9	701.0	735.7	774.0	822.2	877.8	940.2
37.5°	596.8	604.8	611.9	623.6	639.9	662.1	692.0	731.8	775.5	829.0	888.9
40°	576.3	582.6	588.3	601.0	617.2	638.1	666.0	701.7	747.8	797.6	847.4
42.5°	555.7	561.6	566.5	577.4	592.5	612.6	639.1	673.9	716.7	763.2	807.1
45°	523.3	527.0	532.8	542.2	554.3	572.6	598.3	629.2	665.4	709.5	742.6
47.5°	488.3	494.0	498.8	507.1	516.9	534.9	559.6	585.9	618.7	651.5	674.8
50°	461.4	467.3	474.0	481.9	491.3	508.2	530.7	557.4	585.2	610.4	630.3
52.5°	436.3	441.6	448.9	456.4	467.9	482.1	501.3	525.1	552.5	570.6	587.1
55°	399.1	401.6	410.1	417.4	428.4	438.9	458.3	479.3	496.0	509.7	523.3
57.5°	361.0	364.6	369.4	376.0	386.9	399.2	412.8	431.3	441.2	448.3	458.8
60°	336.7	337.7	340.8	348.7	357.1	368.1	383.8	397.0	404.2	410.1	419.0
62.5°	309.8	310.0	315.3	321.0	327.3	339.2	351.9	362.5	368.6	371.4	380.0
65°	272.2	271.1	274.3	278.9	286.3	294.2	305.2	314.7	314.1	317.2	322.4
67.5°	233.7	232.6	232.6	237.1	243.1	250.1	257.7	263.2	263.3	267.4	270.0
70°	207.6	204.5	206.6	210.3	212.9	218.6	227.0	229.1	229.6	231.8	234.4
72.5°	180.8	179.8	181.5	183.0	184.8	189.3	196.4	197.7	197.8	199.0	203.4
75°	143.7	142.6	141.6	143.2	145.2	148.3	151.0	153.1	152.6	153.1	156.2
77.5°	107.8	104.7	104.2	105.1	105.6	107.4	110.2	110.0	110.6	110.5	114.0
80°	85.4	81.3	80.8	80.8	81.3	82.3	83.4	84.4	82.8	84.4	85.4
82.5°	62.8	60.3	60.2	59.8	59.9	60.1	60.7	61.4	61.0	61.8	62.4
85°	34.6	33.5	32.0	33.0	32.5	30.9	32.0	30.4	29.9	30.4	30.9
87.5°	15.1	15.3	14.1	13.9	13.1	13.3	12.1	11.3	10.5	10.5	11.5
90°	17.2	16.2	14.1	13.1	11.1	10.1	8.1	6.1	4.0	2.0	1.0
92.5°	263.1	325.0	330.2	230.0	137.7	82.7	53.2	35.9	23.4	14.9	12.3
95°	874.0	893.2	728.9	450.6	228.8	121.0	75.6	53.4	42.3	34.2	33.2
97.5°	1105.9	953.9	650.9	359.7	197.2	125.8	93.1	73.2	62.1	56.5	55.2
100°	1162.4	910.3	580.7	326.6	195.6	137.1	106.8	87.7	76.6	72.6	70.6
102.5°	1128.5	833.7	527.5	313.0	202.9	150.8	121.4	103.8	91.9	88.7	87.6
105°	1020.3	730.8	475.8	307.5	217.7	173.4	145.2	129.1	119.0	113.9	113.9
107.5°	909.7	660.1	454.0	316.8	239.9	197.0	171.6	154.8	146.5	141.8	139.8
110°	846.8	627.0	447.6	325.6	256.1	214.7	188.5	173.4	164.3	160.3	158.2



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	800.0	607.7	447.6	336.9	271.4	231.7	206.2	191.2	182.1	178.8	176.8
115°	749.0	586.7	450.6	353.9	295.4	258.1	232.9	217.7	208.6	205.6	203.7
117.5°	718.6	576.4	457.3	373.2	320.0	284.7	260.3	243.2	234.1	230.9	227.8
120°	701.7	571.6	463.7	386.1	337.7	302.5	277.2	260.1	251.1	247.0	244.0
122.5°	687.1	567.5	469.4	400.6	354.7	319.4	294.2	275.4	266.3	263.1	260.9
125°	667.4	562.5	478.9	420.4	377.1	343.8	317.6	298.4	289.3	284.3	282.3
127.5°	649.2	560.1	489.6	438.5	398.6	366.6	340.3	320.0	308.5	302.1	299.0
130°	637.1	558.5	496.0	450.6	412.3	381.0	354.9	333.7	320.6	312.6	309.5
132.5°	627.4	558.5	503.2	461.1	425.3	393.9	367.8	345.8	331.0	321.3	317.6
135°	615.9	558.5	513.1	475.8	442.5	411.3	384.1	362.9	346.8	334.7	330.6
137.5°	605.7	559.7	522.2	486.8	454.8	426.5	398.4	377.7	361.5	350.2	347.2
140°	600.9	560.5	526.2	494.0	463.7	434.5	407.3	388.1	372.0	359.9	356.9
142.5°	596.8	561.3	528.7	498.0	469.4	441.7	416.2	397.8	381.6	370.4	368.2
145°	590.8	560.5	531.3	504.0	478.9	452.6	429.5	411.3	397.2	387.1	385.1
147.5°	584.5	557.8	532.3	507.7	484.9	461.9	441.5	425.9	412.7	404.0	402.8
150°	579.7	555.4	532.3	510.1	489.0	466.8	449.6	435.6	422.4	415.4	413.3
152.5°	574.0	552.3	531.5	511.7	493.0	472.4	456.9	443.5	432.1	425.9	424.6
155°	564.5	546.4	529.3	513.1	497.0	479.9	465.7	455.7	445.6	439.5	439.5
157.5°	555.6	540.4	526.6	514.1	500.4	485.7	475.0	466.2	457.5	452.6	452.8
160°	548.5	536.3	524.2	514.1	502.0	489.0	479.9	471.8	464.7	460.7	461.7
162.5°	542.0	531.5	521.8	513.3	503.6	492.2	484.7	478.3	472.0	468.0	469.0
165°	532.3	524.2	518.2	512.1	504.0	496.0	490.0	485.9	480.9	477.9	479.9
167.5°	522.8	517.2	512.5	509.7	504.0	497.4	493.6	490.8	488.0	486.1	487.2
170°	517.2	513.1	510.1	508.1	504.0	499.0	496.0	494.0	492.0	491.0	492.0
172.5°	511.5	508.3	506.9	506.4	503.2	499.0	497.6	496.3	494.4	493.4	495.2
175°	504.0	503.0	503.0	504.0	502.0	499.0	499.0	499.0	498.0	497.0	499.0
177.5°	500.8	500.0	500.0	501.6	500.8	499.2	499.2	500.0	499.2	499.2	500.8
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1242.1	1248.0	1251.8	1258.9	1264.8	1268.2	1271.1	1273.6	1276.6	1279.1	1286.2
5°	1250.1	1263.7	1275.3	1293.1	1309.4	1321.9	1335.5	1347.7	1357.7	1371.8	1382.8
7.5°	1246.7	1270.9	1296.3	1323.8	1352.0	1378.3	1402.4	1424.9	1445.4	1470.2	1491.9
10°	1243.3	1276.4	1308.9	1346.0	1384.3	1416.8	1447.2	1478.2	1500.8	1532.3	1558.9
12.5°	1240.8	1279.7	1318.9	1363.7	1405.7	1451.7	1492.2	1514.7	1549.0	1574.2	1606.0
15°	1230.2	1281.6	1335.5	1385.9	1445.7	1488.1	1523.9	1567.9	1599.8	1631.8	1666.5
17.5°	1211.2	1269.4	1329.8	1395.8	1453.2	1498.7	1544.7	1587.2	1625.4	1668.3	1711.3
20°	1202.4	1260.6	1329.8	1397.5	1453.6	1501.3	1548.5	1595.2	1637.1	1692.1	1742.0
22.5°	1184.0	1254.4	1318.1	1384.0	1441.8	1493.8	1547.2	1600.2	1656.0	1718.2	1780.6
25°	1151.0	1222.3	1290.0	1355.0	1413.2	1478.2	1535.4	1606.2	1677.5	1759.8	1837.4
27.5°	1116.8	1185.1	1247.1	1309.9	1377.8	1451.4	1525.5	1605.9	1699.2	1803.1	1912.6
30°	1089.1	1153.7	1214.0	1278.4	1349.2	1432.1	1513.4	1608.8	1716.8	1833.7	1963.8
32.5°	1056.8	1116.3	1174.9	1243.2	1320.3	1407.8	1502.5	1607.1	1737.0	1869.9	2003.7
35°	1001.6	1051.4	1111.7	1184.6	1271.6	1371.8	1481.4	1605.1	1754.0	1906.6	2019.4
37.5°	936.0	982.4	1045.9	1125.8	1217.1	1324.5	1454.6	1601.4	1759.6	1881.3	1917.6
40°	892.0	934.9	1001.1	1083.9	1177.2	1291.0	1433.6	1588.8	1742.0	1819.6	1789.7
42.5°	845.0	890.1	954.4	1036.5	1137.0	1260.8	1407.2	1562.5	1690.8	1720.2	1616.9
45°	770.8	817.5	880.9	963.8	1071.9	1206.1	1358.7	1499.8	1573.7	1520.7	1360.8
47.5°	702.0	745.7	804.5	890.0	1001.5	1140.3	1287.3	1399.8	1405.6	1279.3	1108.4
50°	655.0	695.3	754.6	840.0	950.7	1091.3	1223.9	1312.5	1272.6	1129.5	965.3
52.5°	608.8	648.3	706.8	791.4	900.8	1029.6	1153.0	1215.2	1140.1	993.2	852.9
55°	542.2	576.8	634.0	712.1	816.0	935.5	1040.4	1061.9	964.3	819.6	705.8
57.5°	477.2	509.5	561.5	633.5	728.3	834.2	916.3	911.7	808.6	684.4	594.1
60°	433.1	464.6	510.8	581.0	667.5	758.8	829.0	812.2	710.0	603.0	527.0
62.5°	393.7	421.8	465.4	526.8	605.8	690.4	748.1	723.4	623.2	529.6	469.5
65°	335.6	359.2	396.5	448.9	514.4	584.2	628.7	596.7	511.3	438.4	390.1
67.5°	280.1	299.0	330.2	372.1	428.0	484.0	511.2	479.0	410.6	357.4	321.6
70°	244.9	261.7	285.8	323.1	371.8	419.0	439.4	410.6	351.8	306.2	280.5
72.5°	209.6	223.5	244.7	278.1	317.2	358.2	376.1	348.5	300.2	261.8	237.7
75°	162.1	171.5	186.1	209.2	240.1	272.7	282.7	258.5	227.6	198.7	183.0
77.5°	116.0	124.0	135.1	149.7	171.6	192.3	201.0	187.0	163.1	144.8	131.9
80°	89.2	93.3	102.8	114.8	132.2	145.2	151.0	142.1	125.3	111.7	101.7
82.5°	63.5	67.8	73.4	83.4	94.4	103.3	109.5	103.5	91.4	80.7	74.8
85°	30.9	33.5	36.7	40.9	49.3	54.5	54.0	50.3	45.6	41.4	38.3
87.5°	11.3	12.1	13.8	16.3	18.0	19.8	21.1	20.4	19.2	18.1	17.1
90°	2.0	4.0	6.1	8.1	10.1	11.1	13.1	14.1	16.2	17.2	18.2
92.5°	14.9	23.4	35.9	53.2	82.7	137.7	230.0	330.2	325.0	263.1	178.6
95°	34.2	42.3	53.4	75.6	121.0	228.8	450.6	728.9	893.2	874.0	724.9
97.5°	56.5	62.1	73.2	93.1	125.8	197.2	359.7	650.9	953.9	1105.9	1079.5
100°	72.6	76.6	87.7	106.8	137.1	195.6	326.6	580.7	910.3	1162.4	1240.0
102.5°	88.7	91.9	103.8	121.4	150.8	202.9	313.0	527.5	833.7	1128.5	1294.0
105°	113.9	119.0	129.1	145.2	173.4	217.7	307.5	475.8	730.8	1020.3	1262.1
107.5°	141.8	146.5	154.8	171.6	197.0	239.9	316.8	454.0	660.1	909.7	1148.4
110°	160.3	164.3	173.4	188.5	214.7	256.1	325.6	447.6	627.0	846.8	1064.6



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	178.8	182.1	191.2	206.2	231.7	271.4	336.9	447.6	607.7	800.0	998.5
115°	205.6	208.6	217.7	232.9	258.1	295.4	353.9	450.6	586.7	749.0	915.3
117.5°	230.9	234.1	243.2	260.3	284.7	320.0	373.2	457.3	576.4	718.6	861.7
120°	247.0	251.1	260.1	277.2	302.5	337.7	386.1	463.7	571.6	701.7	832.7
122.5°	263.1	266.3	275.4	294.2	319.4	354.7	400.6	469.4	567.5	687.1	810.9
125°	284.3	289.3	298.4	317.6	343.8	377.1	420.4	478.9	562.5	667.4	779.3
127.5°	302.1	308.5	320.0	340.3	366.6	398.6	438.5	489.6	560.1	649.2	747.0
130°	312.6	320.6	333.7	354.9	381.0	412.3	450.6	496.0	558.5	637.1	726.9
132.5°	321.3	331.0	345.8	367.8	393.9	425.3	461.1	503.2	558.5	627.4	706.7
135°	334.7	346.8	362.9	384.1	411.3	442.5	475.8	513.1	558.5	615.9	680.4
137.5°	350.2	361.5	377.7	398.4	426.5	454.8	486.8	522.2	559.7	605.7	658.3
140°	359.9	372.0	388.1	407.3	434.5	463.7	494.0	526.2	560.5	600.9	646.2
142.5°	370.4	381.6	397.8	416.2	441.7	469.4	498.0	528.7	561.3	596.8	635.7
145°	387.1	397.2	411.3	429.5	452.6	478.9	504.0	531.3	560.5	590.8	622.0
147.5°	404.0	412.7	425.9	441.5	461.9	484.9	507.7	532.3	557.8	584.5	609.2
150°	415.4	422.4	435.6	449.6	466.8	489.0	510.1	532.3	555.4	579.7	601.9
152.5°	425.9	432.1	443.5	456.9	472.4	493.0	511.7	531.5	552.3	574.0	593.8
155°	439.5	445.6	455.7	465.7	479.9	497.0	513.1	529.3	546.4	564.5	581.7
157.5°	452.6	457.5	466.2	475.0	485.7	500.4	514.1	526.6	540.4	555.6	569.6
160°	460.7	464.7	471.8	479.9	489.0	502.0	514.1	524.2	536.3	548.5	561.5
162.5°	468.0	472.0	478.3	484.7	492.2	503.6	513.3	521.8	531.5	542.0	552.7
165°	477.9	480.9	485.9	490.0	496.0	504.0	512.1	518.2	524.2	532.3	540.4
167.5°	486.1	488.0	490.8	493.6	497.4	504.0	509.7	512.5	517.2	522.8	528.7
170°	491.0	492.0	494.0	496.0	499.0	504.0	508.1	510.1	513.1	517.2	522.2
172.5°	493.4	494.4	496.3	497.6	499.0	503.2	506.4	506.9	508.3	511.5	514.9
175°	497.0	498.0	499.0	499.0	499.0	502.0	504.0	503.0	503.0	504.0	507.1
177.5°	499.2	499.2	500.0	499.2	499.2	500.8	501.6	500.0	500.0	500.8	501.6
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1292.0	1295.5	1302.5	1300.0	1303.4	1305.0	1306.8
5°	1396.4	1413.2	1420.6	1419.5	1430.5	1427.8	1425.2
7.5°	1514.3	1532.0	1541.8	1554.1	1561.2	1561.7	1567.9
10°	1581.0	1604.1	1613.6	1626.6	1635.0	1639.7	1639.2
12.5°	1632.1	1650.2	1671.4	1677.8	1689.1	1695.1	1692.9
15°	1693.7	1722.6	1744.6	1755.7	1769.8	1773.9	1779.8
17.5°	1748.7	1787.4	1813.1	1847.2	1860.2	1868.0	1863.4
20°	1790.2	1841.1	1866.8	1907.7	1930.3	1942.3	1938.1
22.5°	1839.3	1894.4	1941.9	1977.3	2011.7	2027.9	2031.2
25°	1923.4	1998.9	2068.7	2115.4	2157.8	2167.8	2189.8
27.5°	2017.4	2106.5	2181.0	2230.1	2259.7	2270.8	2277.6
30°	2076.6	2165.2	2221.3	2252.7	2262.2	2261.1	2260.1
32.5°	2105.5	2161.0	2171.7	2162.9	2141.3	2123.1	2104.1
35°	2064.5	2023.1	1961.2	1881.5	1822.7	1763.5	1757.7
37.5°	1856.7	1724.2	1621.2	1506.2	1439.9	1398.9	1370.5
40°	1661.2	1510.8	1385.9	1288.9	1221.2	1194.6	1168.3
42.5°	1449.0	1305.1	1194.7	1113.6	1062.7	1033.0	1012.3
45°	1177.2	1050.4	963.8	905.0	864.7	841.6	828.5
47.5°	964.6	870.8	797.3	754.9	727.0	709.0	709.1
50°	850.5	760.8	712.1	678.5	654.4	640.3	642.9
52.5°	749.4	682.5	640.8	612.7	594.8	586.1	585.8
55°	626.6	578.3	551.1	530.7	518.6	508.7	510.8
57.5°	536.0	495.3	477.1	460.1	451.7	447.7	441.9
60°	479.8	448.4	432.6	419.0	410.6	407.5	401.6
62.5°	429.9	405.2	389.8	378.7	371.1	370.1	365.6
65°	361.3	342.4	328.8	323.6	315.7	313.6	313.6
67.5°	297.8	284.3	273.8	268.9	265.4	266.0	263.5
70°	258.0	247.0	240.1	234.9	232.3	232.8	230.8
72.5°	225.7	213.4	207.4	204.3	200.9	202.2	201.4
75°	171.0	164.6	161.5	158.3	156.2	155.2	154.2
77.5°	125.5	120.0	117.5	115.8	116.1	113.6	115.5
80°	97.0	92.3	90.7	88.1	87.6	87.6	87.1
82.5°	71.0	68.4	67.3	65.0	64.1	64.9	63.5
85°	36.7	34.6	34.1	34.1	33.0	32.0	34.6
87.5°	17.3	15.8	16.2	15.8	15.8	15.6	14.7
90°	19.2	20.2	22.2	22.2	22.2	23.2	23.2
92.5°	129.7	97.6	82.7	69.8	67.4	65.9	64.3
95°	571.6	447.6	362.9	291.3	261.2	253.1	236.9
97.5°	972.0	851.2	733.5	671.3	614.7	585.5	572.6
100°	1190.6	1086.7	981.9	912.3	839.8	802.4	786.4
102.5°	1324.4	1274.7	1203.7	1129.3	1077.7	1037.1	1025.0
105°	1400.3	1444.6	1433.5	1401.3	1368.1	1347.9	1335.7
107.5°	1332.7	1446.6	1499.2	1515.6	1515.4	1508.7	1500.7
110°	1256.1	1398.3	1484.0	1529.3	1548.4	1555.5	1555.5



TEST NUMBER: P333234-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1180.3	1324.0	1425.1	1491.4	1524.3	1541.9	1549.0
115°	1071.7	1209.7	1319.6	1398.3	1446.6	1474.9	1488.0
117.5°	996.4	1115.4	1216.2	1294.8	1344.8	1372.8	1380.9
120°	953.7	1064.6	1153.3	1227.9	1276.3	1303.5	1311.6
122.5°	923.0	1021.8	1104.9	1171.4	1215.8	1243.0	1250.3
125°	882.1	969.8	1042.4	1098.8	1140.1	1162.4	1172.5
127.5°	843.0	924.8	992.8	1044.0	1080.5	1101.5	1105.9
130°	815.6	894.2	959.8	1010.2	1043.4	1063.6	1069.6
132.5°	789.7	861.1	924.2	974.6	1007.9	1026.4	1033.3
135°	750.0	814.6	872.0	916.4	949.7	967.8	973.8
137.5°	714.6	768.2	817.0	856.7	887.0	903.7	910.3
140°	693.6	739.9	782.3	819.6	845.9	860.9	866.0
142.5°	675.8	715.8	752.5	784.2	806.3	820.6	824.9
145°	653.3	684.5	711.8	735.9	753.1	764.2	768.2
147.5°	634.5	658.5	679.0	698.2	712.0	718.4	720.2
150°	624.0	643.2	661.4	676.4	688.5	692.6	693.6
152.5°	613.5	631.1	645.2	657.9	667.6	671.6	672.6
155°	597.8	612.0	623.0	633.1	640.2	643.2	644.2
157.5°	582.9	593.8	602.5	610.4	616.1	618.9	618.7
160°	571.6	581.7	588.8	595.8	600.9	602.9	601.9
162.5°	561.9	570.4	576.6	582.1	586.3	586.7	586.5
165°	547.4	553.5	558.5	562.5	564.5	564.5	564.5
167.5°	533.3	538.0	541.6	543.6	545.4	544.6	544.4
170°	525.2	528.3	530.3	532.3	533.3	533.3	532.3
172.5°	518.0	520.2	521.4	521.8	523.6	522.0	521.0
175°	507.1	509.1	509.1	509.1	510.1	508.1	507.1
177.5°	502.4	502.4	502.4	501.6	502.4	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0

(END OF REPORT)