

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333260-930

Luminaire Tested: **S125DIP-S1090D590U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333260-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D590U930-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5327.5 lumens  
Efficiency: N/A  
Efficacy: 109.2 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333260-930  
CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69	69	69	69	69	69	69	69	69	69	69	69																
	1	102	98	94	91	96	93	89	86	83	80	78	74	72	70	65	64	63	59	59	59	59	59	59	59	59	59	59	59	59																
	2	93	86	80	75	88	81	76	71	73	69	65	65	62	59	58	55	53	49	49	49	49	49	49	49	49	49	49	49	49																
	3	85	76	68	62	80	72	65	60	65	59	55	58	54	50	51	48	46	42	42	42	42	42	42	42	42	42	42	42	42																
	4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	42	39	36	36	36	36	36	36	36	36	36	36	36	36																
	5	72	60	52	46	68	57	50	44	52	46	41	46	42	38	42	38	34	32	32	32	32	32	32	32	32	32	32	32	32																
	6	66	54	46	40	63	52	44	38	47	40	36	42	37	33	38	34	30	28	28	28	28	28	28	28	28	28	28	28	28																
	7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	35	30	27	25	25	25	25	25	25	25	25	25	25	25	25																
	8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	27	24	22	22	22	22	22	22	22	22	22	22	22	22																
	9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20	20	20	20	20	20	20	20	20	20	20	20																
	10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18	18	18	18	18	18	18	18	18	18	18	18																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8373	8373	8373	8373
5°	9697	8401	7356	8401
10°	11281	8358	6445	8358
15°	12488	8297	5945	8297
20°	13978	8199	5544	8199
25°	16376	8089	5349	8089
30°	17687	7982	5179	7982
35°	14542	7779	5067	7779
40°	10336	7497	4945	7497
45°	7941	7117	4875	7117
50°	6779	6646	4866	6646
55°	6035	6184	4908	6184
60°	5444	5679	5032	5679
65°	5029	5171	5164	5171
70°	4572	4645	5238	4645
75°	4037	4092	5190	4092
80°	3396	3336	4749	3336
85°	2690	2401	3831	2401



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.8	2.3
10°-20°	371.6	7.0
20°-30°	603.4	11.3
30°-40°	736.0	13.8
40°-50°	669.6	12.6
50°-60°	533.4	10.0
60°-70°	371.5	7.0
70°-80°	198.1	3.7
80°-90°	51.3	1.0
90°-100°	40.0	0.8
100°-110°	118.2	2.2
110°-120°	200.2	3.8
120°-130°	263.5	4.9
130°-140°	295.3	5.5
140°-150°	289.4	5.4
150°-160°	243.0	4.6
160°-170°	161.6	3.0
170°-180°	56.5	1.1
0°-30°	1099.8	20.6
0°-40°	1835.9	34.5
0°-60°	3038.8	57.0
0°-90°	3659.7	68.7
90°-120°	358.5	6.7
90°-150°	1206.6	22.6
90°-180°	1668.0	31.3
0°-180°	5327.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1296	1296	1296	1296	1296	
5°	1496	1296	1135	1296	1496	151
15°	1868	1241	889	1241	1868	535
25°	2298	1135	751	1135	2298	1050
35°	1844	987	643	987	1844	1129
45°	869	779	534	779	869	696
55°	536	549	436	549	536	483
65°	329	338	338	338	329	327
75°	162	164	208	164	162	174
85°	36	32	52	32	36	42
90°	11	0	11	0	11	8
95°	40	30	40	30	40	41
105°	115	106	115	106	115	122
115°	202	200	202	200	202	200
125°	294	292	294	292	294	263
135°	382	380	382	380	382	295
145°	463	461	463	461	463	289
155°	527	527	527	527	527	243
165°	572	574	572	574	572	161
175°	594	596	594	596	594	56
180°	598	598	598	598	598	



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1371.3	1369.5	1367.8	1364.2	1366.9	1359.4	1355.9	1349.7	1342.2	1339.6	1336.5
5°	1495.7	1498.4	1501.2	1489.6	1490.7	1483.0	1465.4	1451.1	1439.6	1424.7	1414.2
7.5°	1645.4	1638.8	1638.3	1630.8	1618.0	1607.6	1589.1	1565.5	1542.8	1516.8	1495.3
10°	1720.2	1720.8	1715.8	1707.0	1693.2	1683.3	1659.1	1636.0	1607.9	1574.9	1551.3
12.5°	1776.5	1778.8	1772.6	1760.7	1754.0	1731.8	1712.9	1685.3	1652.0	1625.5	1589.6
15°	1867.7	1861.7	1857.3	1842.3	1830.8	1807.7	1777.4	1748.8	1712.5	1678.9	1645.4
17.5°	1955.5	1960.3	1952.1	1938.5	1902.7	1875.7	1835.1	1795.9	1750.7	1705.7	1665.6
20°	2033.8	2038.2	2025.6	2002.0	1959.0	1932.1	1878.7	1828.1	1775.8	1718.0	1674.0
22.5°	2131.6	2128.1	2111.0	2075.0	2037.8	1987.9	1930.2	1868.6	1803.0	1737.8	1679.3
25°	2298.0	2274.8	2264.4	2219.9	2170.9	2097.7	2018.4	1928.2	1846.7	1760.4	1685.5
27.5°	2390.2	2383.0	2371.3	2340.2	2288.8	2210.5	2117.1	2007.1	1892.2	1783.1	1685.2
30°	2371.7	2372.8	2373.9	2364.0	2331.0	2272.2	2179.1	2060.8	1924.4	1801.6	1688.2
32.5°	2208.0	2228.0	2247.1	2269.8	2279.1	2267.8	2209.5	2102.7	1962.2	1822.8	1686.5
35°	1844.5	1850.6	1912.8	1974.4	2058.1	2123.0	2166.5	2119.1	2000.8	1840.7	1684.4
37.5°	1438.3	1467.9	1511.0	1580.6	1701.4	1809.5	1948.5	2012.4	1974.2	1846.6	1680.6
40°	1226.0	1253.5	1281.7	1352.6	1454.4	1585.3	1743.3	1878.1	1909.5	1828.1	1667.4
42.5°	1062.3	1084.1	1115.2	1168.6	1253.7	1369.7	1520.5	1696.7	1805.2	1774.3	1639.6
45°	869.4	883.2	907.4	949.8	1011.5	1102.2	1235.4	1428.0	1595.9	1651.4	1573.9
47.5°	744.2	744.1	763.0	792.2	836.7	913.8	1012.3	1163.2	1342.5	1475.1	1468.9
50°	674.7	671.9	686.7	712.1	747.3	798.5	892.6	1013.1	1185.3	1335.5	1377.4
52.5°	614.8	615.1	624.3	642.9	672.5	716.2	786.4	895.1	1042.3	1196.5	1275.2
55°	536.0	533.8	544.2	556.9	578.4	607.0	657.6	740.7	860.1	1011.9	1114.4
57.5°	463.7	469.9	474.0	482.8	500.7	519.8	562.5	623.5	718.2	848.6	956.8
60°	421.5	427.5	430.9	439.7	454.0	470.5	503.5	553.0	632.8	745.1	852.4
62.5°	383.7	388.4	389.5	397.4	409.1	425.2	451.1	492.8	555.8	654.0	759.0
65°	329.1	329.1	331.3	339.5	345.0	359.3	379.1	409.4	460.1	536.5	626.2
67.5°	276.5	279.1	278.6	282.2	287.2	298.4	312.6	337.5	375.0	430.9	502.6
70°	242.1	244.3	243.8	246.5	252.0	259.2	270.8	294.4	321.4	369.2	430.9
72.5°	211.3	212.2	210.8	214.4	217.7	224.0	236.8	249.5	274.7	315.1	365.7
75°	161.8	162.9	164.0	166.2	169.5	172.8	179.4	192.1	208.6	238.8	271.3
77.5°	121.3	119.2	121.8	121.5	123.4	125.9	131.8	138.4	152.0	171.1	196.2
80°	91.3	91.9	91.9	92.5	95.2	96.9	101.8	106.7	117.2	131.5	149.1
82.5°	66.7	68.2	67.3	68.2	70.5	71.7	74.5	78.6	84.6	95.9	108.6
85°	36.3	33.6	34.7	35.8	35.8	36.3	38.5	40.2	43.5	47.9	52.8
87.5°	12.8	13.6	14.0	13.9	14.3	14.3	15.9	15.8	17.0	18.2	19.8
90°	11.2	10.8	10.5	10.3	9.9	9.5	9.0	8.5	8.0	7.4	6.7
92.5°	21.9	21.7	21.5	21.3	21.0	20.6	19.9	19.2	18.5	17.9	17.0
95°	40.0	39.8	39.6	39.4	39.1	38.7	38.0	37.3	36.5	35.8	34.8
97.5°	60.7	60.5	60.4	60.3	60.2	59.8	59.1	58.4	57.7	57.0	55.6
100°	76.3	76.1	75.9	75.7	75.4	74.8	73.9	73.1	72.1	71.2	69.8
102.5°	91.9	91.6	91.3	91.1	90.7	90.1	89.1	88.1	87.1	86.0	85.4
105°	115.4	115.0	114.7	114.4	114.1	113.7	113.0	112.4	111.8	111.1	110.6
107.5°	139.3	139.3	139.4	139.4	139.4	139.3	139.0	138.7	138.4	138.0	137.5
110°	157.2	157.3	157.4	157.5	157.6	157.5	157.2	156.9	156.6	156.3	156.0



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	174.7	174.9	175.0	175.3	175.5	175.5	175.3	175.2	175.0	174.9	174.5
115°	202.4	202.4	202.5	202.6	202.8	202.8	202.9	203.0	203.2	203.3	203.0
117.5°	229.3	229.8	230.2	230.6	231.0	231.1	231.1	231.0	230.9	230.8	230.6
120°	247.9	248.3	248.7	249.2	249.6	249.7	249.7	249.7	249.7	249.7	249.6
122.5°	266.5	266.8	267.2	267.5	267.8	268.1	268.2	268.2	268.3	268.4	268.1
125°	294.4	294.5	294.6	294.7	294.8	295.0	295.2	295.4	295.6	295.8	295.7
127.5°	321.2	321.4	321.6	321.8	322.0	322.2	322.3	322.4	322.5	322.6	322.5
130°	339.1	339.2	339.5	339.7	339.9	340.1	340.1	340.2	340.4	340.5	340.2
132.5°	355.8	356.1	356.4	356.7	356.9	357.2	357.3	357.3	357.5	357.6	357.6
135°	381.9	382.3	382.7	383.1	383.5	383.7	383.7	383.7	383.7	383.7	383.6
137.5°	407.3	407.9	408.4	408.9	409.4	409.6	409.4	409.4	409.2	409.1	408.9
140°	423.7	424.2	424.8	425.3	425.7	425.9	425.7	425.5	425.3	425.1	424.8
142.5°	439.4	439.9	440.3	440.9	441.4	441.6	441.5	441.3	441.2	441.1	440.8
145°	462.8	463.1	463.4	463.7	464.0	464.1	464.1	464.1	464.1	464.1	463.9
147.5°	482.8	483.5	484.2	484.9	485.6	485.8	485.6	485.3	485.1	484.9	484.6
150°	497.7	497.9	498.1	498.3	498.5	498.6	498.6	498.6	498.6	498.6	498.1
152.5°	510.0	510.3	510.7	511.0	511.4	511.5	511.3	511.0	510.8	510.5	510.3
155°	527.4	527.9	528.5	529.0	529.5	529.5	529.1	528.7	528.3	527.9	527.8
157.5°	542.0	542.7	543.4	544.0	544.8	544.9	544.5	544.0	543.6	543.2	543.2
160°	552.1	552.6	553.1	553.7	554.2	554.2	553.8	553.3	552.9	552.5	552.4
162.5°	560.6	561.3	561.8	562.5	563.0	563.1	562.6	562.1	561.6	561.1	561.1
165°	572.1	572.7	573.3	574.0	574.5	574.7	574.2	573.8	573.4	573.0	572.9
167.5°	581.2	581.8	582.4	583.1	583.8	583.8	583.2	582.5	581.9	581.3	581.3
170°	586.0	586.8	587.5	588.2	588.9	589.0	588.3	587.7	587.1	586.5	586.5
172.5°	590.1	590.8	591.4	592.1	592.7	592.7	592.1	591.5	590.8	590.2	590.2
175°	593.9	594.7	595.4	596.1	596.8	596.9	596.2	595.7	595.0	594.4	594.4
177.5°	596.1	596.7	597.4	597.9	598.5	598.5	598.0	597.5	597.0	596.6	596.6
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1333.9	1330.8	1327.3	1321.1	1313.6	1309.7	1303.5	1299.6	1291.6	1285.0	1278.0
5°	1401.6	1387.3	1374.1	1357.0	1338.3	1326.2	1311.9	1295.9	1279.4	1262.3	1243.7
7.5°	1471.7	1446.3	1418.9	1389.3	1360.3	1333.7	1308.2	1283.3	1260.0	1231.8	1207.9
10°	1518.8	1486.9	1452.8	1412.6	1373.5	1339.4	1304.7	1274.5	1243.7	1210.6	1181.5
12.5°	1565.9	1523.4	1475.2	1431.1	1384.1	1342.9	1302.1	1263.5	1224.7	1188.2	1154.1
15°	1599.1	1561.7	1517.1	1454.4	1401.6	1344.9	1290.9	1240.9	1194.1	1153.4	1110.5
17.5°	1621.1	1572.8	1524.9	1464.8	1395.5	1332.1	1271.1	1213.7	1161.0	1109.4	1068.0
20°	1625.0	1575.5	1525.4	1466.5	1395.5	1322.9	1261.8	1193.0	1136.4	1083.0	1032.3
22.5°	1623.7	1567.6	1513.0	1452.5	1383.2	1316.3	1242.4	1172.3	1110.8	1058.3	1005.5
25°	1611.3	1551.3	1483.0	1422.0	1353.7	1282.7	1207.9	1135.2	1072.5	1012.5	960.3
27.5°	1600.9	1523.1	1445.9	1374.6	1308.7	1243.7	1172.0	1097.6	1028.0	967.3	918.0
30°	1588.1	1502.8	1415.8	1341.6	1273.9	1210.6	1143.0	1070.3	997.7	938.2	885.4
32.5°	1576.7	1477.3	1385.5	1304.6	1233.0	1171.4	1109.1	1039.9	968.6	908.3	855.5
35°	1554.5	1439.6	1334.5	1243.1	1166.6	1103.3	1051.1	986.7	921.2	862.8	812.2
37.5°	1526.5	1390.0	1277.2	1181.5	1097.6	1030.9	982.3	932.9	870.0	813.8	768.0
40°	1504.5	1354.8	1235.4	1137.4	1050.5	981.1	936.0	889.2	837.0	784.7	736.3
42.5°	1476.8	1323.1	1193.1	1087.7	1001.6	934.1	886.7	847.0	800.9	752.1	707.2
45°	1425.8	1265.7	1124.8	1011.5	924.5	857.9	808.9	779.2	744.5	698.3	660.3
47.5°	1350.9	1196.6	1050.9	933.9	844.2	782.5	736.6	708.1	683.7	649.3	614.9
50°	1284.3	1145.2	997.7	881.6	791.9	729.7	687.3	661.5	640.5	614.1	585.0
52.5°	1210.0	1080.4	945.3	830.5	741.7	680.4	638.9	616.1	598.7	579.8	551.1
55°	1091.8	981.7	856.2	747.3	665.3	605.3	569.0	549.2	534.9	520.6	503.0
57.5°	961.6	875.5	764.3	664.7	589.2	534.7	500.8	481.5	470.3	463.0	452.7
60°	870.0	796.3	700.5	609.7	536.0	487.5	454.5	439.7	430.3	424.3	416.5
62.5°	785.1	724.5	635.8	552.9	488.4	442.6	413.2	398.8	389.8	386.9	380.5
65°	659.8	613.0	539.8	471.1	416.0	376.9	352.2	338.4	332.9	329.6	330.2
67.5°	536.4	507.9	449.1	390.4	346.6	313.8	294.0	283.4	280.6	276.2	276.1
70°	461.1	439.7	390.1	339.0	299.9	274.6	257.0	246.0	243.2	241.0	240.5
72.5°	394.7	375.9	332.9	291.9	256.7	234.6	220.0	213.4	208.9	207.6	207.5
75°	296.6	286.2	252.0	219.6	195.3	179.9	170.1	164.0	160.7	160.1	160.7
77.5°	210.8	201.7	180.0	157.0	141.8	130.1	121.7	119.6	115.9	116.0	115.4
80°	158.5	152.5	138.7	120.5	107.9	97.9	93.5	89.7	88.6	86.9	88.6
82.5°	114.9	108.4	99.1	87.5	77.0	71.1	66.7	65.5	64.8	64.1	64.4
85°	56.7	57.2	51.7	42.9	38.5	35.2	32.4	32.4	31.9	31.4	31.9
87.5°	20.5	19.6	17.6	16.1	13.8	12.3	11.7	12.0	10.8	10.5	11.2
90°	6.0	5.3	4.6	3.8	2.9	2.1	1.3	0.5	1.3	2.1	2.9
92.5°	16.1	15.2	14.3	13.5	13.0	12.4	11.8	11.3	11.8	12.4	13.0
95°	33.8	32.7	31.7	31.1	30.8	30.7	30.4	30.2	30.4	30.7	30.8
97.5°	54.1	52.7	51.3	50.5	50.5	50.4	50.3	50.2	50.3	50.4	50.5
100°	68.5	67.1	65.8	65.1	65.1	65.1	65.1	65.1	65.1	65.1	65.1
102.5°	84.7	84.0	83.3	82.8	82.3	81.9	81.5	81.1	81.5	81.9	82.3
105°	109.9	109.3	108.7	108.1	107.6	107.0	106.6	106.1	106.6	107.0	107.6
107.5°	137.1	136.6	136.2	135.7	135.1	134.6	134.1	133.5	134.1	134.6	135.1
110°	155.6	155.3	155.1	154.7	154.1	153.6	153.0	152.5	153.0	153.6	154.1





TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.1	173.7	173.3	173.0	172.7	172.4	172.2	171.9	172.2	172.4	172.7
115°	202.8	202.6	202.4	202.1	201.7	201.3	200.9	200.5	200.9	201.3	201.7
117.5°	230.4	230.2	230.1	229.8	229.7	229.5	229.3	229.1	229.3	229.5	229.7
120°	249.6	249.5	249.3	249.1	248.5	248.0	247.5	247.0	247.5	248.0	248.5
122.5°	267.8	267.6	267.3	267.1	266.8	266.7	266.5	266.4	266.5	266.7	266.8
125°	295.6	295.5	295.4	295.1	294.4	293.8	293.2	292.5	293.2	293.8	294.4
127.5°	322.4	322.2	322.1	321.9	321.5	321.1	320.8	320.5	320.8	321.1	321.5
130°	340.1	339.8	339.7	339.2	338.8	338.3	337.7	337.2	337.7	338.3	338.8
132.5°	357.7	357.7	357.8	357.3	356.4	355.6	354.8	353.9	354.8	355.6	356.4
135°	383.5	383.4	383.3	382.9	382.3	381.7	381.1	380.4	381.1	381.7	382.3
137.5°	408.6	408.5	408.2	407.8	407.2	406.6	406.0	405.4	406.0	406.6	407.2
140°	424.5	424.2	423.9	423.5	422.9	422.4	421.9	421.3	421.9	422.4	422.9
142.5°	440.3	439.9	439.5	439.1	438.7	438.2	437.8	437.4	437.8	438.2	438.7
145°	463.6	463.3	462.9	462.6	462.2	461.8	461.3	460.9	461.3	461.8	462.2
147.5°	484.4	484.0	483.8	483.6	483.4	483.1	482.9	482.7	482.9	483.1	483.4
150°	497.7	497.3	496.9	496.8	496.9	497.0	497.1	497.2	497.1	497.0	496.9
152.5°	510.1	510.0	509.8	509.6	509.6	509.4	509.2	509.1	509.2	509.4	509.6
155°	527.7	527.6	527.5	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4
157.5°	543.1	542.9	542.8	542.9	543.2	543.3	543.6	543.8	543.6	543.3	543.2
160°	552.4	552.2	552.1	552.2	552.5	552.9	553.2	553.5	553.2	552.9	552.5
162.5°	561.1	561.0	561.0	561.1	561.3	561.6	561.8	562.1	561.8	561.6	561.3
165°	572.8	572.7	572.6	572.7	572.8	573.1	573.2	573.5	573.2	573.1	572.8
167.5°	581.3	581.3	581.3	581.5	581.9	582.3	582.8	583.2	582.8	582.3	581.9
170°	586.5	586.5	586.5	586.7	587.1	587.5	587.9	588.3	587.9	587.5	587.1
172.5°	590.2	590.2	590.2	590.4	590.8	591.3	591.7	592.1	591.7	591.3	590.8
175°	594.4	594.4	594.4	594.6	595.0	595.4	595.8	596.2	595.8	595.4	595.0
177.5°	596.7	596.8	596.9	597.0	597.5	597.8	598.1	598.4	598.1	597.8	597.5
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1274.0	1269.2	1265.2	1256.4	1251.6	1245.0	1239.7	1245.4	1239.3	1241.9	1238.0
5°	1234.3	1218.9	1207.9	1191.9	1178.2	1165.5	1156.2	1154.5	1150.1	1147.9	1141.3
7.5°	1186.5	1167.3	1148.3	1127.4	1109.8	1091.8	1080.4	1071.0	1064.7	1056.5	1050.8
10°	1158.4	1132.5	1110.5	1085.2	1063.2	1043.9	1028.5	1020.8	1013.7	1003.1	999.3
12.5°	1123.6	1096.8	1070.0	1042.9	1021.7	1000.3	987.1	975.4	970.5	958.7	957.5
15°	1081.9	1041.7	1015.3	987.7	958.6	941.0	930.0	917.3	911.8	903.6	897.5
17.5°	1032.1	996.2	963.2	934.7	909.7	894.9	881.3	872.5	863.1	857.7	847.7
20°	996.1	961.9	928.9	898.6	879.4	862.3	851.3	843.0	833.2	830.4	820.5
22.5°	965.6	928.0	896.3	870.9	849.9	830.6	818.7	813.1	806.2	797.8	795.8
25°	916.2	877.2	850.2	824.9	806.2	788.6	780.3	773.1	766.5	760.5	758.3
27.5°	873.5	838.6	806.6	783.7	767.4	751.4	744.1	735.4	730.6	725.7	719.7
30°	843.6	807.8	779.8	757.7	740.1	725.9	718.1	712.1	707.7	703.3	699.9
32.5°	812.8	779.7	752.4	730.9	713.3	702.5	695.7	691.4	686.6	681.3	677.1
35°	772.1	735.7	709.3	690.6	676.9	668.6	660.9	657.0	651.5	651.5	647.1
37.5°	726.2	694.8	671.5	654.4	642.0	634.7	626.3	623.7	620.2	617.8	616.3
40°	698.9	669.7	647.7	630.6	617.4	611.4	604.8	600.4	598.2	595.4	594.3
42.5°	670.7	642.9	621.7	606.0	594.5	589.4	583.2	580.1	575.7	572.1	571.4
45°	627.9	600.9	581.6	569.0	559.1	553.0	549.2	542.6	540.4	536.0	535.4
47.5°	587.3	561.4	542.5	532.1	523.4	518.4	512.4	505.8	503.3	501.1	500.8
50°	556.9	533.2	515.6	505.7	497.5	490.3	484.3	479.9	478.2	478.2	479.3
52.5°	526.1	505.9	491.0	478.8	471.1	463.4	457.9	455.2	452.7	455.3	457.3
55°	480.9	460.6	449.6	438.1	430.3	421.5	418.7	417.7	416.0	420.4	422.7
57.5°	433.2	418.9	406.0	394.5	387.6	382.5	378.8	378.1	381.2	383.4	390.4
60°	402.8	386.3	374.7	365.9	357.7	354.4	353.3	352.2	354.4	360.4	369.8
62.5°	369.3	356.0	343.5	336.9	330.8	325.3	325.1	325.8	330.2	337.1	346.4
65°	320.2	308.7	300.4	292.8	287.8	284.5	285.6	287.8	292.8	302.1	312.6
67.5°	270.4	262.5	255.1	248.8	244.1	244.1	245.2	248.5	254.4	265.1	274.7
70°	238.3	229.5	223.4	220.7	216.8	214.6	217.9	223.4	228.4	238.3	246.5
72.5°	206.1	198.7	194.0	192.1	190.4	188.7	189.7	195.7	202.4	212.3	221.8
75°	158.5	155.7	152.5	150.3	148.5	149.7	150.7	156.3	161.8	172.3	183.3
77.5°	115.7	112.8	110.8	110.3	109.4	110.0	113.0	117.1	122.5	130.1	138.4
80°	87.5	86.4	85.3	84.7	84.7	85.3	89.7	92.5	97.4	104.5	111.1
82.5°	63.8	63.0	62.9	62.7	63.2	63.3	66.0	69.5	73.6	79.0	84.7
85°	33.6	32.4	34.1	34.7	33.6	35.2	36.3	38.5	40.2	42.9	45.7
87.5°	11.7	12.8	12.5	13.0	13.2	14.3	13.9	15.8	16.8	17.8	17.4
90°	3.8	4.6	5.3	6.0	6.7	7.4	8.0	8.5	9.0	9.5	9.9
92.5°	13.5	14.3	15.2	16.1	17.0	17.9	18.5	19.2	19.9	20.6	21.0
95°	31.1	31.7	32.7	33.8	34.8	35.8	36.5	37.3	38.0	38.7	39.1
97.5°	50.5	51.3	52.7	54.1	55.6	57.0	57.7	58.4	59.1	59.8	60.2
100°	65.1	65.8	67.1	68.5	69.8	71.2	72.1	73.1	73.9	74.8	75.4
102.5°	82.8	83.3	84.0	84.7	85.4	86.0	87.1	88.1	89.1	90.1	90.7
105°	108.1	108.7	109.3	109.9	110.6	111.1	111.8	112.4	113.0	113.7	114.1
107.5°	135.7	136.2	136.6	137.1	137.5	138.0	138.4	138.7	139.0	139.3	139.4
110°	154.7	155.1	155.3	155.6	156.0	156.3	156.6	156.9	157.2	157.5	157.6



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	173.0	173.3	173.7	174.1	174.5	174.9	175.0	175.2	175.3	175.5	175.5
115°	202.1	202.4	202.6	202.8	203.0	203.3	203.2	203.0	202.9	202.8	202.8
117.5°	229.8	230.1	230.2	230.4	230.6	230.8	230.9	231.0	231.1	231.1	231.0
120°	249.1	249.3	249.5	249.6	249.6	249.7	249.7	249.7	249.7	249.7	249.6
122.5°	267.1	267.3	267.6	267.8	268.1	268.4	268.3	268.2	268.2	268.1	267.8
125°	295.1	295.4	295.5	295.6	295.7	295.8	295.6	295.4	295.2	295.0	294.8
127.5°	321.9	322.1	322.2	322.4	322.5	322.6	322.5	322.4	322.3	322.2	322.0
130°	339.2	339.7	339.8	340.1	340.2	340.5	340.4	340.2	340.1	340.1	339.9
132.5°	357.3	357.8	357.7	357.7	357.6	357.6	357.5	357.3	357.3	357.2	356.9
135°	382.9	383.3	383.4	383.5	383.6	383.7	383.7	383.7	383.7	383.7	383.5
137.5°	407.8	408.2	408.5	408.6	408.9	409.1	409.2	409.4	409.4	409.6	409.4
140°	423.5	423.9	424.2	424.5	424.8	425.1	425.3	425.5	425.7	425.9	425.7
142.5°	439.1	439.5	439.9	440.3	440.8	441.1	441.2	441.3	441.5	441.6	441.4
145°	462.6	462.9	463.3	463.6	463.9	464.1	464.1	464.1	464.1	464.1	464.0
147.5°	483.6	483.8	484.0	484.4	484.6	484.9	485.1	485.3	485.6	485.8	485.6
150°	496.8	496.9	497.3	497.7	498.1	498.6	498.6	498.6	498.6	498.6	498.5
152.5°	509.6	509.8	510.0	510.1	510.3	510.5	510.8	511.0	511.3	511.5	511.4
155°	527.4	527.5	527.6	527.7	527.8	527.9	528.3	528.7	529.1	529.5	529.5
157.5°	542.9	542.8	542.9	543.1	543.2	543.2	543.6	544.0	544.5	544.9	544.8
160°	552.2	552.1	552.2	552.4	552.4	552.5	552.9	553.3	553.8	554.2	554.2
162.5°	561.1	561.0	561.0	561.1	561.1	561.1	561.6	562.1	562.6	563.1	563.0
165°	572.7	572.6	572.7	572.8	572.9	573.0	573.4	573.8	574.2	574.7	574.5
167.5°	581.5	581.3	581.3	581.3	581.3	581.3	581.9	582.5	583.2	583.8	583.8
170°	586.7	586.5	586.5	586.5	586.5	586.5	587.1	587.7	588.3	589.0	588.9
172.5°	590.4	590.2	590.2	590.2	590.2	590.2	590.8	591.5	592.1	592.7	592.7
175°	594.6	594.4	594.4	594.4	594.4	594.4	595.0	595.7	596.2	596.9	596.8
177.5°	597.0	596.9	596.8	596.7	596.6	596.6	597.0	597.5	598.0	598.5	598.5
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1235.3	1238.4	1235.7	1239.3	1235.7	1238.4	1235.3	1238.0	1241.9	1239.3	1245.4
5°	1138.6	1133.6	1136.9	1134.7	1136.9	1133.6	1138.6	1141.3	1147.9	1150.1	1154.5
7.5°	1049.2	1044.5	1039.0	1036.5	1039.0	1044.5	1049.2	1050.8	1056.5	1064.7	1071.0
10°	993.3	987.2	986.7	982.8	986.7	987.2	993.3	999.3	1003.1	1013.7	1020.8
12.5°	952.4	946.7	940.4	938.8	940.4	946.7	952.4	957.5	958.7	970.5	975.4
15°	894.2	889.8	886.0	889.2	886.0	889.8	894.2	897.5	903.6	911.8	917.3
17.5°	845.9	842.3	841.6	837.6	841.6	842.3	845.9	847.7	857.7	863.1	872.5
20°	815.5	812.8	813.9	806.7	813.9	812.8	815.5	820.5	830.4	833.2	843.0
22.5°	791.3	785.9	785.3	783.8	785.3	785.9	791.3	795.8	797.8	806.2	813.1
25°	753.3	750.6	747.9	750.6	747.9	750.6	753.3	758.3	760.5	766.5	773.1
27.5°	720.2	716.9	716.2	716.5	716.2	716.9	720.2	719.7	725.7	730.6	735.4
30°	699.9	694.5	695.0	694.5	695.0	694.5	699.9	699.9	703.3	707.7	712.1
32.5°	677.9	674.2	673.4	672.5	673.4	674.2	677.9	677.1	681.3	686.6	691.4
35°	645.5	645.5	642.7	642.7	642.7	645.5	645.5	647.1	651.5	651.5	657.0
37.5°	615.0	614.4	612.8	613.0	612.8	614.4	615.0	616.3	617.8	620.2	623.7
40°	592.1	591.6	589.9	586.6	589.9	591.6	592.1	594.3	595.4	598.2	600.4
42.5°	570.1	568.3	567.4	566.4	567.4	568.3	570.1	571.4	572.1	575.7	580.1
45°	535.4	535.4	534.3	533.8	534.3	535.4	535.4	535.4	536.0	540.4	542.6
47.5°	501.7	502.7	504.8	504.5	504.8	502.7	501.7	500.8	501.1	503.3	505.8
50°	481.5	482.1	483.7	484.3	483.7	482.1	481.5	479.3	478.2	478.2	479.9
52.5°	459.0	462.3	464.3	464.0	464.3	462.3	459.0	457.3	455.3	452.7	455.2
55°	427.5	431.5	435.3	435.9	435.3	431.5	427.5	422.7	420.4	416.0	417.7
57.5°	396.4	401.8	405.9	407.2	405.9	401.8	396.4	390.4	383.4	381.2	378.1
60°	375.3	382.5	387.4	389.6	387.4	382.5	375.3	369.8	360.4	354.4	352.2
62.5°	355.1	363.1	368.0	368.4	368.0	363.1	355.1	346.4	337.1	330.2	325.8
65°	321.9	330.2	334.6	337.9	334.6	330.2	321.9	312.6	302.1	292.8	287.8
67.5°	286.3	294.5	299.4	302.0	299.4	294.5	286.3	274.7	265.1	254.4	248.5
70°	260.3	268.6	275.2	277.4	275.2	268.6	260.3	246.5	238.3	228.4	223.4
72.5°	234.7	242.1	247.4	250.1	247.4	242.1	234.7	221.8	212.3	202.4	195.7
75°	190.4	200.3	205.3	208.0	205.3	200.3	190.4	183.3	172.3	161.8	156.3
77.5°	146.8	155.8	158.8	160.2	158.8	155.8	146.8	138.4	130.1	122.5	117.1
80°	117.7	123.3	127.1	127.7	127.1	123.3	117.7	111.1	104.5	97.4	92.5
82.5°	90.5	95.1	96.3	97.8	96.3	95.1	90.5	84.7	79.0	73.6	69.5
85°	49.5	51.7	52.3	51.7	52.3	51.7	49.5	45.7	42.9	40.2	38.5
87.5°	18.3	17.9	18.0	19.0	18.0	17.9	18.3	17.4	17.8	16.8	15.8
90°	10.3	10.5	10.8	11.2	10.8	10.5	10.3	9.9	9.5	9.0	8.5
92.5°	21.3	21.5	21.7	21.9	21.7	21.5	21.3	21.0	20.6	19.9	19.2
95°	39.4	39.6	39.8	40.0	39.8	39.6	39.4	39.1	38.7	38.0	37.3
97.5°	60.3	60.4	60.5	60.7	60.5	60.4	60.3	60.2	59.8	59.1	58.4
100°	75.7	75.9	76.1	76.3	76.1	75.9	75.7	75.4	74.8	73.9	73.1
102.5°	91.1	91.3	91.6	91.9	91.6	91.3	91.1	90.7	90.1	89.1	88.1
105°	114.4	114.7	115.0	115.4	115.0	114.7	114.4	114.1	113.7	113.0	112.4
107.5°	139.4	139.4	139.3	139.3	139.3	139.4	139.4	139.4	139.3	139.0	138.7
110°	157.5	157.4	157.3	157.2	157.3	157.4	157.5	157.6	157.5	157.2	156.9



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	175.3	175.0	174.9	174.7	174.9	175.0	175.3	175.5	175.5	175.3	175.2
115°	202.6	202.5	202.4	202.4	202.4	202.5	202.6	202.8	202.8	202.9	203.0
117.5°	230.6	230.2	229.8	229.3	229.8	230.2	230.6	231.0	231.1	231.1	231.0
120°	249.2	248.7	248.3	247.9	248.3	248.7	249.2	249.6	249.7	249.7	249.7
122.5°	267.5	267.2	266.8	266.5	266.8	267.2	267.5	267.8	268.1	268.2	268.2
125°	294.7	294.6	294.5	294.4	294.5	294.6	294.7	294.8	295.0	295.2	295.4
127.5°	321.8	321.6	321.4	321.2	321.4	321.6	321.8	322.0	322.2	322.3	322.4
130°	339.7	339.5	339.2	339.1	339.2	339.5	339.7	339.9	340.1	340.1	340.2
132.5°	356.7	356.4	356.1	355.8	356.1	356.4	356.7	356.9	357.2	357.3	357.3
135°	383.1	382.7	382.3	381.9	382.3	382.7	383.1	383.5	383.7	383.7	383.7
137.5°	408.9	408.4	407.9	407.3	407.9	408.4	408.9	409.4	409.6	409.4	409.4
140°	425.3	424.8	424.2	423.7	424.2	424.8	425.3	425.7	425.9	425.7	425.5
142.5°	440.9	440.3	439.9	439.4	439.9	440.3	440.9	441.4	441.6	441.5	441.3
145°	463.7	463.4	463.1	462.8	463.1	463.4	463.7	464.0	464.1	464.1	464.1
147.5°	484.9	484.2	483.5	482.8	483.5	484.2	484.9	485.6	485.8	485.6	485.3
150°	498.3	498.1	497.9	497.7	497.9	498.1	498.3	498.5	498.6	498.6	498.6
152.5°	511.0	510.7	510.3	510.0	510.3	510.7	511.0	511.4	511.5	511.3	511.0
155°	529.0	528.5	527.9	527.4	527.9	528.5	529.0	529.5	529.5	529.1	528.7
157.5°	544.0	543.4	542.7	542.0	542.7	543.4	544.0	544.8	544.9	544.5	544.0
160°	553.7	553.1	552.6	552.1	552.6	553.1	553.7	554.2	554.2	553.8	553.3
162.5°	562.5	561.8	561.3	560.6	561.3	561.8	562.5	563.0	563.1	562.6	562.1
165°	574.0	573.3	572.7	572.1	572.7	573.3	574.0	574.5	574.7	574.2	573.8
167.5°	583.1	582.4	581.8	581.2	581.8	582.4	583.1	583.8	583.8	583.2	582.5
170°	588.2	587.5	586.8	586.0	586.8	587.5	588.2	588.9	589.0	588.3	587.7
172.5°	592.1	591.4	590.8	590.1	590.8	591.4	592.1	592.7	592.7	592.1	591.5
175°	596.1	595.4	594.7	593.9	594.7	595.4	596.1	596.8	596.9	596.2	595.7
177.5°	597.9	597.4	596.7	596.1	596.7	597.4	597.9	598.5	598.5	598.0	597.5
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1239.7	1245.0	1251.6	1256.4	1265.2	1269.2	1274.0	1278.0	1285.0	1291.6	1299.6
5°	1156.2	1165.5	1178.2	1191.9	1207.9	1218.9	1234.3	1243.7	1262.3	1279.4	1295.9
7.5°	1080.4	1091.8	1109.8	1127.4	1148.3	1167.3	1186.5	1207.9	1231.8	1260.0	1283.3
10°	1028.5	1043.9	1063.2	1085.2	1110.5	1132.5	1158.4	1181.5	1210.6	1243.7	1274.5
12.5°	987.1	1000.3	1021.7	1042.9	1070.0	1096.8	1123.6	1154.1	1188.2	1224.7	1263.5
15°	930.0	941.0	958.6	987.7	1015.3	1041.7	1081.9	1110.5	1153.4	1194.1	1240.9
17.5°	881.3	894.9	909.7	934.7	963.2	996.2	1032.1	1068.0	1109.4	1161.0	1213.7
20°	851.3	862.3	879.4	898.6	928.9	961.9	996.1	1032.3	1083.0	1136.4	1193.0
22.5°	818.7	830.6	849.9	870.9	896.3	928.0	965.6	1005.5	1058.3	1110.8	1172.3
25°	780.3	788.6	806.2	824.9	850.2	877.2	916.2	960.3	1012.5	1072.5	1135.2
27.5°	744.1	751.4	767.4	783.7	806.6	838.6	873.5	918.0	967.3	1028.0	1097.6
30°	718.1	725.9	740.1	757.7	779.8	807.8	843.6	885.4	938.2	997.7	1070.3
32.5°	695.7	702.5	713.3	730.9	752.4	779.7	812.8	855.5	908.3	968.6	1039.9
35°	660.9	668.6	676.9	690.6	709.3	735.7	772.1	812.2	862.8	921.2	986.7
37.5°	626.3	634.7	642.0	654.4	671.5	694.8	726.2	768.0	813.8	870.0	932.9
40°	604.8	611.4	617.4	630.6	647.7	669.7	698.9	736.3	784.7	837.0	889.2
42.5°	583.2	589.4	594.5	606.0	621.7	642.9	670.7	707.2	752.1	800.9	847.0
45°	549.2	553.0	559.1	569.0	581.6	600.9	627.9	660.3	698.3	744.5	779.2
47.5°	512.4	518.4	523.4	532.1	542.5	561.4	587.3	614.9	649.3	683.7	708.1
50°	484.3	490.3	497.5	505.7	515.6	533.2	556.9	585.0	614.1	640.5	661.5
52.5°	457.9	463.4	471.1	478.8	491.0	505.9	526.1	551.1	579.8	598.7	616.1
55°	418.7	421.5	430.3	438.1	449.6	460.6	480.9	503.0	520.6	534.9	549.2
57.5°	378.8	382.5	387.6	394.5	406.0	418.9	433.2	452.7	463.0	470.3	481.5
60°	353.3	354.4	357.7	365.9	374.7	386.3	402.8	416.5	424.3	430.3	439.7
62.5°	325.1	325.3	330.8	336.9	343.5	356.0	369.3	380.5	386.9	389.8	398.8
65°	285.6	284.5	287.8	292.8	300.4	308.7	320.2	330.2	329.6	332.9	338.4
67.5°	245.2	244.1	244.1	248.8	255.1	262.5	270.4	276.1	276.2	280.6	283.4
70°	217.9	214.6	216.8	220.7	223.4	229.5	238.3	240.5	241.0	243.2	246.0
72.5°	189.7	188.7	190.4	192.1	194.0	198.7	206.1	207.5	207.6	208.9	213.4
75°	150.7	149.7	148.5	150.3	152.5	155.7	158.5	160.7	160.1	160.7	164.0
77.5°	113.0	110.0	109.4	110.3	110.8	112.8	115.7	115.4	116.0	115.9	119.6
80°	89.7	85.3	84.7	84.7	85.3	86.4	87.5	88.6	86.9	88.6	89.7
82.5°	66.0	63.3	63.2	62.7	62.9	63.0	63.8	64.4	64.1	64.8	65.5
85°	36.3	35.2	33.6	34.7	34.1	32.4	33.6	31.9	31.4	31.9	32.4
87.5°	13.9	14.3	13.2	13.0	12.5	12.8	11.7	11.2	10.5	10.8	12.0
90°	8.0	7.4	6.7	6.0	5.3	4.6	3.8	2.9	2.1	1.3	0.5
92.5°	18.5	17.9	17.0	16.1	15.2	14.3	13.5	13.0	12.4	11.8	11.3
95°	36.5	35.8	34.8	33.8	32.7	31.7	31.1	30.8	30.7	30.4	30.2
97.5°	57.7	57.0	55.6	54.1	52.7	51.3	50.5	50.5	50.4	50.3	50.2
100°	72.1	71.2	69.8	68.5	67.1	65.8	65.1	65.1	65.1	65.1	65.1
102.5°	87.1	86.0	85.4	84.7	84.0	83.3	82.8	82.3	81.9	81.5	81.1
105°	111.8	111.1	110.6	109.9	109.3	108.7	108.1	107.6	107.0	106.6	106.1
107.5°	138.4	138.0	137.5	137.1	136.6	136.2	135.7	135.1	134.6	134.1	133.5
110°	156.6	156.3	156.0	155.6	155.3	155.1	154.7	154.1	153.6	153.0	152.5



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	175.0	174.9	174.5	174.1	173.7	173.3	173.0	172.7	172.4	172.2	171.9
115°	203.2	203.3	203.0	202.8	202.6	202.4	202.1	201.7	201.3	200.9	200.5
117.5°	230.9	230.8	230.6	230.4	230.2	230.1	229.8	229.7	229.5	229.3	229.1
120°	249.7	249.7	249.6	249.6	249.5	249.3	249.1	248.5	248.0	247.5	247.0
122.5°	268.3	268.4	268.1	267.8	267.6	267.3	267.1	266.8	266.7	266.5	266.4
125°	295.6	295.8	295.7	295.6	295.5	295.4	295.1	294.4	293.8	293.2	292.5
127.5°	322.5	322.6	322.5	322.4	322.2	322.1	321.9	321.5	321.1	320.8	320.5
130°	340.4	340.5	340.2	340.1	339.8	339.7	339.2	338.8	338.3	337.7	337.2
132.5°	357.5	357.6	357.6	357.7	357.7	357.8	357.3	356.4	355.6	354.8	353.9
135°	383.7	383.7	383.6	383.5	383.4	383.3	382.9	382.3	381.7	381.1	380.4
137.5°	409.2	409.1	408.9	408.6	408.5	408.2	407.8	407.2	406.6	406.0	405.4
140°	425.3	425.1	424.8	424.5	424.2	423.9	423.5	422.9	422.4	421.9	421.3
142.5°	441.2	441.1	440.8	440.3	439.9	439.5	439.1	438.7	438.2	437.8	437.4
145°	464.1	464.1	463.9	463.6	463.3	462.9	462.6	462.2	461.8	461.3	460.9
147.5°	485.1	484.9	484.6	484.4	484.0	483.8	483.6	483.4	483.1	482.9	482.7
150°	498.6	498.6	498.1	497.7	497.3	496.9	496.8	496.9	497.0	497.1	497.2
152.5°	510.8	510.5	510.3	510.1	510.0	509.8	509.6	509.6	509.4	509.2	509.1
155°	528.3	527.9	527.8	527.7	527.6	527.5	527.4	527.4	527.4	527.4	527.4
157.5°	543.6	543.2	543.2	543.1	542.9	542.8	542.9	543.2	543.3	543.6	543.8
160°	552.9	552.5	552.4	552.4	552.2	552.1	552.2	552.5	552.9	553.2	553.5
162.5°	561.6	561.1	561.1	561.1	561.0	561.0	561.1	561.3	561.6	561.8	562.1
165°	573.4	573.0	572.9	572.8	572.7	572.6	572.7	572.8	573.1	573.2	573.5
167.5°	581.9	581.3	581.3	581.3	581.3	581.3	581.5	581.9	582.3	582.8	583.2
170°	587.1	586.5	586.5	586.5	586.5	586.5	586.7	587.1	587.5	587.9	588.3
172.5°	590.8	590.2	590.2	590.2	590.2	590.2	590.4	590.8	591.3	591.7	592.1
175°	595.0	594.4	594.4	594.4	594.4	594.4	594.6	595.0	595.4	595.8	596.2
177.5°	597.0	596.6	596.6	596.7	596.8	596.9	597.0	597.5	597.8	598.1	598.4
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7



TEST NUMBER: P333260-930  
 CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1303.5	1309.7	1313.6	1321.1	1327.3	1330.8	1333.9	1336.5	1339.6	1342.2	1349.7
5°	1311.9	1326.2	1338.3	1357.0	1374.1	1387.3	1401.6	1414.2	1424.7	1439.6	1451.1
7.5°	1308.2	1333.7	1360.3	1389.3	1418.9	1446.3	1471.7	1495.3	1516.8	1542.8	1565.5
10°	1304.7	1339.4	1373.5	1412.6	1452.8	1486.9	1518.8	1551.3	1574.9	1607.9	1636.0
12.5°	1302.1	1342.9	1384.1	1431.1	1475.2	1523.4	1565.9	1589.6	1625.5	1652.0	1685.3
15°	1290.9	1344.9	1401.6	1454.4	1517.1	1561.7	1599.1	1645.4	1678.9	1712.5	1748.8
17.5°	1271.1	1332.1	1395.5	1464.8	1524.9	1572.8	1621.1	1665.6	1705.7	1750.7	1795.9
20°	1261.8	1322.9	1395.5	1466.5	1525.4	1575.5	1625.0	1674.0	1718.0	1775.8	1828.1
22.5°	1242.4	1316.3	1383.2	1452.5	1513.0	1567.6	1623.7	1679.3	1737.8	1803.0	1868.6
25°	1207.9	1282.7	1353.7	1422.0	1483.0	1551.3	1611.3	1685.5	1760.4	1846.7	1928.2
27.5°	1172.0	1243.7	1308.7	1374.6	1445.9	1523.1	1600.9	1685.2	1783.1	1892.2	2007.1
30°	1143.0	1210.6	1273.9	1341.6	1415.8	1502.8	1588.1	1688.2	1801.6	1924.4	2060.8
32.5°	1109.1	1171.4	1233.0	1304.6	1385.5	1477.3	1576.7	1686.5	1822.8	1962.2	2102.7
35°	1051.1	1103.3	1166.6	1243.1	1334.5	1439.6	1554.5	1684.4	1840.7	2000.8	2119.1
37.5°	982.3	1030.9	1097.6	1181.5	1277.2	1390.0	1526.5	1680.6	1846.6	1974.2	2012.4
40°	936.0	981.1	1050.5	1137.4	1235.4	1354.8	1504.5	1667.4	1828.1	1909.5	1878.1
42.5°	886.7	934.1	1001.6	1087.7	1193.1	1323.1	1476.8	1639.6	1774.3	1805.2	1696.7
45°	808.9	857.9	924.5	1011.5	1124.8	1265.7	1425.8	1573.9	1651.4	1595.9	1428.0
47.5°	736.6	782.5	844.2	933.9	1050.9	1196.6	1350.9	1468.9	1475.1	1342.5	1163.2
50°	687.3	729.7	791.9	881.6	997.7	1145.2	1284.3	1377.4	1335.5	1185.3	1013.1
52.5°	638.9	680.4	741.7	830.5	945.3	1080.4	1210.0	1275.2	1196.5	1042.3	895.1
55°	569.0	605.3	665.3	747.3	856.2	981.7	1091.8	1114.4	1011.9	860.1	740.7
57.5°	500.8	534.7	589.2	664.7	764.3	875.5	961.6	956.8	848.6	718.2	623.5
60°	454.5	487.5	536.0	609.7	700.5	796.3	870.0	852.4	745.1	632.8	553.0
62.5°	413.2	442.6	488.4	552.9	635.8	724.5	785.1	759.0	654.0	555.8	492.8
65°	352.2	376.9	416.0	471.1	539.8	613.0	659.8	626.2	536.5	460.1	409.4
67.5°	294.0	313.8	346.6	390.4	449.1	507.9	536.4	502.6	430.9	375.0	337.5
70°	257.0	274.6	299.9	339.0	390.1	439.7	461.1	430.9	369.2	321.4	294.4
72.5°	220.0	234.6	256.7	291.9	332.9	375.9	394.7	365.7	315.1	274.7	249.5
75°	170.1	179.9	195.3	219.6	252.0	286.2	296.6	271.3	238.8	208.6	192.1
77.5°	121.7	130.1	141.8	157.0	180.0	201.7	210.8	196.2	171.1	152.0	138.4
80°	93.5	97.9	107.9	120.5	138.7	152.5	158.5	149.1	131.5	117.2	106.7
82.5°	66.7	71.1	77.0	87.5	99.1	108.4	114.9	108.6	95.9	84.6	78.6
85°	32.4	35.2	38.5	42.9	51.7	57.2	56.7	52.8	47.9	43.5	40.2
87.5°	11.7	12.3	13.8	16.1	17.6	19.6	20.5	19.8	18.2	17.0	15.8
90°	1.3	2.1	2.9	3.8	4.6	5.3	6.0	6.7	7.4	8.0	8.5
92.5°	11.8	12.4	13.0	13.5	14.3	15.2	16.1	17.0	17.9	18.5	19.2
95°	30.4	30.7	30.8	31.1	31.7	32.7	33.8	34.8	35.8	36.5	37.3
97.5°	50.3	50.4	50.5	50.5	51.3	52.7	54.1	55.6	57.0	57.7	58.4
100°	65.1	65.1	65.1	65.1	65.8	67.1	68.5	69.8	71.2	72.1	73.1
102.5°	81.5	81.9	82.3	82.8	83.3	84.0	84.7	85.4	86.0	87.1	88.1
105°	106.6	107.0	107.6	108.1	108.7	109.3	109.9	110.6	111.1	111.8	112.4
107.5°	134.1	134.6	135.1	135.7	136.2	136.6	137.1	137.5	138.0	138.4	138.7
110°	153.0	153.6	154.1	154.7	155.1	155.3	155.6	156.0	156.3	156.6	156.9





TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	172.2	172.4	172.7	173.0	173.3	173.7	174.1	174.5	174.9	175.0	175.2
115°	200.9	201.3	201.7	202.1	202.4	202.6	202.8	203.0	203.3	203.2	203.0
117.5°	229.3	229.5	229.7	229.8	230.1	230.2	230.4	230.6	230.8	230.9	231.0
120°	247.5	248.0	248.5	249.1	249.3	249.5	249.6	249.6	249.7	249.7	249.7
122.5°	266.5	266.7	266.8	267.1	267.3	267.6	267.8	268.1	268.4	268.3	268.2
125°	293.2	293.8	294.4	295.1	295.4	295.5	295.6	295.7	295.8	295.6	295.4
127.5°	320.8	321.1	321.5	321.9	322.1	322.2	322.4	322.5	322.6	322.5	322.4
130°	337.7	338.3	338.8	339.2	339.7	339.8	340.1	340.2	340.5	340.4	340.2
132.5°	354.8	355.6	356.4	357.3	357.8	357.7	357.7	357.6	357.6	357.5	357.3
135°	381.1	381.7	382.3	382.9	383.3	383.4	383.5	383.6	383.7	383.7	383.7
137.5°	406.0	406.6	407.2	407.8	408.2	408.5	408.6	408.9	409.1	409.2	409.4
140°	421.9	422.4	422.9	423.5	423.9	424.2	424.5	424.8	425.1	425.3	425.5
142.5°	437.8	438.2	438.7	439.1	439.5	439.9	440.3	440.8	441.1	441.2	441.3
145°	461.3	461.8	462.2	462.6	462.9	463.3	463.6	463.9	464.1	464.1	464.1
147.5°	482.9	483.1	483.4	483.6	483.8	484.0	484.4	484.6	484.9	485.1	485.3
150°	497.1	497.0	496.9	496.8	496.9	497.3	497.7	498.1	498.6	498.6	498.6
152.5°	509.2	509.4	509.6	509.6	509.8	510.0	510.1	510.3	510.5	510.8	511.0
155°	527.4	527.4	527.4	527.4	527.5	527.6	527.7	527.8	527.9	528.3	528.7
157.5°	543.6	543.3	543.2	542.9	542.8	542.9	543.1	543.2	543.2	543.6	544.0
160°	553.2	552.9	552.5	552.2	552.1	552.2	552.4	552.4	552.5	552.9	553.3
162.5°	561.8	561.6	561.3	561.1	561.0	561.0	561.1	561.1	561.1	561.6	562.1
165°	573.2	573.1	572.8	572.7	572.6	572.7	572.8	572.9	573.0	573.4	573.8
167.5°	582.8	582.3	581.9	581.5	581.3	581.3	581.3	581.3	581.3	581.9	582.5
170°	587.9	587.5	587.1	586.7	586.5	586.5	586.5	586.5	586.5	587.1	587.7
172.5°	591.7	591.3	590.8	590.4	590.2	590.2	590.2	590.2	590.2	590.8	591.5
175°	595.8	595.4	595.0	594.6	594.4	594.4	594.4	594.4	594.4	595.0	595.7
177.5°	598.1	597.8	597.5	597.0	596.9	596.8	596.7	596.6	596.6	597.0	597.5
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1355.9	1359.4	1366.9	1364.2	1367.8	1369.5	1371.3
5°	1465.4	1483.0	1490.7	1489.6	1501.2	1498.4	1495.7
7.5°	1589.1	1607.6	1618.0	1630.8	1638.3	1638.8	1645.4
10°	1659.1	1683.3	1693.2	1707.0	1715.8	1720.8	1720.2
12.5°	1712.9	1731.8	1754.0	1760.7	1772.6	1778.8	1776.5
15°	1777.4	1807.7	1830.8	1842.3	1857.3	1861.7	1867.7
17.5°	1835.1	1875.7	1902.7	1938.5	1952.1	1960.3	1955.5
20°	1878.7	1932.1	1959.0	2002.0	2025.6	2038.2	2033.8
22.5°	1930.2	1987.9	2037.8	2075.0	2111.0	2128.1	2131.6
25°	2018.4	2097.7	2170.9	2219.9	2264.4	2274.8	2298.0
27.5°	2117.1	2210.5	2288.8	2340.2	2371.3	2383.0	2390.2
30°	2179.1	2272.2	2331.0	2364.0	2373.9	2372.8	2371.7
32.5°	2209.5	2267.8	2279.1	2269.8	2247.1	2228.0	2208.0
35°	2166.5	2123.0	2058.1	1974.4	1912.8	1850.6	1844.5
37.5°	1948.5	1809.5	1701.4	1580.6	1511.0	1467.9	1438.3
40°	1743.3	1585.3	1454.4	1352.6	1281.7	1253.5	1226.0
42.5°	1520.5	1369.7	1253.7	1168.6	1115.2	1084.1	1062.3
45°	1235.4	1102.2	1011.5	949.8	907.4	883.2	869.4
47.5°	1012.3	913.8	836.7	792.2	763.0	744.1	744.2
50°	892.6	798.5	747.3	712.1	686.7	671.9	674.7
52.5°	786.4	716.2	672.5	642.9	624.3	615.1	614.8
55°	657.6	607.0	578.4	556.9	544.2	533.8	536.0
57.5°	562.5	519.8	500.7	482.8	474.0	469.9	463.7
60°	503.5	470.5	454.0	439.7	430.9	427.5	421.5
62.5°	451.1	425.2	409.1	397.4	389.5	388.4	383.7
65°	379.1	359.3	345.0	339.5	331.3	329.1	329.1
67.5°	312.6	298.4	287.2	282.2	278.6	279.1	276.5
70°	270.8	259.2	252.0	246.5	243.8	244.3	242.1
72.5°	236.8	224.0	217.7	214.4	210.8	212.2	211.3
75°	179.4	172.8	169.5	166.2	164.0	162.9	161.8
77.5°	131.8	125.9	123.4	121.5	121.8	119.2	121.3
80°	101.8	96.9	95.2	92.5	91.9	91.9	91.3
82.5°	74.5	71.7	70.5	68.2	67.3	68.2	66.7
85°	38.5	36.3	35.8	35.8	34.7	33.6	36.3
87.5°	15.9	14.3	14.3	13.9	14.0	13.6	12.8
90°	9.0	9.5	9.9	10.3	10.5	10.8	11.2
92.5°	19.9	20.6	21.0	21.3	21.5	21.7	21.9
95°	38.0	38.7	39.1	39.4	39.6	39.8	40.0
97.5°	59.1	59.8	60.2	60.3	60.4	60.5	60.7
100°	73.9	74.8	75.4	75.7	75.9	76.1	76.3
102.5°	89.1	90.1	90.7	91.1	91.3	91.6	91.9
105°	113.0	113.7	114.1	114.4	114.7	115.0	115.4
107.5°	139.0	139.3	139.4	139.4	139.4	139.3	139.3
110°	157.2	157.5	157.6	157.5	157.4	157.3	157.2



TEST NUMBER: P333260-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	175.3	175.5	175.5	175.3	175.0	174.9	174.7
115°	202.9	202.8	202.8	202.6	202.5	202.4	202.4
117.5°	231.1	231.1	231.0	230.6	230.2	229.8	229.3
120°	249.7	249.7	249.6	249.2	248.7	248.3	247.9
122.5°	268.2	268.1	267.8	267.5	267.2	266.8	266.5
125°	295.2	295.0	294.8	294.7	294.6	294.5	294.4
127.5°	322.3	322.2	322.0	321.8	321.6	321.4	321.2
130°	340.1	340.1	339.9	339.7	339.5	339.2	339.1
132.5°	357.3	357.2	356.9	356.7	356.4	356.1	355.8
135°	383.7	383.7	383.5	383.1	382.7	382.3	381.9
137.5°	409.4	409.6	409.4	408.9	408.4	407.9	407.3
140°	425.7	425.9	425.7	425.3	424.8	424.2	423.7
142.5°	441.5	441.6	441.4	440.9	440.3	439.9	439.4
145°	464.1	464.1	464.0	463.7	463.4	463.1	462.8
147.5°	485.6	485.8	485.6	484.9	484.2	483.5	482.8
150°	498.6	498.6	498.5	498.3	498.1	497.9	497.7
152.5°	511.3	511.5	511.4	511.0	510.7	510.3	510.0
155°	529.1	529.5	529.5	529.0	528.5	527.9	527.4
157.5°	544.5	544.9	544.8	544.0	543.4	542.7	542.0
160°	553.8	554.2	554.2	553.7	553.1	552.6	552.1
162.5°	562.6	563.1	563.0	562.5	561.8	561.3	560.6
165°	574.2	574.7	574.5	574.0	573.3	572.7	572.1
167.5°	583.2	583.8	583.8	583.1	582.4	581.8	581.2
170°	588.3	589.0	588.9	588.2	587.5	586.8	586.0
172.5°	592.1	592.7	592.7	592.1	591.4	590.8	590.1
175°	596.2	596.9	596.8	596.1	595.4	594.7	593.9
177.5°	598.0	598.5	598.5	597.9	597.4	596.7	596.1
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7

(END OF REPORT)