

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333240-840

Luminaire Tested: **S125DIP-S850D1035U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333240-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1035U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7202.3 lumens
Efficiency: N/A
Efficacy: 138.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333240-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333240-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	85	89	86	82	79	72	70	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38	34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	28
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	22	19
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19	16
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333240-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	1.7
10°-20°	353.1	4.9
20°-30°	521.3	7.2
30°-40°	608.3	8.4
40°-50°	611.0	8.5
50°-60°	536.3	7.4
60°-70°	399.6	5.5
70°-80°	228.5	3.2
80°-90°	69.3	1.0
90°-100°	362.4	5.0
100°-110°	779.1	10.8
110°-120°	731.2	10.2
120°-130°	592.6	8.2
130°-140°	475.6	6.6
140°-150°	358.9	5.0
150°-160°	252.6	3.5
160°-170°	148.9	2.1
170°-180°	48.4	0.7
0°-30°	999.4	13.9
0°-40°	1607.8	22.3
0°-60°	2755.1	38.3
0°-90°	3452.5	47.9
90°-120°	1872.8	26.0
90°-150°	3299.8	45.8
90°-180°	3750.0	52.1
0°-180°	7202.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	1	9	16	21	23	5
95°	33	98	893	405	237	35
105°	114	159	731	1439	1336	120
115°	204	246	587	1265	1488	200
125°	282	331	562	1006	1172	250
135°	331	398	558	843	974	257
145°	385	441	560	698	768	241
155°	440	473	546	618	644	202
165°	480	493	524	556	564	135
175°	499	499	503	509	507	47
180°	500	500	500	500	500	



TEST NUMBER: P333240-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.8	23.0	23.4	23.8	24.2	24.5	24.6	24.8	24.8	25.0	25.2
90°	1.0	2.0	4.0	6.1	8.1	10.1	11.1	13.1	14.1	16.2	17.2
92.5°	12.3	14.9	23.4	35.9	53.2	82.7	137.7	230.0	330.2	325.0	263.1
95°	33.2	34.2	42.3	53.4	75.6	121.0	228.8	450.6	728.9	893.2	874.0
97.5°	55.2	56.5	62.1	73.2	93.1	125.8	197.2	359.7	650.9	953.9	1105.9
100°	70.6	72.6	76.6	87.7	106.8	137.1	195.6	326.6	580.7	910.3	1162.4
102.5°	87.6	88.7	91.9	103.8	121.4	150.8	202.9	313.0	527.5	833.7	1128.5
105°	113.9	113.9	119.0	129.1	145.2	173.4	217.7	307.5	475.8	730.8	1020.3
107.5°	139.8	141.8	146.5	154.8	171.6	197.0	239.9	316.8	454.0	660.1	909.7
110°	158.2	160.3	164.3	173.4	188.5	214.7	256.1	325.6	447.6	627.0	846.8



TEST NUMBER: P333240-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.8	178.8	182.1	191.2	206.2	231.7	271.4	336.9	447.6	607.7	800.0
115°	203.7	205.6	208.6	217.7	232.9	258.1	295.4	353.9	450.6	586.7	749.0
117.5°	227.8	230.9	234.1	243.2	260.3	284.7	320.0	373.2	457.3	576.4	718.6
120°	244.0	247.0	251.1	260.1	277.2	302.5	337.7	386.1	463.7	571.6	701.7
122.5°	260.9	263.1	266.3	275.4	294.2	319.4	354.7	400.6	469.4	567.5	687.1
125°	282.3	284.3	289.3	298.4	317.6	343.8	377.1	420.4	478.9	562.5	667.4
127.5°	299.0	302.1	308.5	320.0	340.3	366.6	398.6	438.5	489.6	560.1	649.2
130°	309.5	312.6	320.6	333.7	354.9	381.0	412.3	450.6	496.0	558.5	637.1
132.5°	317.6	321.3	331.0	345.8	367.8	393.9	425.3	461.1	503.2	558.5	627.4
135°	330.6	334.7	346.8	362.9	384.1	411.3	442.5	475.8	513.1	558.5	615.9
137.5°	347.2	350.2	361.5	377.7	398.4	426.5	454.8	486.8	522.2	559.7	605.7
140°	356.9	359.9	372.0	388.1	407.3	434.5	463.7	494.0	526.2	560.5	600.9
142.5°	368.2	370.4	381.6	397.8	416.2	441.7	469.4	498.0	528.7	561.3	596.8
145°	385.1	387.1	397.2	411.3	429.5	452.6	478.9	504.0	531.3	560.5	590.8
147.5°	402.8	404.0	412.7	425.9	441.5	461.9	484.9	507.7	532.3	557.8	584.5
150°	413.3	415.4	422.4	435.6	449.6	466.8	489.0	510.1	532.3	555.4	579.7
152.5°	424.6	425.9	432.1	443.5	456.9	472.4	493.0	511.7	531.5	552.3	574.0
155°	439.5	439.5	445.6	455.7	465.7	479.9	497.0	513.1	529.3	546.4	564.5
157.5°	452.8	452.6	457.5	466.2	475.0	485.7	500.4	514.1	526.6	540.4	555.6
160°	461.7	460.7	464.7	471.8	479.9	489.0	502.0	514.1	524.2	536.3	548.5
162.5°	469.0	468.0	472.0	478.3	484.7	492.2	503.6	513.3	521.8	531.5	542.0
165°	479.9	477.9	480.9	485.9	490.0	496.0	504.0	512.1	518.2	524.2	532.3
167.5°	487.2	486.1	488.0	490.8	493.6	497.4	504.0	509.7	512.5	517.2	522.8
170°	492.0	491.0	492.0	494.0	496.0	499.0	504.0	508.1	510.1	513.1	517.2
172.5°	495.2	493.4	494.4	496.3	497.6	499.0	503.2	506.4	506.9	508.3	511.5
175°	499.0	497.0	498.0	499.0	499.0	499.0	502.0	504.0	503.0	503.0	504.0
177.5°	500.8	499.2	499.2	500.0	499.2	499.2	500.8	501.6	500.0	500.0	500.8
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333240-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	25.4	25.7	25.9	26.1	25.7	25.3	25.1	24.7
90°	18.2	19.2	20.2	22.2	22.2	22.2	23.2	23.2
92.5°	178.6	129.7	97.6	82.7	69.8	67.4	65.9	64.3
95°	724.9	571.6	447.6	362.9	291.3	261.2	253.1	236.9
97.5°	1079.5	972.0	851.2	733.5	671.3	614.7	585.5	572.6
100°	1240.0	1190.6	1086.7	981.9	912.3	839.8	802.4	786.4
102.5°	1294.0	1324.4	1274.7	1203.7	1129.3	1077.7	1037.1	1025.0
105°	1262.1	1400.3	1444.6	1433.5	1401.3	1368.1	1347.9	1335.7
107.5°	1148.4	1332.7	1446.6	1499.2	1515.6	1515.4	1508.7	1500.7
110°	1064.6	1256.1	1398.3	1484.0	1529.3	1548.4	1555.5	1555.5



TEST NUMBER: P333240-840

CATALOG NUMBER: S125DIP-S850D1035U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	998.5	1180.3	1324.0	1425.1	1491.4	1524.3	1541.9	1549.0
115°	915.3	1071.7	1209.7	1319.6	1398.3	1446.6	1474.9	1488.0
117.5°	861.7	996.4	1115.4	1216.2	1294.8	1344.8	1372.8	1380.9
120°	832.7	953.7	1064.6	1153.3	1227.9	1276.3	1303.5	1311.6
122.5°	810.9	923.0	1021.8	1104.9	1171.4	1215.8	1243.0	1250.3
125°	779.3	882.1	969.8	1042.4	1098.8	1140.1	1162.4	1172.5
127.5°	747.0	843.0	924.8	992.8	1044.0	1080.5	1101.5	1105.9
130°	726.9	815.6	894.2	959.8	1010.2	1043.4	1063.6	1069.6
132.5°	706.7	789.7	861.1	924.2	974.6	1007.9	1026.4	1033.3
135°	680.4	750.0	814.6	872.0	916.4	949.7	967.8	973.8
137.5°	658.3	714.6	768.2	817.0	856.7	887.0	903.7	910.3
140°	646.2	693.6	739.9	782.3	819.6	845.9	860.9	866.0
142.5°	635.7	675.8	715.8	752.5	784.2	806.3	820.6	824.9
145°	622.0	653.3	684.5	711.8	735.9	753.1	764.2	768.2
147.5°	609.2	634.5	658.5	679.0	698.2	712.0	718.4	720.2
150°	601.9	624.0	643.2	661.4	676.4	688.5	692.6	693.6
152.5°	593.8	613.5	631.1	645.2	657.9	667.6	671.6	672.6
155°	581.7	597.8	612.0	623.0	633.1	640.2	643.2	644.2
157.5°	569.6	582.9	593.8	602.5	610.4	616.1	618.9	618.7
160°	561.5	571.6	581.7	588.8	595.8	600.9	602.9	601.9
162.5°	552.7	561.9	570.4	576.6	582.1	586.3	586.7	586.5
165°	540.4	547.4	553.5	558.5	562.5	564.5	564.5	564.5
167.5°	528.7	533.3	538.0	541.6	543.6	545.4	544.6	544.4
170°	522.2	525.2	528.3	530.3	532.3	533.3	533.3	532.3
172.5°	514.9	518.0	520.2	521.4	521.8	523.6	522.0	521.0
175°	507.1	507.1	509.1	509.1	509.1	510.1	508.1	507.1
177.5°	501.6	502.4	502.4	502.4	501.6	502.4	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0

(END OF REPORT)