

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333266-930

Luminaire Tested: **S125DIP-S1090D590U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333266-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D590U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5289.1 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333266-930
CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333266-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68																												
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	62	57																												
2	93	85	79	73	87	80	75	70	72	67	64	64	61	58	57	54	52	48																												
3	85	75	67	61	80	71	64	58	63	58	53	57	52	49	50	47	44	41																												
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38	35																												
5	71	59	51	44	67	56	48	43	51	44	39	45	40	36	40	36	33	30																												
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29	27																												
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26	24																												
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21																												
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	28	24	21	19																												
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8985	8985	8985
5°	9005	8919	8976
10°	8950	8857	8907
15°	8852	8750	8787
20°	8715	8601	8616
25°	8565	8424	8416
30°	8380	8232	8192
35°	8183	8027	7914
40°	7981	7804	7692
45°	7761	7600	7448
50°	7519	7354	7133
55°	7287	7076	6877
60°	7009	6795	6554
65°	6677	6460	6240
70°	6360	6069	5861
75°	5794	5602	5410
80°	5159	5077	4950
85°	4483	4565	4320



TEST NUMBER: P333266-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.2	2.5
10°-20°	370.5	7.0
20°-30°	547.1	10.3
30°-40°	638.4	12.1
40°-50°	641.2	12.1
50°-60°	562.8	10.6
60°-70°	419.4	7.9
70°-80°	239.8	4.5
80°-90°	71.1	1.3
90°-100°	40.0	0.8
100°-110°	118.2	2.2
110°-120°	200.2	3.8
120°-130°	263.5	5.0
130°-140°	295.3	5.6
140°-150°	289.4	5.5
150°-160°	243.0	4.6
160°-170°	161.6	3.1
170°-180°	56.5	1.1
0°-30°	1048.8	19.8
0°-40°	1687.2	31.9
0°-60°	2891.2	54.7
0°-90°	3621.4	68.5
90°-120°	358.5	6.8
90°-150°	1206.6	22.8
90°-180°	1668.0	31.5
0°-180°	5289.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1389	1386	1376	1385	1385	132
15°	1324	1320	1309	1314	1314	373
25°	1202	1196	1182	1184	1181	553
35°	1038	1033	1018	1012	1004	649
45°	850	845	832	819	816	655
55°	647	643	628	619	611	578
65°	437	434	423	413	408	433
75°	232	230	224	221	217	248
85°	60	62	62	60	58	68
90°	0	4	7	10	11	5
95°	30	31	36	39	40	32
105°	106	108	111	114	115	113
115°	200	202	203	203	202	198
125°	292	295	296	295	294	262
135°	380	383	384	384	382	293
145°	461	463	464	464	463	288
155°	527	527	528	530	527	243
165°	574	573	573	575	572	162
175°	596	594	594	597	594	57
180°	598	598	598	598	598	



TEST NUMBER: P333266-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1394.7	1394.2	1393.5	1392.9	1392.4	1391.1	1389.1	1387.2	1385.2	1383.2	1385.2
5°	1389.0	1388.5	1388.0	1387.6	1387.1	1385.6	1383.2	1380.7	1378.3	1375.8	1378.0
7.5°	1376.2	1375.7	1375.2	1374.8	1374.3	1372.6	1369.9	1367.3	1364.6	1361.9	1364.1
10°	1364.8	1364.3	1363.8	1363.3	1362.9	1361.2	1358.5	1355.8	1353.2	1350.5	1352.4
12.5°	1350.7	1349.8	1348.9	1348.0	1347.2	1345.5	1343.0	1340.5	1338.0	1335.5	1337.1
15°	1324.0	1323.3	1322.6	1321.8	1321.1	1319.4	1316.7	1314.0	1311.3	1308.6	1309.9
17.5°	1293.5	1292.4	1291.3	1290.2	1289.2	1287.2	1284.4	1281.7	1278.9	1276.0	1277.6
20°	1268.0	1267.5	1267.0	1266.5	1266.0	1264.1	1260.9	1257.8	1254.6	1251.4	1253.1
22.5°	1242.4	1241.5	1240.6	1239.7	1238.8	1236.9	1234.0	1230.9	1228.0	1225.0	1226.1
25°	1201.9	1200.7	1199.5	1198.2	1197.0	1194.8	1191.6	1188.5	1185.3	1182.1	1182.6
27.5°	1154.5	1153.8	1153.1	1152.3	1151.6	1149.7	1146.3	1143.0	1139.8	1136.5	1136.6
30°	1123.7	1123.0	1122.3	1121.5	1120.8	1118.6	1114.9	1111.3	1107.6	1103.9	1103.4
32.5°	1090.3	1089.2	1088.0	1086.9	1085.8	1083.6	1080.3	1077.0	1073.7	1070.5	1069.6
35°	1037.9	1036.9	1035.9	1034.9	1034.0	1031.8	1028.3	1024.9	1021.5	1018.1	1016.8
37.5°	983.5	982.3	981.0	979.8	978.6	976.4	973.1	970.0	966.7	963.5	961.6
40°	946.6	945.3	944.1	942.9	941.7	939.3	935.9	932.5	929.0	925.6	923.4
42.5°	906.9	905.9	904.9	903.8	902.8	900.6	897.2	893.7	890.3	886.9	884.8
45°	849.7	848.7	847.7	846.8	845.8	843.8	840.9	838.0	835.0	832.1	829.2
47.5°	788.1	788.1	788.1	788.2	788.2	786.5	783.0	779.4	775.9	772.4	769.4
50°	748.4	747.7	747.0	746.2	745.5	743.6	740.7	737.8	734.8	731.9	728.7
52.5°	707.9	707.4	706.9	706.3	705.8	703.9	700.8	697.7	694.6	691.4	688.6
55°	647.2	646.5	645.7	645.0	644.2	642.1	638.7	635.3	631.9	628.4	626.2
57.5°	583.1	582.7	582.4	582.0	581.6	579.9	577.0	574.1	571.3	568.3	565.5
60°	542.6	541.6	540.6	539.6	538.7	536.9	534.2	531.5	528.8	526.1	523.7
62.5°	500.3	499.5	498.8	498.0	497.3	495.7	493.3	491.1	488.8	486.5	483.8
65°	436.9	436.4	435.9	435.5	435.0	433.4	430.7	428.0	425.3	422.7	420.4
67.5°	375.5	374.5	373.5	372.4	371.5	369.9	367.9	365.9	363.9	361.9	360.0
70°	336.8	335.6	334.4	333.1	331.9	330.2	328.0	325.8	323.6	321.4	319.9
72.5°	294.6	293.7	292.9	292.0	291.2	290.1	288.7	287.2	285.8	284.4	282.7
75°	232.2	231.7	231.2	230.7	230.2	229.4	228.2	227.0	225.8	224.5	223.8
77.5°	174.8	174.6	174.4	174.2	174.0	173.6	172.8	172.2	171.5	170.8	170.4
80°	138.7	138.7	138.7	138.7	138.7	138.4	137.9	137.5	137.0	136.5	136.2
82.5°	107.0	106.6	106.2	105.8	105.4	105.2	105.1	105.0	104.8	104.8	104.4
85°	60.5	60.7	61.0	61.2	61.5	61.6	61.6	61.6	61.6	61.6	61.4
87.5°	23.9	24.1	24.2	24.4	24.5	24.6	24.5	24.5	24.5	24.4	24.5
90°	0.5	1.3	2.1	2.9	3.8	4.6	5.3	6.0	6.7	7.4	8.0
92.5°	11.3	11.8	12.4	13.0	13.5	14.3	15.2	16.1	17.0	17.9	18.5
95°	30.2	30.4	30.7	30.8	31.1	31.7	32.7	33.8	34.8	35.8	36.5
97.5°	50.2	50.3	50.4	50.5	50.5	51.3	52.7	54.1	55.6	57.0	57.7
100°	65.1	65.1	65.1	65.1	65.1	65.8	67.1	68.5	69.8	71.2	72.1
102.5°	81.1	81.5	81.9	82.3	82.8	83.3	84.0	84.7	85.4	86.0	87.1
105°	106.1	106.6	107.0	107.6	108.1	108.7	109.3	109.9	110.6	111.1	111.8
107.5°	133.5	134.1	134.6	135.1	135.7	136.2	136.6	137.1	137.5	138.0	138.4
110°	152.5	153.0	153.6	154.1	154.7	155.1	155.3	155.6	156.0	156.3	156.6



TEST NUMBER: P333266-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.9	172.2	172.4	172.7	173.0	173.3	173.7	174.1	174.5	174.9	175.0
115°	200.5	200.9	201.3	201.7	202.1	202.4	202.6	202.8	203.0	203.3	203.2
117.5°	229.1	229.3	229.5	229.7	229.8	230.1	230.2	230.4	230.6	230.8	230.9
120°	247.0	247.5	248.0	248.5	249.1	249.3	249.5	249.6	249.6	249.7	249.7
122.5°	266.4	266.5	266.7	266.8	267.1	267.3	267.6	267.8	268.1	268.4	268.3
125°	292.5	293.2	293.8	294.4	295.1	295.4	295.5	295.6	295.7	295.8	295.6
127.5°	320.5	320.8	321.1	321.5	321.9	322.1	322.2	322.4	322.5	322.6	322.5
130°	337.2	337.7	338.3	338.8	339.2	339.7	339.8	340.1	340.2	340.5	340.4
132.5°	353.9	354.8	355.6	356.4	357.3	357.8	357.7	357.7	357.6	357.6	357.5
135°	380.4	381.1	381.7	382.3	382.9	383.3	383.4	383.5	383.6	383.7	383.7
137.5°	405.4	406.0	406.6	407.2	407.8	408.2	408.5	408.6	408.9	409.1	409.2
140°	421.3	421.9	422.4	422.9	423.5	423.9	424.2	424.5	424.8	425.1	425.3
142.5°	437.4	437.8	438.2	438.7	439.1	439.5	439.9	440.3	440.8	441.1	441.2
145°	460.9	461.3	461.8	462.2	462.6	462.9	463.3	463.6	463.9	464.1	464.1
147.5°	482.7	482.9	483.1	483.4	483.6	483.8	484.0	484.4	484.6	484.9	485.1
150°	497.2	497.1	497.0	496.9	496.8	496.9	497.3	497.7	498.1	498.6	498.6
152.5°	509.1	509.2	509.4	509.6	509.6	509.8	510.0	510.1	510.3	510.5	510.8
155°	527.4	527.4	527.4	527.4	527.4	527.5	527.6	527.7	527.8	527.9	528.3
157.5°	543.8	543.6	543.3	543.2	542.9	542.8	542.9	543.1	543.2	543.2	543.6
160°	553.5	553.2	552.9	552.5	552.2	552.1	552.2	552.4	552.4	552.5	552.9
162.5°	562.1	561.8	561.6	561.3	561.1	561.0	561.0	561.1	561.1	561.1	561.6
165°	573.5	573.2	573.1	572.8	572.7	572.6	572.7	572.8	572.9	573.0	573.4
167.5°	583.2	582.8	582.3	581.9	581.5	581.3	581.3	581.3	581.3	581.3	581.9
170°	588.3	587.9	587.5	587.1	586.7	586.5	586.5	586.5	586.5	586.5	587.1
172.5°	592.1	591.7	591.3	590.8	590.4	590.2	590.2	590.2	590.2	590.2	590.8
175°	596.2	595.8	595.4	595.0	594.6	594.4	594.4	594.4	594.4	594.4	595.0
177.5°	598.4	598.1	597.8	597.5	597.0	596.9	596.8	596.7	596.6	596.6	597.0
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7



TEST NUMBER: P333266-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1387.2	1389.1	1391.1	1392.0	1391.8	1391.6	1391.4	1391.2
5°	1380.2	1382.4	1384.6	1385.6	1385.4	1385.1	1384.9	1384.6
7.5°	1366.2	1368.4	1370.5	1371.5	1371.3	1371.0	1370.8	1370.5
10°	1354.4	1356.3	1358.3	1359.2	1358.9	1358.7	1358.5	1358.2
12.5°	1338.6	1340.2	1341.7	1342.6	1342.5	1342.4	1342.4	1342.3
15°	1311.1	1312.3	1313.5	1314.2	1314.2	1314.2	1314.2	1314.2
17.5°	1279.1	1280.6	1282.1	1282.3	1281.1	1279.9	1278.6	1277.4
20°	1254.8	1256.5	1258.3	1258.5	1257.3	1256.1	1254.8	1253.6
22.5°	1227.3	1228.4	1229.5	1229.6	1228.8	1228.0	1227.2	1226.3
25°	1183.1	1183.6	1184.1	1183.9	1183.2	1182.4	1181.7	1181.0
27.5°	1136.7	1136.8	1136.9	1136.6	1135.9	1135.1	1134.4	1133.7
30°	1102.9	1102.4	1102.0	1101.4	1100.7	1099.9	1099.2	1098.5
32.5°	1068.7	1067.8	1067.0	1065.8	1064.5	1063.2	1061.8	1060.5
35°	1015.6	1014.4	1013.2	1011.6	1009.7	1007.7	1005.8	1003.8
37.5°	959.9	958.1	956.3	954.8	953.7	952.5	951.4	950.3
40°	921.2	919.0	916.8	915.3	914.6	913.9	913.1	912.4
42.5°	882.9	880.8	878.9	877.3	876.2	875.1	873.9	872.8
45°	826.2	823.3	820.4	818.5	817.7	817.0	816.3	815.5
47.5°	766.5	763.4	760.5	758.1	756.4	754.7	753.0	751.3
50°	725.5	722.4	719.2	716.7	715.0	713.3	711.6	709.9
52.5°	685.8	683.1	680.3	677.9	676.0	674.1	672.2	670.3
55°	624.0	621.8	619.6	617.7	616.0	614.2	612.5	610.8
57.5°	562.7	559.9	557.0	555.1	554.2	553.3	552.4	551.4
60°	521.2	518.8	516.3	514.2	512.5	510.8	509.1	507.4
62.5°	481.2	478.6	475.9	473.9	472.6	471.3	469.9	468.6
65°	418.2	416.0	413.8	412.2	411.2	410.3	409.3	408.3
67.5°	358.2	356.3	354.4	353.2	352.6	352.0	351.5	350.9
70°	318.5	317.0	315.5	314.3	313.3	312.3	311.4	310.4
72.5°	281.1	279.4	277.8	276.5	275.5	274.5	273.5	272.6
75°	223.1	222.3	221.6	220.7	219.7	218.7	217.8	216.8
77.5°	169.9	169.5	169.1	168.5	167.8	167.1	166.4	165.8
80°	136.0	135.7	135.5	135.1	134.6	134.1	133.6	133.1
82.5°	103.9	103.5	103.1	102.7	102.6	102.6	102.5	102.3
85°	61.1	60.9	60.7	60.3	59.8	59.3	58.8	58.3
87.5°	24.6	24.7	24.8	24.7	24.4	24.1	23.7	23.4
90°	8.5	9.0	9.5	9.9	10.3	10.5	10.8	11.2
92.5°	19.2	19.9	20.6	21.0	21.3	21.5	21.7	21.9
95°	37.3	38.0	38.7	39.1	39.4	39.6	39.8	40.0
97.5°	58.4	59.1	59.8	60.2	60.3	60.4	60.5	60.7
100°	73.1	73.9	74.8	75.4	75.7	75.9	76.1	76.3
102.5°	88.1	89.1	90.1	90.7	91.1	91.3	91.6	91.9
105°	112.4	113.0	113.7	114.1	114.4	114.7	115.0	115.4
107.5°	138.7	139.0	139.3	139.4	139.4	139.4	139.3	139.3
110°	156.9	157.2	157.5	157.6	157.5	157.4	157.3	157.2



TEST NUMBER: P333266-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	175.2	175.3	175.5	175.5	175.3	175.0	174.9	174.7
115°	203.0	202.9	202.8	202.8	202.6	202.5	202.4	202.4
117.5°	231.0	231.1	231.1	231.0	230.6	230.2	229.8	229.3
120°	249.7	249.7	249.7	249.6	249.2	248.7	248.3	247.9
122.5°	268.2	268.2	268.1	267.8	267.5	267.2	266.8	266.5
125°	295.4	295.2	295.0	294.8	294.7	294.6	294.5	294.4
127.5°	322.4	322.3	322.2	322.0	321.8	321.6	321.4	321.2
130°	340.2	340.1	340.1	339.9	339.7	339.5	339.2	339.1
132.5°	357.3	357.3	357.2	356.9	356.7	356.4	356.1	355.8
135°	383.7	383.7	383.7	383.5	383.1	382.7	382.3	381.9
137.5°	409.4	409.4	409.6	409.4	408.9	408.4	407.9	407.3
140°	425.5	425.7	425.9	425.7	425.3	424.8	424.2	423.7
142.5°	441.3	441.5	441.6	441.4	440.9	440.3	439.9	439.4
145°	464.1	464.1	464.1	464.0	463.7	463.4	463.1	462.8
147.5°	485.3	485.6	485.8	485.6	484.9	484.2	483.5	482.8
150°	498.6	498.6	498.6	498.5	498.3	498.1	497.9	497.7
152.5°	511.0	511.3	511.5	511.4	511.0	510.7	510.3	510.0
155°	528.7	529.1	529.5	529.5	529.0	528.5	527.9	527.4
157.5°	544.0	544.5	544.9	544.8	544.0	543.4	542.7	542.0
160°	553.3	553.8	554.2	554.2	553.7	553.1	552.6	552.1
162.5°	562.1	562.6	563.1	563.0	562.5	561.8	561.3	560.6
165°	573.8	574.2	574.7	574.5	574.0	573.3	572.7	572.1
167.5°	582.5	583.2	583.8	583.8	583.1	582.4	581.8	581.2
170°	587.7	588.3	589.0	588.9	588.2	587.5	586.8	586.0
172.5°	591.5	592.1	592.7	592.7	592.1	591.4	590.8	590.1
175°	595.7	596.2	596.9	596.8	596.1	595.4	594.7	593.9
177.5°	597.5	598.0	598.5	598.5	597.9	597.4	596.7	596.1
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7

(END OF REPORT)