

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333206-840

Luminaire Tested: **S125DIP-S850D365U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333206-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D365U840-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4767.0 lumens  
Efficiency: N/A  
Efficacy: 136.2 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	99	95	92	98	94	91	88	85	82	80	77	75	73	69	67	66	62
2	94	87	81	75	89	83	77	72	75	71	67	68	64	61	61	58	56	53
3	86	77	69	63	82	73	66	61	66	61	56	60	56	52	54	51	48	45
4	79	68	60	54	75	65	58	52	59	53	48	54	49	45	49	45	42	39
5	73	61	53	46	69	58	51	45	53	47	42	48	43	39	44	40	36	34
6	67	55	46	40	64	52	45	39	48	42	37	44	39	34	40	36	32	30
7	62	50	41	36	59	48	40	35	44	37	33	40	35	31	37	32	29	26
8	58	45	37	32	55	43	36	31	40	34	29	37	31	27	34	29	26	24
9	54	41	34	28	51	40	33	28	37	30	26	34	28	25	31	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	29	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7979	7979	7979	7979
5°	9240	8006	7010	8006
10°	10750	7965	6142	7965
15°	11900	7906	5666	7906
20°	13320	7813	5283	7813
25°	15605	7709	5097	7709
30°	16855	7607	4935	7607
35°	13858	7413	4829	7413
40°	9850	7144	4713	7144
45°	7567	6783	4646	6783
50°	6459	6333	4636	6333
55°	5751	5892	4677	5892
60°	5187	5412	4795	5412
65°	4792	4927	4919	4927
70°	4358	4426	4991	4426
75°	3848	3898	4946	3898
80°	3239	3176	4526	3176
85°	2564	2290	3653	2290



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.9	2.5
10°-20°	354.1	7.4
20°-30°	575.0	12.1
30°-40°	701.4	14.7
40°-50°	638.1	13.4
50°-60°	508.2	10.7
60°-70°	354.0	7.4
70°-80°	188.8	4.0
80°-90°	48.6	1.0
90°-100°	30.7	0.6
100°-110°	90.7	1.9
110°-120°	153.6	3.2
120°-130°	202.2	4.2
130°-140°	226.6	4.8
140°-150°	222.1	4.7
150°-160°	186.5	3.9
160°-170°	124.0	2.6
170°-180°	43.4	0.9
0°-30°	1048.1	22.0
0°-40°	1749.5	36.7
0°-60°	2895.8	60.7
0°-90°	3487.2	73.2
90°-120°	275.1	5.8
90°-150°	925.9	19.4
90°-180°	1280.0	26.9
0°-180°	4767.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1236	1236	1236	1236	1236	
5°	1425	1235	1081	1235	1425	144
15°	1780	1182	847	1182	1780	509
25°	2190	1082	715	1082	2190	1000
35°	1758	940	612	940	1758	1076
45°	828	743	509	743	828	663
55°	511	523	415	523	511	460
65°	314	322	322	322	314	311
75°	154	156	198	156	154	166
85°	35	31	49	31	35	40
90°	9	0	9	0	9	6
95°	31	23	31	23	31	31
105°	89	81	89	81	89	94
115°	155	154	155	154	155	154
125°	226	224	226	224	226	202
135°	293	292	293	292	293	226
145°	355	354	355	354	355	222
155°	405	405	405	405	405	186
165°	439	440	439	440	439	124
175°	456	458	456	458	456	43
180°	459	459	459	459	459	



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1306.8	1305.0	1303.4	1300.0	1302.5	1295.5	1292.0	1286.2	1279.1	1276.6	1273.6
5°	1425.2	1427.8	1430.5	1419.5	1420.6	1413.2	1396.4	1382.8	1371.8	1357.7	1347.7
7.5°	1567.9	1561.7	1561.2	1554.1	1541.8	1532.0	1514.3	1491.9	1470.2	1445.4	1424.9
10°	1639.2	1639.7	1635.0	1626.6	1613.6	1604.1	1581.0	1558.9	1532.3	1500.8	1478.2
12.5°	1692.9	1695.1	1689.1	1677.8	1671.4	1650.2	1632.1	1606.0	1574.2	1549.0	1514.7
15°	1779.8	1773.9	1769.8	1755.7	1744.6	1722.6	1693.7	1666.5	1631.8	1599.8	1567.9
17.5°	1863.4	1868.0	1860.2	1847.2	1813.1	1787.4	1748.7	1711.3	1668.3	1625.4	1587.2
20°	1938.1	1942.3	1930.3	1907.7	1866.8	1841.1	1790.2	1742.0	1692.1	1637.1	1595.2
22.5°	2031.2	2027.9	2011.7	1977.3	1941.9	1894.4	1839.3	1780.6	1718.2	1656.0	1600.2
25°	2189.8	2167.8	2157.8	2115.4	2068.7	1998.9	1923.4	1837.4	1759.8	1677.5	1606.2
27.5°	2277.6	2270.8	2259.7	2230.1	2181.0	2106.5	2017.4	1912.6	1803.1	1699.2	1605.9
30°	2260.1	2261.1	2262.2	2252.7	2221.3	2165.2	2076.6	1963.8	1833.7	1716.8	1608.8
32.5°	2104.1	2123.1	2141.3	2162.9	2171.7	2161.0	2105.5	2003.7	1869.9	1737.0	1607.1
35°	1757.7	1763.5	1822.7	1881.5	1961.2	2023.1	2064.5	2019.4	1906.6	1754.0	1605.1
37.5°	1370.5	1398.9	1439.9	1506.2	1621.2	1724.2	1856.7	1917.6	1881.3	1759.6	1601.4
40°	1168.3	1194.6	1221.2	1288.9	1385.9	1510.8	1661.2	1789.7	1819.6	1742.0	1588.8
42.5°	1012.3	1033.0	1062.7	1113.6	1194.7	1305.1	1449.0	1616.9	1720.2	1690.8	1562.5
45°	828.5	841.6	864.7	905.0	963.8	1050.4	1177.2	1360.8	1520.7	1573.7	1499.8
47.5°	709.1	709.0	727.0	754.9	797.3	870.8	964.6	1108.4	1279.3	1405.6	1399.8
50°	642.9	640.3	654.4	678.5	712.1	760.8	850.5	965.3	1129.5	1272.6	1312.5
52.5°	585.8	586.1	594.8	612.7	640.8	682.5	749.4	852.9	993.2	1140.1	1215.2
55°	510.8	508.7	518.6	530.7	551.1	578.3	626.6	705.8	819.6	964.3	1061.9
57.5°	441.9	447.7	451.7	460.1	477.1	495.3	536.0	594.1	684.4	808.6	911.7
60°	401.6	407.5	410.6	419.0	432.6	448.4	479.8	527.0	603.0	710.0	812.2
62.5°	365.6	370.1	371.1	378.7	389.8	405.2	429.9	469.5	529.6	623.2	723.4
65°	313.6	313.6	315.7	323.6	328.8	342.4	361.3	390.1	438.4	511.3	596.7
67.5°	263.5	266.0	265.4	268.9	273.8	284.3	297.8	321.6	357.4	410.6	479.0
70°	230.8	232.8	232.3	234.9	240.1	247.0	258.0	280.5	306.2	351.8	410.6
72.5°	201.4	202.2	200.9	204.3	207.4	213.4	225.7	237.7	261.8	300.2	348.5
75°	154.2	155.2	156.2	158.3	161.5	164.6	171.0	183.0	198.7	227.6	258.5
77.5°	115.5	113.6	116.1	115.8	117.5	120.0	125.5	131.9	144.8	163.1	187.0
80°	87.1	87.6	87.6	88.1	90.7	92.3	97.0	101.7	111.7	125.3	142.1
82.5°	63.5	64.9	64.1	65.0	67.3	68.4	71.0	74.8	80.7	91.4	103.5
85°	34.6	32.0	33.0	34.1	34.1	34.6	36.7	38.3	41.4	45.6	50.3
87.5°	11.8	12.5	12.9	12.9	13.2	13.2	14.8	14.7	15.9	17.1	18.7
90°	8.6	8.3	8.1	7.9	7.6	7.3	6.9	6.5	6.1	5.8	5.2
92.5°	16.9	16.7	16.5	16.4	16.2	15.8	15.2	14.7	14.2	13.7	13.0
95°	30.7	30.5	30.4	30.2	30.1	29.7	29.2	28.6	28.1	27.5	26.7
97.5°	46.6	46.5	46.4	46.3	46.2	45.8	45.3	44.8	44.3	43.7	42.6
100°	58.6	58.4	58.3	58.1	57.9	57.5	56.8	56.0	55.3	54.6	53.6
102.5°	70.5	70.3	70.1	69.9	69.7	69.2	68.4	67.6	66.9	66.0	65.5
105°	88.6	88.3	88.1	87.8	87.6	87.3	86.7	86.2	85.7	85.3	84.8
107.5°	106.9	106.9	106.9	106.9	107.0	106.8	106.6	106.4	106.1	105.9	105.5
110°	120.7	120.7	120.8	120.9	121.0	120.9	120.7	120.4	120.2	120.0	119.7



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.1	134.2	134.3	134.5	134.6	134.6	134.5	134.4	134.3	134.2	133.9
115°	155.2	155.3	155.4	155.5	155.6	155.6	155.7	155.8	155.9	156.0	155.8
117.5°	175.9	176.3	176.6	176.9	177.2	177.3	177.3	177.2	177.1	177.1	176.9
120°	190.3	190.6	190.9	191.2	191.5	191.7	191.7	191.7	191.7	191.7	191.6
122.5°	204.5	204.8	205.0	205.3	205.5	205.7	205.7	205.8	205.9	205.9	205.7
125°	225.9	226.0	226.1	226.2	226.2	226.4	226.5	226.7	226.8	227.0	226.9
127.5°	246.5	246.6	246.8	247.0	247.1	247.2	247.3	247.4	247.5	247.5	247.5
130°	260.2	260.3	260.5	260.6	260.8	260.9	261.1	261.2	261.2	261.3	261.2
132.5°	273.1	273.3	273.5	273.7	274.0	274.1	274.2	274.3	274.3	274.4	274.5
135°	293.1	293.4	293.7	294.0	294.3	294.5	294.5	294.5	294.5	294.5	294.4
137.5°	312.6	313.0	313.4	313.8	314.2	314.4	314.3	314.2	314.1	314.0	313.8
140°	325.2	325.6	326.0	326.4	326.8	326.9	326.7	326.6	326.4	326.2	326.0
142.5°	337.2	337.6	337.9	338.3	338.7	338.9	338.8	338.7	338.6	338.5	338.2
145°	355.2	355.4	355.6	355.9	356.1	356.2	356.2	356.2	356.2	356.2	356.0
147.5°	370.5	371.0	371.5	372.1	372.6	372.8	372.6	372.4	372.2	372.0	371.8
150°	381.9	382.0	382.2	382.4	382.5	382.6	382.6	382.6	382.6	382.6	382.3
152.5°	391.3	391.6	391.9	392.2	392.4	392.5	392.3	392.1	391.9	391.7	391.6
155°	404.8	405.2	405.6	406.0	406.4	406.4	406.1	405.8	405.5	405.2	405.1
157.5°	416.0	416.5	417.0	417.6	418.1	418.2	417.9	417.5	417.2	416.9	416.8
160°	423.6	424.0	424.4	424.9	425.3	425.3	425.0	424.6	424.3	424.0	423.9
162.5°	430.2	430.7	431.1	431.6	432.1	432.1	431.7	431.3	431.0	430.6	430.6
165°	439.0	439.5	440.0	440.4	440.9	441.0	440.7	440.4	440.1	439.7	439.7
167.5°	446.1	446.5	447.0	447.5	448.0	448.0	447.5	447.1	446.6	446.1	446.1
170°	449.7	450.3	450.8	451.4	451.9	452.0	451.5	451.0	450.6	450.1	450.1
172.5°	452.8	453.3	453.8	454.3	454.8	454.8	454.3	453.9	453.4	452.9	452.9
175°	455.8	456.4	456.9	457.5	458.0	458.1	457.6	457.1	456.7	456.2	456.2
177.5°	457.5	458.0	458.4	458.9	459.3	459.3	459.0	458.6	458.2	457.8	457.9
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1271.1	1268.2	1264.8	1258.9	1251.8	1248.0	1242.1	1238.4	1230.8	1224.6	1217.8
5°	1335.5	1321.9	1309.4	1293.1	1275.3	1263.7	1250.1	1234.9	1219.2	1203.0	1185.1
7.5°	1402.4	1378.3	1352.0	1323.8	1296.3	1270.9	1246.7	1222.8	1200.6	1173.8	1151.0
10°	1447.2	1416.8	1384.3	1346.0	1308.9	1276.4	1243.3	1214.5	1185.1	1153.7	1125.8
12.5°	1492.2	1451.7	1405.7	1363.7	1318.9	1279.7	1240.8	1204.0	1167.1	1132.3	1099.8
15°	1523.9	1488.1	1445.7	1385.9	1335.5	1281.6	1230.2	1182.5	1137.9	1099.1	1058.2
17.5°	1544.7	1498.7	1453.2	1395.8	1329.8	1269.4	1211.2	1156.6	1106.3	1057.1	1017.7
20°	1548.5	1501.3	1453.6	1397.5	1329.8	1260.6	1202.4	1136.8	1082.9	1032.0	983.7
22.5°	1547.2	1493.8	1441.8	1384.0	1318.1	1254.4	1184.0	1117.1	1058.5	1008.5	958.2
25°	1535.4	1478.2	1413.2	1355.0	1290.0	1222.3	1151.0	1081.8	1022.0	964.8	915.0
27.5°	1525.5	1451.4	1377.8	1309.9	1247.1	1185.1	1116.8	1045.9	979.7	921.7	874.7
30°	1513.4	1432.1	1349.2	1278.4	1214.0	1153.7	1089.1	1020.0	950.7	894.0	843.7
32.5°	1502.5	1407.8	1320.3	1243.2	1174.9	1116.3	1056.8	991.0	923.0	865.6	815.2
35°	1481.4	1371.8	1271.6	1184.6	1111.7	1051.4	1001.6	940.2	877.8	822.2	774.0
37.5°	1454.6	1324.5	1217.1	1125.8	1045.9	982.4	936.0	888.9	829.0	775.5	731.8
40°	1433.6	1291.0	1177.2	1083.9	1001.1	934.9	892.0	847.4	797.6	747.8	701.7
42.5°	1407.2	1260.8	1137.0	1036.5	954.4	890.1	845.0	807.1	763.2	716.7	673.9
45°	1358.7	1206.1	1071.9	963.8	880.9	817.5	770.8	742.6	709.5	665.4	629.2
47.5°	1287.3	1140.3	1001.5	890.0	804.5	745.7	702.0	674.8	651.5	618.7	585.9
50°	1223.9	1091.3	950.7	840.0	754.6	695.3	655.0	630.3	610.4	585.2	557.4
52.5°	1153.0	1029.6	900.8	791.4	706.8	648.3	608.8	587.1	570.6	552.5	525.1
55°	1040.4	935.5	816.0	712.1	634.0	576.8	542.2	523.3	509.7	496.0	479.3
57.5°	916.3	834.2	728.3	633.5	561.5	509.5	477.2	458.8	448.3	441.2	431.3
60°	829.0	758.8	667.5	581.0	510.8	464.6	433.1	419.0	410.1	404.2	397.0
62.5°	748.1	690.4	605.8	526.8	465.4	421.8	393.7	380.0	371.4	368.6	362.5
65°	628.7	584.2	514.4	448.9	396.5	359.2	335.6	322.4	317.2	314.1	314.7
67.5°	511.2	484.0	428.0	372.1	330.2	299.0	280.1	270.0	267.4	263.3	263.2
70°	439.4	419.0	371.8	323.1	285.8	261.7	244.9	234.4	231.8	229.6	229.1
72.5°	376.1	358.2	317.2	278.1	244.7	223.5	209.6	203.4	199.0	197.8	197.7
75°	282.7	272.7	240.1	209.2	186.1	171.5	162.1	156.2	153.1	152.6	153.1
77.5°	201.0	192.3	171.6	149.7	135.1	124.0	116.0	114.0	110.5	110.6	110.0
80°	151.0	145.2	132.2	114.8	102.8	93.3	89.2	85.4	84.4	82.8	84.4
82.5°	109.5	103.3	94.4	83.4	73.4	67.8	63.5	62.4	61.8	61.0	61.4
85°	54.0	54.5	49.3	40.9	36.7	33.5	30.9	30.9	30.4	29.9	30.4
87.5°	19.4	18.4	16.7	15.2	13.0	11.6	11.1	11.4	10.3	10.0	10.5
90°	4.6	4.0	3.5	2.9	2.2	1.6	1.0	0.4	1.0	1.6	2.2
92.5°	12.3	11.6	11.0	10.4	10.0	9.5	9.1	8.7	9.1	9.5	10.0
95°	25.9	25.1	24.3	23.8	23.6	23.5	23.3	23.2	23.3	23.5	23.6
97.5°	41.6	40.5	39.4	38.8	38.8	38.7	38.6	38.6	38.6	38.7	38.8
100°	52.5	51.5	50.5	50.0	50.0	50.0	50.0	50.0	50.0	50.0	50.0
102.5°	64.9	64.4	63.9	63.5	63.2	62.9	62.6	62.2	62.6	62.9	63.2
105°	84.3	83.9	83.4	83.0	82.6	82.2	81.8	81.4	81.8	82.2	82.6
107.5°	105.2	104.8	104.5	104.1	103.7	103.3	102.9	102.5	102.9	103.3	103.7
110°	119.5	119.2	119.0	118.7	118.3	117.9	117.4	117.0	117.4	117.9	118.3





TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	133.6	133.3	133.0	132.7	132.5	132.3	132.1	131.9	132.1	132.3	132.5
115°	155.6	155.5	155.3	155.1	154.8	154.5	154.1	153.8	154.1	154.5	154.8
117.5°	176.8	176.7	176.5	176.4	176.2	176.1	175.9	175.8	175.9	176.1	176.2
120°	191.5	191.5	191.4	191.1	190.8	190.4	190.0	189.6	190.0	190.4	190.8
122.5°	205.5	205.3	205.1	204.9	204.8	204.7	204.5	204.4	204.5	204.7	204.8
125°	226.8	226.8	226.7	226.4	225.9	225.5	225.0	224.5	225.0	225.5	225.9
127.5°	247.4	247.3	247.2	247.0	246.7	246.5	246.2	245.9	246.2	246.5	246.7
130°	260.9	260.7	260.6	260.3	259.9	259.5	259.1	258.7	259.1	259.5	259.9
132.5°	274.5	274.5	274.6	274.2	273.6	273.0	272.3	271.7	272.3	273.0	273.6
135°	294.3	294.3	294.2	293.9	293.4	293.0	292.5	292.0	292.5	293.0	293.4
137.5°	313.6	313.5	313.3	313.0	312.5	312.0	311.5	311.1	311.5	312.0	312.5
140°	325.8	325.5	325.3	325.0	324.6	324.2	323.8	323.4	323.8	324.2	324.6
142.5°	337.9	337.6	337.3	337.0	336.7	336.3	336.0	335.7	336.0	336.3	336.7
145°	355.8	355.5	355.3	355.0	354.7	354.4	354.1	353.8	354.1	354.4	354.7
147.5°	371.7	371.5	371.3	371.1	370.9	370.7	370.6	370.4	370.6	370.7	370.9
150°	382.0	381.6	381.3	381.2	381.3	381.4	381.5	381.5	381.5	381.4	381.3
152.5°	391.5	391.4	391.2	391.1	391.0	390.9	390.8	390.7	390.8	390.9	391.0
155°	405.0	404.9	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8
157.5°	416.8	416.7	416.6	416.7	416.8	417.0	417.2	417.3	417.2	417.0	416.8
160°	423.8	423.8	423.7	423.8	424.0	424.2	424.5	424.7	424.5	424.2	424.0
162.5°	430.6	430.5	430.5	430.6	430.8	431.0	431.1	431.3	431.1	431.0	430.8
165°	439.6	439.5	439.4	439.5	439.6	439.8	439.9	440.1	439.9	439.8	439.6
167.5°	446.1	446.1	446.1	446.3	446.6	446.9	447.2	447.5	447.2	446.9	446.6
170°	450.1	450.1	450.1	450.2	450.6	450.9	451.2	451.5	451.2	450.9	450.6
172.5°	452.9	452.9	452.9	453.1	453.4	453.7	454.0	454.3	454.0	453.7	453.4
175°	456.2	456.2	456.2	456.4	456.7	457.0	457.3	457.6	457.3	457.0	456.7
177.5°	458.0	458.0	458.1	458.2	458.5	458.7	459.0	459.2	459.0	458.7	458.5
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1214.1	1209.4	1205.7	1197.3	1192.7	1186.4	1181.3	1186.8	1180.9	1183.5	1179.6
5°	1176.2	1161.5	1151.0	1135.8	1122.7	1110.6	1101.8	1100.1	1095.9	1093.9	1087.5
7.5°	1130.6	1112.3	1094.3	1074.4	1057.5	1040.5	1029.6	1020.6	1014.6	1006.7	1001.4
10°	1103.8	1079.1	1058.2	1034.1	1013.1	994.7	980.1	972.7	965.9	955.9	952.3
12.5°	1070.7	1045.2	1019.6	993.8	973.7	953.2	940.6	929.5	924.8	913.5	912.4
15°	1031.0	992.7	967.5	941.3	913.4	896.7	886.2	874.1	868.9	861.0	855.3
17.5°	983.5	949.4	917.9	890.7	866.9	852.7	839.7	831.4	822.4	817.3	807.9
20°	949.2	916.7	885.1	856.3	838.0	821.7	811.2	803.3	794.0	791.3	781.8
22.5°	920.2	884.3	854.1	829.9	809.8	791.5	780.1	774.9	768.3	760.2	758.3
25°	873.1	835.9	810.2	786.1	768.2	751.4	743.6	736.8	730.4	724.7	722.6
27.5°	832.4	799.1	768.6	746.8	731.3	716.0	709.0	700.7	696.2	691.6	685.9
30°	803.9	769.8	743.1	722.1	705.3	691.7	684.3	678.5	674.4	670.1	667.0
32.5°	774.5	743.0	717.0	696.5	679.7	669.4	662.9	658.8	654.2	649.1	645.2
35°	735.7	701.0	675.9	658.1	645.0	637.1	629.8	626.1	620.9	620.9	616.6
37.5°	692.0	662.1	639.9	623.6	611.9	604.8	596.8	594.3	591.0	588.8	587.3
40°	666.0	638.1	617.2	601.0	588.3	582.6	576.3	572.1	570.0	567.3	566.3
42.5°	639.1	612.6	592.5	577.4	566.5	561.6	555.7	552.8	548.6	545.1	544.5
45°	598.3	572.6	554.3	542.2	532.8	527.0	523.3	517.1	514.9	510.8	510.2
47.5°	559.6	534.9	516.9	507.1	498.8	494.0	488.3	482.0	479.6	477.5	477.3
50°	530.7	508.2	491.3	481.9	474.0	467.3	461.4	457.3	455.7	455.7	456.8
52.5°	501.3	482.1	467.9	456.4	448.9	441.6	436.3	433.7	431.3	433.8	435.8
55°	458.3	438.9	428.4	417.4	410.1	401.6	399.1	398.0	396.5	400.6	402.7
57.5°	412.8	399.2	386.9	376.0	369.4	364.6	361.0	360.3	363.2	365.3	372.1
60°	383.8	368.1	357.1	348.7	340.8	337.7	336.7	335.6	337.7	343.5	352.3
62.5°	351.9	339.2	327.3	321.0	315.3	310.0	309.8	310.4	314.7	321.2	330.1
65°	305.2	294.2	286.3	278.9	274.3	271.1	272.2	274.3	278.9	287.9	297.8
67.5°	257.7	250.1	243.1	237.1	232.6	232.6	233.7	236.8	242.4	252.7	261.8
70°	227.0	218.6	212.9	210.3	206.6	204.5	207.6	212.9	217.6	227.0	234.9
72.5°	196.4	189.3	184.8	183.0	181.5	179.8	180.8	186.4	192.9	202.3	211.5
75°	151.0	148.3	145.2	143.2	141.6	142.6	143.7	149.0	154.2	164.1	174.6
77.5°	110.2	107.4	105.6	105.1	104.2	104.7	107.8	111.6	116.7	124.0	131.9
80°	83.4	82.3	81.3	80.8	80.8	81.3	85.4	88.1	92.8	99.7	105.9
82.5°	60.7	60.1	59.9	59.8	60.2	60.3	62.8	66.2	70.2	75.3	80.8
85°	32.0	30.9	32.5	33.0	32.0	33.5	34.6	36.7	38.3	40.9	43.5
87.5°	11.1	12.0	11.7	12.2	12.3	13.3	12.9	14.7	15.7	16.6	16.2
90°	2.9	3.5	4.0	4.6	5.2	5.8	6.1	6.5	6.9	7.3	7.6
92.5°	10.4	11.0	11.6	12.3	13.0	13.7	14.2	14.7	15.2	15.8	16.2
95°	23.8	24.3	25.1	25.9	26.7	27.5	28.1	28.6	29.2	29.7	30.1
97.5°	38.8	39.4	40.5	41.6	42.6	43.7	44.3	44.8	45.3	45.8	46.2
100°	50.0	50.5	51.5	52.5	53.6	54.6	55.3	56.0	56.8	57.5	57.9
102.5°	63.5	63.9	64.4	64.9	65.5	66.0	66.9	67.6	68.4	69.2	69.7
105°	83.0	83.4	83.9	84.3	84.8	85.3	85.7	86.2	86.7	87.3	87.6
107.5°	104.1	104.5	104.8	105.2	105.5	105.9	106.1	106.4	106.6	106.8	107.0
110°	118.7	119.0	119.2	119.5	119.7	120.0	120.2	120.4	120.7	120.9	121.0



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	132.7	133.0	133.3	133.6	133.9	134.2	134.3	134.4	134.5	134.6	134.6
115°	155.1	155.3	155.5	155.6	155.8	156.0	155.9	155.8	155.7	155.6	155.6
117.5°	176.4	176.5	176.7	176.8	176.9	177.1	177.1	177.2	177.3	177.3	177.2
120°	191.1	191.4	191.5	191.5	191.6	191.7	191.7	191.7	191.7	191.7	191.5
122.5°	204.9	205.1	205.3	205.5	205.7	205.9	205.9	205.8	205.7	205.7	205.5
125°	226.4	226.7	226.8	226.8	226.9	227.0	226.8	226.7	226.5	226.4	226.2
127.5°	247.0	247.2	247.3	247.4	247.5	247.5	247.5	247.4	247.3	247.2	247.1
130°	260.3	260.6	260.7	260.9	261.2	261.3	261.2	261.2	261.1	260.9	260.8
132.5°	274.2	274.6	274.5	274.5	274.5	274.4	274.3	274.3	274.2	274.1	274.0
135°	293.9	294.2	294.3	294.3	294.4	294.5	294.5	294.5	294.5	294.5	294.3
137.5°	313.0	313.3	313.5	313.6	313.8	314.0	314.1	314.2	314.3	314.4	314.2
140°	325.0	325.3	325.5	325.8	326.0	326.2	326.4	326.6	326.7	326.9	326.8
142.5°	337.0	337.3	337.6	337.9	338.2	338.5	338.6	338.7	338.8	338.9	338.7
145°	355.0	355.3	355.5	355.8	356.0	356.2	356.2	356.2	356.2	356.2	356.1
147.5°	371.1	371.3	371.5	371.7	371.8	372.0	372.2	372.4	372.6	372.8	372.6
150°	381.2	381.3	381.6	382.0	382.3	382.6	382.6	382.6	382.6	382.6	382.5
152.5°	391.1	391.2	391.4	391.5	391.6	391.7	391.9	392.1	392.3	392.5	392.4
155°	404.8	404.8	404.9	405.0	405.1	405.2	405.5	405.8	406.1	406.4	406.4
157.5°	416.7	416.6	416.7	416.8	416.8	416.9	417.2	417.5	417.9	418.2	418.1
160°	423.8	423.7	423.8	423.8	423.9	424.0	424.3	424.6	425.0	425.3	425.3
162.5°	430.6	430.5	430.5	430.6	430.6	430.6	431.0	431.3	431.7	432.1	432.1
165°	439.5	439.4	439.5	439.6	439.7	439.7	440.1	440.4	440.7	441.0	440.9
167.5°	446.3	446.1	446.1	446.1	446.1	446.1	446.6	447.1	447.5	448.0	448.0
170°	450.2	450.1	450.1	450.1	450.1	450.1	450.6	451.0	451.5	452.0	451.9
172.5°	453.1	452.9	452.9	452.9	452.9	452.9	453.4	453.9	454.3	454.8	454.8
175°	456.4	456.2	456.2	456.2	456.2	456.2	456.7	457.1	457.6	458.1	458.0
177.5°	458.2	458.1	458.0	458.0	457.9	457.8	458.2	458.6	459.0	459.3	459.3
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1177.1	1180.0	1177.5	1180.9	1177.5	1180.0	1177.1	1179.6	1183.5	1180.9	1186.8
5°	1084.9	1080.3	1083.4	1081.3	1083.4	1080.3	1084.9	1087.5	1093.9	1095.9	1100.1
7.5°	999.8	995.2	990.2	987.7	990.2	995.2	999.8	1001.4	1006.7	1014.6	1020.6
10°	946.5	940.7	940.2	936.5	940.2	940.7	946.5	952.3	955.9	965.9	972.7
12.5°	907.5	902.1	896.2	894.6	896.2	902.1	907.5	912.4	913.5	924.8	929.5
15°	852.1	847.9	844.2	847.4	844.2	847.9	852.1	855.3	861.0	868.9	874.1
17.5°	806.1	802.6	801.9	798.1	801.9	802.6	806.1	807.9	817.3	822.4	831.4
20°	777.1	774.5	775.6	768.7	775.6	774.5	777.1	781.8	791.3	794.0	803.3
22.5°	754.1	748.9	748.3	746.9	748.3	748.9	754.1	758.3	760.2	768.3	774.9
25°	717.9	715.3	712.7	715.3	712.7	715.3	717.9	722.6	724.7	730.4	736.8
27.5°	686.3	683.2	682.5	682.8	682.5	683.2	686.3	685.9	691.6	696.2	700.7
30°	667.0	661.8	662.3	661.8	662.3	661.8	667.0	667.0	670.1	674.4	678.5
32.5°	646.0	642.5	641.8	640.8	641.8	642.5	646.0	645.2	649.1	654.2	658.8
35°	615.1	615.1	612.5	612.5	612.5	615.1	615.1	616.6	620.9	620.9	626.1
37.5°	586.0	585.5	583.9	584.2	583.9	585.5	586.0	587.3	588.8	591.0	594.3
40°	564.2	563.7	562.1	559.0	562.1	563.7	564.2	566.3	567.3	570.0	572.1
42.5°	543.2	541.5	540.8	539.7	540.8	541.5	543.2	544.5	545.1	548.6	552.8
45°	510.2	510.2	509.2	508.7	509.2	510.2	510.2	510.2	510.8	514.9	517.1
47.5°	478.2	479.1	481.1	480.8	481.1	479.1	478.2	477.3	477.5	479.6	482.0
50°	458.8	459.4	460.9	461.4	460.9	459.4	458.8	456.8	455.7	455.7	457.3
52.5°	437.5	440.5	442.4	442.1	442.4	440.5	437.5	435.8	433.8	431.3	433.7
55°	407.5	411.1	414.8	415.4	414.8	411.1	407.5	402.7	400.6	396.5	398.0
57.5°	377.8	382.9	386.8	388.0	386.8	382.9	377.8	372.1	365.3	363.2	360.3
60°	357.6	364.5	369.2	371.2	369.2	364.5	357.6	352.3	343.5	337.7	335.6
62.5°	338.3	346.0	350.7	351.1	350.7	346.0	338.3	330.1	321.2	314.7	310.4
65°	306.8	314.7	318.8	321.9	318.8	314.7	306.8	297.8	287.9	278.9	274.3
67.5°	272.8	280.6	285.3	287.8	285.3	280.6	272.8	261.8	252.7	242.4	236.8
70°	248.0	255.9	262.2	264.3	262.2	255.9	248.0	234.9	227.0	217.6	212.9
72.5°	223.7	230.8	235.8	238.2	235.8	230.8	223.7	211.5	202.3	192.9	186.4
75°	181.5	190.9	195.6	198.2	195.6	190.9	181.5	174.6	164.1	154.2	149.0
77.5°	139.9	148.6	151.4	152.7	151.4	148.6	139.9	131.9	124.0	116.7	111.6
80°	112.2	117.4	121.1	121.7	121.1	117.4	112.2	105.9	99.7	92.8	88.1
82.5°	86.2	90.6	91.8	93.1	91.8	90.6	86.2	80.8	75.3	70.2	66.2
85°	47.2	49.3	49.8	49.3	49.8	49.3	47.2	43.5	40.9	38.3	36.7
87.5°	17.1	16.8	16.8	17.7	16.8	16.8	17.1	16.2	16.6	15.7	14.7
90°	7.9	8.1	8.3	8.6	8.3	8.1	7.9	7.6	7.3	6.9	6.5
92.5°	16.4	16.5	16.7	16.9	16.7	16.5	16.4	16.2	15.8	15.2	14.7
95°	30.2	30.4	30.5	30.7	30.5	30.4	30.2	30.1	29.7	29.2	28.6
97.5°	46.3	46.4	46.5	46.6	46.5	46.4	46.3	46.2	45.8	45.3	44.8
100°	58.1	58.3	58.4	58.6	58.4	58.3	58.1	57.9	57.5	56.8	56.0
102.5°	69.9	70.1	70.3	70.5	70.3	70.1	69.9	69.7	69.2	68.4	67.6
105°	87.8	88.1	88.3	88.6	88.3	88.1	87.8	87.6	87.3	86.7	86.2
107.5°	106.9	106.9	106.9	106.9	106.9	106.9	106.9	107.0	106.8	106.6	106.4
110°	120.9	120.8	120.7	120.7	120.7	120.8	120.9	121.0	120.9	120.7	120.4



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	134.5	134.3	134.2	134.1	134.2	134.3	134.5	134.6	134.6	134.5	134.4
115°	155.5	155.4	155.3	155.2	155.3	155.4	155.5	155.6	155.6	155.7	155.8
117.5°	176.9	176.6	176.3	175.9	176.3	176.6	176.9	177.2	177.3	177.3	177.2
120°	191.2	190.9	190.6	190.3	190.6	190.9	191.2	191.5	191.7	191.7	191.7
122.5°	205.3	205.0	204.8	204.5	204.8	205.0	205.3	205.5	205.7	205.7	205.8
125°	226.2	226.1	226.0	225.9	226.0	226.1	226.2	226.2	226.4	226.5	226.7
127.5°	247.0	246.8	246.6	246.5	246.6	246.8	247.0	247.1	247.2	247.3	247.4
130°	260.6	260.5	260.3	260.2	260.3	260.5	260.6	260.8	260.9	261.1	261.2
132.5°	273.7	273.5	273.3	273.1	273.3	273.5	273.7	274.0	274.1	274.2	274.3
135°	294.0	293.7	293.4	293.1	293.4	293.7	294.0	294.3	294.5	294.5	294.5
137.5°	313.8	313.4	313.0	312.6	313.0	313.4	313.8	314.2	314.4	314.3	314.2
140°	326.4	326.0	325.6	325.2	325.6	326.0	326.4	326.8	326.9	326.7	326.6
142.5°	338.3	337.9	337.6	337.2	337.6	337.9	338.3	338.7	338.9	338.8	338.7
145°	355.9	355.6	355.4	355.2	355.4	355.6	355.9	356.1	356.2	356.2	356.2
147.5°	372.1	371.5	371.0	370.5	371.0	371.5	372.1	372.6	372.8	372.6	372.4
150°	382.4	382.2	382.0	381.9	382.0	382.2	382.4	382.5	382.6	382.6	382.6
152.5°	392.2	391.9	391.6	391.3	391.6	391.9	392.2	392.4	392.5	392.3	392.1
155°	406.0	405.6	405.2	404.8	405.2	405.6	406.0	406.4	406.4	406.1	405.8
157.5°	417.6	417.0	416.5	416.0	416.5	417.0	417.6	418.1	418.2	417.9	417.5
160°	424.9	424.4	424.0	423.6	424.0	424.4	424.9	425.3	425.3	425.0	424.6
162.5°	431.6	431.1	430.7	430.2	430.7	431.1	431.6	432.1	432.1	431.7	431.3
165°	440.4	440.0	439.5	439.0	439.5	440.0	440.4	440.9	441.0	440.7	440.4
167.5°	447.5	447.0	446.5	446.1	446.5	447.0	447.5	448.0	448.0	447.5	447.1
170°	451.4	450.8	450.3	449.7	450.3	450.8	451.4	451.9	452.0	451.5	451.0
172.5°	454.3	453.8	453.3	452.8	453.3	453.8	454.3	454.8	454.8	454.3	453.9
175°	457.5	456.9	456.4	455.8	456.4	456.9	457.5	458.0	458.1	457.6	457.1
177.5°	458.9	458.4	458.0	457.5	458.0	458.4	458.9	459.3	459.3	459.0	458.6
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1181.3	1186.4	1192.7	1197.3	1205.7	1209.4	1214.1	1217.8	1224.6	1230.8	1238.4
5°	1101.8	1110.6	1122.7	1135.8	1151.0	1161.5	1176.2	1185.1	1203.0	1219.2	1234.9
7.5°	1029.6	1040.5	1057.5	1074.4	1094.3	1112.3	1130.6	1151.0	1173.8	1200.6	1222.8
10°	980.1	994.7	1013.1	1034.1	1058.2	1079.1	1103.8	1125.8	1153.7	1185.1	1214.5
12.5°	940.6	953.2	973.7	993.8	1019.6	1045.2	1070.7	1099.8	1132.3	1167.1	1204.0
15°	886.2	896.7	913.4	941.3	967.5	992.7	1031.0	1058.2	1099.1	1137.9	1182.5
17.5°	839.7	852.7	866.9	890.7	917.9	949.4	983.5	1017.7	1057.1	1106.3	1156.6
20°	811.2	821.7	838.0	856.3	885.1	916.7	949.2	983.7	1032.0	1082.9	1136.8
22.5°	780.1	791.5	809.8	829.9	854.1	884.3	920.2	958.2	1008.5	1058.5	1117.1
25°	743.6	751.4	768.2	786.1	810.2	835.9	873.1	915.0	964.8	1022.0	1081.8
27.5°	709.0	716.0	731.3	746.8	768.6	799.1	832.4	874.7	921.7	979.7	1045.9
30°	684.3	691.7	705.3	722.1	743.1	769.8	803.9	843.7	894.0	950.7	1020.0
32.5°	662.9	669.4	679.7	696.5	717.0	743.0	774.5	815.2	865.6	923.0	991.0
35°	629.8	637.1	645.0	658.1	675.9	701.0	735.7	774.0	822.2	877.8	940.2
37.5°	596.8	604.8	611.9	623.6	639.9	662.1	692.0	731.8	775.5	829.0	888.9
40°	576.3	582.6	588.3	601.0	617.2	638.1	666.0	701.7	747.8	797.6	847.4
42.5°	555.7	561.6	566.5	577.4	592.5	612.6	639.1	673.9	716.7	763.2	807.1
45°	523.3	527.0	532.8	542.2	554.3	572.6	598.3	629.2	665.4	709.5	742.6
47.5°	488.3	494.0	498.8	507.1	516.9	534.9	559.6	585.9	618.7	651.5	674.8
50°	461.4	467.3	474.0	481.9	491.3	508.2	530.7	557.4	585.2	610.4	630.3
52.5°	436.3	441.6	448.9	456.4	467.9	482.1	501.3	525.1	552.5	570.6	587.1
55°	399.1	401.6	410.1	417.4	428.4	438.9	458.3	479.3	496.0	509.7	523.3
57.5°	361.0	364.6	369.4	376.0	386.9	399.2	412.8	431.3	441.2	448.3	458.8
60°	336.7	337.7	340.8	348.7	357.1	368.1	383.8	397.0	404.2	410.1	419.0
62.5°	309.8	310.0	315.3	321.0	327.3	339.2	351.9	362.5	368.6	371.4	380.0
65°	272.2	271.1	274.3	278.9	286.3	294.2	305.2	314.7	314.1	317.2	322.4
67.5°	233.7	232.6	232.6	237.1	243.1	250.1	257.7	263.2	263.3	267.4	270.0
70°	207.6	204.5	206.6	210.3	212.9	218.6	227.0	229.1	229.6	231.8	234.4
72.5°	180.8	179.8	181.5	183.0	184.8	189.3	196.4	197.7	197.8	199.0	203.4
75°	143.7	142.6	141.6	143.2	145.2	148.3	151.0	153.1	152.6	153.1	156.2
77.5°	107.8	104.7	104.2	105.1	105.6	107.4	110.2	110.0	110.6	110.5	114.0
80°	85.4	81.3	80.8	80.8	81.3	82.3	83.4	84.4	82.8	84.4	85.4
82.5°	62.8	60.3	60.2	59.8	59.9	60.1	60.7	61.4	61.0	61.8	62.4
85°	34.6	33.5	32.0	33.0	32.5	30.9	32.0	30.4	29.9	30.4	30.9
87.5°	12.9	13.3	12.3	12.2	11.7	12.0	11.1	10.5	10.0	10.3	11.4
90°	6.1	5.8	5.2	4.6	4.0	3.5	2.9	2.2	1.6	1.0	0.4
92.5°	14.2	13.7	13.0	12.3	11.6	11.0	10.4	10.0	9.5	9.1	8.7
95°	28.1	27.5	26.7	25.9	25.1	24.3	23.8	23.6	23.5	23.3	23.2
97.5°	44.3	43.7	42.6	41.6	40.5	39.4	38.8	38.8	38.7	38.6	38.6
100°	55.3	54.6	53.6	52.5	51.5	50.5	50.0	50.0	50.0	50.0	50.0
102.5°	66.9	66.0	65.5	64.9	64.4	63.9	63.5	63.2	62.9	62.6	62.2
105°	85.7	85.3	84.8	84.3	83.9	83.4	83.0	82.6	82.2	81.8	81.4
107.5°	106.1	105.9	105.5	105.2	104.8	104.5	104.1	103.7	103.3	102.9	102.5
110°	120.2	120.0	119.7	119.5	119.2	119.0	118.7	118.3	117.9	117.4	117.0



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	134.3	134.2	133.9	133.6	133.3	133.0	132.7	132.5	132.3	132.1	131.9
115°	155.9	156.0	155.8	155.6	155.5	155.3	155.1	154.8	154.5	154.1	153.8
117.5°	177.1	177.1	176.9	176.8	176.7	176.5	176.4	176.2	176.1	175.9	175.8
120°	191.7	191.7	191.6	191.5	191.5	191.4	191.1	190.8	190.4	190.0	189.6
122.5°	205.9	205.9	205.7	205.5	205.3	205.1	204.9	204.8	204.7	204.5	204.4
125°	226.8	227.0	226.9	226.8	226.8	226.7	226.4	225.9	225.5	225.0	224.5
127.5°	247.5	247.5	247.5	247.4	247.3	247.2	247.0	246.7	246.5	246.2	245.9
130°	261.2	261.3	261.2	260.9	260.7	260.6	260.3	259.9	259.5	259.1	258.7
132.5°	274.3	274.4	274.5	274.5	274.5	274.6	274.2	273.6	273.0	272.3	271.7
135°	294.5	294.5	294.4	294.3	294.3	294.2	293.9	293.4	293.0	292.5	292.0
137.5°	314.1	314.0	313.8	313.6	313.5	313.3	313.0	312.5	312.0	311.5	311.1
140°	326.4	326.2	326.0	325.8	325.5	325.3	325.0	324.6	324.2	323.8	323.4
142.5°	338.6	338.5	338.2	337.9	337.6	337.3	337.0	336.7	336.3	336.0	335.7
145°	356.2	356.2	356.0	355.8	355.5	355.3	355.0	354.7	354.4	354.1	353.8
147.5°	372.2	372.0	371.8	371.7	371.5	371.3	371.1	370.9	370.7	370.6	370.4
150°	382.6	382.6	382.3	382.0	381.6	381.3	381.2	381.3	381.4	381.5	381.5
152.5°	391.9	391.7	391.6	391.5	391.4	391.2	391.1	391.0	390.9	390.8	390.7
155°	405.5	405.2	405.1	405.0	404.9	404.8	404.8	404.8	404.8	404.8	404.8
157.5°	417.2	416.9	416.8	416.8	416.7	416.6	416.7	416.8	417.0	417.2	417.3
160°	424.3	424.0	423.9	423.8	423.8	423.7	423.8	424.0	424.2	424.5	424.7
162.5°	431.0	430.6	430.6	430.6	430.5	430.5	430.6	430.8	431.0	431.1	431.3
165°	440.1	439.7	439.7	439.6	439.5	439.4	439.5	439.6	439.8	439.9	440.1
167.5°	446.6	446.1	446.1	446.1	446.1	446.1	446.3	446.6	446.9	447.2	447.5
170°	450.6	450.1	450.1	450.1	450.1	450.1	450.2	450.6	450.9	451.2	451.5
172.5°	453.4	452.9	452.9	452.9	452.9	452.9	453.1	453.4	453.7	454.0	454.3
175°	456.7	456.2	456.2	456.2	456.2	456.2	456.4	456.7	457.0	457.3	457.6
177.5°	458.2	457.8	457.9	458.0	458.0	458.1	458.2	458.5	458.7	459.0	459.2
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1242.1	1248.0	1251.8	1258.9	1264.8	1268.2	1271.1	1273.6	1276.6	1279.1	1286.2
5°	1250.1	1263.7	1275.3	1293.1	1309.4	1321.9	1335.5	1347.7	1357.7	1371.8	1382.8
7.5°	1246.7	1270.9	1296.3	1323.8	1352.0	1378.3	1402.4	1424.9	1445.4	1470.2	1491.9
10°	1243.3	1276.4	1308.9	1346.0	1384.3	1416.8	1447.2	1478.2	1500.8	1532.3	1558.9
12.5°	1240.8	1279.7	1318.9	1363.7	1405.7	1451.7	1492.2	1514.7	1549.0	1574.2	1606.0
15°	1230.2	1281.6	1335.5	1385.9	1445.7	1488.1	1523.9	1567.9	1599.8	1631.8	1666.5
17.5°	1211.2	1269.4	1329.8	1395.8	1453.2	1498.7	1544.7	1587.2	1625.4	1668.3	1711.3
20°	1202.4	1260.6	1329.8	1397.5	1453.6	1501.3	1548.5	1595.2	1637.1	1692.1	1742.0
22.5°	1184.0	1254.4	1318.1	1384.0	1441.8	1493.8	1547.2	1600.2	1656.0	1718.2	1780.6
25°	1151.0	1222.3	1290.0	1355.0	1413.2	1478.2	1535.4	1606.2	1677.5	1759.8	1837.4
27.5°	1116.8	1185.1	1247.1	1309.9	1377.8	1451.4	1525.5	1605.9	1699.2	1803.1	1912.6
30°	1089.1	1153.7	1214.0	1278.4	1349.2	1432.1	1513.4	1608.8	1716.8	1833.7	1963.8
32.5°	1056.8	1116.3	1174.9	1243.2	1320.3	1407.8	1502.5	1607.1	1737.0	1869.9	2003.7
35°	1001.6	1051.4	1111.7	1184.6	1271.6	1371.8	1481.4	1605.1	1754.0	1906.6	2019.4
37.5°	936.0	982.4	1045.9	1125.8	1217.1	1324.5	1454.6	1601.4	1759.6	1881.3	1917.6
40°	892.0	934.9	1001.1	1083.9	1177.2	1291.0	1433.6	1588.8	1742.0	1819.6	1789.7
42.5°	845.0	890.1	954.4	1036.5	1137.0	1260.8	1407.2	1562.5	1690.8	1720.2	1616.9
45°	770.8	817.5	880.9	963.8	1071.9	1206.1	1358.7	1499.8	1573.7	1520.7	1360.8
47.5°	702.0	745.7	804.5	890.0	1001.5	1140.3	1287.3	1399.8	1405.6	1279.3	1108.4
50°	655.0	695.3	754.6	840.0	950.7	1091.3	1223.9	1312.5	1272.6	1129.5	965.3
52.5°	608.8	648.3	706.8	791.4	900.8	1029.6	1153.0	1215.2	1140.1	993.2	852.9
55°	542.2	576.8	634.0	712.1	816.0	935.5	1040.4	1061.9	964.3	819.6	705.8
57.5°	477.2	509.5	561.5	633.5	728.3	834.2	916.3	911.7	808.6	684.4	594.1
60°	433.1	464.6	510.8	581.0	667.5	758.8	829.0	812.2	710.0	603.0	527.0
62.5°	393.7	421.8	465.4	526.8	605.8	690.4	748.1	723.4	623.2	529.6	469.5
65°	335.6	359.2	396.5	448.9	514.4	584.2	628.7	596.7	511.3	438.4	390.1
67.5°	280.1	299.0	330.2	372.1	428.0	484.0	511.2	479.0	410.6	357.4	321.6
70°	244.9	261.7	285.8	323.1	371.8	419.0	439.4	410.6	351.8	306.2	280.5
72.5°	209.6	223.5	244.7	278.1	317.2	358.2	376.1	348.5	300.2	261.8	237.7
75°	162.1	171.5	186.1	209.2	240.1	272.7	282.7	258.5	227.6	198.7	183.0
77.5°	116.0	124.0	135.1	149.7	171.6	192.3	201.0	187.0	163.1	144.8	131.9
80°	89.2	93.3	102.8	114.8	132.2	145.2	151.0	142.1	125.3	111.7	101.7
82.5°	63.5	67.8	73.4	83.4	94.4	103.3	109.5	103.5	91.4	80.7	74.8
85°	30.9	33.5	36.7	40.9	49.3	54.5	54.0	50.3	45.6	41.4	38.3
87.5°	11.1	11.6	13.0	15.2	16.7	18.4	19.4	18.7	17.1	15.9	14.7
90°	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.2	5.8	6.1	6.5
92.5°	9.1	9.5	10.0	10.4	11.0	11.6	12.3	13.0	13.7	14.2	14.7
95°	23.3	23.5	23.6	23.8	24.3	25.1	25.9	26.7	27.5	28.1	28.6
97.5°	38.6	38.7	38.8	38.8	39.4	40.5	41.6	42.6	43.7	44.3	44.8
100°	50.0	50.0	50.0	50.0	50.5	51.5	52.5	53.6	54.6	55.3	56.0
102.5°	62.6	62.9	63.2	63.5	63.9	64.4	64.9	65.5	66.0	66.9	67.6
105°	81.8	82.2	82.6	83.0	83.4	83.9	84.3	84.8	85.3	85.7	86.2
107.5°	102.9	103.3	103.7	104.1	104.5	104.8	105.2	105.5	105.9	106.1	106.4
110°	117.4	117.9	118.3	118.7	119.0	119.2	119.5	119.7	120.0	120.2	120.4





TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	132.1	132.3	132.5	132.7	133.0	133.3	133.6	133.9	134.2	134.3	134.4
115°	154.1	154.5	154.8	155.1	155.3	155.5	155.6	155.8	156.0	155.9	155.8
117.5°	175.9	176.1	176.2	176.4	176.5	176.7	176.8	176.9	177.1	177.1	177.2
120°	190.0	190.4	190.8	191.1	191.4	191.5	191.5	191.6	191.7	191.7	191.7
122.5°	204.5	204.7	204.8	204.9	205.1	205.3	205.5	205.7	205.9	205.9	205.8
125°	225.0	225.5	225.9	226.4	226.7	226.8	226.8	226.9	227.0	226.8	226.7
127.5°	246.2	246.5	246.7	247.0	247.2	247.3	247.4	247.5	247.5	247.5	247.4
130°	259.1	259.5	259.9	260.3	260.6	260.7	260.9	261.2	261.3	261.2	261.2
132.5°	272.3	273.0	273.6	274.2	274.6	274.5	274.5	274.5	274.4	274.3	274.3
135°	292.5	293.0	293.4	293.9	294.2	294.3	294.3	294.4	294.5	294.5	294.5
137.5°	311.5	312.0	312.5	313.0	313.3	313.5	313.6	313.8	314.0	314.1	314.2
140°	323.8	324.2	324.6	325.0	325.3	325.5	325.8	326.0	326.2	326.4	326.6
142.5°	336.0	336.3	336.7	337.0	337.3	337.6	337.9	338.2	338.5	338.6	338.7
145°	354.1	354.4	354.7	355.0	355.3	355.5	355.8	356.0	356.2	356.2	356.2
147.5°	370.6	370.7	370.9	371.1	371.3	371.5	371.7	371.8	372.0	372.2	372.4
150°	381.5	381.4	381.3	381.2	381.3	381.6	382.0	382.3	382.6	382.6	382.6
152.5°	390.8	390.9	391.0	391.1	391.2	391.4	391.5	391.6	391.7	391.9	392.1
155°	404.8	404.8	404.8	404.8	404.8	404.9	405.0	405.1	405.2	405.5	405.8
157.5°	417.2	417.0	416.8	416.7	416.6	416.7	416.8	416.8	416.9	417.2	417.5
160°	424.5	424.2	424.0	423.8	423.7	423.8	423.8	423.9	424.0	424.3	424.6
162.5°	431.1	431.0	430.8	430.6	430.5	430.5	430.6	430.6	430.6	431.0	431.3
165°	439.9	439.8	439.6	439.5	439.4	439.5	439.6	439.7	439.7	440.1	440.4
167.5°	447.2	446.9	446.6	446.3	446.1	446.1	446.1	446.1	446.1	446.6	447.1
170°	451.2	450.9	450.6	450.2	450.1	450.1	450.1	450.1	450.1	450.6	451.0
172.5°	454.0	453.7	453.4	453.1	452.9	452.9	452.9	452.9	452.9	453.4	453.9
175°	457.3	457.0	456.7	456.4	456.2	456.2	456.2	456.2	456.2	456.7	457.1
177.5°	459.0	458.7	458.5	458.2	458.1	458.0	458.0	457.9	457.8	458.2	458.6
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1292.0	1295.5	1302.5	1300.0	1303.4	1305.0	1306.8
5°	1396.4	1413.2	1420.6	1419.5	1430.5	1427.8	1425.2
7.5°	1514.3	1532.0	1541.8	1554.1	1561.2	1561.7	1567.9
10°	1581.0	1604.1	1613.6	1626.6	1635.0	1639.7	1639.2
12.5°	1632.1	1650.2	1671.4	1677.8	1689.1	1695.1	1692.9
15°	1693.7	1722.6	1744.6	1755.7	1769.8	1773.9	1779.8
17.5°	1748.7	1787.4	1813.1	1847.2	1860.2	1868.0	1863.4
20°	1790.2	1841.1	1866.8	1907.7	1930.3	1942.3	1938.1
22.5°	1839.3	1894.4	1941.9	1977.3	2011.7	2027.9	2031.2
25°	1923.4	1998.9	2068.7	2115.4	2157.8	2167.8	2189.8
27.5°	2017.4	2106.5	2181.0	2230.1	2259.7	2270.8	2277.6
30°	2076.6	2165.2	2221.3	2252.7	2262.2	2261.1	2260.1
32.5°	2105.5	2161.0	2171.7	2162.9	2141.3	2123.1	2104.1
35°	2064.5	2023.1	1961.2	1881.5	1822.7	1763.5	1757.7
37.5°	1856.7	1724.2	1621.2	1506.2	1439.9	1398.9	1370.5
40°	1661.2	1510.8	1385.9	1288.9	1221.2	1194.6	1168.3
42.5°	1449.0	1305.1	1194.7	1113.6	1062.7	1033.0	1012.3
45°	1177.2	1050.4	963.8	905.0	864.7	841.6	828.5
47.5°	964.6	870.8	797.3	754.9	727.0	709.0	709.1
50°	850.5	760.8	712.1	678.5	654.4	640.3	642.9
52.5°	749.4	682.5	640.8	612.7	594.8	586.1	585.8
55°	626.6	578.3	551.1	530.7	518.6	508.7	510.8
57.5°	536.0	495.3	477.1	460.1	451.7	447.7	441.9
60°	479.8	448.4	432.6	419.0	410.6	407.5	401.6
62.5°	429.9	405.2	389.8	378.7	371.1	370.1	365.6
65°	361.3	342.4	328.8	323.6	315.7	313.6	313.6
67.5°	297.8	284.3	273.8	268.9	265.4	266.0	263.5
70°	258.0	247.0	240.1	234.9	232.3	232.8	230.8
72.5°	225.7	213.4	207.4	204.3	200.9	202.2	201.4
75°	171.0	164.6	161.5	158.3	156.2	155.2	154.2
77.5°	125.5	120.0	117.5	115.8	116.1	113.6	115.5
80°	97.0	92.3	90.7	88.1	87.6	87.6	87.1
82.5°	71.0	68.4	67.3	65.0	64.1	64.9	63.5
85°	36.7	34.6	34.1	34.1	33.0	32.0	34.6
87.5°	14.8	13.2	13.2	12.9	12.9	12.5	11.8
90°	6.9	7.3	7.6	7.9	8.1	8.3	8.6
92.5°	15.2	15.8	16.2	16.4	16.5	16.7	16.9
95°	29.2	29.7	30.1	30.2	30.4	30.5	30.7
97.5°	45.3	45.8	46.2	46.3	46.4	46.5	46.6
100°	56.8	57.5	57.9	58.1	58.3	58.4	58.6
102.5°	68.4	69.2	69.7	69.9	70.1	70.3	70.5
105°	86.7	87.3	87.6	87.8	88.1	88.3	88.6
107.5°	106.6	106.8	107.0	106.9	106.9	106.9	106.9
110°	120.7	120.9	121.0	120.9	120.8	120.7	120.7



TEST NUMBER: P333206-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	134.5	134.6	134.6	134.5	134.3	134.2	134.1
115°	155.7	155.6	155.6	155.5	155.4	155.3	155.2
117.5°	177.3	177.3	177.2	176.9	176.6	176.3	175.9
120°	191.7	191.7	191.5	191.2	190.9	190.6	190.3
122.5°	205.7	205.7	205.5	205.3	205.0	204.8	204.5
125°	226.5	226.4	226.2	226.2	226.1	226.0	225.9
127.5°	247.3	247.2	247.1	247.0	246.8	246.6	246.5
130°	261.1	260.9	260.8	260.6	260.5	260.3	260.2
132.5°	274.2	274.1	274.0	273.7	273.5	273.3	273.1
135°	294.5	294.5	294.3	294.0	293.7	293.4	293.1
137.5°	314.3	314.4	314.2	313.8	313.4	313.0	312.6
140°	326.7	326.9	326.8	326.4	326.0	325.6	325.2
142.5°	338.8	338.9	338.7	338.3	337.9	337.6	337.2
145°	356.2	356.2	356.1	355.9	355.6	355.4	355.2
147.5°	372.6	372.8	372.6	372.1	371.5	371.0	370.5
150°	382.6	382.6	382.5	382.4	382.2	382.0	381.9
152.5°	392.3	392.5	392.4	392.2	391.9	391.6	391.3
155°	406.1	406.4	406.4	406.0	405.6	405.2	404.8
157.5°	417.9	418.2	418.1	417.6	417.0	416.5	416.0
160°	425.0	425.3	425.3	424.9	424.4	424.0	423.6
162.5°	431.7	432.1	432.1	431.6	431.1	430.7	430.2
165°	440.7	441.0	440.9	440.4	440.0	439.5	439.0
167.5°	447.5	448.0	448.0	447.5	447.0	446.5	446.1
170°	451.5	452.0	451.9	451.4	450.8	450.3	449.7
172.5°	454.3	454.8	454.8	454.3	453.8	453.3	452.8
175°	457.6	458.1	458.0	457.5	456.9	456.4	455.8
177.5°	459.0	459.3	459.3	458.9	458.4	458.0	457.5
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7

(END OF REPORT)