

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333207-840

Luminaire Tested: **S125DIP-S850D365U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333207-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D365U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4814.7 lumens
Efficiency: N/A
Efficacy: 137.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	66	62
2	94	87	80	75	89	82	77	72	75	70	66	67	64	61	61	58	56	52
3	86	76	69	63	81	73	66	61	66	61	56	60	55	52	54	51	48	44
4	79	68	60	54	75	65	57	52	59	53	48	53	49	45	48	44	41	38
5	73	61	52	46	69	58	50	45	53	47	42	48	43	39	44	39	36	33
6	67	55	46	40	63	52	45	39	48	41	37	44	38	34	40	35	32	29
7	62	50	41	36	59	47	40	35	43	37	32	40	34	30	36	32	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23
9	54	41	34	28	51	40	32	28	36	30	26	34	28	24	31	26	23	21
10	50	38	31	26	48	36	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7979	7979	7979	7979
5°	9240	8006	7010	8006
10°	10750	7965	6142	7965
15°	11900	7906	5666	7906
20°	13320	7813	5283	7813
25°	15605	7709	5097	7709
30°	16855	7607	4935	7607
35°	13858	7413	4829	7413
40°	9850	7144	4713	7144
45°	7567	6783	4646	6783
50°	6459	6333	4636	6333
55°	5751	5892	4677	5892
60°	5187	5412	4795	5412
65°	4792	4927	4919	4927
70°	4358	4426	4991	4426
75°	3848	3898	4946	3898
80°	3239	3176	4526	3176
85°	2564	2290	3653	2290



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.9	2.5
10°-20°	354.1	7.4
20°-30°	575.0	11.9
30°-40°	701.4	14.6
40°-50°	638.1	13.3
50°-60°	508.2	10.6
60°-70°	354.0	7.4
70°-80°	188.8	3.9
80°-90°	48.6	1.0
90°-100°	128.3	2.7
100°-110°	275.8	5.7
110°-120°	258.9	5.4
120°-130°	209.8	4.4
130°-140°	168.4	3.5
140°-150°	127.0	2.6
150°-160°	89.4	1.9
160°-170°	52.7	1.1
170°-180°	17.1	0.4
0°-30°	1048.1	21.8
0°-40°	1749.5	36.3
0°-60°	2895.8	60.1
0°-90°	3487.2	72.4
90°-120°	663.0	13.8
90°-150°	1168.2	24.3
90°-180°	1328.0	27.6
0°-180°	4814.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1236	1236	1236	1236	1236	
5°	1425	1235	1081	1235	1425	144
15°	1780	1182	847	1182	1780	509
25°	2190	1082	715	1082	2190	1000
35°	1758	940	612	940	1758	1076
45°	828	743	509	743	828	663
55°	511	523	415	523	511	460
65°	314	322	322	322	314	311
75°	154	156	198	156	154	166
85°	35	31	49	31	35	40
90°	8	0	8	0	8	7
95°	84	12	84	12	84	119
105°	473	40	473	40	473	470
115°	527	72	527	72	527	515
125°	415	100	415	100	415	376
135°	345	117	345	117	345	267
145°	272	136	272	136	272	173
155°	228	156	228	156	228	106
165°	200	170	200	170	200	57
175°	180	177	180	177	180	17
180°	177	177	177	177	177	



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1306.8	1305.0	1303.4	1300.0	1302.5	1295.5	1292.0	1286.2	1279.1	1276.6	1273.6
5°	1425.2	1427.8	1430.5	1419.5	1420.6	1413.2	1396.4	1382.8	1371.8	1357.7	1347.7
7.5°	1567.9	1561.7	1561.2	1554.1	1541.8	1532.0	1514.3	1491.9	1470.2	1445.4	1424.9
10°	1639.2	1639.7	1635.0	1626.6	1613.6	1604.1	1581.0	1558.9	1532.3	1500.8	1478.2
12.5°	1692.9	1695.1	1689.1	1677.8	1671.4	1650.2	1632.1	1606.0	1574.2	1549.0	1514.7
15°	1779.8	1773.9	1769.8	1755.7	1744.6	1722.6	1693.7	1666.5	1631.8	1599.8	1567.9
17.5°	1863.4	1868.0	1860.2	1847.2	1813.1	1787.4	1748.7	1711.3	1668.3	1625.4	1587.2
20°	1938.1	1942.3	1930.3	1907.7	1866.8	1841.1	1790.2	1742.0	1692.1	1637.1	1595.2
22.5°	2031.2	2027.9	2011.7	1977.3	1941.9	1894.4	1839.3	1780.6	1718.2	1656.0	1600.2
25°	2189.8	2167.8	2157.8	2115.4	2068.7	1998.9	1923.4	1837.4	1759.8	1677.5	1606.2
27.5°	2277.6	2270.8	2259.7	2230.1	2181.0	2106.5	2017.4	1912.6	1803.1	1699.2	1605.9
30°	2260.1	2261.1	2262.2	2252.7	2221.3	2165.2	2076.6	1963.8	1833.7	1716.8	1608.8
32.5°	2104.1	2123.1	2141.3	2162.9	2171.7	2161.0	2105.5	2003.7	1869.9	1737.0	1607.1
35°	1757.7	1763.5	1822.7	1881.5	1961.2	2023.1	2064.5	2019.4	1906.6	1754.0	1605.1
37.5°	1370.5	1398.9	1439.9	1506.2	1621.2	1724.2	1856.7	1917.6	1881.3	1759.6	1601.4
40°	1168.3	1194.6	1221.2	1288.9	1385.9	1510.8	1661.2	1789.7	1819.6	1742.0	1588.8
42.5°	1012.3	1033.0	1062.7	1113.6	1194.7	1305.1	1449.0	1616.9	1720.2	1690.8	1562.5
45°	828.5	841.6	864.7	905.0	963.8	1050.4	1177.2	1360.8	1520.7	1573.7	1499.8
47.5°	709.1	709.0	727.0	754.9	797.3	870.8	964.6	1108.4	1279.3	1405.6	1399.8
50°	642.9	640.3	654.4	678.5	712.1	760.8	850.5	965.3	1129.5	1272.6	1312.5
52.5°	585.8	586.1	594.8	612.7	640.8	682.5	749.4	852.9	993.2	1140.1	1215.2
55°	510.8	508.7	518.6	530.7	551.1	578.3	626.6	705.8	819.6	964.3	1061.9
57.5°	441.9	447.7	451.7	460.1	477.1	495.3	536.0	594.1	684.4	808.6	911.7
60°	401.6	407.5	410.6	419.0	432.6	448.4	479.8	527.0	603.0	710.0	812.2
62.5°	365.6	370.1	371.1	378.7	389.8	405.2	429.9	469.5	529.6	623.2	723.4
65°	313.6	313.6	315.7	323.6	328.8	342.4	361.3	390.1	438.4	511.3	596.7
67.5°	263.5	266.0	265.4	268.9	273.8	284.3	297.8	321.6	357.4	410.6	479.0
70°	230.8	232.8	232.3	234.9	240.1	247.0	258.0	280.5	306.2	351.8	410.6
72.5°	201.4	202.2	200.9	204.3	207.4	213.4	225.7	237.7	261.8	300.2	348.5
75°	154.2	155.2	156.2	158.3	161.5	164.6	171.0	183.0	198.7	227.6	258.5
77.5°	115.5	113.6	116.1	115.8	117.5	120.0	125.5	131.9	144.8	163.1	187.0
80°	87.1	87.6	87.6	88.1	90.7	92.3	97.0	101.7	111.7	125.3	142.1
82.5°	63.5	64.9	64.1	65.0	67.3	68.4	71.0	74.8	80.7	91.4	103.5
85°	34.6	32.0	33.0	34.1	34.1	34.6	36.7	38.3	41.4	45.6	50.3
87.5°	11.7	12.5	12.9	12.9	13.3	13.1	14.7	14.7	15.9	17.1	18.6
90°	8.2	8.2	7.9	7.9	7.9	7.2	6.8	6.5	6.1	5.8	4.9
92.5°	22.7	23.3	23.8	24.7	29.3	34.5	45.8	63.2	93.1	115.0	116.9
95°	83.9	89.6	92.4	103.1	128.5	158.4	202.4	256.6	309.4	316.2	258.0
97.5°	202.7	207.3	217.6	237.6	259.6	301.3	344.2	382.1	391.5	337.7	230.5
100°	278.4	284.1	297.3	323.0	347.6	384.8	421.5	439.0	411.5	322.2	205.6
102.5°	362.9	367.2	381.5	399.8	426.2	451.3	468.9	458.1	399.5	295.2	186.7
105°	472.9	477.2	484.3	496.0	507.6	511.4	495.7	446.9	361.2	258.7	168.4
107.5°	531.3	534.1	536.5	536.5	530.8	512.1	471.8	406.6	322.0	233.7	160.8
110°	550.7	550.7	548.2	541.4	525.3	495.0	444.7	376.9	299.8	222.0	158.4



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	548.5	545.8	539.7	528.0	504.5	468.8	417.9	353.5	283.3	215.1	158.4
115°	526.7	522.1	512.1	495.0	467.2	428.3	379.4	324.1	265.2	207.7	159.6
117.5°	488.9	486.0	476.2	458.4	430.6	394.9	352.7	305.1	254.4	204.1	161.9
120°	464.3	461.5	451.8	434.7	408.3	376.9	337.6	294.8	248.4	202.4	164.2
122.5°	442.6	440.1	430.4	414.8	391.1	361.7	326.8	287.1	243.3	201.0	166.1
125°	415.1	411.5	403.6	389.0	369.0	343.4	312.3	275.9	236.3	199.1	169.6
127.5°	391.5	389.9	382.5	369.6	351.4	327.4	298.4	264.5	229.8	198.3	173.3
130°	378.7	376.6	369.4	357.6	339.8	316.6	288.7	257.3	225.6	197.7	175.6
132.5°	365.8	363.3	356.8	345.1	327.2	304.9	279.6	250.1	222.2	197.7	178.1
135°	344.8	342.6	336.2	324.5	308.7	288.4	265.5	241.0	218.0	197.7	181.7
137.5°	322.2	319.9	314.0	303.3	289.2	272.0	253.0	233.1	214.4	198.1	184.9
140°	306.6	304.8	299.4	290.1	276.9	262.0	245.5	228.7	212.7	198.4	186.3
142.5°	292.1	290.5	285.5	277.6	266.4	253.4	239.2	225.1	211.3	198.7	187.1
145°	272.0	270.5	266.6	260.5	252.0	242.4	231.3	220.3	209.1	198.4	188.0
147.5°	255.0	254.3	252.1	247.2	240.4	233.2	224.6	215.6	206.9	197.5	188.4
150°	245.5	245.2	243.8	239.4	234.1	227.7	221.0	213.1	205.2	196.6	188.4
152.5°	238.1	237.7	236.3	232.9	228.4	223.4	217.2	210.3	203.2	195.5	188.1
155°	228.0	227.7	226.6	224.1	220.6	216.6	211.7	205.9	199.9	193.5	187.3
157.5°	219.0	219.1	218.1	216.1	213.3	210.3	206.3	201.7	196.7	191.3	186.4
160°	213.1	213.4	212.7	211.0	208.4	205.9	202.4	198.8	194.2	189.9	185.6
162.5°	207.6	207.7	207.5	206.1	204.2	202.0	198.9	195.6	191.9	188.1	184.7
165°	199.9	199.9	199.9	199.1	197.7	195.9	193.8	191.3	188.4	185.6	183.5
167.5°	192.7	192.8	193.1	192.5	191.8	190.5	188.8	187.1	185.1	183.1	181.5
170°	188.4	188.8	188.8	188.4	187.7	187.0	185.9	184.9	183.1	181.7	180.6
172.5°	184.4	184.8	185.4	184.7	184.6	184.2	183.4	182.3	181.1	180.0	179.5
175°	179.6	179.9	180.6	180.3	180.3	180.3	179.6	179.6	178.4	178.1	178.1
177.5°	177.0	177.0	177.8	177.6	177.8	177.8	177.8	177.6	177.3	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1271.1	1268.2	1264.8	1258.9	1251.8	1248.0	1242.1	1238.4	1230.8	1224.6	1217.8
5°	1335.5	1321.9	1309.4	1293.1	1275.3	1263.7	1250.1	1234.9	1219.2	1203.0	1185.1
7.5°	1402.4	1378.3	1352.0	1323.8	1296.3	1270.9	1246.7	1222.8	1200.6	1173.8	1151.0
10°	1447.2	1416.8	1384.3	1346.0	1308.9	1276.4	1243.3	1214.5	1185.1	1153.7	1125.8
12.5°	1492.2	1451.7	1405.7	1363.7	1318.9	1279.7	1240.8	1204.0	1167.1	1132.3	1099.8
15°	1523.9	1488.1	1445.7	1385.9	1335.5	1281.6	1230.2	1182.5	1137.9	1099.1	1058.2
17.5°	1544.7	1498.7	1453.2	1395.8	1329.8	1269.4	1211.2	1156.6	1106.3	1057.1	1017.7
20°	1548.5	1501.3	1453.6	1397.5	1329.8	1260.6	1202.4	1136.8	1082.9	1032.0	983.7
22.5°	1547.2	1493.8	1441.8	1384.0	1318.1	1254.4	1184.0	1117.1	1058.5	1008.5	958.2
25°	1535.4	1478.2	1413.2	1355.0	1290.0	1222.3	1151.0	1081.8	1022.0	964.8	915.0
27.5°	1525.5	1451.4	1377.8	1309.9	1247.1	1185.1	1116.8	1045.9	979.7	921.7	874.7
30°	1513.4	1432.1	1349.2	1278.4	1214.0	1153.7	1089.1	1020.0	950.7	894.0	843.7
32.5°	1502.5	1407.8	1320.3	1243.2	1174.9	1116.3	1056.8	991.0	923.0	865.6	815.2
35°	1481.4	1371.8	1271.6	1184.6	1111.7	1051.4	1001.6	940.2	877.8	822.2	774.0
37.5°	1454.6	1324.5	1217.1	1125.8	1045.9	982.4	936.0	888.9	829.0	775.5	731.8
40°	1433.6	1291.0	1177.2	1083.9	1001.1	934.9	892.0	847.4	797.6	747.8	701.7
42.5°	1407.2	1260.8	1137.0	1036.5	954.4	890.1	845.0	807.1	763.2	716.7	673.9
45°	1358.7	1206.1	1071.9	963.8	880.9	817.5	770.8	742.6	709.5	665.4	629.2
47.5°	1287.3	1140.3	1001.5	890.0	804.5	745.7	702.0	674.8	651.5	618.7	585.9
50°	1223.9	1091.3	950.7	840.0	754.6	695.3	655.0	630.3	610.4	585.2	557.4
52.5°	1153.0	1029.6	900.8	791.4	706.8	648.3	608.8	587.1	570.6	552.5	525.1
55°	1040.4	935.5	816.0	712.1	634.0	576.8	542.2	523.3	509.7	496.0	479.3
57.5°	916.3	834.2	728.3	633.5	561.5	509.5	477.2	458.8	448.3	441.2	431.3
60°	829.0	758.8	667.5	581.0	510.8	464.6	433.1	419.0	410.1	404.2	397.0
62.5°	748.1	690.4	605.8	526.8	465.4	421.8	393.7	380.0	371.4	368.6	362.5
65°	628.7	584.2	514.4	448.9	396.5	359.2	335.6	322.4	317.2	314.1	314.7
67.5°	511.2	484.0	428.0	372.1	330.2	299.0	280.1	270.0	267.4	263.3	263.2
70°	439.4	419.0	371.8	323.1	285.8	261.7	244.9	234.4	231.8	229.6	229.1
72.5°	376.1	358.2	317.2	278.1	244.7	223.5	209.6	203.4	199.0	197.8	197.7
75°	282.7	272.7	240.1	209.2	186.1	171.5	162.1	156.2	153.1	152.6	153.1
77.5°	201.0	192.3	171.6	149.7	135.1	124.0	116.0	114.0	110.5	110.6	110.0
80°	151.0	145.2	132.2	114.8	102.8	93.3	89.2	85.4	84.4	82.8	84.4
82.5°	109.5	103.3	94.4	83.4	73.4	67.8	63.5	62.4	61.8	61.0	61.4
85°	54.0	54.5	49.3	40.9	36.7	33.5	30.9	30.9	30.4	29.9	30.4
87.5°	19.4	18.4	16.7	15.2	13.0	11.6	11.0	11.4	10.2	9.9	10.5
90°	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	81.4	48.8	29.3	18.9	12.7	8.3	5.3	4.3	5.3	8.3	12.7
95°	159.6	81.0	42.8	26.8	18.9	14.9	12.1	11.8	12.1	14.9	18.9
97.5°	127.3	69.8	44.5	33.0	26.0	22.0	20.0	19.6	20.0	22.0	26.0
100°	115.6	69.3	48.6	37.9	31.0	27.2	25.7	24.9	25.7	27.2	31.0
102.5°	110.8	71.8	53.4	43.0	36.8	32.5	31.4	31.0	31.4	32.5	36.8
105°	108.9	77.1	61.4	51.4	45.6	42.1	40.3	40.3	40.3	42.1	45.6
107.5°	112.1	84.9	69.8	60.8	54.8	51.9	50.2	49.5	50.2	51.9	54.8
110°	115.3	90.7	76.0	66.8	61.4	58.2	56.8	56.0	56.8	58.2	61.4



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	119.3	96.0	82.0	73.0	67.7	64.4	63.3	62.6	63.3	64.4	67.7
115°	125.2	104.6	91.4	82.4	77.1	73.9	72.8	72.1	72.8	73.9	77.1
117.5°	132.1	113.3	100.8	92.2	86.0	82.9	81.7	80.7	81.7	82.9	86.0
120°	136.7	119.6	107.0	98.2	92.1	88.9	87.5	86.3	87.5	88.9	92.1
122.5°	141.8	125.5	113.1	104.1	97.6	94.3	93.1	92.4	93.1	94.3	97.6
125°	148.9	133.5	121.7	112.4	105.6	102.4	100.7	100.0	100.7	102.4	105.6
127.5°	155.2	141.1	129.8	120.5	113.3	109.2	106.9	105.8	106.9	109.2	113.3
130°	159.6	145.9	134.9	125.6	118.2	113.5	110.7	109.6	110.7	113.5	118.2
132.5°	163.3	150.6	139.5	130.2	122.4	117.2	113.8	112.4	113.8	117.2	122.4
135°	168.4	156.6	145.6	136.0	128.5	122.8	118.5	117.0	118.5	122.8	128.5
137.5°	172.3	161.1	151.0	141.1	133.7	127.9	124.0	122.9	124.0	127.9	133.7
140°	174.9	164.2	153.8	144.2	137.4	131.7	127.4	126.3	127.4	131.7	137.4
142.5°	176.3	166.1	156.4	147.3	140.9	135.1	131.1	130.4	131.1	135.1	140.9
145°	178.4	169.6	160.3	152.1	145.6	140.6	137.0	136.3	137.0	140.6	145.6
147.5°	179.8	171.7	163.5	156.3	150.8	146.1	143.0	142.6	143.0	146.1	150.8
150°	180.6	173.1	165.2	159.2	154.2	149.6	147.0	146.3	147.0	149.6	154.2
152.5°	181.2	174.5	167.2	161.8	157.0	153.0	150.8	150.4	150.8	153.0	157.0
155°	181.7	175.9	169.9	164.9	161.3	157.7	155.6	155.6	155.6	157.7	161.3
157.5°	182.0	177.1	172.0	168.1	165.0	162.0	160.3	160.4	160.3	162.0	165.0
160°	182.0	177.7	173.1	169.9	167.0	164.5	163.1	163.5	163.1	164.5	167.0
162.5°	181.8	178.3	174.2	171.6	169.4	167.1	165.7	166.0	165.7	167.1	169.4
165°	181.3	178.4	175.6	173.5	172.0	170.3	169.2	169.9	169.2	170.3	172.0
167.5°	180.5	178.4	176.1	174.7	173.7	172.8	172.1	172.5	172.1	172.8	173.7
170°	179.9	178.4	176.6	175.6	174.9	174.2	173.8	174.2	173.8	174.2	174.9
172.5°	179.4	178.1	176.6	176.1	175.7	175.0	174.7	175.3	174.7	175.0	175.7
175°	178.4	177.7	176.6	176.6	176.6	176.3	175.9	176.6	175.9	176.3	176.6
177.5°	177.6	177.3	176.7	176.7	177.0	176.7	176.7	177.3	176.7	176.7	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1214.1	1209.4	1205.7	1197.3	1192.7	1186.4	1181.3	1186.8	1180.9	1183.5	1179.6
5°	1176.2	1161.5	1151.0	1135.8	1122.7	1110.6	1101.8	1100.1	1095.9	1093.9	1087.5
7.5°	1130.6	1112.3	1094.3	1074.4	1057.5	1040.5	1029.6	1020.6	1014.6	1006.7	1001.4
10°	1103.8	1079.1	1058.2	1034.1	1013.1	994.7	980.1	972.7	965.9	955.9	952.3
12.5°	1070.7	1045.2	1019.6	993.8	973.7	953.2	940.6	929.5	924.8	913.5	912.4
15°	1031.0	992.7	967.5	941.3	913.4	896.7	886.2	874.1	868.9	861.0	855.3
17.5°	983.5	949.4	917.9	890.7	866.9	852.7	839.7	831.4	822.4	817.3	807.9
20°	949.2	916.7	885.1	856.3	838.0	821.7	811.2	803.3	794.0	791.3	781.8
22.5°	920.2	884.3	854.1	829.9	809.8	791.5	780.1	774.9	768.3	760.2	758.3
25°	873.1	835.9	810.2	786.1	768.2	751.4	743.6	736.8	730.4	724.7	722.6
27.5°	832.4	799.1	768.6	746.8	731.3	716.0	709.0	700.7	696.2	691.6	685.9
30°	803.9	769.8	743.1	722.1	705.3	691.7	684.3	678.5	674.4	670.1	667.0
32.5°	774.5	743.0	717.0	696.5	679.7	669.4	662.9	658.8	654.2	649.1	645.2
35°	735.7	701.0	675.9	658.1	645.0	637.1	629.8	626.1	620.9	620.9	616.6
37.5°	692.0	662.1	639.9	623.6	611.9	604.8	596.8	594.3	591.0	588.8	587.3
40°	666.0	638.1	617.2	601.0	588.3	582.6	576.3	572.1	570.0	567.3	566.3
42.5°	639.1	612.6	592.5	577.4	566.5	561.6	555.7	552.8	548.6	545.1	544.5
45°	598.3	572.6	554.3	542.2	532.8	527.0	523.3	517.1	514.9	510.8	510.2
47.5°	559.6	534.9	516.9	507.1	498.8	494.0	488.3	482.0	479.6	477.5	477.3
50°	530.7	508.2	491.3	481.9	474.0	467.3	461.4	457.3	455.7	455.7	456.8
52.5°	501.3	482.1	467.9	456.4	448.9	441.6	436.3	433.7	431.3	433.8	435.8
55°	458.3	438.9	428.4	417.4	410.1	401.6	399.1	398.0	396.5	400.6	402.7
57.5°	412.8	399.2	386.9	376.0	369.4	364.6	361.0	360.3	363.2	365.3	372.1
60°	383.8	368.1	357.1	348.7	340.8	337.7	336.7	335.6	337.7	343.5	352.3
62.5°	351.9	339.2	327.3	321.0	315.3	310.0	309.8	310.4	314.7	321.2	330.1
65°	305.2	294.2	286.3	278.9	274.3	271.1	272.2	274.3	278.9	287.9	297.8
67.5°	257.7	250.1	243.1	237.1	232.6	232.6	233.7	236.8	242.4	252.7	261.8
70°	227.0	218.6	212.9	210.3	206.6	204.5	207.6	212.9	217.6	227.0	234.9
72.5°	196.4	189.3	184.8	183.0	181.5	179.8	180.8	186.4	192.9	202.3	211.5
75°	151.0	148.3	145.2	143.2	141.6	142.6	143.7	149.0	154.2	164.1	174.6
77.5°	110.2	107.4	105.6	105.1	104.2	104.7	107.8	111.6	116.7	124.0	131.9
80°	83.4	82.3	81.3	80.8	80.8	81.3	85.4	88.1	92.8	99.7	105.9
82.5°	60.7	60.1	59.9	59.8	60.2	60.3	62.8	66.2	70.2	75.3	80.8
85°	32.0	30.9	32.5	33.0	32.0	33.5	34.6	36.7	38.3	40.9	43.5
87.5°	11.1	12.0	11.7	12.2	12.3	13.3	12.9	14.7	15.7	16.6	16.3
90°	2.8	3.5	3.9	4.6	4.9	5.8	6.1	6.5	6.8	7.2	7.9
92.5°	18.9	29.3	48.8	81.4	116.9	115.0	93.1	63.2	45.8	34.5	29.3
95°	26.8	42.8	81.0	159.6	258.0	316.2	309.4	256.6	202.4	158.4	128.5
97.5°	33.0	44.5	69.8	127.3	230.5	337.7	391.5	382.1	344.2	301.3	259.6
100°	37.9	48.6	69.3	115.6	205.6	322.2	411.5	439.0	421.5	384.8	347.6
102.5°	43.0	53.4	71.8	110.8	186.7	295.2	399.5	458.1	468.9	451.3	426.2
105°	51.4	61.4	77.1	108.9	168.4	258.7	361.2	446.9	495.7	511.4	507.6
107.5°	60.8	69.8	84.9	112.1	160.8	233.7	322.0	406.6	471.8	512.1	530.8
110°	66.8	76.0	90.7	115.3	158.4	222.0	299.8	376.9	444.7	495.0	525.3



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	73.0	82.0	96.0	119.3	158.4	215.1	283.3	353.5	417.9	468.8	504.5
115°	82.4	91.4	104.6	125.2	159.6	207.7	265.2	324.1	379.4	428.3	467.2
117.5°	92.2	100.8	113.3	132.1	161.9	204.1	254.4	305.1	352.7	394.9	430.6
120°	98.2	107.0	119.6	136.7	164.2	202.4	248.4	294.8	337.6	376.9	408.3
122.5°	104.1	113.1	125.5	141.8	166.1	201.0	243.3	287.1	326.8	361.7	391.1
125°	112.4	121.7	133.5	148.9	169.6	199.1	236.3	275.9	312.3	343.4	369.0
127.5°	120.5	129.8	141.1	155.2	173.3	198.3	229.8	264.5	298.4	327.4	351.4
130°	125.6	134.9	145.9	159.6	175.6	197.7	225.6	257.3	288.7	316.6	339.8
132.5°	130.2	139.5	150.6	163.3	178.1	197.7	222.2	250.1	279.6	304.9	327.2
135°	136.0	145.6	156.6	168.4	181.7	197.7	218.0	241.0	265.5	288.4	308.7
137.5°	141.1	151.0	161.1	172.3	184.9	198.1	214.4	233.1	253.0	272.0	289.2
140°	144.2	153.8	164.2	174.9	186.3	198.4	212.7	228.7	245.5	262.0	276.9
142.5°	147.3	156.4	166.1	176.3	187.1	198.7	211.3	225.1	239.2	253.4	266.4
145°	152.1	160.3	169.6	178.4	188.0	198.4	209.1	220.3	231.3	242.4	252.0
147.5°	156.3	163.5	171.7	179.8	188.4	197.5	206.9	215.6	224.6	233.2	240.4
150°	159.2	165.2	173.1	180.6	188.4	196.6	205.2	213.1	221.0	227.7	234.1
152.5°	161.8	167.2	174.5	181.2	188.1	195.5	203.2	210.3	217.2	223.4	228.4
155°	164.9	169.9	175.9	181.7	187.3	193.5	199.9	205.9	211.7	216.6	220.6
157.5°	168.1	172.0	177.1	182.0	186.4	191.3	196.7	201.7	206.3	210.3	213.3
160°	169.9	173.1	177.7	182.0	185.6	189.9	194.2	198.8	202.4	205.9	208.4
162.5°	171.6	174.2	178.3	181.8	184.7	188.1	191.9	195.6	198.9	202.0	204.2
165°	173.5	175.6	178.4	181.3	183.5	185.6	188.4	191.3	193.8	195.9	197.7
167.5°	174.7	176.1	178.4	180.5	181.5	183.1	185.1	187.1	188.8	190.5	191.8
170°	175.6	176.6	178.4	179.9	180.6	181.7	183.1	184.9	185.9	187.0	187.7
172.5°	176.1	176.6	178.1	179.4	179.5	180.0	181.1	182.3	183.4	184.2	184.6
175°	176.6	176.6	177.7	178.4	178.1	178.1	178.4	179.6	179.6	180.3	180.3
177.5°	176.7	176.7	177.3	177.6	177.0	177.0	177.3	177.6	177.8	177.8	177.8
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1177.1	1180.0	1177.5	1180.9	1177.5	1180.0	1177.1	1179.6	1183.5	1180.9	1186.8
5°	1084.9	1080.3	1083.4	1081.3	1083.4	1080.3	1084.9	1087.5	1093.9	1095.9	1100.1
7.5°	999.8	995.2	990.2	987.7	990.2	995.2	999.8	1001.4	1006.7	1014.6	1020.6
10°	946.5	940.7	940.2	936.5	940.2	940.7	946.5	952.3	955.9	965.9	972.7
12.5°	907.5	902.1	896.2	894.6	896.2	902.1	907.5	912.4	913.5	924.8	929.5
15°	852.1	847.9	844.2	847.4	844.2	847.9	852.1	855.3	861.0	868.9	874.1
17.5°	806.1	802.6	801.9	798.1	801.9	802.6	806.1	807.9	817.3	822.4	831.4
20°	777.1	774.5	775.6	768.7	775.6	774.5	777.1	781.8	791.3	794.0	803.3
22.5°	754.1	748.9	748.3	746.9	748.3	748.9	754.1	758.3	760.2	768.3	774.9
25°	717.9	715.3	712.7	715.3	712.7	715.3	717.9	722.6	724.7	730.4	736.8
27.5°	686.3	683.2	682.5	682.8	682.5	683.2	686.3	685.9	691.6	696.2	700.7
30°	667.0	661.8	662.3	661.8	662.3	661.8	667.0	667.0	670.1	674.4	678.5
32.5°	646.0	642.5	641.8	640.8	641.8	642.5	646.0	645.2	649.1	654.2	658.8
35°	615.1	615.1	612.5	612.5	612.5	615.1	615.1	616.6	620.9	620.9	626.1
37.5°	586.0	585.5	583.9	584.2	583.9	585.5	586.0	587.3	588.8	591.0	594.3
40°	564.2	563.7	562.1	559.0	562.1	563.7	564.2	566.3	567.3	570.0	572.1
42.5°	543.2	541.5	540.8	539.7	540.8	541.5	543.2	544.5	545.1	548.6	552.8
45°	510.2	510.2	509.2	508.7	509.2	510.2	510.2	510.2	510.8	514.9	517.1
47.5°	478.2	479.1	481.1	480.8	481.1	479.1	478.2	477.3	477.5	479.6	482.0
50°	458.8	459.4	460.9	461.4	460.9	459.4	458.8	456.8	455.7	455.7	457.3
52.5°	437.5	440.5	442.4	442.1	442.4	440.5	437.5	435.8	433.8	431.3	433.7
55°	407.5	411.1	414.8	415.4	414.8	411.1	407.5	402.7	400.6	396.5	398.0
57.5°	377.8	382.9	386.8	388.0	386.8	382.9	377.8	372.1	365.3	363.2	360.3
60°	357.6	364.5	369.2	371.2	369.2	364.5	357.6	352.3	343.5	337.7	335.6
62.5°	338.3	346.0	350.7	351.1	350.7	346.0	338.3	330.1	321.2	314.7	310.4
65°	306.8	314.7	318.8	321.9	318.8	314.7	306.8	297.8	287.9	278.9	274.3
67.5°	272.8	280.6	285.3	287.8	285.3	280.6	272.8	261.8	252.7	242.4	236.8
70°	248.0	255.9	262.2	264.3	262.2	255.9	248.0	234.9	227.0	217.6	212.9
72.5°	223.7	230.8	235.8	238.2	235.8	230.8	223.7	211.5	202.3	192.9	186.4
75°	181.5	190.9	195.6	198.2	195.6	190.9	181.5	174.6	164.1	154.2	149.0
77.5°	139.9	148.6	151.4	152.7	151.4	148.6	139.9	131.9	124.0	116.7	111.6
80°	112.2	117.4	121.1	121.7	121.1	117.4	112.2	105.9	99.7	92.8	88.1
82.5°	86.2	90.6	91.8	93.1	91.8	90.6	86.2	80.8	75.3	70.2	66.2
85°	47.2	49.3	49.8	49.3	49.8	49.3	47.2	43.5	40.9	38.3	36.7
87.5°	17.1	16.7	16.8	17.6	16.8	16.7	17.1	16.3	16.6	15.7	14.7
90°	7.9	7.9	8.2	8.2	8.2	7.9	7.9	7.9	7.2	6.8	6.5
92.5°	24.7	23.8	23.3	22.7	23.3	23.8	24.7	29.3	34.5	45.8	63.2
95°	103.1	92.4	89.6	83.9	89.6	92.4	103.1	128.5	158.4	202.4	256.6
97.5°	237.6	217.6	207.3	202.7	207.3	217.6	237.6	259.6	301.3	344.2	382.1
100°	323.0	297.3	284.1	278.4	284.1	297.3	323.0	347.6	384.8	421.5	439.0
102.5°	399.8	381.5	367.2	362.9	367.2	381.5	399.8	426.2	451.3	468.9	458.1
105°	496.0	484.3	477.2	472.9	477.2	484.3	496.0	507.6	511.4	495.7	446.9
107.5°	536.5	536.5	534.1	531.3	534.1	536.5	536.5	530.8	512.1	471.8	406.6
110°	541.4	548.2	550.7	550.7	550.7	548.2	541.4	525.3	495.0	444.7	376.9



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	528.0	539.7	545.8	548.5	545.8	539.7	528.0	504.5	468.8	417.9	353.5
115°	495.0	512.1	522.1	526.7	522.1	512.1	495.0	467.2	428.3	379.4	324.1
117.5°	458.4	476.2	486.0	488.9	486.0	476.2	458.4	430.6	394.9	352.7	305.1
120°	434.7	451.8	461.5	464.3	461.5	451.8	434.7	408.3	376.9	337.6	294.8
122.5°	414.8	430.4	440.1	442.6	440.1	430.4	414.8	391.1	361.7	326.8	287.1
125°	389.0	403.6	411.5	415.1	411.5	403.6	389.0	369.0	343.4	312.3	275.9
127.5°	369.6	382.5	389.9	391.5	389.9	382.5	369.6	351.4	327.4	298.4	264.5
130°	357.6	369.4	376.6	378.7	376.6	369.4	357.6	339.8	316.6	288.7	257.3
132.5°	345.1	356.8	363.3	365.8	363.3	356.8	345.1	327.2	304.9	279.6	250.1
135°	324.5	336.2	342.6	344.8	342.6	336.2	324.5	308.7	288.4	265.5	241.0
137.5°	303.3	314.0	319.9	322.2	319.9	314.0	303.3	289.2	272.0	253.0	233.1
140°	290.1	299.4	304.8	306.6	304.8	299.4	290.1	276.9	262.0	245.5	228.7
142.5°	277.6	285.5	290.5	292.1	290.5	285.5	277.6	266.4	253.4	239.2	225.1
145°	260.5	266.6	270.5	272.0	270.5	266.6	260.5	252.0	242.4	231.3	220.3
147.5°	247.2	252.1	254.3	255.0	254.3	252.1	247.2	240.4	233.2	224.6	215.6
150°	239.4	243.8	245.2	245.5	245.2	243.8	239.4	234.1	227.7	221.0	213.1
152.5°	232.9	236.3	237.7	238.1	237.7	236.3	232.9	228.4	223.4	217.2	210.3
155°	224.1	226.6	227.7	228.0	227.7	226.6	224.1	220.6	216.6	211.7	205.9
157.5°	216.1	218.1	219.1	219.0	219.1	218.1	216.1	213.3	210.3	206.3	201.7
160°	211.0	212.7	213.4	213.1	213.4	212.7	211.0	208.4	205.9	202.4	198.8
162.5°	206.1	207.5	207.7	207.6	207.7	207.5	206.1	204.2	202.0	198.9	195.6
165°	199.1	199.9	199.9	199.9	199.9	199.9	199.1	197.7	195.9	193.8	191.3
167.5°	192.5	193.1	192.8	192.7	192.8	193.1	192.5	191.8	190.5	188.8	187.1
170°	188.4	188.8	188.8	188.4	188.8	188.8	188.4	187.7	187.0	185.9	184.9
172.5°	184.7	185.4	184.8	184.4	184.8	185.4	184.7	184.6	184.2	183.4	182.3
175°	180.3	180.6	179.9	179.6	179.9	180.6	180.3	180.3	180.3	179.6	179.6
177.5°	177.6	177.8	177.0	177.0	177.0	177.8	177.6	177.8	177.8	177.8	177.6
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1181.3	1186.4	1192.7	1197.3	1205.7	1209.4	1214.1	1217.8	1224.6	1230.8	1238.4
5°	1101.8	1110.6	1122.7	1135.8	1151.0	1161.5	1176.2	1185.1	1203.0	1219.2	1234.9
7.5°	1029.6	1040.5	1057.5	1074.4	1094.3	1112.3	1130.6	1151.0	1173.8	1200.6	1222.8
10°	980.1	994.7	1013.1	1034.1	1058.2	1079.1	1103.8	1125.8	1153.7	1185.1	1214.5
12.5°	940.6	953.2	973.7	993.8	1019.6	1045.2	1070.7	1099.8	1132.3	1167.1	1204.0
15°	886.2	896.7	913.4	941.3	967.5	992.7	1031.0	1058.2	1099.1	1137.9	1182.5
17.5°	839.7	852.7	866.9	890.7	917.9	949.4	983.5	1017.7	1057.1	1106.3	1156.6
20°	811.2	821.7	838.0	856.3	885.1	916.7	949.2	983.7	1032.0	1082.9	1136.8
22.5°	780.1	791.5	809.8	829.9	854.1	884.3	920.2	958.2	1008.5	1058.5	1117.1
25°	743.6	751.4	768.2	786.1	810.2	835.9	873.1	915.0	964.8	1022.0	1081.8
27.5°	709.0	716.0	731.3	746.8	768.6	799.1	832.4	874.7	921.7	979.7	1045.9
30°	684.3	691.7	705.3	722.1	743.1	769.8	803.9	843.7	894.0	950.7	1020.0
32.5°	662.9	669.4	679.7	696.5	717.0	743.0	774.5	815.2	865.6	923.0	991.0
35°	629.8	637.1	645.0	658.1	675.9	701.0	735.7	774.0	822.2	877.8	940.2
37.5°	596.8	604.8	611.9	623.6	639.9	662.1	692.0	731.8	775.5	829.0	888.9
40°	576.3	582.6	588.3	601.0	617.2	638.1	666.0	701.7	747.8	797.6	847.4
42.5°	555.7	561.6	566.5	577.4	592.5	612.6	639.1	673.9	716.7	763.2	807.1
45°	523.3	527.0	532.8	542.2	554.3	572.6	598.3	629.2	665.4	709.5	742.6
47.5°	488.3	494.0	498.8	507.1	516.9	534.9	559.6	585.9	618.7	651.5	674.8
50°	461.4	467.3	474.0	481.9	491.3	508.2	530.7	557.4	585.2	610.4	630.3
52.5°	436.3	441.6	448.9	456.4	467.9	482.1	501.3	525.1	552.5	570.6	587.1
55°	399.1	401.6	410.1	417.4	428.4	438.9	458.3	479.3	496.0	509.7	523.3
57.5°	361.0	364.6	369.4	376.0	386.9	399.2	412.8	431.3	441.2	448.3	458.8
60°	336.7	337.7	340.8	348.7	357.1	368.1	383.8	397.0	404.2	410.1	419.0
62.5°	309.8	310.0	315.3	321.0	327.3	339.2	351.9	362.5	368.6	371.4	380.0
65°	272.2	271.1	274.3	278.9	286.3	294.2	305.2	314.7	314.1	317.2	322.4
67.5°	233.7	232.6	232.6	237.1	243.1	250.1	257.7	263.2	263.3	267.4	270.0
70°	207.6	204.5	206.6	210.3	212.9	218.6	227.0	229.1	229.6	231.8	234.4
72.5°	180.8	179.8	181.5	183.0	184.8	189.3	196.4	197.7	197.8	199.0	203.4
75°	143.7	142.6	141.6	143.2	145.2	148.3	151.0	153.1	152.6	153.1	156.2
77.5°	107.8	104.7	104.2	105.1	105.6	107.4	110.2	110.0	110.6	110.5	114.0
80°	85.4	81.3	80.8	80.8	81.3	82.3	83.4	84.4	82.8	84.4	85.4
82.5°	62.8	60.3	60.2	59.8	59.9	60.1	60.7	61.4	61.0	61.8	62.4
85°	34.6	33.5	32.0	33.0	32.5	30.9	32.0	30.4	29.9	30.4	30.9
87.5°	12.9	13.3	12.3	12.2	11.7	12.0	11.1	10.5	9.9	10.2	11.4
90°	6.1	5.8	4.9	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4
92.5°	93.1	115.0	116.9	81.4	48.8	29.3	18.9	12.7	8.3	5.3	4.3
95°	309.4	316.2	258.0	159.6	81.0	42.8	26.8	18.9	14.9	12.1	11.8
97.5°	391.5	337.7	230.5	127.3	69.8	44.5	33.0	26.0	22.0	20.0	19.6
100°	411.5	322.2	205.6	115.6	69.3	48.6	37.9	31.0	27.2	25.7	24.9
102.5°	399.5	295.2	186.7	110.8	71.8	53.4	43.0	36.8	32.5	31.4	31.0
105°	361.2	258.7	168.4	108.9	77.1	61.4	51.4	45.6	42.1	40.3	40.3
107.5°	322.0	233.7	160.8	112.1	84.9	69.8	60.8	54.8	51.9	50.2	49.5
110°	299.8	222.0	158.4	115.3	90.7	76.0	66.8	61.4	58.2	56.8	56.0



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.3	215.1	158.4	119.3	96.0	82.0	73.0	67.7	64.4	63.3	62.6
115°	265.2	207.7	159.6	125.2	104.6	91.4	82.4	77.1	73.9	72.8	72.1
117.5°	254.4	204.1	161.9	132.1	113.3	100.8	92.2	86.0	82.9	81.7	80.7
120°	248.4	202.4	164.2	136.7	119.6	107.0	98.2	92.1	88.9	87.5	86.3
122.5°	243.3	201.0	166.1	141.8	125.5	113.1	104.1	97.6	94.3	93.1	92.4
125°	236.3	199.1	169.6	148.9	133.5	121.7	112.4	105.6	102.4	100.7	100.0
127.5°	229.8	198.3	173.3	155.2	141.1	129.8	120.5	113.3	109.2	106.9	105.8
130°	225.6	197.7	175.6	159.6	145.9	134.9	125.6	118.2	113.5	110.7	109.6
132.5°	222.2	197.7	178.1	163.3	150.6	139.5	130.2	122.4	117.2	113.8	112.4
135°	218.0	197.7	181.7	168.4	156.6	145.6	136.0	128.5	122.8	118.5	117.0
137.5°	214.4	198.1	184.9	172.3	161.1	151.0	141.1	133.7	127.9	124.0	122.9
140°	212.7	198.4	186.3	174.9	164.2	153.8	144.2	137.4	131.7	127.4	126.3
142.5°	211.3	198.7	187.1	176.3	166.1	156.4	147.3	140.9	135.1	131.1	130.4
145°	209.1	198.4	188.0	178.4	169.6	160.3	152.1	145.6	140.6	137.0	136.3
147.5°	206.9	197.5	188.4	179.8	171.7	163.5	156.3	150.8	146.1	143.0	142.6
150°	205.2	196.6	188.4	180.6	173.1	165.2	159.2	154.2	149.6	147.0	146.3
152.5°	203.2	195.5	188.1	181.2	174.5	167.2	161.8	157.0	153.0	150.8	150.4
155°	199.9	193.5	187.3	181.7	175.9	169.9	164.9	161.3	157.7	155.6	155.6
157.5°	196.7	191.3	186.4	182.0	177.1	172.0	168.1	165.0	162.0	160.3	160.4
160°	194.2	189.9	185.6	182.0	177.7	173.1	169.9	167.0	164.5	163.1	163.5
162.5°	191.9	188.1	184.7	181.8	178.3	174.2	171.6	169.4	167.1	165.7	166.0
165°	188.4	185.6	183.5	181.3	178.4	175.6	173.5	172.0	170.3	169.2	169.9
167.5°	185.1	183.1	181.5	180.5	178.4	176.1	174.7	173.7	172.8	172.1	172.5
170°	183.1	181.7	180.6	179.9	178.4	176.6	175.6	174.9	174.2	173.8	174.2
172.5°	181.1	180.0	179.5	179.4	178.1	176.6	176.1	175.7	175.0	174.7	175.3
175°	178.4	178.1	178.1	178.4	177.7	176.6	176.6	176.6	176.3	175.9	176.6
177.5°	177.3	177.0	177.0	177.6	177.3	176.7	176.7	177.0	176.7	176.7	177.3
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1242.1	1248.0	1251.8	1258.9	1264.8	1268.2	1271.1	1273.6	1276.6	1279.1	1286.2
5°	1250.1	1263.7	1275.3	1293.1	1309.4	1321.9	1335.5	1347.7	1357.7	1371.8	1382.8
7.5°	1246.7	1270.9	1296.3	1323.8	1352.0	1378.3	1402.4	1424.9	1445.4	1470.2	1491.9
10°	1243.3	1276.4	1308.9	1346.0	1384.3	1416.8	1447.2	1478.2	1500.8	1532.3	1558.9
12.5°	1240.8	1279.7	1318.9	1363.7	1405.7	1451.7	1492.2	1514.7	1549.0	1574.2	1606.0
15°	1230.2	1281.6	1335.5	1385.9	1445.7	1488.1	1523.9	1567.9	1599.8	1631.8	1666.5
17.5°	1211.2	1269.4	1329.8	1395.8	1453.2	1498.7	1544.7	1587.2	1625.4	1668.3	1711.3
20°	1202.4	1260.6	1329.8	1397.5	1453.6	1501.3	1548.5	1595.2	1637.1	1692.1	1742.0
22.5°	1184.0	1254.4	1318.1	1384.0	1441.8	1493.8	1547.2	1600.2	1656.0	1718.2	1780.6
25°	1151.0	1222.3	1290.0	1355.0	1413.2	1478.2	1535.4	1606.2	1677.5	1759.8	1837.4
27.5°	1116.8	1185.1	1247.1	1309.9	1377.8	1451.4	1525.5	1605.9	1699.2	1803.1	1912.6
30°	1089.1	1153.7	1214.0	1278.4	1349.2	1432.1	1513.4	1608.8	1716.8	1833.7	1963.8
32.5°	1056.8	1116.3	1174.9	1243.2	1320.3	1407.8	1502.5	1607.1	1737.0	1869.9	2003.7
35°	1001.6	1051.4	1111.7	1184.6	1271.6	1371.8	1481.4	1605.1	1754.0	1906.6	2019.4
37.5°	936.0	982.4	1045.9	1125.8	1217.1	1324.5	1454.6	1601.4	1759.6	1881.3	1917.6
40°	892.0	934.9	1001.1	1083.9	1177.2	1291.0	1433.6	1588.8	1742.0	1819.6	1789.7
42.5°	845.0	890.1	954.4	1036.5	1137.0	1260.8	1407.2	1562.5	1690.8	1720.2	1616.9
45°	770.8	817.5	880.9	963.8	1071.9	1206.1	1358.7	1499.8	1573.7	1520.7	1360.8
47.5°	702.0	745.7	804.5	890.0	1001.5	1140.3	1287.3	1399.8	1405.6	1279.3	1108.4
50°	655.0	695.3	754.6	840.0	950.7	1091.3	1223.9	1312.5	1272.6	1129.5	965.3
52.5°	608.8	648.3	706.8	791.4	900.8	1029.6	1153.0	1215.2	1140.1	993.2	852.9
55°	542.2	576.8	634.0	712.1	816.0	935.5	1040.4	1061.9	964.3	819.6	705.8
57.5°	477.2	509.5	561.5	633.5	728.3	834.2	916.3	911.7	808.6	684.4	594.1
60°	433.1	464.6	510.8	581.0	667.5	758.8	829.0	812.2	710.0	603.0	527.0
62.5°	393.7	421.8	465.4	526.8	605.8	690.4	748.1	723.4	623.2	529.6	469.5
65°	335.6	359.2	396.5	448.9	514.4	584.2	628.7	596.7	511.3	438.4	390.1
67.5°	280.1	299.0	330.2	372.1	428.0	484.0	511.2	479.0	410.6	357.4	321.6
70°	244.9	261.7	285.8	323.1	371.8	419.0	439.4	410.6	351.8	306.2	280.5
72.5°	209.6	223.5	244.7	278.1	317.2	358.2	376.1	348.5	300.2	261.8	237.7
75°	162.1	171.5	186.1	209.2	240.1	272.7	282.7	258.5	227.6	198.7	183.0
77.5°	116.0	124.0	135.1	149.7	171.6	192.3	201.0	187.0	163.1	144.8	131.9
80°	89.2	93.3	102.8	114.8	132.2	145.2	151.0	142.1	125.3	111.7	101.7
82.5°	63.5	67.8	73.4	83.4	94.4	103.3	109.5	103.5	91.4	80.7	74.8
85°	30.9	33.5	36.7	40.9	49.3	54.5	54.0	50.3	45.6	41.4	38.3
87.5°	11.0	11.6	13.0	15.2	16.7	18.4	19.4	18.6	17.1	15.9	14.7
90°	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.8	6.1	6.5
92.5°	5.3	8.3	12.7	18.9	29.3	48.8	81.4	116.9	115.0	93.1	63.2
95°	12.1	14.9	18.9	26.8	42.8	81.0	159.6	258.0	316.2	309.4	256.6
97.5°	20.0	22.0	26.0	33.0	44.5	69.8	127.3	230.5	337.7	391.5	382.1
100°	25.7	27.2	31.0	37.9	48.6	69.3	115.6	205.6	322.2	411.5	439.0
102.5°	31.4	32.5	36.8	43.0	53.4	71.8	110.8	186.7	295.2	399.5	458.1
105°	40.3	42.1	45.6	51.4	61.4	77.1	108.9	168.4	258.7	361.2	446.9
107.5°	50.2	51.9	54.8	60.8	69.8	84.9	112.1	160.8	233.7	322.0	406.6
110°	56.8	58.2	61.4	66.8	76.0	90.7	115.3	158.4	222.0	299.8	376.9



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	63.3	64.4	67.7	73.0	82.0	96.0	119.3	158.4	215.1	283.3	353.5
115°	72.8	73.9	77.1	82.4	91.4	104.6	125.2	159.6	207.7	265.2	324.1
117.5°	81.7	82.9	86.0	92.2	100.8	113.3	132.1	161.9	204.1	254.4	305.1
120°	87.5	88.9	92.1	98.2	107.0	119.6	136.7	164.2	202.4	248.4	294.8
122.5°	93.1	94.3	97.6	104.1	113.1	125.5	141.8	166.1	201.0	243.3	287.1
125°	100.7	102.4	105.6	112.4	121.7	133.5	148.9	169.6	199.1	236.3	275.9
127.5°	106.9	109.2	113.3	120.5	129.8	141.1	155.2	173.3	198.3	229.8	264.5
130°	110.7	113.5	118.2	125.6	134.9	145.9	159.6	175.6	197.7	225.6	257.3
132.5°	113.8	117.2	122.4	130.2	139.5	150.6	163.3	178.1	197.7	222.2	250.1
135°	118.5	122.8	128.5	136.0	145.6	156.6	168.4	181.7	197.7	218.0	241.0
137.5°	124.0	127.9	133.7	141.1	151.0	161.1	172.3	184.9	198.1	214.4	233.1
140°	127.4	131.7	137.4	144.2	153.8	164.2	174.9	186.3	198.4	212.7	228.7
142.5°	131.1	135.1	140.9	147.3	156.4	166.1	176.3	187.1	198.7	211.3	225.1
145°	137.0	140.6	145.6	152.1	160.3	169.6	178.4	188.0	198.4	209.1	220.3
147.5°	143.0	146.1	150.8	156.3	163.5	171.7	179.8	188.4	197.5	206.9	215.6
150°	147.0	149.6	154.2	159.2	165.2	173.1	180.6	188.4	196.6	205.2	213.1
152.5°	150.8	153.0	157.0	161.8	167.2	174.5	181.2	188.1	195.5	203.2	210.3
155°	155.6	157.7	161.3	164.9	169.9	175.9	181.7	187.3	193.5	199.9	205.9
157.5°	160.3	162.0	165.0	168.1	172.0	177.1	182.0	186.4	191.3	196.7	201.7
160°	163.1	164.5	167.0	169.9	173.1	177.7	182.0	185.6	189.9	194.2	198.8
162.5°	165.7	167.1	169.4	171.6	174.2	178.3	181.8	184.7	188.1	191.9	195.6
165°	169.2	170.3	172.0	173.5	175.6	178.4	181.3	183.5	185.6	188.4	191.3
167.5°	172.1	172.8	173.7	174.7	176.1	178.4	180.5	181.5	183.1	185.1	187.1
170°	173.8	174.2	174.9	175.6	176.6	178.4	179.9	180.6	181.7	183.1	184.9
172.5°	174.7	175.0	175.7	176.1	176.6	178.1	179.4	179.5	180.0	181.1	182.3
175°	175.9	176.3	176.6	176.6	176.6	177.7	178.4	178.1	178.1	178.4	179.6
177.5°	176.7	176.7	177.0	176.7	176.7	177.3	177.6	177.0	177.0	177.3	177.6
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1292.0	1295.5	1302.5	1300.0	1303.4	1305.0	1306.8
5°	1396.4	1413.2	1420.6	1419.5	1430.5	1427.8	1425.2
7.5°	1514.3	1532.0	1541.8	1554.1	1561.2	1561.7	1567.9
10°	1581.0	1604.1	1613.6	1626.6	1635.0	1639.7	1639.2
12.5°	1632.1	1650.2	1671.4	1677.8	1689.1	1695.1	1692.9
15°	1693.7	1722.6	1744.6	1755.7	1769.8	1773.9	1779.8
17.5°	1748.7	1787.4	1813.1	1847.2	1860.2	1868.0	1863.4
20°	1790.2	1841.1	1866.8	1907.7	1930.3	1942.3	1938.1
22.5°	1839.3	1894.4	1941.9	1977.3	2011.7	2027.9	2031.2
25°	1923.4	1998.9	2068.7	2115.4	2157.8	2167.8	2189.8
27.5°	2017.4	2106.5	2181.0	2230.1	2259.7	2270.8	2277.6
30°	2076.6	2165.2	2221.3	2252.7	2262.2	2261.1	2260.1
32.5°	2105.5	2161.0	2171.7	2162.9	2141.3	2123.1	2104.1
35°	2064.5	2023.1	1961.2	1881.5	1822.7	1763.5	1757.7
37.5°	1856.7	1724.2	1621.2	1506.2	1439.9	1398.9	1370.5
40°	1661.2	1510.8	1385.9	1288.9	1221.2	1194.6	1168.3
42.5°	1449.0	1305.1	1194.7	1113.6	1062.7	1033.0	1012.3
45°	1177.2	1050.4	963.8	905.0	864.7	841.6	828.5
47.5°	964.6	870.8	797.3	754.9	727.0	709.0	709.1
50°	850.5	760.8	712.1	678.5	654.4	640.3	642.9
52.5°	749.4	682.5	640.8	612.7	594.8	586.1	585.8
55°	626.6	578.3	551.1	530.7	518.6	508.7	510.8
57.5°	536.0	495.3	477.1	460.1	451.7	447.7	441.9
60°	479.8	448.4	432.6	419.0	410.6	407.5	401.6
62.5°	429.9	405.2	389.8	378.7	371.1	370.1	365.6
65°	361.3	342.4	328.8	323.6	315.7	313.6	313.6
67.5°	297.8	284.3	273.8	268.9	265.4	266.0	263.5
70°	258.0	247.0	240.1	234.9	232.3	232.8	230.8
72.5°	225.7	213.4	207.4	204.3	200.9	202.2	201.4
75°	171.0	164.6	161.5	158.3	156.2	155.2	154.2
77.5°	125.5	120.0	117.5	115.8	116.1	113.6	115.5
80°	97.0	92.3	90.7	88.1	87.6	87.6	87.1
82.5°	71.0	68.4	67.3	65.0	64.1	64.9	63.5
85°	36.7	34.6	34.1	34.1	33.0	32.0	34.6
87.5°	14.7	13.1	13.3	12.9	12.9	12.5	11.7
90°	6.8	7.2	7.9	7.9	7.9	8.2	8.2
92.5°	45.8	34.5	29.3	24.7	23.8	23.3	22.7
95°	202.4	158.4	128.5	103.1	92.4	89.6	83.9
97.5°	344.2	301.3	259.6	237.6	217.6	207.3	202.7
100°	421.5	384.8	347.6	323.0	297.3	284.1	278.4
102.5°	468.9	451.3	426.2	399.8	381.5	367.2	362.9
105°	495.7	511.4	507.6	496.0	484.3	477.2	472.9
107.5°	471.8	512.1	530.8	536.5	536.5	534.1	531.3
110°	444.7	495.0	525.3	541.4	548.2	550.7	550.7



TEST NUMBER: P333207-840

CATALOG NUMBER: S125DIP-S850D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	417.9	468.8	504.5	528.0	539.7	545.8	548.5
115°	379.4	428.3	467.2	495.0	512.1	522.1	526.7
117.5°	352.7	394.9	430.6	458.4	476.2	486.0	488.9
120°	337.6	376.9	408.3	434.7	451.8	461.5	464.3
122.5°	326.8	361.7	391.1	414.8	430.4	440.1	442.6
125°	312.3	343.4	369.0	389.0	403.6	411.5	415.1
127.5°	298.4	327.4	351.4	369.6	382.5	389.9	391.5
130°	288.7	316.6	339.8	357.6	369.4	376.6	378.7
132.5°	279.6	304.9	327.2	345.1	356.8	363.3	365.8
135°	265.5	288.4	308.7	324.5	336.2	342.6	344.8
137.5°	253.0	272.0	289.2	303.3	314.0	319.9	322.2
140°	245.5	262.0	276.9	290.1	299.4	304.8	306.6
142.5°	239.2	253.4	266.4	277.6	285.5	290.5	292.1
145°	231.3	242.4	252.0	260.5	266.6	270.5	272.0
147.5°	224.6	233.2	240.4	247.2	252.1	254.3	255.0
150°	221.0	227.7	234.1	239.4	243.8	245.2	245.5
152.5°	217.2	223.4	228.4	232.9	236.3	237.7	238.1
155°	211.7	216.6	220.6	224.1	226.6	227.7	228.0
157.5°	206.3	210.3	213.3	216.1	218.1	219.1	219.0
160°	202.4	205.9	208.4	211.0	212.7	213.4	213.1
162.5°	198.9	202.0	204.2	206.1	207.5	207.7	207.6
165°	193.8	195.9	197.7	199.1	199.9	199.9	199.9
167.5°	188.8	190.5	191.8	192.5	193.1	192.8	192.7
170°	185.9	187.0	187.7	188.4	188.8	188.8	188.4
172.5°	183.4	184.2	184.6	184.7	185.4	184.8	184.4
175°	179.6	180.3	180.3	180.3	180.6	179.9	179.6
177.5°	177.8	177.8	177.8	177.6	177.8	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0

(END OF REPORT)