

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333601-840

Luminaire Tested: **S125RDIP-S1090D1035U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333601-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1035U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8444.0 lumens
Efficiency: N/A
Efficacy: 139.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333601-840

CATALOG NUMBER: S125RDIP-S1090D1035U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333601-840

CATALOG NUMBER: S125RDIP-S1090D1035U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	90	87	84	81	74	71	69	62	60	58	50	49	48	43
2	90	82	76	71	82	76	71	66	65	61	58	54	52	49	45	43	41	36
3	82	72	65	59	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333601-840

CATALOG NUMBER: S125RDIP-S1090D1035U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.7	2.0
10°-20°	474.3	5.6
20°-30°	687.8	8.1
30°-40°	783.9	9.3
40°-50°	764.1	9.0
50°-60°	643.2	7.6
60°-70°	450.9	5.3
70°-80°	231.8	2.7
80°-90°	61.4	0.7
90°-100°	49.4	0.6
100°-110°	304.6	3.6
110°-120°	552.5	6.5
120°-130°	709.1	8.4
130°-140°	762.7	9.0
140°-150°	715.9	8.5
150°-160°	579.1	6.9
160°-170°	374.5	4.4
170°-180°	129.2	1.5
0°-30°	1331.9	15.8
0°-40°	2115.8	25.1
0°-60°	3523.1	41.7
0°-90°	4267.0	50.5
90°-120°	906.6	10.7
90°-150°	3094.2	36.6
90°-180°	4177.0	49.5
0°-180°	8444.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	1	9	16	21	24	6
95°	58	52	16	21	21	73
105°	296	300	300	300	299	314
115°	557	561	563	559	553	552
125°	792	798	799	795	792	707
135°	987	993	991	989	983	761
145°	1144	1146	1146	1147	1142	715
155°	1260	1255	1256	1259	1251	580
165°	1330	1324	1325	1330	1323	376
175°	1360	1355	1355	1362	1354	129
180°	1360	1360	1360	1360	1360	



TEST NUMBER: P333601-840

CATALOG NUMBER: S125RDIP-S1090D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.2	23.9	22.6	21.3	19.9	19.3	19.4	19.5	19.5	19.6	19.8
90°	1.0	2.8	4.5	6.4	8.2	9.9	11.4	13.0	14.5	16.2	17.3
92.5°	15.6	14.2	13.0	11.7	10.5	10.6	11.9	13.3	14.7	16.2	17.3
95°	57.5	56.8	56.1	55.4	54.8	50.2	41.7	33.1	24.6	16.2	17.3
97.5°	120.0	121.2	122.4	123.6	124.8	117.0	100.2	83.3	66.4	49.6	43.3
100°	168.3	169.1	169.8	170.4	171.1	171.9	172.8	173.7	174.5	175.4	142.1
102.5°	217.6	218.4	219.3	220.2	221.0	221.7	222.3	222.8	223.3	223.9	217.5
105°	296.4	297.3	298.2	299.1	300.0	300.4	300.4	300.4	300.4	300.4	300.4
107.5°	378.3	378.3	378.3	378.3	378.3	378.5	379.0	379.4	379.9	380.3	380.4
110°	431.5	431.5	431.5	431.5	431.5	431.8	432.2	432.7	433.1	433.5	432.9



TEST NUMBER: P333601-840

CATALOG NUMBER: S125RDIP-S1090D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.6	482.1	482.6	483.2	483.7	484.1	484.4	484.6	484.9	485.2	484.3
115°	556.6	557.7	558.9	560.0	561.1	561.8	562.0	562.2	562.4	562.6	561.8
117.5°	634.2	634.2	634.1	634.1	634.1	634.5	635.3	636.1	637.0	637.8	636.7
120°	682.7	682.4	682.2	682.0	681.8	682.0	682.7	683.3	684.0	684.7	684.2
122.5°	725.4	726.2	727.1	727.9	728.8	729.3	729.7	730.0	730.3	730.6	730.1
125°	791.5	793.0	794.7	796.3	797.8	798.6	798.6	798.6	798.6	798.6	797.7
127.5°	854.6	855.8	856.9	858.0	859.1	859.6	859.5	859.4	859.2	859.1	858.6
130°	893.3	894.5	895.6	896.8	897.9	898.5	898.8	899.0	899.2	899.4	898.8
132.5°	932.1	933.4	934.7	935.9	937.3	937.7	937.2	936.8	936.2	935.7	935.5
135°	987.1	988.5	989.9	991.2	992.5	993.0	992.5	992.1	991.6	991.2	990.7
137.5°	1037.7	1038.9	1040.1	1041.3	1042.4	1042.8	1042.4	1042.0	1041.6	1041.2	1041.3
140°	1070.9	1071.3	1071.8	1072.2	1072.6	1072.8	1072.5	1072.3	1072.1	1071.9	1072.3
142.5°	1100.7	1101.0	1101.3	1101.5	1101.8	1102.1	1102.4	1102.7	1103.0	1103.3	1103.4
145°	1144.5	1144.9	1145.3	1145.8	1146.2	1146.5	1146.5	1146.5	1146.5	1146.5	1146.7
147.5°	1182.8	1182.7	1182.6	1182.5	1182.3	1182.5	1182.8	1183.1	1183.3	1183.6	1183.9
150°	1207.0	1206.5	1206.1	1205.6	1205.2	1205.2	1205.6	1206.1	1206.5	1207.0	1207.4
152.5°	1230.3	1229.4	1228.4	1227.4	1226.4	1226.2	1226.6	1227.0	1227.5	1227.9	1228.4
155°	1260.4	1259.1	1257.7	1256.4	1255.1	1254.6	1255.1	1255.5	1255.9	1256.4	1257.1
157.5°	1283.5	1282.7	1282.0	1281.2	1280.4	1280.0	1280.0	1280.1	1280.1	1280.2	1280.9
160°	1299.7	1298.4	1297.1	1295.7	1294.3	1293.7	1294.0	1294.2	1294.4	1294.6	1295.6
162.5°	1312.6	1311.3	1309.9	1308.6	1307.3	1306.7	1306.9	1307.2	1307.4	1307.6	1308.9
165°	1330.0	1328.6	1327.3	1326.0	1324.6	1324.0	1324.2	1324.4	1324.7	1324.9	1326.3
167.5°	1342.9	1341.5	1340.1	1338.7	1337.4	1336.8	1337.0	1337.2	1337.4	1337.7	1339.3
170°	1350.1	1348.6	1347.0	1345.4	1343.8	1343.2	1343.4	1343.6	1343.8	1344.1	1345.8
172.5°	1354.9	1353.4	1351.8	1350.3	1348.7	1348.2	1348.5	1348.9	1349.3	1349.7	1351.3
175°	1360.2	1358.9	1357.6	1356.1	1354.8	1354.3	1354.5	1354.7	1354.9	1355.1	1357.0
177.5°	1362.6	1361.6	1360.5	1359.4	1358.4	1357.9	1358.1	1358.3	1358.5	1358.6	1359.9
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333601-840

CATALOG NUMBER: S125RDIP-S1090D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	20.0	20.3	20.5	20.5	20.4	20.3	20.2	20.1
90°	18.4	19.5	20.6	21.5	22.2	22.8	23.5	24.2
92.5°	18.4	19.5	20.6	21.3	21.6	21.9	22.3	22.6
95°	18.4	19.5	20.6	21.2	21.2	21.2	21.2	21.2
97.5°	37.0	30.7	24.3	21.2	21.2	21.2	21.2	21.2
100°	108.7	75.3	41.9	24.7	23.8	22.9	22.1	21.2
102.5°	211.2	204.9	198.5	187.8	172.6	157.3	142.1	126.8
105°	300.4	300.4	300.4	300.3	300.1	299.9	299.7	299.4
107.5°	380.4	380.5	380.5	380.2	379.5	378.9	378.2	377.5
110°	432.2	431.5	430.9	430.7	430.9	431.1	431.3	431.5



TEST NUMBER: P333601-840

CATALOG NUMBER: S125RDIP-S1090D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	483.5	482.6	481.8	481.2	480.9	480.6	480.3	480.0
115°	560.9	560.0	559.1	558.0	556.6	555.2	553.9	552.6
117.5°	635.5	634.4	633.2	632.3	631.8	631.2	630.6	630.0
120°	683.8	683.3	682.9	682.1	681.0	679.8	678.7	677.6
122.5°	729.7	729.3	728.8	727.9	726.7	725.4	724.1	722.8
125°	796.8	795.9	795.0	794.3	793.6	792.8	792.2	791.5
127.5°	858.1	857.6	857.1	856.1	854.3	852.7	851.1	849.4
130°	898.1	897.4	896.8	895.9	894.7	893.6	892.5	891.3
132.5°	935.4	935.3	935.1	934.5	933.4	932.3	931.2	930.1
135°	990.3	989.9	989.4	988.5	987.1	985.8	984.4	983.1
137.5°	1041.4	1041.5	1041.6	1041.0	1039.9	1038.6	1037.5	1036.3
140°	1072.8	1073.2	1073.6	1073.2	1071.9	1070.5	1069.1	1067.8
142.5°	1103.5	1103.6	1103.7	1103.1	1101.7	1100.3	1099.0	1097.6
145°	1146.9	1147.1	1147.3	1146.8	1145.5	1144.1	1142.8	1141.5
147.5°	1184.1	1184.4	1184.7	1184.0	1182.3	1180.7	1179.1	1177.5
150°	1207.9	1208.3	1208.7	1208.1	1206.3	1204.5	1202.6	1200.9
152.5°	1228.8	1229.3	1229.7	1229.1	1227.5	1225.9	1224.3	1222.6
155°	1257.7	1258.4	1259.1	1258.5	1256.7	1254.9	1253.1	1251.3
157.5°	1281.6	1282.3	1283.0	1282.5	1280.7	1278.9	1277.1	1275.4
160°	1296.5	1297.4	1298.3	1297.8	1296.1	1294.2	1292.4	1290.6
162.5°	1310.1	1311.3	1312.6	1312.2	1310.3	1308.3	1306.4	1304.3
165°	1327.6	1329.0	1330.3	1330.1	1328.3	1326.5	1324.7	1322.9
167.5°	1340.9	1342.5	1344.1	1343.9	1341.9	1339.9	1337.9	1335.8
170°	1347.7	1349.5	1351.3	1351.1	1349.1	1347.2	1345.1	1343.1
172.5°	1352.9	1354.5	1356.1	1355.9	1353.9	1351.9	1349.9	1348.0
175°	1358.8	1360.6	1362.3	1362.2	1360.2	1358.2	1356.1	1354.1
177.5°	1361.1	1362.4	1363.6	1363.5	1362.1	1360.7	1359.3	1357.8
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2

(END OF REPORT)