

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333139-930

Luminaire Tested: **S125DIP-S375D810U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333139-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3882.4 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333139-930

CATALOG NUMBER: S125DIP-S375D810U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333139-930

CATALOG NUMBER: S125DIP-S375D810U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32					32			
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27					27			
2	85	78	72	67	76	70	65	61	56	53	50	43	41	38	31	29	28	22					22			
3	78	69	61	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19					19			
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16					16			
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14					14			
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12					12			
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11					11			
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10					10			
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9					9			
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8					8			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3076	3076	3076
5°	3083	3053	3073
10°	3064	3032	3049
15°	3031	2995	3008
20°	2983	2944	2950
25°	2932	2884	2881
30°	2869	2818	2804
35°	2801	2748	2709
40°	2732	2672	2633
45°	2657	2602	2550
50°	2574	2517	2442
55°	2494	2423	2354
60°	2399	2326	2244
65°	2286	2211	2136
70°	2177	2079	2005
75°	1984	1919	1852
80°	1767	1737	1696
85°	1534	1564	1482



TEST NUMBER: P333139-930

CATALOG NUMBER: S125DIP-S375D810U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.9	1.2
10°-20°	126.9	3.3
20°-30°	187.3	4.8
30°-40°	218.5	5.6
40°-50°	219.5	5.7
50°-60°	192.7	5.0
60°-70°	143.6	3.7
70°-80°	82.1	2.1
80°-90°	25.7	0.7
90°-100°	31.3	0.8
100°-110°	192.6	5.0
110°-120°	349.4	9.0
120°-130°	448.4	11.5
130°-140°	482.3	12.4
140°-150°	452.7	11.7
150°-160°	366.2	9.4
160°-170°	236.8	6.1
170°-180°	81.7	2.1
0°-30°	359.1	9.2
0°-40°	577.6	14.9
0°-60°	989.8	25.5
0°-90°	1241.1	32.0
90°-120°	573.3	14.8
90°-150°	1956.6	50.4
90°-180°	2641.0	68.0
0°-180°	3882.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	476	476	476	476	476	
5°	476	475	471	474	474	45
15°	453	452	448	450	450	128
25°	412	409	405	405	404	189
35°	355	354	348	347	344	222
45°	291	289	285	281	279	224
55°	222	220	215	212	209	198
65°	150	149	145	141	140	148
75°	80	79	77	76	74	85
85°	21	21	21	21	20	23
90°	1	6	10	13	15	3
95°	36	33	10	13	13	46
105°	187	190	190	190	189	199
115°	352	355	356	353	349	349
125°	500	505	505	502	500	447
135°	624	628	627	625	622	481
145°	724	725	725	725	722	452
155°	797	793	794	796	791	367
165°	841	837	838	841	836	237
175°	860	857	857	861	856	82
180°	860	860	860	860	860	



TEST NUMBER: P333139-930

CATALOG NUMBER: S125DIP-S375D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	476.3	476.3	476.3	476.3	476.3	476.3	476.3	476.3	476.3	476.3	476.3
2.5°	477.4	477.3	477.1	476.9	476.7	476.2	475.6	474.9	474.3	473.5	474.3
5°	475.5	475.3	475.2	475.0	474.8	474.3	473.5	472.7	471.8	471.0	471.7
7.5°	471.2	471.0	470.8	470.7	470.5	469.9	469.0	468.1	467.2	466.3	467.0
10°	467.2	467.1	466.9	466.8	466.6	466.0	465.1	464.1	463.3	462.4	463.0
12.5°	462.4	462.1	461.8	461.5	461.2	460.6	459.7	458.9	458.0	457.2	457.7
15°	453.3	453.1	452.8	452.6	452.2	451.7	450.8	449.9	448.9	448.0	448.4
17.5°	442.8	442.5	442.1	441.7	441.3	440.7	439.7	438.8	437.8	436.8	437.4
20°	434.1	433.9	433.7	433.6	433.4	432.8	431.7	430.6	429.5	428.4	429.0
22.5°	425.3	425.0	424.7	424.4	424.1	423.5	422.4	421.4	420.4	419.4	419.8
25°	411.5	411.1	410.6	410.2	409.8	409.0	408.0	406.8	405.8	404.7	404.9
27.5°	395.3	395.0	394.8	394.5	394.3	393.5	392.5	391.3	390.2	389.1	389.1
30°	384.7	384.5	384.2	383.9	383.7	382.9	381.7	380.4	379.2	377.9	377.7
32.5°	373.2	372.8	372.5	372.1	371.7	371.0	369.8	368.7	367.6	366.5	366.2
35°	355.3	355.0	354.7	354.3	354.0	353.2	352.0	350.9	349.7	348.5	348.1
37.5°	336.7	336.3	335.9	335.4	335.0	334.3	333.1	332.1	330.9	329.9	329.2
40°	324.1	323.6	323.2	322.8	322.4	321.6	320.4	319.3	318.0	316.9	316.2
42.5°	310.5	310.1	309.8	309.4	309.1	308.3	307.1	306.0	304.8	303.6	303.0
45°	290.9	290.6	290.2	289.9	289.5	288.9	287.9	286.9	285.8	284.9	283.9
47.5°	269.8	269.8	269.8	269.9	269.9	269.3	268.1	266.8	265.6	264.4	263.4
50°	256.2	256.0	255.8	255.4	255.2	254.6	253.6	252.6	251.6	250.5	249.5
52.5°	242.4	242.1	242.0	241.8	241.7	241.0	239.9	238.9	237.7	236.7	235.8
55°	221.5	221.3	221.0	220.8	220.5	219.8	218.7	217.5	216.3	215.2	214.4
57.5°	199.7	199.5	199.3	199.3	199.1	198.5	197.5	196.6	195.6	194.6	193.6
60°	185.7	185.4	185.1	184.7	184.4	183.8	182.9	182.0	181.0	180.1	179.3
62.5°	171.3	171.0	170.7	170.5	170.2	169.7	168.9	168.1	167.3	166.6	165.7
65°	149.6	149.4	149.3	149.1	149.0	148.4	147.5	146.5	145.6	144.7	143.9
67.5°	128.6	128.2	127.8	127.5	127.2	126.6	126.0	125.2	124.6	123.9	123.3
70°	115.3	114.9	114.5	114.1	113.7	113.0	112.3	111.5	110.8	110.1	109.5
72.5°	100.9	100.5	100.3	100.0	99.7	99.3	98.8	98.3	97.8	97.3	96.8
75°	79.5	79.3	79.2	79.0	78.8	78.5	78.1	77.7	77.3	76.9	76.6
77.5°	59.8	59.8	59.7	59.6	59.6	59.4	59.2	58.9	58.7	58.5	58.3
80°	47.5	47.5	47.5	47.5	47.5	47.4	47.2	47.0	46.9	46.7	46.6
82.5°	36.6	36.5	36.4	36.2	36.1	36.0	36.0	36.0	35.9	35.9	35.7
85°	20.7	20.8	20.9	21.0	21.0	21.1	21.1	21.1	21.1	21.1	21.0
87.5°	8.2	8.5	8.7	9.0	9.2	9.4	9.5	9.6	9.8	9.9	10.0
90°	0.7	1.8	2.9	4.1	5.1	6.2	7.3	8.2	9.2	10.2	10.9
92.5°	9.8	9.0	8.2	7.4	6.7	6.7	7.6	8.5	9.3	10.2	10.9
95°	36.4	36.0	35.5	35.1	34.7	31.7	26.3	21.0	15.6	10.2	10.9
97.5°	75.9	76.6	77.4	78.2	78.9	74.0	63.3	52.7	42.0	31.4	27.4
100°	106.5	106.9	107.3	107.8	108.2	108.7	109.3	109.8	110.4	111.0	89.8
102.5°	137.6	138.1	138.7	139.2	139.7	140.1	140.6	140.9	141.2	141.5	137.5
105°	187.4	188.0	188.6	189.1	189.7	190.0	190.0	190.0	190.0	190.0	190.0
107.5°	239.2	239.2	239.2	239.2	239.2	239.4	239.6	239.9	240.2	240.5	240.5
110°	272.9	272.9	272.9	272.9	272.9	273.0	273.3	273.6	273.9	274.2	273.8



TEST NUMBER: P333139-930

CATALOG NUMBER: S125DIP-S375D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.5	304.8	305.2	305.6	305.9	306.1	306.3	306.5	306.6	306.8	306.3
115°	352.0	352.7	353.4	354.1	354.8	355.2	355.4	355.5	355.6	355.8	355.2
117.5°	401.0	401.0	401.0	401.0	401.0	401.2	401.7	402.3	402.8	403.3	402.6
120°	431.6	431.5	431.4	431.2	431.0	431.2	431.6	432.1	432.5	432.9	432.7
122.5°	458.7	459.3	459.7	460.3	460.8	461.2	461.4	461.6	461.8	462.0	461.7
125°	500.5	501.5	502.5	503.5	504.5	505.0	505.0	505.0	505.0	505.0	504.4
127.5°	540.5	541.1	541.8	542.6	543.2	543.6	543.5	543.4	543.3	543.2	542.9
130°	564.9	565.7	566.3	567.0	567.8	568.2	568.3	568.4	568.6	568.8	568.3
132.5°	589.4	590.2	591.0	591.8	592.7	593.0	592.6	592.3	592.0	591.7	591.6
135°	624.2	625.1	625.9	626.8	627.6	627.9	627.6	627.3	627.0	626.8	626.5
137.5°	656.2	657.0	657.7	658.4	659.2	659.4	659.2	658.9	658.7	658.4	658.4
140°	677.1	677.4	677.7	678.0	678.2	678.3	678.2	678.1	677.9	677.8	678.1
142.5°	696.0	696.2	696.3	696.5	696.7	696.8	697.1	697.2	697.5	697.7	697.7
145°	723.7	724.0	724.2	724.6	724.8	725.0	725.0	725.0	725.0	725.0	725.1
147.5°	747.9	747.9	747.8	747.7	747.7	747.7	747.9	748.0	748.3	748.4	748.6
150°	763.2	763.0	762.6	762.4	762.1	762.1	762.4	762.6	763.0	763.2	763.5
152.5°	778.0	777.4	776.7	776.2	775.5	775.3	775.6	775.9	776.2	776.5	776.7
155°	797.0	796.1	795.3	794.4	793.6	793.3	793.6	793.9	794.2	794.4	794.8
157.5°	811.6	811.1	810.7	810.2	809.6	809.3	809.4	809.4	809.4	809.5	809.9
160°	821.9	821.0	820.2	819.3	818.5	818.2	818.2	818.4	818.6	818.6	819.2
162.5°	830.1	829.2	828.3	827.4	826.6	826.3	826.4	826.6	826.7	826.9	827.6
165°	841.0	840.2	839.3	838.5	837.6	837.2	837.4	837.6	837.6	837.8	838.7
167.5°	849.1	848.3	847.4	846.5	845.6	845.3	845.4	845.5	845.7	845.9	846.9
170°	853.8	852.7	851.7	850.8	849.8	849.4	849.5	849.6	849.8	849.9	851.1
172.5°	856.8	855.8	854.8	853.9	852.8	852.5	852.7	853.0	853.2	853.5	854.5
175°	860.1	859.2	858.4	857.6	856.7	856.4	856.5	856.6	856.8	857.0	858.1
177.5°	861.7	861.0	860.3	859.7	858.9	858.7	858.8	858.8	859.0	859.1	859.9
180°	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1



TEST NUMBER: P333139-930

CATALOG NUMBER: S125DIP-S375D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	476.3	476.3	476.3	476.3	476.3	476.3	476.3	476.3
2.5°	474.9	475.6	476.2	476.5	476.5	476.4	476.4	476.3
5°	472.5	473.3	474.0	474.3	474.3	474.2	474.1	474.0
7.5°	467.7	468.5	469.2	469.5	469.4	469.4	469.3	469.2
10°	463.7	464.3	465.0	465.3	465.2	465.1	465.0	465.0
12.5°	458.3	458.9	459.3	459.6	459.6	459.6	459.6	459.5
15°	448.8	449.2	449.7	449.9	449.9	449.9	449.9	449.9
17.5°	437.9	438.4	439.0	439.0	438.5	438.1	437.7	437.3
20°	429.6	430.2	430.7	430.9	430.4	430.0	429.6	429.2
22.5°	420.1	420.5	420.9	420.9	420.7	420.4	420.1	419.8
25°	405.0	405.2	405.4	405.3	405.0	404.8	404.6	404.3
27.5°	389.1	389.1	389.2	389.1	388.8	388.6	388.3	388.1
30°	377.6	377.4	377.2	377.1	376.8	376.6	376.3	376.0
32.5°	365.9	365.6	365.3	364.9	364.4	363.9	363.5	363.1
35°	347.7	347.3	346.8	346.3	345.7	345.0	344.3	343.6
37.5°	328.6	328.0	327.3	326.9	326.4	326.1	325.7	325.3
40°	315.4	314.6	313.9	313.4	313.2	312.8	312.6	312.3
42.5°	302.2	301.6	300.8	300.4	299.9	299.5	299.2	298.8
45°	282.8	281.8	280.9	280.2	280.0	279.7	279.5	279.2
47.5°	262.4	261.4	260.3	259.5	258.9	258.4	257.8	257.2
50°	248.4	247.3	246.2	245.4	244.8	244.2	243.6	243.0
52.5°	234.8	233.8	232.8	232.1	231.5	230.8	230.2	229.5
55°	213.6	212.9	212.1	211.5	210.9	210.3	209.7	209.1
57.5°	192.7	191.7	190.7	190.0	189.7	189.4	189.1	188.7
60°	178.5	177.6	176.8	176.0	175.5	174.9	174.3	173.7
62.5°	164.8	163.8	162.9	162.2	161.8	161.3	160.9	160.5
65°	143.2	142.4	141.7	141.1	140.8	140.5	140.1	139.8
67.5°	122.6	122.0	121.3	120.9	120.7	120.5	120.3	120.1
70°	109.0	108.5	108.0	107.6	107.3	107.0	106.6	106.2
72.5°	96.2	95.6	95.1	94.7	94.3	94.0	93.6	93.3
75°	76.4	76.1	75.8	75.6	75.3	74.9	74.6	74.2
77.5°	58.2	58.0	57.9	57.7	57.5	57.2	57.0	56.7
80°	46.6	46.5	46.4	46.2	46.1	45.9	45.7	45.6
82.5°	35.5	35.4	35.3	35.1	35.1	35.1	35.1	35.1
85°	21.0	20.9	20.8	20.6	20.5	20.3	20.1	20.0
87.5°	10.2	10.3	10.4	10.5	10.4	10.4	10.4	10.3
90°	11.7	12.3	13.0	13.6	14.0	14.4	14.8	15.3
92.5°	11.7	12.3	13.0	13.5	13.7	13.9	14.1	14.3
95°	11.7	12.3	13.0	13.4	13.4	13.4	13.4	13.4
97.5°	23.4	19.4	15.4	13.4	13.4	13.4	13.4	13.4
100°	68.7	47.6	26.5	15.7	15.1	14.5	13.9	13.4
102.5°	133.5	129.6	125.6	118.8	109.1	99.5	89.8	80.2
105°	190.0	190.0	190.0	190.0	189.8	189.6	189.5	189.4
107.5°	240.6	240.6	240.6	240.4	240.0	239.5	239.1	238.7
110°	273.3	272.9	272.5	272.3	272.5	272.6	272.7	272.9



TEST NUMBER: P333139-930

CATALOG NUMBER: S125DIP-S375D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	305.7	305.2	304.7	304.3	304.1	303.9	303.7	303.5
115°	354.7	354.1	353.5	352.8	352.0	351.1	350.3	349.4
117.5°	401.9	401.1	400.4	399.8	399.5	399.1	398.8	398.4
120°	432.4	432.1	431.8	431.3	430.6	429.9	429.2	428.4
122.5°	461.5	461.1	460.9	460.3	459.5	458.7	457.9	457.1
125°	503.9	503.3	502.7	502.2	501.8	501.3	500.9	500.5
127.5°	542.6	542.3	542.0	541.3	540.3	539.2	538.2	537.1
130°	567.9	567.4	567.0	566.5	565.7	565.1	564.4	563.6
132.5°	591.5	591.4	591.3	590.9	590.3	589.5	588.8	588.2
135°	626.2	625.9	625.7	625.1	624.2	623.4	622.5	621.7
137.5°	658.5	658.5	658.6	658.3	657.5	656.8	656.1	655.3
140°	678.3	678.7	678.9	678.7	677.8	676.9	676.0	675.2
142.5°	697.8	697.8	697.9	697.5	696.7	695.8	695.0	694.1
145°	725.2	725.4	725.5	725.1	724.3	723.5	722.6	721.8
147.5°	748.8	748.9	749.1	748.7	747.6	746.7	745.6	744.6
150°	763.8	764.1	764.3	763.9	762.8	761.7	760.5	759.4
152.5°	777.1	777.3	777.6	777.2	776.2	775.2	774.2	773.1
155°	795.3	795.7	796.1	795.8	794.7	793.5	792.4	791.2
157.5°	810.4	810.9	811.3	811.0	809.8	808.7	807.6	806.4
160°	819.8	820.4	820.9	820.7	819.5	818.4	817.3	816.1
162.5°	828.4	829.2	830.0	829.8	828.5	827.3	826.1	824.8
165°	839.5	840.3	841.2	841.1	839.9	838.8	837.6	836.5
167.5°	847.9	848.9	849.9	849.8	848.5	847.3	846.0	844.7
170°	852.2	853.3	854.4	854.4	853.1	851.8	850.5	849.3
172.5°	855.5	856.6	857.6	857.5	856.1	854.9	853.6	852.3
175°	859.2	860.3	861.4	861.4	860.1	858.8	857.6	856.3
177.5°	860.7	861.4	862.3	862.3	861.3	860.4	859.5	858.6
180°	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1

(END OF REPORT)