

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333176-930

Luminaire Tested: **S125DIP-S610D590U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333176-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3706.5 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333176-930

CATALOG NUMBER: S125DIP-S610D590U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333176-930

CATALOG NUMBER: S125DIP-S610D590U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	90	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27	24
6	64	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21	19
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5057	5057	5057
5°	5068	5020	5052
10°	5037	4985	5013
15°	4983	4924	4945
20°	4904	4841	4849
25°	4821	4741	4737
30°	4716	4633	4610
35°	4606	4518	4454
40°	4491	4392	4330
45°	4369	4277	4192
50°	4233	4140	4015
55°	4102	3983	3871
60°	3945	3825	3689
65°	3758	3636	3512
70°	3580	3416	3299
75°	3261	3154	3047
80°	2901	2856	2786
85°	2527	2571	2438



TEST NUMBER: P333176-930

CATALOG NUMBER: S125DIP-S610D590U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	2.0
10°-20°	208.5	5.6
20°-30°	307.9	8.3
30°-40°	359.3	9.7
40°-50°	360.9	9.7
50°-60°	316.8	8.5
60°-70°	236.0	6.4
70°-80°	135.0	3.6
80°-90°	40.6	1.1
90°-100°	40.0	1.1
100°-110°	118.2	3.2
110°-120°	200.2	5.4
120°-130°	263.5	7.1
130°-140°	295.3	8.0
140°-150°	289.4	7.8
150°-160°	243.0	6.6
160°-170°	161.6	4.4
170°-180°	56.5	1.5
0°-30°	590.3	15.9
0°-40°	949.6	25.6
0°-60°	1627.2	43.9
0°-90°	2038.8	55.0
90°-120°	358.5	9.7
90°-150°	1206.6	32.6
90°-180°	1668.0	45.0
0°-180°	3706.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	783	783	783	783	783	
5°	782	780	774	780	779	74
15°	745	743	736	739	740	210
25°	676	673	665	666	665	311
35°	584	581	573	570	565	365
45°	478	476	468	461	459	368
55°	364	362	354	348	344	325
65°	246	244	238	232	230	244
75°	131	129	126	124	122	139
85°	34	35	35	34	33	38
90°	0	4	7	10	11	4
95°	30	31	36	39	40	32
105°	106	108	111	114	115	113
115°	200	202	203	203	202	198
125°	292	295	296	295	294	262
135°	380	383	384	384	382	293
145°	461	463	464	464	463	288
155°	527	527	528	530	527	243
165°	574	573	573	575	572	162
175°	596	594	594	597	594	57
180°	598	598	598	598	598	



TEST NUMBER: P333176-930

CATALOG NUMBER: S125DIP-S610D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	785.0	784.6	784.3	784.0	783.7	782.9	781.9	780.7	779.7	778.5	779.7
5°	781.8	781.5	781.2	780.9	780.6	779.8	778.4	777.1	775.7	774.3	775.6
7.5°	774.5	774.3	774.0	773.7	773.5	772.6	771.0	769.6	768.0	766.5	767.7
10°	768.1	767.8	767.6	767.3	767.0	766.1	764.6	763.1	761.6	760.1	761.2
12.5°	760.2	759.7	759.2	758.7	758.2	757.2	755.9	754.5	753.0	751.6	752.5
15°	745.2	744.8	744.4	744.0	743.6	742.6	741.1	739.6	738.0	736.5	737.2
17.5°	728.0	727.4	726.8	726.2	725.5	724.5	722.9	721.3	719.7	718.2	719.0
20°	713.6	713.3	713.1	712.8	712.5	711.5	709.7	707.9	706.1	704.3	705.3
22.5°	699.2	698.7	698.2	697.7	697.2	696.2	694.5	692.8	691.1	689.4	690.1
25°	676.5	675.7	675.1	674.4	673.7	672.5	670.7	668.9	667.1	665.3	665.6
27.5°	649.8	649.4	649.0	648.6	648.2	647.0	645.1	643.4	641.5	639.7	639.7
30°	632.4	632.0	631.6	631.2	630.8	629.6	627.5	625.4	623.4	621.3	621.0
32.5°	613.6	613.0	612.4	611.7	611.1	609.8	608.1	606.2	604.3	602.5	602.0
35°	584.2	583.6	583.0	582.5	582.0	580.7	578.8	576.8	574.9	573.0	572.3
37.5°	553.5	552.9	552.2	551.5	550.8	549.5	547.7	545.9	544.0	542.3	541.3
40°	532.7	532.1	531.3	530.7	529.9	528.6	526.8	524.8	522.9	521.0	519.8
42.5°	510.5	509.9	509.2	508.7	508.1	506.9	504.9	503.0	501.1	499.1	498.1
45°	478.3	477.7	477.1	476.5	476.1	474.9	473.3	471.7	469.9	468.3	466.7
47.5°	443.5	443.5	443.6	443.6	443.6	442.6	440.7	438.7	436.8	434.7	433.1
50°	421.3	420.8	420.4	420.0	419.6	418.6	416.9	415.2	413.6	412.0	410.2
52.5°	398.4	398.1	397.9	397.5	397.2	396.2	394.4	392.6	390.9	389.1	387.6
55°	364.3	363.8	363.4	363.0	362.6	361.4	359.5	357.6	355.6	353.7	352.5
57.5°	328.2	328.0	327.8	327.5	327.3	326.4	324.7	323.1	321.5	319.9	318.3
60°	305.4	304.8	304.3	303.7	303.2	302.1	300.7	299.1	297.6	296.1	294.7
62.5°	281.6	281.2	280.7	280.3	279.8	279.0	277.7	276.4	275.1	273.8	272.3
65°	245.9	245.6	245.4	245.1	244.8	243.9	242.4	240.9	239.4	237.9	236.6
67.5°	211.3	210.8	210.2	209.6	209.0	208.2	207.1	205.9	204.8	203.7	202.6
70°	189.6	188.9	188.2	187.5	186.8	185.8	184.6	183.4	182.1	180.9	180.0
72.5°	165.8	165.3	164.9	164.4	163.9	163.2	162.5	161.7	160.9	160.0	159.1
75°	130.7	130.4	130.1	129.9	129.6	129.1	128.4	127.8	127.0	126.4	126.0
77.5°	98.4	98.2	98.2	98.0	97.9	97.7	97.3	96.9	96.5	96.1	95.9
80°	78.0	78.0	78.0	78.0	78.0	77.9	77.6	77.4	77.1	76.8	76.6
82.5°	60.3	60.0	59.8	59.5	59.4	59.2	59.1	59.1	59.0	58.9	58.7
85°	34.1	34.2	34.3	34.5	34.7	34.7	34.7	34.7	34.7	34.7	34.6
87.5°	13.5	13.6	13.8	13.9	14.1	14.3	14.3	14.3	14.3	14.3	14.5
90°	0.5	1.3	2.1	2.9	3.8	4.6	5.3	6.0	6.7	7.4	8.0
92.5°	11.3	11.8	12.4	13.0	13.5	14.3	15.2	16.1	17.0	17.9	18.5
95°	30.2	30.4	30.7	30.8	31.1	31.7	32.7	33.8	34.8	35.8	36.5
97.5°	50.2	50.3	50.4	50.5	50.5	51.3	52.7	54.1	55.6	57.0	57.7
100°	65.1	65.1	65.1	65.1	65.1	65.8	67.1	68.5	69.8	71.2	72.1
102.5°	81.1	81.5	81.9	82.3	82.8	83.3	84.0	84.7	85.4	86.0	87.1
105°	106.1	106.6	107.0	107.6	108.1	108.7	109.3	109.9	110.6	111.1	111.8
107.5°	133.5	134.1	134.6	135.1	135.7	136.2	136.6	137.1	137.5	138.0	138.4
110°	152.5	153.0	153.6	154.1	154.7	155.1	155.3	155.6	156.0	156.3	156.6



TEST NUMBER: P333176-930

CATALOG NUMBER: S125DIP-S610D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.9	172.2	172.4	172.7	173.0	173.3	173.7	174.1	174.5	174.9	175.0
115°	200.5	200.9	201.3	201.7	202.1	202.4	202.6	202.8	203.0	203.3	203.2
117.5°	229.1	229.3	229.5	229.7	229.8	230.1	230.2	230.4	230.6	230.8	230.9
120°	247.0	247.5	248.0	248.5	249.1	249.3	249.5	249.6	249.6	249.7	249.7
122.5°	266.4	266.5	266.7	266.8	267.1	267.3	267.6	267.8	268.1	268.4	268.3
125°	292.5	293.2	293.8	294.4	295.1	295.4	295.5	295.6	295.7	295.8	295.6
127.5°	320.5	320.8	321.1	321.5	321.9	322.1	322.2	322.4	322.5	322.6	322.5
130°	337.2	337.7	338.3	338.8	339.2	339.7	339.8	340.1	340.2	340.5	340.4
132.5°	353.9	354.8	355.6	356.4	357.3	357.8	357.7	357.7	357.6	357.6	357.5
135°	380.4	381.1	381.7	382.3	382.9	383.3	383.4	383.5	383.6	383.7	383.7
137.5°	405.4	406.0	406.6	407.2	407.8	408.2	408.5	408.6	408.9	409.1	409.2
140°	421.3	421.9	422.4	422.9	423.5	423.9	424.2	424.5	424.8	425.1	425.3
142.5°	437.4	437.8	438.2	438.7	439.1	439.5	439.9	440.3	440.8	441.1	441.2
145°	460.9	461.3	461.8	462.2	462.6	462.9	463.3	463.6	463.9	464.1	464.1
147.5°	482.7	482.9	483.1	483.4	483.6	483.8	484.0	484.4	484.6	484.9	485.1
150°	497.2	497.1	497.0	496.9	496.8	496.9	497.3	497.7	498.1	498.6	498.6
152.5°	509.1	509.2	509.4	509.6	509.6	509.8	510.0	510.1	510.3	510.5	510.8
155°	527.4	527.4	527.4	527.4	527.4	527.5	527.6	527.7	527.8	527.9	528.3
157.5°	543.8	543.6	543.3	543.2	542.9	542.8	542.9	543.1	543.2	543.2	543.6
160°	553.5	553.2	552.9	552.5	552.2	552.1	552.2	552.4	552.4	552.5	552.9
162.5°	562.1	561.8	561.6	561.3	561.1	561.0	561.0	561.1	561.1	561.1	561.6
165°	573.5	573.2	573.1	572.8	572.7	572.6	572.7	572.8	572.9	573.0	573.4
167.5°	583.2	582.8	582.3	581.9	581.5	581.3	581.3	581.3	581.3	581.3	581.9
170°	588.3	587.9	587.5	587.1	586.7	586.5	586.5	586.5	586.5	586.5	587.1
172.5°	592.1	591.7	591.3	590.8	590.4	590.2	590.2	590.2	590.2	590.2	590.8
175°	596.2	595.8	595.4	595.0	594.6	594.4	594.4	594.4	594.4	594.4	595.0
177.5°	598.4	598.1	597.8	597.5	597.0	596.9	596.8	596.7	596.6	596.6	597.0
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7



TEST NUMBER: P333176-930

CATALOG NUMBER: S125DIP-S610D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	780.7	781.9	782.9	783.4	783.3	783.2	783.1	783.0
5°	776.8	778.0	779.3	779.8	779.7	779.6	779.4	779.3
7.5°	768.9	770.1	771.4	771.9	771.8	771.6	771.5	771.4
10°	762.3	763.4	764.5	765.0	764.8	764.7	764.5	764.4
12.5°	753.4	754.3	755.1	755.6	755.5	755.5	755.5	755.5
15°	737.9	738.6	739.3	739.6	739.6	739.6	739.6	739.6
17.5°	719.9	720.7	721.6	721.7	721.0	720.3	719.7	718.9
20°	706.2	707.2	708.2	708.3	707.6	706.9	706.2	705.6
22.5°	690.7	691.4	692.0	692.1	691.6	691.1	690.6	690.2
25°	665.9	666.1	666.4	666.3	665.9	665.5	665.1	664.7
27.5°	639.8	639.8	639.8	639.7	639.3	638.9	638.5	638.1
30°	620.8	620.5	620.2	619.9	619.5	619.1	618.6	618.2
32.5°	601.5	601.0	600.5	599.9	599.2	598.4	597.6	596.9
35°	571.6	571.0	570.2	569.3	568.3	567.1	566.1	564.9
37.5°	540.2	539.2	538.2	537.4	536.7	536.1	535.5	534.8
40°	518.4	517.2	516.0	515.2	514.8	514.4	514.0	513.6
42.5°	496.9	495.8	494.6	493.7	493.1	492.5	491.9	491.2
45°	465.0	463.3	461.7	460.6	460.2	459.8	459.4	459.0
47.5°	431.4	429.7	428.0	426.7	425.7	424.8	423.8	422.8
50°	408.4	406.6	404.8	403.4	402.4	401.5	400.5	399.6
52.5°	386.0	384.4	382.9	381.6	380.5	379.4	378.3	377.2
55°	351.2	350.0	348.8	347.6	346.7	345.7	344.8	343.8
57.5°	316.7	315.1	313.5	312.4	311.9	311.4	310.9	310.4
60°	293.3	292.0	290.6	289.4	288.5	287.5	286.5	285.6
62.5°	270.8	269.4	267.8	266.8	266.0	265.2	264.5	263.7
65°	235.4	234.2	232.9	232.0	231.5	230.9	230.4	229.8
67.5°	201.6	200.6	199.5	198.8	198.4	198.1	197.8	197.5
70°	179.2	178.4	177.6	176.9	176.3	175.8	175.2	174.7
72.5°	158.2	157.3	156.3	155.6	155.0	154.5	153.9	153.4
75°	125.6	125.1	124.7	124.3	123.7	123.1	122.6	122.1
77.5°	95.6	95.4	95.1	94.8	94.4	94.1	93.7	93.3
80°	76.6	76.4	76.2	76.1	75.7	75.5	75.3	74.9
82.5°	58.5	58.2	58.0	57.8	57.8	57.7	57.6	57.6
85°	34.4	34.2	34.2	33.9	33.7	33.3	33.1	32.9
87.5°	14.6	14.7	14.8	14.8	14.6	14.4	14.3	14.1
90°	8.5	9.0	9.5	9.9	10.3	10.5	10.8	11.2
92.5°	19.2	19.9	20.6	21.0	21.3	21.5	21.7	21.9
95°	37.3	38.0	38.7	39.1	39.4	39.6	39.8	40.0
97.5°	58.4	59.1	59.8	60.2	60.3	60.4	60.5	60.7
100°	73.1	73.9	74.8	75.4	75.7	75.9	76.1	76.3
102.5°	88.1	89.1	90.1	90.7	91.1	91.3	91.6	91.9
105°	112.4	113.0	113.7	114.1	114.4	114.7	115.0	115.4
107.5°	138.7	139.0	139.3	139.4	139.4	139.4	139.3	139.3
110°	156.9	157.2	157.5	157.6	157.5	157.4	157.3	157.2



TEST NUMBER: P333176-930

CATALOG NUMBER: S125DIP-S610D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	175.2	175.3	175.5	175.5	175.3	175.0	174.9	174.7
115°	203.0	202.9	202.8	202.8	202.6	202.5	202.4	202.4
117.5°	231.0	231.1	231.1	231.0	230.6	230.2	229.8	229.3
120°	249.7	249.7	249.7	249.6	249.2	248.7	248.3	247.9
122.5°	268.2	268.2	268.1	267.8	267.5	267.2	266.8	266.5
125°	295.4	295.2	295.0	294.8	294.7	294.6	294.5	294.4
127.5°	322.4	322.3	322.2	322.0	321.8	321.6	321.4	321.2
130°	340.2	340.1	340.1	339.9	339.7	339.5	339.2	339.1
132.5°	357.3	357.3	357.2	356.9	356.7	356.4	356.1	355.8
135°	383.7	383.7	383.7	383.5	383.1	382.7	382.3	381.9
137.5°	409.4	409.4	409.6	409.4	408.9	408.4	407.9	407.3
140°	425.5	425.7	425.9	425.7	425.3	424.8	424.2	423.7
142.5°	441.3	441.5	441.6	441.4	440.9	440.3	439.9	439.4
145°	464.1	464.1	464.1	464.0	463.7	463.4	463.1	462.8
147.5°	485.3	485.6	485.8	485.6	484.9	484.2	483.5	482.8
150°	498.6	498.6	498.6	498.5	498.3	498.1	497.9	497.7
152.5°	511.0	511.3	511.5	511.4	511.0	510.7	510.3	510.0
155°	528.7	529.1	529.5	529.5	529.0	528.5	527.9	527.4
157.5°	544.0	544.5	544.9	544.8	544.0	543.4	542.7	542.0
160°	553.3	553.8	554.2	554.2	553.7	553.1	552.6	552.1
162.5°	562.1	562.6	563.1	563.0	562.5	561.8	561.3	560.6
165°	573.8	574.2	574.7	574.5	574.0	573.3	572.7	572.1
167.5°	582.5	583.2	583.8	583.8	583.1	582.4	581.8	581.2
170°	587.7	588.3	589.0	588.9	588.2	587.5	586.8	586.0
172.5°	591.5	592.1	592.7	592.7	592.1	591.4	590.8	590.1
175°	595.7	596.2	596.9	596.8	596.1	595.4	594.7	593.9
177.5°	597.5	598.0	598.5	598.5	597.9	597.4	596.7	596.1
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7

(END OF REPORT)