

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333234-930

Luminaire Tested: **S125DIP-S850D1035U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333234-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D1035U930-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5844.1 lumens  
Efficiency: N/A  
Efficacy: 112.4 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48														
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41	41	41	41														
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35	35	35	35														
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30	30	30	30	30	30	30														
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25	25	25	25	25	25	25														
5	68	57	49	43	63	53	46	40	45	39	35	38	34	30	31	28	25	22	22	22	22	22	22	22														
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	20	20	20	20	20	20	20														
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	26	22	20	17	17	17	17	17	17	17														
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16	16	16	16	16	16	16														
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14	14	14	14	14	14	14														
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13	13	13	13	13	13	13														

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6442	6442	6442	6442
5°	7459	6463	5659	6463
10°	8679	6430	4958	6430
15°	9607	6383	4574	6383
20°	10754	6308	4265	6308
25°	12598	6223	4115	6223
30°	13607	6141	3985	6141
35°	11188	5984	3899	5984
40°	7952	5767	3805	5767
45°	6109	5476	3751	5476
50°	5215	5112	3743	5112
55°	4644	4757	3775	4757
60°	4188	4370	3871	4370
65°	3869	3978	3972	3978
70°	3518	3573	4030	3573
75°	3107	3147	3992	3147
80°	2615	2566	3652	2566
85°	2075	1845	2949	1845



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	1.6
10°-20°	285.9	4.9
20°-30°	464.2	7.9
30°-40°	566.3	9.7
40°-50°	515.1	8.8
50°-60°	410.3	7.0
60°-70°	285.8	4.9
70°-80°	152.4	2.6
80°-90°	40.7	0.7
90°-100°	292.6	5.0
100°-110°	629.0	10.8
110°-120°	590.3	10.1
120°-130°	478.4	8.2
130°-140°	383.9	6.6
140°-150°	289.7	5.0
150°-160°	203.9	3.5
160°-170°	120.2	2.1
170°-180°	39.1	0.7
0°-30°	846.1	14.5
0°-40°	1412.4	24.2
0°-60°	2337.8	40.0
0°-90°	2816.7	48.2
90°-120°	1512.0	25.9
90°-150°	2664.1	45.6
90°-180°	3027.0	51.8
0°-180°	5844.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1151	997	873	997	1151	116
15°	1437	955	684	955	1437	411
25°	1768	873	578	873	1768	807
35°	1419	759	494	759	1419	868
45°	669	600	411	600	669	535
55°	412	422	335	422	412	371
65°	253	260	260	260	253	251
75°	124	126	160	126	124	134
85°	28	25	40	25	28	33
90°	19	1	19	1	19	14
95°	191	27	191	27	191	271
105°	1078	92	1078	92	1078	1072
115°	1201	164	1201	164	1201	1174
125°	947	228	947	228	947	856
135°	786	267	786	267	786	609
145°	620	311	620	311	620	394
155°	520	355	520	355	520	242
165°	456	387	456	387	456	130
175°	409	403	409	403	409	40
180°	404	404	404	404	404	



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1055.0	1053.6	1052.3	1049.5	1051.6	1045.9	1043.1	1038.4	1032.7	1030.6	1028.3
5°	1150.6	1152.8	1154.9	1146.0	1146.9	1140.9	1127.4	1116.4	1107.5	1096.1	1088.0
7.5°	1265.8	1260.8	1260.4	1254.7	1244.7	1236.8	1222.5	1204.4	1186.9	1166.9	1150.4
10°	1323.4	1323.8	1320.0	1313.2	1302.7	1295.0	1276.4	1258.6	1237.1	1211.6	1193.4
12.5°	1366.8	1368.5	1363.7	1354.5	1349.4	1332.3	1317.7	1296.6	1270.9	1250.6	1222.9
15°	1436.9	1432.2	1428.8	1417.4	1408.5	1390.7	1367.4	1345.4	1317.4	1291.6	1265.8
17.5°	1504.4	1508.1	1501.8	1491.3	1463.8	1443.0	1411.8	1381.6	1346.9	1312.2	1281.4
20°	1564.7	1568.1	1558.4	1540.2	1507.2	1486.4	1445.3	1406.4	1366.1	1321.7	1287.8
22.5°	1639.9	1637.2	1624.1	1596.4	1567.7	1529.4	1484.9	1437.5	1387.2	1336.9	1291.9
25°	1767.9	1750.1	1742.1	1707.8	1670.1	1613.8	1552.8	1483.4	1420.7	1354.3	1296.7
27.5°	1838.8	1833.3	1824.3	1800.4	1760.8	1700.6	1628.7	1544.1	1455.7	1371.8	1296.5
30°	1824.6	1825.5	1826.4	1818.7	1793.3	1748.0	1676.5	1585.4	1480.4	1386.0	1298.9
32.5°	1698.7	1714.1	1728.8	1746.2	1753.3	1744.7	1699.8	1617.6	1509.6	1402.3	1297.5
35°	1419.0	1423.8	1471.5	1519.0	1583.3	1633.3	1666.7	1630.4	1539.3	1416.1	1295.8
37.5°	1106.4	1129.4	1162.5	1216.0	1308.9	1392.0	1499.0	1548.2	1518.8	1420.6	1292.9
40°	943.2	964.4	985.9	1040.6	1118.9	1219.7	1341.2	1444.9	1469.0	1406.4	1282.7
42.5°	817.3	834.0	857.9	899.0	964.5	1053.7	1169.8	1305.4	1388.8	1365.1	1261.4
45°	668.9	679.5	698.1	730.7	778.1	848.0	950.4	1098.6	1227.7	1270.5	1210.8
47.5°	572.5	572.4	586.9	609.4	643.7	703.0	778.8	894.9	1032.8	1134.8	1130.1
50°	519.0	516.9	528.3	547.8	574.9	614.2	686.6	779.3	911.9	1027.4	1059.6
52.5°	473.0	473.2	480.2	494.6	517.3	551.0	605.0	688.6	801.8	920.5	981.0
55°	412.4	410.7	418.7	428.4	444.9	466.9	505.9	569.8	661.7	778.5	857.3
57.5°	356.8	361.4	364.7	371.5	385.1	399.9	432.8	479.6	552.5	652.8	736.1
60°	324.2	329.0	331.5	338.3	349.3	362.0	387.3	425.5	486.8	573.2	655.7
62.5°	295.1	298.8	299.6	305.7	314.7	327.1	347.1	379.0	427.5	503.1	584.0
65°	253.2	253.2	254.9	261.2	265.5	276.5	291.7	315.0	353.9	412.8	481.8
67.5°	212.7	214.7	214.3	217.1	221.0	229.5	240.4	259.7	288.5	331.5	386.7
70°	186.3	187.9	187.5	189.6	193.9	199.4	208.3	226.5	247.2	284.1	331.5
72.5°	162.6	163.2	162.2	164.9	167.5	172.3	182.2	191.9	211.3	242.4	281.4
75°	124.5	125.3	126.1	127.8	130.4	132.9	138.0	147.7	160.5	183.8	208.7
77.5°	93.3	91.7	93.8	93.5	94.9	96.9	101.3	106.5	116.9	131.7	151.0
80°	70.3	70.7	70.7	71.1	73.2	74.5	78.4	82.1	90.2	101.2	114.7
82.5°	51.3	52.4	51.8	52.5	54.3	55.2	57.3	60.4	65.1	73.8	83.6
85°	28.0	25.8	26.7	27.6	27.6	28.0	29.6	30.9	33.4	36.9	40.6
87.5°	11.9	12.6	12.7	12.7	13.0	12.7	13.9	13.8	14.6	15.5	16.5
90°	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7	13.9	13.0	11.4
92.5°	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2	212.4	262.4	266.6
95°	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2	705.6	721.1	588.5
97.5°	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6	892.8	770.1	525.5
100°	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1	938.4	734.9	468.8
102.5°	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7	911.1	673.1	425.8
105°	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0	823.7	590.0	384.2
107.5°	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2	734.4	533.0	366.6
110°	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5	683.6	506.2	361.3



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1	645.9	490.6	361.3
115°	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0	604.7	473.7	363.8
117.5°	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7	580.2	465.4	369.2
120°	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3	566.5	461.5	374.4
122.5°	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7	554.7	458.2	379.0
125°	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2	538.8	454.1	386.6
127.5°	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1	524.2	452.2	395.3
130°	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9	514.4	450.9	400.5
132.5°	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5	506.5	450.9	406.3
135°	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3	497.3	450.9	414.3
137.5°	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5	489.0	451.8	421.6
140°	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7	485.1	452.5	424.9
142.5°	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2	481.8	453.1	426.8
145°	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1	477.0	452.5	428.9
147.5°	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8	471.9	450.4	429.7
150°	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9	468.0	448.4	429.7
152.5°	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4	463.4	445.9	429.1
155°	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6	455.8	441.2	427.3
157.5°	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8	448.6	436.3	425.2
160°	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3	442.8	433.0	423.2
162.5°	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2	437.6	429.1	421.3
165°	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3	429.7	423.2	418.3
167.5°	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8	422.1	417.5	413.8
170°	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6	417.5	414.3	411.8
172.5°	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7	412.9	410.3	409.2
175°	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4	406.9	406.1	406.1
177.5°	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0	404.3	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1026.2	1023.9	1021.1	1016.4	1010.6	1007.5	1002.8	999.8	993.7	988.6	983.2
5°	1078.2	1067.2	1057.1	1044.0	1029.6	1020.3	1009.3	996.9	984.3	971.2	956.8
7.5°	1132.2	1112.7	1091.5	1068.8	1046.5	1026.1	1006.5	987.2	969.3	947.6	929.3
10°	1168.4	1143.9	1117.6	1086.7	1056.7	1030.5	1003.8	980.5	956.8	931.4	908.9
12.5°	1204.7	1172.0	1134.9	1101.0	1064.8	1033.1	1001.8	972.0	942.2	914.1	887.9
15°	1230.3	1201.4	1167.2	1118.9	1078.2	1034.7	993.2	954.6	918.7	887.4	854.4
17.5°	1247.1	1210.0	1173.2	1126.9	1073.6	1024.8	977.9	933.8	893.2	853.5	821.7
20°	1250.2	1212.0	1173.5	1128.2	1073.6	1017.7	970.8	917.8	874.2	833.2	794.2
22.5°	1249.1	1206.0	1164.0	1117.4	1064.1	1012.7	955.9	901.9	854.6	814.2	773.6
25°	1239.6	1193.4	1140.9	1094.0	1041.5	986.8	929.3	873.3	825.1	778.9	738.7
27.5°	1231.6	1171.7	1112.3	1057.5	1006.8	956.8	901.6	844.4	790.9	744.1	706.2
30°	1221.8	1156.2	1089.2	1032.1	980.1	931.4	879.3	823.5	767.5	721.8	681.2
32.5°	1213.0	1136.5	1065.9	1003.7	948.5	901.2	853.2	800.1	745.2	698.8	658.1
35°	1196.0	1107.5	1026.6	956.3	897.5	848.8	808.6	759.0	708.7	663.8	624.8
37.5°	1174.4	1069.3	982.6	908.9	844.4	793.1	755.7	717.6	669.3	626.1	590.8
40°	1157.4	1042.3	950.4	875.1	808.2	754.8	720.2	684.1	643.9	603.7	566.5
42.5°	1136.1	1017.9	917.9	836.8	770.5	718.6	682.2	651.6	616.1	578.6	544.0
45°	1096.9	973.7	865.4	778.1	711.2	660.0	622.3	599.5	572.8	537.2	508.0
47.5°	1039.3	920.6	808.5	718.5	649.5	602.0	566.7	544.8	525.9	499.5	473.0
50°	988.1	881.0	767.5	678.2	609.2	561.3	528.8	508.8	492.8	472.5	450.0
52.5°	930.8	831.2	727.2	639.0	570.6	523.4	491.5	474.0	460.6	446.1	424.0
55°	839.9	755.3	658.8	574.9	511.8	465.7	437.7	422.5	411.5	400.5	386.9
57.5°	739.7	673.5	588.0	511.4	453.3	411.3	385.2	370.4	361.9	356.2	348.2
60°	669.3	612.6	538.9	469.0	412.4	375.1	349.7	338.3	331.1	326.4	320.5
62.5°	604.0	557.4	489.1	425.3	375.8	340.6	317.9	306.8	299.9	297.6	292.7
65°	507.6	471.7	415.3	362.4	320.1	290.0	270.9	260.3	256.1	253.6	254.0
67.5°	412.7	390.8	345.5	300.4	266.6	241.4	226.2	218.0	215.9	212.5	212.5
70°	354.7	338.3	300.2	260.8	230.7	211.2	197.7	189.2	187.1	185.4	185.0
72.5°	303.6	289.2	256.1	224.5	197.5	180.4	169.3	164.2	160.7	159.7	159.6
75°	228.2	220.1	193.9	168.9	150.3	138.4	130.9	126.1	123.6	123.2	123.6
77.5°	162.2	155.2	138.5	120.8	109.1	100.1	93.7	92.0	89.2	89.3	88.8
80°	121.9	117.2	106.7	92.7	83.0	75.3	72.0	69.0	68.2	66.9	68.2
82.5°	88.4	83.4	76.2	67.3	59.3	54.7	51.3	50.4	49.9	49.2	49.6
85°	43.6	44.0	39.8	33.0	29.6	27.1	24.9	24.9	24.5	24.1	24.5
87.5°	17.0	16.0	14.5	13.1	11.2	9.8	9.1	9.3	8.5	8.5	9.1
90°	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8	1.6	3.3	4.9
92.5°	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9	12.1	18.9	28.9
95°	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8	27.6	34.2	43.1
97.5°	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6	45.6	50.1	59.1
100°	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0	58.6	61.9	70.8
102.5°	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7	71.6	74.2	83.8
105°	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0	92.0	96.0	104.2
107.5°	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8	114.5	118.3	125.0
110°	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8	129.4	132.6	140.0





TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8	144.4	147.0	154.3
115°	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4	166.0	168.4	175.8
117.5°	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9	186.4	189.0	196.3
120°	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0	199.4	202.7	210.0
122.5°	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7	212.4	215.0	222.3
125°	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9	229.5	233.6	240.9
127.5°	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4	243.9	249.1	258.4
130°	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9	252.3	258.9	269.4
132.5°	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4	259.4	267.3	279.2
135°	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9	270.2	280.0	293.0
137.5°	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3	282.7	291.9	304.9
140°	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1	290.6	300.4	313.3
142.5°	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3	299.1	308.1	321.1
145°	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9	312.5	320.7	332.1
147.5°	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2	326.2	333.2	343.8
150°	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7	335.3	341.0	351.6
152.5°	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8	343.8	348.9	358.1
155°	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8	354.8	359.7	367.9
157.5°	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6	365.4	369.3	376.3
160°	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8	371.9	375.2	380.9
162.5°	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6	377.8	381.1	386.1
165°	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4	385.8	388.2	392.3
167.5°	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3	392.5	394.0	396.2
170°	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2	396.4	397.2	398.8
172.5°	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8	398.4	399.2	400.7
175°	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8	401.2	402.0	402.8
177.5°	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3	403.0	403.0	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	980.2	976.4	973.4	966.6	962.9	957.8	953.7	958.1	953.4	955.4	952.4
5°	949.6	937.8	929.3	917.0	906.4	896.7	889.5	888.2	884.8	883.1	878.0
7.5°	912.8	898.0	883.5	867.4	853.8	840.0	831.2	823.9	819.1	812.8	808.5
10°	891.1	871.2	854.4	834.9	817.9	803.1	791.2	785.3	779.8	771.8	768.8
12.5°	864.4	843.8	823.1	802.3	786.1	769.6	759.4	750.4	746.7	737.5	736.6
15°	832.3	801.4	781.1	759.9	737.4	723.9	715.4	705.7	701.5	695.1	690.5
17.5°	794.0	766.5	741.0	719.1	699.9	688.4	677.9	671.2	664.0	659.8	652.2
20°	766.3	740.0	714.6	691.3	676.5	663.4	654.9	648.6	641.0	638.9	631.2
22.5°	742.9	714.0	689.6	670.0	653.8	639.0	629.8	625.6	620.3	613.8	612.2
25°	704.9	674.8	654.1	634.6	620.2	606.7	600.3	594.8	589.7	585.1	583.3
27.5°	672.1	645.1	620.5	602.9	590.4	578.0	572.4	565.7	562.1	558.3	553.8
30°	649.0	621.5	599.9	582.9	569.4	558.4	552.4	547.8	544.5	541.0	538.5
32.5°	625.3	599.8	578.9	562.3	548.8	540.5	535.2	531.9	528.2	524.1	520.9
35°	593.9	566.0	545.7	531.3	520.7	514.4	508.4	505.5	501.2	501.2	497.8
37.5°	558.6	534.5	516.6	503.4	494.0	488.3	481.8	479.8	477.1	475.3	474.2
40°	537.7	515.2	498.3	485.2	475.0	470.3	465.3	461.9	460.2	458.0	457.2
42.5°	516.0	494.6	478.3	466.2	457.4	453.4	448.7	446.3	442.9	440.1	439.6
45°	483.1	462.3	447.5	437.7	430.2	425.5	422.5	417.4	415.7	412.4	411.9
47.5°	451.8	431.9	417.4	409.4	402.7	398.8	394.2	389.1	387.2	385.5	385.3
50°	428.4	410.3	396.6	389.1	382.7	377.2	372.5	369.2	367.9	367.9	368.8
52.5°	404.7	389.2	377.7	368.4	362.4	356.5	352.2	350.2	348.2	350.3	351.8
55°	370.0	354.3	345.8	337.0	331.1	324.2	322.2	321.3	320.1	323.4	325.1
57.5°	333.3	322.3	312.3	303.5	298.2	294.3	291.5	290.9	293.3	294.9	300.4
60°	309.9	297.2	288.3	281.5	275.2	272.6	271.8	270.9	272.6	277.3	284.5
62.5°	284.1	273.9	264.2	259.2	254.5	250.3	250.1	250.6	254.0	259.3	266.5
65°	246.4	237.5	231.1	225.2	221.4	218.9	219.7	221.4	225.2	232.4	240.4
67.5°	208.1	201.9	196.2	191.4	187.8	187.8	188.7	191.2	195.7	204.0	211.3
70°	183.3	176.5	171.9	169.7	166.8	165.1	167.6	171.9	175.7	183.3	189.6
72.5°	158.6	152.9	149.2	147.7	146.5	145.1	145.9	150.5	155.7	163.3	170.7
75°	121.9	119.8	117.2	115.6	114.3	115.1	116.0	120.3	124.5	132.5	141.0
77.5°	88.9	86.7	85.3	84.9	84.1	84.5	87.0	90.1	94.2	100.1	106.5
80°	67.3	66.4	65.6	65.2	65.2	65.6	69.0	71.1	74.9	80.5	85.5
82.5°	49.0	48.5	48.3	48.3	48.6	48.7	50.7	53.5	56.7	60.8	65.2
85°	25.8	24.9	26.3	26.7	25.8	27.1	28.0	29.6	30.9	33.0	35.1
87.5°	9.8	10.8	10.6	11.3	11.4	12.4	12.2	13.8	14.6	15.4	15.4
90°	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7	15.5	16.3	17.9
92.5°	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2	104.7	78.8	66.8
95°	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2	461.5	361.3	293.0
97.5°	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6	784.7	687.2	592.2
100°	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1	961.2	877.3	792.7
102.5°	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7	1069.3	1029.1	971.8
105°	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0	1130.5	1166.3	1157.3
107.5°	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2	1076.0	1167.9	1210.4
110°	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5	1014.1	1128.9	1198.1



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1	952.9	1068.9	1150.6
115°	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0	865.2	976.6	1065.4
117.5°	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7	804.5	900.5	981.9
120°	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3	770.0	859.5	931.1
122.5°	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7	745.2	824.9	892.0
125°	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2	712.2	782.9	841.6
127.5°	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1	680.6	746.7	801.5
130°	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9	658.4	721.9	774.9
132.5°	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5	637.6	695.2	746.2
135°	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3	605.5	657.6	704.0
137.5°	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5	576.9	620.2	659.6
140°	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7	559.9	597.4	631.6
142.5°	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2	545.6	577.9	607.5
145°	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1	527.4	552.6	574.6
147.5°	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8	512.3	531.7	548.2
150°	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9	503.8	519.3	533.9
152.5°	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4	495.3	509.5	520.9
155°	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6	482.7	494.1	503.0
157.5°	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8	470.6	479.4	486.4
160°	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3	461.5	469.6	475.3
162.5°	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2	453.6	460.5	465.5
165°	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3	442.0	446.9	450.9
167.5°	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8	430.6	434.3	437.2
170°	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6	424.0	426.5	428.1
172.5°	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7	418.2	420.0	420.9
175°	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4	409.4	411.0	411.0
177.5°	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0	405.6	405.6	405.6
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	950.3	952.7	950.6	953.4	950.6	952.7	950.3	952.4	955.4	953.4	958.1
5°	875.9	872.1	874.7	872.9	874.7	872.1	875.9	878.0	883.1	884.8	888.2
7.5°	807.1	803.5	799.4	797.4	799.4	803.5	807.1	808.5	812.8	819.1	823.9
10°	764.2	759.5	759.0	756.1	759.0	759.5	764.2	768.8	771.8	779.8	785.3
12.5°	732.6	728.3	723.5	722.3	723.5	728.3	732.6	736.6	737.5	746.7	750.4
15°	687.9	684.5	681.6	684.1	681.6	684.5	687.9	690.5	695.1	701.5	705.7
17.5°	650.8	648.0	647.4	644.3	647.4	648.0	650.8	652.2	659.8	664.0	671.2
20°	627.4	625.3	626.1	620.6	626.1	625.3	627.4	631.2	638.9	641.0	648.6
22.5°	608.8	604.6	604.1	603.0	604.1	604.6	608.8	612.2	613.8	620.3	625.6
25°	579.6	577.5	575.4	577.5	575.4	577.5	579.6	583.3	585.1	589.7	594.8
27.5°	554.1	551.5	551.0	551.2	551.0	551.5	554.1	553.8	558.3	562.1	565.7
30°	538.5	534.3	534.7	534.3	534.7	534.3	538.5	538.5	541.0	544.5	547.8
32.5°	521.5	518.7	518.1	517.3	518.1	518.7	521.5	520.9	524.1	528.2	531.9
35°	496.6	496.6	494.5	494.5	494.5	496.6	496.6	497.8	501.2	501.2	505.5
37.5°	473.1	472.7	471.4	471.7	471.4	472.7	473.1	474.2	475.3	477.1	479.8
40°	455.5	455.1	453.8	451.3	453.8	455.1	455.5	457.2	458.0	460.2	461.9
42.5°	438.5	437.2	436.6	435.7	436.6	437.2	438.5	439.6	440.1	442.9	446.3
45°	411.9	411.9	411.1	410.7	411.1	411.9	411.9	411.9	412.4	415.7	417.4
47.5°	386.0	386.8	388.4	388.2	388.4	386.8	386.0	385.3	385.5	387.2	389.1
50°	370.4	370.9	372.1	372.5	372.1	370.9	370.4	368.8	367.9	367.9	369.2
52.5°	353.2	355.6	357.2	356.9	357.2	355.6	353.2	351.8	350.3	348.2	350.2
55°	329.0	331.9	334.8	335.3	334.8	331.9	329.0	325.1	323.4	320.1	321.3
57.5°	305.0	309.2	312.3	313.2	312.3	309.2	305.0	300.4	294.9	293.3	290.9
60°	288.7	294.2	298.1	299.7	298.1	294.2	288.7	284.5	277.3	272.6	270.9
62.5°	273.1	279.3	283.2	283.5	283.2	279.3	273.1	266.5	259.3	254.0	250.6
65°	247.7	254.0	257.4	259.9	257.4	254.0	247.7	240.4	232.4	225.2	221.4
67.5°	220.2	226.6	230.3	232.4	230.3	226.6	220.2	211.3	204.0	195.7	191.2
70°	200.2	206.6	211.7	213.4	211.7	206.6	200.2	189.6	183.3	175.7	171.9
72.5°	180.6	186.3	190.4	192.3	190.4	186.3	180.6	170.7	163.3	155.7	150.5
75°	146.5	154.1	157.9	160.0	157.9	154.1	146.5	141.0	132.5	124.5	120.3
77.5°	112.9	119.9	122.2	123.3	122.2	119.9	112.9	106.5	100.1	94.2	90.1
80°	90.6	94.8	97.8	98.2	97.8	94.8	90.6	85.5	80.5	74.9	71.1
82.5°	69.6	73.1	74.1	75.2	74.1	73.1	69.6	65.2	60.8	56.7	53.5
85°	38.1	39.8	40.2	39.8	40.2	39.8	38.1	35.1	33.0	30.9	29.6
87.5°	16.1	15.7	15.9	16.6	15.9	15.7	16.1	15.4	15.4	14.6	13.8
90°	17.9	17.9	18.8	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7
92.5°	56.3	54.4	53.2	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2
95°	235.2	210.8	204.3	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2
97.5°	541.9	496.3	472.7	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6
100°	736.5	678.0	647.8	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1
102.5°	911.7	870.1	837.3	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7
105°	1131.3	1104.5	1088.2	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0
107.5°	1223.6	1223.4	1218.1	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2
110°	1234.7	1250.1	1255.8	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1204.0	1230.6	1244.8	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1
115°	1128.9	1167.9	1190.7	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0
117.5°	1045.4	1085.7	1108.3	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7
120°	991.3	1030.4	1052.4	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3
122.5°	945.7	981.5	1003.6	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7
125°	887.1	920.5	938.4	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2
127.5°	842.9	872.3	889.2	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1
130°	815.5	842.4	858.7	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9
132.5°	786.8	813.8	828.7	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5
135°	739.8	766.7	781.3	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3
137.5°	691.6	716.1	729.6	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5
140°	661.7	682.9	695.0	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7
142.5°	633.1	650.9	662.5	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2
145°	594.1	608.0	616.9	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1
147.5°	563.7	574.8	580.0	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8
150°	546.1	555.9	559.1	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9
152.5°	531.2	539.0	542.2	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4
155°	511.1	516.8	519.3	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6
157.5°	492.8	497.4	499.7	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8
160°	481.0	485.1	486.7	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3
162.5°	469.9	473.4	473.7	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2
165°	454.1	455.8	455.8	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3
167.5°	438.9	440.3	439.7	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8
170°	429.7	430.6	430.6	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6
172.5°	421.3	422.7	421.4	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7
175°	411.0	411.8	410.2	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4
177.5°	405.0	405.6	403.7	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	953.7	957.8	962.9	966.6	973.4	976.4	980.2	983.2	988.6	993.7	999.8
5°	889.5	896.7	906.4	917.0	929.3	937.8	949.6	956.8	971.2	984.3	996.9
7.5°	831.2	840.0	853.8	867.4	883.5	898.0	912.8	929.3	947.6	969.3	987.2
10°	791.2	803.1	817.9	834.9	854.4	871.2	891.1	908.9	931.4	956.8	980.5
12.5°	759.4	769.6	786.1	802.3	823.1	843.8	864.4	887.9	914.1	942.2	972.0
15°	715.4	723.9	737.4	759.9	781.1	801.4	832.3	854.4	887.4	918.7	954.6
17.5°	677.9	688.4	699.9	719.1	741.0	766.5	794.0	821.7	853.5	893.2	933.8
20°	654.9	663.4	676.5	691.3	714.6	740.0	766.3	794.2	833.2	874.2	917.8
22.5°	629.8	639.0	653.8	670.0	689.6	714.0	742.9	773.6	814.2	854.6	901.9
25°	600.3	606.7	620.2	634.6	654.1	674.8	704.9	738.7	778.9	825.1	873.3
27.5°	572.4	578.0	590.4	602.9	620.5	645.1	672.1	706.2	744.1	790.9	844.4
30°	552.4	558.4	569.4	582.9	599.9	621.5	649.0	681.2	721.8	767.5	823.5
32.5°	535.2	540.5	548.8	562.3	578.9	599.8	625.3	658.1	698.8	745.2	800.1
35°	508.4	514.4	520.7	531.3	545.7	566.0	593.9	624.8	663.8	708.7	759.0
37.5°	481.8	488.3	494.0	503.4	516.6	534.5	558.6	590.8	626.1	669.3	717.6
40°	465.3	470.3	475.0	485.2	498.3	515.2	537.7	566.5	603.7	643.9	684.1
42.5°	448.7	453.4	457.4	466.2	478.3	494.6	516.0	544.0	578.6	616.1	651.6
45°	422.5	425.5	430.2	437.7	447.5	462.3	483.1	508.0	537.2	572.8	599.5
47.5°	394.2	398.8	402.7	409.4	417.4	431.9	451.8	473.0	499.5	525.9	544.8
50°	372.5	377.2	382.7	389.1	396.6	410.3	428.4	450.0	472.5	492.8	508.8
52.5°	352.2	356.5	362.4	368.4	377.7	389.2	404.7	424.0	446.1	460.6	474.0
55°	322.2	324.2	331.1	337.0	345.8	354.3	370.0	386.9	400.5	411.5	422.5
57.5°	291.5	294.3	298.2	303.5	312.3	322.3	333.3	348.2	356.2	361.9	370.4
60°	271.8	272.6	275.2	281.5	288.3	297.2	309.9	320.5	326.4	331.1	338.3
62.5°	250.1	250.3	254.5	259.2	264.2	273.9	284.1	292.7	297.6	299.9	306.8
65°	219.7	218.9	221.4	225.2	231.1	237.5	246.4	254.0	253.6	256.1	260.3
67.5°	188.7	187.8	187.8	191.4	196.2	201.9	208.1	212.5	212.5	215.9	218.0
70°	167.6	165.1	166.8	169.7	171.9	176.5	183.3	185.0	185.4	187.1	189.2
72.5°	145.9	145.1	146.5	147.7	149.2	152.9	158.6	159.6	159.7	160.7	164.2
75°	116.0	115.1	114.3	115.6	117.2	119.8	121.9	123.6	123.2	123.6	126.1
77.5°	87.0	84.5	84.1	84.9	85.3	86.7	88.9	88.8	89.3	89.2	92.0
80°	69.0	65.6	65.2	65.2	65.6	66.4	67.3	68.2	66.9	68.2	69.0
82.5°	50.7	48.7	48.6	48.3	48.3	48.5	49.0	49.6	49.2	49.9	50.4
85°	28.0	27.1	25.8	26.7	26.3	24.9	25.8	24.5	24.1	24.5	24.9
87.5°	12.2	12.4	11.4	11.3	10.6	10.8	9.8	9.1	8.5	8.5	9.3
90°	13.9	13.0	11.4	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8
92.5°	212.4	262.4	266.6	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9
95°	705.6	721.1	588.5	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8
97.5°	892.8	770.1	525.5	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6
100°	938.4	734.9	468.8	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0
102.5°	911.1	673.1	425.8	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7
105°	823.7	590.0	384.2	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0
107.5°	734.4	533.0	366.6	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8
110°	683.6	506.2	361.3	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.9	490.6	361.3	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8
115°	604.7	473.7	363.8	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4
117.5°	580.2	465.4	369.2	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9
120°	566.5	461.5	374.4	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0
122.5°	554.7	458.2	379.0	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7
125°	538.8	454.1	386.6	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9
127.5°	524.2	452.2	395.3	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4
130°	514.4	450.9	400.5	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9
132.5°	506.5	450.9	406.3	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4
135°	497.3	450.9	414.3	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9
137.5°	489.0	451.8	421.6	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3
140°	485.1	452.5	424.9	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1
142.5°	481.8	453.1	426.8	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3
145°	477.0	452.5	428.9	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9
147.5°	471.9	450.4	429.7	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2
150°	468.0	448.4	429.7	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7
152.5°	463.4	445.9	429.1	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8
155°	455.8	441.2	427.3	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8
157.5°	448.6	436.3	425.2	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6
160°	442.8	433.0	423.2	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8
162.5°	437.6	429.1	421.3	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6
165°	429.7	423.2	418.3	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4
167.5°	422.1	417.5	413.8	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3
170°	417.5	414.3	411.8	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2
172.5°	412.9	410.3	409.2	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8
175°	406.9	406.1	406.1	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8
177.5°	404.3	403.7	403.7	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1002.8	1007.5	1010.6	1016.4	1021.1	1023.9	1026.2	1028.3	1030.6	1032.7	1038.4
5°	1009.3	1020.3	1029.6	1044.0	1057.1	1067.2	1078.2	1088.0	1096.1	1107.5	1116.4
7.5°	1006.5	1026.1	1046.5	1068.8	1091.5	1112.7	1132.2	1150.4	1166.9	1186.9	1204.4
10°	1003.8	1030.5	1056.7	1086.7	1117.6	1143.9	1168.4	1193.4	1211.6	1237.1	1258.6
12.5°	1001.8	1033.1	1064.8	1101.0	1134.9	1172.0	1204.7	1222.9	1250.6	1270.9	1296.6
15°	993.2	1034.7	1078.2	1118.9	1167.2	1201.4	1230.3	1265.8	1291.6	1317.4	1345.4
17.5°	977.9	1024.8	1073.6	1126.9	1173.2	1210.0	1247.1	1281.4	1312.2	1346.9	1381.6
20°	970.8	1017.7	1073.6	1128.2	1173.5	1212.0	1250.2	1287.8	1321.7	1366.1	1406.4
22.5°	955.9	1012.7	1064.1	1117.4	1164.0	1206.0	1249.1	1291.9	1336.9	1387.2	1437.5
25°	929.3	986.8	1041.5	1094.0	1140.9	1193.4	1239.6	1296.7	1354.3	1420.7	1483.4
27.5°	901.6	956.8	1006.8	1057.5	1112.3	1171.7	1231.6	1296.5	1371.8	1455.7	1544.1
30°	879.3	931.4	980.1	1032.1	1089.2	1156.2	1221.8	1298.9	1386.0	1480.4	1585.4
32.5°	853.2	901.2	948.5	1003.7	1065.9	1136.5	1213.0	1297.5	1402.3	1509.6	1617.6
35°	808.6	848.8	897.5	956.3	1026.6	1107.5	1196.0	1295.8	1416.1	1539.3	1630.4
37.5°	755.7	793.1	844.4	908.9	982.6	1069.3	1174.4	1292.9	1420.6	1518.8	1548.2
40°	720.2	754.8	808.2	875.1	950.4	1042.3	1157.4	1282.7	1406.4	1469.0	1444.9
42.5°	682.2	718.6	770.5	836.8	917.9	1017.9	1136.1	1261.4	1365.1	1388.8	1305.4
45°	622.3	660.0	711.2	778.1	865.4	973.7	1096.9	1210.8	1270.5	1227.7	1098.6
47.5°	566.7	602.0	649.5	718.5	808.5	920.6	1039.3	1130.1	1134.8	1032.8	894.9
50°	528.8	561.3	609.2	678.2	767.5	881.0	988.1	1059.6	1027.4	911.9	779.3
52.5°	491.5	523.4	570.6	639.0	727.2	831.2	930.8	981.0	920.5	801.8	688.6
55°	437.7	465.7	511.8	574.9	658.8	755.3	839.9	857.3	778.5	661.7	569.8
57.5°	385.2	411.3	453.3	511.4	588.0	673.5	739.7	736.1	652.8	552.5	479.6
60°	349.7	375.1	412.4	469.0	538.9	612.6	669.3	655.7	573.2	486.8	425.5
62.5°	317.9	340.6	375.8	425.3	489.1	557.4	604.0	584.0	503.1	427.5	379.0
65°	270.9	290.0	320.1	362.4	415.3	471.7	507.6	481.8	412.8	353.9	315.0
67.5°	226.2	241.4	266.6	300.4	345.5	390.8	412.7	386.7	331.5	288.5	259.7
70°	197.7	211.2	230.7	260.8	300.2	338.3	354.7	331.5	284.1	247.2	226.5
72.5°	169.3	180.4	197.5	224.5	256.1	289.2	303.6	281.4	242.4	211.3	191.9
75°	130.9	138.4	150.3	168.9	193.9	220.1	228.2	208.7	183.8	160.5	147.7
77.5°	93.7	100.1	109.1	120.8	138.5	155.2	162.2	151.0	131.7	116.9	106.5
80°	72.0	75.3	83.0	92.7	106.7	117.2	121.9	114.7	101.2	90.2	82.1
82.5°	51.3	54.7	59.3	67.3	76.2	83.4	88.4	83.6	73.8	65.1	60.4
85°	24.9	27.1	29.6	33.0	39.8	44.0	43.6	40.6	36.9	33.4	30.9
87.5°	9.1	9.8	11.2	13.1	14.5	16.0	17.0	16.5	15.5	14.6	13.8
90°	1.6	3.3	4.9	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7
92.5°	12.1	18.9	28.9	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2
95°	27.6	34.2	43.1	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2
97.5°	45.6	50.1	59.1	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6
100°	58.6	61.9	70.8	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1
102.5°	71.6	74.2	83.8	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7
105°	92.0	96.0	104.2	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0
107.5°	114.5	118.3	125.0	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2
110°	129.4	132.6	140.0	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5





TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	147.0	154.3	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1
115°	166.0	168.4	175.8	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0
117.5°	186.4	189.0	196.3	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7
120°	199.4	202.7	210.0	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3
122.5°	212.4	215.0	222.3	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7
125°	229.5	233.6	240.9	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2
127.5°	243.9	249.1	258.4	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1
130°	252.3	258.9	269.4	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9
132.5°	259.4	267.3	279.2	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5
135°	270.2	280.0	293.0	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3
137.5°	282.7	291.9	304.9	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5
140°	290.6	300.4	313.3	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7
142.5°	299.1	308.1	321.1	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2
145°	312.5	320.7	332.1	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1
147.5°	326.2	333.2	343.8	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8
150°	335.3	341.0	351.6	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9
152.5°	343.8	348.9	358.1	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4
155°	354.8	359.7	367.9	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6
157.5°	365.4	369.3	376.3	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8
160°	371.9	375.2	380.9	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3
162.5°	377.8	381.1	386.1	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2
165°	385.8	388.2	392.3	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3
167.5°	392.5	394.0	396.2	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8
170°	396.4	397.2	398.8	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6
172.5°	398.4	399.2	400.7	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7
175°	401.2	402.0	402.8	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4
177.5°	403.0	403.0	403.7	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1043.1	1045.9	1051.6	1049.5	1052.3	1053.6	1055.0
5°	1127.4	1140.9	1146.9	1146.0	1154.9	1152.8	1150.6
7.5°	1222.5	1236.8	1244.7	1254.7	1260.4	1260.8	1265.8
10°	1276.4	1295.0	1302.7	1313.2	1320.0	1323.8	1323.4
12.5°	1317.7	1332.3	1349.4	1354.5	1363.7	1368.5	1366.8
15°	1367.4	1390.7	1408.5	1417.4	1428.8	1432.2	1436.9
17.5°	1411.8	1443.0	1463.8	1491.3	1501.8	1508.1	1504.4
20°	1445.3	1486.4	1507.2	1540.2	1558.4	1568.1	1564.7
22.5°	1484.9	1529.4	1567.7	1596.4	1624.1	1637.2	1639.9
25°	1552.8	1613.8	1670.1	1707.8	1742.1	1750.1	1767.9
27.5°	1628.7	1700.6	1760.8	1800.4	1824.3	1833.3	1838.8
30°	1676.5	1748.0	1793.3	1818.7	1826.4	1825.5	1824.6
32.5°	1699.8	1744.7	1753.3	1746.2	1728.8	1714.1	1698.7
35°	1666.7	1633.3	1583.3	1519.0	1471.5	1423.8	1419.0
37.5°	1499.0	1392.0	1308.9	1216.0	1162.5	1129.4	1106.4
40°	1341.2	1219.7	1118.9	1040.6	985.9	964.4	943.2
42.5°	1169.8	1053.7	964.5	899.0	857.9	834.0	817.3
45°	950.4	848.0	778.1	730.7	698.1	679.5	668.9
47.5°	778.8	703.0	643.7	609.4	586.9	572.4	572.5
50°	686.6	614.2	574.9	547.8	528.3	516.9	519.0
52.5°	605.0	551.0	517.3	494.6	480.2	473.2	473.0
55°	505.9	466.9	444.9	428.4	418.7	410.7	412.4
57.5°	432.8	399.9	385.1	371.5	364.7	361.4	356.8
60°	387.3	362.0	349.3	338.3	331.5	329.0	324.2
62.5°	347.1	327.1	314.7	305.7	299.6	298.8	295.1
65°	291.7	276.5	265.5	261.2	254.9	253.2	253.2
67.5°	240.4	229.5	221.0	217.1	214.3	214.7	212.7
70°	208.3	199.4	193.9	189.6	187.5	187.9	186.3
72.5°	182.2	172.3	167.5	164.9	162.2	163.2	162.6
75°	138.0	132.9	130.4	127.8	126.1	125.3	124.5
77.5°	101.3	96.9	94.9	93.5	93.8	91.7	93.3
80°	78.4	74.5	73.2	71.1	70.7	70.7	70.3
82.5°	57.3	55.2	54.3	52.5	51.8	52.4	51.3
85°	29.6	28.0	27.6	27.6	26.7	25.8	28.0
87.5°	13.9	12.7	13.0	12.7	12.7	12.6	11.9
90°	15.5	16.3	17.9	17.9	17.9	18.8	18.8
92.5°	104.7	78.8	66.8	56.3	54.4	53.2	51.9
95°	461.5	361.3	293.0	235.2	210.8	204.3	191.3
97.5°	784.7	687.2	592.2	541.9	496.3	472.7	462.3
100°	961.2	877.3	792.7	736.5	678.0	647.8	634.9
102.5°	1069.3	1029.1	971.8	911.7	870.1	837.3	827.5
105°	1130.5	1166.3	1157.3	1131.3	1104.5	1088.2	1078.4
107.5°	1076.0	1167.9	1210.4	1223.6	1223.4	1218.1	1211.5
110°	1014.1	1128.9	1198.1	1234.7	1250.1	1255.8	1255.8



TEST NUMBER: P333234-930

CATALOG NUMBER: S125DIP-S850D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	952.9	1068.9	1150.6	1204.0	1230.6	1244.8	1250.6
115°	865.2	976.6	1065.4	1128.9	1167.9	1190.7	1201.3
117.5°	804.5	900.5	981.9	1045.4	1085.7	1108.3	1114.8
120°	770.0	859.5	931.1	991.3	1030.4	1052.4	1058.9
122.5°	745.2	824.9	892.0	945.7	981.5	1003.6	1009.4
125°	712.2	782.9	841.6	887.1	920.5	938.4	946.6
127.5°	680.6	746.7	801.5	842.9	872.3	889.2	892.8
130°	658.4	721.9	774.9	815.5	842.4	858.7	863.6
132.5°	637.6	695.2	746.2	786.8	813.8	828.7	834.2
135°	605.5	657.6	704.0	739.8	766.7	781.3	786.2
137.5°	576.9	620.2	659.6	691.6	716.1	729.6	734.9
140°	559.9	597.4	631.6	661.7	682.9	695.0	699.1
142.5°	545.6	577.9	607.5	633.1	650.9	662.5	665.9
145°	527.4	552.6	574.6	594.1	608.0	616.9	620.2
147.5°	512.3	531.7	548.2	563.7	574.8	580.0	581.5
150°	503.8	519.3	533.9	546.1	555.9	559.1	559.9
152.5°	495.3	509.5	520.9	531.2	539.0	542.2	543.0
155°	482.7	494.1	503.0	511.1	516.8	519.3	520.1
157.5°	470.6	479.4	486.4	492.8	497.4	499.7	499.5
160°	461.5	469.6	475.3	481.0	485.1	486.7	485.9
162.5°	453.6	460.5	465.5	469.9	473.4	473.7	473.5
165°	442.0	446.9	450.9	454.1	455.8	455.8	455.8
167.5°	430.6	434.3	437.2	438.9	440.3	439.7	439.5
170°	424.0	426.5	428.1	429.7	430.6	430.6	429.7
172.5°	418.2	420.0	420.9	421.3	422.7	421.4	420.6
175°	409.4	411.0	411.0	411.0	411.8	410.2	409.4
177.5°	405.6	405.6	405.6	405.0	405.6	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7

(END OF REPORT)