

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333587-840

Luminaire Tested: **S125RDIP-S1090D590U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333587-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D590U840-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6369.1 lumens  
Efficiency: N/A  
Efficacy: 130.5 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	98	94	91	96	93	89	86	83	80	78	73	72	70	65	63	62	58
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	58	55	53	50
3	86	76	69	63	81	72	66	61	65	60	56	58	54	51	52	48	46	43
4	79	68	60	54	74	64	57	52	58	52	48	52	47	44	46	43	40	37
5	72	61	53	47	68	58	50	45	52	46	42	47	42	38	42	38	35	32
6	67	55	47	41	63	52	45	39	47	41	36	43	38	34	38	34	31	28
7	62	50	42	36	58	47	40	35	43	37	32	39	34	30	35	31	28	25
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	22	20
10	50	38	31	26	48	36	30	25	33	28	24	30	25	22	28	23	20	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10723	10723	10723	10723
5°	12337	10738	9483	10738
10°	14152	10683	8368	10683
15°	15285	10573	7438	10573
20°	16855	10446	6868	10446
25°	19506	10278	6372	10278
30°	21227	10100	6049	10100
35°	17906	9894	5750	9894
40°	12505	9522	5493	9522
45°	9276	9020	5242	9020
50°	7396	8499	5027	8499
55°	6277	7851	4835	7851
60°	5424	7272	4525	7272
65°	4834	6645	3895	6645
70°	4247	6086	3552	6086
75°	3673	5273	3334	5273
80°	2786	4437	2786	4437
85°	2319	3490	2623	3490



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.2	2.5
10°-20°	466.6	7.3
20°-30°	739.8	11.6
30°-40°	892.2	14.0
40°-50°	796.7	12.5
50°-60°	611.0	9.6
60°-70°	397.1	6.2
70°-80°	193.0	3.0
80°-90°	47.7	0.7
90°-100°	49.6	0.8
100°-110°	146.4	2.3
110°-120°	248.0	3.9
120°-130°	326.4	5.1
130°-140°	365.7	5.7
140°-150°	358.4	5.6
150°-160°	301.1	4.7
160°-170°	200.1	3.1
170°-180°	70.0	1.1
0°-30°	1365.7	21.4
0°-40°	2257.9	35.5
0°-60°	3665.6	57.6
0°-90°	4303.4	67.6
90°-120°	444.0	7.0
90°-150°	1494.5	23.5
90°-180°	2066.0	32.4
0°-180°	6369.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1660	1660	1660	1660	1660	
5°	1903	1656	1463	1656	1903	190
15°	2286	1581	1112	1581	2286	655
25°	2737	1442	894	1442	2737	1257
35°	2271	1255	729	1255	2271	1372
45°	1016	988	574	988	1016	810
55°	558	697	429	697	558	506
65°	316	435	255	435	316	315
75°	147	211	134	211	147	157
85°	31	47	35	47	31	36
90°	14	1	14	1	14	10
95°	50	38	50	38	50	50
105°	143	131	143	131	143	151
115°	251	248	251	248	251	248
125°	365	362	365	362	365	326
135°	473	471	473	471	473	365
145°	573	571	573	571	573	358
155°	653	653	653	653	653	301
165°	709	710	709	710	709	200
175°	736	738	736	738	736	70
180°	740	740	740	740	740	



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1746.6	1745.5	1747.7	1741.6	1742.2	1732.9	1732.9	1725.9	1716.6	1709.5	1706.2
5°	1903.0	1904.4	1901.7	1891.5	1884.6	1874.4	1862.8	1842.4	1825.3	1809.0	1796.0
7.5°	2064.2	2065.1	2056.1	2053.0	2035.8	2023.3	1997.5	1969.6	1945.0	1913.7	1889.7
10°	2158.0	2157.3	2147.7	2140.2	2125.3	2106.2	2080.9	2048.2	2017.5	1983.5	1950.8
12.5°	2212.5	2210.7	2207.7	2198.6	2184.6	2167.8	2146.4	2114.2	2076.4	2039.1	2000.9
15°	2286.1	2281.3	2272.5	2260.9	2241.1	2221.3	2197.5	2168.9	2132.7	2090.4	2055.1
17.5°	2377.1	2377.3	2363.7	2347.5	2320.7	2285.8	2249.0	2202.8	2153.7	2107.3	2069.5
20°	2452.4	2450.3	2436.7	2405.4	2374.7	2331.1	2288.9	2232.2	2172.2	2111.6	2064.6
22.5°	2560.4	2555.1	2540.8	2499.7	2452.2	2396.0	2331.4	2262.2	2189.7	2120.8	2059.1
25°	2737.3	2733.2	2705.2	2657.6	2590.8	2504.2	2419.6	2324.9	2220.7	2130.0	2055.1
27.5°	2858.3	2853.9	2833.2	2793.5	2731.9	2640.8	2526.4	2399.7	2269.6	2144.9	2036.8
30°	2846.4	2856.6	2853.9	2835.5	2789.1	2707.3	2601.7	2459.2	2304.5	2158.0	2029.1
32.5°	2675.1	2684.3	2708.3	2744.4	2747.1	2714.4	2635.4	2504.0	2343.8	2177.1	2023.2
35°	2271.1	2283.4	2329.8	2402.7	2498.1	2577.8	2594.1	2523.2	2379.4	2200.2	2014.2
37.5°	1746.0	1813.0	1852.1	1928.8	2073.1	2219.7	2360.8	2412.8	2351.5	2190.7	1999.5
40°	1483.2	1499.5	1569.0	1655.6	1777.0	1929.7	2130.7	2275.8	2280.7	2168.9	1976.6
42.5°	1269.4	1290.1	1337.9	1406.9	1510.9	1663.6	1871.2	2062.6	2151.4	2108.9	1946.6
45°	1015.6	1031.3	1066.0	1119.2	1198.9	1325.0	1503.6	1725.2	1901.0	1969.8	1866.2
47.5°	834.2	842.7	873.0	913.5	972.5	1064.4	1202.6	1394.9	1605.9	1753.7	1739.2
50°	736.1	745.7	768.8	799.5	849.3	927.0	1037.4	1197.6	1415.0	1595.6	1631.7
52.5°	659.7	667.7	682.2	711.1	752.2	811.9	901.1	1046.0	1241.6	1433.7	1517.2
55°	557.5	563.0	574.6	591.0	623.7	666.6	743.7	843.8	1002.0	1195.5	1318.2
57.5°	473.3	476.1	483.4	498.6	521.2	552.5	608.1	693.1	806.5	980.8	1116.2
60°	419.9	422.6	432.1	442.3	460.1	488.7	532.3	591.6	700.6	844.6	981.5
62.5°	377.3	379.0	383.0	393.2	408.8	430.9	465.2	513.6	600.4	726.7	856.1
65°	316.3	316.9	318.3	326.5	336.0	352.3	374.9	409.0	474.4	569.9	684.3
67.5°	257.6	258.6	263.4	266.2	276.2	284.8	298.0	324.1	370.1	434.4	523.5
70°	224.9	224.3	229.0	232.5	235.8	246.1	254.9	276.1	304.7	353.8	428.1
72.5°	194.4	192.6	194.7	195.9	200.4	207.3	216.2	229.1	251.3	285.1	341.9
75°	147.2	147.9	147.9	149.3	152.7	155.4	158.1	164.9	177.2	199.8	230.4
77.5°	103.3	102.2	105.1	105.5	107.6	110.6	112.9	115.6	120.7	129.9	145.7
80°	74.9	74.9	75.6	77.7	77.1	78.4	81.8	84.5	90.7	96.1	101.6
82.5°	57.6	57.0	57.7	58.1	58.0	59.3	60.5	61.1	63.4	66.1	69.9
85°	31.3	31.3	32.0	32.0	32.7	32.7	33.4	33.4	33.4	34.0	34.7
87.5°	14.7	14.1	13.5	13.4	13.9	14.9	14.2	13.5	13.4	13.3	13.6
90°	13.8	13.4	13.0	12.7	12.3	11.8	11.1	10.5	9.9	9.2	8.3
92.5°	27.2	26.9	26.7	26.4	26.1	25.5	24.6	23.8	22.9	22.1	21.0
95°	49.6	49.3	49.1	48.8	48.5	48.0	47.1	46.2	45.2	44.3	43.1
97.5°	75.1	74.9	74.8	74.6	74.5	74.0	73.2	72.3	71.5	70.6	68.9
100°	94.5	94.2	94.0	93.7	93.4	92.7	91.6	90.5	89.3	88.2	86.4
102.5°	113.8	113.5	113.1	112.8	112.4	111.6	110.4	109.1	107.9	106.5	105.7
105°	142.9	142.5	142.1	141.7	141.4	140.8	140.0	139.3	138.5	137.6	136.9
107.5°	172.6	172.6	172.7	172.7	172.7	172.5	172.2	171.8	171.4	171.0	170.4
110°	194.7	194.8	195.0	195.1	195.2	195.1	194.7	194.3	194.0	193.6	193.2



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	216.4	216.6	216.8	217.1	217.3	217.3	217.1	217.0	216.8	216.6	216.1
115°	250.6	250.7	250.9	251.0	251.2	251.3	251.4	251.5	251.7	251.8	251.5
117.5°	284.0	284.6	285.1	285.6	286.1	286.3	286.2	286.1	286.0	285.9	285.6
120°	307.1	307.6	308.1	308.6	309.1	309.3	309.3	309.3	309.3	309.3	309.2
122.5°	330.1	330.5	330.9	331.3	331.7	332.0	332.1	332.2	332.3	332.4	332.0
125°	364.7	364.8	365.0	365.1	365.2	365.4	365.7	365.9	366.2	366.4	366.3
127.5°	397.9	398.1	398.4	398.6	398.9	399.1	399.2	399.3	399.5	399.6	399.4
130°	420.0	420.2	420.5	420.7	421.0	421.2	421.3	421.4	421.6	421.7	421.4
132.5°	440.7	441.1	441.4	441.8	442.1	442.4	442.5	442.6	442.8	442.9	442.9
135°	473.0	473.5	474.0	474.5	475.0	475.2	475.2	475.2	475.2	475.2	475.1
137.5°	504.5	505.2	505.8	506.4	507.2	507.4	507.2	507.1	506.9	506.8	506.4
140°	524.8	525.4	526.1	526.7	527.4	527.6	527.4	527.0	526.8	526.5	526.1
142.5°	544.2	544.8	545.4	546.1	546.7	546.9	546.8	546.6	546.5	546.3	545.9
145°	573.2	573.6	574.0	574.4	574.7	574.9	574.9	574.9	574.9	574.9	574.6
147.5°	598.0	598.8	599.8	600.6	601.5	601.8	601.5	601.2	600.9	600.6	600.3
150°	616.4	616.7	616.9	617.2	617.4	617.5	617.5	617.5	617.5	617.5	617.0
152.5°	631.7	632.1	632.6	633.0	633.5	633.6	633.3	633.0	632.7	632.4	632.1
155°	653.3	653.9	654.6	655.2	655.9	655.9	655.4	654.9	654.4	653.9	653.8
157.5°	671.4	672.3	673.1	673.9	674.8	674.9	674.4	673.9	673.4	672.9	672.8
160°	683.9	684.5	685.1	685.8	686.4	686.4	685.9	685.4	684.9	684.4	684.3
162.5°	694.4	695.2	695.9	696.7	697.4	697.5	696.8	696.2	695.6	695.0	695.0
165°	708.6	709.3	710.1	710.9	711.7	711.9	711.2	710.7	710.2	709.7	709.6
167.5°	719.9	720.6	721.4	722.3	723.1	723.1	722.4	721.5	720.7	720.0	720.0
170°	725.9	726.8	727.7	728.6	729.4	729.5	728.7	728.0	727.2	726.5	726.5
172.5°	730.9	731.7	732.6	733.4	734.2	734.2	733.4	732.7	731.8	731.0	731.0
175°	735.7	736.6	737.5	738.4	739.2	739.3	738.5	737.8	737.0	736.3	736.3
177.5°	738.4	739.1	739.9	740.6	741.3	741.3	740.7	740.1	739.5	738.9	739.0
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1706.2	1702.3	1695.3	1688.7	1680.5	1673.4	1668.6	1662.5	1655.0	1645.7	1638.0
5°	1781.7	1766.7	1747.0	1729.9	1708.1	1691.0	1673.3	1656.3	1639.2	1617.4	1598.3
7.5°	1865.4	1834.4	1804.3	1766.5	1732.1	1701.4	1671.9	1642.1	1613.0	1582.0	1552.2
10°	1916.6	1879.2	1837.6	1789.9	1746.3	1704.7	1666.5	1629.0	1589.5	1554.7	1517.2
12.5°	1964.7	1916.2	1868.7	1808.5	1756.1	1705.3	1656.7	1609.9	1567.7	1522.6	1482.4
15°	2008.0	1960.2	1907.1	1833.5	1760.6	1699.2	1641.9	1581.3	1528.8	1478.3	1433.4
17.5°	2024.8	1974.7	1913.0	1842.2	1762.5	1685.4	1611.5	1545.1	1483.3	1424.5	1373.9
20°	2018.2	1969.8	1906.4	1839.0	1753.7	1673.3	1593.6	1519.9	1451.2	1389.1	1335.2
22.5°	2002.4	1952.4	1891.2	1819.9	1739.0	1653.7	1568.5	1490.0	1417.9	1353.6	1294.9
25°	1978.7	1910.6	1847.9	1778.3	1701.3	1616.8	1528.8	1442.3	1365.2	1299.8	1235.8
27.5°	1954.0	1869.0	1789.2	1720.1	1638.7	1563.3	1478.5	1389.8	1308.8	1242.1	1176.4
30°	1931.7	1836.2	1748.3	1669.9	1592.9	1521.4	1440.9	1354.3	1271.2	1202.3	1135.6
32.5°	1903.8	1802.4	1705.8	1615.4	1541.1	1470.1	1397.2	1314.5	1233.6	1162.6	1094.7
35°	1869.0	1739.5	1634.5	1538.3	1455.9	1387.0	1321.6	1254.9	1173.8	1100.1	1034.0
37.5°	1823.1	1676.2	1554.7	1450.1	1363.0	1293.9	1242.2	1181.2	1107.2	1036.7	975.3
40°	1795.3	1630.4	1497.4	1393.9	1302.5	1229.6	1181.2	1129.4	1062.0	995.8	934.4
42.5°	1758.3	1588.4	1439.7	1331.7	1239.8	1169.6	1120.6	1075.4	1018.9	956.5	890.8
45°	1685.6	1507.0	1350.9	1235.1	1142.4	1073.5	1027.8	987.6	944.7	887.5	830.2
47.5°	1590.9	1422.1	1258.8	1132.3	1041.5	977.5	933.2	901.5	870.8	822.1	766.5
50°	1515.2	1352.3	1192.8	1070.2	973.3	912.6	871.1	845.9	817.9	773.7	727.3
52.5°	1425.7	1280.3	1124.1	998.7	907.4	850.5	810.5	785.4	762.3	726.2	682.0
55°	1284.9	1157.4	1014.2	900.4	816.6	759.3	721.1	697.3	683.7	653.0	618.2
57.5°	1122.2	1030.9	904.6	794.9	720.7	664.2	636.2	615.9	600.5	578.9	554.3
60°	1008.8	944.7	831.5	727.3	659.1	605.2	580.1	563.0	548.7	530.3	511.2
62.5°	893.7	847.1	748.7	659.1	596.4	551.3	527.7	512.3	495.8	483.4	464.8
65°	739.5	697.9	629.8	559.6	501.7	465.5	448.5	434.8	424.6	411.0	398.1
67.5°	575.3	558.4	511.3	462.9	421.3	389.2	374.5	365.0	352.6	344.5	335.6
70°	474.4	466.3	432.8	400.8	361.9	340.1	326.5	322.3	307.4	299.2	293.1
72.5°	385.0	381.1	361.9	339.7	312.4	293.3	280.6	276.1	266.5	259.9	256.0
75°	263.8	265.2	261.8	247.4	237.2	224.9	214.0	211.3	204.5	199.0	195.6
77.5°	166.8	173.8	174.1	173.4	169.4	161.8	157.3	155.3	148.6	146.5	145.7
80°	114.5	122.0	128.9	128.2	126.7	124.7	121.3	119.3	115.8	113.8	112.5
82.5°	76.3	83.3	89.0	92.7	92.4	90.4	88.1	87.2	86.4	84.9	84.6
85°	36.2	37.5	39.5	44.3	47.7	48.4	47.7	47.1	44.9	45.6	46.4
87.5°	14.0	13.8	14.2	14.0	13.2	15.8	17.3	17.6	16.7	15.8	14.9
90°	7.5	6.6	5.7	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	19.9	18.8	17.7	16.8	16.1	15.3	14.6	13.9	14.6	15.3	16.1
95°	41.8	40.5	39.3	38.5	38.2	38.0	37.7	37.5	37.7	38.0	38.2
97.5°	67.1	65.3	63.5	62.6	62.5	62.4	62.3	62.2	62.3	62.4	62.5
100°	84.8	83.1	81.5	80.7	80.7	80.7	80.7	80.7	80.7	80.7	80.7
102.5°	104.9	104.0	103.2	102.5	102.0	101.5	101.0	100.5	101.0	101.5	102.0
105°	136.1	135.4	134.6	133.9	133.3	132.6	132.0	131.4	132.0	132.6	133.3
107.5°	169.8	169.3	168.6	168.0	167.3	166.7	166.1	165.4	166.1	166.7	167.3
110°	192.8	192.4	192.1	191.6	190.9	190.3	189.6	188.9	189.6	190.3	190.9





TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	215.6	215.2	214.7	214.3	213.9	213.6	213.3	212.9	213.3	213.6	213.9
115°	251.3	251.0	250.7	250.3	249.8	249.3	248.8	248.3	248.8	249.3	249.8
117.5°	285.4	285.2	285.0	284.7	284.5	284.3	284.0	283.8	284.0	284.3	284.5
120°	309.1	309.0	308.8	308.5	307.8	307.2	306.6	305.9	306.6	307.2	307.8
122.5°	331.7	331.4	331.0	330.8	330.5	330.3	330.1	329.9	330.1	330.3	330.5
125°	366.2	366.0	365.9	365.5	364.7	363.9	363.1	362.3	363.1	363.9	364.7
127.5°	399.3	399.1	399.0	398.7	398.2	397.8	397.4	397.0	397.4	397.8	398.2
130°	421.2	420.9	420.7	420.2	419.6	419.0	418.3	417.7	418.3	419.0	419.6
132.5°	443.0	443.0	443.1	442.6	441.5	440.5	439.5	438.4	439.5	440.5	441.5
135°	475.0	474.9	474.7	474.3	473.5	472.8	472.0	471.2	472.0	472.8	473.5
137.5°	506.1	505.9	505.6	505.1	504.3	503.6	502.9	502.1	502.9	503.6	504.3
140°	525.8	525.4	525.0	524.5	523.8	523.2	522.6	521.9	522.6	523.2	523.8
142.5°	545.4	544.9	544.4	543.9	543.4	542.8	542.3	541.8	542.3	542.8	543.4
145°	574.2	573.8	573.4	573.0	572.5	572.0	571.4	570.9	571.4	572.0	572.5
147.5°	600.0	599.6	599.3	599.1	598.7	598.4	598.1	597.8	598.1	598.4	598.7
150°	616.5	616.0	615.5	615.3	615.5	615.6	615.7	615.8	615.7	615.6	615.5
152.5°	631.9	631.7	631.5	631.3	631.2	631.0	630.8	630.6	630.8	631.0	631.2
155°	653.6	653.5	653.4	653.3	653.3	653.3	653.3	653.3	653.3	653.3	653.3
157.5°	672.7	672.5	672.4	672.5	672.8	673.0	673.3	673.6	673.3	673.0	672.8
160°	684.2	684.0	683.9	684.0	684.4	684.8	685.2	685.6	685.2	684.8	684.4
162.5°	695.0	694.9	694.9	695.0	695.3	695.6	695.9	696.2	695.9	695.6	695.3
165°	709.5	709.3	709.2	709.3	709.5	709.8	710.0	710.3	710.0	709.8	709.5
167.5°	720.0	720.0	720.0	720.2	720.7	721.2	721.9	722.4	721.9	721.2	720.7
170°	726.5	726.5	726.5	726.7	727.2	727.7	728.2	728.7	728.2	727.7	727.2
172.5°	731.0	731.0	731.0	731.3	731.8	732.4	732.9	733.4	732.9	732.4	731.8
175°	736.3	736.3	736.3	736.5	737.0	737.5	738.0	738.5	738.0	737.5	737.0
177.5°	739.1	739.2	739.3	739.5	740.0	740.4	740.8	741.2	740.8	740.4	740.0
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1632.5	1625.0	1619.5	1608.6	1600.9	1597.7	1591.6	1590.0	1596.0	1591.6	1591.1
5°	1584.1	1564.3	1548.6	1532.9	1515.9	1505.0	1488.6	1485.9	1481.8	1475.6	1474.3
7.5°	1525.8	1500.1	1479.9	1454.0	1431.5	1413.4	1392.9	1383.2	1378.0	1370.0	1359.4
10°	1486.5	1455.9	1428.7	1402.7	1374.8	1352.3	1331.8	1316.2	1306.0	1296.4	1292.3
12.5°	1447.8	1416.6	1381.7	1350.4	1319.2	1293.9	1271.3	1261.1	1249.8	1238.6	1229.1
15°	1387.8	1346.2	1308.0	1271.8	1245.3	1218.0	1196.2	1181.2	1164.2	1159.4	1141.0
17.5°	1323.9	1283.1	1238.5	1200.4	1169.6	1139.6	1115.6	1098.6	1085.8	1068.2	1059.8
20°	1284.1	1235.8	1192.1	1157.4	1123.3	1087.8	1063.3	1048.9	1036.7	1022.4	1015.6
22.5°	1241.6	1194.3	1149.6	1108.8	1074.2	1039.4	1021.9	1007.0	993.1	979.9	970.9
25°	1179.1	1131.5	1084.4	1042.2	1006.0	980.8	960.4	943.3	935.8	922.9	913.3
27.5°	1117.4	1066.7	1017.9	975.7	947.5	922.5	905.7	892.2	878.7	867.4	859.1
30°	1077.6	1025.8	972.6	939.3	909.3	885.3	867.0	854.0	843.8	833.6	827.5
32.5°	1037.8	984.4	937.2	901.1	872.7	852.1	833.1	820.8	810.0	798.7	791.4
35°	974.0	919.5	881.3	845.9	817.9	798.8	785.9	768.2	759.3	751.1	743.7
37.5°	914.7	864.0	822.7	791.6	767.3	748.4	731.6	722.1	711.1	703.8	697.5
40°	871.1	824.8	787.3	754.6	736.8	715.7	700.0	687.7	679.5	670.0	663.2
42.5°	831.8	788.7	752.3	722.9	700.8	683.0	667.8	655.6	645.2	638.4	632.7
45°	776.4	733.4	697.9	670.7	650.3	633.2	617.5	611.4	597.7	589.6	586.8
47.5°	718.9	680.5	646.3	621.2	600.3	584.1	569.4	556.8	549.4	541.3	536.9
50°	680.2	643.4	611.4	586.8	566.4	548.7	535.0	526.8	516.6	509.2	503.7
52.5°	641.6	607.4	575.4	552.0	534.2	516.5	501.3	493.1	483.4	478.6	474.8
55°	586.2	550.1	522.8	499.6	481.2	464.8	450.5	442.3	436.3	431.4	430.1
57.5°	523.5	494.8	469.5	448.6	429.5	414.1	401.6	393.8	388.4	387.7	383.6
60°	482.6	456.7	433.5	411.0	394.7	380.3	369.4	360.5	355.1	354.5	353.0
62.5°	441.7	416.9	395.4	375.6	360.8	347.1	336.7	326.8	323.5	320.1	317.1
65°	381.0	358.5	340.8	325.1	309.4	297.8	287.6	281.6	274.0	269.9	262.5
67.5°	321.4	304.0	287.0	273.8	261.5	250.4	242.0	232.9	227.8	224.5	219.0
70°	282.2	268.5	251.6	237.2	227.6	218.8	212.0	201.8	198.3	195.6	192.9
72.5°	245.1	233.1	218.8	207.2	197.6	189.3	181.5	176.6	173.3	170.6	169.0
75°	192.9	181.3	169.1	160.9	154.0	147.2	143.1	139.8	138.4	137.6	134.9
77.5°	141.7	135.5	125.7	119.2	114.6	111.9	108.3	106.4	106.3	103.3	102.4
80°	108.4	104.9	96.7	94.0	90.7	88.0	85.8	82.5	79.1	77.7	75.6
82.5°	80.6	77.2	73.9	69.5	66.7	65.0	63.0	61.7	62.2	60.3	59.3
85°	42.9	39.5	38.2	37.5	36.2	37.5	36.8	36.2	35.4	34.7	35.4
87.5°	14.5	14.7	14.4	15.7	14.2	14.9	15.0	14.6	14.7	14.9	14.4
90°	4.6	5.7	6.6	7.5	8.3	9.2	9.9	10.5	11.1	11.8	12.3
92.5°	16.8	17.7	18.8	19.9	21.0	22.1	22.9	23.8	24.6	25.5	26.1
95°	38.5	39.3	40.5	41.8	43.1	44.3	45.2	46.2	47.1	48.0	48.5
97.5°	62.6	63.5	65.3	67.1	68.9	70.6	71.5	72.3	73.2	74.0	74.5
100°	80.7	81.5	83.1	84.8	86.4	88.2	89.3	90.5	91.6	92.7	93.4
102.5°	102.5	103.2	104.0	104.9	105.7	106.5	107.9	109.1	110.4	111.6	112.4
105°	133.9	134.6	135.4	136.1	136.9	137.6	138.5	139.3	140.0	140.8	141.4
107.5°	168.0	168.6	169.3	169.8	170.4	171.0	171.4	171.8	172.2	172.5	172.7
110°	191.6	192.1	192.4	192.8	193.2	193.6	194.0	194.3	194.7	195.1	195.2



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	214.3	214.7	215.2	215.6	216.1	216.6	216.8	217.0	217.1	217.3	217.3
115°	250.3	250.7	251.0	251.3	251.5	251.8	251.7	251.5	251.4	251.3	251.2
117.5°	284.7	285.0	285.2	285.4	285.6	285.9	286.0	286.1	286.2	286.3	286.1
120°	308.5	308.8	309.0	309.1	309.2	309.3	309.3	309.3	309.3	309.3	309.1
122.5°	330.8	331.0	331.4	331.7	332.0	332.4	332.3	332.2	332.1	332.0	331.7
125°	365.5	365.9	366.0	366.2	366.3	366.4	366.2	365.9	365.7	365.4	365.2
127.5°	398.7	399.0	399.1	399.3	399.4	399.6	399.5	399.3	399.2	399.1	398.9
130°	420.2	420.7	420.9	421.2	421.4	421.7	421.6	421.4	421.3	421.2	421.0
132.5°	442.6	443.1	443.0	443.0	442.9	442.9	442.8	442.6	442.5	442.4	442.1
135°	474.3	474.7	474.9	475.0	475.1	475.2	475.2	475.2	475.2	475.2	475.0
137.5°	505.1	505.6	505.9	506.1	506.4	506.8	506.9	507.1	507.2	507.4	507.2
140°	524.5	525.0	525.4	525.8	526.1	526.5	526.8	527.0	527.4	527.6	527.4
142.5°	543.9	544.4	544.9	545.4	545.9	546.3	546.5	546.6	546.8	546.9	546.7
145°	573.0	573.4	573.8	574.2	574.6	574.9	574.9	574.9	574.9	574.9	574.7
147.5°	599.1	599.3	599.6	600.0	600.3	600.6	600.9	601.2	601.5	601.8	601.5
150°	615.3	615.5	616.0	616.5	617.0	617.5	617.5	617.5	617.5	617.5	617.4
152.5°	631.3	631.5	631.7	631.9	632.1	632.4	632.7	633.0	633.3	633.6	633.5
155°	653.3	653.4	653.5	653.6	653.8	653.9	654.4	654.9	655.4	655.9	655.9
157.5°	672.5	672.4	672.5	672.7	672.8	672.9	673.4	673.9	674.4	674.9	674.8
160°	684.0	683.9	684.0	684.2	684.3	684.4	684.9	685.4	685.9	686.4	686.4
162.5°	695.0	694.9	694.9	695.0	695.0	695.0	695.6	696.2	696.8	697.5	697.4
165°	709.3	709.2	709.3	709.5	709.6	709.7	710.2	710.7	711.2	711.9	711.7
167.5°	720.2	720.0	720.0	720.0	720.0	720.0	720.7	721.5	722.4	723.1	723.1
170°	726.7	726.5	726.5	726.5	726.5	726.5	727.2	728.0	728.7	729.5	729.4
172.5°	731.3	731.0	731.0	731.0	731.0	731.0	731.8	732.7	733.4	734.2	734.2
175°	736.5	736.3	736.3	736.3	736.3	736.3	737.0	737.8	738.5	739.3	739.2
177.5°	739.5	739.3	739.2	739.1	739.0	738.9	739.5	740.1	740.7	741.3	741.3
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1590.5	1584.6	1583.0	1585.1	1583.0	1584.6	1590.5	1591.1	1591.6	1596.0	1590.0
5°	1467.5	1460.7	1464.1	1462.7	1464.1	1460.7	1467.5	1474.3	1475.6	1481.8	1485.9
7.5°	1359.3	1350.8	1341.8	1344.6	1341.8	1350.8	1359.3	1359.4	1370.0	1378.0	1383.2
10°	1283.4	1276.7	1272.5	1276.0	1272.5	1276.7	1283.4	1292.3	1296.4	1306.0	1316.2
12.5°	1219.6	1215.6	1212.0	1210.5	1212.0	1215.6	1219.6	1229.1	1238.6	1249.8	1261.1
15°	1132.9	1124.7	1121.3	1112.4	1121.3	1124.7	1132.9	1141.0	1159.4	1164.2	1181.2
17.5°	1052.8	1050.1	1041.2	1037.4	1041.2	1050.1	1052.8	1059.8	1068.2	1085.8	1098.6
20°	1005.3	1002.6	993.8	999.3	993.8	1002.6	1005.3	1015.6	1022.4	1036.7	1048.9
22.5°	966.1	960.1	957.3	955.6	957.3	960.1	966.1	970.9	979.9	993.1	1007.0
25°	910.6	901.7	898.4	894.2	898.4	901.7	910.6	913.3	922.9	935.8	943.3
27.5°	855.3	850.5	846.0	845.0	846.0	850.5	855.3	859.1	867.4	878.7	892.2
30°	819.3	814.6	811.1	811.1	811.1	814.6	819.3	827.5	833.6	843.8	854.0
32.5°	787.1	783.5	780.0	779.5	780.0	783.5	787.1	791.4	798.7	810.0	820.8
35°	740.2	734.8	733.4	729.3	733.4	734.8	740.2	743.7	751.1	759.3	768.2
37.5°	691.6	687.0	686.9	686.5	686.9	687.0	691.6	697.5	703.8	711.1	722.1
40°	660.5	657.0	656.4	651.6	656.4	657.0	660.5	663.2	670.0	679.5	687.7
42.5°	627.2	625.4	623.1	621.1	623.1	625.4	627.2	632.7	638.4	645.2	655.6
45°	582.1	577.3	577.3	573.9	577.3	577.3	582.1	586.8	589.6	597.7	611.4
47.5°	535.4	531.8	532.2	528.7	532.2	531.8	535.4	536.9	541.3	549.4	556.8
50°	504.4	502.3	501.7	500.3	501.7	502.3	504.4	503.7	509.2	516.6	526.8
52.5°	473.3	472.3	474.9	471.9	474.9	472.3	473.3	474.8	478.6	483.4	493.1
55°	431.4	429.4	433.5	429.4	433.5	429.4	431.4	430.1	431.4	436.3	442.3
57.5°	383.3	381.4	385.1	383.0	385.1	381.4	383.3	383.6	387.7	388.4	393.8
60°	351.7	347.6	349.6	350.3	349.6	347.6	351.7	353.0	354.5	355.1	360.5
62.5°	314.1	311.6	313.2	310.0	313.2	311.6	314.1	317.1	320.1	323.5	326.8
65°	261.1	259.0	256.3	254.9	256.3	259.0	261.1	262.5	269.9	274.0	281.6
67.5°	219.3	214.4	214.3	215.4	214.3	214.4	219.3	219.0	224.5	227.8	232.9
70°	188.8	188.8	188.1	188.1	188.1	188.8	188.8	192.9	195.6	198.3	201.8
72.5°	167.5	167.0	165.7	165.2	165.7	167.0	167.5	169.0	170.6	173.3	176.6
75°	134.9	135.6	134.3	133.6	134.3	135.6	134.9	134.9	137.6	138.4	139.8
77.5°	99.7	96.7	98.3	96.7	98.3	96.7	99.7	102.4	103.3	106.3	106.4
80°	75.6	74.9	77.1	74.9	77.1	74.9	75.6	75.6	77.7	79.1	82.5
82.5°	59.9	59.2	60.1	58.6	60.1	59.2	59.9	59.3	60.3	62.2	61.7
85°	36.2	35.4	34.7	35.4	34.7	35.4	36.2	35.4	34.7	35.4	36.2
87.5°	15.0	14.6	14.6	14.7	14.6	14.6	15.0	14.4	14.9	14.7	14.6
90°	12.7	13.0	13.4	13.8	13.4	13.0	12.7	12.3	11.8	11.1	10.5
92.5°	26.4	26.7	26.9	27.2	26.9	26.7	26.4	26.1	25.5	24.6	23.8
95°	48.8	49.1	49.3	49.6	49.3	49.1	48.8	48.5	48.0	47.1	46.2
97.5°	74.6	74.8	74.9	75.1	74.9	74.8	74.6	74.5	74.0	73.2	72.3
100°	93.7	94.0	94.2	94.5	94.2	94.0	93.7	93.4	92.7	91.6	90.5
102.5°	112.8	113.1	113.5	113.8	113.5	113.1	112.8	112.4	111.6	110.4	109.1
105°	141.7	142.1	142.5	142.9	142.5	142.1	141.7	141.4	140.8	140.0	139.3
107.5°	172.7	172.7	172.6	172.6	172.6	172.7	172.7	172.7	172.5	172.2	171.8
110°	195.1	195.0	194.8	194.7	194.8	195.0	195.1	195.2	195.1	194.7	194.3



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	217.1	216.8	216.6	216.4	216.6	216.8	217.1	217.3	217.3	217.1	217.0
115°	251.0	250.9	250.7	250.6	250.7	250.9	251.0	251.2	251.3	251.4	251.5
117.5°	285.6	285.1	284.6	284.0	284.6	285.1	285.6	286.1	286.3	286.2	286.1
120°	308.6	308.1	307.6	307.1	307.6	308.1	308.6	309.1	309.3	309.3	309.3
122.5°	331.3	330.9	330.5	330.1	330.5	330.9	331.3	331.7	332.0	332.1	332.2
125°	365.1	365.0	364.8	364.7	364.8	365.0	365.1	365.2	365.4	365.7	365.9
127.5°	398.6	398.4	398.1	397.9	398.1	398.4	398.6	398.9	399.1	399.2	399.3
130°	420.7	420.5	420.2	420.0	420.2	420.5	420.7	421.0	421.2	421.3	421.4
132.5°	441.8	441.4	441.1	440.7	441.1	441.4	441.8	442.1	442.4	442.5	442.6
135°	474.5	474.0	473.5	473.0	473.5	474.0	474.5	475.0	475.2	475.2	475.2
137.5°	506.4	505.8	505.2	504.5	505.2	505.8	506.4	507.2	507.4	507.2	507.1
140°	526.7	526.1	525.4	524.8	525.4	526.1	526.7	527.4	527.6	527.4	527.0
142.5°	546.1	545.4	544.8	544.2	544.8	545.4	546.1	546.7	546.9	546.8	546.6
145°	574.4	574.0	573.6	573.2	573.6	574.0	574.4	574.7	574.9	574.9	574.9
147.5°	600.6	599.8	598.8	598.0	598.8	599.8	600.6	601.5	601.8	601.5	601.2
150°	617.2	616.9	616.7	616.4	616.7	616.9	617.2	617.4	617.5	617.5	617.5
152.5°	633.0	632.6	632.1	631.7	632.1	632.6	633.0	633.5	633.6	633.3	633.0
155°	655.2	654.6	653.9	653.3	653.9	654.6	655.2	655.9	655.9	655.4	654.9
157.5°	673.9	673.1	672.3	671.4	672.3	673.1	673.9	674.8	674.9	674.4	673.9
160°	685.8	685.1	684.5	683.9	684.5	685.1	685.8	686.4	686.4	685.9	685.4
162.5°	696.7	695.9	695.2	694.4	695.2	695.9	696.7	697.4	697.5	696.8	696.2
165°	710.9	710.1	709.3	708.6	709.3	710.1	710.9	711.7	711.9	711.2	710.7
167.5°	722.3	721.4	720.6	719.9	720.6	721.4	722.3	723.1	723.1	722.4	721.5
170°	728.6	727.7	726.8	725.9	726.8	727.7	728.6	729.4	729.5	728.7	728.0
172.5°	733.4	732.6	731.7	730.9	731.7	732.6	733.4	734.2	734.2	733.4	732.7
175°	738.4	737.5	736.6	735.7	736.6	737.5	738.4	739.2	739.3	738.5	737.8
177.5°	740.6	739.9	739.1	738.4	739.1	739.9	740.6	741.3	741.3	740.7	740.1
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1591.6	1597.7	1600.9	1608.6	1619.5	1625.0	1632.5	1638.0	1645.7	1655.0	1662.5
5°	1488.6	1505.0	1515.9	1532.9	1548.6	1564.3	1584.1	1598.3	1617.4	1639.2	1656.3
7.5°	1392.9	1413.4	1431.5	1454.0	1479.9	1500.1	1525.8	1552.2	1582.0	1613.0	1642.1
10°	1331.8	1352.3	1374.8	1402.7	1428.7	1455.9	1486.5	1517.2	1554.7	1589.5	1629.0
12.5°	1271.3	1293.9	1319.2	1350.4	1381.7	1416.6	1447.8	1482.4	1522.6	1567.7	1609.9
15°	1196.2	1218.0	1245.3	1271.8	1308.0	1346.2	1387.8	1433.4	1478.3	1528.8	1581.3
17.5°	1115.6	1139.6	1169.6	1200.4	1238.5	1283.1	1323.9	1373.9	1424.5	1483.3	1545.1
20°	1063.3	1087.8	1123.3	1157.4	1192.1	1235.8	1284.1	1335.2	1389.1	1451.2	1519.9
22.5°	1021.9	1039.4	1074.2	1108.8	1149.6	1194.3	1241.6	1294.9	1353.6	1417.9	1490.0
25°	960.4	980.8	1006.0	1042.2	1084.4	1131.5	1179.1	1235.8	1299.8	1365.2	1442.3
27.5°	905.7	922.5	947.5	975.7	1017.9	1066.7	1117.4	1176.4	1242.1	1308.8	1389.8
30°	867.0	885.3	909.3	939.3	972.6	1025.8	1077.6	1135.6	1202.3	1271.2	1354.3
32.5°	833.1	852.1	872.7	901.1	937.2	984.4	1037.8	1094.7	1162.6	1233.6	1314.5
35°	785.9	798.8	817.9	845.9	881.3	919.5	974.0	1034.0	1100.1	1173.8	1254.9
37.5°	731.6	748.4	767.3	791.6	822.7	864.0	914.7	975.3	1036.7	1107.2	1181.2
40°	700.0	715.7	736.8	754.6	787.3	824.8	871.1	934.4	995.8	1062.0	1129.4
42.5°	667.8	683.0	700.8	722.9	752.3	788.7	831.8	890.8	956.5	1018.9	1075.4
45°	617.5	633.2	650.3	670.7	697.9	733.4	776.4	830.2	887.5	944.7	987.6
47.5°	569.4	584.1	600.3	621.2	646.3	680.5	718.9	766.5	822.1	870.8	901.5
50°	535.0	548.7	566.4	586.8	611.4	643.4	680.2	727.3	773.7	817.9	845.9
52.5°	501.3	516.5	534.2	552.0	575.4	607.4	641.6	682.0	726.2	762.3	785.4
55°	450.5	464.8	481.2	499.6	522.8	550.1	586.2	618.2	653.0	683.7	697.3
57.5°	401.6	414.1	429.5	448.6	469.5	494.8	523.5	554.3	578.9	600.5	615.9
60°	369.4	380.3	394.7	411.0	433.5	456.7	482.6	511.2	530.3	548.7	563.0
62.5°	336.7	347.1	360.8	375.6	395.4	416.9	441.7	464.8	483.4	495.8	512.3
65°	287.6	297.8	309.4	325.1	340.8	358.5	381.0	398.1	411.0	424.6	434.8
67.5°	242.0	250.4	261.5	273.8	287.0	304.0	321.4	335.6	344.5	352.6	365.0
70°	212.0	218.8	227.6	237.2	251.6	268.5	282.2	293.1	299.2	307.4	322.3
72.5°	181.5	189.3	197.6	207.2	218.8	233.1	245.1	256.0	259.9	266.5	276.1
75°	143.1	147.2	154.0	160.9	169.1	181.3	192.9	195.6	199.0	204.5	211.3
77.5°	108.3	111.9	114.6	119.2	125.7	135.5	141.7	145.7	146.5	148.6	155.3
80°	85.8	88.0	90.7	94.0	96.7	104.9	108.4	112.5	113.8	115.8	119.3
82.5°	63.0	65.0	66.7	69.5	73.9	77.2	80.6	84.6	84.9	86.4	87.2
85°	36.8	37.5	36.2	37.5	38.2	39.5	42.9	46.4	45.6	44.9	47.1
87.5°	15.0	14.9	14.2	15.7	14.4	14.7	14.5	14.9	15.8	16.7	17.6
90°	9.9	9.2	8.3	7.5	6.6	5.7	4.6	3.6	2.6	1.6	0.6
92.5°	22.9	22.1	21.0	19.9	18.8	17.7	16.8	16.1	15.3	14.6	13.9
95°	45.2	44.3	43.1	41.8	40.5	39.3	38.5	38.2	38.0	37.7	37.5
97.5°	71.5	70.6	68.9	67.1	65.3	63.5	62.6	62.5	62.4	62.3	62.2
100°	89.3	88.2	86.4	84.8	83.1	81.5	80.7	80.7	80.7	80.7	80.7
102.5°	107.9	106.5	105.7	104.9	104.0	103.2	102.5	102.0	101.5	101.0	100.5
105°	138.5	137.6	136.9	136.1	135.4	134.6	133.9	133.3	132.6	132.0	131.4
107.5°	171.4	171.0	170.4	169.8	169.3	168.6	168.0	167.3	166.7	166.1	165.4
110°	194.0	193.6	193.2	192.8	192.4	192.1	191.6	190.9	190.3	189.6	188.9



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	216.8	216.6	216.1	215.6	215.2	214.7	214.3	213.9	213.6	213.3	212.9
115°	251.7	251.8	251.5	251.3	251.0	250.7	250.3	249.8	249.3	248.8	248.3
117.5°	286.0	285.9	285.6	285.4	285.2	285.0	284.7	284.5	284.3	284.0	283.8
120°	309.3	309.3	309.2	309.1	309.0	308.8	308.5	307.8	307.2	306.6	305.9
122.5°	332.3	332.4	332.0	331.7	331.4	331.0	330.8	330.5	330.3	330.1	329.9
125°	366.2	366.4	366.3	366.2	366.0	365.9	365.5	364.7	363.9	363.1	362.3
127.5°	399.5	399.6	399.4	399.3	399.1	399.0	398.7	398.2	397.8	397.4	397.0
130°	421.6	421.7	421.4	421.2	420.9	420.7	420.2	419.6	419.0	418.3	417.7
132.5°	442.8	442.9	442.9	443.0	443.0	443.1	442.6	441.5	440.5	439.5	438.4
135°	475.2	475.2	475.1	475.0	474.9	474.7	474.3	473.5	472.8	472.0	471.2
137.5°	506.9	506.8	506.4	506.1	505.9	505.6	505.1	504.3	503.6	502.9	502.1
140°	526.8	526.5	526.1	525.8	525.4	525.0	524.5	523.8	523.2	522.6	521.9
142.5°	546.5	546.3	545.9	545.4	544.9	544.4	543.9	543.4	542.8	542.3	541.8
145°	574.9	574.9	574.6	574.2	573.8	573.4	573.0	572.5	572.0	571.4	570.9
147.5°	600.9	600.6	600.3	600.0	599.6	599.3	599.1	598.7	598.4	598.1	597.8
150°	617.5	617.5	617.0	616.5	616.0	615.5	615.3	615.5	615.6	615.7	615.8
152.5°	632.7	632.4	632.1	631.9	631.7	631.5	631.3	631.2	631.0	630.8	630.6
155°	654.4	653.9	653.8	653.6	653.5	653.4	653.3	653.3	653.3	653.3	653.3
157.5°	673.4	672.9	672.8	672.7	672.5	672.4	672.5	672.8	673.0	673.3	673.6
160°	684.9	684.4	684.3	684.2	684.0	683.9	684.0	684.4	684.8	685.2	685.6
162.5°	695.6	695.0	695.0	695.0	694.9	694.9	695.0	695.3	695.6	695.9	696.2
165°	710.2	709.7	709.6	709.5	709.3	709.2	709.3	709.5	709.8	710.0	710.3
167.5°	720.7	720.0	720.0	720.0	720.0	720.0	720.2	720.7	721.2	721.9	722.4
170°	727.2	726.5	726.5	726.5	726.5	726.5	726.7	727.2	727.7	728.2	728.7
172.5°	731.8	731.0	731.0	731.0	731.0	731.0	731.3	731.8	732.4	732.9	733.4
175°	737.0	736.3	736.3	736.3	736.3	736.3	736.5	737.0	737.5	738.0	738.5
177.5°	739.5	738.9	739.0	739.1	739.2	739.3	739.5	740.0	740.4	740.8	741.2
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1668.6	1673.4	1680.5	1688.7	1695.3	1702.3	1706.2	1706.2	1709.5	1716.6	1725.9
5°	1673.3	1691.0	1708.1	1729.9	1747.0	1766.7	1781.7	1796.0	1809.0	1825.3	1842.4
7.5°	1671.9	1701.4	1732.1	1766.5	1804.3	1834.4	1865.4	1889.7	1913.7	1945.0	1969.6
10°	1666.5	1704.7	1746.3	1789.9	1837.6	1879.2	1916.6	1950.8	1983.5	2017.5	2048.2
12.5°	1656.7	1705.3	1756.1	1808.5	1868.7	1916.2	1964.7	2000.9	2039.1	2076.4	2114.2
15°	1641.9	1699.2	1760.6	1833.5	1907.1	1960.2	2008.0	2055.1	2090.4	2132.7	2168.9
17.5°	1611.5	1685.4	1762.5	1842.2	1913.0	1974.7	2024.8	2069.5	2107.3	2153.7	2202.8
20°	1593.6	1673.3	1753.7	1839.0	1906.4	1969.8	2018.2	2064.6	2111.6	2172.2	2232.2
22.5°	1568.5	1653.7	1739.0	1819.9	1891.2	1952.4	2002.4	2059.1	2120.8	2189.7	2262.2
25°	1528.8	1616.8	1701.3	1778.3	1847.9	1910.6	1978.7	2055.1	2130.0	2220.7	2324.9
27.5°	1478.5	1563.3	1638.7	1720.1	1789.2	1869.0	1954.0	2036.8	2144.9	2269.6	2399.7
30°	1440.9	1521.4	1592.9	1669.9	1748.3	1836.2	1931.7	2029.1	2158.0	2304.5	2459.2
32.5°	1397.2	1470.1	1541.1	1615.4	1705.8	1802.4	1903.8	2023.2	2177.1	2343.8	2504.0
35°	1321.6	1387.0	1455.9	1538.3	1634.5	1739.5	1869.0	2014.2	2200.2	2379.4	2523.2
37.5°	1242.2	1293.9	1363.0	1450.1	1554.7	1676.2	1823.1	1999.5	2190.7	2351.5	2412.8
40°	1181.2	1229.6	1302.5	1393.9	1497.4	1630.4	1795.3	1976.6	2168.9	2280.7	2275.8
42.5°	1120.6	1169.6	1239.8	1331.7	1439.7	1588.4	1758.3	1946.6	2108.9	2151.4	2062.6
45°	1027.8	1073.5	1142.4	1235.1	1350.9	1507.0	1685.6	1866.2	1969.8	1901.0	1725.2
47.5°	933.2	977.5	1041.5	1132.3	1258.8	1422.1	1590.9	1739.2	1753.7	1605.9	1394.9
50°	871.1	912.6	973.3	1070.2	1192.8	1352.3	1515.2	1631.7	1595.6	1415.0	1197.6
52.5°	810.5	850.5	907.4	998.7	1124.1	1280.3	1425.7	1517.2	1433.7	1241.6	1046.0
55°	721.1	759.3	816.6	900.4	1014.2	1157.4	1284.9	1318.2	1195.5	1002.0	843.8
57.5°	636.2	664.2	720.7	794.9	904.6	1030.9	1122.2	1116.2	980.8	806.5	693.1
60°	580.1	605.2	659.1	727.3	831.5	944.7	1008.8	981.5	844.6	700.6	591.6
62.5°	527.7	551.3	596.4	659.1	748.7	847.1	893.7	856.1	726.7	600.4	513.6
65°	448.5	465.5	501.7	559.6	629.8	697.9	739.5	684.3	569.9	474.4	409.0
67.5°	374.5	389.2	421.3	462.9	511.3	558.4	575.3	523.5	434.4	370.1	324.1
70°	326.5	340.1	361.9	400.8	432.8	466.3	474.4	428.1	353.8	304.7	276.1
72.5°	280.6	293.3	312.4	339.7	361.9	381.1	385.0	341.9	285.1	251.3	229.1
75°	214.0	224.9	237.2	247.4	261.8	265.2	263.8	230.4	199.8	177.2	164.9
77.5°	157.3	161.8	169.4	173.4	174.1	173.8	166.8	145.7	129.9	120.7	115.6
80°	121.3	124.7	126.7	128.2	128.9	122.0	114.5	101.6	96.1	90.7	84.5
82.5°	88.1	90.4	92.4	92.7	89.0	83.3	76.3	69.9	66.1	63.4	61.1
85°	47.7	48.4	47.7	44.3	39.5	37.5	36.2	34.7	34.0	33.4	33.4
87.5°	17.3	15.8	13.2	14.0	14.2	13.8	14.0	13.6	13.3	13.4	13.5
90°	1.6	2.6	3.6	4.6	5.7	6.6	7.5	8.3	9.2	9.9	10.5
92.5°	14.6	15.3	16.1	16.8	17.7	18.8	19.9	21.0	22.1	22.9	23.8
95°	37.7	38.0	38.2	38.5	39.3	40.5	41.8	43.1	44.3	45.2	46.2
97.5°	62.3	62.4	62.5	62.6	63.5	65.3	67.1	68.9	70.6	71.5	72.3
100°	80.7	80.7	80.7	80.7	81.5	83.1	84.8	86.4	88.2	89.3	90.5
102.5°	101.0	101.5	102.0	102.5	103.2	104.0	104.9	105.7	106.5	107.9	109.1
105°	132.0	132.6	133.3	133.9	134.6	135.4	136.1	136.9	137.6	138.5	139.3
107.5°	166.1	166.7	167.3	168.0	168.6	169.3	169.8	170.4	171.0	171.4	171.8
110°	189.6	190.3	190.9	191.6	192.1	192.4	192.8	193.2	193.6	194.0	194.3





TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	213.3	213.6	213.9	214.3	214.7	215.2	215.6	216.1	216.6	216.8	217.0
115°	248.8	249.3	249.8	250.3	250.7	251.0	251.3	251.5	251.8	251.7	251.5
117.5°	284.0	284.3	284.5	284.7	285.0	285.2	285.4	285.6	285.9	286.0	286.1
120°	306.6	307.2	307.8	308.5	308.8	309.0	309.1	309.2	309.3	309.3	309.3
122.5°	330.1	330.3	330.5	330.8	331.0	331.4	331.7	332.0	332.4	332.3	332.2
125°	363.1	363.9	364.7	365.5	365.9	366.0	366.2	366.3	366.4	366.2	365.9
127.5°	397.4	397.8	398.2	398.7	399.0	399.1	399.3	399.4	399.6	399.5	399.3
130°	418.3	419.0	419.6	420.2	420.7	420.9	421.2	421.4	421.7	421.6	421.4
132.5°	439.5	440.5	441.5	442.6	443.1	443.0	443.0	442.9	442.9	442.8	442.6
135°	472.0	472.8	473.5	474.3	474.7	474.9	475.0	475.1	475.2	475.2	475.2
137.5°	502.9	503.6	504.3	505.1	505.6	505.9	506.1	506.4	506.8	506.9	507.1
140°	522.6	523.2	523.8	524.5	525.0	525.4	525.8	526.1	526.5	526.8	527.0
142.5°	542.3	542.8	543.4	543.9	544.4	544.9	545.4	545.9	546.3	546.5	546.6
145°	571.4	572.0	572.5	573.0	573.4	573.8	574.2	574.6	574.9	574.9	574.9
147.5°	598.1	598.4	598.7	599.1	599.3	599.6	600.0	600.3	600.6	600.9	601.2
150°	615.7	615.6	615.5	615.3	615.5	616.0	616.5	617.0	617.5	617.5	617.5
152.5°	630.8	631.0	631.2	631.3	631.5	631.7	631.9	632.1	632.4	632.7	633.0
155°	653.3	653.3	653.3	653.3	653.4	653.5	653.6	653.8	653.9	654.4	654.9
157.5°	673.3	673.0	672.8	672.5	672.4	672.5	672.7	672.8	672.9	673.4	673.9
160°	685.2	684.8	684.4	684.0	683.9	684.0	684.2	684.3	684.4	684.9	685.4
162.5°	695.9	695.6	695.3	695.0	694.9	694.9	695.0	695.0	695.0	695.6	696.2
165°	710.0	709.8	709.5	709.3	709.2	709.3	709.5	709.6	709.7	710.2	710.7
167.5°	721.9	721.2	720.7	720.2	720.0	720.0	720.0	720.0	720.0	720.7	721.5
170°	728.2	727.7	727.2	726.7	726.5	726.5	726.5	726.5	726.5	727.2	728.0
172.5°	732.9	732.4	731.8	731.3	731.0	731.0	731.0	731.0	731.0	731.8	732.7
175°	738.0	737.5	737.0	736.5	736.3	736.3	736.3	736.3	736.3	737.0	737.8
177.5°	740.8	740.4	740.0	739.5	739.3	739.2	739.1	739.0	738.9	739.5	740.1
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1732.9	1732.9	1742.2	1741.6	1747.7	1745.5	1746.6
5°	1862.8	1874.4	1884.6	1891.5	1901.7	1904.4	1903.0
7.5°	1997.5	2023.3	2035.8	2053.0	2056.1	2065.1	2064.2
10°	2080.9	2106.2	2125.3	2140.2	2147.7	2157.3	2158.0
12.5°	2146.4	2167.8	2184.6	2198.6	2207.7	2210.7	2212.5
15°	2197.5	2221.3	2241.1	2260.9	2272.5	2281.3	2286.1
17.5°	2249.0	2285.8	2320.7	2347.5	2363.7	2377.3	2377.1
20°	2288.9	2331.1	2374.7	2405.4	2436.7	2450.3	2452.4
22.5°	2331.4	2396.0	2452.2	2499.7	2540.8	2555.1	2560.4
25°	2419.6	2504.2	2590.8	2657.6	2705.2	2733.2	2737.3
27.5°	2526.4	2640.8	2731.9	2793.5	2833.2	2853.9	2858.3
30°	2601.7	2707.3	2789.1	2835.5	2853.9	2856.6	2846.4
32.5°	2635.4	2714.4	2747.1	2744.4	2708.3	2684.3	2675.1
35°	2594.1	2577.8	2498.1	2402.7	2329.8	2283.4	2271.1
37.5°	2360.8	2219.7	2073.1	1928.8	1852.1	1813.0	1746.0
40°	2130.7	1929.7	1777.0	1655.6	1569.0	1499.5	1483.2
42.5°	1871.2	1663.6	1510.9	1406.9	1337.9	1290.1	1269.4
45°	1503.6	1325.0	1198.9	1119.2	1066.0	1031.3	1015.6
47.5°	1202.6	1064.4	972.5	913.5	873.0	842.7	834.2
50°	1037.4	927.0	849.3	799.5	768.8	745.7	736.1
52.5°	901.1	811.9	752.2	711.1	682.2	667.7	659.7
55°	743.7	666.6	623.7	591.0	574.6	563.0	557.5
57.5°	608.1	552.5	521.2	498.6	483.4	476.1	473.3
60°	532.3	488.7	460.1	442.3	432.1	422.6	419.9
62.5°	465.2	430.9	408.8	393.2	383.0	379.0	377.3
65°	374.9	352.3	336.0	326.5	318.3	316.9	316.3
67.5°	298.0	284.8	276.2	266.2	263.4	258.6	257.6
70°	254.9	246.1	235.8	232.5	229.0	224.3	224.9
72.5°	216.2	207.3	200.4	195.9	194.7	192.6	194.4
75°	158.1	155.4	152.7	149.3	147.9	147.9	147.2
77.5°	112.9	110.6	107.6	105.5	105.1	102.2	103.3
80°	81.8	78.4	77.1	77.7	75.6	74.9	74.9
82.5°	60.5	59.3	58.0	58.1	57.7	57.0	57.6
85°	33.4	32.7	32.7	32.0	32.0	31.3	31.3
87.5°	14.2	14.9	13.9	13.4	13.5	14.1	14.7
90°	11.1	11.8	12.3	12.7	13.0	13.4	13.8
92.5°	24.6	25.5	26.1	26.4	26.7	26.9	27.2
95°	47.1	48.0	48.5	48.8	49.1	49.3	49.6
97.5°	73.2	74.0	74.5	74.6	74.8	74.9	75.1
100°	91.6	92.7	93.4	93.7	94.0	94.2	94.5
102.5°	110.4	111.6	112.4	112.8	113.1	113.5	113.8
105°	140.0	140.8	141.4	141.7	142.1	142.5	142.9
107.5°	172.2	172.5	172.7	172.7	172.7	172.6	172.6
110°	194.7	195.1	195.2	195.1	195.0	194.8	194.7



TEST NUMBER: P333587-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	217.1	217.3	217.3	217.1	216.8	216.6	216.4
115°	251.4	251.3	251.2	251.0	250.9	250.7	250.6
117.5°	286.2	286.3	286.1	285.6	285.1	284.6	284.0
120°	309.3	309.3	309.1	308.6	308.1	307.6	307.1
122.5°	332.1	332.0	331.7	331.3	330.9	330.5	330.1
125°	365.7	365.4	365.2	365.1	365.0	364.8	364.7
127.5°	399.2	399.1	398.9	398.6	398.4	398.1	397.9
130°	421.3	421.2	421.0	420.7	420.5	420.2	420.0
132.5°	442.5	442.4	442.1	441.8	441.4	441.1	440.7
135°	475.2	475.2	475.0	474.5	474.0	473.5	473.0
137.5°	507.2	507.4	507.2	506.4	505.8	505.2	504.5
140°	527.4	527.6	527.4	526.7	526.1	525.4	524.8
142.5°	546.8	546.9	546.7	546.1	545.4	544.8	544.2
145°	574.9	574.9	574.7	574.4	574.0	573.6	573.2
147.5°	601.5	601.8	601.5	600.6	599.8	598.8	598.0
150°	617.5	617.5	617.4	617.2	616.9	616.7	616.4
152.5°	633.3	633.6	633.5	633.0	632.6	632.1	631.7
155°	655.4	655.9	655.9	655.2	654.6	653.9	653.3
157.5°	674.4	674.9	674.8	673.9	673.1	672.3	671.4
160°	685.9	686.4	686.4	685.8	685.1	684.5	683.9
162.5°	696.8	697.5	697.4	696.7	695.9	695.2	694.4
165°	711.2	711.9	711.7	710.9	710.1	709.3	708.6
167.5°	722.4	723.1	723.1	722.3	721.4	720.6	719.9
170°	728.7	729.5	729.4	728.6	727.7	726.8	725.9
172.5°	733.4	734.2	734.2	733.4	732.6	731.7	730.9
175°	738.5	739.3	739.2	738.4	737.5	736.6	735.7
177.5°	740.7	741.3	741.3	740.6	739.9	739.1	738.4
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3

(END OF REPORT)