

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333625-840

Luminaire Tested: **S125RDIP-S1270D810U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333625-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D810U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8198.7 lumens
Efficiency: N/A
Efficacy: 135.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333625-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333625-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	52	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	71	62	55	49	54	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13464	13464	13464
5°	13494	13341	13422
10°	13392	13217	13217
15°	13233	12948	12843
20°	13029	12575	12423
25°	12790	12207	11938
30°	12493	11777	11401
35°	12191	11334	10800
40°	11907	10871	10208
45°	11562	10355	9563
50°	11216	9792	8890
55°	10815	9254	8173
60°	10413	8603	7403
65°	9938	7844	6521
70°	9396	6898	5620
75°	8644	5814	4674
80°	7613	4567	3924
85°	6417	3735	3505



TEST NUMBER: P333625-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.0	2.4
10°-20°	547.8	6.7
20°-30°	794.4	9.7
30°-40°	905.3	11.0
40°-50°	882.5	10.8
50°-60°	742.8	9.1
60°-70°	520.7	6.4
70°-80°	267.7	3.3
80°-90°	69.8	0.9
90°-100°	38.7	0.5
100°-110°	238.6	2.9
110°-120°	432.8	5.3
120°-130°	555.4	6.8
130°-140°	597.4	7.3
140°-150°	560.7	6.8
150°-160°	453.6	5.5
160°-170°	293.3	3.6
170°-180°	101.2	1.2
0°-30°	1538.2	18.8
0°-40°	2443.5	29.8
0°-60°	4068.9	49.6
0°-90°	4927.1	60.1
90°-120°	710.1	8.7
90°-150°	2423.5	29.6
90°-180°	3272.0	39.9
0°-180°	8198.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2058	2073	2070	197
15°	1979	1968	1937	1934	1921	558
25°	1795	1769	1713	1693	1675	826
35°	1546	1507	1438	1393	1370	968
45°	1266	1218	1134	1073	1047	976
55°	960	908	822	754	726	859
65°	650	595	513	452	427	644
75°	346	298	233	200	187	367
85°	87	59	50	49	47	97
90°	1	7	13	17	19	6
95°	45	41	13	16	17	57
105°	232	235	235	235	235	246
115°	436	440	441	437	433	432
125°	620	625	626	622	620	554
135°	773	778	776	775	770	596
145°	896	898	898	898	894	560
155°	987	983	984	986	980	455
165°	1042	1037	1038	1042	1036	294
175°	1065	1061	1062	1067	1061	101
180°	1065	1065	1065	1065	1065	



TEST NUMBER: P333625-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2088.4	2087.6	2086.7	2085.9	2085.1	2083.3	2080.4	2077.6	2074.9	2072.0	2074.9
5°	2081.5	2080.1	2078.7	2077.3	2075.9	2073.3	2069.4	2065.6	2061.7	2057.9	2061.3
7.5°	2061.0	2059.7	2058.4	2057.0	2055.7	2052.8	2048.1	2043.5	2038.9	2034.3	2036.7
10°	2042.1	2041.0	2040.0	2039.0	2037.9	2035.0	2030.0	2025.2	2020.2	2015.4	2016.4
12.5°	2020.7	2019.4	2018.0	2016.7	2015.4	2011.4	2004.9	1998.3	1991.7	1985.1	1985.9
15°	1979.1	1977.0	1975.0	1972.9	1970.8	1966.0	1958.6	1951.4	1944.0	1936.6	1936.3
17.5°	1932.2	1929.0	1925.8	1922.6	1919.3	1913.1	1903.9	1894.6	1885.4	1876.1	1874.4
20°	1895.7	1892.2	1888.6	1885.2	1881.7	1874.3	1863.2	1852.0	1840.8	1829.6	1827.9
22.5°	1855.4	1851.9	1848.4	1844.9	1841.4	1833.8	1822.0	1810.3	1798.5	1786.8	1783.3
25°	1794.9	1789.7	1784.4	1779.2	1773.9	1764.8	1751.9	1739.0	1726.0	1713.0	1708.5
27.5°	1725.7	1719.3	1712.9	1706.6	1700.2	1690.1	1676.2	1662.3	1648.5	1634.7	1628.3
30°	1675.3	1668.6	1661.9	1655.4	1648.7	1638.0	1623.3	1608.6	1593.9	1579.2	1571.1
32.5°	1626.2	1618.4	1610.6	1602.9	1595.1	1583.7	1568.7	1553.8	1538.7	1523.8	1514.9
35°	1546.2	1537.7	1529.3	1521.0	1512.6	1500.5	1484.7	1469.1	1453.3	1437.5	1427.3
37.5°	1467.7	1457.5	1447.3	1437.1	1426.8	1413.6	1397.5	1381.2	1364.9	1348.7	1336.6
40°	1412.3	1401.8	1391.3	1380.8	1370.4	1356.7	1339.9	1323.1	1306.3	1289.5	1276.3
42.5°	1354.4	1343.6	1332.8	1322.0	1311.3	1297.2	1279.9	1262.5	1245.2	1227.8	1215.1
45°	1265.9	1255.8	1245.6	1235.5	1225.3	1210.6	1191.3	1172.2	1152.9	1133.7	1119.6
47.5°	1174.3	1163.6	1152.9	1142.2	1131.5	1116.4	1097.0	1077.6	1058.2	1038.8	1024.4
50°	1116.3	1104.8	1093.2	1081.7	1070.2	1054.4	1034.4	1014.5	994.5	974.6	959.9
52.5°	1053.3	1041.5	1029.7	1017.8	1006.0	990.7	971.9	953.1	934.2	915.4	899.6
55°	960.5	949.3	938.1	926.9	915.6	900.3	880.7	861.1	841.5	821.9	806.2
57.5°	866.6	854.6	842.6	830.7	818.7	803.3	784.5	765.5	746.6	727.7	712.4
60°	806.2	793.9	781.6	769.4	757.2	741.5	722.7	703.8	684.9	666.0	650.7
62.5°	741.9	730.2	718.5	706.8	695.2	679.7	660.6	641.4	622.2	603.0	588.8
65°	650.3	638.3	626.5	614.6	602.7	587.4	569.0	550.4	531.8	513.3	499.3
67.5°	559.3	547.3	535.4	523.6	511.7	496.9	479.1	461.3	443.5	425.8	412.9
70°	497.6	485.6	473.7	461.8	450.0	435.3	417.8	400.3	382.7	365.3	354.5
72.5°	437.1	425.5	413.8	402.2	390.6	376.6	360.2	343.9	327.5	311.1	301.1
75°	346.4	335.9	325.4	314.9	304.4	291.9	277.1	262.5	247.7	233.0	225.3
77.5°	256.3	247.9	239.5	231.2	222.8	212.7	200.9	189.1	177.4	165.6	160.3
80°	204.7	196.3	187.9	179.5	171.1	162.0	152.2	142.4	132.6	122.8	119.7
82.5°	154.3	146.7	139.2	131.6	124.1	116.9	110.2	103.5	96.7	90.1	88.6
85°	86.6	80.3	74.0	67.7	61.4	57.4	55.6	53.9	52.1	50.4	50.0
87.5°	29.1	27.5	25.8	24.1	22.4	21.5	21.5	21.5	21.4	21.4	21.6
90°	0.8	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5
92.5°	12.1	11.2	10.2	9.2	8.3	8.3	9.4	10.5	11.5	12.6	13.5
95°	45.0	44.5	43.9	43.4	42.9	39.3	32.6	26.0	19.3	12.6	13.5
97.5°	94.0	94.9	95.8	96.8	97.8	91.7	78.5	65.2	52.0	38.9	33.9
100°	131.9	132.4	132.9	133.5	134.0	134.6	135.3	136.0	136.7	137.4	111.3
102.5°	170.5	171.1	171.8	172.4	173.1	173.6	174.1	174.5	174.9	175.3	170.4
105°	232.2	232.9	233.6	234.3	235.0	235.3	235.3	235.3	235.3	235.3	235.3
107.5°	296.3	296.3	296.3	296.3	296.3	296.5	296.8	297.2	297.5	297.9	297.9
110°	338.0	338.0	338.0	338.0	338.0	338.2	338.5	338.9	339.2	339.6	339.1



TEST NUMBER: P333625-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	377.2	377.6	378.0	378.5	378.9	379.2	379.4	379.6	379.8	380.0	379.4
115°	436.0	436.9	437.7	438.6	439.5	440.0	440.2	440.3	440.5	440.7	440.0
117.5°	496.8	496.8	496.7	496.7	496.7	497.0	497.6	498.3	499.0	499.6	498.7
120°	534.6	534.5	534.3	534.1	533.9	534.1	534.6	535.2	535.7	536.2	535.9
122.5°	568.2	568.9	569.5	570.2	570.8	571.3	571.5	571.8	572.0	572.3	571.9
125°	620.0	621.2	622.4	623.7	624.9	625.5	625.5	625.5	625.5	625.5	624.8
127.5°	669.4	670.2	671.2	672.1	672.9	673.3	673.2	673.1	673.0	672.9	672.5
130°	699.7	700.6	701.5	702.4	703.3	703.8	704.0	704.1	704.3	704.5	704.0
132.5°	730.0	731.0	732.1	733.1	734.2	734.5	734.1	733.7	733.3	732.9	732.8
135°	773.2	774.3	775.3	776.4	777.4	777.7	777.4	777.0	776.7	776.4	776.0
137.5°	812.8	813.7	814.7	815.6	816.5	816.8	816.5	816.2	815.9	815.5	815.6
140°	838.7	839.1	839.4	839.8	840.1	840.2	840.0	839.9	839.7	839.5	839.9
142.5°	862.1	862.3	862.5	862.7	862.9	863.1	863.4	863.6	863.9	864.1	864.2
145°	896.4	896.8	897.1	897.5	897.8	898.0	898.0	898.0	898.0	898.0	898.2
147.5°	926.3	926.3	926.2	926.1	926.1	926.1	926.3	926.6	926.9	927.1	927.3
150°	945.3	945.0	944.6	944.3	943.9	943.9	944.3	944.6	945.0	945.3	945.7
152.5°	963.7	962.9	962.1	961.4	960.6	960.4	960.7	961.1	961.4	961.8	962.1
155°	987.2	986.1	985.1	984.0	983.0	982.6	983.0	983.3	983.7	984.0	984.5
157.5°	1005.3	1004.7	1004.1	1003.5	1002.8	1002.5	1002.6	1002.6	1002.6	1002.7	1003.2
160°	1018.0	1016.9	1015.9	1014.8	1013.8	1013.4	1013.5	1013.7	1013.9	1014.0	1014.7
162.5°	1028.1	1027.0	1026.0	1024.9	1023.9	1023.5	1023.6	1023.8	1024.0	1024.2	1025.1
165°	1041.7	1040.7	1039.6	1038.5	1037.4	1037.0	1037.2	1037.4	1037.5	1037.7	1038.8
167.5°	1051.8	1050.8	1049.7	1048.5	1047.4	1047.0	1047.1	1047.3	1047.5	1047.7	1048.9
170°	1057.5	1056.2	1055.0	1053.8	1052.6	1052.1	1052.2	1052.4	1052.6	1052.8	1054.2
172.5°	1061.3	1060.1	1058.8	1057.6	1056.3	1055.9	1056.2	1056.5	1056.8	1057.1	1058.4
175°	1065.4	1064.3	1063.3	1062.3	1061.2	1060.8	1060.9	1061.1	1061.3	1061.5	1062.9
177.5°	1067.3	1066.4	1065.6	1064.8	1063.9	1063.6	1063.7	1063.8	1064.0	1064.1	1065.1
180°	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4



TEST NUMBER: P333625-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2077.6	2080.4	2083.3	2084.5	2084.3	2084.0	2083.7	2083.4
5°	2064.9	2068.4	2071.8	2073.3	2072.5	2071.8	2071.1	2070.4
7.5°	2039.1	2041.6	2044.1	2044.9	2044.1	2043.4	2042.6	2041.8
10°	2017.4	2018.5	2019.5	2019.5	2018.5	2017.4	2016.4	2015.4
12.5°	1986.7	1987.4	1988.2	1987.8	1986.2	1984.6	1983.0	1981.4
15°	1935.9	1935.6	1935.2	1933.5	1930.4	1927.2	1924.0	1920.9
17.5°	1872.7	1870.9	1869.2	1867.0	1864.4	1861.8	1859.3	1856.6
20°	1826.0	1824.3	1822.6	1820.1	1816.9	1813.8	1810.7	1807.6
22.5°	1779.9	1776.5	1773.0	1770.0	1767.5	1764.8	1762.2	1759.7
25°	1703.9	1699.4	1694.9	1690.6	1686.8	1682.9	1679.1	1675.3
27.5°	1621.9	1615.6	1609.2	1604.2	1600.4	1596.7	1593.0	1589.3
30°	1563.2	1555.1	1547.0	1541.5	1538.3	1535.1	1532.0	1528.8
32.5°	1506.0	1497.1	1488.2	1481.8	1477.8	1473.8	1469.9	1465.8
35°	1417.2	1407.0	1396.9	1389.4	1384.5	1379.6	1374.7	1369.8
37.5°	1324.3	1312.2	1300.0	1291.5	1286.8	1282.0	1277.3	1272.5
40°	1262.9	1249.6	1236.4	1227.6	1223.4	1219.2	1215.0	1210.8
42.5°	1202.3	1189.6	1176.9	1167.4	1161.2	1155.1	1148.9	1142.8
45°	1105.6	1091.7	1077.6	1068.0	1062.8	1057.5	1052.3	1047.0
47.5°	1010.1	995.6	981.2	971.1	965.2	959.5	953.6	947.9
50°	945.2	930.5	915.8	905.8	900.6	895.3	890.1	884.8
52.5°	883.7	868.0	852.1	841.6	836.4	831.1	825.9	820.6
55°	790.4	774.7	758.9	748.2	742.7	737.0	731.4	725.9
57.5°	696.9	681.6	666.1	656.0	651.0	646.0	641.1	636.1
60°	635.2	619.9	604.4	594.1	588.9	583.6	578.3	573.1
62.5°	574.5	560.2	545.9	536.1	530.9	525.6	520.4	515.1
65°	485.3	471.3	457.3	447.7	442.4	437.2	431.9	426.7
67.5°	400.1	387.3	374.6	366.0	361.8	357.6	353.5	349.2
70°	343.6	332.8	321.9	314.4	310.1	306.0	301.7	297.6
72.5°	291.1	281.1	271.0	264.7	261.9	259.1	256.3	253.5
75°	217.6	210.0	202.3	197.1	194.7	192.3	189.9	187.3
77.5°	154.8	149.5	144.1	140.5	138.7	136.8	135.0	133.2
80°	116.5	113.4	110.2	108.3	107.6	106.8	106.2	105.5
82.5°	87.2	85.6	84.2	83.2	82.8	82.4	82.0	81.6
85°	49.7	49.4	49.0	48.7	48.3	48.0	47.6	47.3
87.5°	21.8	21.9	22.1	22.1	21.9	21.8	21.6	21.4
90°	14.4	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	14.4	15.2	16.2	16.7	17.0	17.2	17.5	17.7
95°	14.4	15.2	16.2	16.6	16.6	16.6	16.6	16.6
97.5°	29.0	24.0	19.1	16.6	16.6	16.6	16.6	16.6
100°	85.1	59.0	32.8	19.4	18.7	18.0	17.3	16.6
102.5°	165.4	160.5	155.5	147.1	135.1	123.2	111.3	99.4
105°	235.3	235.3	235.3	235.3	235.1	234.9	234.7	234.6
107.5°	298.0	298.0	298.0	297.8	297.3	296.7	296.2	295.7
110°	338.5	338.0	337.5	337.3	337.5	337.7	337.8	338.0



TEST NUMBER: P333625-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.7	378.0	377.4	376.9	376.7	376.4	376.2	376.0
115°	439.3	438.6	437.9	437.0	436.0	434.8	433.8	432.8
117.5°	497.8	496.9	495.9	495.2	494.8	494.3	493.9	493.4
120°	535.5	535.2	534.8	534.2	533.3	532.5	531.6	530.7
122.5°	571.6	571.2	570.9	570.2	569.2	568.2	567.1	566.1
125°	624.1	623.4	622.7	622.1	621.6	621.0	620.5	620.0
127.5°	672.1	671.8	671.4	670.4	669.2	667.9	666.6	665.3
130°	703.4	702.9	702.4	701.7	700.7	699.9	699.0	698.1
132.5°	732.7	732.6	732.5	732.0	731.1	730.2	729.3	728.5
135°	775.7	775.3	775.0	774.3	773.2	772.1	771.0	770.0
137.5°	815.7	815.7	815.8	815.4	814.5	813.5	812.6	811.7
140°	840.2	840.6	840.9	840.6	839.5	838.5	837.4	836.4
142.5°	864.3	864.3	864.4	863.9	862.9	861.8	860.8	859.7
145°	898.3	898.5	898.7	898.2	897.2	896.2	895.0	894.0
147.5°	927.5	927.7	927.9	927.4	926.0	924.8	923.5	922.3
150°	946.0	946.4	946.7	946.2	944.8	943.4	942.0	940.6
152.5°	962.5	962.8	963.2	962.7	961.5	960.2	959.0	957.7
155°	985.1	985.6	986.1	985.7	984.3	982.9	981.5	980.1
157.5°	1003.8	1004.4	1004.9	1004.5	1003.1	1001.7	1000.3	998.9
160°	1015.4	1016.1	1016.8	1016.5	1015.1	1013.7	1012.3	1010.9
162.5°	1026.1	1027.1	1028.0	1027.8	1026.2	1024.7	1023.2	1021.7
165°	1039.9	1040.9	1042.0	1041.8	1040.4	1038.9	1037.5	1036.1
167.5°	1050.3	1051.5	1052.8	1052.6	1051.0	1049.5	1047.8	1046.3
170°	1055.5	1056.9	1058.3	1058.2	1056.7	1055.1	1053.5	1052.0
172.5°	1059.7	1061.0	1062.3	1062.1	1060.5	1058.9	1057.3	1055.7
175°	1064.2	1065.6	1067.0	1066.9	1065.4	1063.8	1062.3	1060.7
177.5°	1066.1	1067.0	1068.0	1068.0	1066.8	1065.7	1064.6	1063.5
180°	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4

(END OF REPORT)