

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333609-930

Luminaire Tested: **S125RDIP-S1090D1205U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333609-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D1205U930-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6969.0 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333609-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333609-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49																												
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42																												
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	36																												
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	34	30																												
4	75	64	56	50	69	59	53	47	51	45	41	43	39	35	35	32	30	26																												
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	32	29	26	23																												
6	63	51	43	38	58	48	41	35	41	35	31	35	30	27	29	26	23	20																												
7	59	46	38	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18																												
8	54	42	34	29	50	39	32	28	34	28	25	29	25	21	24	21	18	16																												
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15																												
10	47	35	28	23	44	33	27	22	29	23	20	25	20	18	21	18	15	13																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9412	9412	9412
5°	9433	9326	9383
10°	9362	9239	9239
15°	9250	9052	8978
20°	9108	8790	8685
25°	8941	8533	8345
30°	8733	8232	7970
35°	8521	7923	7550
40°	8323	7599	7136
45°	8082	7238	6685
50°	7840	6845	6215
55°	7560	6469	5713
60°	7279	6013	5174
65°	6946	5483	4557
70°	6567	4823	3928
75°	6041	4065	3266
80°	5322	3195	2741
85°	4483	2608	2445



TEST NUMBER: P333609-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.0	2.0
10°-20°	382.9	5.5
20°-30°	555.3	8.0
30°-40°	632.9	9.1
40°-50°	616.9	8.9
50°-60°	519.3	7.5
60°-70°	364.0	5.2
70°-80°	187.1	2.7
80°-90°	49.9	0.7
90°-100°	340.6	4.9
100°-110°	732.2	10.5
110°-120°	687.1	9.9
120°-130°	556.9	8.0
130°-140°	446.9	6.4
140°-150°	337.2	4.8
150°-160°	237.4	3.4
160°-170°	139.9	2.0
170°-180°	45.5	0.7
0°-30°	1075.3	15.4
0°-40°	1708.1	24.5
0°-60°	2844.3	40.8
0°-90°	3445.3	49.4
90°-120°	1759.9	25.3
90°-150°	3100.9	44.5
90°-180°	3524.0	50.6
0°-180°	6969.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1457	1457	1457	1457	1457	
5°	1455	1450	1438	1449	1447	138
15°	1384	1376	1354	1352	1343	390
25°	1255	1237	1198	1183	1171	577
35°	1081	1053	1005	974	958	676
45°	885	851	792	750	732	682
55°	671	635	574	527	507	600
65°	454	416	359	316	298	450
75°	242	208	163	140	131	256
85°	60	42	35	34	33	68
90°	1	9	15	20	22	5
95°	31	92	839	381	223	33
105°	107	150	687	1352	1255	113
115°	191	231	551	1188	1398	188
125°	265	311	529	945	1102	235
135°	311	374	525	792	915	241
145°	362	414	527	656	722	227
155°	413	444	514	580	605	190
165°	451	463	493	522	530	127
175°	469	469	473	478	476	45
180°	470	470	470	470	470	



TEST NUMBER: P333609-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1459.9	1459.3	1458.7	1458.1	1457.5	1456.3	1454.3	1452.4	1450.4	1448.5	1450.4
5°	1455.1	1454.1	1453.1	1452.1	1451.2	1449.3	1446.6	1443.9	1441.2	1438.5	1441.0
7.5°	1440.7	1439.8	1438.8	1437.9	1437.0	1434.9	1431.7	1428.5	1425.2	1422.0	1423.8
10°	1427.5	1426.8	1426.0	1425.3	1424.6	1422.5	1419.1	1415.7	1412.3	1408.8	1409.6
12.5°	1412.5	1411.6	1410.7	1409.7	1408.8	1406.1	1401.5	1396.9	1392.3	1387.6	1388.2
15°	1383.5	1382.0	1380.5	1379.1	1377.6	1374.4	1369.2	1364.1	1358.9	1353.8	1353.6
17.5°	1350.7	1348.4	1346.2	1343.9	1341.7	1337.3	1330.9	1324.5	1317.9	1311.5	1310.3
20°	1325.2	1322.7	1320.3	1317.8	1315.4	1310.3	1302.4	1294.6	1286.8	1279.0	1277.7
22.5°	1297.0	1294.5	1292.1	1289.6	1287.2	1281.9	1273.7	1265.4	1257.2	1249.0	1246.6
25°	1254.7	1251.1	1247.4	1243.7	1240.1	1233.7	1224.7	1215.6	1206.6	1197.5	1194.3
27.5°	1206.3	1201.8	1197.3	1192.9	1188.5	1181.5	1171.7	1162.0	1152.3	1142.6	1138.2
30°	1171.1	1166.4	1161.8	1157.2	1152.5	1145.0	1134.7	1124.5	1114.2	1103.9	1098.3
32.5°	1136.7	1131.3	1125.8	1120.5	1115.0	1107.1	1096.6	1086.1	1075.6	1065.2	1059.0
35°	1080.8	1075.0	1069.1	1063.2	1057.4	1048.9	1037.9	1026.9	1015.9	1004.9	997.8
37.5°	1026.0	1018.9	1011.7	1004.6	997.4	988.2	976.8	965.5	954.1	942.8	934.3
40°	987.2	979.9	972.6	965.2	957.9	948.4	936.6	924.9	913.1	901.4	892.1
42.5°	946.7	939.2	931.7	924.1	916.6	906.8	894.6	882.6	870.4	858.3	849.4
45°	884.9	877.8	870.7	863.6	856.6	846.3	832.8	819.4	805.9	792.5	782.7
47.5°	820.8	813.3	805.8	798.4	790.9	780.4	766.9	753.3	739.7	726.2	716.1
50°	780.3	772.3	764.2	756.1	748.0	737.0	723.1	709.1	695.2	681.3	671.0
52.5°	736.3	728.1	719.7	711.5	703.3	692.5	679.4	666.2	653.1	639.9	628.8
55°	671.4	663.6	655.7	647.9	640.1	629.3	615.6	601.9	588.2	574.5	563.5
57.5°	605.8	597.5	589.1	580.7	572.3	561.6	548.4	535.2	522.0	508.7	498.0
60°	563.5	555.0	546.4	537.9	529.3	518.4	505.2	492.0	478.7	465.5	454.8
62.5°	518.6	510.5	502.3	494.1	485.9	475.2	461.8	448.3	435.0	421.5	411.6
65°	454.5	446.2	437.9	429.6	421.3	410.7	397.7	384.7	371.8	358.8	349.0
67.5°	390.9	382.6	374.3	366.0	357.7	347.3	334.8	322.5	310.1	297.6	288.7
70°	347.8	339.5	331.2	322.9	314.5	304.3	292.0	279.8	267.6	255.4	247.8
72.5°	305.6	297.4	289.3	281.2	273.0	263.3	251.8	240.4	228.9	217.5	210.5
75°	242.1	234.8	227.5	220.1	212.8	204.0	193.7	183.4	173.2	162.9	157.5
77.5°	179.2	173.3	167.5	161.6	155.7	148.6	140.5	132.2	124.0	115.8	112.0
80°	143.1	137.2	131.3	125.5	119.6	113.2	106.4	99.5	92.7	85.9	83.6
82.5°	107.9	102.6	97.3	92.0	86.7	81.8	77.0	72.3	67.7	62.9	62.0
85°	60.5	56.1	51.7	47.3	42.9	40.1	38.9	37.7	36.4	35.2	35.0
87.5°	20.5	19.2	18.3	17.3	16.3	15.9	15.9	16.1	16.1	16.2	16.5
90°	1.0	1.9	3.8	5.7	7.6	9.5	10.4	12.3	13.3	15.2	16.1
92.5°	11.6	14.0	22.0	33.8	50.1	77.7	129.4	216.2	310.4	305.4	247.3
95°	31.2	32.2	39.8	50.2	71.0	113.7	215.1	423.5	684.9	839.4	821.3
97.5°	51.9	53.1	58.4	68.8	87.6	118.2	185.3	338.0	611.6	896.3	1039.3
100°	66.3	68.2	72.0	82.4	100.4	128.8	183.8	307.0	545.7	855.4	1092.3
102.5°	82.3	83.4	86.4	97.6	114.1	141.7	190.6	294.1	495.6	783.4	1060.5
105°	107.0	107.0	111.8	121.2	136.4	163.0	204.6	288.9	447.1	686.8	958.7
107.5°	131.3	133.2	137.7	145.5	161.3	185.1	225.4	297.7	426.6	620.3	854.9
110°	148.7	150.7	154.4	163.0	177.2	201.8	240.6	306.0	420.6	589.2	795.7



TEST NUMBER: P333609-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.2	168.0	171.0	179.6	193.8	217.7	255.0	316.6	420.6	571.0	751.8
115°	191.4	193.2	196.1	204.6	218.8	242.6	277.6	332.5	423.5	551.4	703.8
117.5°	214.1	217.0	220.0	228.5	244.6	267.5	300.7	350.7	429.7	541.7	675.2
120°	229.3	232.1	235.9	244.4	260.5	284.2	317.4	362.8	435.8	537.1	659.3
122.5°	245.2	247.3	250.3	258.8	276.5	300.1	333.3	376.5	441.1	533.4	645.7
125°	265.2	267.2	271.9	280.4	298.4	323.0	354.3	395.0	450.0	528.6	627.1
127.5°	281.0	283.8	289.9	300.7	319.8	344.5	374.5	412.1	460.0	526.4	610.1
130°	290.8	293.7	301.3	313.6	333.5	358.1	387.4	423.5	466.1	524.8	598.8
132.5°	298.4	302.0	311.1	325.0	345.6	370.2	399.6	433.3	472.9	524.8	589.6
135°	310.7	314.5	325.9	341.0	360.9	386.5	415.9	447.1	482.2	524.8	578.9
137.5°	326.3	329.1	339.7	354.9	374.4	400.7	427.5	457.4	490.7	525.9	569.2
140°	335.3	338.2	349.6	364.8	382.7	408.3	435.8	464.2	494.5	526.7	564.6
142.5°	345.9	348.1	358.7	373.8	391.1	415.2	441.1	468.0	496.8	527.5	560.8
145°	361.9	363.8	373.2	386.5	403.6	425.3	450.0	473.7	499.3	526.7	555.1
147.5°	378.5	379.7	387.8	400.1	414.9	434.1	455.7	477.1	500.2	524.2	549.3
150°	388.4	390.3	397.0	409.3	422.5	438.6	459.4	479.4	500.2	522.0	544.7
152.5°	399.0	400.1	406.0	416.9	429.3	443.9	463.3	480.9	499.5	518.9	539.4
155°	413.0	413.0	418.7	428.2	437.7	450.9	467.0	482.2	497.3	513.5	530.5
157.5°	425.6	425.3	429.9	438.1	446.4	456.4	470.3	483.1	494.9	507.8	522.2
160°	433.9	432.9	436.8	443.4	450.9	459.4	471.8	483.1	492.6	504.0	515.4
162.5°	440.7	439.8	443.5	449.4	455.5	462.5	473.3	482.4	490.3	499.5	509.3
165°	450.9	449.1	451.9	456.6	460.4	466.1	473.7	481.3	486.9	492.6	500.2
167.5°	457.8	456.8	458.5	461.1	463.8	467.4	473.7	479.0	481.6	486.0	491.3
170°	462.3	461.4	462.3	464.2	466.1	469.0	473.7	477.4	479.4	482.2	486.0
172.5°	465.4	463.7	464.6	466.4	467.6	469.0	472.9	476.0	476.3	477.7	480.7
175°	469.0	467.0	468.0	469.0	469.0	469.0	471.8	473.7	472.7	472.7	473.7
177.5°	470.7	469.1	469.1	469.9	469.1	469.1	470.7	471.4	469.9	469.9	470.7
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333609-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1452.4	1454.3	1456.3	1457.1	1456.9	1456.8	1456.5	1456.4
5°	1443.4	1445.9	1448.3	1449.3	1448.8	1448.3	1447.8	1447.3
7.5°	1425.5	1427.2	1428.9	1429.5	1428.9	1428.4	1427.8	1427.3
10°	1410.3	1411.0	1411.8	1411.8	1411.0	1410.3	1409.6	1408.8
12.5°	1388.8	1389.3	1389.8	1389.5	1388.4	1387.3	1386.2	1385.0
15°	1353.3	1353.1	1352.8	1351.6	1349.4	1347.2	1345.0	1342.8
17.5°	1309.0	1307.8	1306.6	1305.1	1303.3	1301.5	1299.7	1297.9
20°	1276.5	1275.3	1274.1	1272.4	1270.2	1268.0	1265.8	1263.6
22.5°	1244.2	1241.8	1239.4	1237.3	1235.5	1233.7	1231.8	1230.0
25°	1191.2	1188.0	1184.8	1181.9	1179.2	1176.5	1173.8	1171.1
27.5°	1133.8	1129.4	1124.9	1121.4	1118.8	1116.1	1113.5	1111.0
30°	1092.7	1087.0	1081.4	1077.5	1075.3	1073.1	1070.9	1068.7
32.5°	1052.8	1046.5	1040.3	1035.8	1033.1	1030.3	1027.4	1024.7
35°	990.7	983.6	976.5	971.3	967.8	964.4	961.0	957.6
37.5°	925.8	917.3	908.7	902.9	899.5	896.2	892.8	889.5
40°	882.8	873.5	864.2	858.1	855.2	852.2	849.3	846.4
42.5°	840.5	831.5	822.6	816.0	811.7	807.5	803.2	798.8
45°	772.9	763.1	753.3	746.6	742.9	739.2	735.6	731.9
47.5°	706.0	695.9	685.9	678.8	674.7	670.7	666.7	662.6
50°	660.7	650.4	640.2	633.2	629.6	625.9	622.2	618.6
52.5°	617.8	606.7	595.7	588.3	584.7	581.0	577.3	573.6
55°	552.5	541.5	530.5	523.0	519.1	515.2	511.3	507.4
57.5°	487.2	476.5	465.7	458.5	455.1	451.6	448.1	444.7
60°	444.0	433.3	422.5	415.3	411.6	408.0	404.3	400.6
62.5°	401.6	391.6	381.6	374.8	371.1	367.5	363.8	360.1
65°	339.2	329.5	319.7	312.9	309.2	305.6	301.9	298.2
67.5°	279.7	270.8	261.8	255.8	252.9	250.0	247.0	244.1
70°	240.2	232.6	225.0	219.7	216.8	213.9	210.9	208.0
72.5°	203.5	196.5	189.5	185.0	183.0	181.1	179.1	177.2
75°	152.1	146.8	141.4	137.8	136.1	134.4	132.6	130.9
77.5°	108.3	104.5	100.7	98.2	96.9	95.6	94.4	93.1
80°	81.4	79.2	77.0	75.7	75.2	74.7	74.2	73.7
82.5°	60.9	59.8	58.9	58.2	57.9	57.6	57.3	57.0
85°	34.7	34.5	34.2	34.0	33.8	33.5	33.3	33.0
87.5°	16.6	16.8	17.0	17.3	17.1	16.9	16.9	16.7
90°	17.0	18.0	18.9	20.9	20.9	20.9	21.8	21.8
92.5°	167.9	121.8	91.7	77.7	65.6	63.3	62.0	60.4
95°	681.1	537.1	420.6	341.0	273.8	245.3	237.8	222.7
97.5°	1014.4	913.5	800.0	689.3	630.7	577.7	550.2	538.1
100°	1165.2	1118.8	1021.2	922.7	857.4	789.1	754.1	738.9
102.5°	1216.0	1244.6	1197.8	1131.1	1061.2	1012.7	974.6	963.3
105°	1186.1	1315.9	1357.6	1347.1	1316.8	1285.6	1266.6	1255.2
107.5°	1079.2	1252.4	1359.4	1408.9	1424.2	1424.1	1417.8	1410.2
110°	1000.4	1180.4	1313.9	1394.5	1437.1	1455.1	1461.8	1461.8





TEST NUMBER: P333609-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	938.2	1109.1	1244.2	1339.1	1401.5	1432.4	1448.9	1455.7
115°	860.2	1007.1	1136.8	1240.1	1313.9	1359.4	1385.9	1398.2
117.5°	809.8	936.4	1048.1	1142.9	1216.8	1263.8	1290.1	1297.6
120°	782.5	896.2	1000.4	1083.8	1153.9	1199.3	1224.9	1232.5
122.5°	762.1	867.4	960.3	1038.3	1100.8	1142.5	1168.1	1174.9
125°	732.3	828.9	911.3	979.6	1032.6	1071.5	1092.3	1101.8
127.5°	702.0	792.1	869.1	932.9	981.0	1015.4	1035.1	1039.3
130°	683.1	766.4	840.3	901.9	949.3	980.5	999.5	1005.1
132.5°	664.1	742.2	809.2	868.5	915.9	947.1	964.6	971.0
135°	639.4	704.8	765.5	819.5	861.1	892.4	909.5	915.2
137.5°	618.6	671.5	721.9	767.8	805.0	833.5	849.2	855.4
140°	607.2	651.8	695.4	735.2	770.2	794.8	809.0	813.8
142.5°	597.4	635.1	672.6	707.1	736.9	757.7	771.1	775.1
145°	584.5	613.8	643.3	668.8	691.5	707.7	718.1	721.9
147.5°	572.4	596.2	618.8	638.1	656.2	669.0	675.1	676.8
150°	565.6	586.4	604.4	621.4	635.7	647.0	650.9	651.8
152.5°	558.0	576.6	593.0	606.3	618.2	627.3	631.1	632.1
155°	546.6	561.7	575.0	585.5	594.9	601.5	604.4	605.4
157.5°	535.2	547.7	558.0	566.1	573.5	579.0	581.6	581.5
160°	527.7	537.1	546.6	553.3	559.9	564.6	566.6	565.6
162.5°	519.3	528.1	536.0	541.8	547.0	551.0	551.4	551.1
165°	507.8	514.4	520.1	524.8	528.6	530.5	530.5	530.5
167.5°	496.8	501.2	505.5	508.9	510.8	512.5	511.8	511.6
170°	490.7	493.6	496.4	498.3	500.2	501.2	501.2	500.2
172.5°	483.9	486.7	488.9	490.0	490.3	492.0	490.6	489.6
175°	476.5	476.5	478.4	478.4	478.4	479.4	477.4	476.5
177.5°	471.4	472.1	472.1	472.1	471.4	472.1	469.9	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9

(END OF REPORT)