

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333501-840

Luminaire Tested: **S125RDIP-S375D590U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333501-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D590U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3604.1 lumens
Efficiency: N/A
Efficacy: 140.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333501-840

CATALOG NUMBER: S125RDIP-S375D590U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333501-840

CATALOG NUMBER: S125RDIP-S375D590U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	92	88	84	87	84	80	78	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20	17
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	20	17	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3991	3991	3991
5°	4000	3955	3979
10°	3970	3918	3918
15°	3922	3839	3807
20°	3862	3727	3682
25°	3792	3619	3539
30°	3703	3491	3380
35°	3613	3360	3202
40°	3530	3222	3026
45°	3428	3070	2834
50°	3325	2903	2635
55°	3206	2743	2423
60°	3086	2550	2195
65°	2946	2326	1932
70°	2783	2045	1665
75°	2563	1724	1385
80°	2258	1354	1164
85°	1904	1104	1037



TEST NUMBER: P333501-840

CATALOG NUMBER: S125RDIP-S375D590U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	1.6
10°-20°	162.4	4.5
20°-30°	235.5	6.5
30°-40°	268.4	7.4
40°-50°	261.6	7.3
50°-60°	220.2	6.1
60°-70°	154.3	4.3
70°-80°	79.3	2.2
80°-90°	21.6	0.6
90°-100°	207.1	5.7
100°-110°	445.2	12.4
110°-120°	417.8	11.6
120°-130°	338.6	9.4
130°-140°	271.7	7.5
140°-150°	205.1	5.7
150°-160°	144.3	4.0
160°-170°	85.1	2.4
170°-180°	27.7	0.8
0°-30°	456.0	12.7
0°-40°	724.3	20.1
0°-60°	1206.1	33.5
0°-90°	1461.4	40.5
90°-120°	1070.2	29.7
90°-150°	1885.6	52.3
90°-180°	2143.0	59.5
0°-180°	3604.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	614	58
15°	587	584	574	573	569	165
25°	532	524	508	502	497	245
35°	458	447	426	413	406	287
45°	375	361	336	318	310	289
55°	285	269	244	223	215	255
65°	193	176	152	134	126	191
75°	103	88	69	59	56	109
85°	26	18	15	14	14	29
90°	1	5	9	12	13	2
95°	19	56	510	232	135	20
105°	65	91	418	822	763	69
115°	116	140	335	723	850	114
125°	161	189	321	575	670	143
135°	189	227	319	482	556	147
145°	220	252	320	399	439	138
155°	251	270	312	353	368	116
165°	274	282	300	318	323	77
175°	285	285	287	291	290	27
180°	286	286	286	286	286	



TEST NUMBER: P333501-840

CATALOG NUMBER: S125RDIP-S375D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	619.0	618.8	618.5	618.3	618.0	617.5	616.7	615.8	615.0	614.2	615.0
5°	617.0	616.6	616.2	615.7	615.3	614.6	613.4	612.3	611.2	610.0	611.1
7.5°	611.0	610.6	610.2	609.8	609.4	608.4	607.1	605.7	604.4	603.0	603.7
10°	605.3	605.0	604.7	604.4	604.1	603.2	601.8	600.3	598.8	597.4	597.7
12.5°	599.0	598.5	598.2	597.8	597.4	596.2	594.3	592.4	590.4	588.4	588.7
15°	586.6	586.0	585.4	584.8	584.2	582.8	580.6	578.5	576.2	574.1	574.0
17.5°	572.8	571.8	570.9	569.9	569.0	567.1	564.3	561.6	558.9	556.1	555.6
20°	561.9	560.9	559.9	558.9	557.7	555.6	552.3	549.0	545.6	542.3	541.8
22.5°	550.0	549.0	548.0	546.8	545.8	543.6	540.1	536.6	533.1	529.7	528.7
25°	532.1	530.5	529.0	527.4	525.8	523.1	519.3	515.4	511.6	507.8	506.4
27.5°	511.5	509.7	507.8	505.8	503.9	501.0	496.9	492.7	488.7	484.5	482.6
30°	496.6	494.6	492.6	490.7	488.7	485.5	481.2	476.9	472.5	468.1	465.7
32.5°	482.0	479.7	477.5	475.1	472.8	469.5	465.0	460.6	456.2	451.7	449.1
35°	458.3	455.9	453.3	450.8	448.4	444.7	440.1	435.5	430.8	426.2	423.1
37.5°	435.0	432.0	429.0	426.0	422.9	419.0	414.2	409.4	404.7	399.8	396.2
40°	418.7	415.6	412.4	409.3	406.2	402.1	397.2	392.2	387.2	382.2	378.3
42.5°	401.4	398.3	395.1	391.9	388.7	384.6	379.4	374.3	369.1	364.0	360.2
45°	375.3	372.2	369.2	366.2	363.2	358.8	353.1	347.5	341.7	336.1	331.8
47.5°	348.1	344.9	341.7	338.5	335.4	330.9	325.2	319.4	313.7	307.9	303.7
50°	330.9	327.5	324.1	320.6	317.2	312.6	306.6	300.7	294.8	288.9	284.6
52.5°	312.3	308.7	305.2	301.7	298.2	293.7	288.1	282.5	276.9	271.4	266.7
55°	284.7	281.3	278.0	274.8	271.5	266.9	261.1	255.2	249.4	243.6	238.9
57.5°	256.9	253.4	249.7	246.2	242.7	238.1	232.5	226.9	221.4	215.7	211.2
60°	238.9	235.3	231.7	228.0	224.4	219.8	214.2	208.6	203.0	197.4	192.9
62.5°	219.9	216.4	213.0	209.5	206.0	201.5	195.8	190.2	184.4	178.7	174.5
65°	192.8	189.2	185.7	182.2	178.6	174.1	168.6	163.2	157.6	152.2	148.0
67.5°	165.8	162.3	158.8	155.2	151.7	147.2	142.0	136.7	131.5	126.2	122.4
70°	147.4	144.0	140.5	136.9	133.4	129.1	123.8	118.7	113.5	108.3	105.0
72.5°	129.6	126.1	122.7	119.3	115.8	111.6	106.7	101.9	97.0	92.2	89.3
75°	102.7	99.6	96.4	93.3	90.3	86.5	82.1	77.8	73.4	69.1	66.8
77.5°	75.9	73.5	71.0	68.5	66.0	63.0	59.6	56.0	52.6	49.1	47.5
80°	60.7	58.2	55.7	53.2	50.7	48.1	45.1	42.2	39.3	36.4	35.4
82.5°	45.7	43.5	41.3	39.0	36.8	34.6	32.7	30.7	28.7	26.7	26.3
85°	25.7	23.8	21.9	20.1	18.2	17.0	16.5	16.0	15.5	14.9	14.8
87.5°	8.7	8.3	7.9	7.6	7.2	7.1	7.1	7.3	7.3	7.5	7.6
90°	0.6	1.1	2.3	3.4	4.6	5.8	6.4	7.5	8.1	9.2	9.8
92.5°	7.1	8.5	13.3	20.5	30.4	47.3	78.7	131.5	188.7	185.7	150.4
95°	19.0	19.6	24.2	30.5	43.2	69.2	130.8	257.5	416.5	510.4	499.5
97.5°	31.6	32.2	35.4	41.8	53.2	71.9	112.7	205.5	371.9	545.0	632.0
100°	40.3	41.5	43.8	50.1	61.1	78.4	111.8	186.6	331.8	520.2	664.2
102.5°	50.0	50.7	52.5	59.4	69.4	86.1	115.9	178.8	301.3	476.4	644.8
105°	65.1	65.1	68.0	73.7	82.9	99.1	124.4	175.7	271.9	417.7	583.0
107.5°	79.9	81.0	83.7	88.5	98.1	112.6	137.1	181.0	259.4	377.2	519.9
110°	90.5	91.6	93.9	99.1	107.8	122.7	146.3	186.0	255.8	358.3	483.9



TEST NUMBER: P333501-840

CATALOG NUMBER: S125RDIP-S375D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	101.1	102.2	104.0	109.3	117.9	132.4	155.1	192.5	255.8	347.3	457.2
115°	116.3	117.5	119.3	124.4	133.1	147.4	168.7	202.2	257.5	335.3	428.0
117.5°	130.2	131.9	133.8	139.0	148.8	162.7	182.9	213.3	261.3	329.4	410.6
120°	139.4	141.2	143.4	148.7	158.4	172.8	193.0	220.7	265.0	326.6	400.9
122.5°	149.1	150.4	152.2	157.3	168.1	182.5	202.7	228.9	268.2	324.4	392.6
125°	161.3	162.5	165.3	170.5	181.5	196.4	215.4	240.2	273.7	321.4	381.3
127.5°	170.9	172.6	176.3	182.9	194.5	209.4	227.7	250.5	279.7	320.0	371.0
130°	176.8	178.5	183.2	190.7	202.8	217.7	235.6	257.5	283.5	319.1	364.1
132.5°	181.5	183.7	189.1	197.6	210.2	225.1	243.0	263.5	287.6	319.1	358.5
135°	188.9	191.3	198.1	207.4	219.4	235.0	252.9	271.9	293.2	319.1	351.9
137.5°	198.4	200.2	206.6	215.8	227.6	243.7	259.9	278.1	298.4	319.8	346.1
140°	203.9	205.6	212.6	221.8	232.8	248.3	265.0	282.3	300.7	320.3	343.4
142.5°	210.4	211.7	218.1	227.3	237.8	252.5	268.2	284.6	302.1	320.7	341.0
145°	220.0	221.2	226.9	235.0	245.4	258.6	273.7	288.0	303.6	320.3	337.6
147.5°	230.1	230.9	235.8	243.3	252.3	264.0	277.1	290.1	304.2	318.8	334.0
150°	236.2	237.3	241.4	248.8	256.9	266.7	279.4	291.4	304.2	317.4	331.2
152.5°	242.7	243.3	246.9	253.5	261.1	269.9	281.7	292.4	303.7	315.6	328.0
155°	251.2	251.2	254.6	260.3	266.1	274.2	284.0	293.2	302.5	312.3	322.6
157.5°	258.7	258.6	261.5	266.4	271.5	277.5	286.0	293.8	300.9	308.7	317.5
160°	263.9	263.3	265.6	269.6	274.2	279.4	286.9	293.8	299.5	306.5	313.4
162.5°	268.0	267.4	269.7	273.3	277.0	281.2	287.8	293.4	298.2	303.7	309.7
165°	274.2	273.1	274.8	277.6	279.9	283.5	288.0	292.7	296.1	299.5	304.2
167.5°	278.3	277.8	278.8	280.4	282.1	284.2	288.0	291.2	292.9	295.5	298.7
170°	281.1	280.5	281.1	282.3	283.5	285.2	288.0	290.3	291.4	293.2	295.5
172.5°	283.0	282.0	282.5	283.7	284.4	285.2	287.6	289.4	289.6	290.4	292.3
175°	285.2	284.0	284.6	285.2	285.2	285.2	286.9	288.0	287.4	287.4	288.0
177.5°	286.2	285.3	285.3	285.7	285.3	285.3	286.2	286.6	285.7	285.7	286.2
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333501-840

CATALOG NUMBER: S125RDIP-S375D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	617.9	617.9	617.9	617.9	617.9	617.9	617.9	617.9
2.5°	615.8	616.7	617.5	617.9	617.8	617.7	617.6	617.5
5°	612.1	613.1	614.1	614.6	614.4	614.1	613.9	613.7
7.5°	604.4	605.2	605.9	606.1	605.9	605.7	605.5	605.2
10°	598.0	598.3	598.6	598.6	598.3	598.0	597.7	597.4
12.5°	588.9	589.2	589.4	589.3	588.8	588.2	587.8	587.3
15°	573.8	573.7	573.6	573.1	572.2	571.3	570.4	569.4
17.5°	555.1	554.6	554.1	553.4	552.7	551.9	551.1	550.4
20°	541.3	540.8	540.3	539.6	538.6	537.7	536.7	535.8
22.5°	527.6	526.5	525.5	524.6	523.9	523.1	522.4	521.6
25°	505.1	503.7	502.4	501.2	500.0	498.9	497.8	496.6
27.5°	480.8	478.9	477.0	475.5	474.4	473.3	472.2	471.1
30°	463.3	461.0	458.6	457.0	456.0	455.0	454.1	453.2
32.5°	446.5	443.8	441.1	439.3	438.1	436.9	435.7	434.5
35°	420.1	417.1	414.0	411.8	410.4	409.0	407.5	406.1
37.5°	392.5	389.0	385.4	382.8	381.4	380.0	378.6	377.2
40°	374.4	370.4	366.5	363.9	362.6	361.4	360.1	358.9
42.5°	356.4	352.6	348.8	346.1	344.3	342.3	340.5	338.7
45°	327.7	323.6	319.4	316.6	315.1	313.5	311.9	310.3
47.5°	299.4	295.1	290.8	287.8	286.1	284.4	282.7	280.9
50°	280.1	275.8	271.5	268.5	267.0	265.4	263.9	262.3
52.5°	262.0	257.3	252.6	249.4	247.9	246.4	244.8	243.3
55°	234.3	229.6	225.0	221.8	220.2	218.4	216.8	215.2
57.5°	206.6	202.1	197.4	194.4	193.0	191.5	190.1	188.5
60°	188.3	183.7	179.2	176.1	174.5	173.0	171.5	169.9
62.5°	170.3	166.0	161.8	159.0	157.3	155.8	154.3	152.7
65°	143.8	139.7	135.5	132.7	131.2	129.6	128.1	126.4
67.5°	118.6	114.8	111.0	108.5	107.2	106.0	104.7	103.5
70°	101.9	98.7	95.4	93.2	91.9	90.7	89.5	88.2
72.5°	86.2	83.3	80.4	78.5	77.7	76.9	75.9	75.1
75°	64.5	62.2	60.0	58.5	57.8	57.0	56.2	55.5
77.5°	45.9	44.3	42.7	41.6	41.1	40.6	40.0	39.5
80°	34.5	33.6	32.7	32.1	31.9	31.7	31.5	31.3
82.5°	25.9	25.3	24.9	24.6	24.5	24.4	24.3	24.1
85°	14.7	14.6	14.5	14.4	14.3	14.2	14.1	14.0
87.5°	7.7	7.8	7.9	8.1	8.0	8.0	8.0	7.9
90°	10.4	10.9	11.5	12.6	12.6	12.6	13.2	13.2
92.5°	102.1	74.1	55.7	47.3	39.9	38.5	37.7	36.8
95°	414.1	326.6	255.8	207.4	166.5	149.2	144.6	135.4
97.5°	616.8	555.4	486.5	419.1	383.5	351.2	334.6	327.2
100°	708.5	680.3	621.0	561.1	521.3	479.9	458.6	449.3
102.5°	739.4	756.8	728.3	687.8	645.3	615.8	592.7	585.7
105°	721.2	800.1	825.5	819.1	800.7	781.7	770.2	763.3
107.5°	656.2	761.5	826.7	856.7	866.1	866.0	862.1	857.5
110°	608.3	717.8	799.0	848.0	873.8	884.8	888.9	888.9



TEST NUMBER: P333501-840

CATALOG NUMBER: S125RDIP-S375D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	570.6	674.5	756.6	814.4	852.2	871.0	881.0	885.1
115°	523.0	612.4	691.3	754.1	799.0	826.7	842.7	850.3
117.5°	492.4	569.4	637.3	695.0	739.9	768.5	784.5	789.1
120°	475.8	544.9	608.3	659.0	701.7	729.3	744.9	749.4
122.5°	463.4	527.5	583.9	631.4	669.3	694.7	710.2	714.4
125°	445.2	504.0	554.2	595.6	627.9	651.6	664.2	669.9
127.5°	426.9	481.7	528.5	567.3	596.5	617.4	629.3	632.0
130°	415.4	466.1	511.0	548.4	577.2	596.2	607.7	611.2
132.5°	403.8	451.3	492.1	528.2	556.9	575.9	586.5	590.5
135°	388.8	428.6	465.4	498.3	523.6	542.6	553.0	556.4
137.5°	376.2	408.3	439.0	466.9	489.5	506.9	516.3	520.2
140°	369.2	396.4	422.8	447.1	468.4	483.3	491.9	494.8
142.5°	363.2	386.2	409.0	430.0	448.1	460.7	468.9	471.3
145°	355.5	373.2	391.1	406.7	420.5	430.3	436.7	439.0
147.5°	348.1	362.5	376.3	388.0	399.0	406.8	410.5	411.5
150°	343.9	356.6	367.5	377.9	386.6	393.4	395.8	396.4
152.5°	339.3	350.6	360.6	368.7	376.0	381.4	383.7	384.4
155°	332.3	341.6	349.6	356.0	361.7	365.8	367.5	368.1
157.5°	325.5	333.1	339.3	344.3	348.7	352.0	353.7	353.6
160°	320.8	326.6	332.3	336.4	340.4	343.4	344.5	343.9
162.5°	315.8	321.1	325.9	329.5	332.6	335.1	335.3	335.2
165°	308.7	312.8	316.3	319.1	321.4	322.6	322.6	322.6
167.5°	302.1	304.8	307.4	309.4	310.6	311.6	311.1	311.0
170°	298.4	300.1	301.8	303.0	304.2	304.8	304.8	304.2
172.5°	294.3	296.0	297.2	297.9	298.2	299.2	298.3	297.7
175°	289.7	289.7	290.9	290.9	290.9	291.4	290.3	289.7
177.5°	286.6	287.1	287.1	287.1	286.6	287.1	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7

(END OF REPORT)