

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333597-930

Luminaire Tested: **S125RDIP-S1090D810U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333597-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D810U930-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5815.5 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333597-930

CATALOG NUMBER: S125RDIP-S1090D810U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333597-930

CATALOG NUMBER: S125RDIP-S1090D810U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	43	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	51	45	65	55	48	42	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	43	36	30	52	41	34	29	36	31	27	32	27	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	24	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9412	9412	9412
5°	9433	9326	9383
10°	9362	9239	9239
15°	9250	9052	8978
20°	9108	8790	8685
25°	8941	8533	8345
30°	8733	8232	7970
35°	8521	7923	7550
40°	8323	7599	7136
45°	8082	7238	6685
50°	7840	6845	6215
55°	7560	6469	5713
60°	7279	6013	5174
65°	6946	5483	4557
70°	6567	4823	3928
75°	6041	4065	3266
80°	5322	3195	2741
85°	4483	2608	2445



TEST NUMBER: P333597-930

CATALOG NUMBER: S125RDIP-S1090D810U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.0	2.4
10°-20°	382.9	6.6
20°-30°	555.3	9.5
30°-40°	632.9	10.9
40°-50°	616.9	10.6
50°-60°	519.3	8.9
60°-70°	364.0	6.3
70°-80°	187.1	3.2
80°-90°	49.0	0.8
90°-100°	229.2	3.9
100°-110°	492.7	8.5
110°-120°	462.4	8.0
120°-130°	374.7	6.4
130°-140°	300.7	5.2
140°-150°	226.9	3.9
150°-160°	159.7	2.7
160°-170°	94.2	1.6
170°-180°	30.6	0.5
0°-30°	1075.3	18.5
0°-40°	1708.1	29.4
0°-60°	2844.3	48.9
0°-90°	3444.4	59.2
90°-120°	1184.3	20.4
90°-150°	2086.6	35.9
90°-180°	2371.0	40.8
0°-180°	5815.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1457	1457	1457	1457	1457	
5°	1455	1450	1438	1449	1447	138
15°	1384	1376	1354	1352	1343	390
25°	1255	1237	1198	1183	1171	577
35°	1081	1053	1005	974	958	676
45°	885	851	792	750	732	682
55°	671	635	574	527	507	600
65°	454	416	359	316	298	450
75°	242	208	163	140	131	256
85°	60	42	35	34	33	68
90°	1	6	10	13	15	4
95°	21	62	565	256	150	22
105°	72	101	462	910	845	76
115°	129	155	371	800	941	127
125°	178	209	356	636	741	158
135°	209	252	353	533	616	162
145°	244	279	354	441	486	153
155°	278	299	346	390	407	128
165°	304	312	332	352	357	85
175°	316	316	318	322	321	30
180°	316	316	316	316	316	



TEST NUMBER: P333597-930

CATALOG NUMBER: S125RDIP-S1090D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1459.9	1459.3	1458.7	1458.1	1457.5	1456.3	1454.3	1452.4	1450.4	1448.5	1450.4
5°	1455.1	1454.1	1453.1	1452.1	1451.2	1449.3	1446.6	1443.9	1441.2	1438.5	1441.0
7.5°	1440.7	1439.8	1438.8	1437.9	1437.0	1434.9	1431.7	1428.5	1425.2	1422.0	1423.8
10°	1427.5	1426.8	1426.0	1425.3	1424.6	1422.5	1419.1	1415.7	1412.3	1408.8	1409.6
12.5°	1412.5	1411.6	1410.7	1409.7	1408.8	1406.1	1401.5	1396.9	1392.3	1387.6	1388.2
15°	1383.5	1382.0	1380.5	1379.1	1377.6	1374.4	1369.2	1364.1	1358.9	1353.8	1353.6
17.5°	1350.7	1348.4	1346.2	1343.9	1341.7	1337.3	1330.9	1324.5	1317.9	1311.5	1310.3
20°	1325.2	1322.7	1320.3	1317.8	1315.4	1310.3	1302.4	1294.6	1286.8	1279.0	1277.7
22.5°	1297.0	1294.5	1292.1	1289.6	1287.2	1281.9	1273.7	1265.4	1257.2	1249.0	1246.6
25°	1254.7	1251.1	1247.4	1243.7	1240.1	1233.7	1224.7	1215.6	1206.6	1197.5	1194.3
27.5°	1206.3	1201.8	1197.3	1192.9	1188.5	1181.5	1171.7	1162.0	1152.3	1142.6	1138.2
30°	1171.1	1166.4	1161.8	1157.2	1152.5	1145.0	1134.7	1124.5	1114.2	1103.9	1098.3
32.5°	1136.7	1131.3	1125.8	1120.5	1115.0	1107.1	1096.6	1086.1	1075.6	1065.2	1059.0
35°	1080.8	1075.0	1069.1	1063.2	1057.4	1048.9	1037.9	1026.9	1015.9	1004.9	997.8
37.5°	1026.0	1018.9	1011.7	1004.6	997.4	988.2	976.8	965.5	954.1	942.8	934.3
40°	987.2	979.9	972.6	965.2	957.9	948.4	936.6	924.9	913.1	901.4	892.1
42.5°	946.7	939.2	931.7	924.1	916.6	906.8	894.6	882.6	870.4	858.3	849.4
45°	884.9	877.8	870.7	863.6	856.6	846.3	832.8	819.4	805.9	792.5	782.7
47.5°	820.8	813.3	805.8	798.4	790.9	780.4	766.9	753.3	739.7	726.2	716.1
50°	780.3	772.3	764.2	756.1	748.0	737.0	723.1	709.1	695.2	681.3	671.0
52.5°	736.3	728.1	719.7	711.5	703.3	692.5	679.4	666.2	653.1	639.9	628.8
55°	671.4	663.6	655.7	647.9	640.1	629.3	615.6	601.9	588.2	574.5	563.5
57.5°	605.8	597.5	589.1	580.7	572.3	561.6	548.4	535.2	522.0	508.7	498.0
60°	563.5	555.0	546.4	537.9	529.3	518.4	505.2	492.0	478.7	465.5	454.8
62.5°	518.6	510.5	502.3	494.1	485.9	475.2	461.8	448.3	435.0	421.5	411.6
65°	454.5	446.2	437.9	429.6	421.3	410.7	397.7	384.7	371.8	358.8	349.0
67.5°	390.9	382.6	374.3	366.0	357.7	347.3	334.8	322.5	310.1	297.6	288.7
70°	347.8	339.5	331.2	322.9	314.5	304.3	292.0	279.8	267.6	255.4	247.8
72.5°	305.6	297.4	289.3	281.2	273.0	263.3	251.8	240.4	228.9	217.5	210.5
75°	242.1	234.8	227.5	220.1	212.8	204.0	193.7	183.4	173.2	162.9	157.5
77.5°	179.2	173.3	167.5	161.6	155.7	148.6	140.5	132.2	124.0	115.8	112.0
80°	143.1	137.2	131.3	125.5	119.6	113.2	106.4	99.5	92.7	85.9	83.6
82.5°	107.9	102.6	97.3	92.0	86.7	81.8	77.0	72.3	67.7	62.9	62.0
85°	60.5	56.1	51.7	47.3	42.9	40.1	38.9	37.7	36.4	35.2	35.0
87.5°	20.4	19.2	18.0	16.9	15.8	15.2	15.2	15.2	15.2	15.2	15.4
90°	0.7	1.3	2.5	3.8	5.1	6.4	7.0	8.3	8.9	10.2	10.8
92.5°	7.7	9.5	14.8	22.7	33.7	52.3	87.1	145.4	208.8	205.5	166.4
95°	21.0	21.7	26.7	33.8	47.8	76.5	144.7	284.9	460.9	564.8	552.7
97.5°	34.9	35.7	39.3	46.3	58.9	79.6	124.7	227.5	411.6	603.2	699.3
100°	44.6	45.9	48.4	55.4	67.6	86.7	123.7	206.5	367.2	575.7	735.0
102.5°	55.4	56.1	58.1	65.6	76.7	95.4	128.2	197.9	333.5	527.2	713.6
105°	72.1	72.1	75.3	81.6	91.8	109.7	137.7	194.4	300.9	462.2	645.1
107.5°	88.4	89.6	92.7	97.9	108.5	124.6	151.7	200.3	287.1	417.4	575.3
110°	100.1	101.3	103.9	109.7	119.2	135.7	161.9	205.9	283.1	396.5	535.5



TEST NUMBER: P333597-930

CATALOG NUMBER: S125RDIP-S1090D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.8	113.1	115.1	120.8	130.4	146.5	171.6	213.0	283.1	384.3	505.9
115°	128.7	130.0	132.0	137.7	147.2	163.2	186.8	223.7	284.9	371.0	473.6
117.5°	144.1	146.0	148.1	153.8	164.6	180.0	202.4	236.0	289.2	364.5	454.4
120°	154.3	156.2	158.7	164.4	175.3	191.3	213.5	244.2	293.3	361.4	443.7
122.5°	165.0	166.4	168.4	174.1	186.1	201.9	224.3	253.3	296.8	358.9	434.5
125°	178.5	179.8	183.0	188.7	200.8	217.4	238.4	265.8	302.8	355.7	422.0
127.5°	189.1	191.0	195.1	202.4	215.2	231.8	252.1	277.3	309.6	354.2	410.5
130°	195.7	197.6	202.7	211.0	224.4	241.0	260.7	284.9	313.6	353.2	402.9
132.5°	200.8	203.3	209.4	218.7	232.5	249.2	268.9	291.6	318.2	353.2	396.8
135°	209.1	211.7	219.3	229.5	242.9	260.1	279.9	300.9	324.5	353.2	389.5
137.5°	219.6	221.4	228.6	238.8	251.9	269.6	287.6	307.8	330.2	353.9	383.0
140°	225.7	227.6	235.2	245.4	257.6	274.8	293.3	312.3	332.7	354.4	379.9
142.5°	232.8	234.2	241.3	251.5	263.2	279.3	296.8	315.0	334.3	355.0	377.4
145°	243.5	244.8	251.2	260.1	271.6	286.3	302.8	318.7	336.0	354.4	373.6
147.5°	254.7	255.5	261.0	269.3	279.2	292.1	306.6	321.1	336.6	352.8	369.6
150°	261.4	262.6	267.1	275.4	284.3	295.1	309.2	322.5	336.6	351.2	366.6
152.5°	268.5	269.3	273.2	280.5	288.9	298.7	311.7	323.6	336.1	349.2	363.0
155°	277.9	277.9	281.8	288.1	294.5	303.5	314.3	324.5	334.7	345.5	357.0
157.5°	286.3	286.3	289.3	294.7	300.4	307.1	316.4	325.1	333.0	341.7	351.4
160°	292.0	291.3	293.9	298.3	303.5	309.2	317.5	325.1	331.5	339.2	346.8
162.5°	296.5	296.0	298.5	302.4	306.5	311.2	318.5	324.6	330.0	336.1	342.7
165°	303.5	302.1	304.1	307.3	309.8	313.6	318.7	323.8	327.7	331.5	336.6
167.5°	308.0	307.4	308.5	310.3	312.1	314.5	318.7	322.3	324.1	327.0	330.6
170°	311.1	310.5	311.1	312.3	313.6	315.5	318.7	321.3	322.5	324.5	327.0
172.5°	313.2	312.0	312.6	313.9	314.6	315.5	318.2	320.2	320.5	321.4	323.4
175°	315.5	314.3	315.0	315.5	315.5	315.5	317.5	318.7	318.1	318.1	318.7
177.5°	316.7	315.7	315.7	316.2	315.7	315.7	316.7	317.2	316.2	316.2	316.7
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333597-930

CATALOG NUMBER: S125RDIP-S1090D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1452.4	1454.3	1456.3	1457.1	1456.9	1456.8	1456.5	1456.4
5°	1443.4	1445.9	1448.3	1449.3	1448.8	1448.3	1447.8	1447.3
7.5°	1425.5	1427.2	1428.9	1429.5	1428.9	1428.4	1427.8	1427.3
10°	1410.3	1411.0	1411.8	1411.8	1411.0	1410.3	1409.6	1408.8
12.5°	1388.8	1389.3	1389.8	1389.5	1388.4	1387.3	1386.2	1385.0
15°	1353.3	1353.1	1352.8	1351.6	1349.4	1347.2	1345.0	1342.8
17.5°	1309.0	1307.8	1306.6	1305.1	1303.3	1301.5	1299.7	1297.9
20°	1276.5	1275.3	1274.1	1272.4	1270.2	1268.0	1265.8	1263.6
22.5°	1244.2	1241.8	1239.4	1237.3	1235.5	1233.7	1231.8	1230.0
25°	1191.2	1188.0	1184.8	1181.9	1179.2	1176.5	1173.8	1171.1
27.5°	1133.8	1129.4	1124.9	1121.4	1118.8	1116.1	1113.5	1111.0
30°	1092.7	1087.0	1081.4	1077.5	1075.3	1073.1	1070.9	1068.7
32.5°	1052.8	1046.5	1040.3	1035.8	1033.1	1030.3	1027.4	1024.7
35°	990.7	983.6	976.5	971.3	967.8	964.4	961.0	957.6
37.5°	925.8	917.3	908.7	902.9	899.5	896.2	892.8	889.5
40°	882.8	873.5	864.2	858.1	855.2	852.2	849.3	846.4
42.5°	840.5	831.5	822.6	816.0	811.7	807.5	803.2	798.8
45°	772.9	763.1	753.3	746.6	742.9	739.2	735.6	731.9
47.5°	706.0	695.9	685.9	678.8	674.7	670.7	666.7	662.6
50°	660.7	650.4	640.2	633.2	629.6	625.9	622.2	618.6
52.5°	617.8	606.7	595.7	588.3	584.7	581.0	577.3	573.6
55°	552.5	541.5	530.5	523.0	519.1	515.2	511.3	507.4
57.5°	487.2	476.5	465.7	458.5	455.1	451.6	448.1	444.7
60°	444.0	433.3	422.5	415.3	411.6	408.0	404.3	400.6
62.5°	401.6	391.6	381.6	374.8	371.1	367.5	363.8	360.1
65°	339.2	329.5	319.7	312.9	309.2	305.6	301.9	298.2
67.5°	279.7	270.8	261.8	255.8	252.9	250.0	247.0	244.1
70°	240.2	232.6	225.0	219.7	216.8	213.9	210.9	208.0
72.5°	203.5	196.5	189.5	185.0	183.0	181.1	179.1	177.2
75°	152.1	146.8	141.4	137.8	136.1	134.4	132.6	130.9
77.5°	108.3	104.5	100.7	98.2	96.9	95.6	94.4	93.1
80°	81.4	79.2	77.0	75.7	75.2	74.7	74.2	73.7
82.5°	60.9	59.8	58.9	58.2	57.9	57.6	57.3	57.0
85°	34.7	34.5	34.2	34.0	33.8	33.5	33.3	33.0
87.5°	15.5	15.7	15.7	15.9	15.7	15.5	15.5	15.2
90°	11.5	12.1	12.7	14.0	14.0	14.0	14.7	14.7
92.5°	113.0	82.0	61.7	52.3	44.1	42.6	41.7	40.7
95°	458.4	361.4	283.1	229.5	184.3	165.1	160.0	149.8
97.5°	682.7	614.7	538.3	463.8	424.4	388.7	370.2	362.1
100°	784.1	752.8	687.2	620.9	576.9	531.0	507.4	497.3
102.5°	818.2	837.6	806.0	761.2	714.1	681.4	655.8	648.2
105°	798.1	885.5	913.5	906.5	886.1	865.0	852.3	844.7
107.5°	726.2	842.8	914.8	948.0	958.4	958.2	954.1	948.9
110°	673.2	794.3	884.2	938.3	967.0	979.2	983.7	983.7



TEST NUMBER: P333597-930

CATALOG NUMBER: S125RDIP-S1090D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	631.4	746.3	837.2	901.2	943.1	963.8	974.9	979.6
115°	578.9	677.7	765.0	834.5	884.2	914.8	932.6	940.9
117.5°	544.9	630.1	705.3	769.1	818.8	850.4	868.1	873.2
120°	526.5	603.1	673.2	729.3	776.4	807.1	824.3	829.3
122.5°	512.8	583.7	646.1	698.7	740.8	768.8	786.0	790.6
125°	492.8	557.8	613.3	659.2	694.9	721.0	735.0	741.4
127.5°	472.4	533.0	584.8	627.8	660.1	683.2	696.5	699.3
130°	459.6	515.8	565.4	606.9	638.8	659.8	672.5	676.4
132.5°	446.9	499.4	544.5	584.4	616.3	637.3	649.1	653.4
135°	430.3	474.3	515.1	551.4	579.4	600.5	612.0	615.8
137.5°	416.3	451.8	485.8	516.6	541.8	560.8	571.4	575.7
140°	408.6	438.5	467.9	494.6	518.3	534.8	544.4	547.6
142.5°	402.0	427.4	452.6	475.8	495.9	509.9	518.9	521.5
145°	393.3	413.1	432.8	450.0	465.4	476.2	483.2	485.8
147.5°	385.1	401.2	416.4	429.4	441.5	450.2	454.3	455.4
150°	380.6	394.6	406.7	418.2	427.8	435.4	438.0	438.5
152.5°	375.4	388.0	399.1	408.0	416.0	422.2	424.7	425.3
155°	367.9	378.1	386.9	394.0	400.3	404.8	406.7	407.3
157.5°	360.2	368.6	375.4	381.0	386.0	389.6	391.4	391.3
160°	355.1	361.4	367.9	372.3	376.7	379.9	381.2	380.6
162.5°	349.4	355.3	360.7	364.6	368.1	370.7	371.0	370.9
165°	341.7	346.2	350.0	353.2	355.7	357.0	357.0	357.0
167.5°	334.3	337.2	340.1	342.4	343.7	344.9	344.4	344.2
170°	330.2	332.2	334.0	335.3	336.6	337.2	337.2	336.6
172.5°	325.6	327.5	329.0	329.7	330.0	331.1	330.1	329.5
175°	320.7	320.7	322.0	322.0	322.0	322.5	321.3	320.7
177.5°	317.2	317.7	317.7	317.7	317.2	317.7	316.2	316.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2

(END OF REPORT)