

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333524-840

Luminaire Tested: **S125RDIP-S610D365U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333524-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D365U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3680.8 lumens  
Efficiency: N/A  
Efficacy: 133.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333524-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333524-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	56
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	50	56	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	57	49	44	51	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	23	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333524-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.5	2.6
10°-20°	267.0	7.3
20°-30°	387.1	10.5
30°-40°	441.2	12.0
40°-50°	430.0	11.7
50°-60°	362.0	9.8
60°-70°	253.8	6.9
70°-80°	130.4	3.5
80°-90°	33.9	0.9
90°-100°	30.7	0.8
100°-110°	90.7	2.5
110°-120°	153.6	4.2
120°-130°	202.2	5.5
130°-140°	226.6	6.2
140°-150°	222.1	6.0
150°-160°	186.5	5.1
160°-170°	124.0	3.4
170°-180°	43.4	1.2
0°-30°	749.6	20.4
0°-40°	1190.8	32.4
0°-60°	1982.8	53.9
0°-90°	2401.0	65.2
90°-120°	275.1	7.5
90°-150°	925.9	25.2
90°-180°	1280.0	34.8
0°-180°	3680.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	0	3	6	7	9	3
95°	23	24	28	30	31	25
105°	81	83	85	87	89	87
115°	154	155	156	156	155	152
125°	224	227	227	226	226	201
135°	292	294	294	294	293	225
145°	354	355	356	356	355	221
155°	405	405	405	406	405	186
165°	440	439	440	441	439	124
175°	458	456	456	458	456	43
180°	459	459	459	459	459	



TEST NUMBER: P333524-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.2	13.3	12.5	11.7	10.9	10.4	10.4	10.4	10.4	10.3	10.4
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.2	5.8	6.1
92.5°	8.7	9.1	9.5	10.0	10.4	11.0	11.6	12.3	13.0	13.7	14.2
95°	23.2	23.3	23.5	23.6	23.8	24.3	25.1	25.9	26.7	27.5	28.1
97.5°	38.6	38.6	38.7	38.8	38.8	39.4	40.5	41.6	42.6	43.7	44.3
100°	50.0	50.0	50.0	50.0	50.0	50.5	51.5	52.5	53.6	54.6	55.3
102.5°	62.2	62.6	62.9	63.2	63.5	63.9	64.4	64.9	65.5	66.0	66.9
105°	81.4	81.8	82.2	82.6	83.0	83.4	83.9	84.3	84.8	85.3	85.7
107.5°	102.5	102.9	103.3	103.7	104.1	104.5	104.8	105.2	105.5	105.9	106.1
110°	117.0	117.4	117.9	118.3	118.7	119.0	119.2	119.5	119.7	120.0	120.2



TEST NUMBER: P333524-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	131.9	132.1	132.3	132.5	132.7	133.0	133.3	133.6	133.9	134.2	134.3
115°	153.8	154.1	154.5	154.8	155.1	155.3	155.5	155.6	155.8	156.0	155.9
117.5°	175.8	175.9	176.1	176.2	176.4	176.5	176.7	176.8	176.9	177.1	177.1
120°	189.6	190.0	190.4	190.8	191.1	191.4	191.5	191.5	191.6	191.7	191.7
122.5°	204.4	204.5	204.7	204.8	204.9	205.1	205.3	205.5	205.7	205.9	205.9
125°	224.5	225.0	225.5	225.9	226.4	226.7	226.8	226.8	226.9	227.0	226.8
127.5°	245.9	246.2	246.5	246.7	247.0	247.2	247.3	247.4	247.5	247.5	247.5
130°	258.7	259.1	259.5	259.9	260.3	260.6	260.7	260.9	261.2	261.3	261.2
132.5°	271.7	272.3	273.0	273.6	274.2	274.6	274.5	274.5	274.5	274.4	274.3
135°	292.0	292.5	293.0	293.4	293.9	294.2	294.3	294.3	294.4	294.5	294.5
137.5°	311.1	311.5	312.0	312.5	313.0	313.3	313.5	313.6	313.8	314.0	314.1
140°	323.4	323.8	324.2	324.6	325.0	325.3	325.5	325.8	326.0	326.2	326.4
142.5°	335.7	336.0	336.3	336.7	337.0	337.3	337.6	337.9	338.2	338.5	338.6
145°	353.8	354.1	354.4	354.7	355.0	355.3	355.5	355.8	356.0	356.2	356.2
147.5°	370.4	370.6	370.7	370.9	371.1	371.3	371.5	371.7	371.8	372.0	372.2
150°	381.5	381.5	381.4	381.3	381.2	381.3	381.6	382.0	382.3	382.6	382.6
152.5°	390.7	390.8	390.9	391.0	391.1	391.2	391.4	391.5	391.6	391.7	391.9
155°	404.8	404.8	404.8	404.8	404.8	404.8	404.9	405.0	405.1	405.2	405.5
157.5°	417.3	417.2	417.0	416.8	416.7	416.6	416.7	416.8	416.8	416.9	417.2
160°	424.7	424.5	424.2	424.0	423.8	423.7	423.8	423.8	423.9	424.0	424.3
162.5°	431.3	431.1	431.0	430.8	430.6	430.5	430.5	430.6	430.6	430.6	431.0
165°	440.1	439.9	439.8	439.6	439.5	439.4	439.5	439.6	439.7	439.7	440.1
167.5°	447.5	447.2	446.9	446.6	446.3	446.1	446.1	446.1	446.1	446.1	446.6
170°	451.5	451.2	450.9	450.6	450.2	450.1	450.1	450.1	450.1	450.1	450.6
172.5°	454.3	454.0	453.7	453.4	453.1	452.9	452.9	452.9	452.9	452.9	453.4
175°	457.6	457.3	457.0	456.7	456.4	456.2	456.2	456.2	456.2	456.2	456.7
177.5°	459.2	459.0	458.7	458.5	458.2	458.1	458.0	458.0	457.9	457.8	458.2
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333524-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	10.5	10.6	10.7	10.7	10.6	10.5	10.4	10.3
90°	6.5	6.9	7.3	7.6	7.9	8.1	8.3	8.6
92.5°	14.7	15.2	15.8	16.2	16.4	16.5	16.7	16.9
95°	28.6	29.2	29.7	30.1	30.2	30.4	30.5	30.7
97.5°	44.8	45.3	45.8	46.2	46.3	46.4	46.5	46.6
100°	56.0	56.8	57.5	57.9	58.1	58.3	58.4	58.6
102.5°	67.6	68.4	69.2	69.7	69.9	70.1	70.3	70.5
105°	86.2	86.7	87.3	87.6	87.8	88.1	88.3	88.6
107.5°	106.4	106.6	106.8	107.0	106.9	106.9	106.9	106.9
110°	120.4	120.7	120.9	121.0	120.9	120.8	120.7	120.7





TEST NUMBER: P333524-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	134.4	134.5	134.6	134.6	134.5	134.3	134.2	134.1
115°	155.8	155.7	155.6	155.6	155.5	155.4	155.3	155.2
117.5°	177.2	177.3	177.3	177.2	176.9	176.6	176.3	175.9
120°	191.7	191.7	191.7	191.5	191.2	190.9	190.6	190.3
122.5°	205.8	205.7	205.7	205.5	205.3	205.0	204.8	204.5
125°	226.7	226.5	226.4	226.2	226.2	226.1	226.0	225.9
127.5°	247.4	247.3	247.2	247.1	247.0	246.8	246.6	246.5
130°	261.2	261.1	260.9	260.8	260.6	260.5	260.3	260.2
132.5°	274.3	274.2	274.1	274.0	273.7	273.5	273.3	273.1
135°	294.5	294.5	294.5	294.3	294.0	293.7	293.4	293.1
137.5°	314.2	314.3	314.4	314.2	313.8	313.4	313.0	312.6
140°	326.6	326.7	326.9	326.8	326.4	326.0	325.6	325.2
142.5°	338.7	338.8	338.9	338.7	338.3	337.9	337.6	337.2
145°	356.2	356.2	356.2	356.1	355.9	355.6	355.4	355.2
147.5°	372.4	372.6	372.8	372.6	372.1	371.5	371.0	370.5
150°	382.6	382.6	382.6	382.5	382.4	382.2	382.0	381.9
152.5°	392.1	392.3	392.5	392.4	392.2	391.9	391.6	391.3
155°	405.8	406.1	406.4	406.4	406.0	405.6	405.2	404.8
157.5°	417.5	417.9	418.2	418.1	417.6	417.0	416.5	416.0
160°	424.6	425.0	425.3	425.3	424.9	424.4	424.0	423.6
162.5°	431.3	431.7	432.1	432.1	431.6	431.1	430.7	430.2
165°	440.4	440.7	441.0	440.9	440.4	440.0	439.5	439.0
167.5°	447.1	447.5	448.0	448.0	447.5	447.0	446.5	446.1
170°	451.0	451.5	452.0	451.9	451.4	450.8	450.3	449.7
172.5°	453.9	454.3	454.8	454.8	454.3	453.8	453.3	452.8
175°	457.1	457.6	458.1	458.0	457.5	456.9	456.4	455.8
177.5°	458.6	459.0	459.3	459.3	458.9	458.4	458.0	457.5
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

(END OF REPORT)