

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333623-930

Luminaire Tested: **S125RDIP-S1270D810U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333623-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D810U930-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6298.8 lumens  
Efficiency: N/A  
Efficacy: 103.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	93	86	79	74	87	81	75	71	71	67	64	63	60	57	55	53	51	47
3	85	76	68	63	80	71	65	60	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	64	56	51	57	51	47	50	46	42	44	41	38	35
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	39	46	40	36	41	36	32	36	32	29	27
7	61	49	41	35	58	47	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	32	54	42	35	30	38	32	28	34	29	26	30	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	38	30	25	47	36	29	25	32	27	23	29	24	21	26	22	19	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.5	2.4
10°-20°	435.1	6.9
20°-30°	689.8	11.0
30°-40°	831.9	13.2
40°-50°	742.9	11.8
50°-60°	569.7	9.0
60°-70°	370.2	5.9
70°-80°	180.0	2.9
80°-90°	44.8	0.7
90°-100°	54.9	0.9
100°-110°	162.0	2.6
110°-120°	274.4	4.4
120°-130°	361.2	5.7
130°-140°	404.7	6.4
140°-150°	396.7	6.3
150°-160°	333.1	5.3
160°-170°	221.5	3.5
170°-180°	77.5	1.2
0°-30°	1273.4	20.2
0°-40°	2105.3	33.4
0°-60°	3417.9	54.3
0°-90°	4012.8	63.7
90°-120°	491.4	7.8
90°-150°	1653.9	26.3
90°-180°	2286.0	36.3
0°-180°	6298.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	15	1	15	1	15	10
95°	55	41	55	41	55	56
105°	158	145	158	145	158	168
115°	277	275	277	275	277	274
125°	404	401	404	401	404	360
135°	523	522	523	522	523	404
145°	634	632	634	632	634	396
155°	723	723	723	723	723	333
165°	784	786	784	786	784	221
175°	814	817	814	817	814	77
180°	819	819	819	819	819	



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	14.3	13.6	13.0	13.0	13.4	14.3	13.6	13.0	12.9	12.7	13.0
90°	15.3	14.8	14.4	14.0	13.6	13.0	12.3	11.6	10.9	10.2	9.2
92.5°	30.1	29.8	29.4	29.2	28.9	28.2	27.3	26.3	25.4	24.5	23.2
95°	54.8	54.5	54.3	54.0	53.7	53.1	52.1	51.0	50.1	49.1	47.7
97.5°	83.2	83.0	82.8	82.6	82.4	81.9	81.0	80.1	79.1	78.2	76.2
100°	104.5	104.3	104.0	103.7	103.5	102.6	101.3	100.1	98.8	97.5	95.7
102.5°	126.0	125.6	125.1	124.8	124.4	123.5	122.1	120.7	119.4	118.0	117.0
105°	158.1	157.7	157.3	156.9	156.4	155.8	154.9	154.1	153.2	152.4	151.5
107.5°	191.0	191.0	191.0	191.1	191.1	190.9	190.5	190.0	189.6	189.2	188.6
110°	215.5	215.6	215.7	215.9	216.1	215.9	215.5	215.1	214.7	214.2	213.8



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	239.5	239.7	239.9	240.2	240.5	240.5	240.3	240.1	239.9	239.7	239.2
115°	277.4	277.4	277.6	277.8	277.9	278.0	278.2	278.3	278.4	278.6	278.3
117.5°	314.3	314.9	315.4	316.0	316.6	316.8	316.7	316.6	316.4	316.3	316.1
120°	339.8	340.4	341.0	341.5	342.1	342.3	342.3	342.3	342.3	342.3	342.2
122.5°	365.3	365.7	366.2	366.6	367.1	367.4	367.5	367.6	367.7	367.9	367.5
125°	403.6	403.7	403.8	404.0	404.1	404.3	404.6	404.9	405.2	405.4	405.3
127.5°	440.3	440.6	440.8	441.2	441.4	441.6	441.7	441.9	442.1	442.2	442.1
130°	464.7	465.0	465.3	465.6	465.9	466.1	466.3	466.4	466.5	466.7	466.4
132.5°	487.7	488.1	488.5	488.9	489.3	489.6	489.7	489.8	490.0	490.2	490.2
135°	523.4	524.0	524.6	525.1	525.7	525.9	525.9	525.9	525.9	525.9	525.8
137.5°	558.3	559.1	559.8	560.4	561.2	561.4	561.3	561.1	560.9	560.8	560.4
140°	580.8	581.5	582.2	582.9	583.6	583.8	583.5	583.3	583.0	582.7	582.3
142.5°	602.2	602.9	603.6	604.3	605.0	605.3	605.1	605.0	604.8	604.6	604.1
145°	634.3	634.8	635.2	635.6	636.0	636.3	636.3	636.3	636.3	636.3	635.9
147.5°	661.8	662.8	663.7	664.6	665.6	665.9	665.6	665.2	664.9	664.6	664.2
150°	682.2	682.4	682.7	683.0	683.3	683.5	683.5	683.5	683.5	683.5	682.9
152.5°	699.0	699.5	700.0	700.5	701.0	701.1	700.7	700.4	700.1	699.8	699.5
155°	722.9	723.7	724.4	725.0	725.8	725.9	725.3	724.7	724.1	723.6	723.4
157.5°	743.0	743.9	744.9	745.8	746.7	746.9	746.3	745.8	745.2	744.6	744.4
160°	756.8	757.4	758.1	758.9	759.6	759.6	759.0	758.6	758.0	757.4	757.2
162.5°	768.5	769.3	770.1	770.9	771.8	771.8	771.2	770.5	769.8	769.2	769.1
165°	784.2	785.0	785.9	786.7	787.6	787.7	787.2	786.6	786.0	785.5	785.3
167.5°	796.6	797.5	798.4	799.3	800.1	800.2	799.3	798.5	797.6	796.8	796.8
170°	803.3	804.3	805.3	806.2	807.2	807.3	806.5	805.6	804.8	803.9	803.9
172.5°	808.9	809.8	810.7	811.5	812.4	812.4	811.5	810.7	809.8	809.0	809.0
175°	814.2	815.1	816.1	817.1	818.1	818.2	817.3	816.4	815.6	814.7	814.7
177.5°	817.2	818.0	818.8	819.5	820.4	820.4	819.7	819.0	818.4	817.7	817.8
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	13.4	13.1	13.5	13.2	12.5	14.8	16.1	16.4	15.6	14.8	14.0
90°	8.2	7.3	6.2	5.1	4.1	2.9	1.8	0.7	1.8	2.9	4.1
92.5°	22.0	20.8	19.6	18.6	17.8	17.0	16.2	15.4	16.2	17.0	17.8
95°	46.2	44.8	43.5	42.6	42.3	42.0	41.7	41.4	41.7	42.0	42.3
97.5°	74.3	72.3	70.4	69.3	69.2	69.1	69.0	68.9	69.0	69.1	69.2
100°	93.8	92.0	90.2	89.3	89.3	89.3	89.3	89.3	89.3	89.3	89.3
102.5°	116.1	115.1	114.2	113.5	112.9	112.3	111.8	111.2	111.8	112.3	112.9
105°	150.7	149.9	149.0	148.2	147.5	146.8	146.1	145.4	146.1	146.8	147.5
107.5°	187.9	187.3	186.6	186.0	185.2	184.5	183.8	183.1	183.8	184.5	185.2
110°	213.4	213.0	212.5	212.0	211.2	210.5	209.9	209.1	209.9	210.5	211.2





TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	238.6	238.1	237.6	237.1	236.8	236.4	236.0	235.6	236.0	236.4	236.8
115°	278.0	277.8	277.4	277.0	276.5	275.9	275.3	274.8	275.3	275.9	276.5
117.5°	315.8	315.6	315.4	315.0	314.8	314.5	314.3	314.1	314.3	314.5	314.8
120°	342.1	341.9	341.8	341.4	340.6	340.0	339.2	338.5	339.2	340.0	340.6
122.5°	367.1	366.7	366.4	366.1	365.8	365.6	365.3	365.0	365.3	365.6	365.8
125°	405.2	405.0	404.9	404.4	403.6	402.7	401.9	401.0	401.9	402.7	403.6
127.5°	441.8	441.6	441.5	441.2	440.7	440.2	439.8	439.3	439.8	440.2	440.7
130°	466.1	465.8	465.5	465.0	464.3	463.7	462.9	462.2	462.9	463.7	464.3
132.5°	490.2	490.3	490.3	489.8	488.6	487.5	486.3	485.2	486.3	487.5	488.6
135°	525.7	525.5	525.4	524.9	524.1	523.2	522.4	521.5	522.4	523.2	524.1
137.5°	560.1	559.9	559.5	559.0	558.2	557.3	556.5	555.7	556.5	557.3	558.2
140°	581.9	581.4	581.0	580.4	579.8	579.0	578.3	577.6	578.3	579.0	579.8
142.5°	603.6	603.0	602.5	601.9	601.3	600.7	600.1	599.6	600.1	600.7	601.3
145°	635.4	635.0	634.5	634.1	633.5	632.9	632.3	631.8	632.3	632.9	633.5
147.5°	663.9	663.6	663.2	662.8	662.6	662.3	661.9	661.6	661.9	662.3	662.6
150°	682.3	681.8	681.2	680.9	681.1	681.3	681.3	681.5	681.3	681.3	681.1
152.5°	699.3	699.0	698.9	698.6	698.5	698.2	698.1	697.8	698.1	698.2	698.5
155°	723.3	723.2	723.0	722.9	722.9	722.9	722.9	722.9	722.9	722.9	722.9
157.5°	744.4	744.2	744.0	744.1	744.4	744.8	745.1	745.4	745.1	744.8	744.4
160°	757.1	756.9	756.8	756.9	757.4	757.8	758.2	758.6	758.2	757.8	757.4
162.5°	769.1	769.0	769.0	769.2	769.5	769.7	770.1	770.4	770.1	769.7	769.5
165°	785.1	785.0	784.9	785.0	785.2	785.5	785.8	786.1	785.8	785.5	785.2
167.5°	796.8	796.8	796.8	797.0	797.6	798.2	798.7	799.3	798.7	798.2	797.6
170°	803.9	803.9	803.9	804.2	804.8	805.4	805.9	806.5	805.9	805.4	804.8
172.5°	809.0	809.0	809.0	809.3	809.8	810.4	811.0	811.5	811.0	810.4	809.8
175°	814.7	814.7	814.7	815.1	815.6	816.2	816.8	817.3	816.8	816.2	815.6
177.5°	817.9	818.1	818.2	818.4	818.9	819.4	819.8	820.3	819.8	819.4	818.9
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	13.8	13.9	13.6	14.8	13.5	14.3	14.3	14.0	14.2	14.3	13.9
90°	5.1	6.2	7.3	8.2	9.2	10.2	10.9	11.6	12.3	13.0	13.6
92.5°	18.6	19.6	20.8	22.0	23.2	24.5	25.4	26.3	27.3	28.2	28.9
95°	42.6	43.5	44.8	46.2	47.7	49.1	50.1	51.0	52.1	53.1	53.7
97.5°	69.3	70.4	72.3	74.3	76.2	78.2	79.1	80.1	81.0	81.9	82.4
100°	89.3	90.2	92.0	93.8	95.7	97.5	98.8	100.1	101.3	102.6	103.5
102.5°	113.5	114.2	115.1	116.1	117.0	118.0	119.4	120.7	122.1	123.5	124.4
105°	148.2	149.0	149.9	150.7	151.5	152.4	153.2	154.1	154.9	155.8	156.4
107.5°	186.0	186.6	187.3	187.9	188.6	189.2	189.6	190.0	190.5	190.9	191.1
110°	212.0	212.5	213.0	213.4	213.8	214.2	214.7	215.1	215.5	215.9	216.1



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.1	237.6	238.1	238.6	239.2	239.7	239.9	240.1	240.3	240.5	240.5
115°	277.0	277.4	277.8	278.0	278.3	278.6	278.4	278.3	278.2	278.0	277.9
117.5°	315.0	315.4	315.6	315.8	316.1	316.3	316.4	316.6	316.7	316.8	316.6
120°	341.4	341.8	341.9	342.1	342.2	342.3	342.3	342.3	342.3	342.3	342.1
122.5°	366.1	366.4	366.7	367.1	367.5	367.9	367.7	367.6	367.5	367.4	367.1
125°	404.4	404.9	405.0	405.2	405.3	405.4	405.2	404.9	404.6	404.3	404.1
127.5°	441.2	441.5	441.6	441.8	442.1	442.2	442.1	441.9	441.7	441.6	441.4
130°	465.0	465.5	465.8	466.1	466.4	466.7	466.5	466.4	466.3	466.1	465.9
132.5°	489.8	490.3	490.3	490.2	490.2	490.2	490.0	489.8	489.7	489.6	489.3
135°	524.9	525.4	525.5	525.7	525.8	525.9	525.9	525.9	525.9	525.9	525.7
137.5°	559.0	559.5	559.9	560.1	560.4	560.8	560.9	561.1	561.3	561.4	561.2
140°	580.4	581.0	581.4	581.9	582.3	582.7	583.0	583.3	583.5	583.8	583.6
142.5°	601.9	602.5	603.0	603.6	604.1	604.6	604.8	605.0	605.1	605.3	605.0
145°	634.1	634.5	635.0	635.4	635.9	636.3	636.3	636.3	636.3	636.3	636.0
147.5°	662.8	663.2	663.6	663.9	664.2	664.6	664.9	665.2	665.6	665.9	665.6
150°	680.9	681.2	681.8	682.3	682.9	683.5	683.5	683.5	683.5	683.5	683.3
152.5°	698.6	698.9	699.0	699.3	699.5	699.8	700.1	700.4	700.7	701.1	701.0
155°	722.9	723.0	723.2	723.3	723.4	723.6	724.1	724.7	725.3	725.9	725.8
157.5°	744.1	744.0	744.2	744.4	744.4	744.6	745.2	745.8	746.3	746.9	746.7
160°	756.9	756.8	756.9	757.1	757.2	757.4	758.0	758.6	759.0	759.6	759.6
162.5°	769.2	769.0	769.0	769.1	769.1	769.2	769.8	770.5	771.2	771.8	771.8
165°	785.0	784.9	785.0	785.1	785.3	785.5	786.0	786.6	787.2	787.7	787.6
167.5°	797.0	796.8	796.8	796.8	796.8	796.8	797.6	798.5	799.3	800.2	800.1
170°	804.2	803.9	803.9	803.9	803.9	803.9	804.8	805.6	806.5	807.3	807.2
172.5°	809.3	809.0	809.0	809.0	809.0	809.0	809.8	810.7	811.5	812.4	812.4
175°	815.1	814.7	814.7	814.7	814.7	814.7	815.6	816.4	817.3	818.2	818.1
177.5°	818.4	818.2	818.1	817.9	817.8	817.7	818.4	819.0	819.7	820.4	820.4
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	14.5	14.1	14.2	14.3	14.2	14.1	14.5	13.9	14.3	14.2	14.0
90°	14.0	14.4	14.8	15.3	14.8	14.4	14.0	13.6	13.0	12.3	11.6
92.5°	29.2	29.4	29.8	30.1	29.8	29.4	29.2	28.9	28.2	27.3	26.3
95°	54.0	54.3	54.5	54.8	54.5	54.3	54.0	53.7	53.1	52.1	51.0
97.5°	82.6	82.8	83.0	83.2	83.0	82.8	82.6	82.4	81.9	81.0	80.1
100°	103.7	104.0	104.3	104.5	104.3	104.0	103.7	103.5	102.6	101.3	100.1
102.5°	124.8	125.1	125.6	126.0	125.6	125.1	124.8	124.4	123.5	122.1	120.7
105°	156.9	157.3	157.7	158.1	157.7	157.3	156.9	156.4	155.8	154.9	154.1
107.5°	191.1	191.0	191.0	191.0	191.0	191.0	191.1	191.1	190.9	190.5	190.0
110°	215.9	215.7	215.6	215.5	215.6	215.7	215.9	216.1	215.9	215.5	215.1



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	240.2	239.9	239.7	239.5	239.7	239.9	240.2	240.5	240.5	240.3	240.1
115°	277.8	277.6	277.4	277.4	277.4	277.6	277.8	277.9	278.0	278.2	278.3
117.5°	316.0	315.4	314.9	314.3	314.9	315.4	316.0	316.6	316.8	316.7	316.6
120°	341.5	341.0	340.4	339.8	340.4	341.0	341.5	342.1	342.3	342.3	342.3
122.5°	366.6	366.2	365.7	365.3	365.7	366.2	366.6	367.1	367.4	367.5	367.6
125°	404.0	403.8	403.7	403.6	403.7	403.8	404.0	404.1	404.3	404.6	404.9
127.5°	441.2	440.8	440.6	440.3	440.6	440.8	441.2	441.4	441.6	441.7	441.9
130°	465.6	465.3	465.0	464.7	465.0	465.3	465.6	465.9	466.1	466.3	466.4
132.5°	488.9	488.5	488.1	487.7	488.1	488.5	488.9	489.3	489.6	489.7	489.8
135°	525.1	524.6	524.0	523.4	524.0	524.6	525.1	525.7	525.9	525.9	525.9
137.5°	560.4	559.8	559.1	558.3	559.1	559.8	560.4	561.2	561.4	561.3	561.1
140°	582.9	582.2	581.5	580.8	581.5	582.2	582.9	583.6	583.8	583.5	583.3
142.5°	604.3	603.6	602.9	602.2	602.9	603.6	604.3	605.0	605.3	605.1	605.0
145°	635.6	635.2	634.8	634.3	634.8	635.2	635.6	636.0	636.3	636.3	636.3
147.5°	664.6	663.7	662.8	661.8	662.8	663.7	664.6	665.6	665.9	665.6	665.2
150°	683.0	682.7	682.4	682.2	682.4	682.7	683.0	683.3	683.5	683.5	683.5
152.5°	700.5	700.0	699.5	699.0	699.5	700.0	700.5	701.0	701.1	700.7	700.4
155°	725.0	724.4	723.7	722.9	723.7	724.4	725.0	725.8	725.9	725.3	724.7
157.5°	745.8	744.9	743.9	743.0	743.9	744.9	745.8	746.7	746.9	746.3	745.8
160°	758.9	758.1	757.4	756.8	757.4	758.1	758.9	759.6	759.6	759.0	758.6
162.5°	770.9	770.1	769.3	768.5	769.3	770.1	770.9	771.8	771.8	771.2	770.5
165°	786.7	785.9	785.0	784.2	785.0	785.9	786.7	787.6	787.7	787.2	786.6
167.5°	799.3	798.4	797.5	796.6	797.5	798.4	799.3	800.1	800.2	799.3	798.5
170°	806.2	805.3	804.3	803.3	804.3	805.3	806.2	807.2	807.3	806.5	805.6
172.5°	811.5	810.7	809.8	808.9	809.8	810.7	811.5	812.4	812.4	811.5	810.7
175°	817.1	816.1	815.1	814.2	815.1	816.1	817.1	818.1	818.2	817.3	816.4
177.5°	819.5	818.8	818.0	817.2	818.0	818.8	819.5	820.4	820.4	819.7	819.0
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	14.3	14.3	13.5	14.8	13.6	13.9	13.8	14.0	14.8	15.6	16.4
90°	10.9	10.2	9.2	8.2	7.3	6.2	5.1	4.1	2.9	1.8	0.7
92.5°	25.4	24.5	23.2	22.0	20.8	19.6	18.6	17.8	17.0	16.2	15.4
95°	50.1	49.1	47.7	46.2	44.8	43.5	42.6	42.3	42.0	41.7	41.4
97.5°	79.1	78.2	76.2	74.3	72.3	70.4	69.3	69.2	69.1	69.0	68.9
100°	98.8	97.5	95.7	93.8	92.0	90.2	89.3	89.3	89.3	89.3	89.3
102.5°	119.4	118.0	117.0	116.1	115.1	114.2	113.5	112.9	112.3	111.8	111.2
105°	153.2	152.4	151.5	150.7	149.9	149.0	148.2	147.5	146.8	146.1	145.4
107.5°	189.6	189.2	188.6	187.9	187.3	186.6	186.0	185.2	184.5	183.8	183.1
110°	214.7	214.2	213.8	213.4	213.0	212.5	212.0	211.2	210.5	209.9	209.1



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	239.9	239.7	239.2	238.6	238.1	237.6	237.1	236.8	236.4	236.0	235.6
115°	278.4	278.6	278.3	278.0	277.8	277.4	277.0	276.5	275.9	275.3	274.8
117.5°	316.4	316.3	316.1	315.8	315.6	315.4	315.0	314.8	314.5	314.3	314.1
120°	342.3	342.3	342.2	342.1	341.9	341.8	341.4	340.6	340.0	339.2	338.5
122.5°	367.7	367.9	367.5	367.1	366.7	366.4	366.1	365.8	365.6	365.3	365.0
125°	405.2	405.4	405.3	405.2	405.0	404.9	404.4	403.6	402.7	401.9	401.0
127.5°	442.1	442.2	442.1	441.8	441.6	441.5	441.2	440.7	440.2	439.8	439.3
130°	466.5	466.7	466.4	466.1	465.8	465.5	465.0	464.3	463.7	462.9	462.2
132.5°	490.0	490.2	490.2	490.2	490.3	490.3	489.8	488.6	487.5	486.3	485.2
135°	525.9	525.9	525.8	525.7	525.5	525.4	524.9	524.1	523.2	522.4	521.5
137.5°	560.9	560.8	560.4	560.1	559.9	559.5	559.0	558.2	557.3	556.5	555.7
140°	583.0	582.7	582.3	581.9	581.4	581.0	580.4	579.8	579.0	578.3	577.6
142.5°	604.8	604.6	604.1	603.6	603.0	602.5	601.9	601.3	600.7	600.1	599.6
145°	636.3	636.3	635.9	635.4	635.0	634.5	634.1	633.5	632.9	632.3	631.8
147.5°	664.9	664.6	664.2	663.9	663.6	663.2	662.8	662.6	662.3	661.9	661.6
150°	683.5	683.5	682.9	682.3	681.8	681.2	680.9	681.1	681.3	681.3	681.5
152.5°	700.1	699.8	699.5	699.3	699.0	698.9	698.6	698.5	698.2	698.1	697.8
155°	724.1	723.6	723.4	723.3	723.2	723.0	722.9	722.9	722.9	722.9	722.9
157.5°	745.2	744.6	744.4	744.4	744.2	744.0	744.1	744.4	744.8	745.1	745.4
160°	758.0	757.4	757.2	757.1	756.9	756.8	756.9	757.4	757.8	758.2	758.6
162.5°	769.8	769.2	769.1	769.1	769.0	769.0	769.2	769.5	769.7	770.1	770.4
165°	786.0	785.5	785.3	785.1	785.0	784.9	785.0	785.2	785.5	785.8	786.1
167.5°	797.6	796.8	796.8	796.8	796.8	796.8	797.0	797.6	798.2	798.7	799.3
170°	804.8	803.9	803.9	803.9	803.9	803.9	804.2	804.8	805.4	805.9	806.5
172.5°	809.8	809.0	809.0	809.0	809.0	809.0	809.3	809.8	810.4	811.0	811.5
175°	815.6	814.7	814.7	814.7	814.7	814.7	815.1	815.6	816.2	816.8	817.3
177.5°	818.4	817.7	817.8	817.9	818.1	818.2	818.4	818.9	819.4	819.8	820.3
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.1	14.8	12.5	13.2	13.5	13.1	13.4	13.0	12.7	12.9	13.0
90°	1.8	2.9	4.1	5.1	6.2	7.3	8.2	9.2	10.2	10.9	11.6
92.5°	16.2	17.0	17.8	18.6	19.6	20.8	22.0	23.2	24.5	25.4	26.3
95°	41.7	42.0	42.3	42.6	43.5	44.8	46.2	47.7	49.1	50.1	51.0
97.5°	69.0	69.1	69.2	69.3	70.4	72.3	74.3	76.2	78.2	79.1	80.1
100°	89.3	89.3	89.3	89.3	90.2	92.0	93.8	95.7	97.5	98.8	100.1
102.5°	111.8	112.3	112.9	113.5	114.2	115.1	116.1	117.0	118.0	119.4	120.7
105°	146.1	146.8	147.5	148.2	149.0	149.9	150.7	151.5	152.4	153.2	154.1
107.5°	183.8	184.5	185.2	186.0	186.6	187.3	187.9	188.6	189.2	189.6	190.0
110°	209.9	210.5	211.2	212.0	212.5	213.0	213.4	213.8	214.2	214.7	215.1





TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	236.0	236.4	236.8	237.1	237.6	238.1	238.6	239.2	239.7	239.9	240.1
115°	275.3	275.9	276.5	277.0	277.4	277.8	278.0	278.3	278.6	278.4	278.3
117.5°	314.3	314.5	314.8	315.0	315.4	315.6	315.8	316.1	316.3	316.4	316.6
120°	339.2	340.0	340.6	341.4	341.8	341.9	342.1	342.2	342.3	342.3	342.3
122.5°	365.3	365.6	365.8	366.1	366.4	366.7	367.1	367.5	367.9	367.7	367.6
125°	401.9	402.7	403.6	404.4	404.9	405.0	405.2	405.3	405.4	405.2	404.9
127.5°	439.8	440.2	440.7	441.2	441.5	441.6	441.8	442.1	442.2	442.1	441.9
130°	462.9	463.7	464.3	465.0	465.5	465.8	466.1	466.4	466.7	466.5	466.4
132.5°	486.3	487.5	488.6	489.8	490.3	490.3	490.2	490.2	490.2	490.0	489.8
135°	522.4	523.2	524.1	524.9	525.4	525.5	525.7	525.8	525.9	525.9	525.9
137.5°	556.5	557.3	558.2	559.0	559.5	559.9	560.1	560.4	560.8	560.9	561.1
140°	578.3	579.0	579.8	580.4	581.0	581.4	581.9	582.3	582.7	583.0	583.3
142.5°	600.1	600.7	601.3	601.9	602.5	603.0	603.6	604.1	604.6	604.8	605.0
145°	632.3	632.9	633.5	634.1	634.5	635.0	635.4	635.9	636.3	636.3	636.3
147.5°	661.9	662.3	662.6	662.8	663.2	663.6	663.9	664.2	664.6	664.9	665.2
150°	681.3	681.3	681.1	680.9	681.2	681.8	682.3	682.9	683.5	683.5	683.5
152.5°	698.1	698.2	698.5	698.6	698.9	699.0	699.3	699.5	699.8	700.1	700.4
155°	722.9	722.9	722.9	722.9	723.0	723.2	723.3	723.4	723.6	724.1	724.7
157.5°	745.1	744.8	744.4	744.1	744.0	744.2	744.4	744.4	744.6	745.2	745.8
160°	758.2	757.8	757.4	756.9	756.8	756.9	757.1	757.2	757.4	758.0	758.6
162.5°	770.1	769.7	769.5	769.2	769.0	769.0	769.1	769.1	769.2	769.8	770.5
165°	785.8	785.5	785.2	785.0	784.9	785.0	785.1	785.3	785.5	786.0	786.6
167.5°	798.7	798.2	797.6	797.0	796.8	796.8	796.8	796.8	796.8	797.6	798.5
170°	805.9	805.4	804.8	804.2	803.9	803.9	803.9	803.9	803.9	804.8	805.6
172.5°	811.0	810.4	809.8	809.3	809.0	809.0	809.0	809.0	809.0	809.8	810.7
175°	816.8	816.2	815.6	815.1	814.7	814.7	814.7	814.7	814.7	815.6	816.4
177.5°	819.8	819.4	818.9	818.4	818.2	818.1	817.9	817.8	817.7	818.4	819.0
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	13.6	14.3	13.4	13.0	13.0	13.6	14.3
90°	12.3	13.0	13.6	14.0	14.4	14.8	15.3
92.5°	27.3	28.2	28.9	29.2	29.4	29.8	30.1
95°	52.1	53.1	53.7	54.0	54.3	54.5	54.8
97.5°	81.0	81.9	82.4	82.6	82.8	83.0	83.2
100°	101.3	102.6	103.5	103.7	104.0	104.3	104.5
102.5°	122.1	123.5	124.4	124.8	125.1	125.6	126.0
105°	154.9	155.8	156.4	156.9	157.3	157.7	158.1
107.5°	190.5	190.9	191.1	191.1	191.0	191.0	191.0
110°	215.5	215.9	216.1	215.9	215.7	215.6	215.5



TEST NUMBER: P333623-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	240.3	240.5	240.5	240.2	239.9	239.7	239.5
115°	278.2	278.0	277.9	277.8	277.6	277.4	277.4
117.5°	316.7	316.8	316.6	316.0	315.4	314.9	314.3
120°	342.3	342.3	342.1	341.5	341.0	340.4	339.8
122.5°	367.5	367.4	367.1	366.6	366.2	365.7	365.3
125°	404.6	404.3	404.1	404.0	403.8	403.7	403.6
127.5°	441.7	441.6	441.4	441.2	440.8	440.6	440.3
130°	466.3	466.1	465.9	465.6	465.3	465.0	464.7
132.5°	489.7	489.6	489.3	488.9	488.5	488.1	487.7
135°	525.9	525.9	525.7	525.1	524.6	524.0	523.4
137.5°	561.3	561.4	561.2	560.4	559.8	559.1	558.3
140°	583.5	583.8	583.6	582.9	582.2	581.5	580.8
142.5°	605.1	605.3	605.0	604.3	603.6	602.9	602.2
145°	636.3	636.3	636.0	635.6	635.2	634.8	634.3
147.5°	665.6	665.9	665.6	664.6	663.7	662.8	661.8
150°	683.5	683.5	683.3	683.0	682.7	682.4	682.2
152.5°	700.7	701.1	701.0	700.5	700.0	699.5	699.0
155°	725.3	725.9	725.8	725.0	724.4	723.7	722.9
157.5°	746.3	746.9	746.7	745.8	744.9	743.9	743.0
160°	759.0	759.6	759.6	758.9	758.1	757.4	756.8
162.5°	771.2	771.8	771.8	770.9	770.1	769.3	768.5
165°	787.2	787.7	787.6	786.7	785.9	785.0	784.2
167.5°	799.3	800.2	800.1	799.3	798.4	797.5	796.6
170°	806.5	807.3	807.2	806.2	805.3	804.3	803.3
172.5°	811.5	812.4	812.4	811.5	810.7	809.8	808.9
175°	817.3	818.2	818.1	817.1	816.1	815.1	814.2
177.5°	819.7	820.4	820.4	819.5	818.8	818.0	817.2
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2

(END OF REPORT)