

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333577-840

Luminaire Tested: **S125RDIP-S850D1205U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333577-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1205U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8145.7 lumens
Efficiency: N/A
Efficacy: 143.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333577-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333577-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																				
1	96	92	88	84	87	84	80	78	69	66	64	55	53	52	42	41	40	34																				
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	36	34	29																				
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25																				
4	73	62	55	49	66	57	51	45	47	42	38	38	35	32	30	27	25	21																				
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19																				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16																				
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17	15																				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13																				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	17	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333577-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	1.6
10°-20°	364.9	4.5
20°-30°	529.2	6.5
30°-40°	603.1	7.4
40°-50°	587.8	7.2
50°-60°	494.8	6.1
60°-70°	346.9	4.3
70°-80°	178.3	2.2
80°-90°	48.3	0.6
90°-100°	57.5	0.7
100°-110°	354.6	4.4
110°-120°	643.1	7.9
120°-130°	825.3	10.1
130°-140°	887.7	10.9
140°-150°	833.2	10.2
150°-160°	674.0	8.3
160°-170°	435.9	5.4
170°-180°	150.4	1.8
0°-30°	1024.6	12.6
0°-40°	1627.7	20.0
0°-60°	2710.4	33.3
0°-90°	3283.8	40.3
90°-120°	1055.2	13.0
90°-150°	3601.6	44.2
90°-180°	4862.0	59.7
0°-180°	8145.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	1	10	19	24	28	5
95°	67	61	19	24	25	85
105°	345	349	350	350	349	366
115°	648	654	655	650	643	642
125°	921	929	930	925	921	823
135°	1149	1156	1154	1151	1144	885
145°	1332	1334	1334	1335	1329	833
155°	1467	1461	1462	1465	1456	676
165°	1548	1542	1542	1548	1540	437
175°	1583	1577	1577	1586	1576	151
180°	1583	1583	1583	1583	1583	



TEST NUMBER: P333577-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.5	18.7	17.8	16.9	16.0	15.7	15.9	16.0	16.2	16.4	16.6
90°	1.2	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1
92.5°	18.1	16.7	15.1	13.7	12.2	12.3	13.9	15.6	17.2	18.8	20.1
95°	66.9	66.1	65.3	64.5	63.7	58.5	48.5	38.6	28.7	18.8	20.1
97.5°	139.7	141.1	142.5	143.9	145.3	136.2	116.5	96.9	77.4	57.8	50.4
100°	196.0	196.8	197.5	198.3	199.1	200.1	201.1	202.2	203.2	204.2	165.3
102.5°	253.3	254.3	255.3	256.2	257.2	258.0	258.6	259.3	259.9	260.5	253.2
105°	345.1	346.1	347.1	348.2	349.2	349.7	349.7	349.7	349.7	349.7	349.7
107.5°	440.4	440.4	440.4	440.4	440.4	440.6	441.1	441.6	442.2	442.7	442.7
110°	502.3	502.3	502.3	502.3	502.3	502.6	503.1	503.6	504.1	504.6	503.9



TEST NUMBER: P333577-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	560.6	561.2	561.8	562.4	563.0	563.5	563.8	564.1	564.4	564.7	563.8
115°	647.8	649.1	650.5	651.8	653.1	653.9	654.1	654.4	654.6	654.9	653.9
117.5°	738.2	738.2	738.1	738.1	738.0	738.5	739.5	740.4	741.4	742.5	741.1
120°	794.6	794.3	794.1	793.8	793.6	793.8	794.6	795.4	796.1	796.9	796.4
122.5°	844.3	845.4	846.3	847.3	848.3	849.0	849.3	849.7	850.1	850.4	849.9
125°	921.3	923.1	924.9	926.8	928.6	929.5	929.5	929.5	929.5	929.5	928.5
127.5°	994.8	996.1	997.3	998.7	1000.0	1000.6	1000.4	1000.3	1000.1	1000.0	999.4
130°	1039.9	1041.2	1042.5	1043.8	1045.1	1045.8	1046.1	1046.4	1046.6	1046.9	1046.1
132.5°	1084.9	1086.4	1087.9	1089.4	1091.0	1091.5	1090.9	1090.3	1089.7	1089.1	1089.0
135°	1149.0	1150.5	1152.2	1153.7	1155.3	1155.8	1155.3	1154.8	1154.2	1153.7	1153.2
137.5°	1207.9	1209.3	1210.6	1211.9	1213.4	1213.8	1213.4	1212.8	1212.3	1211.9	1212.0
140°	1246.4	1247.0	1247.5	1248.0	1248.5	1248.6	1248.4	1248.1	1247.9	1247.6	1248.1
142.5°	1281.1	1281.4	1281.8	1282.1	1282.4	1282.7	1283.1	1283.4	1283.8	1284.2	1284.3
145°	1332.1	1332.6	1333.1	1333.6	1334.1	1334.4	1334.4	1334.4	1334.4	1334.4	1334.7
147.5°	1376.6	1376.5	1376.4	1376.3	1376.2	1376.3	1376.6	1377.0	1377.4	1377.7	1378.0
150°	1404.8	1404.3	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1405.3
152.5°	1432.1	1431.0	1429.8	1428.7	1427.4	1427.1	1427.7	1428.3	1428.8	1429.3	1429.8
155°	1467.0	1465.5	1463.9	1462.4	1460.8	1460.3	1460.8	1461.3	1461.9	1462.4	1463.2
157.5°	1494.1	1493.1	1492.2	1491.3	1490.3	1489.9	1490.0	1490.0	1490.1	1490.1	1490.9
160°	1512.9	1511.3	1509.7	1508.1	1506.6	1505.9	1506.2	1506.4	1506.7	1506.9	1508.0
162.5°	1527.8	1526.3	1524.7	1523.2	1521.6	1521.0	1521.2	1521.5	1521.8	1522.0	1523.5
165°	1548.0	1546.5	1544.9	1543.4	1541.8	1541.2	1541.4	1541.7	1541.9	1542.2	1543.8
167.5°	1563.1	1561.5	1559.8	1558.2	1556.6	1555.9	1556.2	1556.4	1556.7	1557.0	1558.8
170°	1571.6	1569.7	1567.8	1566.0	1564.2	1563.5	1563.7	1564.0	1564.2	1564.5	1566.6
172.5°	1577.1	1575.3	1573.5	1571.7	1569.8	1569.1	1569.6	1570.1	1570.5	1571.0	1573.0
175°	1583.3	1581.7	1580.1	1578.5	1577.0	1576.3	1576.6	1576.9	1577.1	1577.4	1579.4
177.5°	1586.1	1584.8	1583.6	1582.4	1581.0	1580.5	1580.7	1580.9	1581.1	1581.3	1582.9
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333577-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	16.9	17.2	17.4	17.5	17.5	17.5	17.4	17.4
90°	21.4	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	21.4	22.7	24.0	24.8	25.1	25.5	26.0	26.3
95°	21.4	22.7	24.0	24.6	24.6	24.6	24.6	24.6
97.5°	43.0	35.6	28.3	24.6	24.6	24.6	24.6	24.6
100°	126.5	87.7	48.8	28.8	27.8	26.8	25.7	24.6
102.5°	245.8	238.5	231.2	218.6	200.9	183.1	165.4	147.6
105°	349.7	349.7	349.7	349.6	349.3	349.1	348.8	348.6
107.5°	442.8	442.8	442.9	442.5	441.7	441.0	440.2	439.4
110°	503.1	502.3	501.5	501.3	501.5	501.8	502.1	502.3



TEST NUMBER: P333577-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	562.8	561.8	560.8	560.1	559.8	559.4	559.1	558.7
115°	652.8	651.8	650.8	649.4	647.8	646.3	644.7	643.2
117.5°	739.7	738.4	737.0	736.0	735.3	734.7	734.0	733.3
120°	795.9	795.4	794.9	794.0	792.6	791.3	790.0	788.7
122.5°	849.4	848.9	848.4	847.3	845.8	844.2	842.8	841.3
125°	927.5	926.3	925.3	924.4	923.6	922.9	922.1	921.3
127.5°	998.8	998.3	997.6	996.4	994.5	992.5	990.6	988.7
130°	1045.3	1044.5	1043.8	1042.7	1041.4	1040.2	1038.8	1037.5
132.5°	1088.8	1088.6	1088.5	1087.8	1086.5	1085.2	1083.9	1082.6
135°	1152.7	1152.2	1151.7	1150.5	1149.0	1147.4	1145.9	1144.3
137.5°	1212.1	1212.2	1212.3	1211.7	1210.3	1209.0	1207.6	1206.3
140°	1248.6	1249.1	1249.7	1249.1	1247.6	1246.1	1244.5	1242.9
142.5°	1284.4	1284.5	1284.6	1283.9	1282.3	1280.8	1279.2	1277.7
145°	1334.9	1335.2	1335.4	1334.8	1333.2	1331.7	1330.1	1328.6
147.5°	1378.3	1378.6	1378.9	1378.1	1376.2	1374.3	1372.5	1370.6
150°	1405.9	1406.4	1406.9	1406.1	1404.1	1402.0	1399.9	1397.9
152.5°	1430.3	1430.9	1431.4	1430.7	1428.8	1426.9	1425.0	1423.2
155°	1463.9	1464.7	1465.5	1464.8	1462.8	1460.7	1458.5	1456.5
157.5°	1491.8	1492.6	1493.4	1492.8	1490.7	1488.6	1486.5	1484.4
160°	1509.0	1510.1	1511.2	1510.7	1508.5	1506.4	1504.4	1502.3
162.5°	1524.9	1526.4	1527.8	1527.4	1525.1	1522.8	1520.6	1518.2
165°	1545.3	1546.9	1548.4	1548.1	1546.1	1544.0	1541.9	1539.8
167.5°	1560.7	1562.6	1564.5	1564.3	1561.9	1559.5	1557.2	1554.9
170°	1568.6	1570.7	1572.9	1572.7	1570.3	1568.0	1565.7	1563.3
172.5°	1574.8	1576.7	1578.5	1578.3	1576.0	1573.7	1571.2	1568.9
175°	1581.5	1583.7	1585.7	1585.6	1583.3	1580.9	1578.5	1576.2
177.5°	1584.3	1585.8	1587.2	1587.1	1585.5	1583.8	1582.1	1580.4
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3

(END OF REPORT)