

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333578-840

Luminaire Tested: **S125RDIP-S850D1205U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333578-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1205U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7491.7 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333578-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333578-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333578-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	1.7
10°-20°	364.9	4.9
20°-30°	529.2	7.1
30°-40°	603.1	8.0
40°-50°	587.8	7.8
50°-60°	494.8	6.6
60°-70°	346.9	4.6
70°-80°	178.3	2.4
80°-90°	48.3	0.6
90°-100°	101.0	1.3
100°-110°	298.2	4.0
110°-120°	505.2	6.7
120°-130°	664.8	8.9
130°-140°	745.0	9.9
140°-150°	730.1	9.7
150°-160°	613.2	8.2
160°-170°	407.6	5.4
170°-180°	142.7	1.9
0°-30°	1024.6	13.7
0°-40°	1627.7	21.7
0°-60°	2710.4	36.2
0°-90°	3283.8	43.8
90°-120°	904.4	12.1
90°-150°	3044.3	40.6
90°-180°	4208.0	56.2
0°-180°	7491.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	1	10	19	24	28	7
95°	76	79	90	98	101	81
105°	268	274	280	287	291	286
115°	506	510	513	512	510	500
125°	738	745	746	744	743	661
135°	960	967	968	968	963	740
145°	1163	1168	1171	1171	1168	727
155°	1331	1331	1332	1336	1331	613
165°	1447	1445	1446	1450	1443	408
175°	1504	1500	1500	1506	1498	143
180°	1508	1508	1508	1508	1508	



TEST NUMBER: P333578-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.5	18.7	17.8	16.9	16.0	15.7	15.9	16.0	16.2	16.4	16.6
90°	1.2	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1
92.5°	28.4	29.9	31.3	32.8	34.2	36.1	38.4	40.6	42.8	45.0	46.8
95°	76.2	76.7	77.4	77.9	78.4	79.9	82.5	85.1	87.8	90.4	92.2
97.5°	126.7	126.9	127.1	127.3	127.5	129.5	133.1	136.6	140.3	143.9	145.6
100°	164.3	164.3	164.3	164.3	164.3	166.0	169.4	172.8	176.1	179.6	181.9
102.5°	204.7	205.7	206.7	207.8	208.8	210.3	212.0	213.7	215.4	217.1	219.6
105°	267.5	268.8	270.1	271.5	272.8	274.2	275.8	277.3	278.9	280.4	282.1
107.5°	337.0	338.3	339.6	340.9	342.2	343.5	344.7	345.9	347.1	348.3	349.1
110°	385.0	386.2	387.5	388.8	390.1	391.1	391.9	392.7	393.5	394.3	395.1



TEST NUMBER: P333578-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	433.7	434.4	435.0	435.8	436.5	437.3	438.3	439.3	440.2	441.2	441.6
115°	505.7	506.9	507.9	508.9	510.0	510.7	511.3	511.8	512.3	512.8	512.6
117.5°	578.0	578.6	579.1	579.5	580.0	580.4	580.9	581.4	581.8	582.3	582.5
120°	623.1	624.4	625.7	627.0	628.3	629.1	629.3	629.7	630.0	630.2	630.2
122.5°	672.0	672.5	672.9	673.4	673.8	674.4	675.1	675.8	676.4	677.1	676.9
125°	738.1	739.7	741.2	742.9	744.4	745.3	745.6	745.8	746.1	746.4	745.8
127.5°	808.6	809.4	810.3	811.2	812.1	812.7	813.0	813.3	813.6	814.0	813.6
130°	850.8	852.1	853.4	854.7	856.0	857.0	857.5	858.0	858.5	859.0	858.8
132.5°	893.0	895.1	897.4	899.5	901.6	902.6	902.5	902.4	902.3	902.2	901.9
135°	960.0	961.5	963.1	964.6	966.2	967.1	967.3	967.7	967.9	968.2	968.2
137.5°	1022.8	1024.3	1025.8	1027.3	1028.9	1030.0	1030.5	1031.1	1031.7	1032.2	1032.5
140°	1063.2	1064.5	1065.8	1067.1	1068.4	1069.4	1070.3	1071.1	1071.8	1072.6	1073.1
142.5°	1103.6	1104.7	1105.8	1106.8	1107.9	1109.0	1109.9	1111.0	1112.0	1113.0	1113.3
145°	1163.0	1164.0	1165.1	1166.1	1167.1	1168.0	1168.8	1169.6	1170.3	1171.1	1171.1
147.5°	1217.9	1218.4	1219.0	1219.6	1220.1	1220.7	1221.4	1222.0	1222.6	1223.2	1223.9
150°	1254.5	1254.3	1253.9	1253.7	1253.4	1253.8	1254.9	1255.9	1257.0	1258.0	1258.0
152.5°	1284.5	1284.9	1285.3	1285.7	1286.0	1286.4	1286.8	1287.2	1287.7	1288.1	1288.7
155°	1330.8	1330.8	1330.8	1330.8	1330.8	1330.9	1331.2	1331.4	1331.7	1331.9	1333.0
157.5°	1372.1	1371.5	1370.9	1370.4	1369.8	1369.6	1369.9	1370.2	1370.4	1370.7	1371.7
160°	1396.4	1395.7	1394.9	1394.1	1393.3	1393.1	1393.3	1393.6	1393.9	1394.1	1395.1
162.5°	1418.1	1417.5	1416.9	1416.3	1415.7	1415.5	1415.5	1415.6	1415.6	1415.7	1416.9
165°	1446.9	1446.4	1445.9	1445.4	1444.8	1444.7	1445.0	1445.2	1445.5	1445.7	1446.8
167.5°	1471.4	1470.3	1469.3	1468.2	1467.1	1466.6	1466.6	1466.6	1466.6	1466.6	1468.2
170°	1484.5	1483.5	1482.4	1481.4	1480.4	1479.8	1479.8	1479.8	1479.8	1479.8	1481.4
172.5°	1493.9	1492.9	1491.8	1490.8	1489.8	1489.1	1489.1	1489.1	1489.1	1489.1	1490.8
175°	1504.4	1503.4	1502.4	1501.3	1500.3	1499.8	1499.8	1499.8	1499.8	1499.8	1501.3
177.5°	1509.8	1509.0	1508.1	1507.3	1506.5	1506.0	1505.8	1505.6	1505.3	1505.1	1506.4
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333578-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	16.9	17.2	17.4	17.5	17.5	17.5	17.4	17.4
90°	21.4	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	48.5	50.2	51.9	53.1	53.6	54.2	54.8	55.3
95°	94.0	95.8	97.7	98.9	99.4	99.9	100.4	100.9
97.5°	147.3	149.1	150.8	151.8	152.1	152.4	152.7	153.0
100°	184.2	186.6	188.9	190.4	190.9	191.4	192.0	192.5
102.5°	222.2	224.8	227.3	228.9	229.7	230.5	231.2	231.9
105°	283.6	285.2	286.7	287.9	288.7	289.4	290.2	291.0
107.5°	349.8	350.6	351.4	351.8	351.7	351.7	351.6	351.5
110°	395.9	396.7	397.4	397.7	397.4	397.2	396.9	396.7



TEST NUMBER: P333578-840

CATALOG NUMBER: S125RDIP-S850D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	442.0	442.3	442.7	442.6	442.2	441.7	441.2	440.8
115°	512.3	512.0	511.8	511.5	511.3	511.0	510.7	510.5
117.5°	582.7	582.9	583.1	582.7	581.7	580.7	579.6	578.6
120°	630.2	630.2	630.2	629.7	628.6	627.5	626.5	625.5
122.5°	676.7	676.5	676.3	675.8	674.9	674.1	673.3	672.5
125°	745.3	744.8	744.3	743.9	743.7	743.4	743.1	742.9
127.5°	813.4	813.1	812.9	812.5	812.0	811.4	810.9	810.4
130°	858.5	858.2	858.0	857.6	857.1	856.6	856.0	855.5
132.5°	901.7	901.4	901.1	900.7	899.9	899.2	898.5	897.8
135°	968.2	968.2	968.2	967.7	966.5	965.5	964.5	963.4
137.5°	1032.9	1033.2	1033.5	1033.0	1031.7	1030.4	1029.1	1027.7
140°	1073.6	1074.2	1074.7	1074.3	1073.0	1071.7	1070.4	1069.0
142.5°	1113.6	1113.9	1114.2	1113.7	1112.4	1111.2	1109.8	1108.5
145°	1171.1	1171.1	1171.1	1170.7	1170.0	1169.2	1168.4	1167.6
147.5°	1224.6	1225.2	1225.8	1225.2	1223.5	1221.6	1219.9	1218.1
150°	1258.0	1258.0	1258.0	1257.8	1257.2	1256.7	1256.2	1255.7
152.5°	1289.3	1289.9	1290.5	1290.4	1289.5	1288.5	1287.6	1286.7
155°	1334.0	1335.0	1336.2	1336.0	1334.6	1333.3	1332.1	1330.8
157.5°	1372.7	1373.8	1374.8	1374.5	1372.8	1371.1	1369.4	1367.7
160°	1396.2	1397.2	1398.3	1398.2	1396.8	1395.5	1394.2	1393.0
162.5°	1418.3	1419.5	1420.8	1420.6	1419.1	1417.5	1416.0	1414.5
165°	1447.8	1448.9	1450.0	1449.7	1448.1	1446.5	1445.0	1443.4
167.5°	1469.8	1471.4	1472.9	1472.9	1471.3	1469.7	1468.0	1466.4
170°	1482.9	1484.5	1486.0	1485.9	1484.1	1482.3	1480.5	1478.6
172.5°	1492.3	1493.9	1495.4	1495.4	1493.8	1492.2	1490.6	1488.9
175°	1502.9	1504.4	1506.0	1505.9	1504.1	1502.3	1500.4	1498.5
177.5°	1507.6	1508.9	1510.2	1510.1	1508.6	1507.1	1505.7	1504.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)